

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: METALUX

Report Number: P1433622

Luminaire Tested: EHBR1-48-UNV-N-L935-UPL24

Issue Date: 3/20/2026

Test Information

Test Method: LM-79-2019
Report Number: P1433622
REPORT IS A COMBINATION OF REPORTS P1431847 AND P1431635
Test Lab: INNOVATION CENTER
Issue Date: 3/20/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: METALUX
Catalog Number: EHBR1-48-UNV-N-L935-UPL24
Description: Elevate Round Highbay at, 49000 lumens, 3500K 90CRI LEDs with N lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 45751.2 lumens
Efficiency: N/A
Efficacy: 166.3 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.8
Luminous Opening: Vertical Cylinder (Dia: 1.71' x H: 0.1')
CIE Type: Direct

Input Watts (W): 275.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1433622
CATALOG NUMBER: EHBR1-48-UNV-N-L935-UPL24

Luminous Intensity Polar Plot





TEST NUMBER: P1433622

CATALOG NUMBER: EHBR1-48-UNV-N-L935-UPL24

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	118	118	118	118	115	115	115	115	109	109	109	103	103	103	98	98	98	98	98	98	95
1	111	108	105	102	108	105	103	100	100	98	96	96	94	92	92	90	89	89	89	89	87
2	105	99	94	90	102	97	92	89	93	89	86	89	86	84	85	83	81	81	81	81	79
3	98	91	85	81	96	89	84	80	86	82	78	83	79	76	80	77	74	74	74	74	73
4	93	84	78	73	91	83	77	73	80	75	71	77	73	70	75	72	69	69	69	69	67
5	88	79	72	67	86	77	71	67	75	70	66	73	68	65	71	67	64	64	64	64	62
6	83	73	67	62	81	72	66	62	70	65	61	68	64	60	67	63	59	59	59	59	58
7	79	69	62	58	77	68	62	57	66	61	57	64	60	56	63	59	56	56	56	56	54
8	75	65	58	54	73	64	58	54	62	57	53	61	56	53	60	55	52	52	52	52	51
9	71	61	55	51	70	60	54	50	59	54	50	58	53	49	57	52	49	49	49	49	48
10	68	58	52	48	67	57	51	47	56	51	47	55	50	47	54	49	46	46	46	46	45

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	238975	238975	238975
5°	234335	234335	234335
10°	222412	222412	222412
15°	202365	202365	202365
20°	173585	173585	173585
25°	136552	136552	136552
30°	93710	93710	93710
35°	55667	55667	55667
40°	32937	32937	32937
45°	23643	23643	23643
50°	19434	19434	19434
55°	17663	17663	17663
60°	16908	16908	16908
65°	16127	16127	16127
70°	14998	14998	14998
75°	13558	13558	13558
80°	11253	11253	11253
85°	7125	7125	7125

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 23643 cd/sqm



TEST NUMBER: P1433622

CATALOG NUMBER: EHBR1-48-UNV-N-L935-UPL24

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	4687.6	10.2
10°-20°	11766.6	25.7
20°-30°	12303.2	26.9
30°-40°	6666.2	14.6
40°-50°	3066.8	6.7
50°-60°	2161.2	4.7
60°-70°	1663.2	3.6
70°-80°	1008.3	2.2
80°-90°	287.8	0.6
90°-100°	61.2	0.1
100°-110°	382.3	0.8
110°-120°	683.7	1.5
120°-130°	401.2	0.9
130°-140°	246.1	0.5
140°-150°	170.7	0.4
150°-160°	110.9	0.2
160°-170°	63.2	0.1
170°-180°	20.9	0.0
0°-30°	28757.4	62.9
0°-40°	35423.7	77.4
0°-60°	40651.7	88.9
0°-90°	43611.0	95.3
90°-120°	1127.2	2.5
90°-150°	1945.2	4.3
90°-180°	2140.0	4.7
0°-180°	45751.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	50888	50888	50888	50888	50888	
5°	50034	50034	50034	50034	50034	4688
15°	42455	42455	42455	42455	42455	11767
25°	27269	27269	27269	27269	27269	12303
35°	10217	10217	10217	10217	10217	6666
45°	3825	3825	3825	3825	3825	3067
55°	2387	2387	2387	2387	2387	2161
65°	1683	1683	1683	1683	1683	1663
75°	955	955	955	955	955	1008
85°	245	245	245	245	245	272
90°	17	27	46	30	17	20
95°	27	45	99	49	31	26
105°	134	263	672	290	176	179
115°	615	647	795	762	757	566
125°	444	414	425	431	484	404
135°	323	314	325	305	304	253
145°	266	262	278	274	273	168
155°	233	230	241	241	241	109
165°	218	218	224	224	223	62
175°	216	216	219	219	219	21
180°	218	218	218	218	218	



TEST NUMBER: P1433622

CATALOG NUMBER: EHBR1-48-UNV-N-L935-UPL24

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	50888.0	50888.0	50888.0	50888.0	50888.0
2.5°	50707.5	50707.5	50707.5	50707.5	50707.5
5°	50034.3	50034.3	50034.3	50034.3	50034.3
7.5°	48885.0	48885.0	48885.0	48885.0	48885.0
10°	47254.5	47254.5	47254.5	47254.5	47254.5
12.5°	45147.3	45147.3	45147.3	45147.3	45147.3
15°	42455.2	42455.2	42455.2	42455.2	42455.2
17.5°	39331.9	39331.9	39331.9	39331.9	39331.9
20°	35676.8	35676.8	35676.8	35676.8	35676.8
22.5°	31607.2	31607.2	31607.2	31607.2	31607.2
25°	27269.4	27269.4	27269.4	27269.4	27269.4
27.5°	22670.8	22670.8	22670.8	22670.8	22670.8
30°	18025.0	18025.0	18025.0	18025.0	18025.0
32.5°	13833.6	13833.6	13833.6	13833.6	13833.6
35°	10216.9	10216.9	10216.9	10216.9	10216.9
37.5°	7501.6	7501.6	7501.6	7501.6	7501.6
40°	5708.8	5708.8	5708.8	5708.8	5708.8
42.5°	4577.6	4577.6	4577.6	4577.6	4577.6
45°	3825.4	3825.4	3825.4	3825.4	3825.4
47.5°	3283.4	3283.4	3283.4	3283.4	3283.4
50°	2896.4	2896.4	2896.4	2896.4	2896.4
52.5°	2613.9	2613.9	2613.9	2613.9	2613.9
55°	2387.0	2387.0	2387.0	2387.0	2387.0
57.5°	2202.9	2202.9	2202.9	2202.9	2202.9
60°	2032.6	2032.6	2032.6	2032.6	2032.6
62.5°	1862.3	1862.3	1862.3	1862.3	1862.3
65°	1683.3	1683.3	1683.3	1683.3	1683.3
67.5°	1500.8	1500.8	1500.8	1500.8	1500.8
70°	1316.0	1316.0	1316.0	1316.0	1316.0
72.5°	1136.3	1136.3	1136.3	1136.3	1136.3
75°	955.1	955.1	955.1	955.1	955.1
77.5°	777.5	777.5	777.5	777.5	777.5
80°	592.0	592.0	592.0	592.0	592.0
82.5°	414.5	414.5	414.5	414.5	414.5
85°	244.9	244.9	244.9	244.9	244.9
87.5°	87.6	87.6	87.6	87.6	87.6
90°	17.4	27.2	45.6	29.6	17.4
92.5°	23.3	39.2	71.1	36.7	20.8
95°	26.9	45.3	99.2	49.0	30.6
97.5°	34.3	50.2	113.9	60.0	47.8
100°	45.3	58.8	177.6	73.5	63.7
102.5°	77.1	125.0	377.3	138.4	96.8
105°	133.5	263.4	672.5	290.3	176.4
107.5°	231.5	471.7	886.8	514.5	334.4
110°	432.4	625.9	929.7	706.8	535.3



TEST NUMBER: P1433622

CATALOG NUMBER: EHBR1-48-UNV-N-L935-UPL24

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	584.3	672.5	890.6	780.3	697.0
115°	614.9	646.8	795.0	762.0	757.1
117.5°	594.1	590.5	674.9	684.7	731.3
120°	550.1	525.5	563.5	597.8	660.3
122.5°	494.9	465.5	482.6	508.4	570.8
125°	443.5	414.0	425.1	431.2	483.9
127.5°	398.2	378.5	384.6	377.3	410.4
130°	367.5	350.3	358.9	341.8	357.7
132.5°	341.8	330.7	340.5	319.8	324.6
135°	323.4	313.6	324.6	305.0	303.8
137.5°	307.4	298.9	309.9	295.2	291.6
140°	292.7	285.4	297.6	286.7	284.2
142.5°	276.9	271.9	286.7	279.3	276.9
145°	265.8	262.1	278.1	274.4	273.2
147.5°	256.0	253.6	268.3	267.0	267.0
150°	247.4	245.0	259.7	258.5	259.7
152.5°	238.9	236.5	249.9	248.7	249.9
155°	232.7	230.3	241.4	241.4	241.4
157.5°	227.9	226.6	235.2	235.2	235.2
160°	224.1	223.0	230.3	230.3	229.0
162.5°	220.5	219.2	227.9	226.6	226.6
165°	218.1	218.1	224.1	224.1	223.0
167.5°	218.1	216.8	223.0	223.0	221.7
170°	216.8	216.8	221.7	220.5	219.2
172.5°	216.8	216.8	221.7	220.5	219.2
175°	215.6	215.6	219.2	219.2	219.2
177.5°	216.8	216.8	219.2	219.2	218.1
180°	218.1	218.1	218.1	218.1	218.1



TEST NUMBER: P1433622
 CATALOG NUMBER: EHBR1-48-UNV-N-L935-UPL24

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.07	19.17	18.53	19.58	20.02	18.07	19.17	18.53	19.58	20.02
	3H	19.85	20.83	20.32	21.26	21.74	19.85	20.83	20.32	21.26	21.74
	4H	20.51	21.42	21.00	21.87	22.37	20.51	21.42	21.00	21.87	22.37
	6H	20.97	21.80	21.47	22.27	22.78	20.97	21.80	21.47	22.27	22.78
	8H	21.10	21.88	21.61	22.37	22.89	21.10	21.88	21.61	22.37	22.89
	12H	21.15	21.90	21.67	22.38	22.92	21.15	21.90	21.67	22.38	22.92
4H	2H	18.62	19.52	19.11	19.97	20.47	18.62	19.52	19.11	19.97	20.47
	3H	20.59	21.34	21.09	21.83	22.35	20.59	21.34	21.09	21.83	22.35
	4H	21.36	22.03	21.88	22.54	23.10	21.36	22.03	21.88	22.54	23.10
	6H	21.93	22.51	22.48	23.05	23.62	21.93	22.51	22.48	23.05	23.62
	8H	22.09	22.63	22.64	23.16	23.75	22.09	22.63	22.64	23.16	23.75
	12H	22.17	22.65	22.74	23.21	23.80	22.17	22.65	22.74	23.21	23.80
8H	4H	21.59	22.13	22.14	22.66	23.25	21.59	22.13	22.14	22.66	23.25
	6H	22.27	22.71	22.86	23.29	23.88	22.27	22.71	22.86	23.29	23.88
	8H	22.50	22.88	23.10	23.48	24.08	22.50	22.88	23.10	23.48	24.08
	12H	22.64	22.97	23.23	23.55	24.23	22.64	22.97	23.23	23.55	24.23
12H	4H	21.59	22.06	22.16	22.63	23.21	21.59	22.06	22.16	22.63	23.21
	6H	22.30	22.69	22.90	23.28	23.88	22.30	22.69	22.90	23.28	23.88
	8H	22.56	22.90	23.16	23.48	24.16	22.56	22.90	23.16	23.48	24.16

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2506-472-6

Test Date: 08/01/2025

Luminaire Tested: EHBR-60-L935-N

Data in this report applies to families of products including EHBR-60-L935-N

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2506-472-6
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 08/05/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Metalux
 Catalog Number: **EHBR-60-L935-N**
 Description: Elevate Round Highbay at, 60000 lumens, 3500K 90CRI LEDs with N lens

Spectral Parameters

CCT (K): 3406
 CIE u': 0.2394
 CIE v': 0.5094
 Duv: -0.0028
 CIE x: 0.4076
 CIE y: 0.3856
 CIE z: 0.2068
 Peak Wavelength (nm): 630
 Dominant Wavelength (nm): 582
 Purity: 38.0517
 Rf: 91.3
 Rg: 100

CRI (Ra): 94.6
 R1: 96.6
 R2: 98.4
 R3: 98.1
 R4: 95.8
 R5: 96.2
 R6: 95.4
 R7: 91.8
 R8: 84.4
 R9: 63.8
 R10: 94.7
 R11: 96.6
 R12: 80.9
 R13: 97.4
 R14: 98.3
 R15: 93.1



Test Conditions

Stabilization Time: 35M
 Operation Time: 1H 35M
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP1-2506-472-6

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2506-472-6

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2506-472-6

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)
360	0	NR	490	140	NR	620	338	NR	750	8	NR	880	0	NR
365	0	NR	495	159	NR	625	339	NR	755	7	NR	885	0	NR
370	0	NR	500	182	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	202	NR	635	653	NR	765	5	NR	895	0	NR
380	0	NR	510	216	NR	640	222	NR	770	4	NR	900	0	NR
385	0	NR	515	228	NR	645	214	NR	775	3	NR	905	0	NR
390	0	NR	520	236	NR	650	185	NR	780	3	NR	910	0	NR
395	1	NR	525	242	NR	655	157	NR	785	3	NR	915	0	NR
400	2	NR	530	248	NR	660	133	NR	790	2	NR	920	0	NR
405	3	NR	535	253	NR	665	113	NR	795	2	NR	925	0	NR
410	4	NR	540	258	NR	670	103	NR	800	2	NR	930	0	NR
415	7	NR	545	264	NR	675	85	NR	805	1	NR	935	0	NR
420	13	NR	550	270	NR	680	72	NR	810	1	NR	940	0	NR
425	22	NR	555	278	NR	685	62	NR	815	1	NR	945	0	NR
430	38	NR	560	286	NR	690	53	NR	820	1	NR	950	0	NR
435	65	NR	565	295	NR	695	45	NR	825	1	NR	955	0	NR
440	108	NR	570	303	NR	700	39	NR	830	1	NR	960	0	NR
445	193	NR	575	311	NR	705	33	NR	835	1	NR	965	0	NR
450	312	NR	580	319	NR	710	28	NR	840	1	NR	970	0	NR
455	300	NR	585	326	NR	715	24	NR	845	0	NR	975	0	NR
460	214	NR	590	332	NR	720	20	NR	850	0	NR	980	0	NR
465	184	NR	595	333	NR	725	17	NR	855	0	NR	985	0	NR
470	153	NR	600	336	NR	730	15	NR	860	0	NR	990	0	NR
475	122	NR	605	337	NR	735	12	NR	865	0	NR	995	0	NR
480	115	NR	610	367	NR	740	10	NR	870	0	NR	1000	0	NR
485	125	NR	615	390	NR	745	9	NR	875	0	NR			

REPORT NUMBER: SP1-2506-472-6

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.62

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	140	NR	620	338	NR	750	8	NR	880	0	NR
365	0	NR	495	159	NR	625	339	NR	755	7	NR	885	0	NR
370	0	NR	500	182	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	202	NR	635	653	NR	765	5	NR	895	0	NR
380	0	NR	510	216	NR	640	222	NR	770	4	NR	900	0	NR
385	0	NR	515	228	NR	645	214	NR	775	3	NR	905	0	NR
390	0	NR	520	236	NR	650	185	NR	780	3	NR	910	0	NR
395	1	NR	525	242	NR	655	157	NR	785	3	NR	915	0	NR
400	2	NR	530	248	NR	660	133	NR	790	2	NR	920	0	NR
405	3	NR	535	253	NR	665	113	NR	795	2	NR	925	0	NR
410	4	NR	540	258	NR	670	103	NR	800	2	NR	930	0	NR
415	7	NR	545	264	NR	675	85	NR	805	1	NR	935	0	NR
420	13	NR	550	270	NR	680	72	NR	810	1	NR	940	0	NR
425	22	NR	555	278	NR	685	62	NR	815	1	NR	945	0	NR
430	38	NR	560	286	NR	690	53	NR	820	1	NR	950	0	NR
435	65	NR	565	295	NR	695	45	NR	825	1	NR	955	0	NR
440	108	NR	570	303	NR	700	39	NR	830	1	NR	960	0	NR
445	193	NR	575	311	NR	705	33	NR	835	1	NR	965	0	NR
450	312	NR	580	319	NR	710	28	NR	840	1	NR	970	0	NR
455	300	NR	585	326	NR	715	24	NR	845	0	NR	975	0	NR
460	214	NR	590	332	NR	720	20	NR	850	0	NR	980	0	NR
465	184	NR	595	333	NR	725	17	NR	855	0	NR	985	0	NR
470	153	NR	600	336	NR	730	15	NR	860	0	NR	990	0	NR
475	122	NR	605	337	NR	735	12	NR	865	0	NR	995	0	NR
480	115	NR	610	367	NR	740	10	NR	870	0	NR	1000	0	NR
485	125	NR	615	390	NR	745	9	NR	875	0	NR			

REPORT NUMBER: SP1-2506-472-6

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 3.3

λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)
360	0	NR	490	140	NR	620	338	NR	750	8	NR	880	0	NR
365	0	NR	495	159	NR	625	339	NR	755	7	NR	885	0	NR
370	0	NR	500	182	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	202	NR	635	653	NR	765	5	NR	895	0	NR
380	0	NR	510	216	NR	640	222	NR	770	4	NR	900	0	NR
385	0	NR	515	228	NR	645	214	NR	775	3	NR	905	0	NR
390	0	NR	520	236	NR	650	185	NR	780	3	NR	910	0	NR
395	1	NR	525	242	NR	655	157	NR	785	3	NR	915	0	NR
400	2	NR	530	248	NR	660	133	NR	790	2	NR	920	0	NR
405	3	NR	535	253	NR	665	113	NR	795	2	NR	925	0	NR
410	4	NR	540	258	NR	670	103	NR	800	2	NR	930	0	NR
415	7	NR	545	264	NR	675	85	NR	805	1	NR	935	0	NR
420	13	NR	550	270	NR	680	72	NR	810	1	NR	940	0	NR
425	22	NR	555	278	NR	685	62	NR	815	1	NR	945	0	NR
430	38	NR	560	286	NR	690	53	NR	820	1	NR	950	0	NR
435	65	NR	565	295	NR	695	45	NR	825	1	NR	955	0	NR
440	108	NR	570	303	NR	700	39	NR	830	1	NR	960	0	NR
445	193	NR	575	311	NR	705	33	NR	835	1	NR	965	0	NR
450	312	NR	580	319	NR	710	28	NR	840	1	NR	970	0	NR
455	300	NR	585	326	NR	715	24	NR	845	0	NR	975	0	NR
460	214	NR	590	332	NR	720	20	NR	850	0	NR	980	0	NR
465	184	NR	595	333	NR	725	17	NR	855	0	NR	985	0	NR
470	153	NR	600	336	NR	730	15	NR	860	0	NR	990	0	NR
475	122	NR	605	337	NR	735	12	NR	865	0	NR	995	0	NR
480	115	NR	610	367	NR	740	10	NR	870	0	NR	1000	0	NR
485	125	NR	615	390	NR	745	9	NR	875	0	NR			

Summary

$R_f = 91.3$
 $R_g = 100$
 $CIE R_a = 94.6$
 $R_9 = 63.8$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 94	CES51 = 97	CES76 = 90
CES02 = 63	CES27 = 92	CES52 = 98	CES77 = 86
CES03 = 31	CES28 = 97	CES53 = 98	CES78 = 86
CES04 = 70	CES29 = 97	CES54 = 93	CES79 = 90
CES05 = 50	CES30 = 92	CES55 = 92	CES80 = 91
CES06 = 51	CES31 = 97	CES56 = 96	CES81 = 74
CES07 = 43	CES32 = 89	CES57 = 94	CES82 = 96
CES08 = 41	CES33 = 99	CES58 = 95	CES83 = 94
CES09 = 29	CES34 = 94	CES59 = 98	CES84 = 95
CES10 = 75	CES35 = 97	CES60 = 92	CES85 = 79
CES11 = 58	CES36 = 81	CES61 = 93	CES86 = 79
CES12 = 64	CES37 = 96	CES62 = 86	CES87 = 92
CES13 = 44	CES38 = 87	CES63 = 94	CES88 = 98
CES14 = 74	CES39 = 99	CES64 = 91	CES89 = 84
CES15 = 72	CES40 = 97	CES65 = 90	CES90 = 96
CES16 = 48	CES41 = 96	CES66 = 89	CES91 = 75
CES17 = 49	CES42 = 94	CES67 = 88	CES92 = 76
CES18 = 56	CES43 = 93	CES68 = 89	CES93 = 86
CES19 = 71	CES44 = 99	CES69 = 90	CES94 = 74
CES20 = 67	CES45 = 97	CES70 = 88	CES95 = 83
CES21 = 86	CES46 = 97	CES71 = 83	CES96 = 92
CES22 = 78	CES47 = 91	CES72 = 94	CES97 = 96
CES23 = 91	CES48 = 91	CES73 = 83	CES98 = 95
CES24 = 90	CES49 = 96	CES74 = 90	CES99 = 92
CES25 = 71	CES50 = 98	CES75 = 85	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)