

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: METALUX

Report Number: P1433456

Luminaire Tested: EHBR1-18-UNV-ASM-L935-UPL36

Issue Date: 3/20/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1433456  
REPORT IS A COMBINATION OF REPORTS P1431681 AND P1431635  
Test Lab: INNOVATION CENTER  
Issue Date: 3/20/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: METALUX  
Catalog Number: EHBR1-18-UNV-ASM-L935-UPL36  
Description: Elevate Round Highbay at, 19000 lumens, 3500K 90CRI LEDs with ASM lens  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 19970.1 lumens  
Efficiency: N/A  
Efficacy: 162.2 lumens/watt  
Spacing Criteria (0/90/45): 0.84 / 0.99 / 0.92  
Luminous Opening: Vertical Cylinder (Dia: 1.71' x H: 0.1')  
CIE Type: Semi-Direct

Input Watts (W): 123.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1433456  
CATALOG NUMBER: EHBR1-18-UNV-ASM-L935-UPL36

### Luminous Intensity Polar Plot





TEST NUMBER: P1433456

CATALOG NUMBER: EHBR1-18-UNV-ASM-L935-UPL36

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	115	115	115	115	110	110	110	110	102	102	102	94	94	94	87	87	87	87	87	87	83
1	108	104	101	98	103	100	98	95	93	91	89	87	85	83	81	79	78	78	78	78	75
2	101	95	89	85	97	91	87	83	85	82	79	80	77	74	75	72	71	71	71	71	68
3	94	86	80	75	91	84	78	74	78	74	70	74	70	67	69	66	64	64	64	64	62
4	88	79	72	67	85	77	71	66	72	67	63	68	64	61	65	61	59	59	59	59	56
5	83	73	66	61	80	71	65	60	67	62	58	64	59	56	60	57	54	54	54	54	52
6	78	67	60	55	75	66	59	55	62	57	53	59	55	51	56	53	50	50	50	50	48
7	73	63	56	51	71	61	55	50	58	53	49	56	51	47	53	49	46	46	46	46	44
8	69	58	52	47	67	57	51	46	55	49	45	52	47	44	50	46	43	43	43	43	41
9	65	55	48	43	63	53	47	43	51	46	42	49	44	41	47	43	40	40	40	40	38
10	62	51	45	40	60	50	44	40	48	43	39	46	42	38	44	40	37	37	37	37	36

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°	135°	180°
0°	69856	69856	69856	69856	69856
5°	65828	66597	69431	72761	74070
10°	62301	63620	68578	75098	75972
15°	57549	59086	66553	74327	70601
20°	51260	52987	62243	68321	56613
25°	42958	44584	55091	57306	39225
30°	32141	34005	44732	44285	25518
35°	21397	22689	32083	31565	16526
40°	13494	14421	20742	20876	11391
45°	9615	10014	13161	13727	8823
50°	8008	8073	9774	10028	7498
55°	7070	7086	7980	8190	6830
60°	6546	6490	6910	7056	6507
65°	6248	6192	6299	6422	6274
70°	6069	5964	5971	6085	6147
75°	5769	5596	5583	5780	5948
80°	5250	4883	4904	5250	5615
85°	3823	3171	3171	3628	4009

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 112.5°  
 Vertical Angle: 45°  
 Luminance: 18504 cd/sqm



TEST NUMBER: P1433456  
 CATALOG NUMBER: EHBR1-18-UNV-ASM-L935-UPL36

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1414.4	7.1
10°-20°	3848.0	19.3
20°-30°	4513.0	22.6
30°-40°	3138.5	15.7
40°-50°	1559.7	7.8
50°-60°	932.9	4.7
60°-70°	656.6	3.3
70°-80°	423.0	2.1
80°-90°	140.2	0.7
90°-100°	88.6	0.4
100°-110°	582.6	2.9
110°-120°	1077.1	5.4
120°-130°	639.5	3.2
130°-140°	385.9	1.9
140°-150°	266.2	1.3
150°-160°	172.9	0.9
160°-170°	98.5	0.5
170°-180°	32.5	0.2
0°-30°	9775.4	49.0
0°-40°	12913.9	64.7
0°-60°	15406.4	77.1
0°-90°	16626.2	83.3
90°-120°	1748.4	8.8
90°-150°	3040.0	15.2
90°-180°	3344.0	16.7
0°-180°	19970.1	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	14875	14875	14875	14875	14875	
5°	14055	14220	14825	15536	15815	1318
15°	12074	12396	13962	15593	14812	3367
25°	8579	8903	11002	11444	7833	3871
35°	3927	4164	5888	5793	3033	2502
45°	1556	1620	2129	2221	1428	1257
55°	955	958	1078	1107	923	867
65°	652	646	658	670	655	648
75°	406	394	393	407	419	429
85°	131	109	109	125	138	135
90°	24	67	24	71	26	18
95°	41	150	47	129	43	40
105°	203	1018	268	1086	134	271
115°	931	1204	1146	1332	978	858
125°	672	644	733	714	767	612
135°	490	493	462	516	533	384
145°	405	424	417	427	436	257
155°	358	370	370	370	385	167
165°	338	346	345	344	354	96
175°	336	341	342	339	346	32
180°	340	340	340	340	340	



TEST NUMBER: P1433456  
 CATALOG NUMBER: EHBR1-18-UNV-ASM-L935-UPL36

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	14875.4	14875.4	14875.4	14875.4	14875.4	14875.4	14875.4	14875.4	14875.4
2.5°	14433.8	14443.4	14544.3	14675.7	14866.7	15058.9	15214.6	15317.2	15368.0
5°	14055.4	14107.8	14219.6	14460.9	14824.7	15209.6	15535.7	15749.0	15815.1
7.5°	13686.6	13716.9	13904.2	14209.0	14724.0	15323.7	15808.2	16057.3	16118.1
10°	13236.7	13305.6	13517.0	13876.5	14570.3	15395.6	15955.5	16133.9	16141.2
12.5°	12707.2	12798.5	13016.9	13470.4	14325.1	15370.0	15906.1	15847.5	15714.4
15°	12073.5	12153.5	12396.0	12922.0	13962.5	15217.9	15593.4	15116.7	14811.8
17.5°	11388.9	11461.5	11672.1	12251.4	13451.5	14933.4	14940.7	13997.6	13422.4
20°	10535.5	10592.4	10890.3	11458.7	12792.8	14477.1	14042.0	12317.0	11635.6
22.5°	9627.2	9680.5	9945.2	10536.8	11967.2	13861.8	12790.3	10626.4	9696.6
25°	8578.7	8607.7	8903.3	9438.3	11001.6	13107.8	11444.0	8784.2	7833.1
27.5°	7399.1	7448.4	7757.8	8304.2	9865.7	12152.2	10010.2	7178.1	6300.6
30°	6182.3	6264.1	6540.8	7030.0	8604.1	10927.1	8518.1	5716.5	4908.4
32.5°	5046.8	5105.6	5302.8	5814.1	7191.5	9726.3	7085.2	4580.4	3896.0
35°	3927.1	3986.0	4164.2	4666.3	5888.3	8223.9	5793.3	3599.1	3033.1
37.5°	3001.9	3106.0	3220.3	3627.9	4621.1	6804.4	4618.1	2898.2	2460.2
40°	2338.9	2355.6	2499.6	2760.3	3595.2	5320.4	3618.3	2313.5	1974.3
42.5°	1872.2	1917.7	1979.6	2174.8	2724.1	4068.2	2844.1	1898.8	1677.0
45°	1555.6	1573.5	1620.3	1751.5	2129.4	2993.8	2220.9	1601.9	1427.6
47.5°	1360.9	1353.2	1383.2	1481.4	1734.2	2313.8	1800.0	1374.0	1251.8
50°	1193.5	1188.8	1203.1	1268.6	1456.6	1775.4	1494.5	1199.4	1117.4
52.5°	1063.6	1067.7	1069.2	1109.9	1251.3	1448.0	1272.8	1068.9	1013.6
55°	955.4	960.6	957.6	987.7	1078.4	1217.3	1106.8	961.3	923.0
57.5°	870.8	866.9	862.7	879.0	947.0	1032.6	961.3	869.4	844.1
60°	786.9	783.3	780.2	790.8	830.7	894.3	848.2	789.4	782.2
62.5°	714.9	712.6	712.4	710.5	741.1	781.3	750.1	717.5	711.0
65°	652.2	649.7	646.3	643.2	657.5	694.8	670.3	652.7	654.9
67.5°	589.4	589.4	583.5	578.8	592.7	612.2	601.6	591.7	594.1
70°	532.5	532.7	523.3	519.7	523.9	544.8	533.9	535.3	539.4
72.5°	471.4	464.7	457.7	457.4	458.0	474.2	470.6	473.9	478.4
75°	406.4	398.6	394.2	389.1	393.3	405.6	407.2	412.0	419.0
77.5°	343.7	331.6	328.0	325.6	322.7	336.7	342.0	348.4	358.7
80°	276.2	263.0	256.9	253.3	258.0	264.5	276.2	280.9	295.4
82.5°	204.2	194.4	186.9	186.6	188.9	194.7	204.7	213.6	222.1
85°	131.4	115.7	109.0	111.6	109.0	118.0	124.7	135.3	137.8
87.5°	47.4	37.1	35.4	39.1	38.2	41.0	46.9	51.0	51.3
90°	24.4	39.2	67.0	42.9	24.4	41.3	71.2	38.7	26.4
92.5°	35.5	59.6	107.8	55.9	31.8	56.2	101.0	51.7	35.6
95°	41.1	68.9	150.5	74.4	46.9	69.2	128.7	57.3	43.1
97.5°	52.5	76.3	172.7	91.1	72.9	85.8	145.4	61.0	52.3
100°	69.2	89.3	269.1	111.8	97.0	97.0	265.9	70.2	59.7
102.5°	117.4	189.3	571.3	210.0	147.0	189.9	616.6	141.0	72.7
105°	202.6	398.9	1018.0	439.9	267.5	434.6	1085.6	365.3	134.1
107.5°	350.9	714.0	1342.7	779.2	506.6	810.9	1398.8	721.3	314.0
110°	654.9	947.6	1407.6	1070.2	810.6	1133.5	1526.8	988.3	636.5



TEST NUMBER: P1433456

CATALOG NUMBER: EHBR1-18-UNV-ASM-L935-UPL36

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
112.5°	884.8	1018.0	1348.3	1181.4	1055.3	1263.2	1491.5	1095.8	881.2
115°	931.2	979.1	1203.7	1153.6	1146.5	1244.8	1332.1	1092.0	977.7
117.5°	899.6	893.8	1022.0	1037.1	1107.5	1139.1	1150.4	1025.3	983.2
120°	832.9	795.6	853.3	905.5	1000.0	987.1	969.0	927.1	927.6
122.5°	749.4	705.0	731.2	770.4	865.0	837.2	818.9	827.2	851.6
125°	671.9	627.1	644.4	653.9	733.3	705.6	713.5	741.9	766.6
127.5°	603.3	573.3	583.2	572.3	622.4	609.4	637.5	669.6	690.5
130°	556.9	531.0	544.5	518.9	543.0	546.3	583.8	610.6	623.8
132.5°	518.3	501.7	517.3	486.1	493.2	507.7	543.3	566.4	574.1
135°	490.5	475.9	493.2	464.1	462.0	483.6	515.8	530.8	533.3
137.5°	466.7	454.0	471.6	449.5	443.7	465.4	489.8	501.5	498.0
140°	445.1	434.2	453.3	436.6	432.9	454.6	465.7	479.3	476.1
142.5°	421.5	414.1	436.9	425.8	422.1	441.9	447.5	457.2	453.8
145°	405.4	399.8	424.2	418.4	416.7	431.3	427.3	440.6	435.6
147.5°	391.1	387.4	409.6	407.5	407.5	418.4	412.7	424.2	419.2
150°	378.7	374.9	396.9	394.8	396.6	404.0	396.3	409.6	408.3
152.5°	366.2	362.3	382.4	380.2	382.1	389.5	382.1	397.2	395.6
155°	357.5	353.5	369.9	369.3	369.6	373.3	369.6	384.7	385.0
157.5°	350.9	348.6	361.2	360.9	360.9	363.1	361.2	374.5	374.8
160°	345.9	343.9	354.6	354.4	352.8	356.6	354.9	366.3	366.6
162.5°	341.0	338.8	351.5	349.7	349.7	349.7	348.4	359.7	360.3
165°	337.8	337.5	346.5	346.5	344.9	346.8	343.6	351.6	354.0
167.5°	337.8	335.9	345.2	345.2	343.6	341.8	342.3	348.8	351.2
170°	336.4	336.2	343.6	342.0	340.1	340.4	339.2	345.6	348.0
172.5°	337.0	336.7	344.4	342.6	341.1	341.1	338.2	342.7	346.9
175°	335.8	335.5	341.3	341.3	341.6	340.1	338.7	341.4	345.7
177.5°	337.9	337.6	341.3	341.3	339.8	340.3	340.9	343.5	349.7
180°	340.3	340.3	340.3	340.3	340.3	340.3	340.3	340.3	340.3



TEST NUMBER: P1433456  
 CATALOG NUMBER: EHBR1-18-UNV-ASM-L935-UPL36

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.91	14.90	14.55	15.52	16.23	14.68	15.66	15.31	16.28	16.99
	3H	15.72	16.60	16.37	17.23	17.98	16.23	17.11	16.88	17.74	18.49
	4H	16.46	17.27	17.12	17.92	18.69	16.88	17.69	17.54	18.34	19.11
	6H	17.02	17.77	17.70	18.43	19.21	17.37	18.12	18.05	18.78	19.55
	8H	17.20	17.91	17.89	18.59	19.37	17.52	18.23	18.21	18.91	19.69
	12H	17.30	17.98	17.99	18.65	19.45	17.60	18.28	18.29	18.95	19.75
4H	2H	14.42	15.24	15.09	15.89	16.65	15.05	15.87	15.72	16.52	17.28
	3H	16.45	17.13	17.13	17.82	18.60	16.85	17.53	17.53	18.22	18.99
	4H	17.31	17.93	18.01	18.62	19.43	17.63	18.25	18.33	18.94	19.75
	6H	18.01	18.53	18.72	19.25	20.07	18.27	18.79	18.98	19.51	20.33
	8H	18.23	18.72	18.95	19.44	20.27	18.47	18.96	19.19	19.67	20.51
	12H	18.36	18.80	19.10	19.54	20.37	18.58	19.02	19.32	19.76	20.59
8H	4H	17.57	18.06	18.29	18.77	19.61	17.87	18.36	18.59	19.08	19.91
	6H	18.38	18.78	19.13	19.54	20.38	18.64	19.04	19.39	19.79	20.63
	8H	18.69	19.04	19.45	19.80	20.65	18.92	19.27	19.68	20.04	20.89
	12H	18.88	19.19	19.65	19.94	20.86	19.10	19.41	19.86	20.16	21.07
12H	4H	17.57	18.01	18.31	18.75	19.58	17.88	18.31	18.62	19.05	19.89
	6H	18.42	18.78	19.19	19.54	20.39	18.68	19.04	19.45	19.80	20.65
	8H	18.77	19.08	19.53	19.82	20.74	19.01	19.32	19.77	20.06	20.98

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2506-472-6

Test Date: 08/01/2025

Luminaire Tested: EHBR-60-L935-N

Data in this report applies to families of products including EHBR-60-L935-N


**Test Information**

Test Method: LM-79-2019  
 Report Number: SP1-2506-472-6  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry: 4π  
 Issue Date: 08/05/2025  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: Metalux  
 Catalog Number: **EHBR-60-L935-N**  
 Description: Elevate Round Highbay at, 60000 lumens, 3500K 90CRI LEDs with N lens

**Spectral Parameters**

CCT (K): 3406  
 CIE u': 0.2394  
 CIE v': 0.5094  
 Duv: -0.0028  
 CIE x: 0.4076  
 CIE y: 0.3856  
 CIE z: 0.2068  
 Peak Wavelength (nm): 630  
 Dominant Wavelength (nm): 582  
 Purity: 38.0517  
 Rf: 91.3  
 Rg: 100

CRI (Ra):	94.6		
R1:	96.6	R9:	63.8
R2:	98.4	R10:	94.7
R3:	98.1	R11:	96.6
R4:	95.8	R12:	80.9
R5:	96.2	R13:	97.4
R6:	95.4	R14:	98.3
R7:	91.8	R15:	93.1
R8:	84.4		



**Test Conditions**

Stabilization Time: 35M  
 Operation Time: 1H 35M  
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP1-2506-472-6

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2506-472-6

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2506-472-6

**Photopic Flux vs. Wavelength**



**Photopic Lumens: NR**

λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)
360	0	NR	490	140	NR	620	338	NR	750	8	NR	880	0	NR
365	0	NR	495	159	NR	625	339	NR	755	7	NR	885	0	NR
370	0	NR	500	182	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	202	NR	635	653	NR	765	5	NR	895	0	NR
380	0	NR	510	216	NR	640	222	NR	770	4	NR	900	0	NR
385	0	NR	515	228	NR	645	214	NR	775	3	NR	905	0	NR
390	0	NR	520	236	NR	650	185	NR	780	3	NR	910	0	NR
395	1	NR	525	242	NR	655	157	NR	785	3	NR	915	0	NR
400	2	NR	530	248	NR	660	133	NR	790	2	NR	920	0	NR
405	3	NR	535	253	NR	665	113	NR	795	2	NR	925	0	NR
410	4	NR	540	258	NR	670	103	NR	800	2	NR	930	0	NR
415	7	NR	545	264	NR	675	85	NR	805	1	NR	935	0	NR
420	13	NR	550	270	NR	680	72	NR	810	1	NR	940	0	NR
425	22	NR	555	278	NR	685	62	NR	815	1	NR	945	0	NR
430	38	NR	560	286	NR	690	53	NR	820	1	NR	950	0	NR
435	65	NR	565	295	NR	695	45	NR	825	1	NR	955	0	NR
440	108	NR	570	303	NR	700	39	NR	830	1	NR	960	0	NR
445	193	NR	575	311	NR	705	33	NR	835	1	NR	965	0	NR
450	312	NR	580	319	NR	710	28	NR	840	1	NR	970	0	NR
455	300	NR	585	326	NR	715	24	NR	845	0	NR	975	0	NR
460	214	NR	590	332	NR	720	20	NR	850	0	NR	980	0	NR
465	184	NR	595	333	NR	725	17	NR	855	0	NR	985	0	NR
470	153	NR	600	336	NR	730	15	NR	860	0	NR	990	0	NR
475	122	NR	605	337	NR	735	12	NR	865	0	NR	995	0	NR
480	115	NR	610	367	NR	740	10	NR	870	0	NR	1000	0	NR
485	125	NR	615	390	NR	745	9	NR	875	0	NR			

REPORT NUMBER: SP1-2506-472-6

**Scotopic Flux vs. Wavelength**



**Scotopic Lumens: NR**

**S/P: 1.62**

λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)
360	0	NR	490	140	NR	620	338	NR	750	8	NR	880	0	NR
365	0	NR	495	159	NR	625	339	NR	755	7	NR	885	0	NR
370	0	NR	500	182	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	202	NR	635	653	NR	765	5	NR	895	0	NR
380	0	NR	510	216	NR	640	222	NR	770	4	NR	900	0	NR
385	0	NR	515	228	NR	645	214	NR	775	3	NR	905	0	NR
390	0	NR	520	236	NR	650	185	NR	780	3	NR	910	0	NR
395	1	NR	525	242	NR	655	157	NR	785	3	NR	915	0	NR
400	2	NR	530	248	NR	660	133	NR	790	2	NR	920	0	NR
405	3	NR	535	253	NR	665	113	NR	795	2	NR	925	0	NR
410	4	NR	540	258	NR	670	103	NR	800	2	NR	930	0	NR
415	7	NR	545	264	NR	675	85	NR	805	1	NR	935	0	NR
420	13	NR	550	270	NR	680	72	NR	810	1	NR	940	0	NR
425	22	NR	555	278	NR	685	62	NR	815	1	NR	945	0	NR
430	38	NR	560	286	NR	690	53	NR	820	1	NR	950	0	NR
435	65	NR	565	295	NR	695	45	NR	825	1	NR	955	0	NR
440	108	NR	570	303	NR	700	39	NR	830	1	NR	960	0	NR
445	193	NR	575	311	NR	705	33	NR	835	1	NR	965	0	NR
450	312	NR	580	319	NR	710	28	NR	840	1	NR	970	0	NR
455	300	NR	585	326	NR	715	24	NR	845	0	NR	975	0	NR
460	214	NR	590	332	NR	720	20	NR	850	0	NR	980	0	NR
465	184	NR	595	333	NR	725	17	NR	855	0	NR	985	0	NR
470	153	NR	600	336	NR	730	15	NR	860	0	NR	990	0	NR
475	122	NR	605	337	NR	735	12	NR	865	0	NR	995	0	NR
480	115	NR	610	367	NR	740	10	NR	870	0	NR	1000	0	NR
485	125	NR	615	390	NR	745	9	NR	875	0	NR			

REPORT NUMBER: SP1-2506-472-6

**Melanopic Flux vs. Wavelength**



**Melanopic Lumens: NR**

**M/P: 3.3**

λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)
360	0	NR	490	140	NR	620	338	NR	750	8	NR	880	0	NR
365	0	NR	495	159	NR	625	339	NR	755	7	NR	885	0	NR
370	0	NR	500	182	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	202	NR	635	653	NR	765	5	NR	895	0	NR
380	0	NR	510	216	NR	640	222	NR	770	4	NR	900	0	NR
385	0	NR	515	228	NR	645	214	NR	775	3	NR	905	0	NR
390	0	NR	520	236	NR	650	185	NR	780	3	NR	910	0	NR
395	1	NR	525	242	NR	655	157	NR	785	3	NR	915	0	NR
400	2	NR	530	248	NR	660	133	NR	790	2	NR	920	0	NR
405	3	NR	535	253	NR	665	113	NR	795	2	NR	925	0	NR
410	4	NR	540	258	NR	670	103	NR	800	2	NR	930	0	NR
415	7	NR	545	264	NR	675	85	NR	805	1	NR	935	0	NR
420	13	NR	550	270	NR	680	72	NR	810	1	NR	940	0	NR
425	22	NR	555	278	NR	685	62	NR	815	1	NR	945	0	NR
430	38	NR	560	286	NR	690	53	NR	820	1	NR	950	0	NR
435	65	NR	565	295	NR	695	45	NR	825	1	NR	955	0	NR
440	108	NR	570	303	NR	700	39	NR	830	1	NR	960	0	NR
445	193	NR	575	311	NR	705	33	NR	835	1	NR	965	0	NR
450	312	NR	580	319	NR	710	28	NR	840	1	NR	970	0	NR
455	300	NR	585	326	NR	715	24	NR	845	0	NR	975	0	NR
460	214	NR	590	332	NR	720	20	NR	850	0	NR	980	0	NR
465	184	NR	595	333	NR	725	17	NR	855	0	NR	985	0	NR
470	153	NR	600	336	NR	730	15	NR	860	0	NR	990	0	NR
475	122	NR	605	337	NR	735	12	NR	865	0	NR	995	0	NR
480	115	NR	610	367	NR	740	10	NR	870	0	NR	1000	0	NR
485	125	NR	615	390	NR	745	9	NR	875	0	NR			

**Summary**

$R_f = 91.3$   
 $R_g = 100$   
 $CIE R_a = 94.6$   
 $R_9 = 63.8$




**Color Vector Graphics**



**Individual Sample Fidelity Index ( $R_{f,i}$ )**

CES01 = 86	CES26 = 94	CES51 = 97	CES76 = 90
CES02 = 63	CES27 = 92	CES52 = 98	CES77 = 86
CES03 = 31	CES28 = 97	CES53 = 98	CES78 = 86
CES04 = 70	CES29 = 97	CES54 = 93	CES79 = 90
CES05 = 50	CES30 = 92	CES55 = 92	CES80 = 91
CES06 = 51	CES31 = 97	CES56 = 96	CES81 = 74
CES07 = 43	CES32 = 89	CES57 = 94	CES82 = 96
CES08 = 41	CES33 = 99	CES58 = 95	CES83 = 94
CES09 = 29	CES34 = 94	CES59 = 98	CES84 = 95
CES10 = 75	CES35 = 97	CES60 = 92	CES85 = 79
CES11 = 58	CES36 = 81	CES61 = 93	CES86 = 79
CES12 = 64	CES37 = 96	CES62 = 86	CES87 = 92
CES13 = 44	CES38 = 87	CES63 = 94	CES88 = 98
CES14 = 74	CES39 = 99	CES64 = 91	CES89 = 84
CES15 = 72	CES40 = 97	CES65 = 90	CES90 = 96
CES16 = 48	CES41 = 96	CES66 = 89	CES91 = 75
CES17 = 49	CES42 = 94	CES67 = 88	CES92 = 76
CES18 = 56	CES43 = 93	CES68 = 89	CES93 = 86
CES19 = 71	CES44 = 99	CES69 = 90	CES94 = 74
CES20 = 67	CES45 = 97	CES70 = 88	CES95 = 83
CES21 = 86	CES46 = 97	CES71 = 83	CES96 = 92
CES22 = 78	CES47 = 91	CES72 = 94	CES97 = 96
CES23 = 91	CES48 = 91	CES73 = 83	CES98 = 95
CES24 = 90	CES49 = 96	CES74 = 90	CES99 = 92
CES25 = 71	CES50 = 98	CES75 = 85	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)