

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: METALUX

Report Number: P1433915

Luminaire Tested: EHBR1-48-UNV-W-L940-UPL12

Issue Date: 3/20/2026

Test Information

Test Method: LM-79-2019
Report Number: P1433915
REPORT IS A COMBINATION OF REPORTS P1431852 AND P1431635
Test Lab: INNOVATION CENTER
Issue Date: 3/20/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: METALUX
Catalog Number: EHBR1-48-UNV-W-L940-UPL12
Description: Elevate Round Highbay at, 49000 lumens, 4000K 90CRI LEDs with W lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 45156.4 lumens
Efficiency: N/A
Efficacy: 169.8 lumens/watt
Spacing Criteria (0/90/45): 1.54 / 1.54 / 1.31
Luminous Opening: Vertical Cylinder (Dia: 1.71' x H: 0.1')
CIE Type: Direct

Input Watts (W): 266
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1433915
CATALOG NUMBER: EHBR1-48-UNV-W-L940-UPL12

Luminous Intensity Polar Plot





TEST NUMBER: P1433915
 CATALOG NUMBER: EHBR1-48-UNV-W-L940-UPL12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	118	118	118	118	115	115	115	115	110	110	110	105	105	105	100	100	100	100	100	100	98
1	111	107	104	101	108	104	101	99	100	97	95	96	94	92	92	90	89	89	89	89	87
2	103	96	91	86	100	94	89	85	90	86	83	87	84	81	84	81	79	79	79	79	77
3	96	87	80	75	93	85	79	74	82	77	73	79	75	71	76	73	70	70	70	70	68
4	89	79	72	66	87	77	71	65	75	69	64	72	67	63	70	66	62	62	62	62	60
5	83	72	64	59	81	71	63	58	68	62	57	66	61	57	64	60	56	56	56	56	54
6	77	66	58	52	75	65	57	52	63	56	51	61	55	51	59	54	50	50	50	50	48
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	49	45	45	45	45	44
8	67	55	48	43	66	55	47	42	53	47	42	52	46	42	50	45	41	41	41	41	40
9	63	51	44	39	62	50	43	39	49	43	38	48	42	38	47	42	38	38	38	38	36
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	38	35	35	35	35	33

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	86514	86514	86514
5°	87088	87088	87088
10°	90114	90114	90114
15°	95825	95825	95825
20°	103876	103876	103876
25°	112923	112923	112923
30°	118363	118363	118363
35°	112662	112662	112662
40°	89397	89397	89397
45°	55255	55255	55255
50°	31995	31995	31995
55°	24208	24208	24208
60°	20766	20766	20766
65°	18757	18757	18757
70°	17253	17253	17253
75°	15243	15243	15243
80°	12422	12422	12422
85°	7323	7323	7323

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 55255 cd/sqm



TEST NUMBER: P1433915
 CATALOG NUMBER: EHBR1-48-UNV-W-L940-UPL12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1792.4	4.0
10°-20°	5746.3	12.7
20°-30°	10372.3	23.0
30°-40°	12533.8	27.8
40°-50°	7161.0	15.9
50°-60°	3032.9	6.7
60°-70°	1956.2	4.3
70°-80°	1137.4	2.5
80°-90°	303.0	0.7
90°-100°	32.6	0.1
100°-110°	197.0	0.4
110°-120°	351.4	0.8
120°-130°	207.4	0.5
130°-140°	130.2	0.3
140°-150°	93.1	0.2
150°-160°	61.7	0.1
160°-170°	35.8	0.1
170°-180°	11.9	0.0
0°-30°	17911.0	39.7
0°-40°	30444.8	67.4
0°-60°	40638.7	90.0
0°-90°	44035.3	97.5
90°-120°	581.0	1.3
90°-150°	1011.7	2.2
90°-180°	1121.0	2.5
0°-180°	45156.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	18422	18422	18422	18422	18422	
5°	18595	18595	18595	18595	18595	1792
15°	20104	20104	20104	20104	20104	5746
25°	22551	22551	22551	22551	22551	10372
35°	20678	20678	20678	20678	20678	12534
45°	8940	8940	8940	8940	8940	7161
55°	3272	3272	3272	3272	3272	3033
65°	1958	1958	1958	1958	1958	1956
75°	1074	1074	1074	1074	1074	1137
85°	252	252	252	252	252	290
90°	10	15	24	16	10	15
95°	15	25	52	27	17	14
105°	70	136	345	150	92	93
115°	316	333	408	391	389	292
125°	230	214	220	223	250	209
135°	171	166	172	162	161	134
145°	145	144	152	150	149	92
155°	130	129	134	134	134	60
165°	124	124	127	127	126	35
175°	124	124	126	126	126	12
180°	126	126	126	126	126	



TEST NUMBER: P1433915

CATALOG NUMBER: EHBR1-48-UNV-W-L940-UPL12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	18422.5	18422.5	18422.5	18422.5	18422.5
2.5°	18484.3	18484.3	18484.3	18484.3	18484.3
5°	18594.7	18594.7	18594.7	18594.7	18594.7
7.5°	18811.8	18811.8	18811.8	18811.8	18811.8
10°	19146.0	19146.0	19146.0	19146.0	19146.0
12.5°	19580.2	19580.2	19580.2	19580.2	19580.2
15°	20103.5	20103.5	20103.5	20103.5	20103.5
17.5°	20702.6	20702.6	20702.6	20702.6	20702.6
20°	21349.5	21349.5	21349.5	21349.5	21349.5
22.5°	22000.8	22000.8	22000.8	22000.8	22000.8
25°	22550.7	22550.7	22550.7	22550.7	22550.7
27.5°	22846.5	22846.5	22846.5	22846.5	22846.5
30°	22767.0	22767.0	22767.0	22767.0	22767.0
32.5°	22092.1	22092.1	22092.1	22092.1	22092.1
35°	20677.5	20677.5	20677.5	20677.5	20677.5
37.5°	18471.8	18471.8	18471.8	18471.8	18471.8
40°	15494.8	15494.8	15494.8	15494.8	15494.8
42.5°	12127.6	12127.6	12127.6	12127.6	12127.6
45°	8940.1	8940.1	8940.1	8940.1	8940.1
47.5°	6389.9	6389.9	6389.9	6389.9	6389.9
50°	4768.4	4768.4	4768.4	4768.4	4768.4
52.5°	3861.0	3861.0	3861.0	3861.0	3861.0
55°	3271.5	3271.5	3271.5	3271.5	3271.5
57.5°	2840.9	2840.9	2840.9	2840.9	2840.9
60°	2496.4	2496.4	2496.4	2496.4	2496.4
62.5°	2209.4	2209.4	2209.4	2209.4	2209.4
65°	1957.8	1957.8	1957.8	1957.8	1957.8
67.5°	1735.5	1735.5	1735.5	1735.5	1735.5
70°	1513.9	1513.9	1513.9	1513.9	1513.9
72.5°	1293.1	1293.1	1293.1	1293.1	1293.1
75°	1073.8	1073.8	1073.8	1073.8	1073.8
77.5°	862.6	862.6	862.6	862.6	862.6
80°	653.5	653.5	653.5	653.5	653.5
82.5°	448.2	448.2	448.2	448.2	448.2
85°	251.7	251.7	251.7	251.7	251.7
87.5°	79.5	79.5	79.5	79.5	79.5
90°	9.6	14.6	24.0	15.8	9.6
92.5°	12.7	20.8	37.1	19.5	11.4
95°	15.3	24.6	52.2	26.6	17.1
97.5°	19.0	27.1	59.7	32.1	25.9
100°	24.6	31.5	92.2	39.0	34.0
102.5°	40.9	65.3	194.2	72.2	51.0
105°	69.7	136.0	345.0	149.8	91.6
107.5°	119.7	242.4	454.5	264.3	172.4
110°	223.1	322.0	477.2	363.2	275.7



TEST NUMBER: P1433915

CATALOG NUMBER: EHBR1-48-UNV-W-L940-UPL12

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	300.7	345.7	457.2	400.8	358.2
115°	316.4	332.6	408.3	391.4	389.0
117.5°	305.7	303.8	347.0	352.0	375.8
120°	283.2	270.6	290.0	307.5	339.5
122.5°	255.0	240.0	248.7	261.9	293.8
125°	229.5	214.5	220.1	223.2	250.1
127.5°	206.4	196.3	199.5	195.7	212.6
130°	191.4	182.6	187.0	178.2	186.3
132.5°	179.7	174.0	179.1	168.4	171.0
135°	171.1	166.0	171.7	161.6	161.1
137.5°	163.7	159.3	164.9	157.4	155.5
140°	157.6	153.9	160.1	154.6	153.3
142.5°	150.3	147.8	155.3	151.5	150.3
145°	145.3	143.5	151.7	149.7	149.2
147.5°	141.1	139.8	147.4	146.7	146.7
150°	136.8	135.5	143.0	142.4	143.0
152.5°	132.4	131.1	138.0	137.3	138.0
155°	129.9	128.7	134.3	134.3	134.3
157.5°	127.4	126.7	131.2	131.2	131.2
160°	126.2	125.6	129.4	129.4	128.8
162.5°	125.1	124.5	128.8	128.2	128.2
165°	123.8	123.8	127.0	127.0	126.3
167.5°	123.8	123.3	126.3	126.3	125.8
170°	123.3	123.3	125.8	125.1	124.5
172.5°	124.0	124.0	126.5	125.9	125.2
175°	124.1	124.1	126.0	126.0	126.0
177.5°	124.7	124.7	126.0	126.0	125.3
180°	126.1	126.1	126.1	126.1	126.1



TEST NUMBER: P1433915
 CATALOG NUMBER: EHBR1-48-UNV-W-L940-UPL12

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	19.78	21.05	20.19	21.42	21.80	19.78	21.05	20.19	21.42	21.80
	3H	21.29	22.41	21.71	22.80	23.22	21.29	22.41	21.71	22.80	23.22
	4H	21.85	22.90	22.30	23.30	23.75	21.85	22.90	22.30	23.30	23.75
	6H	22.24	23.20	22.70	23.62	24.08	22.24	23.20	22.70	23.62	24.08
	8H	22.34	23.25	22.81	23.69	24.16	22.34	23.25	22.81	23.69	24.16
	12H	22.38	23.25	22.85	23.68	24.17	22.38	23.25	22.85	23.68	24.17
4H	2H	20.23	21.28	20.68	21.69	22.13	20.23	21.28	20.68	21.69	22.13
	3H	21.96	22.82	22.42	23.27	23.74	21.96	22.82	22.42	23.27	23.74
	4H	22.64	23.41	23.12	23.88	24.38	22.64	23.41	23.12	23.88	24.38
	6H	23.14	23.80	23.64	24.30	24.82	23.14	23.80	23.64	24.30	24.82
	8H	23.27	23.89	23.78	24.39	24.92	23.27	23.89	23.78	24.39	24.92
	12H	23.33	23.88	23.86	24.41	24.94	23.33	23.88	23.86	24.41	24.94
8H	4H	22.84	23.47	23.35	23.96	24.49	22.84	23.47	23.35	23.96	24.49
	6H	23.44	23.95	23.98	24.49	25.03	23.44	23.95	23.98	24.49	25.03
	8H	23.63	24.08	24.19	24.64	25.19	23.63	24.08	24.19	24.64	25.19
	12H	23.74	24.14	24.29	24.68	25.30	23.74	24.14	24.29	24.68	25.30
12H	4H	22.84	23.39	23.37	23.92	24.45	22.84	23.39	23.37	23.92	24.45
	6H	23.46	23.91	24.02	24.47	25.02	23.46	23.91	24.02	24.47	25.02
	8H	23.68	24.09	24.24	24.62	25.25	23.68	24.09	24.24	24.62	25.25

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2506-472-7

Test Date: 08/04/2025

Luminaire Tested: EHBR-60-L940-N

Data in this report applies to families of products including EHBR-60-L940-N

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2506-472-7
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 08/05/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Metalux
 Catalog Number: **EHBR-60-L940-N**
 Description: Elevate Round Highbay at, 60000 lumens, 4000K 90CRI LEDs with N lens

Spectral Parameters

CCT (K): 3963
 CIE u': 0.2267
 CIE v': 0.5003
 Duv: -0.0016
 CIE x: 0.3810
 CIE y: 0.3738
 CIE z: 0.2453
 Peak Wavelength (nm): 630
 Dominant Wavelength (nm): 580
 Purity: 26.49712
 Rf: 90.7
 Rg: 101

CRI (Ra):	93.4		
R1:	95.2	R9:	66.4
R2:	95.1	R10:	86.6
R3:	93.3	R11:	94.4
R4:	94.5	R12:	75.4
R5:	94.2	R13:	95.0
R6:	92.9	R14:	95.4
R7:	94.0	R15:	92.8
R8:	87.7		



Test Conditions

Stabilization Time: 44M
 Operation Time: 1H 44M
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP1-2506-472-7

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2506-472-7

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2506-472-7

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	141	NR	620	276	NR	750	5	NR	880	0	NR
365	0	NR	495	167	NR	625	279	NR	755	4	NR	885	0	NR
370	0	NR	500	193	NR	630	1000	NR	760	4	NR	890	0	NR
375	0	NR	505	215	NR	635	628	NR	765	3	NR	895	0	NR
380	0	NR	510	230	NR	640	164	NR	770	3	NR	900	0	NR
385	0	NR	515	243	NR	645	161	NR	775	2	NR	905	0	NR
390	1	NR	520	251	NR	650	137	NR	780	2	NR	910	0	NR
395	2	NR	525	256	NR	655	111	NR	785	2	NR	915	0	NR
400	3	NR	530	262	NR	660	92	NR	790	1	NR	920	0	NR
405	4	NR	535	267	NR	665	76	NR	795	1	NR	925	0	NR
410	6	NR	540	271	NR	670	71	NR	800	1	NR	930	0	NR
415	11	NR	545	276	NR	675	56	NR	805	1	NR	935	0	NR
420	20	NR	550	280	NR	680	47	NR	810	1	NR	940	0	NR
425	37	NR	555	285	NR	685	40	NR	815	1	NR	945	0	NR
430	63	NR	560	290	NR	690	34	NR	820	1	NR	950	0	NR
435	108	NR	565	294	NR	695	29	NR	825	1	NR	955	0	NR
440	186	NR	570	296	NR	700	25	NR	830	0	NR	960	0	NR
445	323	NR	575	298	NR	705	21	NR	835	0	NR	965	0	NR
450	403	NR	580	299	NR	710	18	NR	840	0	NR	970	0	NR
455	293	NR	585	298	NR	715	15	NR	845	0	NR	975	0	NR
460	214	NR	590	296	NR	720	13	NR	850	0	NR	980	0	NR
465	180	NR	595	288	NR	725	11	NR	855	0	NR	985	0	NR
470	132	NR	600	286	NR	730	9	NR	860	0	NR	990	0	NR
475	109	NR	605	282	NR	735	8	NR	865	0	NR	995	0	NR
480	110	NR	610	311	NR	740	7	NR	870	0	NR	1000	0	NR
485	121	NR	615	334	NR	745	6	NR	875	0	NR			

REPORT NUMBER: SP1-2506-472-7

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.76

λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)
360	0	NR	490	141	NR	620	276	NR	750	5	NR	880	0	NR
365	0	NR	495	167	NR	625	279	NR	755	4	NR	885	0	NR
370	0	NR	500	193	NR	630	1000	NR	760	4	NR	890	0	NR
375	0	NR	505	215	NR	635	628	NR	765	3	NR	895	0	NR
380	0	NR	510	230	NR	640	164	NR	770	3	NR	900	0	NR
385	0	NR	515	243	NR	645	161	NR	775	2	NR	905	0	NR
390	1	NR	520	251	NR	650	137	NR	780	2	NR	910	0	NR
395	2	NR	525	256	NR	655	111	NR	785	2	NR	915	0	NR
400	3	NR	530	262	NR	660	92	NR	790	1	NR	920	0	NR
405	4	NR	535	267	NR	665	76	NR	795	1	NR	925	0	NR
410	6	NR	540	271	NR	670	71	NR	800	1	NR	930	0	NR
415	11	NR	545	276	NR	675	56	NR	805	1	NR	935	0	NR
420	20	NR	550	280	NR	680	47	NR	810	1	NR	940	0	NR
425	37	NR	555	285	NR	685	40	NR	815	1	NR	945	0	NR
430	63	NR	560	290	NR	690	34	NR	820	1	NR	950	0	NR
435	108	NR	565	294	NR	695	29	NR	825	1	NR	955	0	NR
440	186	NR	570	296	NR	700	25	NR	830	0	NR	960	0	NR
445	323	NR	575	298	NR	705	21	NR	835	0	NR	965	0	NR
450	403	NR	580	299	NR	710	18	NR	840	0	NR	970	0	NR
455	293	NR	585	298	NR	715	15	NR	845	0	NR	975	0	NR
460	214	NR	590	296	NR	720	13	NR	850	0	NR	980	0	NR
465	180	NR	595	288	NR	725	11	NR	855	0	NR	985	0	NR
470	132	NR	600	286	NR	730	9	NR	860	0	NR	990	0	NR
475	109	NR	605	282	NR	735	8	NR	865	0	NR	995	0	NR
480	110	NR	610	311	NR	740	7	NR	870	0	NR	1000	0	NR
485	121	NR	615	334	NR	745	6	NR	875	0	NR			

REPORT NUMBER: SP1-2506-472-7

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 3.64

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	141	NR	620	276	NR	750	5	NR	880	0	NR
365	0	NR	495	167	NR	625	279	NR	755	4	NR	885	0	NR
370	0	NR	500	193	NR	630	1000	NR	760	4	NR	890	0	NR
375	0	NR	505	215	NR	635	628	NR	765	3	NR	895	0	NR
380	0	NR	510	230	NR	640	164	NR	770	3	NR	900	0	NR
385	0	NR	515	243	NR	645	161	NR	775	2	NR	905	0	NR
390	1	NR	520	251	NR	650	137	NR	780	2	NR	910	0	NR
395	2	NR	525	256	NR	655	111	NR	785	2	NR	915	0	NR
400	3	NR	530	262	NR	660	92	NR	790	1	NR	920	0	NR
405	4	NR	535	267	NR	665	76	NR	795	1	NR	925	0	NR
410	6	NR	540	271	NR	670	71	NR	800	1	NR	930	0	NR
415	11	NR	545	276	NR	675	56	NR	805	1	NR	935	0	NR
420	20	NR	550	280	NR	680	47	NR	810	1	NR	940	0	NR
425	37	NR	555	285	NR	685	40	NR	815	1	NR	945	0	NR
430	63	NR	560	290	NR	690	34	NR	820	1	NR	950	0	NR
435	108	NR	565	294	NR	695	29	NR	825	1	NR	955	0	NR
440	186	NR	570	296	NR	700	25	NR	830	0	NR	960	0	NR
445	323	NR	575	298	NR	705	21	NR	835	0	NR	965	0	NR
450	403	NR	580	299	NR	710	18	NR	840	0	NR	970	0	NR
455	293	NR	585	298	NR	715	15	NR	845	0	NR	975	0	NR
460	214	NR	590	296	NR	720	13	NR	850	0	NR	980	0	NR
465	180	NR	595	288	NR	725	11	NR	855	0	NR	985	0	NR
470	132	NR	600	286	NR	730	9	NR	860	0	NR	990	0	NR
475	109	NR	605	282	NR	735	8	NR	865	0	NR	995	0	NR
480	110	NR	610	311	NR	740	7	NR	870	0	NR	1000	0	NR
485	121	NR	615	334	NR	745	6	NR	875	0	NR			

Summary

$R_f = 90.7$
 $R_g = 101$
 $CIE R_a = 93.4$
 $R_9 = 66.4$



Color Vector Graphics




Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 90	CES51 = 99	CES76 = 83
CES02 = 62	CES27 = 93	CES52 = 97	CES77 = 87
CES03 = 31	CES28 = 94	CES53 = 95	CES78 = 79
CES04 = 69	CES29 = 91	CES54 = 96	CES79 = 94
CES05 = 49	CES30 = 98	CES55 = 95	CES80 = 91
CES06 = 50	CES31 = 92	CES56 = 95	CES81 = 80
CES07 = 42	CES32 = 84	CES57 = 94	CES82 = 96
CES08 = 41	CES33 = 95	CES58 = 95	CES83 = 95
CES09 = 29	CES34 = 90	CES59 = 98	CES84 = 93
CES10 = 74	CES35 = 94	CES60 = 93	CES85 = 82
CES11 = 57	CES36 = 84	CES61 = 93	CES86 = 84
CES12 = 63	CES37 = 92	CES62 = 90	CES87 = 90
CES13 = 43	CES38 = 93	CES63 = 92	CES88 = 97
CES14 = 74	CES39 = 98	CES64 = 91	CES89 = 84
CES15 = 71	CES40 = 96	CES65 = 88	CES90 = 99
CES16 = 47	CES41 = 98	CES66 = 88	CES91 = 74
CES17 = 49	CES42 = 89	CES67 = 87	CES92 = 78
CES18 = 56	CES43 = 89	CES68 = 87	CES93 = 87
CES19 = 71	CES44 = 99	CES69 = 88	CES94 = 75
CES20 = 66	CES45 = 93	CES70 = 84	CES95 = 83
CES21 = 85	CES46 = 95	CES71 = 80	CES96 = 91
CES22 = 78	CES47 = 92	CES72 = 93	CES97 = 93
CES23 = 91	CES48 = 96	CES73 = 78	CES98 = 93
CES24 = 90	CES49 = 93	CES74 = 92	CES99 = 94
CES25 = 71	CES50 = 99	CES75 = 81	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)