Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: METALUX

Report Number: P1594573

Luminaire Tested: FLXB-1224-N-MED-3000K

Issue Date: 10/2/2026

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-2019
Report Number:	P1594573
	TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (A2601782A001)
Test Lab:	INNOVATION CENTER
Issue Date:	10/2/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	METALUX
Catalog Number:	FLXB-1224-N-MED-3000K
Description:	1224 FlexBay Linear High bay at N beam, MED lumen, 3000K CCT settings
Light Source:	-
Ballast/Driver:	-

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	18309.0 lumens
Efficiency:	N/A
Efficacy:	158.9 lumens/watt
Spacing Criteria (0/90/45):	1.53 / 1 / 1.06
Luminous Opening:	Rectangular (W 1.04' x L: 1.19' x H: 0')
CIE Type:	Direct


Input Watts (W):	115.2
Input Voltage (V):	NR
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	NR
Total Harmonic Distortion (THDi):	NR
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594573
CATALOG NUMBER: FLXB-1224-N-MED-3000K

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594573
CATALOG NUMBER: FLXB-1224-N-MED-3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	91	90
2	104	98	92	88	102	96	91	87	93	89	85	89	86	83	87	84	81	80
3	97	89	82	77	95	87	81	76	84	79	75	82	78	74	79	76	73	71
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64
5	84	74	67	61	83	73	66	61	71	65	60	69	64	60	67	63	59	57
6	79	68	61	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47
8	70	58	51	46	68	58	51	46	56	50	46	55	49	45	54	49	45	43
9	66	54	47	42	64	54	47	42	52	46	42	51	46	42	51	45	42	40
10	62	50	44	39	61	50	43	39	49	43	39	48	43	39	47	42	38	37

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	97848	97848	97848	97848
5°	98266	97799	98266	97799
10°	99398	97349	99398	97349
15°	101414	95665	101414	95665
20°	104222	91544	104222	91544
25°	108227	83043	108227	83043
30°	113477	61933	113477	61933
35°	119894	28744	119894	28744
40°	126927	8976	126927	8976
45°	131332	6221	131332	6221
50°	133345	6113	133345	6113
55°	124496	6027	124496	6027
60°	111644	6375	111644	6375
65°	87153	6177	87153	6177
70°	65614	6332	65614	6332
75°	40226	4905	40226	4905
80°	26478	3538	26478	3538
85°	12709	1617	12709	1617

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 50°
Luminance: 133345 cd/sqm

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594573
CATALOG NUMBER: FLXB-1224-N-MED-3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1066.8	5.8
10°-20°	3079.4	16.8
20°-30°	4559.3	24.9
30°-40°	4258.3	23.3
40°-50°	2410.2	13.2
50°-60°	1513.3	8.3
60°-70°	954.5	5.2
70°-80°	401.3	2.2
80°-90°	66.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	8705.4	47.5
0°-40°	12963.8	70.8
0°-60°	16887.2	92.2
0°-90°	18309.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	18309.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	11245	11245	11245	11245	11245	
5°	11250	11197	11250	11197	11250	1074
15°	11258	10620	11258	10620	11258	3190
25°	11272	8649	11272	8649	11272	5219
35°	11287	2706	11287	2706	11287	7075
45°	10672	506	10672	506	10672	8201
55°	8206	397	8206	397	8206	7310
65°	4233	300	4233	300	4233	4267
75°	1196	146	1196	146	1196	1387
85°	127	16	127	16	127	198
90°	15	2	15	2	15	

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594573
CATALOG NUMBER: FLXB-1224-N-MED-3000K

CANDELA DISTRIBUTION (FULL):

	0°	30°	60°	90°	120°	150°	180°	210°	240°	270°	300°
0°	11245.0	11245.0	11245.0	11245.0	11245.0	11245.0	11245.0	11245.0	11245.0	11245.0	11245.0
0.5°	11245.0	11245.0	11245.0	11245.0	11245.0	11245.0	11245.0	11245.0	11245.0	11245.0	11245.0
1°	11266.2	11256.2	11242.3	11282.4	11153.6	11241.9	11266.2	11256.2	11242.3	11282.4	11153.6
1.5°	11266.2	11261.4	11245.7	11254.7	11153.6	11260.5	11266.2	11261.4	11245.7	11254.7	11153.6
2°	11239.9	11269.0	11220.4	11254.7	11153.6	11256.2	11239.9	11269.0	11220.4	11254.7	11153.6
2.5°	11239.9	11269.0	11209.4	11243.8	11153.6	11256.2	11239.9	11269.0	11209.4	11243.8	11153.6
3°	11264.3	11258.1	11214.7	11243.8	11153.6	11256.6	11264.3	11258.1	11214.7	11243.8	11153.6
3.5°	11264.3	11252.8	11205.1	11230.4	11117.9	11256.6	11264.3	11252.8	11205.1	11230.4	11117.9
4°	11243.3	11269.0	11193.2	11230.4	11179.9	11242.3	11243.3	11269.0	11193.2	11230.4	11179.9
4.5°	11243.3	11262.8	11154.1	11205.1	11187.0	11255.7	11243.3	11262.8	11154.1	11205.1	11187.0
5°	11250.0	11247.1	11171.8	11196.6	11153.1	11237.6	11250.0	11247.1	11171.8	11196.6	11153.1
5.5°	11260.0	11227.6	11180.3	11189.4	11153.1	11208.5	11260.0	11227.6	11180.3	11189.4	11153.1
6°	11260.0	11232.3	11161.7	11181.3	11126.0	11229.9	11260.0	11232.3	11161.7	11181.3	11126.0
6.5°	11238.0	11237.1	11128.8	11158.9	11131.2	11243.8	11238.0	11237.1	11128.8	11158.9	11131.2
7°	11238.0	11238.5	11132.6	11126.9	11122.1	11232.3	11238.0	11238.5	11132.6	11126.9	11122.1
7.5°	11264.3	11207.0	11116.4	11126.9	11100.7	11209.0	11264.3	11207.0	11116.4	11126.9	11100.7
8°	11264.3	11207.0	11090.2	11103.1	11046.8	11209.0	11264.3	11207.0	11090.2	11103.1	11046.8
8.5°	11239.9	11219.0	11066.4	11103.1	11058.3	11198.5	11239.9	11219.0	11066.4	11103.1	11058.3
9°	11258.6	11219.4	11017.7	11042.0	11056.3	11209.4	11258.6	11219.4	11017.7	11042.0	11056.3
9.5°	11249.5	11194.7	11031.1	11028.7	10986.2	11186.1	11249.5	11194.7	11031.1	11028.7	10986.2
10°	11249.5	11169.4	11028.7	11017.7	10986.2	11151.7	11249.5	11169.4	11028.7	11017.7	10986.2
10.5°	11254.7	11185.1	10997.7	10979.6	10960.0	11171.8	11254.7	11185.1	10997.7	10979.6	10960.0
11°	11254.3	11195.6	10942.4	10942.8	10960.0	11171.8	11254.3	11195.6	10942.4	10942.8	10960.0
11.5°	11237.1	11186.5	10945.7	10903.7	10909.0	11157.9	11237.1	11186.5	10945.7	10903.7	10909.0
12°	11264.8	11161.7	10924.7	10903.7	10888.0	11139.3	11264.8	11161.7	10924.7	10903.7	10888.0
12.5°	11264.8	11151.7	10912.3	10830.8	10833.2	11139.3	11264.8	11151.7	10912.3	10830.8	10833.2
13°	11235.6	11147.9	10863.2	10830.8	10833.2	11120.2	11235.6	11147.9	10863.2	10830.8	10833.2
13.5°	11235.6	11147.9	10838.9	10749.2	10804.1	11120.2	11235.6	11147.9	10838.9	10749.2	10804.1
14°	11260.0	11122.1	10776.9	10749.2	10772.1	11106.9	11260.0	11122.1	10776.9	10749.2	10772.1
14.5°	11260.0	11095.9	10744.5	10677.2	10713.9	11073.5	11260.0	11095.9	10744.5	10677.2	10713.9
15°	11257.6	11112.6	10724.9	10619.5	10661.5	11083.1	11257.6	11112.6	10724.9	10619.5	10661.5
15.5°	11246.6	11109.3	10661.5	10572.3	10661.5	11083.1	11246.6	11109.3	10661.5	10572.3	10661.5
16°	11246.6	11087.3	10650.5	10519.8	10570.9	11057.8	11246.6	11087.3	10650.5	10519.8	10570.9
16.5°	11270.9	11056.8	10612.8	10491.7	10543.2	11025.3	11270.9	11056.8	10612.8	10491.7	10543.2
17°	11270.9	11046.3	10589.0	10436.4	10468.8	11036.3	11270.9	11046.3	10589.0	10436.4	10468.8
17.5°	11240.4	11058.3	10519.8	10364.4	10461.7	11010.1	11240.4	11058.3	10519.8	10364.4	10461.7
18°	11240.4	11058.3	10414.5	10241.3	10407.3	11010.1	11240.4	11058.3	10414.5	10241.3	10407.3
18.5°	11266.7	11009.6	10397.3	10241.3	10362.0	10969.5	11266.7	11009.6	10397.3	10241.3	10362.0
19°	11266.7	10980.0	10335.8	10165.5	10269.0	10969.5	11266.7	10980.0	10335.8	10165.5	10269.0
19.5°	11255.2	10999.6	10285.7	10071.1	10259.4	10939.0	11255.2	10999.6	10285.7	10071.1	10259.4
20°	11255.2	10993.4	10194.1	9886.0	10186.5	10922.8	11255.2	10993.4	10194.1	9886.0	10186.5
20.5°	11251.9	10967.6	10172.2	9886.0	10141.7	10902.8	11251.9	10967.6	10172.2	9886.0	10141.7
21°	11274.3	10922.8	10103.0	9731.0	10045.3	10855.1	11274.3	10922.8	10103.0	9731.0	10045.3
21.5°	11274.3	10913.8	10057.2	9597.5	9909.9	10866.1	11274.3	10913.8	10057.2	9597.5	9909.9
22°	11247.1	10899.0	9958.5	9491.2	9879.8	10837.4	11247.1	10899.0	9958.5	9491.2	9879.8

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594573
CATALOG NUMBER: FLXB-1224-N-MED-3000K

CANDELA DISTRIBUTION (continued):

	0°	30°	60°	90°	120°	150°	180°	210°	240°	270°	300°
22.5°	11247.1	10891.3	9912.7	9367.7	9782.6	10820.3	11247.1	10891.3	9912.7	9367.7	9782.6
23°	11281.4	10844.6	9808.3	9271.3	9722.0	10770.7	11281.4	10844.6	9808.3	9271.3	9722.0
23.5°	11281.4	10844.6	9652.9	9093.9	9585.6	10770.7	11281.4	10844.6	9652.9	9093.9	9585.6
24°	11265.7	10800.7	9571.8	8989.5	9547.9	10713.0	11265.7	10800.7	9571.8	8989.5	9547.9
24.5°	11265.7	10774.5	9439.7	8787.8	9431.1	10687.7	11265.7	10774.5	9439.7	8787.8	9431.1
25°	11272.4	10743.5	9373.4	8649.4	9206.9	10661.0	11272.4	10743.5	9373.4	8649.4	9206.9
25.5°	11272.4	10688.7	9254.2	8295.6	9206.9	10600.4	11272.4	10688.7	9254.2	8295.6	9206.9
26°	11299.6	10672.9	9153.5	8295.6	8976.1	10598.5	11299.6	10672.9	9153.5	8295.6	8976.1
26.5°	11265.2	10648.6	9001.4	7864.0	8976.1	10545.6	11265.2	10648.6	9001.4	7864.0	8976.1
27°	11265.2	10617.6	8891.7	7607.4	8724.3	10526.0	11265.2	10617.6	8891.7	7607.4	8724.3
27.5°	11296.2	10565.6	8738.2	7452.9	8606.5	10453.5	11296.2	10565.6	8738.2	7452.9	8606.5
28°	11296.2	10522.2	8618.0	7163.5	8404.8	10372.9	11296.2	10522.2	8618.0	7163.5	8404.8
28.5°	11282.4	10428.8	8446.3	6991.3	8294.2	10354.4	11282.4	10428.8	8446.3	6991.3	8294.2
29°	11282.4	10428.8	8066.7	6693.2	8091.5	10354.4	11282.4	10428.8	8066.7	6693.2	8091.5
29.5°	11293.9	10304.8	7885.9	6484.8	7927.4	10250.9	11293.9	10304.8	7885.9	6484.8	7927.4
30°	11293.9	10236.6	7687.6	6163.9	7680.4	10163.6	11293.9	10236.6	7687.6	6163.9	7680.4
30.5°	11305.3	10170.8	7447.7	5958.3	7245.0	10141.2	11305.3	10170.8	7447.7	5958.3	7245.0
31°	11280.5	10123.5	7199.7	5352.2	7245.0	10071.6	11280.5	10123.5	7199.7	5352.2	7245.0
31.5°	11280.5	10023.9	6940.3	5352.2	6747.6	10012.4	11280.5	10023.9	6940.3	5352.2	6747.6
32°	11314.3	9947.6	6688.9	4727.9	6496.7	9919.0	11314.3	9947.6	6688.9	4727.9	6496.7
32.5°	11314.3	9826.9	6409.9	4321.6	6182.5	9862.7	11314.3	9826.9	6409.9	4321.6	6182.5
33°	11282.4	9603.7	6131.9	4050.3	5922.1	9689.6	11282.4	9603.7	6131.9	4050.3	5922.1
33.5°	11282.4	9603.7	5529.6	3651.1	5602.6	9689.6	11282.4	9603.7	5529.6	3651.1	5602.6
34°	11288.1	9361.0	5214.9	3357.3	5313.6	9498.3	11288.1	9361.0	5214.9	3357.3	5313.6
34.5°	11288.1	9259.9	4908.7	3357.3	4968.3	9498.3	11288.1	9259.9	4908.7	3357.3	4968.3
35°	11286.7	9067.7	4552.0	2705.9	4685.0	9281.3	11286.7	9067.7	4552.0	2705.9	4685.0
35.5°	11286.7	8984.2	4214.3	2139.8	4334.5	9157.8	11286.7	8984.2	4214.3	2139.8	4334.5
36°	11255.2	8721.0	3832.3	2139.8	3676.9	9010.5	11255.2	8721.0	3832.3	2139.8	3676.9
36.5°	11272.9	8607.0	3496.6	1682.5	3676.9	8855.5	11272.9	8607.0	3496.6	1682.5	3676.9
37°	11272.9	8303.7	3070.3	1599.5	3062.6	8707.6	11272.9	8303.7	3070.3	1599.5	3062.6
37.5°	11227.1	8204.5	2741.2	1294.8	2684.4	8535.9	11227.1	8204.5	2741.2	1294.8	2684.4
38°	11227.1	7859.2	2282.4	1270.9	2507.5	8350.4	11227.1	7859.2	2282.4	1270.9	2507.5
38.5°	11218.5	7323.7	1923.8	994.8	2076.4	7927.9	11218.5	7323.7	1923.8	994.8	2076.4
39°	11218.5	7323.7	1497.5	989.6	1976.7	7927.9	11218.5	7323.7	1497.5	989.6	1976.7
39.5°	11174.1	6759.5	1182.7	788.8	1543.2	7431.9	11174.1	6759.5	1182.7	788.8	1543.2
40°	11174.1	6602.6	1025.8	790.2	1104.5	7179.7	11174.1	6602.6	1025.8	790.2	1104.5
40.5°	11114.5	6139.1	728.2	663.4	1086.8	6838.7	11114.5	6139.1	728.2	663.4	1086.8
41°	11120.2	5947.4	728.2	599.5	1086.8	6524.4	11120.2	5947.4	728.2	599.5	1086.8
41.5°	11076.9	5475.2	566.1	599.5	800.7	6163.9	11076.9	5475.2	566.1	599.5	800.7
42°	10957.1	5268.3	566.1	568.5	800.7	5807.2	10957.1	5268.3	566.1	568.5	800.7
42.5°	10957.1	4819.0	506.5	564.6	620.4	5397.5	10957.1	4819.0	506.5	564.6	620.4
43°	10901.4	4570.1	506.5	548.0	520.8	4562.5	10901.4	4570.1	506.5	548.0	520.8
43.5°	10901.4	4176.6	493.1	537.9	514.1	4562.5	10901.4	4176.6	493.1	537.9	514.1
44°	10781.7	3602.5	486.0	519.3	486.0	3684.0	10781.7	3602.5	486.0	519.3	486.0
44.5°	10781.7	3602.5	482.6	505.5	482.6	3684.0	10781.7	3602.5	482.6	505.5	482.6

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594573
CATALOG NUMBER: FLXB-1224-N-MED-3000K

CANDELA DISTRIBUTION (continued):

	0°	30°	60°	90°	120°	150°	180°	210°	240°	270°	300°
45°	10672.4	3098.4	473.6	505.5	475.5	2841.3	10672.4	3098.4	473.6	505.5	475.5
45.5°	10672.4	2705.9	473.6	488.3	472.6	2503.7	10672.4	2705.9	473.6	488.3	472.6
46°	10549.4	2595.3	464.5	488.3	464.0	2096.4	10549.4	2595.3	464.5	488.3	464.0
46.5°	10378.2	2183.2	464.5	473.1	464.0	1851.3	10378.2	2183.2	464.5	473.1	464.0
47°	10378.2	2108.8	455.4	473.1	458.3	1496.0	10378.2	2108.8	455.4	473.1	458.3
47.5°	10239.9	1705.8	455.4	467.8	451.6	1309.1	10239.9	1705.8	455.4	467.8	451.6
48°	10239.9	1655.8	449.7	463.1	445.4	1075.9	10239.9	1655.8	449.7	463.1	445.4
48.5°	10044.8	1271.4	449.7	464.5	442.6	786.4	10044.8	1271.4	449.7	464.5	442.6
49°	10044.8	1271.4	442.1	459.7	437.8	786.4	10044.8	1271.4	442.1	459.7	437.8
49.5°	9850.3	986.7	444.9	456.9	437.3	595.2	9850.3	986.7	444.9	456.9	437.3
50°	9850.3	780.2	444.9	451.6	435.9	560.8	9850.3	780.2	444.9	451.6	435.9
50.5°	9635.2	766.9	452.6	443.5	440.6	500.7	9635.2	766.9	452.6	443.5	440.6
51°	9635.2	601.8	452.6	430.2	441.6	486.0	9635.2	601.8	452.6	430.2	441.6
51.5°	9376.2	590.4	455.4	430.2	453.1	445.9	9376.2	590.4	455.4	430.2	453.1
52°	9135.9	473.6	455.4	427.8	453.1	435.9	9135.9	473.6	455.4	427.8	453.1
52.5°	9135.9	462.6	449.2	424.9	451.2	411.6	9135.9	462.6	449.2	424.9	451.2
53°	8817.3	408.7	449.2	421.1	444.9	404.4	8817.3	408.7	449.2	421.1	444.9
53.5°	8817.3	400.6	426.3	410.6	436.4	390.1	8817.3	400.6	426.3	410.6	436.4
54°	8527.8	368.6	416.8	410.1	419.7	372.0	8527.8	368.6	416.8	410.1	419.7
54.5°	8527.8	368.6	403.0	397.7	407.3	372.0	8527.8	368.6	403.0	397.7	407.3
55°	8206.4	349.1	382.5	397.3	392.5	354.8	8206.4	349.1	382.5	397.3	392.5
55.5°	8206.4	342.4	382.5	387.2	386.3	347.7	8206.4	342.4	382.5	387.2	386.3
56°	7854.0	336.7	370.1	383.9	371.5	337.6	7854.0	336.7	370.1	383.9	371.5
56.5°	7854.0	329.5	370.1	379.1	371.5	329.5	7854.0	329.5	370.1	379.1	371.5
57°	7522.1	325.7	364.3	379.1	362.9	321.4	7522.1	325.7	364.3	379.1	362.9
57.5°	7145.3	318.6	364.3	380.6	362.0	312.8	7145.3	318.6	364.3	380.6	362.0
58°	7145.3	318.6	358.1	377.2	358.1	306.2	7145.3	318.6	358.1	377.2	358.1
58.5°	6790.0	317.1	358.1	377.7	351.5	292.8	6790.0	317.1	358.1	377.7	351.5
59°	6790.0	317.1	349.1	371.5	347.7	292.8	6790.0	317.1	349.1	371.5	347.7
59.5°	6415.2	314.7	341.0	366.3	344.8	279.9	6415.2	314.7	341.0	366.3	344.8
60°	6415.2	314.7	341.0	366.3	343.4	279.9	6415.2	314.7	341.0	366.3	343.4
60.5°	6043.2	306.2	339.1	357.7	336.2	272.3	6043.2	306.2	339.1	357.7	336.2
61°	6043.2	298.1	339.1	348.1	334.3	266.1	6043.2	298.1	339.1	348.1	334.3
61.5°	5680.3	296.6	339.6	341.5	335.3	268.5	5680.3	296.6	339.6	341.5	335.3
62°	5298.3	289.0	339.6	339.6	335.3	263.7	5298.3	289.0	339.6	339.6	335.3
62.5°	5298.3	283.3	336.2	329.5	328.6	269.5	5298.3	283.3	336.2	329.5	328.6
63°	4940.2	276.6	336.2	317.6	328.1	267.1	4940.2	276.6	336.2	317.6	328.1
63.5°	4940.2	272.8	318.6	317.6	321.9	268.0	4940.2	272.8	318.6	317.6	321.9
64°	4579.2	267.1	318.6	309.0	315.2	260.9	4579.2	267.1	318.6	309.0	315.2
64.5°	4579.2	267.1	300.5	309.0	310.5	260.9	4579.2	267.1	300.5	309.0	310.5
65°	4232.9	269.5	286.6	300.0	296.6	262.3	4232.9	269.5	286.6	300.0	296.6
65.5°	4232.9	267.1	286.6	300.0	294.2	266.6	4232.9	267.1	286.6	300.0	294.2
66°	3898.6	285.7	281.4	293.3	283.8	261.3	3898.6	285.7	281.4	293.3	283.8
66.5°	3898.6	284.2	281.4	290.9	283.8	267.1	3898.6	284.2	281.4	290.9	283.8
67°	3543.8	318.6	277.1	285.7	272.3	263.2	3543.8	318.6	277.1	285.7	272.3

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594573
CATALOG NUMBER: FLXB-1224-N-MED-3000K

CANDELA DISTRIBUTION (continued):

	0°	30°	60°	90°	120°	150°	180°	210°	240°	270°	300°
67.5°	3221.9	326.2	277.1	280.4	272.3	269.9	3221.9	326.2	277.1	280.4	272.3
68°	3221.9	358.1	268.5	275.6	263.2	271.8	3221.9	358.1	268.5	275.6	263.2
68.5°	2885.2	358.1	268.5	263.7	262.8	285.7	2885.2	358.1	268.5	263.7	262.8
69°	2885.2	337.2	257.0	263.7	258.5	285.7	2885.2	337.2	257.0	263.7	258.5
69.5°	2579.0	298.1	252.3	248.9	251.8	303.3	2579.0	298.1	252.3	248.9	251.8
70°	2579.0	298.1	247.0	248.9	241.3	303.3	2579.0	298.1	247.0	248.9	241.3
70.5°	2298.2	282.8	230.8	229.4	236.5	332.4	2298.2	282.8	230.8	229.4	236.5
71°	2298.2	286.6	230.8	229.4	225.1	346.2	2298.2	286.6	230.8	229.4	225.1
71.5°	2024.9	272.8	209.4	218.9	209.8	371.5	2024.9	272.8	209.4	218.9	209.8
72°	1953.4	275.6	209.4	214.6	209.8	374.4	1953.4	275.6	209.4	214.6	209.8
72.5°	1787.9	263.2	186.0	207.0	187.9	364.3	1787.9	263.2	186.0	207.0	187.9
73°	1569.5	264.7	186.0	195.0	187.9	367.7	1569.5	264.7	186.0	195.0	187.9
73.5°	1569.5	253.2	174.1	195.0	162.6	328.6	1569.5	253.2	174.1	195.0	162.6
74°	1376.3	256.1	174.1	184.1	150.7	289.0	1376.3	256.1	174.1	184.1	150.7
74.5°	1376.3	256.1	161.7	184.1	144.5	289.0	1376.3	256.1	161.7	184.1	144.5
75°	1196.5	257.0	140.7	145.9	141.2	259.4	1196.5	257.0	140.7	145.9	141.2
75.5°	1196.5	263.2	140.7	145.9	135.9	259.4	1196.5	263.2	140.7	145.9	135.9
76°	1034.4	249.9	128.8	117.8	132.6	236.5	1034.4	249.9	128.8	117.8	132.6
76.5°	924.7	239.4	128.8	110.2	126.9	223.2	924.7	239.4	128.8	110.2	126.9
77°	895.1	239.9	117.8	108.3	111.6	209.4	895.1	239.9	117.8	108.3	111.6
77.5°	760.2	221.8	117.8	99.2	111.6	200.3	760.2	221.8	117.8	99.2	111.6
78°	760.2	205.1	104.0	93.5	96.8	202.2	760.2	205.1	104.0	93.5	96.8
78.5°	639.5	189.8	104.0	78.7	91.1	193.1	639.5	189.8	104.0	78.7	91.1
79°	639.5	170.3	84.4	78.7	85.8	181.2	639.5	170.3	84.4	78.7	85.8
79.5°	528.4	157.4	84.4	70.6	78.7	158.8	528.4	157.4	84.4	70.6	78.7
80°	528.4	145.9	62.5	70.6	72.5	158.8	528.4	145.9	62.5	70.6	72.5
80.5°	435.4	128.3	51.5	54.4	61.0	146.9	435.4	128.3	51.5	54.4	61.0
81°	435.4	117.8	51.5	54.4	56.8	139.3	435.4	117.8	51.5	54.4	56.8
81.5°	354.8	107.8	39.6	42.9	45.3	126.9	354.8	107.8	39.6	42.9	45.3
82°	354.8	101.6	39.6	41.5	42.9	111.1	354.8	101.6	39.6	41.5	42.9
82.5°	282.8	96.8	28.1	38.2	36.3	90.1	282.8	96.8	28.1	38.2	36.3
83°	222.7	87.8	28.1	30.0	36.3	77.7	222.7	87.8	28.1	30.0	36.3
83.5°	222.7	85.4	23.8	28.1	25.3	65.3	222.7	85.4	23.8	28.1	25.3
84°	170.3	76.3	23.8	20.0	19.6	48.2	170.3	76.3	23.8	20.0	19.6
84.5°	170.3	74.4	19.6	20.0	16.7	48.2	170.3	74.4	19.6	20.0	16.7
85°	127.3	65.8	15.7	16.2	14.3	28.1	127.3	65.8	15.7	16.2	14.3
85.5°	127.3	50.1	12.9	16.2	13.8	28.1	127.3	50.1	12.9	16.2	13.8
86°	93.0	49.6	6.2	13.8	11.9	15.7	93.0	49.6	6.2	13.8	11.9
86.5°	93.0	37.2	6.2	13.8	11.0	11.9	93.0	37.2	6.2	13.8	11.0
87°	67.7	37.2	5.3	10.0	6.7	9.5	67.7	37.2	5.3	10.0	6.7
87.5°	67.7	28.1	5.3	4.8	6.7	5.7	67.7	28.1	5.3	4.8	6.7
88°	48.6	28.1	3.8	4.8	3.8	3.3	48.6	28.1	3.8	4.8	3.8
88.5°	34.3	18.6	3.8	3.3	3.3	2.9	34.3	18.6	3.8	3.3	3.3
89°	34.3	18.6	1.9	3.3	3.3	2.9	34.3	18.6	1.9	3.3	3.3
89.5°	23.8	10.5	1.9	2.9	2.4	1.9	23.8	10.5	1.9	2.9	2.4

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594573
CATALOG NUMBER: FLXB-1224-N-MED-3000K

CANDELA DISTRIBUTION (continued):

	0°	30°	60°	90°	120°	150°	180°	210°	240°	270°	300°
90°	*14.8*	6.2	1.0	1.9	1.4	1.4	14.8	6.2	1.0	1.9	1.4

TEST NUMBER: P1594573
CATALOG NUMBER: FLXB-1224-N-MED-3000K

CANDELA DISTRIBUTION (continued):

	330°	360°
0°	11245.0	11245.0
0.5°	11245.0	11245.0
1°	11241.9	11266.2
1.5°	11260.5	11266.2
2°	11256.2	11239.9
2.5°	11256.2	11239.9
3°	11256.6	11264.3
3.5°	11256.6	11264.3
4°	11242.3	11243.3
4.5°	11255.7	11243.3
5°	11237.6	11250.0
5.5°	11208.5	11260.0
6°	11229.9	11260.0
6.5°	11243.8	11238.0
7°	11232.3	11238.0
7.5°	11209.0	11264.3
8°	11209.0	11264.3
8.5°	11198.5	11239.9
9°	11209.4	11258.6
9.5°	11186.1	11249.5
10°	11151.7	11249.5
10.5°	11171.8	11254.7
11°	11171.8	11254.3
11.5°	11157.9	11237.1
12°	11139.3	11264.8
12.5°	11139.3	11264.8
13°	11120.2	11235.6
13.5°	11120.2	11235.6
14°	11106.9	11260.0
14.5°	11073.5	11260.0
15°	11083.1	11257.6
15.5°	11083.1	11246.6
16°	11057.8	11246.6
16.5°	11025.3	11270.9
17°	11036.3	11270.9
17.5°	11010.1	11240.4
18°	11010.1	11240.4
18.5°	10969.5	11266.7
19°	10969.5	11266.7
19.5°	10939.0	11255.2
20°	10922.8	11255.2
20.5°	10902.8	11251.9
21°	10855.1	11274.3
21.5°	10866.1	11274.3
22°	10837.4	11247.1

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594573
CATALOG NUMBER: FLXB-1224-N-MED-3000K

CANDELA DISTRIBUTION (continued):

	330°	360°
22.5°	10820.3	11247.1
23°	10770.7	11281.4
23.5°	10770.7	11281.4
24°	10713.0	11265.7
24.5°	10687.7	11265.7
25°	10661.0	11272.4
25.5°	10600.4	11272.4
26°	10598.5	11299.6
26.5°	10545.6	11265.2
27°	10526.0	11265.2
27.5°	10453.5	11296.2
28°	10372.9	11296.2
28.5°	10354.4	11282.4
29°	10354.4	11282.4
29.5°	10250.9	11293.9
30°	10163.6	11293.9
30.5°	10141.2	11305.3
31°	10071.6	11280.5
31.5°	10012.4	11280.5
32°	*9919.0*	*11314.3*
32.5°	9862.7	11314.3
33°	9689.6	11282.4
33.5°	9689.6	11282.4
34°	9498.3	11288.1
34.5°	9498.3	11288.1
35°	9281.3	11286.7
35.5°	9157.8	11286.7
36°	9010.5	11255.2
36.5°	8855.5	11272.9
37°	8707.6	11272.9
37.5°	8535.9	11227.1
38°	8350.4	11227.1
38.5°	7927.9	11218.5
39°	7927.9	11218.5
39.5°	7431.9	11174.1
40°	7179.7	11174.1
40.5°	6838.7	11114.5
41°	6524.4	11120.2
41.5°	6163.9	11076.9
42°	5807.2	10957.1
42.5°	5397.5	10957.1
43°	4562.5	10901.4
43.5°	4562.5	10901.4
44°	3684.0	10781.7
44.5°	3684.0	10781.7

TEST NUMBER: P1594573
CATALOG NUMBER: FLXB-1224-N-MED-3000K

CANDELA DISTRIBUTION (continued):

	330°	360°
45°	2841.3	10672.4
45.5°	2503.7	10672.4
46°	2096.4	10549.4
46.5°	1851.3	10378.2
47°	1496.0	10378.2
47.5°	1309.1	10239.9
48°	1075.9	10239.9
48.5°	786.4	10044.8
49°	786.4	10044.8
49.5°	595.2	9850.3
50°	560.8	9850.3
50.5°	500.7	9635.2
51°	486.0	9635.2
51.5°	445.9	9376.2
52°	435.9	9135.9
52.5°	411.6	9135.9
53°	404.4	8817.3
53.5°	390.1	8817.3
54°	372.0	8527.8
54.5°	372.0	8527.8
55°	354.8	8206.4
55.5°	347.7	8206.4
56°	337.6	7854.0
56.5°	329.5	7854.0
57°	321.4	7522.1
57.5°	312.8	7145.3
58°	306.2	7145.3
58.5°	292.8	6790.0
59°	292.8	6790.0
59.5°	279.9	6415.2
60°	279.9	6415.2
60.5°	272.3	6043.2
61°	266.1	6043.2
61.5°	268.5	5680.3
62°	263.7	5298.3
62.5°	269.5	5298.3
63°	267.1	4940.2
63.5°	268.0	4940.2
64°	260.9	4579.2
64.5°	260.9	4579.2
65°	262.3	4232.9
65.5°	266.6	4232.9
66°	261.3	3898.6
66.5°	267.1	3898.6
67°	263.2	3543.8

TEST NUMBER: P1594573
CATALOG NUMBER: FLXB-1224-N-MED-3000K

CANDELA DISTRIBUTION (continued):

	330°	360°
67.5°	269.9	3221.9
68°	271.8	3221.9
68.5°	285.7	2885.2
69°	285.7	2885.2
69.5°	303.3	2579.0
70°	303.3	2579.0
70.5°	332.4	2298.2
71°	346.2	2298.2
71.5°	371.5	2024.9
72°	374.4	1953.4
72.5°	364.3	1787.9
73°	367.7	1569.5
73.5°	328.6	1569.5
74°	289.0	1376.3
74.5°	289.0	1376.3
75°	259.4	1196.5
75.5°	259.4	1196.5
76°	236.5	1034.4
76.5°	223.2	924.7
77°	209.4	895.1
77.5°	200.3	760.2
78°	202.2	760.2
78.5°	193.1	639.5
79°	181.2	639.5
79.5°	158.8	528.4
80°	158.8	528.4
80.5°	146.9	435.4
81°	139.3	435.4
81.5°	126.9	354.8
82°	111.1	354.8
82.5°	90.1	282.8
83°	77.7	222.7
83.5°	65.3	222.7
84°	48.2	170.3
84.5°	48.2	170.3
85°	28.1	127.3
85.5°	28.1	127.3
86°	15.7	93.0
86.5°	11.9	93.0
87°	9.5	67.7
87.5°	5.7	67.7
88°	3.3	48.6
88.5°	2.9	34.3
89°	2.9	34.3
89.5°	1.9	23.8

TEST NUMBER: P1594573
CATALOG NUMBER: FLXB-1224-N-MED-3000K

CANDELA DISTRIBUTION (continued):

	330°	360°
90°	1.4	14.8

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594573
CATALOG NUMBER: FLXB-1224-N-MED-3000K

CIE UGR TABLE:

Reflectances:											
	Ceiling	0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
	Wall	0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
	Reference plane	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room Dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	26.0	27.3	26.4	27.6	27.9	11.5	12.8	11.9	13.1	13.5
	3H	27.9	29.1	28.3	29.4	29.8	13.8	14.9	14.1	15.3	15.6
	4H	28.4	29.4	28.8	29.8	30.2	14.5	15.6	14.9	15.9	16.3
	6H	28.5	29.5	29.0	29.9	30.3	14.8	15.7	15.2	16.1	16.5
	8H	28.6	29.5	29.0	29.9	30.3	14.8	15.7	15.2	16.1	16.5
	12H	28.5	29.4	29.0	29.8	30.3	14.8	15.7	15.2	16.0	16.5
4H	2H	25.8	26.8	26.2	27.2	27.6	12.1	13.2	12.5	13.6	14.0
	3H	27.7	28.6	28.1	29.0	29.4	14.6	15.5	15.0	15.9	16.3
	4H	28.2	29.0	28.6	29.4	29.9	15.4	16.2	15.8	16.6	17.0
	6H	28.5	29.1	28.9	29.6	30.1	15.7	16.4	16.2	16.8	17.3
	8H	28.5	29.1	29.0	29.6	30.1	15.8	16.4	16.2	16.8	17.3
	12H	28.5	29.1	29.0	29.5	30.0	15.7	16.3	16.2	16.8	17.3
8H	4H	28.1	28.7	28.6	29.2	29.6	16.0	16.6	16.5	17.1	17.6
	6H	28.3	28.9	28.8	29.4	29.8	16.4	16.9	16.9	17.4	17.9
	8H	28.4	28.9	28.9	29.4	29.9	16.4	16.9	16.9	17.4	17.9
	12H	28.4	28.8	28.9	29.3	29.9	16.4	16.8	16.9	17.3	17.9
12H	4H	28.0	28.6	28.5	29.1	29.6	16.2	16.7	16.7	17.2	17.7
	6H	28.3	28.8	28.8	29.2	29.8	16.5	17.0	17.1	17.5	18.0
	8H	28.4	28.8	28.9	29.3	29.8	16.6	17.0	17.1	17.5	18.1

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP3-2602-684-1

Test Date: 02/20/2026

Luminaire Tested: HLBX-2436-W-HI-3000K

Data in this report applies to families of products including HLBX-2436*

Report Generated By FNC07603 / LDUCLS01DT01661
Version: v7.05


Test Information

Test Method:	LM-79-2019
Report Number:	SP3-2602-684-1
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP3 - 3M SPHERE
Measurement Geometry:	4π
Issue Date:	02/27/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	Metalux
Catalog Number:	**HLBX-2436-W-HI-3000K**
Description:	LDS HLBX 2436 W beam, HI lumen, 3000K CCT settings

Spectral Parameters

CCT (K):	2947	CRI (Ra):	81.4		
CIE u':	0.2523	R1:	79.9	R9:	0.7
CIE v':	0.5232	R2:	91.2	R10:	79.6
Duv:	0.0005	R3:	95.4	R11:	77.4
CIE x:	0.4415	R4:	78.4	R12:	68.4
CIE y:	0.4069	R5:	79.9	R13:	82.7
CIE z:	0.1516	R6:	89.4	R14:	98.3
Peak Wavelength (nm):	605	R7:	81.1	R15:	71.7
Dominant Wavelength (nm):	582	R8:	55.6		
Purity:	54.65632				

Rf:	83.6
Rg:	93.7



Test Conditions


Stabilization Time:	31M
Operation Time:	1H 31M
Sphere Temperature (°C):	25.0

REPORT NUMBER: SP3-2602-684-1


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	3M SPHERE IN02505	1/10/2026	7/10/2026
Power Meter	XITRON INXT2011006	10/21/2025	10/21/2026
AC Power Source	CHROMA 61604 IN6064A	10/20/2025	10/20/2026
DC Power Source	EYSIGHT N5770A IN0534	10/20/2025	10/20/2026
Sphere Thermometer	TANDD IN4036E	10/21/2025	10/21/2026

REPORT NUMBER: SP3-2602-684-1

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2947K
CIE x = 0.4415
CIE y = 0.4069
Duv = 0.0005

Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP3-2602-684-1

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	213	NR	620	916	NR	750	28	NR	880	1	NR
365	0	NR	495	240	NR	625	865	NR	755	24	NR	885	1	NR
370	0	NR	500	283	NR	630	810	NR	760	20	NR	890	1	NR
375	0	NR	505	329	NR	635	746	NR	765	17	NR	895	1	NR
380	0	NR	510	372	NR	640	683	NR	770	15	NR	900	1	NR
385	0	NR	515	410	NR	645	617	NR	775	13	NR	905	0	NR
390	0	NR	520	441	NR	650	554	NR	780	11	NR	910	0	NR
395	0	NR	525	468	NR	655	494	NR	785	9	NR	915	0	NR
400	1	NR	530	488	NR	660	436	NR	790	8	NR	920	0	NR
405	3	NR	535	511	NR	665	384	NR	795	7	NR	925	0	NR
410	5	NR	540	533	NR	670	336	NR	800	6	NR	930	0	NR
415	9	NR	545	557	NR	675	292	NR	805	5	NR	935	0	NR
420	16	NR	550	586	NR	680	253	NR	810	4	NR	940	0	NR
425	28	NR	555	618	NR	685	220	NR	815	4	NR	945	0	NR
430	47	NR	560	658	NR	690	188	NR	820	3	NR	950	0	NR
435	79	NR	565	706	NR	695	162	NR	825	3	NR	955	0	NR
440	132	NR	570	754	NR	700	138	NR	830	2	NR	960	0	NR
445	236	NR	575	810	NR	705	118	NR	835	2	NR	965	0	NR
450	424	NR	580	864	NR	710	101	NR	840	2	NR	970	0	NR
455	532	NR	585	911	NR	715	86	NR	845	2	NR	975	0	NR
460	420	NR	590	954	NR	720	74	NR	850	1	NR	980	0	NR
465	327	NR	595	985	NR	725	63	NR	855	1	NR	985	0	NR
470	286	NR	600	997	NR	730	53	NR	860	1	NR	990	0	NR
475	225	NR	605	1000	NR	735	46	NR	865	1	NR	995	0	NR
480	191	NR	610	985	NR	740	39	NR	870	1	NR	1000	0	NR
485	194	NR	615	956	NR	745	33	NR	875	1	NR			

REPORT NUMBER: SP3-2602-684-1

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.32**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	213	NR	620	916	NR	750	28	NR	880	1	NR
365	0	NR	495	240	NR	625	865	NR	755	24	NR	885	1	NR
370	0	NR	500	283	NR	630	810	NR	760	20	NR	890	1	NR
375	0	NR	505	329	NR	635	746	NR	765	17	NR	895	1	NR
380	0	NR	510	372	NR	640	683	NR	770	15	NR	900	1	NR
385	0	NR	515	410	NR	645	617	NR	775	13	NR	905	0	NR
390	0	NR	520	441	NR	650	554	NR	780	11	NR	910	0	NR
395	0	NR	525	468	NR	655	494	NR	785	9	NR	915	0	NR
400	1	NR	530	488	NR	660	436	NR	790	8	NR	920	0	NR
405	3	NR	535	511	NR	665	384	NR	795	7	NR	925	0	NR
410	5	NR	540	533	NR	670	336	NR	800	6	NR	930	0	NR
415	9	NR	545	557	NR	675	292	NR	805	5	NR	935	0	NR
420	16	NR	550	586	NR	680	253	NR	810	4	NR	940	0	NR
425	28	NR	555	618	NR	685	220	NR	815	4	NR	945	0	NR
430	47	NR	560	658	NR	690	188	NR	820	3	NR	950	0	NR
435	79	NR	565	706	NR	695	162	NR	825	3	NR	955	0	NR
440	132	NR	570	754	NR	700	138	NR	830	2	NR	960	0	NR
445	236	NR	575	810	NR	705	118	NR	835	2	NR	965	0	NR
450	424	NR	580	864	NR	710	101	NR	840	2	NR	970	0	NR
455	532	NR	585	911	NR	715	86	NR	845	2	NR	975	0	NR
460	420	NR	590	954	NR	720	74	NR	850	1	NR	980	0	NR
465	327	NR	595	985	NR	725	63	NR	855	1	NR	985	0	NR
470	286	NR	600	997	NR	730	53	NR	860	1	NR	990	0	NR
475	225	NR	605	1000	NR	735	46	NR	865	1	NR	995	0	NR
480	191	NR	610	985	NR	740	39	NR	870	1	NR	1000	0	NR
485	194	NR	615	956	NR	745	33	NR	875	1	NR			

REPORT NUMBER: SP3-2602-684-1

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.54**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	213	NR	620	916	NR	750	28	NR	880	1	NR
365	0	NR	495	240	NR	625	865	NR	755	24	NR	885	1	NR
370	0	NR	500	283	NR	630	810	NR	760	20	NR	890	1	NR
375	0	NR	505	329	NR	635	746	NR	765	17	NR	895	1	NR
380	0	NR	510	372	NR	640	683	NR	770	15	NR	900	1	NR
385	0	NR	515	410	NR	645	617	NR	775	13	NR	905	0	NR
390	0	NR	520	441	NR	650	554	NR	780	11	NR	910	0	NR
395	0	NR	525	468	NR	655	494	NR	785	9	NR	915	0	NR
400	1	NR	530	488	NR	660	436	NR	790	8	NR	920	0	NR
405	3	NR	535	511	NR	665	384	NR	795	7	NR	925	0	NR
410	5	NR	540	533	NR	670	336	NR	800	6	NR	930	0	NR
415	9	NR	545	557	NR	675	292	NR	805	5	NR	935	0	NR
420	16	NR	550	586	NR	680	253	NR	810	4	NR	940	0	NR
425	28	NR	555	618	NR	685	220	NR	815	4	NR	945	0	NR
430	47	NR	560	658	NR	690	188	NR	820	3	NR	950	0	NR
435	79	NR	565	706	NR	695	162	NR	825	3	NR	955	0	NR
440	132	NR	570	754	NR	700	138	NR	830	2	NR	960	0	NR
445	236	NR	575	810	NR	705	118	NR	835	2	NR	965	0	NR
450	424	NR	580	864	NR	710	101	NR	840	2	NR	970	0	NR
455	532	NR	585	911	NR	715	86	NR	845	2	NR	975	0	NR
460	420	NR	590	954	NR	720	74	NR	850	1	NR	980	0	NR
465	327	NR	595	985	NR	725	63	NR	855	1	NR	985	0	NR
470	286	NR	600	997	NR	730	53	NR	860	1	NR	990	0	NR
475	225	NR	605	1000	NR	735	46	NR	865	1	NR	995	0	NR
480	191	NR	610	985	NR	740	39	NR	870	1	NR	1000	0	NR
485	194	NR	615	956	NR	745	33	NR	875	1	NR			


REPORT NUMBER: SP3-2602-684-1

TM-30-18


Summary


R_f = 83.6
R_g = 93.7
CIE R_a = 81.4
R_9 = 0.7


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP3-2602-684-1

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 86	CES51 = 92	CES76 = 81
CES02 = 63	CES27 = 92	CES52 = 92	CES77 = 84
CES03 = 31	CES28 = 94	CES53 = 88	CES78 = 81
CES04 = 71	CES29 = 91	CES54 = 88	CES79 = 90
CES05 = 50	CES30 = 90	CES55 = 85	CES80 = 89
CES06 = 51	CES31 = 93	CES56 = 83	CES81 = 70
CES07 = 42	CES32 = 84	CES57 = 82	CES82 = 95
CES08 = 41	CES33 = 97	CES58 = 82	CES83 = 94
CES09 = 29	CES34 = 91	CES59 = 90	CES84 = 91
CES10 = 76	CES35 = 95	CES60 = 90	CES85 = 74
CES11 = 59	CES36 = 82	CES61 = 86	CES86 = 66
CES12 = 65	CES37 = 96	CES62 = 83	CES87 = 84
CES13 = 44	CES38 = 86	CES63 = 86	CES88 = 87
CES14 = 74	CES39 = 98	CES64 = 77	CES89 = 74
CES15 = 72	CES40 = 96	CES65 = 76	CES90 = 89
CES16 = 48	CES41 = 95	CES66 = 74	CES91 = 74
CES17 = 50	CES42 = 97	CES67 = 73	CES92 = 62
CES18 = 57	CES43 = 91	CES68 = 79	CES93 = 76
CES19 = 72	CES44 = 99	CES69 = 84	CES94 = 60
CES20 = 67	CES45 = 93	CES70 = 77	CES95 = 73
CES21 = 87	CES46 = 90	CES71 = 73	CES96 = 83
CES22 = 79	CES47 = 93	CES72 = 91	CES97 = 88
CES23 = 92	CES48 = 82	CES73 = 73	CES98 = 83
CES24 = 91	CES49 = 90	CES74 = 90	CES99 = 75
CES25 = 72	CES50 = 92	CES75 = 77	





REPORT NUMBER: SP3-2602-684-1

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP3-2602-684-1

TM-30-18

Measure Comparisons





(END OF REPORT)