Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: METALUX

Report Number: P1594613

Luminaire Tested: FLXB-2436-N-LOW-3000K

Issue Date: 10/2/2026

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-2019
Report Number:	P1594613
	TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (A2601783A001)
Test Lab:	INNOVATION CENTER
Issue Date:	10/2/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	METALUX
Catalog Number:	FLXB-2436-N-LOW-3000K
Description:	2436 FlexBay Linear High bay at N beam, LOW lumen, 3000K CCT settings
Light Source:	-
Ballast/Driver:	-

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	25851.0 lumens
Efficiency:	N/A
Efficacy:	168.4 lumens/watt
Spacing Criteria (0/90/45):	1.55 / 0.99 / 1.02
Luminous Opening:	Rectangular (W 1.04' x L: 1.48' x H: 0')
CIE Type:	Direct


Input Watts (W):	153.5
Input Voltage (V):	NR
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	NR
Total Harmonic Distortion (THDi):	NR
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594613
CATALOG NUMBER: FLXB-2436-N-LOW-3000K

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594613
CATALOG NUMBER: FLXB-2436-N-LOW-3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	80
3	97	89	83	78	95	88	82	77	85	80	76	82	78	75	80	77	74	72
4	91	81	75	69	89	80	74	69	78	72	68	76	71	67	74	70	66	64
5	85	75	67	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58
6	80	69	61	56	78	68	61	56	66	60	56	65	59	55	63	58	55	53
7	75	64	56	51	73	63	56	51	61	55	51	60	55	50	59	54	50	48
8	70	59	52	47	69	58	52	47	57	51	47	56	50	46	55	50	46	44
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	43	41
10	63	51	44	40	62	51	44	40	50	44	40	49	44	40	48	43	39	38

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	116674	116674	116674	116674
5°	117208	116594	117208	116594
10°	118583	115317	118583	115317
15°	120950	112402	120950	112402
20°	124562	107900	124562	107900
25°	129432	95334	129432	95334
30°	135817	66242	135817	66242
35°	143917	21287	143917	21287
40°	153308	5654	153308	5654
45°	161498	5884	161498	5884
50°	160362	5545	160362	5545
55°	142916	6092	142916	6092
60°	120722	6231	120722	6231
65°	88112	7022	88112	7022
70°	62805	7716	62805	7716
75°	33943	5830	33943	5830
80°	13670	3709	13670	3709
85°	5498	1667	5498	1667

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 47.5°
Luminance: 163097 cd/sqm

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594613
CATALOG NUMBER: FLXB-2436-N-LOW-3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1582.0	6.1
10°-20°	4545.3	17.6
20°-30°	6662.6	25.8
30°-40°	5924.9	22.9
40°-50°	3231.1	12.5
50°-60°	2108.5	8.2
60°-70°	1243.8	4.8
70°-80°	491.9	1.9
80°-90°	61.0	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	12789.8	49.5
0°-40°	18714.7	72.4
0°-60°	24054.3	93.0
0°-90°	25851.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	25851.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	16702	16702	16702	16702	16702	
5°	16715	16627	16715	16627	16715	1595
15°	16724	15542	16724	15542	16724	4744
25°	16792	12369	16792	12369	16792	7771
35°	16876	2496	16876	2496	16876	10597
45°	16348	596	16348	596	16348	12452
55°	11735	500	11735	500	11735	10585
65°	5331	425	5331	425	5331	5558
75°	1258	216	1258	216	1258	1453
85°	69	21	69	21	69	107
90°	1	0	1	0	1	

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594613
CATALOG NUMBER: FLXB-2436-N-LOW-3000K

CANDELA DISTRIBUTION (FULL):

	0°	30°	60°	90°	120°	150°	180°	210°	240°	270°	300°
0°	16702.2	16702.2	16702.2	16702.2	16702.2	16702.2	16702.2	16702.2	16702.2	16702.2	16702.2
0.5°	16702.2	16702.2	16702.2	16702.2	16702.2	16702.2	16702.2	16702.2	16702.2	16702.2	16702.2
1°	16720.7	16715.7	16636.6	16743.3	16625.4	16726.6	16720.7	16715.7	16636.6	16743.3	16625.4
1.5°	16702.2	16713.5	16625.8	16723.0	16610.9	16730.7	16702.2	16713.5	16625.8	16723.0	16610.9
2°	16696.3	16724.3	16625.8	16723.0	16610.9	16730.7	16696.3	16724.3	16625.8	16723.0	16610.9
2.5°	16708.0	16719.9	16606.9	16697.7	16596.9	16717.1	16708.0	16719.9	16606.9	16697.7	16596.9
3°	16708.9	16716.6	16606.9	16697.7	16596.9	16717.1	16708.9	16716.6	16606.9	16697.7	16596.9
3.5°	16712.1	16720.7	16580.6	16688.6	16571.1	16694.5	16712.1	16720.7	16580.6	16688.6	16571.1
4°	16707.2	16726.2	16580.6	16688.6	16571.1	16694.5	16707.2	16726.2	16580.6	16688.6	16571.1
4.5°	16693.2	16711.7	16549.0	16639.4	16544.0	16710.3	16693.2	16711.7	16549.0	16639.4	16544.0
5°	16714.8	16708.9	16562.1	16627.2	16545.8	16679.2	16714.8	16708.9	16562.1	16627.2	16545.8
5.5°	16723.0	16708.9	16528.7	16596.1	16517.4	16679.2	16723.0	16708.9	16528.7	16596.1	16517.4
6°	16703.5	16699.0	16522.8	16579.7	16474.9	16681.5	16703.5	16699.0	16522.8	16579.7	16474.9
6.5°	16706.3	16680.1	16472.6	16531.8	16474.9	16676.4	16706.3	16680.1	16472.6	16531.8	16474.9
7°	16721.1	16691.4	16433.3	16500.6	16437.9	16671.5	16721.1	16691.4	16433.3	16500.6	16437.9
7.5°	16708.5	16655.6	16433.3	16472.6	16437.9	16645.7	16708.5	16655.6	16433.3	16472.6	16437.9
8°	16708.5	16647.5	16381.8	16413.9	16382.2	16637.6	16708.5	16647.5	16381.8	16413.9	16382.2
8.5°	16719.4	16647.5	16381.8	16413.9	16382.2	16627.2	16719.4	16647.5	16381.8	16413.9	16382.2
9°	16719.4	16626.3	16307.7	16321.8	16324.9	16637.1	16719.4	16626.3	16307.7	16321.8	16324.9
9.5°	16717.6	16604.1	16309.9	16302.7	16324.9	16581.1	16717.6	16604.1	16309.9	16302.7	16324.9
10°	16717.6	16589.7	16254.9	16257.1	16307.3	16581.1	16717.6	16589.7	16254.9	16257.1	16307.3
10.5°	16706.3	16593.3	16239.0	16145.9	16239.9	16592.4	16706.3	16593.3	16239.0	16145.9	16239.9
11°	16706.3	16571.6	16169.5	16145.9	16183.9	16592.4	16706.3	16571.6	16169.5	16145.9	16183.9
11.5°	16733.0	16577.0	16142.8	16099.8	16108.4	16549.5	16733.0	16577.0	16142.8	16099.8	16108.4
12°	16733.0	16553.5	16142.8	16099.8	16108.4	16530.5	16733.0	16553.5	16142.8	16099.8	16108.4
12.5°	16726.6	16533.2	15995.1	16066.0	16067.3	16532.7	16726.6	16533.2	15995.1	16066.0	16067.3
13°	16737.9	16517.4	15995.1	15905.1	16009.0	16516.9	16737.9	16517.4	15995.1	15905.1	16009.0
13.5°	16733.4	16486.6	15893.3	15834.1	15910.9	16500.2	16733.4	16486.6	15893.3	15834.1	15910.9
14°	16743.3	16475.8	15881.1	15766.8	15910.9	16460.4	16743.3	16475.8	15881.1	15766.8	15910.9
14.5°	16743.3	16450.5	15789.4	15721.1	15804.3	16455.0	16743.3	16450.5	15789.4	15721.1	15804.3
15°	16724.3	16446.8	15755.0	15542.3	15784.9	16444.2	16724.3	16446.8	15755.0	15542.3	15784.9
15.5°	16747.8	16426.5	15661.6	15542.3	15688.6	16444.2	16747.8	16426.5	15661.6	15542.3	15688.6
16°	16742.9	16408.4	15619.0	15410.8	15553.5	16392.7	16742.9	16408.4	15619.0	15410.8	15553.5
16.5°	16729.3	16376.8	15523.7	15310.4	15553.5	16359.7	16729.3	16376.8	15523.7	15310.4	15553.5
17°	16738.8	16359.7	15372.3	15217.7	15456.4	16352.0	16738.8	16359.7	15372.3	15217.7	15456.4
17.5°	16739.3	16328.1	15372.3	15110.7	15394.4	16324.0	16739.3	16328.1	15372.3	15110.7	15394.4
18°	16734.3	16327.6	15205.5	14998.2	15280.6	16311.3	16734.3	16327.6	15205.5	14998.2	15280.6
18.5°	16734.3	16244.4	15205.5	14886.5	15229.6	16269.8	16734.3	16244.4	15205.5	14886.5	15229.6
19°	16740.2	16211.9	15031.2	14650.7	15229.6	16241.8	16740.2	16211.9	15031.2	14650.7	15229.6
19.5°	16737.9	16209.7	15031.2	14650.7	15056.9	16211.4	16737.9	16209.7	15031.2	14650.7	15056.9
20°	16756.0	16167.2	14827.8	14514.7	14918.6	16207.4	16756.0	16167.2	14827.8	14514.7	14918.6
20.5°	16767.2	16138.3	14776.8	14384.1	14874.4	16131.5	16767.2	16138.3	14776.8	14384.1	14874.4
21°	16760.9	16106.6	14623.5	14384.1	14649.7	16091.7	16760.9	16106.6	14623.5	14384.1	14649.7
21.5°	16764.1	16096.7	14373.3	14217.8	14649.7	16082.7	16764.1	16096.7	14373.3	14217.8	14649.7
22°	16770.0	16042.9	14373.3	13843.7	14422.9	16082.7	16770.0	16042.9	14373.3	13843.7	14422.9

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594613
CATALOG NUMBER: FLXB-2436-N-LOW-3000K

CANDELA DISTRIBUTION (continued):

	0°	30°	60°	90°	120°	150°	180°	210°	240°	270°	300°
22.5°	16755.0	16022.1	14135.5	13491.7	14244.4	15980.6	16755.0	16022.1	14135.5	13491.7	14244.4
23°	16767.7	15957.5	14135.5	13491.7	14155.4	15980.6	16767.7	15957.5	14135.5	13491.7	14155.4
23.5°	16771.3	15873.0	13845.4	13094.4	13980.6	15913.2	16771.3	15873.0	13845.4	13094.4	13980.6
24°	16760.5	15854.5	13845.4	13094.4	13892.9	15913.2	16760.5	15854.5	13845.4	13094.4	13892.9
24.5°	16779.4	15778.1	13534.1	12653.0	13572.9	15832.3	16779.4	15778.1	13534.1	12653.0	13572.9
25°	16792.5	15742.4	13434.7	12368.7	13572.9	15786.2	16792.5	15742.4	13434.7	12368.7	13572.9
25.5°	16785.4	15677.3	13187.5	12147.7	13362.4	15713.1	16785.4	15677.3	13187.5	12147.7	13362.4
26°	16791.7	15652.0	13052.4	11801.6	13156.8	15690.0	16791.7	15652.0	13052.4	11801.6	13156.8
26.5°	16803.4	15578.8	12788.5	11562.1	12910.1	15630.8	16803.4	15578.8	12788.5	11562.1	12910.1
27°	16796.7	15543.6	12361.9	10903.3	12498.4	15507.0	16796.7	15543.6	12361.9	10903.3	12498.4
27.5°	16797.1	15441.0	12361.9	10903.3	12498.4	15507.0	16797.1	15441.0	12361.9	10903.3	12498.4
28°	16806.1	15392.7	11679.6	10113.0	12023.9	15384.5	16806.1	15392.7	11679.6	10113.0	12023.9
28.5°	16806.1	15267.0	11679.6	10113.0	12023.9	15384.5	16806.1	15267.0	11679.6	10113.0	12023.9
29°	16831.5	15155.0	11482.1	9229.1	11488.9	15228.7	16831.5	15155.0	11482.1	9229.1	11488.9
29.5°	16840.9	15094.9	11482.1	9229.1	11488.9	15228.7	16840.9	15094.9	11482.1	9229.1	11488.9
30°	16837.8	14998.6	10864.5	8212.3	10860.3	15052.4	16837.8	14998.6	10864.5	8212.3	10860.3
30.5°	16828.3	14941.3	10107.9	7503.8	10581.6	14987.4	16828.3	14941.3	10107.9	7503.8	10581.6
31°	16853.1	14823.8	10107.9	7078.2	10122.0	14884.3	16853.1	14823.8	10107.9	7078.2	10122.0
31.5°	16870.3	14718.5	9251.7	6329.5	9776.8	14884.3	16870.3	14718.5	9251.7	6329.5	9776.8
32°	16859.0	14581.1	8621.8	5861.3	9264.3	14633.5	16859.0	14581.1	8621.8	5861.3	9264.3
32.5°	16871.2	14480.8	8273.8	4589.7	8279.7	14389.5	16871.2	14480.8	8273.8	4589.7	8279.7
33°	16875.7	14343.4	7627.2	4589.7	8279.7	14389.5	16875.7	14343.4	7627.2	4589.7	8279.7
33.5°	16874.4	14222.8	7197.5	3450.1	7176.2	14078.2	16874.4	14222.8	7197.5	3450.1	7176.2
34°	16874.4	13890.6	6602.8	3450.1	7176.2	14078.2	16874.4	13890.6	6602.8	3450.1	7176.2
34.5°	16884.3	13718.0	6091.3	2496.2	5954.4	13711.7	16884.3	13718.0	6091.3	2496.2	5954.4
35°	16876.2	13545.4	5600.1	2496.2	5954.4	13711.7	16876.2	13545.4	5600.1	2496.2	5954.4
35.5°	16885.6	13336.2	4980.6	1749.2	4666.5	13288.8	16885.6	13336.2	4980.6	1749.2	4666.5
36°	16890.6	13092.2	3998.6	1695.5	3813.8	12952.5	16890.6	13092.2	3998.6	1695.5	3813.8
36.5°	16884.3	12859.4	3998.6	1210.1	3423.4	12764.6	16884.3	12859.4	3998.6	1210.1	3423.4
37°	16890.6	12573.0	3063.2	863.1	2311.8	12176.2	16890.6	12573.0	3063.2	863.1	2311.8
37.5°	16892.4	12307.3	3007.7	863.1	2311.8	12176.2	16892.4	12307.3	3007.7	863.1	2311.8
38°	16886.5	11953.9	2168.1	700.4	1458.2	11462.7	16886.5	11953.9	2168.1	700.4	1458.2
38.5°	16870.3	11636.7	2157.7	700.4	1458.2	11462.7	16870.3	11636.7	2157.7	700.4	1458.2
39°	16848.2	10826.9	1453.7	641.2	924.1	10634.0	16848.2	10826.9	1453.7	641.2	924.1
39.5°	16828.3	10335.8	1444.7	641.2	924.1	10634.0	16828.3	10335.8	1444.7	641.2	924.1
40°	16812.0	9880.7	953.0	620.0	691.8	9658.3	16812.0	9880.7	953.0	620.0	691.8
40.5°	16803.0	9268.0	691.4	620.0	691.8	8903.3	16803.0	9268.0	691.4	620.0	691.8
41°	16744.7	8733.9	691.4	610.5	617.7	8498.9	16744.7	8733.9	691.4	610.5	617.7
41.5°	16727.1	7171.3	601.0	610.5	596.0	7653.0	16727.1	7171.3	601.0	610.5	596.0
42°	16695.8	6571.2	601.0	607.8	585.6	7184.8	16695.8	6571.2	601.0	607.8	585.6
42.5°	16661.9	6571.2	568.5	601.0	569.8	5750.1	16661.9	6571.2	568.5	601.0	569.8
43°	16596.4	5954.8	562.1	601.0	569.8	5750.1	16596.4	5954.8	562.1	601.0	569.8
43.5°	16560.8	5031.2	554.0	596.0	553.5	4411.2	16560.8	5031.2	554.0	596.0	553.5
44°	16432.5	3590.2	551.3	596.0	553.5	4411.2	16432.5	3590.2	551.3	596.0	553.5
44.5°	16388.6	3001.8	546.3	595.6	544.1	3308.2	16388.6	3001.8	546.3	595.6	544.1

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594613
CATALOG NUMBER: FLXB-2436-N-LOW-3000K

CANDELA DISTRIBUTION (continued):

	0°	30°	60°	90°	120°	150°	180°	210°	240°	270°	300°
45°	16347.5	2440.6	540.9	595.6	544.1	3308.2	16347.5	2440.6	540.9	595.6	544.1
45.5°	16224.5	1938.5	534.1	592.4	530.5	2452.3	16224.5	1938.5	534.1	592.4	530.5
46°	15997.3	1633.5	514.2	576.6	524.2	2340.7	15997.3	1633.5	514.2	576.6	524.2
46.5°	15997.3	1316.3	514.2	576.6	514.2	1762.3	15997.3	1316.3	514.2	576.6	514.2
47°	15773.5	1184.4	509.7	567.1	508.3	1282.0	15773.5	1184.4	509.7	567.1	508.3
47.5°	15773.5	1012.2	511.1	567.5	508.3	1282.0	15773.5	1012.2	511.1	567.5	508.3
48°	15468.1	930.4	510.6	554.0	510.2	997.7	15468.1	930.4	510.6	554.0	510.2
48.5°	15288.8	813.4	514.7	554.0	510.2	997.7	15288.8	813.4	514.7	554.0	510.2
49°	15140.5	703.5	513.3	531.4	515.1	800.7	15140.5	703.5	513.3	531.4	515.1
49.5°	14756.0	675.1	513.7	531.4	515.1	800.7	14756.0	675.1	513.7	531.4	515.1
50°	14756.0	620.0	515.1	510.2	516.5	689.5	14756.0	620.0	515.1	510.2	516.5
50.5°	14338.9	597.9	513.7	510.2	520.5	689.5	14338.9	597.9	513.7	510.2	520.5
51°	14338.9	566.6	516.0	505.2	519.6	604.2	14338.9	566.6	516.0	505.2	519.6
51.5°	13896.1	545.8	515.1	505.7	519.6	582.5	13896.1	545.8	515.1	505.7	519.6
52°	13896.1	526.4	515.1	505.7	516.9	543.2	13896.1	526.4	515.1	505.7	516.9
52.5°	13405.8	487.5	502.0	507.4	505.7	503.4	13405.8	487.5	502.0	507.4	505.7
53°	13405.8	487.5	489.8	507.4	505.7	503.4	13405.8	487.5	489.8	507.4	505.7
53.5°	12885.6	470.4	488.5	495.7	491.7	468.1	12885.6	470.4	488.5	495.7	491.7
54°	12562.1	470.4	482.6	495.7	491.7	468.1	12562.1	470.4	482.6	495.7	491.7
54.5°	12329.8	419.8	481.2	500.2	481.7	436.0	12329.8	419.8	481.2	500.2	481.7
55°	11734.7	407.6	481.2	500.2	481.7	436.0	11734.7	407.6	481.2	500.2	481.7
55.5°	11734.7	390.8	476.7	488.5	469.5	396.7	11734.7	390.8	476.7	488.5	469.5
56°	11137.8	380.0	457.3	479.0	469.5	396.7	11137.8	380.0	457.3	479.0	469.5
56.5°	11137.8	365.1	457.3	470.9	452.3	380.5	11137.8	365.1	457.3	470.9	452.3
57°	10513.8	357.0	442.4	467.6	445.1	380.5	10513.8	357.0	442.4	467.6	445.1
57.5°	10513.8	345.7	436.5	469.0	438.8	358.8	10513.8	345.7	436.5	469.0	438.8
58°	9883.0	337.5	435.1	458.7	434.7	345.2	9883.0	337.5	435.1	458.7	434.7
58.5°	9883.0	329.0	432.5	458.7	434.7	340.7	9883.0	329.0	432.5	458.7	434.7
59°	8971.9	320.8	432.5	454.2	425.2	330.3	8971.9	320.8	432.5	454.2	425.2
59.5°	8971.9	314.1	432.0	454.2	425.2	330.3	8971.9	314.1	432.0	454.2	425.2
60°	8640.8	308.7	418.9	446.0	405.8	321.8	8640.8	308.7	418.9	446.0	405.8
60.5°	8331.6	308.7	414.0	446.0	405.8	330.3	8331.6	308.7	414.0	446.0	405.8
61°	8033.9	315.0	410.3	445.1	403.9	338.9	8033.9	315.0	410.3	445.1	403.9
61.5°	7441.4	315.0	400.4	438.3	401.3	338.9	7441.4	315.0	400.4	438.3	401.3
62°	7441.4	332.6	400.4	439.2	401.3	329.0	7441.4	332.6	400.4	439.2	401.3
62.5°	6882.0	332.6	394.1	437.4	393.6	329.0	6882.0	332.6	394.1	437.4	393.6
63°	6882.0	339.8	389.0	437.4	387.3	327.6	6882.0	339.8	389.0	437.4	387.3
63.5°	6338.0	339.8	380.0	433.4	379.1	329.0	6338.0	339.8	380.0	433.4	379.1
64°	6099.0	339.8	380.0	433.4	379.1	339.3	6099.0	339.8	380.0	433.4	379.1
64.5°	5819.3	368.3	375.9	424.8	369.2	346.1	5819.3	368.3	375.9	424.8	369.2
65°	5330.7	368.3	373.7	424.8	369.2	352.5	5330.7	368.3	373.7	424.8	369.2
65.5°	5330.7	382.3	366.5	411.7	357.4	364.7	5330.7	382.3	366.5	411.7	357.4
66°	4852.3	382.3	349.7	411.7	357.4	370.1	4852.3	382.3	349.7	411.7	357.4
66.5°	4852.3	386.4	349.7	406.2	346.6	426.6	4852.3	386.4	349.7	406.2	346.6
67°	4390.4	386.4	339.3	406.2	341.2	426.6	4390.4	386.4	339.3	406.2	341.2

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594613
CATALOG NUMBER: FLXB-2436-N-LOW-3000K

CANDELA DISTRIBUTION (continued):

	0°	30°	60°	90°	120°	150°	180°	210°	240°	270°	300°
67.5°	4390.4	410.7	339.3	404.4	338.0	474.4	4390.4	410.7	339.3	404.4	338.0
68°	3941.3	410.7	325.3	397.2	335.3	488.0	3941.3	410.7	325.3	397.2	335.3
68.5°	3941.3	475.3	318.1	390.4	335.3	485.3	3941.3	475.3	318.1	390.4	335.3
69°	3505.7	475.3	320.8	387.7	324.4	488.9	3505.7	475.3	320.8	387.7	324.4
69.5°	3075.0	520.5	315.0	382.7	324.4	483.5	3075.0	520.5	315.0	382.7	324.4
70°	3075.0	533.2	312.2	377.8	314.1	495.2	3075.0	533.2	312.2	377.8	314.1
70.5°	2671.5	533.2	306.4	371.9	314.1	458.2	2671.5	533.2	306.4	371.9	314.1
71°	2671.5	529.6	301.9	367.4	304.5	469.5	2671.5	529.6	301.9	367.4	304.5
71.5°	2294.6	535.5	286.0	329.0	300.0	447.4	2294.6	535.5	286.0	329.0	300.0
72°	2294.6	501.1	286.0	302.3	285.6	461.8	2294.6	501.1	286.0	302.3	285.6
72.5°	1943.6	494.8	256.7	302.3	277.0	461.8	1943.6	494.8	256.7	302.3	277.0
73°	1943.6	475.8	256.7	290.6	268.0	459.1	1943.6	475.8	256.7	290.6	268.0
73.5°	1629.0	448.2	248.5	286.5	253.0	440.2	1629.0	448.2	248.5	286.5	253.0
74°	1629.0	435.1	234.1	259.3	253.0	421.6	1629.0	435.1	234.1	259.3	253.0
74.5°	1352.0	428.3	220.5	259.3	225.1	414.0	1352.0	428.3	220.5	259.3	225.1
75°	1257.6	376.4	220.5	216.0	225.1	400.8	1257.6	376.4	220.5	216.0	225.1
75.5°	1104.8	357.0	205.2	216.0	203.3	374.6	1104.8	357.0	205.2	216.0	203.3
76°	889.3	343.4	205.2	188.4	186.2	375.1	889.3	343.4	205.2	188.4	186.2
76.5°	889.3	330.3	188.9	188.4	178.1	352.0	889.3	330.3	188.9	188.4	178.1
77°	712.6	310.9	171.7	155.9	171.7	321.3	712.6	310.9	171.7	155.9	171.7
77.5°	712.6	314.1	151.4	155.9	126.6	293.7	712.6	314.1	151.4	155.9	126.6
78°	563.5	306.8	136.9	137.4	118.9	293.7	563.5	306.8	136.9	137.4	118.9
78.5°	563.5	269.8	109.8	125.6	118.9	264.8	563.5	269.8	109.8	125.6	118.9
79°	440.6	269.8	103.0	125.6	108.4	246.2	440.6	269.8	103.0	125.6	108.4
79.5°	406.2	239.5	103.0	92.2	108.4	228.7	406.2	239.5	103.0	92.2	108.4
80°	339.8	201.5	95.3	92.2	82.7	223.7	339.8	201.5	95.3	92.2	82.7
80.5°	259.8	201.5	95.3	55.2	82.7	200.1	259.8	201.5	95.3	55.2	82.7
81°	259.8	170.8	67.8	55.2	58.7	175.8	259.8	170.8	67.8	55.2	58.7
81.5°	194.7	170.8	67.8	51.5	58.7	147.7	194.7	170.8	67.8	51.5	58.7
82°	194.7	131.5	61.9	49.7	46.6	136.0	194.7	131.5	61.9	49.7	46.6
82.5°	145.1	131.5	44.7	44.3	39.8	136.0	145.1	131.5	44.7	44.3	39.8
83°	145.1	95.8	40.7	41.2	35.3	124.3	145.1	95.8	40.7	41.2	35.3
83.5°	106.2	95.8	32.1	30.2	28.5	124.3	106.2	95.8	32.1	30.2	28.5
84°	106.2	68.6	32.1	23.5	28.5	120.2	106.2	68.6	32.1	23.5	28.5
84.5°	75.4	68.6	23.9	23.5	21.7	72.8	75.4	68.6	23.9	23.5	21.7
85°	68.6	37.5	23.9	20.8	19.9	68.6	68.6	37.5	23.9	20.8	19.9
85.5°	52.4	25.3	17.6	20.8	15.8	51.1	52.4	25.3	17.6	20.8	15.8
86°	34.8	25.3	17.6	16.3	15.8	50.1	34.8	25.3	17.6	16.3	15.8
86.5°	34.8	19.0	14.0	16.3	11.3	37.9	34.8	19.0	14.0	16.3	11.3
87°	25.3	15.4	11.3	9.5	8.6	36.6	25.3	15.4	11.3	9.5	8.6
87.5°	21.2	7.7	10.8	7.7	7.2	23.5	21.2	7.7	10.8	7.7	7.2
88°	19.0	7.7	6.8	5.4	6.8	23.5	19.0	7.7	6.8	5.4	6.8
88.5°	19.0	4.0	6.8	4.9	5.4	13.1	19.0	4.0	6.8	4.9	5.4
89°	19.0	4.0	4.9	4.9	3.2	8.2	19.0	4.0	4.9	4.9	3.2
89.5°	19.0	2.7	4.9	4.9	3.2	8.2	19.0	2.7	4.9	4.9	3.2

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594613
CATALOG NUMBER: FLXB-2436-N-LOW-3000K

CANDELA DISTRIBUTION (continued):

	0°	30°	60°	90°	120°	150°	180°	210°	240°	270°	300°
90°	*0.9*	1.8	2.3	0.5	0.5	2.3	0.9	1.8	2.3	0.5	0.5

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594613
CATALOG NUMBER: FLXB-2436-N-LOW-3000K

CANDELA DISTRIBUTION (continued):

	330°	360°
0°	16702.2	16702.2
0.5°	16702.2	16702.2
1°	16726.6	16720.7
1.5°	16730.7	16702.2
2°	16730.7	16696.3
2.5°	16717.1	16708.0
3°	16717.1	16708.9
3.5°	16694.5	16712.1
4°	16694.5	16707.2
4.5°	16710.3	16693.2
5°	16679.2	16714.8
5.5°	16679.2	16723.0
6°	16681.5	16703.5
6.5°	16676.4	16706.3
7°	16671.5	16721.1
7.5°	16645.7	16708.5
8°	16637.6	16708.5
8.5°	16627.2	16719.4
9°	16637.1	16719.4
9.5°	16581.1	16717.6
10°	16581.1	16717.6
10.5°	16592.4	16706.3
11°	16592.4	16706.3
11.5°	16549.5	16733.0
12°	16530.5	16733.0
12.5°	16532.7	16726.6
13°	16516.9	16737.9
13.5°	16500.2	16733.4
14°	16460.4	16743.3
14.5°	16455.0	16743.3
15°	16444.2	16724.3
15.5°	16444.2	16747.8
16°	16392.7	16742.9
16.5°	16359.7	16729.3
17°	16352.0	16738.8
17.5°	16324.0	16739.3
18°	16311.3	16734.3
18.5°	16269.8	16734.3
19°	16241.8	16740.2
19.5°	16211.4	16737.9
20°	16207.4	16756.0
20.5°	16131.5	16767.2
21°	16091.7	16760.9
21.5°	16082.7	16764.1
22°	16082.7	16770.0

TEST NUMBER: P1594613
CATALOG NUMBER: FLXB-2436-N-LOW-3000K

CANDELA DISTRIBUTION (continued):

	330°	360°
22.5°	15980.6	16755.0
23°	15980.6	16767.7
23.5°	15913.2	16771.3
24°	15913.2	16760.5
24.5°	15832.3	16779.4
25°	15786.2	16792.5
25.5°	15713.1	16785.4
26°	15690.0	16791.7
26.5°	15630.8	16803.4
27°	15507.0	16796.7
27.5°	15507.0	16797.1
28°	15384.5	16806.1
28.5°	15384.5	16806.1
29°	15228.7	16831.5
29.5°	15228.7	16840.9
30°	15052.4	16837.8
30.5°	14987.4	16828.3
31°	14884.3	16853.1
31.5°	14884.3	16870.3
32°	14633.5	16859.0
32.5°	14389.5	16871.2
33°	14389.5	16875.7
33.5°	14078.2	16874.4
34°	14078.2	16874.4
34.5°	13711.7	16884.3
35°	13711.7	16876.2
35.5°	13288.8	16885.6
36°	12952.5	16890.6
36.5°	12764.6	16884.3
37°	12176.2	16890.6
37.5°	*12176.2*	*16892.4*
38°	11462.7	16886.5
38.5°	11462.7	16870.3
39°	10634.0	16848.2
39.5°	10634.0	16828.3
40°	9658.3	16812.0
40.5°	8903.3	16803.0
41°	8498.9	16744.7
41.5°	7653.0	16727.1
42°	7184.8	16695.8
42.5°	5750.1	16661.9
43°	5750.1	16596.4
43.5°	4411.2	16560.8
44°	4411.2	16432.5
44.5°	3308.2	16388.6

TEST NUMBER: P1594613
CATALOG NUMBER: FLXB-2436-N-LOW-3000K

CANDELA DISTRIBUTION (continued):

	330°	360°
45°	3308.2	16347.5
45.5°	2452.3	16224.5
46°	2340.7	15997.3
46.5°	1762.3	15997.3
47°	1282.0	15773.5
47.5°	1282.0	15773.5
48°	997.7	15468.1
48.5°	997.7	15288.8
49°	800.7	15140.5
49.5°	800.7	14756.0
50°	689.5	14756.0
50.5°	689.5	14338.9
51°	604.2	14338.9
51.5°	582.5	13896.1
52°	543.2	13896.1
52.5°	503.4	13405.8
53°	503.4	13405.8
53.5°	468.1	12885.6
54°	468.1	12562.1
54.5°	436.0	12329.8
55°	436.0	11734.7
55.5°	396.7	11734.7
56°	396.7	11137.8
56.5°	380.5	11137.8
57°	380.5	10513.8
57.5°	358.8	10513.8
58°	345.2	9883.0
58.5°	340.7	9883.0
59°	330.3	8971.9
59.5°	330.3	8971.9
60°	321.8	8640.8
60.5°	330.3	8331.6
61°	338.9	8033.9
61.5°	338.9	7441.4
62°	329.0	7441.4
62.5°	329.0	6882.0
63°	327.6	6882.0
63.5°	329.0	6338.0
64°	339.3	6099.0
64.5°	346.1	5819.3
65°	352.5	5330.7
65.5°	364.7	5330.7
66°	370.1	4852.3
66.5°	426.6	4852.3
67°	426.6	4390.4

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594613
CATALOG NUMBER: FLXB-2436-N-LOW-3000K

CANDELA DISTRIBUTION (continued):

	330°	360°
67.5°	474.4	4390.4
68°	488.0	3941.3
68.5°	485.3	3941.3
69°	488.9	3505.7
69.5°	483.5	3075.0
70°	495.2	3075.0
70.5°	458.2	2671.5
71°	469.5	2671.5
71.5°	447.4	2294.6
72°	461.8	2294.6
72.5°	461.8	1943.6
73°	459.1	1943.6
73.5°	440.2	1629.0
74°	421.6	1629.0
74.5°	414.0	1352.0
75°	400.8	1257.6
75.5°	374.6	1104.8
76°	375.1	889.3
76.5°	352.0	889.3
77°	321.3	712.6
77.5°	293.7	712.6
78°	293.7	563.5
78.5°	264.8	563.5
79°	246.2	440.6
79.5°	228.7	406.2
80°	223.7	339.8
80.5°	200.1	259.8
81°	175.8	259.8
81.5°	147.7	194.7
82°	136.0	194.7
82.5°	136.0	145.1
83°	124.3	145.1
83.5°	124.3	106.2
84°	120.2	106.2
84.5°	72.8	75.4
85°	68.6	68.6
85.5°	51.1	52.4
86°	50.1	34.8
86.5°	37.9	34.8
87°	36.6	25.3
87.5°	23.5	21.2
88°	23.5	19.0
88.5°	13.1	19.0
89°	8.2	19.0
89.5°	8.2	19.0

TEST NUMBER: P1594613
CATALOG NUMBER: FLXB-2436-N-LOW-3000K

CANDELA DISTRIBUTION (continued):

	330°	360°
90°	2.3	0.9

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594613
CATALOG NUMBER: FLXB-2436-N-LOW-3000K

CIE UGR TABLE:

Reflectances:											
	Ceiling	0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
	Wall	0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
	Reference plane	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room Dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	26.5	27.8	26.8	28.1	28.4	11.0	12.2	11.3	12.5	12.9
	3H	28.2	29.4	28.6	29.7	30.1	13.7	14.8	14.1	15.1	15.5
	4H	28.5	29.6	28.9	29.9	30.3	14.5	15.6	14.9	15.9	16.3
	6H	28.6	29.5	29.0	29.9	30.3	14.8	15.8	15.3	16.2	16.6
	8H	28.5	29.4	29.0	29.8	30.2	14.9	15.8	15.3	16.2	16.6
	12H	28.5	29.4	28.9	29.7	30.2	14.8	15.7	15.3	16.1	16.5
4H	2H	26.3	27.3	26.7	27.7	28.0	11.7	12.7	12.1	13.1	13.5
	3H	28.0	28.9	28.5	29.3	29.7	14.6	15.4	15.0	15.8	16.2
	4H	28.4	29.1	28.8	29.5	30.0	15.5	16.3	15.9	16.7	17.1
	6H	28.4	29.1	28.9	29.5	30.0	15.9	16.5	16.3	17.0	17.4
	8H	28.4	29.0	28.9	29.5	29.9	15.9	16.5	16.3	16.9	17.4
	12H	28.4	28.9	28.8	29.4	29.9	15.9	16.4	16.3	16.9	17.4
8H	4H	28.2	28.9	28.7	29.3	29.8	16.2	16.8	16.7	17.3	17.7
	6H	28.3	28.8	28.8	29.3	29.8	16.6	17.1	17.1	17.6	18.0
	8H	28.3	28.7	28.8	29.2	29.7	16.6	17.0	17.1	17.5	18.0
	12H	28.2	28.6	28.8	29.1	29.7	16.6	17.0	17.1	17.5	18.0
12H	4H	28.2	28.7	28.7	29.2	29.7	16.3	16.8	16.8	17.3	17.8
	6H	28.3	28.7	28.8	29.2	29.7	16.7	17.1	17.2	17.6	18.2
	8H	28.2	28.6	28.8	29.1	29.7	16.7	17.1	17.3	17.6	18.2

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP3-2602-684-1

Test Date: 02/20/2026

Luminaire Tested: HLBX-2436-W-HI-3000K

Data in this report applies to families of products including HLBX-2436*

Report Generated By FNC07603 / LDUCLS01DT01661
Version: v7.05


Test Information

Test Method:	LM-79-2019
Report Number:	SP3-2602-684-1
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP3 - 3M SPHERE
Measurement Geometry:	4π
Issue Date:	02/27/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	Metalux
Catalog Number:	**HLBX-2436-W-HI-3000K**
Description:	LDS HLBX 2436 W beam, HI lumen, 3000K CCT settings

Spectral Parameters

CCT (K):	2947	CRI (Ra):	81.4		
CIE u':	0.2523	R1:	79.9	R9:	0.7
CIE v':	0.5232	R2:	91.2	R10:	79.6
Duv:	0.0005	R3:	95.4	R11:	77.4
CIE x:	0.4415	R4:	78.4	R12:	68.4
CIE y:	0.4069	R5:	79.9	R13:	82.7
CIE z:	0.1516	R6:	89.4	R14:	98.3
Peak Wavelength (nm):	605	R7:	81.1	R15:	71.7
Dominant Wavelength (nm):	582	R8:	55.6		
Purity:	54.65632				

Rf:	83.6
Rg:	93.7



Test Conditions


Stabilization Time:	31M
Operation Time:	1H 31M
Sphere Temperature (°C):	25.0

REPORT NUMBER: SP3-2602-684-1


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	3M SPHERE IN02505	1/10/2026	7/10/2026
Power Meter	XITRON INXT2011006	10/21/2025	10/21/2026
AC Power Source	CHROMA 61604 IN6064A	10/20/2025	10/20/2026
DC Power Source	EYSIGHT N5770A IN0534	10/20/2025	10/20/2026
Sphere Thermometer	TANDD IN4036E	10/21/2025	10/21/2026

REPORT NUMBER: SP3-2602-684-1

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2947K
CIE x = 0.4415
CIE y = 0.4069
Duv = 0.0005

Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP3-2602-684-1

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	213	NR	620	916	NR	750	28	NR	880	1	NR
365	0	NR	495	240	NR	625	865	NR	755	24	NR	885	1	NR
370	0	NR	500	283	NR	630	810	NR	760	20	NR	890	1	NR
375	0	NR	505	329	NR	635	746	NR	765	17	NR	895	1	NR
380	0	NR	510	372	NR	640	683	NR	770	15	NR	900	1	NR
385	0	NR	515	410	NR	645	617	NR	775	13	NR	905	0	NR
390	0	NR	520	441	NR	650	554	NR	780	11	NR	910	0	NR
395	0	NR	525	468	NR	655	494	NR	785	9	NR	915	0	NR
400	1	NR	530	488	NR	660	436	NR	790	8	NR	920	0	NR
405	3	NR	535	511	NR	665	384	NR	795	7	NR	925	0	NR
410	5	NR	540	533	NR	670	336	NR	800	6	NR	930	0	NR
415	9	NR	545	557	NR	675	292	NR	805	5	NR	935	0	NR
420	16	NR	550	586	NR	680	253	NR	810	4	NR	940	0	NR
425	28	NR	555	618	NR	685	220	NR	815	4	NR	945	0	NR
430	47	NR	560	658	NR	690	188	NR	820	3	NR	950	0	NR
435	79	NR	565	706	NR	695	162	NR	825	3	NR	955	0	NR
440	132	NR	570	754	NR	700	138	NR	830	2	NR	960	0	NR
445	236	NR	575	810	NR	705	118	NR	835	2	NR	965	0	NR
450	424	NR	580	864	NR	710	101	NR	840	2	NR	970	0	NR
455	532	NR	585	911	NR	715	86	NR	845	2	NR	975	0	NR
460	420	NR	590	954	NR	720	74	NR	850	1	NR	980	0	NR
465	327	NR	595	985	NR	725	63	NR	855	1	NR	985	0	NR
470	286	NR	600	997	NR	730	53	NR	860	1	NR	990	0	NR
475	225	NR	605	1000	NR	735	46	NR	865	1	NR	995	0	NR
480	191	NR	610	985	NR	740	39	NR	870	1	NR	1000	0	NR
485	194	NR	615	956	NR	745	33	NR	875	1	NR			

REPORT NUMBER: SP3-2602-684-1

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.32**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	213	NR	620	916	NR	750	28	NR	880	1	NR
365	0	NR	495	240	NR	625	865	NR	755	24	NR	885	1	NR
370	0	NR	500	283	NR	630	810	NR	760	20	NR	890	1	NR
375	0	NR	505	329	NR	635	746	NR	765	17	NR	895	1	NR
380	0	NR	510	372	NR	640	683	NR	770	15	NR	900	1	NR
385	0	NR	515	410	NR	645	617	NR	775	13	NR	905	0	NR
390	0	NR	520	441	NR	650	554	NR	780	11	NR	910	0	NR
395	0	NR	525	468	NR	655	494	NR	785	9	NR	915	0	NR
400	1	NR	530	488	NR	660	436	NR	790	8	NR	920	0	NR
405	3	NR	535	511	NR	665	384	NR	795	7	NR	925	0	NR
410	5	NR	540	533	NR	670	336	NR	800	6	NR	930	0	NR
415	9	NR	545	557	NR	675	292	NR	805	5	NR	935	0	NR
420	16	NR	550	586	NR	680	253	NR	810	4	NR	940	0	NR
425	28	NR	555	618	NR	685	220	NR	815	4	NR	945	0	NR
430	47	NR	560	658	NR	690	188	NR	820	3	NR	950	0	NR
435	79	NR	565	706	NR	695	162	NR	825	3	NR	955	0	NR
440	132	NR	570	754	NR	700	138	NR	830	2	NR	960	0	NR
445	236	NR	575	810	NR	705	118	NR	835	2	NR	965	0	NR
450	424	NR	580	864	NR	710	101	NR	840	2	NR	970	0	NR
455	532	NR	585	911	NR	715	86	NR	845	2	NR	975	0	NR
460	420	NR	590	954	NR	720	74	NR	850	1	NR	980	0	NR
465	327	NR	595	985	NR	725	63	NR	855	1	NR	985	0	NR
470	286	NR	600	997	NR	730	53	NR	860	1	NR	990	0	NR
475	225	NR	605	1000	NR	735	46	NR	865	1	NR	995	0	NR
480	191	NR	610	985	NR	740	39	NR	870	1	NR	1000	0	NR
485	194	NR	615	956	NR	745	33	NR	875	1	NR			

REPORT NUMBER: SP3-2602-684-1

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.54**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	213	NR	620	916	NR	750	28	NR	880	1	NR
365	0	NR	495	240	NR	625	865	NR	755	24	NR	885	1	NR
370	0	NR	500	283	NR	630	810	NR	760	20	NR	890	1	NR
375	0	NR	505	329	NR	635	746	NR	765	17	NR	895	1	NR
380	0	NR	510	372	NR	640	683	NR	770	15	NR	900	1	NR
385	0	NR	515	410	NR	645	617	NR	775	13	NR	905	0	NR
390	0	NR	520	441	NR	650	554	NR	780	11	NR	910	0	NR
395	0	NR	525	468	NR	655	494	NR	785	9	NR	915	0	NR
400	1	NR	530	488	NR	660	436	NR	790	8	NR	920	0	NR
405	3	NR	535	511	NR	665	384	NR	795	7	NR	925	0	NR
410	5	NR	540	533	NR	670	336	NR	800	6	NR	930	0	NR
415	9	NR	545	557	NR	675	292	NR	805	5	NR	935	0	NR
420	16	NR	550	586	NR	680	253	NR	810	4	NR	940	0	NR
425	28	NR	555	618	NR	685	220	NR	815	4	NR	945	0	NR
430	47	NR	560	658	NR	690	188	NR	820	3	NR	950	0	NR
435	79	NR	565	706	NR	695	162	NR	825	3	NR	955	0	NR
440	132	NR	570	754	NR	700	138	NR	830	2	NR	960	0	NR
445	236	NR	575	810	NR	705	118	NR	835	2	NR	965	0	NR
450	424	NR	580	864	NR	710	101	NR	840	2	NR	970	0	NR
455	532	NR	585	911	NR	715	86	NR	845	2	NR	975	0	NR
460	420	NR	590	954	NR	720	74	NR	850	1	NR	980	0	NR
465	327	NR	595	985	NR	725	63	NR	855	1	NR	985	0	NR
470	286	NR	600	997	NR	730	53	NR	860	1	NR	990	0	NR
475	225	NR	605	1000	NR	735	46	NR	865	1	NR	995	0	NR
480	191	NR	610	985	NR	740	39	NR	870	1	NR	1000	0	NR
485	194	NR	615	956	NR	745	33	NR	875	1	NR			


REPORT NUMBER: SP3-2602-684-1

TM-30-18


Summary


R_f = 83.6
R_g = 93.7
CIE R_a = 81.4
R_9 = 0.7


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP3-2602-684-1

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 86	CES51 = 92	CES76 = 81
CES02 = 63	CES27 = 92	CES52 = 92	CES77 = 84
CES03 = 31	CES28 = 94	CES53 = 88	CES78 = 81
CES04 = 71	CES29 = 91	CES54 = 88	CES79 = 90
CES05 = 50	CES30 = 90	CES55 = 85	CES80 = 89
CES06 = 51	CES31 = 93	CES56 = 83	CES81 = 70
CES07 = 42	CES32 = 84	CES57 = 82	CES82 = 95
CES08 = 41	CES33 = 97	CES58 = 82	CES83 = 94
CES09 = 29	CES34 = 91	CES59 = 90	CES84 = 91
CES10 = 76	CES35 = 95	CES60 = 90	CES85 = 74
CES11 = 59	CES36 = 82	CES61 = 86	CES86 = 66
CES12 = 65	CES37 = 96	CES62 = 83	CES87 = 84
CES13 = 44	CES38 = 86	CES63 = 86	CES88 = 87
CES14 = 74	CES39 = 98	CES64 = 77	CES89 = 74
CES15 = 72	CES40 = 96	CES65 = 76	CES90 = 89
CES16 = 48	CES41 = 95	CES66 = 74	CES91 = 74
CES17 = 50	CES42 = 97	CES67 = 73	CES92 = 62
CES18 = 57	CES43 = 91	CES68 = 79	CES93 = 76
CES19 = 72	CES44 = 99	CES69 = 84	CES94 = 60
CES20 = 67	CES45 = 93	CES70 = 77	CES95 = 73
CES21 = 87	CES46 = 90	CES71 = 73	CES96 = 83
CES22 = 79	CES47 = 93	CES72 = 91	CES97 = 88
CES23 = 92	CES48 = 82	CES73 = 73	CES98 = 83
CES24 = 91	CES49 = 90	CES74 = 90	CES99 = 75
CES25 = 72	CES50 = 92	CES75 = 77	





REPORT NUMBER: SP3-2602-684-1

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP3-2602-684-1

TM-30-18

Measure Comparisons





(END OF REPORT)