Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: METALUX

Report Number: P1594680

Luminaire Tested: FLXB-4860-W-MED-4000K

Issue Date: 10/2/2026

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-2019
Report Number:	P1594680
	TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (A2601781A001)
Test Lab:	INNOVATION CENTER
Issue Date:	10/2/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	METALUX
Catalog Number:	FLXB-4860-W-MED-4000K
Description:	4860 FlexBay Linear High bay at W beam, MED lumen, 4000K CCT settings
Light Source:	-
Ballast/Driver:	-

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	54360.0 lumens
Efficiency:	N/A
Efficacy:	163.7 lumens/watt
Spacing Criteria (0/90/45):	1.28 / 1.33 / 1.41
Luminous Opening:	Rectangular (W 1.04' x L: 2.12' x H: 0')
CIE Type:	Direct


Input Watts (W):	332
Input Voltage (V):	NR
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	NR
Total Harmonic Distortion (THDi):	NR
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594680
CATALOG NUMBER: FLXB-4860-W-MED-4000K

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594680
CATALOG NUMBER: FLXB-4860-W-MED-4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87
2	101	94	87	82	98	92	86	81	88	83	79	85	81	78	82	79	76	74
3	93	83	75	69	90	81	74	69	78	72	67	76	71	66	73	69	65	63
4	85	74	65	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54
5	78	66	57	51	76	65	57	51	63	56	50	61	55	50	59	54	49	47
6	72	60	51	45	70	59	50	45	57	50	44	55	49	44	54	48	43	41
7	67	54	46	40	65	53	45	39	52	44	39	50	44	39	49	43	39	37
8	62	49	41	35	61	49	41	35	47	40	35	46	40	35	45	39	35	33
9	58	45	37	32	57	45	37	32	43	36	32	42	36	31	41	36	31	29
10	55	42	34	29	53	41	34	29	40	33	29	39	33	29	38	33	28	27

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	100811	100811	100811	100811
5°	100937	100949	100937	100949
10°	101017	100973	101017	100973
15°	101032	100821	101032	100821
20°	100893	100890	100893	100890
25°	100903	101259	100903	101259
30°	100586	103150	100586	103150
35°	99945	105770	99945	105770
40°	98858	102119	98858	102119
45°	97609	92381	97609	92381
50°	95140	86789	95140	86789
55°	91559	76774	91559	76774
60°	85521	63601	85521	63601
65°	77169	42904	77169	42904
70°	65567	20284	65567	20284
75°	52976	8359	52976	8359
80°	34958	4679	34958	4679
85°	22239	4051	22239	4051

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 60°
Vertical Angle: 45.5°
Luminance: 101468 cd/sqm

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594680
CATALOG NUMBER: FLXB-4860-W-MED-4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1967.4	3.6
10°-20°	5662.9	10.4
20°-30°	8682.2	16.0
30°-40°	10750.4	19.8
40°-50°	10980.5	20.2
50°-60°	8960.6	16.5
60°-70°	5491.5	10.1
70°-80°	1650.8	3.0
80°-90°	181.8	0.3
90°-100°	2.4	0.0
100°-110°	1.1	0.0
110°-120°	2.9	0.0
120°-130°	4.7	0.0
130°-140°	5.7	0.0
140°-150°	5.7	0.0
150°-160°	4.9	0.0
160°-170°	3.3	0.0
170°-180°	1.2	0.0
0°-30°	16312.5	30.0
0°-40°	27062.8	49.8
0°-60°	47004.0	86.5
0°-90°	54328.0	99.9
90°-120°	6.4	0.0
90°-150°	22.6	0.0
90°-180°	32.0	0.1
0°-180°	54360.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	20732	20732	20732	20732	20732	
5°	20679	20681	20679	20681	20679	1966
15°	20069	20027	20069	20027	20069	5667
25°	18807	18873	18807	18873	18807	8672
35°	16837	17818	16837	17818	16837	10539
45°	14194	13434	14194	13434	14194	10958
55°	10800	9056	10800	9056	10800	9667
65°	6707	3729	6707	3729	6707	6696
75°	2820	445	2820	445	2820	2943
85°	399	73	399	73	399	462
90°	49	14	49	14	49	32
95°	1	0	1	0	1	1
105°	1	1	1	1	1	2
115°	3	2	3	2	3	3
125°	6	4	6	4	6	5
135°	8	8	8	8	8	6
145°	9	9	9	9	9	6
155°	11	11	11	11	11	5
165°	11	11	11	11	11	3
175°	12	12	12	12	12	1
180°	12	12	12	12	12	

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594680
CATALOG NUMBER: FLXB-4860-W-MED-4000K

CANDELA DISTRIBUTION (FULL):

	0°	30°	60°	90°	120°	150°	180°	210°	240°	270°	300°
0°	20732.0	20732.0	20732.0	20732.0	20732.0	*20732.0*	20732.0	20732.0	20732.0	20732.0	20732.0
0.5°	20732.0	20732.0	20732.0	20732.0	20732.0	*20732.0*	20732.0	20732.0	20732.0	20732.0	20732.0
1°	20753.9	20755.8	20765.2	20769.6	20765.8	*20777.7*	20753.9	20755.8	20765.2	20769.6	20765.8
1.5°	20746.4	20744.5	20765.2	20747.0	20760.2	*20765.2*	20746.4	20744.5	20765.2	20747.0	20760.2
2°	*20724.5*	*20744.5*	*20730.8*	*20748.9*	*20760.2*	*20782.1*	*20724.5*	*20744.5*	*20730.8*	*20748.9*	*20760.2*
2.5°	20719.5	20737.0	20730.8	20750.8	20748.9	*20782.1*	20719.5	20737.0	20730.8	20750.8	20748.9
3°	20726.4	20737.0	20742.0	20719.5	20748.9	*20737.7*	20726.4	20737.0	20742.0	20719.5	20748.9
3.5°	20712.0	20715.8	20742.0	20728.9	20732.0	*20740.8*	20712.0	20715.8	20742.0	20728.9	20732.0
4°	20698.9	20710.7	20700.7	20710.1	20732.0	*20742.7*	20698.9	20710.7	20700.7	20710.1	20732.0
4.5°	20666.3	20688.9	20700.7	20688.9	20705.1	*20720.1*	20666.3	20688.9	20700.7	20688.9	20705.1
5°	20678.8	20682.0	20683.8	20681.3	20705.1	*20709.5*	20678.8	20682.0	20683.8	20681.3	20705.1
5.5°	20670.1	20669.4	20673.8	20682.0	20675.7	*20692.6*	20670.1	20669.4	20673.8	20682.0	20675.7
6°	20651.3	20657.6	20657.6	20648.2	20643.2	*20673.8*	20651.3	20657.6	20657.6	20648.2	20643.2
6.5°	20611.3	20633.2	20605.0	20631.3	20643.2	*20660.1*	20611.3	20633.2	20605.0	20631.3	20643.2
7°	20614.4	20596.9	20605.0	20620.0	20603.7	*20657.6*	20614.4	20596.9	20605.0	20620.0	20603.7
7.5°	20591.2	20596.9	20585.6	20601.2	20603.7	*20590.6*	20591.2	20596.9	20585.6	20601.2	20603.7
8°	20547.4	20555.6	20585.6	20553.1	20561.8	*20590.6*	20547.4	20555.6	20585.6	20553.1	20561.8
8.5°	20528.7	20555.6	20515.5	20524.9	20561.8	*20574.3*	20528.7	20555.6	20515.5	20524.9	20561.8
9°	20484.9	20511.1	20515.5	20489.2	20510.5	*20534.9*	20484.9	20511.1	20515.5	20489.2	20510.5
9.5°	20482.4	20489.9	20481.7	20458.6	20510.5	*20504.3*	20482.4	20489.9	20481.7	20458.6	20510.5
10°	20458.6	20454.8	20451.7	20449.8	20450.4	*20481.1*	20458.6	20454.8	20451.7	20449.8	20450.4
10.5°	20426.7	20431.0	20415.4	20402.9	20389.7	*20455.4*	20426.7	20431.0	20415.4	20402.9	20389.7
11°	20371.0	20394.7	20340.3	20366.6	20389.7	*20422.9*	20371.0	20394.7	20340.3	20366.6	20389.7
11.5°	20362.2	20369.7	20340.3	20344.1	20319.0	*20401.0*	20362.2	20369.7	20340.3	20344.1	20319.0
12°	20331.5	20329.0	20283.4	20317.2	20319.0	*20355.3*	20331.5	20329.0	20283.4	20317.2	20319.0
12.5°	20303.4	20257.1	20283.4	20262.1	20246.4	*20307.8*	20303.4	20257.1	20283.4	20262.1	20246.4
13°	20250.2	20257.1	20181.4	20200.1	20246.4	*20264.0*	20250.2	20257.1	20181.4	20200.1	20246.4
13.5°	20225.2	20180.7	20181.4	20150.7	20163.8	*20264.0*	20225.2	20180.7	20181.4	20150.7	20163.8
14°	20153.2	20180.7	20122.5	20103.8	20163.8	*20156.3*	20153.2	20180.7	20122.5	20103.8	20163.8
14.5°	20111.9	20096.9	20122.5	20078.7	20082.5	*20121.9*	20111.9	20096.9	20122.5	20078.7	20082.5
15°	20069.3	20058.7	20022.4	20027.4	20082.5	*20086.9*	20069.3	20058.7	20022.4	20027.4	20082.5
15.5°	20001.8	20011.1	19966.7	19974.9	19993.6	*20035.6*	20001.8	20011.1	19966.7	19974.9	19993.6
16°	19980.5	19969.2	19934.8	19940.4	19902.3	*19994.3*	19980.5	19969.2	19934.8	19940.4	19902.3
16.5°	19937.9	19913.5	19852.8	19907.3	19902.3	*19937.3*	19937.9	19913.5	19852.8	19907.3	19902.3
17°	19892.3	19812.8	19852.8	19842.2	19810.9	*19879.7*	19892.3	19812.8	19852.8	19842.2	19810.9
17.5°	19823.4	19812.8	19730.8	19800.3	19810.9	*19802.1*	19823.4	19812.8	19730.8	19800.3	19810.9
18°	19730.2	19712.7	19730.8	19763.4	19710.2	*19802.1*	19730.2	19712.7	19730.8	19763.4	19710.2
18.5°	19691.4	19712.7	19653.2	19651.3	19662.6	*19664.5*	19691.4	19712.7	19653.2	19651.3	19662.6
19°	19631.9	19601.3	19653.2	19617.5	19606.9	*19619.4*	19631.9	19601.3	19653.2	19617.5	19606.9
19.5°	19577.5	19553.7	19531.2	19617.5	19606.9	*19576.3*	19577.5	19553.7	19531.2	19617.5	19606.9
20°	19497.4	19487.4	19469.9	19496.8	19492.4	*19508.7*	19497.4	19487.4	19469.9	19496.8	19492.4
20.5°	19463.0	19430.5	19431.1	19446.1	19492.4	*19446.7*	19463.0	19430.5	19431.1	19446.1	19492.4
21°	19406.0	19366.6	19319.7	19407.9	19380.4	*19384.1*	19406.0	19366.6	19319.7	19407.9	19380.4
21.5°	19343.5	19309.7	19319.7	19339.1	19264.6	*19318.4*	19343.5	19309.7	19319.7	19339.1	19264.6
22°	19257.1	19235.8	19187.7	19278.4	19264.6	*19258.4*	19257.1	19235.8	19187.7	19278.4	19264.6

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594680
CATALOG NUMBER: FLXB-4860-W-MED-4000K

CANDELA DISTRIBUTION (continued):

	0°	30°	60°	90°	120°	150°	180°	210°	240°	270°	300°
22.5°	19214.6	19110.7	19187.7	19235.2	19141.3	*19207.1*	19214.6	19110.7	19187.7	19235.2	19141.3
23°	19145.7	19110.7	19079.4	19174.5	19141.3	*19044.4*	19145.7	19110.7	19079.4	19174.5	19141.3
23.5°	19009.3	18979.3	19079.4	19053.7	19018.7	*19044.4*	19009.3	18979.3	19079.4	19053.7	19018.7
24°	18948.0	18979.3	18928.0	19004.3	19018.7	*18933.6*	18948.0	18979.3	18928.0	19004.3	19018.7
24.5°	18856.6	18838.5	18928.0	18931.1	18883.5	*18849.1*	18856.6	18838.5	18928.0	18931.1	18883.5
25°	18806.6	18767.8	18812.8	18872.9	18883.5	*18769.0*	18806.6	18767.8	18812.8	18872.9	18883.5
25.5°	18734.0	18687.0	18744.0	18824.7	18752.1	*18700.2*	18734.0	18687.0	18744.0	18824.7	18752.1
26°	18658.3	18612.0	18667.0	18760.9	18613.2	*18628.8*	18658.3	18612.0	18667.0	18760.9	18613.2
26.5°	18558.8	18533.7	18528.7	18691.4	18613.2	*18548.1*	18558.8	18533.7	18528.7	18691.4	18613.2
27°	18501.8	18461.1	18528.7	18673.3	18475.5	*18479.9*	18501.8	18461.1	18528.7	18673.3	18475.5
27.5°	18423.6	18380.4	18407.3	18615.7	18475.5	*18298.5*	18423.6	18380.4	18407.3	18615.7	18475.5
28°	18347.9	18217.7	18407.3	18576.3	18352.3	*18298.5*	18347.9	18217.7	18407.3	18576.3	18352.3
28.5°	18248.4	18217.7	18240.9	18498.1	18352.3	*18158.9*	18248.4	18217.7	18240.9	18498.1	18352.3
29°	18076.3	18053.8	18240.9	18444.2	18223.4	*18158.9*	18076.3	18053.8	18240.9	18444.2	18223.4
29.5°	18006.2	18053.8	18132.6	18405.5	18223.4	*17965.6*	18006.2	18053.8	18132.6	18405.5	18223.4
30°	17914.2	17878.6	18132.6	18371.0	18100.1	*17809.7*	17914.2	17878.6	18132.6	18371.0	18100.1
30.5°	17825.4	17792.8	17983.1	18339.8	18100.1	*17809.7*	17825.4	17792.8	17983.1	18339.8	18100.1
31°	17709.6	17705.9	17983.1	18289.1	17974.3	*17714.6*	17709.6	17705.9	17983.1	18289.1	17974.3
31.5°	17638.3	17615.8	17858.5	18292.8	17847.9	*17630.1*	17638.3	17615.8	17858.5	18292.8	17847.9
32°	17545.7	17525.0	17746.5	18261.5	17847.9	*17533.2*	17545.7	17525.0	17746.5	18261.5	17847.9
32.5°	17449.9	17332.9	17746.5	18113.9	17743.4	*17435.5*	17449.9	17332.9	17746.5	18113.9	17743.4
33°	17332.3	17332.9	17616.4	18113.9	17743.4	*17268.4*	17332.3	17332.9	17616.4	18113.9	17743.4
33.5°	17139.5	17241.5	17616.4	18022.5	17608.2	*17268.4*	17139.5	17241.5	17616.4	18022.5	17608.2
34°	17050.1	17151.4	17536.3	17944.9	17608.2	*17051.3*	17050.1	17151.4	17536.3	17944.9	17608.2
34.5°	16939.9	16949.3	17536.3	17886.7	17464.9	*16962.5*	16939.9	16949.3	17536.3	17886.7	17464.9
35°	16836.7	16856.7	17378.6	17817.9	17464.9	*16877.4*	16836.7	16856.7	17378.6	17817.9	17464.9
35.5°	16709.0	16755.3	17251.6	17779.7	17332.9	*16770.3*	16709.0	16755.3	17251.6	17779.7	17332.9
36°	16620.8	16655.2	17206.5	17592.6	17270.3	*16669.6*	16620.8	16655.2	17206.5	17592.6	17270.3
36.5°	16515.0	16562.0	17135.2	17524.4	17193.4	*16573.2*	16515.0	16562.0	17135.2	17524.4	17193.4
37°	16403.0	16460.0	17038.8	17295.4	17014.4	*16473.7*	16403.0	16460.0	17038.8	17295.4	17014.4
37.5°	16269.7	16366.1	16878.6	17235.3	17014.4	*16381.1*	16269.7	16366.1	16878.6	17235.3	17014.4
38°	16174.0	16170.2	16878.6	17003.1	16936.2	*16295.4*	16174.0	16170.2	16878.6	17003.1	16936.2
38.5°	16057.0	16170.2	16753.4	16652.1	16936.2	*16043.2*	16057.0	16170.2	16753.4	16652.1	16936.2
39°	15821.1	15954.4	16753.4	16536.9	16782.2	*16043.2*	15821.1	15954.4	16753.4	16536.9	16782.2
39.5°	15709.1	15954.4	16558.8	16296.6	16782.2	*15962.5*	15709.1	15954.4	16558.8	16296.6	16782.2
40°	15573.9	15745.3	16558.8	16087.6	16459.3	*15863.0*	15573.9	15745.3	16558.8	16087.6	16459.3
40.5°	15470.0	15639.0	16403.6	15857.4	16459.3	*15645.2*	15470.0	15639.0	16403.6	15857.4	16459.3
41°	15348.0	15521.3	16214.0	15608.9	16200.9	*15645.2*	15348.0	15521.3	16214.0	15608.9	16200.9
41.5°	15226.0	15420.0	16145.8	15378.7	15910.6	*15445.0*	15226.0	15420.0	16145.8	15378.7	15910.6
42°	15080.8	15291.7	15853.0	15083.3	15910.6	*15445.0*	15080.8	15291.7	15853.0	15083.3	15910.6
42.5°	14973.8	15192.8	15853.0	14879.3	15538.2	*15224.1*	14973.8	15192.8	15853.0	14879.3	15538.2
43°	14846.8	15055.8	15511.9	14632.1	15538.2	*15097.7*	14846.8	15055.8	15511.9	14632.1	15538.2
43.5°	14579.6	14790.4	15511.9	14400.0	15126.5	*14968.2*	14579.6	14790.4	15511.9	14400.0	15126.5
44°	14579.6	14790.4	15049.5	13923.8	15126.5	*14859.3*	14579.6	14790.4	15049.5	13923.8	15126.5
44.5°	14313.0	14495.1	15049.5	13674.7	14700.3	*14700.3*	14313.0	14495.1	15049.5	13674.7	14700.3

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594680
CATALOG NUMBER: FLXB-4860-W-MED-4000K

CANDELA DISTRIBUTION (continued):

	0°	30°	60°	90°	120°	150°	180°	210°	240°	270°	300°
45°	14194.1	14383.7	14625.9	13433.8	14700.3	*14356.2*	14194.1	14383.7	14625.9	13433.8	14700.3
45.5°	14194.1	14179.1	14625.9	13216.0	14261.7	*14356.2*	14194.1	14179.1	14625.9	13216.0	14261.7
46°	13917.5	14052.7	14137.1	13109.7	14261.7	*14000.7*	13917.5	14052.7	14137.1	13109.7	14261.7
46.5°	13760.4	13833.7	13897.5	12876.9	13742.3	*14000.7*	13760.4	13833.7	13897.5	12876.9	13742.3
47°	13638.4	13687.9	13403.1	12796.1	13257.3	*13595.9*	13638.4	13687.9	13403.1	12796.1	13257.3
47.5°	13492.0	13481.4	13160.3	12571.5	13257.3	*13397.5*	13492.0	13481.4	13160.3	12571.5	13257.3
48°	13351.2	13127.2	13160.3	12322.5	12795.5	*13186.6*	13351.2	13127.2	13160.3	12322.5	12795.5
48.5°	13181.6	13127.2	12681.0	12322.5	12795.5	*12988.9*	13181.6	13127.2	12681.0	12322.5	12795.5
49°	12884.4	12783.0	12681.0	11940.7	12323.7	*12783.0*	12884.4	12783.0	12681.0	11940.7	12323.7
49.5°	12746.7	12783.0	12238.6	11646.6	12323.7	*12552.1*	12746.7	12783.0	12238.6	11646.6	12323.7
50°	12576.5	12416.9	12238.6	11472.7	11819.3	*12360.6*	12576.5	12416.9	12238.6	11472.7	11819.3
50.5°	12432.0	12217.3	11756.1	11152.3	11819.3	*11973.9*	12432.0	12217.3	11756.1	11152.3	11819.3
51°	12249.9	12040.9	11470.8	11107.9	11338.8	*11973.9*	12249.9	12040.9	11470.8	11107.9	11338.8
51.5°	12113.4	11831.2	11234.9	10858.8	11072.2	*11592.2*	12113.4	11831.2	11234.9	10858.8	11072.2
52°	11945.7	11652.9	10985.8	10781.8	10842.5	*11592.2*	11945.7	11652.9	10985.8	10781.8	10842.5
52.5°	11794.3	11442.6	10700.5	10431.4	10428.9	*11229.2*	11794.3	11442.6	10700.5	10431.4	10428.9
53°	11609.7	11261.8	10211.1	10380.7	10428.9	*11229.2*	11609.7	11261.8	10211.1	10380.7	10428.9
53.5°	11468.3	10881.3	10211.1	10097.9	10122.3	*10869.4*	11468.3	10881.3	10211.1	10097.9	10122.3
54°	11297.5	10881.3	9833.2	9826.3	10122.3	*10679.8*	11297.5	10881.3	9833.2	9826.3	10122.3
54.5°	10958.9	10499.6	9833.2	9278.1	9788.1	*10509.0*	10958.9	10499.6	9833.2	9278.1	9788.1
55°	10800.0	10499.6	9582.3	9056.0	9788.1	*10336.9*	10800.0	10499.6	9582.3	9056.0	9788.1
55.5°	10609.1	10156.1	9582.3	8797.5	9495.9	*10181.7*	10609.1	10156.1	9582.3	8797.5	9495.9
56°	10452.7	9966.5	9356.4	8605.4	9495.9	*9892.6*	10452.7	9966.5	9356.4	8605.4	9495.9
56.5°	10268.1	9850.7	9134.8	8352.0	9219.3	*9892.6*	10268.1	9850.7	9134.8	8352.0	9219.3
57°	10095.4	9668.0	9031.0	8215.0	8805.1	*9651.1*	10095.4	9668.0	9031.0	8215.0	8805.1
57.5°	9893.3	9536.6	8761.9	7866.4	8805.1	*9651.1*	9893.3	9536.6	8761.9	7866.4	8805.1
58°	9727.4	9352.0	8761.9	7678.1	8230.6	*9331.9*	9727.4	9352.0	8761.9	7678.1	8230.6
58.5°	9539.1	9191.2	8199.3	7397.7	8230.6	*9165.5*	9539.1	9191.2	8199.3	7397.7	8230.6
59°	9165.5	8832.0	8199.3	7182.5	7729.4	*8988.4*	9165.5	8832.0	8199.3	7182.5	7729.4
59.5°	9165.5	8832.0	7513.5	6721.3	7729.4	*8915.2*	9165.5	8832.0	7513.5	6721.3	7729.4
60°	8793.8	8476.5	7513.5	6539.8	7200.6	*8733.7*	8793.8	8476.5	7513.5	6539.8	7200.6
60.5°	8619.2	8287.6	6937.8	6195.6	7200.6	*8511.0*	8619.2	8287.6	6937.8	6195.6	7200.6
61°	8425.2	8131.1	6937.8	6063.6	6620.5	*8511.0*	8425.2	8131.1	6937.8	6063.6	6620.5
61.5°	8242.5	7943.4	6491.6	5743.8	6620.5	*8203.7*	8242.5	7943.4	6491.6	5743.8	6620.5
62°	8039.1	7810.7	6256.3	5625.6	6133.7	*8203.7*	8039.1	7810.7	6256.3	5625.6	6133.7
62.5°	7862.0	7628.0	5996.7	5625.6	5742.6	*7834.5*	7862.0	7628.0	5996.7	5625.6	5742.6
63°	7669.3	7456.5	5600.5	5403.4	5742.6	*7834.5*	7669.3	7456.5	5600.5	5403.4	5742.6
63.5°	7478.4	7091.1	5600.5	4876.5	5273.3	*7431.5*	7478.4	7091.1	5600.5	4876.5	5273.3
64°	7279.5	7091.1	5163.1	4583.7	5273.3	*7267.6*	7279.5	7091.1	5163.1	4583.7	5273.3
64.5°	6899.6	6802.0	4952.9	3980.5	4780.8	*7056.1*	6899.6	6802.0	4952.9	3980.5	4780.8
65°	6706.9	6802.0	4628.7	3728.9	4780.8	*6905.9*	6706.9	6802.0	4628.7	3728.9	4780.8
65.5°	6518.5	6400.3	4628.7	3407.3	4320.9	*6673.1*	6518.5	6400.3	4628.7	3407.3	4320.9
66°	6322.7	6230.1	4185.7	3161.3	4320.9	*6246.3*	6322.7	6230.1	4185.7	3161.3	4320.9
66.5°	6128.1	5993.5	3925.4	2874.7	3854.1	*6246.3*	6128.1	5993.5	3925.4	2874.7	3854.1
67°	5939.1	5792.7	3703.2	2676.4	3406.0	*5762.6*	5939.1	5792.7	3703.2	2676.4	3406.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594680
CATALOG NUMBER: FLXB-4860-W-MED-4000K

CANDELA DISTRIBUTION (continued):

	0°	30°	60°	90°	120°	150°	180°	210°	240°	270°	300°
67.5°	5556.7	5566.1	3469.8	2434.8	3406.0	5762.6	5556.7	5566.1	3469.8	2434.8	3406.0
68°	5556.7	5424.7	3222.0	2287.8	2917.3	5303.3	5556.7	5424.7	3222.0	2287.8	2917.3
68.5°	5363.4	5185.0	2752.7	2041.2	2917.3	5303.3	5363.4	5185.0	2752.7	2041.2	2917.3
69°	5173.8	4730.7	2752.7	1932.3	2487.4	4865.3	5173.8	4730.7	2752.7	1932.3	2487.4
69.5°	4988.6	4730.7	2361.0	1605.1	2487.4	4629.4	4988.6	4730.7	2361.0	1605.1	2487.4
70°	4611.8	4290.2	2361.0	1426.7	2097.5	4364.7	4611.8	4290.2	2361.0	1426.7	2097.5
70.5°	4409.7	4069.3	1933.6	1302.2	2097.5	3838.4	4409.7	4069.3	1933.6	1302.2	2097.5
71°	4223.9	3838.4	1933.6	1148.9	1713.3	3838.4	4223.9	3838.4	1933.6	1148.9	1713.3
71.5°	4023.6	3635.0	1551.3	1058.8	1713.3	3337.2	4023.6	3635.0	1551.3	1058.8	1713.3
72°	3857.8	3421.0	1467.4	935.5	1381.7	3337.2	3857.8	3421.0	1467.4	935.5	1381.7
72.5°	3659.4	3217.7	1249.0	888.6	1106.3	2884.8	3659.4	3217.7	1249.0	888.6	1106.3
73°	3494.2	3028.0	990.0	760.3	1106.3	2884.8	3494.2	3028.0	990.0	760.3	1106.3
73.5°	3306.5	2794.6	990.0	727.8	884.8	2455.5	3306.5	2794.6	990.0	727.8	884.8
74°	3153.8	2637.6	812.2	605.7	884.8	2234.6	3153.8	2637.6	812.2	605.7	884.8
74.5°	2819.7	2250.9	812.2	571.9	755.3	2075.0	2819.7	2250.9	812.2	571.9	755.3
75°	2819.7	2250.9	696.5	444.9	755.3	1887.3	2819.7	2250.9	696.5	444.9	755.3
75.5°	2499.9	1886.0	696.5	393.0	638.3	1734.6	2499.9	1886.0	696.5	393.0	638.3
76°	2314.1	1665.1	568.8	360.4	638.3	1566.9	2314.1	1665.1	568.8	360.4	638.3
76.5°	2197.0	1521.2	568.8	332.9	504.4	1416.7	2197.0	1521.2	568.8	332.9	504.4
77°	2013.1	1335.4	456.8	317.3	504.4	1103.2	2013.1	1335.4	456.8	317.3	504.4
77.5°	1912.3	1210.8	412.4	276.0	399.9	1103.2	1912.3	1210.8	412.4	276.0	399.9
78°	1734.0	1052.5	373.0	269.7	336.7	815.4	1734.0	1052.5	373.0	269.7	336.7
78.5°	1653.3	976.2	308.5	235.9	336.7	815.4	1653.3	976.2	308.5	235.9	336.7
79°	1479.3	770.9	308.5	230.3	292.9	580.7	1479.3	770.9	308.5	230.3	292.9
79.5°	1413.6	770.9	260.3	197.7	292.9	462.4	1413.6	770.9	260.3	197.7	292.9
80°	1248.4	594.5	260.3	167.1	237.2	409.9	1248.4	594.5	260.3	167.1	237.2
80.5°	1039.4	594.5	197.1	155.8	237.2	329.8	1039.4	594.5	197.1	155.8	237.2
81°	1000.6	434.9	197.1	149.6	172.7	297.9	1000.6	434.9	197.1	149.6	172.7
81.5°	847.9	324.8	156.4	142.7	172.7	227.2	847.9	324.8	156.4	142.7	172.7
82°	820.4	302.9	147.7	138.3	144.6	227.2	820.4	302.9	147.7	138.3	144.6
82.5°	684.0	228.4	137.7	129.5	128.3	180.2	684.0	228.4	137.7	129.5	128.3
83°	664.6	212.1	120.1	118.9	128.3	180.2	664.6	212.1	120.1	118.9	128.3
83.5°	538.8	168.3	120.1	103.9	103.9	143.9	538.8	168.3	120.1	103.9	103.9
84°	525.6	156.4	92.0	93.9	103.9	143.9	525.6	156.4	92.0	93.9	103.9
84.5°	416.1	121.4	92.0	82.0	77.0	112.6	416.1	121.4	92.0	82.0	77.0
85°	398.6	121.4	68.8	72.6	77.0	96.4	398.6	121.4	68.8	72.6	77.0
85.5°	290.4	88.9	68.8	63.8	65.7	86.4	290.4	88.9	68.8	63.8	65.7
86°	213.4	88.9	58.8	60.7	65.7	62.6	213.4	88.9	58.8	60.7	65.7
86.5°	213.4	62.6	58.8	45.1	54.4	62.6	213.4	62.6	58.8	45.1	54.4
87°	152.7	50.1	41.9	38.8	54.4	40.7	152.7	50.1	41.9	38.8	54.4
87.5°	152.7	45.1	35.7	25.0	34.4	40.7	152.7	45.1	35.7	25.0	34.4
88°	106.4	34.4	20.7	19.4	18.1	23.8	106.4	34.4	20.7	19.4	18.1
88.5°	106.4	33.2	15.6	17.5	18.1	23.8	106.4	33.2	15.6	17.5	18.1
89°	72.6	21.3	15.6	16.9	15.6	8.8	72.6	21.3	15.6	16.9	15.6
89.5°	72.6	21.3	11.9	13.8	15.6	5.6	72.6	21.3	11.9	13.8	15.6

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594680
CATALOG NUMBER: FLXB-4860-W-MED-4000K

CANDELA DISTRIBUTION (continued):

	0°	30°	60°	90°	120°	150°	180°	210°	240°	270°	300°
90°	48.8	9.4	11.9	13.8	11.3	5.6	48.8	9.4	11.9	13.8	11.3
90.5°	31.9	9.4	5.0	7.5	11.3	0.6	31.9	9.4	5.0	7.5	11.3
91°	31.9	6.3	5.0	1.9	4.4	0.6	31.9	6.3	5.0	1.9	4.4
91.5°	18.8	1.3	0.6	1.9	4.4	0.6	18.8	1.3	0.6	1.9	4.4
92°	18.8	0.6	0.6	0.6	0.6	0.6	18.8	0.6	0.6	0.6	0.6
92.5°	8.1	0.6	0.6	0.6	0.6	0.6	8.1	0.6	0.6	0.6	0.6
93°	8.1	0.6	0.6	0.6	0.6	0.6	8.1	0.6	0.6	0.6	0.6
93.5°	1.3	0.6	0.6	0.6	0.6	0.6	1.3	0.6	0.6	0.6	0.6
94°	1.3	0.6	0.6	0.0	0.6	0.6	1.3	0.6	0.6	0.0	0.6
94.5°	0.6	0.6	0.6	0.0	0.0	0.6	0.6	0.6	0.6	0.0	0.0
95°	0.6	0.6	0.0	0.0	0.0	0.6	0.6	0.6	0.0	0.0	0.0
95.5°	0.6	0.6	0.0	0.0	0.0	0.6	0.6	0.6	0.0	0.0	0.0
96°	0.6	0.6	0.0	0.0	0.0	0.6	0.6	0.6	0.0	0.0	0.0
96.5°	0.6	0.6	0.0	0.0	0.0	0.6	0.6	0.6	0.0	0.0	0.0
97°	0.6	0.6	0.0	0.0	0.0	0.6	0.6	0.6	0.0	0.0	0.0
97.5°	0.6	0.6	0.0	0.0	0.0	0.6	0.6	0.6	0.0	0.0	0.0
98°	0.6	0.6	0.0	0.0	0.0	0.6	0.6	0.6	0.0	0.0	0.0
98.5°	0.6	0.6	0.0	0.0	0.0	0.6	0.6	0.6	0.0	0.0	0.0
99°	0.6	0.6	0.0	0.0	0.0	0.6	0.6	0.6	0.0	0.0	0.0
99.5°	0.6	0.6	0.0	0.0	0.0	0.6	0.6	0.6	0.0	0.0	0.0
100°	1.3	0.6	0.0	0.0	0.0	0.6	1.3	0.6	0.0	0.0	0.0
100.5°	1.3	0.6	0.0	0.0	0.0	0.6	1.3	0.6	0.0	0.0	0.0
101°	1.3	0.6	0.0	0.0	0.0	0.6	1.3	0.6	0.0	0.0	0.0
101.5°	1.3	0.6	0.0	0.0	0.0	0.6	1.3	0.6	0.0	0.0	0.0
102°	1.3	0.6	0.0	0.6	0.0	0.6	1.3	0.6	0.0	0.6	0.0
102.5°	1.3	0.6	0.0	0.6	0.0	0.6	1.3	0.6	0.0	0.6	0.0
103°	1.3	0.6	0.0	0.6	0.0	0.6	1.3	0.6	0.0	0.6	0.0
103.5°	1.3	0.6	0.0	0.6	0.0	0.6	1.3	0.6	0.0	0.6	0.0
104°	1.3	0.6	1.3	0.6	0.0	0.6	1.3	0.6	1.3	0.6	0.0
104.5°	1.3	1.3	1.3	0.6	0.6	0.6	1.3	1.3	1.3	0.6	0.6
105°	1.3	1.3	1.3	0.6	0.6	1.3	1.3	1.3	1.3	0.6	0.6
105.5°	1.9	1.9	1.3	0.6	0.6	1.3	1.9	1.9	1.3	0.6	0.6
106°	1.9	1.9	1.3	0.6	0.6	1.3	1.9	1.9	1.3	0.6	0.6
106.5°	1.9	1.9	1.3	0.6	1.3	1.3	1.9	1.9	1.3	0.6	1.3
107°	1.9	1.9	1.3	0.6	1.3	1.9	1.9	1.9	1.3	0.6	1.3
107.5°	1.9	1.9	1.3	0.6	1.3	1.9	1.9	1.9	1.3	0.6	1.3
108°	1.9	1.9	1.3	0.6	1.3	1.9	1.9	1.9	1.3	0.6	1.3
108.5°	1.9	1.9	1.3	0.6	1.3	1.9	1.9	1.9	1.3	0.6	1.3
109°	1.9	1.9	1.3	0.6	1.3	1.9	1.9	1.9	1.3	0.6	1.3
109.5°	1.9	1.9	1.3	0.6	1.3	1.9	1.9	1.9	1.3	0.6	1.3
110°	1.9	2.5	1.3	1.3	1.9	1.9	1.9	2.5	1.3	1.3	1.9
110.5°	2.5	2.5	1.9	1.3	1.9	1.9	2.5	2.5	1.9	1.3	1.9
111°	2.5	2.5	1.9	1.9	1.9	1.9	2.5	2.5	1.9	1.9	1.9
111.5°	3.1	2.5	1.9	1.9	1.9	1.9	3.1	2.5	1.9	1.9	1.9
112°	3.1	3.1	1.9	1.9	1.9	1.9	3.1	3.1	1.9	1.9	1.9

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594680
CATALOG NUMBER: FLXB-4860-W-MED-4000K

CANDELA DISTRIBUTION (continued):

	0°	30°	60°	90°	120°	150°	180°	210°	240°	270°	300°
112.5°	3.1	3.1	2.5	1.9	1.9	3.1	3.1	3.1	2.5	1.9	1.9
113°	3.1	3.1	2.5	1.9	1.9	3.1	3.1	3.1	2.5	1.9	1.9
113.5°	3.1	3.1	2.5	1.9	1.9	3.1	3.1	3.1	2.5	1.9	1.9
114°	3.1	3.1	2.5	1.9	2.5	3.1	3.1	3.1	2.5	1.9	2.5
114.5°	3.1	3.1	2.5	1.9	3.1	3.1	3.1	3.1	2.5	1.9	3.1
115°	3.1	3.1	3.1	1.9	3.1	3.1	3.1	3.1	3.1	1.9	3.1
115.5°	3.8	3.1	3.1	2.5	3.1	3.1	3.8	3.1	3.1	2.5	3.1
116°	3.8	3.1	3.1	2.5	3.1	3.1	3.8	3.1	3.1	2.5	3.1
116.5°	3.8	3.8	3.1	3.1	3.1	3.1	3.8	3.8	3.1	3.1	3.1
117°	3.8	3.8	3.1	3.1	3.1	3.1	3.8	3.8	3.1	3.1	3.1
117.5°	3.8	3.8	3.1	3.1	3.1	3.1	3.8	3.8	3.1	3.1	3.1
118°	3.8	3.8	3.1	3.1	3.1	4.4	3.8	3.8	3.1	3.1	3.1
118.5°	3.8	3.8	3.1	3.1	3.1	4.4	3.8	3.8	3.1	3.1	3.1
119°	4.4	4.4	3.1	3.1	3.1	4.4	4.4	4.4	3.1	3.1	3.1
119.5°	4.4	4.4	4.4	3.1	3.1	4.4	4.4	4.4	4.4	3.1	3.1
120°	4.4	4.4	4.4	3.8	4.4	4.4	4.4	4.4	4.4	3.8	4.4
120.5°	4.4	4.4	4.4	3.8	4.4	4.4	4.4	4.4	4.4	3.8	4.4
121°	4.4	5.0	4.4	3.8	4.4	4.4	4.4	5.0	4.4	3.8	4.4
121.5°	5.0	5.0	4.4	3.8	4.4	4.4	5.0	5.0	4.4	3.8	4.4
122°	5.0	5.0	4.4	4.4	4.4	4.4	5.0	5.0	4.4	4.4	4.4
122.5°	5.0	5.0	4.4	4.4	4.4	4.4	5.0	5.0	4.4	4.4	4.4
123°	5.0	5.0	4.4	4.4	4.4	4.4	5.0	5.0	4.4	4.4	4.4
123.5°	5.0	5.0	4.4	4.4	4.4	5.6	5.0	5.0	4.4	4.4	4.4
124°	5.0	5.0	5.0	4.4	5.0	5.6	5.0	5.0	5.0	4.4	5.0
124.5°	5.6	5.6	5.6	4.4	5.6	5.6	5.6	5.6	5.6	4.4	5.6
125°	5.6	5.6	5.6	4.4	5.6	5.6	5.6	5.6	5.6	4.4	5.6
125.5°	5.6	5.6	5.6	5.0	5.6	5.6	5.6	5.6	5.6	5.0	5.6
126°	5.6	5.6	5.6	5.0	5.6	5.6	5.6	5.6	5.6	5.0	5.6
126.5°	5.6	6.3	5.6	5.6	5.6	5.6	5.6	6.3	5.6	5.6	5.6
127°	5.6	6.3	5.6	5.6	5.6	5.6	5.6	6.3	5.6	5.6	5.6
127.5°	5.6	6.3	5.6	5.6	5.6	5.6	5.6	6.3	5.6	5.6	5.6
128°	6.3	6.3	5.6	5.6	5.6	6.3	6.3	6.3	5.6	5.6	5.6
128.5°	6.3	6.3	6.3	5.6	5.6	6.3	6.3	6.3	6.3	5.6	5.6
129°	6.3	6.3	6.9	6.3	6.3	6.9	6.3	6.3	6.9	6.3	6.3
129.5°	6.3	6.3	6.9	6.3	6.3	6.9	6.3	6.3	6.9	6.3	6.3
130°	6.3	6.9	6.9	6.3	6.9	6.9	6.3	6.9	6.9	6.3	6.9
130.5°	6.3	6.9	6.9	6.3	6.9	6.9	6.3	6.9	6.9	6.3	6.9
131°	6.9	6.9	6.9	6.3	6.9	6.9	6.9	6.9	6.9	6.3	6.9
131.5°	6.9	6.9	6.9	6.9	6.9	6.9	6.9	6.9	6.9	6.9	6.9
132°	6.9	6.9	6.9	6.9	6.9	6.9	6.9	6.9	6.9	6.9	6.9
132.5°	6.9	6.9	6.9	6.9	6.9	6.9	6.9	6.9	6.9	6.9	6.9
133°	6.9	6.9	6.9	6.9	6.9	6.9	6.9	6.9	6.9	6.9	6.9
133.5°	6.9	6.9	6.9	6.9	6.9	6.9	6.9	6.9	6.9	6.9	6.9
134°	6.9	7.5	7.5	6.9	6.9	6.9	6.9	7.5	7.5	6.9	6.9
134.5°	7.5	7.5	7.5	7.5	6.9	7.5	7.5	7.5	7.5	7.5	6.9

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594680
CATALOG NUMBER: FLXB-4860-W-MED-4000K

CANDELA DISTRIBUTION (continued):

	0°	30°	60°	90°	120°	150°	180°	210°	240°	270°	300°
135°	7.5	7.5	7.5	7.5	6.9	7.5	7.5	7.5	7.5	7.5	6.9
135.5°	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5
136°	7.5	7.5	8.1	7.5	7.5	8.1	7.5	7.5	8.1	7.5	7.5
136.5°	7.5	8.1	8.1	7.5	8.1	8.1	7.5	8.1	8.1	7.5	8.1
137°	7.5	8.1	8.1	8.1	8.1	8.1	7.5	8.1	8.1	8.1	8.1
137.5°	7.5	8.1	8.1	7.5	8.1	8.1	7.5	8.1	8.1	7.5	8.1
138°	8.1	8.1	8.1	7.5	8.1	8.1	8.1	8.1	8.1	7.5	8.1
138.5°	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1
139°	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1
139.5°	8.1	8.8	8.1	8.1	8.1	8.1	8.1	8.8	8.1	8.1	8.1
140°	8.1	8.8	8.1	8.1	8.1	8.1	8.1	8.8	8.1	8.1	8.1
140.5°	8.1	8.8	8.1	8.1	8.1	8.1	8.1	8.8	8.1	8.1	8.1
141°	8.8	8.8	8.1	8.8	8.1	8.1	8.8	8.8	8.1	8.8	8.1
141.5°	8.8	8.8	8.8	8.8	8.1	8.1	8.8	8.8	8.8	8.8	8.1
142°	8.8	8.8	8.8	8.8	8.1	8.8	8.8	8.8	8.8	8.8	8.1
142.5°	8.8	8.8	9.4	8.8	8.1	8.8	8.8	8.8	9.4	8.8	8.1
143°	8.8	8.8	9.4	8.8	9.4	8.8	8.8	8.8	9.4	8.8	9.4
143.5°	8.8	8.8	9.4	8.8	9.4	9.4	8.8	8.8	9.4	8.8	9.4
144°	8.8	8.8	9.4	9.4	9.4	9.4	8.8	8.8	9.4	9.4	9.4
144.5°	8.8	9.4	9.4	9.4	9.4	9.4	8.8	9.4	9.4	9.4	9.4
145°	8.8	9.4	9.4	9.4	9.4	9.4	8.8	9.4	9.4	9.4	9.4
145.5°	9.4	9.4	9.4	9.4	9.4	9.4	9.4	9.4	9.4	9.4	9.4
146°	9.4	9.4	9.4	9.4	9.4	9.4	9.4	9.4	9.4	9.4	9.4
146.5°	9.4	9.4	9.4	9.4	9.4	9.4	9.4	9.4	9.4	9.4	9.4
147°	9.4	9.4	9.4	9.4	9.4	9.4	9.4	9.4	9.4	9.4	9.4
147.5°	9.4	9.4	9.4	9.4	9.4	9.4	9.4	9.4	9.4	9.4	9.4
148°	9.4	9.4	9.4	9.4	9.4	9.4	9.4	9.4	9.4	9.4	9.4
148.5°	9.4	10.0	9.4	9.4	9.4	9.4	9.4	10.0	9.4	9.4	9.4
149°	9.4	10.0	10.0	9.4	9.4	9.4	9.4	10.0	10.0	9.4	9.4
149.5°	9.4	10.0	10.6	9.4	9.4	9.4	9.4	10.0	10.6	9.4	9.4
150°	9.4	10.0	10.0	10.0	10.0	9.4	9.4	10.0	10.0	10.0	10.0
150.5°	9.4	10.0	10.0	10.0	10.0	9.4	9.4	10.0	10.0	10.0	10.0
151°	10.0	10.0	10.0	10.0	10.6	10.0	10.0	10.0	10.0	10.0	10.6
151.5°	10.0	10.0	10.6	10.0	10.6	10.6	10.0	10.0	10.6	10.0	10.6
152°	10.0	10.6	10.6	10.6	10.6	10.6	10.0	10.6	10.6	10.6	10.6
152.5°	10.0	10.6	10.6	10.6	10.6	10.6	10.0	10.6	10.6	10.6	10.6
153°	10.0	10.6	10.6	10.6	10.6	10.6	10.0	10.6	10.6	10.6	10.6
153.5°	10.6	10.6	10.6	10.6	10.6	10.6	10.6	10.6	10.6	10.6	10.6
154°	10.6	10.6	10.6	10.6	10.6	10.6	10.6	10.6	10.6	10.6	10.6
154.5°	10.6	10.6	10.6	10.6	10.6	10.6	10.6	10.6	10.6	10.6	10.6
155°	10.6	10.6	10.6	10.6	10.6	10.6	10.6	10.6	10.6	10.6	10.6
155.5°	10.6	10.6	10.6	10.6	10.6	10.6	10.6	10.6	10.6	10.6	10.6
156°	10.6	11.3	10.6	10.6	10.6	10.6	10.6	11.3	10.6	10.6	10.6
156.5°	10.6	10.6	10.6	11.3	10.6	10.6	10.6	10.6	10.6	11.3	10.6
157°	10.6	10.6	10.6	11.3	10.6	10.6	10.6	10.6	10.6	11.3	10.6

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594680
CATALOG NUMBER: FLXB-4860-W-MED-4000K

CANDELA DISTRIBUTION (continued):

	0°	30°	60°	90°	120°	150°	180°	210°	240°	270°	300°
157.5°	10.6	11.3	10.6	11.3	10.6	10.6	10.6	11.3	10.6	11.3	10.6
158°	10.6	11.3	11.3	11.3	10.6	10.6	10.6	11.3	11.3	11.3	10.6
158.5°	10.6	11.3	11.3	11.3	11.3	11.3	10.6	11.3	11.3	11.3	11.3
159°	10.6	11.3	11.3	11.3	11.3	11.3	10.6	11.3	11.3	11.3	11.3
159.5°	10.6	11.3	11.3	11.3	11.3	11.3	10.6	11.3	11.3	11.3	11.3
160°	10.6	11.3	11.3	11.3	11.3	11.3	10.6	11.3	11.3	11.3	11.3
160.5°	10.6	11.3	11.3	11.3	11.3	11.3	10.6	11.3	11.3	11.3	11.3
161°	10.6	11.3	11.3	11.3	11.3	11.3	10.6	11.3	11.3	11.3	11.3
161.5°	10.6	11.3	11.3	11.3	11.3	11.3	10.6	11.3	11.3	11.3	11.3
162°	10.6	11.3	11.3	11.3	11.3	11.3	10.6	11.3	11.3	11.3	11.3
162.5°	10.6	11.3	11.9	11.3	11.3	11.3	10.6	11.3	11.9	11.3	11.3
163°	11.3	11.9	11.9	11.3	11.3	11.3	11.3	11.9	11.9	11.3	11.3
163.5°	11.3	11.3	11.9	11.9	11.3	11.3	11.3	11.3	11.9	11.9	11.3
164°	11.3	11.3	11.9	12.5	11.3	11.3	11.3	11.3	11.9	12.5	11.3
164.5°	11.3	11.3	11.9	11.9	11.3	11.3	11.3	11.3	11.9	11.9	11.3
165°	11.3	11.3	11.9	11.3	11.9	11.3	11.3	11.3	11.9	11.3	11.9
165.5°	11.9	11.9	11.9	11.9	11.9	11.3	11.9	11.9	11.9	11.9	11.9
166°	11.9	11.9	11.9	12.5	11.9	11.3	11.9	11.9	11.9	12.5	11.9
166.5°	11.3	11.9	11.9	11.9	11.9	11.3	11.3	11.9	11.9	11.9	11.9
167°	11.3	11.9	11.9	11.9	11.9	11.3	11.3	11.9	11.9	11.9	11.9
167.5°	11.9	11.9	11.9	12.5	12.5	11.3	11.9	11.9	11.9	12.5	12.5
168°	11.3	11.9	11.9	12.5	12.5	11.9	11.3	11.9	11.9	12.5	12.5
168.5°	11.3	12.5	11.9	12.5	11.9	11.9	11.3	12.5	11.9	12.5	11.9
169°	11.9	12.5	12.5	12.5	11.9	11.9	11.9	12.5	12.5	12.5	11.9
169.5°	11.9	12.5	12.5	12.5	12.5	11.9	11.9	12.5	12.5	12.5	12.5
170°	11.9	12.5	11.9	12.5	11.9	11.9	11.9	12.5	11.9	12.5	11.9
170.5°	11.9	12.5	11.9	12.5	11.9	11.9	11.9	12.5	11.9	12.5	11.9
171°	11.9	12.5	12.5	12.5	12.5	12.5	11.9	12.5	12.5	12.5	12.5
171.5°	11.9	12.5	12.5	12.5	12.5	12.5	11.9	12.5	12.5	12.5	12.5
172°	11.9	12.5	12.5	12.5	12.5	11.9	11.9	12.5	12.5	12.5	12.5
172.5°	11.9	12.5	12.5	12.5	12.5	11.9	11.9	12.5	12.5	12.5	12.5
173°	11.9	12.5	12.5	12.5	12.5	11.9	11.9	12.5	12.5	12.5	12.5
173.5°	11.9	12.5	12.5	12.5	12.5	11.9	11.9	12.5	12.5	12.5	12.5
174°	11.9	12.5	12.5	12.5	12.5	11.9	11.9	12.5	12.5	12.5	12.5
174.5°	11.9	12.5	12.5	12.5	12.5	12.5	11.9	12.5	12.5	12.5	12.5
175°	11.9	11.9	12.5	12.5	12.5	12.5	11.9	11.9	12.5	12.5	12.5
175.5°	11.9	11.9	12.5	12.5	12.5	11.9	11.9	11.9	12.5	12.5	12.5
176°	11.9	12.5	12.5	12.5	12.5	11.9	11.9	12.5	12.5	12.5	12.5
176.5°	11.9	12.5	12.5	12.5	12.5	12.5	11.9	12.5	12.5	12.5	12.5
177°	11.9	12.5	12.5	12.5	12.5	12.5	11.9	12.5	12.5	12.5	12.5
177.5°	11.3	12.5	12.5	12.5	12.5	11.9	11.3	12.5	12.5	12.5	12.5
178°	11.3	12.5	12.5	12.5	12.5	11.9	11.3	12.5	12.5	12.5	12.5
178.5°	11.3	12.5	12.5	12.5	12.5	12.5	11.3	12.5	12.5	12.5	12.5
179°	12.5	12.5	12.5	12.5	12.5	12.5	12.5	12.5	12.5	12.5	12.5
179.5°	12.5	12.5	12.5	12.5	12.5	12.5	12.5	12.5	12.5	12.5	12.5

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594680
CATALOG NUMBER: FLXB-4860-W-MED-4000K

CANDELA DISTRIBUTION (continued):

	0°	30°	60°	90°	120°	150°	180°	210°	240°	270°	300°
180°	12.5	12.5	12.5	12.5	12.5	*12.5*	12.5	12.5	12.5	12.5	12.5

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594680
CATALOG NUMBER: FLXB-4860-W-MED-4000K

CANDELA DISTRIBUTION (continued):

	330°	360°
0°	20732.0	20732.0
0.5°	20732.0	20732.0
1°	20777.7	20753.9
1.5°	20765.2	20746.4
2°	*20782.1*	*20724.5*
2.5°	20782.1	20719.5
3°	20737.7	20726.4
3.5°	20740.8	20712.0
4°	20742.7	20698.9
4.5°	20720.1	20666.3
5°	20709.5	20678.8
5.5°	20692.6	20670.1
6°	20673.8	20651.3
6.5°	20660.1	20611.3
7°	20657.6	20614.4
7.5°	20590.6	20591.2
8°	20590.6	20547.4
8.5°	20574.3	20528.7
9°	20534.9	20484.9
9.5°	20504.3	20482.4
10°	20481.1	20458.6
10.5°	20455.4	20426.7
11°	20422.9	20371.0
11.5°	20401.0	20362.2
12°	20355.3	20331.5
12.5°	20307.8	20303.4
13°	20264.0	20250.2
13.5°	20264.0	20225.2
14°	20156.3	20153.2
14.5°	20121.9	20111.9
15°	20086.9	20069.3
15.5°	20035.6	20001.8
16°	19994.3	19980.5
16.5°	19937.3	19937.9
17°	19879.7	19892.3
17.5°	19802.1	19823.4
18°	19802.1	19730.2
18.5°	19664.5	19691.4
19°	19619.4	19631.9
19.5°	19576.3	19577.5
20°	19508.7	19497.4
20.5°	19446.7	19463.0
21°	19384.1	19406.0
21.5°	19318.4	19343.5
22°	19258.4	19257.1

TEST NUMBER: P1594680
CATALOG NUMBER: FLXB-4860-W-MED-4000K

CANDELA DISTRIBUTION (continued):

	330°	360°
22.5°	19207.1	19214.6
23°	19044.4	19145.7
23.5°	19044.4	19009.3
24°	18933.6	18948.0
24.5°	18849.1	18856.6
25°	18769.0	18806.6
25.5°	18700.2	18734.0
26°	18628.8	18658.3
26.5°	18548.1	18558.8
27°	18479.9	18501.8
27.5°	18298.5	18423.6
28°	18298.5	18347.9
28.5°	18158.9	18248.4
29°	18158.9	18076.3
29.5°	17965.6	18006.2
30°	17809.7	17914.2
30.5°	17809.7	17825.4
31°	17714.6	17709.6
31.5°	17630.1	17638.3
32°	17533.2	17545.7
32.5°	17435.5	17449.9
33°	17268.4	17332.3
33.5°	17268.4	17139.5
34°	17051.3	17050.1
34.5°	16962.5	16939.9
35°	16877.4	16836.7
35.5°	16770.3	16709.0
36°	16669.6	16620.8
36.5°	16573.2	16515.0
37°	16473.7	16403.0
37.5°	16381.1	16269.7
38°	16295.4	16174.0
38.5°	16043.2	16057.0
39°	16043.2	15821.1
39.5°	15962.5	15709.1
40°	15863.0	15573.9
40.5°	15645.2	15470.0
41°	15645.2	15348.0
41.5°	15445.0	15226.0
42°	15445.0	15080.8
42.5°	15224.1	14973.8
43°	15097.7	14846.8
43.5°	14968.2	14579.6
44°	14859.3	14579.6
44.5°	14700.3	14313.0

TEST NUMBER: P1594680
CATALOG NUMBER: FLXB-4860-W-MED-4000K

CANDELA DISTRIBUTION (continued):

	330°	360°
45°	14356.2	14194.1
45.5°	14356.2	14194.1
46°	14000.7	13917.5
46.5°	14000.7	13760.4
47°	13595.9	13638.4
47.5°	13397.5	13492.0
48°	13186.6	13351.2
48.5°	12988.9	13181.6
49°	12783.0	12884.4
49.5°	12552.1	12746.7
50°	12360.6	12576.5
50.5°	11973.9	12432.0
51°	11973.9	12249.9
51.5°	11592.2	12113.4
52°	11592.2	11945.7
52.5°	11229.2	11794.3
53°	11229.2	11609.7
53.5°	10869.4	11468.3
54°	10679.8	11297.5
54.5°	10509.0	10958.9
55°	10336.9	10800.0
55.5°	10181.7	10609.1
56°	9892.6	10452.7
56.5°	9892.6	10268.1
57°	9651.1	10095.4
57.5°	9651.1	9893.3
58°	9331.9	9727.4
58.5°	9165.5	9539.1
59°	8988.4	9165.5
59.5°	8915.2	9165.5
60°	8733.7	8793.8
60.5°	8511.0	8619.2
61°	8511.0	8425.2
61.5°	8203.7	8242.5
62°	8203.7	8039.1
62.5°	7834.5	7862.0
63°	7834.5	7669.3
63.5°	7431.5	7478.4
64°	7267.6	7279.5
64.5°	7056.1	6899.6
65°	6905.9	6706.9
65.5°	6673.1	6518.5
66°	6246.3	6322.7
66.5°	6246.3	6128.1
67°	5762.6	5939.1

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594680
CATALOG NUMBER: FLXB-4860-W-MED-4000K

CANDELA DISTRIBUTION (continued):

	330°	360°
67.5°	5762.6	5556.7
68°	5303.3	5556.7
68.5°	5303.3	5363.4
69°	4865.3	5173.8
69.5°	4629.4	4988.6
70°	4364.7	4611.8
70.5°	3838.4	4409.7
71°	3838.4	4223.9
71.5°	3337.2	4023.6
72°	3337.2	3857.8
72.5°	2884.8	3659.4
73°	2884.8	3494.2
73.5°	2455.5	3306.5
74°	2234.6	3153.8
74.5°	2075.0	2819.7
75°	1887.3	2819.7
75.5°	1734.6	2499.9
76°	1566.9	2314.1
76.5°	1416.7	2197.0
77°	1103.2	2013.1
77.5°	1103.2	1912.3
78°	815.4	1734.0
78.5°	815.4	1653.3
79°	580.7	1479.3
79.5°	462.4	1413.6
80°	409.9	1248.4
80.5°	329.8	1039.4
81°	297.9	1000.6
81.5°	227.2	847.9
82°	227.2	820.4
82.5°	180.2	684.0
83°	180.2	664.6
83.5°	143.9	538.8
84°	143.9	525.6
84.5°	112.6	416.1
85°	96.4	398.6
85.5°	86.4	290.4
86°	62.6	213.4
86.5°	62.6	213.4
87°	40.7	152.7
87.5°	40.7	152.7
88°	23.8	106.4
88.5°	23.8	106.4
89°	8.8	72.6
89.5°	5.6	72.6

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594680
CATALOG NUMBER: FLXB-4860-W-MED-4000K

CANDELA DISTRIBUTION (continued):

	330°	360°
90°	5.6	48.8
90.5°	0.6	31.9
91°	0.6	31.9
91.5°	0.6	18.8
92°	0.6	18.8
92.5°	0.6	8.1
93°	0.6	8.1
93.5°	0.6	1.3
94°	0.6	1.3
94.5°	0.6	0.6
95°	0.6	0.6
95.5°	0.6	0.6
96°	0.6	0.6
96.5°	0.6	0.6
97°	0.6	0.6
97.5°	0.6	0.6
98°	0.6	0.6
98.5°	0.6	0.6
99°	0.6	0.6
99.5°	0.6	0.6
100°	0.6	1.3
100.5°	0.6	1.3
101°	0.6	1.3
101.5°	0.6	1.3
102°	0.6	1.3
102.5°	0.6	1.3
103°	0.6	1.3
103.5°	0.6	1.3
104°	0.6	1.3
104.5°	0.6	1.3
105°	1.3	1.3
105.5°	1.3	1.9
106°	1.3	1.9
106.5°	1.3	1.9
107°	1.9	1.9
107.5°	1.9	1.9
108°	1.9	1.9
108.5°	1.9	1.9
109°	1.9	1.9
109.5°	1.9	1.9
110°	1.9	1.9
110.5°	1.9	2.5
111°	1.9	2.5
111.5°	1.9	3.1
112°	1.9	3.1

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594680
CATALOG NUMBER: FLXB-4860-W-MED-4000K

CANDELA DISTRIBUTION (continued):

	330°	360°
112.5°	3.1	3.1
113°	3.1	3.1
113.5°	3.1	3.1
114°	3.1	3.1
114.5°	3.1	3.1
115°	3.1	3.1
115.5°	3.1	3.8
116°	3.1	3.8
116.5°	3.1	3.8
117°	3.1	3.8
117.5°	3.1	3.8
118°	4.4	3.8
118.5°	4.4	3.8
119°	4.4	4.4
119.5°	4.4	4.4
120°	4.4	4.4
120.5°	4.4	4.4
121°	4.4	4.4
121.5°	4.4	5.0
122°	4.4	5.0
122.5°	4.4	5.0
123°	4.4	5.0
123.5°	5.6	5.0
124°	5.6	5.0
124.5°	5.6	5.6
125°	5.6	5.6
125.5°	5.6	5.6
126°	5.6	5.6
126.5°	5.6	5.6
127°	5.6	5.6
127.5°	5.6	5.6
128°	6.3	6.3
128.5°	6.3	6.3
129°	6.9	6.3
129.5°	6.9	6.3
130°	6.9	6.3
130.5°	6.9	6.3
131°	6.9	6.9
131.5°	6.9	6.9
132°	6.9	6.9
132.5°	6.9	6.9
133°	6.9	6.9
133.5°	6.9	6.9
134°	6.9	6.9
134.5°	7.5	7.5

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594680
CATALOG NUMBER: FLXB-4860-W-MED-4000K

CANDELA DISTRIBUTION (continued):

	330°	360°
135°	7.5	7.5
135.5°	7.5	7.5
136°	8.1	7.5
136.5°	8.1	7.5
137°	8.1	7.5
137.5°	8.1	7.5
138°	8.1	8.1
138.5°	8.1	8.1
139°	8.1	8.1
139.5°	8.1	8.1
140°	8.1	8.1
140.5°	8.1	8.1
141°	8.1	8.8
141.5°	8.1	8.8
142°	8.8	8.8
142.5°	8.8	8.8
143°	8.8	8.8
143.5°	9.4	8.8
144°	9.4	8.8
144.5°	9.4	8.8
145°	9.4	8.8
145.5°	9.4	9.4
146°	9.4	9.4
146.5°	9.4	9.4
147°	9.4	9.4
147.5°	9.4	9.4
148°	9.4	9.4
148.5°	9.4	9.4
149°	9.4	9.4
149.5°	9.4	9.4
150°	9.4	9.4
150.5°	9.4	9.4
151°	10.0	10.0
151.5°	10.6	10.0
152°	10.6	10.0
152.5°	10.6	10.0
153°	10.6	10.0
153.5°	10.6	10.6
154°	10.6	10.6
154.5°	10.6	10.6
155°	10.6	10.6
155.5°	10.6	10.6
156°	10.6	10.6
156.5°	10.6	10.6
157°	10.6	10.6

TEST NUMBER: P1594680
CATALOG NUMBER: FLXB-4860-W-MED-4000K

CANDELA DISTRIBUTION (continued):

	330°	360°
157.5°	10.6	10.6
158°	10.6	10.6
158.5°	11.3	10.6
159°	11.3	10.6
159.5°	11.3	10.6
160°	11.3	10.6
160.5°	11.3	10.6
161°	11.3	10.6
161.5°	11.3	10.6
162°	11.3	10.6
162.5°	11.3	10.6
163°	11.3	11.3
163.5°	11.3	11.3
164°	11.3	11.3
164.5°	11.3	11.3
165°	11.3	11.3
165.5°	11.3	11.9
166°	11.3	11.9
166.5°	11.3	11.3
167°	11.3	11.3
167.5°	11.3	11.9
168°	11.9	11.3
168.5°	11.9	11.3
169°	11.9	11.9
169.5°	11.9	11.9
170°	11.9	11.9
170.5°	11.9	11.9
171°	12.5	11.9
171.5°	12.5	11.9
172°	11.9	11.9
172.5°	11.9	11.9
173°	11.9	11.9
173.5°	11.9	11.9
174°	11.9	11.9
174.5°	12.5	11.9
175°	12.5	11.9
175.5°	11.9	11.9
176°	11.9	11.9
176.5°	12.5	11.9
177°	12.5	11.9
177.5°	11.9	11.3
178°	11.9	11.3
178.5°	12.5	11.3
179°	12.5	12.5
179.5°	12.5	12.5

TEST NUMBER: P1594680
CATALOG NUMBER: FLXB-4860-W-MED-4000K

CANDELA DISTRIBUTION (continued):

	330°	360°
180°	12.5	12.5

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594680
CATALOG NUMBER: FLXB-4860-W-MED-4000K

CIE UGR TABLE:

Reflectances:											
	Ceiling	0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
	Wall	0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
	Reference plane	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room Dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	28.1	29.6	28.4	29.9	30.3	27.1	28.6	27.4	28.9	29.3
	3H	29.5	30.9	29.9	31.3	31.6	27.4	28.8	27.8	29.2	29.5
	4H	29.9	31.2	30.3	31.5	31.9	27.4	28.7	27.8	29.1	29.4
	6H	30.0	31.2	30.4	31.6	32.0	27.4	28.6	27.8	28.9	29.3
	8H	30.0	31.2	30.5	31.6	32.0	27.3	28.5	27.8	28.9	29.3
	12H	30.0	31.1	30.5	31.5	31.9	27.3	28.4	27.7	28.8	29.2
4H	2H	28.4	29.8	28.8	30.1	30.5	27.6	28.9	28.0	29.3	29.6
	3H	30.1	31.1	30.5	31.5	31.9	28.0	29.1	28.5	29.5	29.9
	4H	30.4	31.4	30.9	31.8	32.3	28.0	29.0	28.5	29.4	29.8
	6H	30.6	31.5	31.1	31.9	32.4	28.0	28.8	28.4	29.3	29.7
	8H	30.6	31.4	31.1	31.9	32.3	28.0	28.7	28.4	29.2	29.6
	12H	30.6	31.3	31.1	31.8	32.3	27.9	28.6	28.4	29.1	29.6
8H	4H	30.4	31.2	30.9	31.6	32.1	28.1	28.9	28.6	29.3	29.8
	6H	30.6	31.2	31.1	31.7	32.2	28.1	28.7	28.6	29.2	29.7
	8H	30.6	31.2	31.1	31.7	32.2	28.0	28.6	28.5	29.1	29.6
	12H	30.6	31.1	31.1	31.6	32.2	28.0	28.5	28.5	29.0	29.6
12H	4H	30.4	31.1	30.9	31.6	32.0	28.1	28.8	28.6	29.3	29.7
	6H	30.5	31.1	31.1	31.6	32.1	28.0	28.6	28.6	29.1	29.6
	8H	30.6	31.1	31.1	31.6	32.1	28.0	28.5	28.5	29.0	29.6

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP3-2602-684-3

Test Date: 02/20/2026

Luminaire Tested: HLBX-2436-W-HI-4000K

Data in this report applies to families of products including HLBX-2436*

Report Generated By FNC07603 / LDUCLS01DT01661
Version: v7.05


Test Information

Test Method:	LM-79-2019
Report Number:	SP3-2602-684-3
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP3 - 3M SPHERE
Measurement Geometry:	4π
Issue Date:	02/27/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	Metalux
Catalog Number:	**HLBX-2436-W-HI-4000K**
Description:	LDS HLBX 2436 W beam, HI lumen, 4000K CCT settings

Spectral Parameters

CCT (K):	4000
CIE u':	0.2271
CIE v':	0.4972
Duv:	-0.0036
CIE x:	0.3780
CIE y:	0.3677
CIE z:	0.2543
Peak Wavelength (nm):	454
Dominant Wavelength (nm):	581
Purity:	23.78071
Rf:	83.8
Rg:	95.3

CRI (Ra):	84.8
R1:	84.5
R2:	92.5
R3:	95.4
R4:	82.5
R5:	84.0
R6:	87.9
R7:	85.2
R8:	66.3
R9:	16.8
R10:	80.6
R11:	81.5
R12:	62.9
R13:	87.1
R14:	98.1
R15:	79.5



Test Conditions


Stabilization Time:	22M
Operation Time:	1H 22M
Sphere Temperature (°C):	25.0

REPORT NUMBER: SP3-2602-684-3


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	3M SPHERE IN02505	1/10/2026	7/10/2026
Power Meter	XITRON INXT2011006	10/21/2025	10/21/2026
AC Power Source	CHROMA 61604 IN6064A	10/20/2025	10/20/2026
DC Power Source	EYSIGHT N5770A IN0534	10/20/2025	10/20/2026
Sphere Thermometer	TANDD IN4036E	10/21/2025	10/21/2026

REPORT NUMBER: SP3-2602-684-3

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 4000K
CIE x = 0.3780
CIE y = 0.3677
Duv = -0.0036

Point lies inside the ANSI 4000K 7-step quadrangle

REPORT NUMBER: SP3-2602-684-3

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	258	NR	620	689	NR	750	21	NR	880	1	NR
365	0	NR	495	283	NR	625	645	NR	755	18	NR	885	1	NR
370	0	NR	500	331	NR	630	600	NR	760	15	NR	890	1	NR
375	0	NR	505	383	NR	635	550	NR	765	13	NR	895	0	NR
380	0	NR	510	428	NR	640	501	NR	770	11	NR	900	0	NR
385	0	NR	515	469	NR	645	450	NR	775	9	NR	905	0	NR
390	1	NR	520	502	NR	650	404	NR	780	8	NR	910	0	NR
395	3	NR	525	526	NR	655	359	NR	785	7	NR	915	0	NR
400	4	NR	530	543	NR	660	317	NR	790	6	NR	920	0	NR
405	7	NR	535	559	NR	665	278	NR	795	5	NR	925	0	NR
410	10	NR	540	573	NR	670	243	NR	800	4	NR	930	0	NR
415	18	NR	545	587	NR	675	212	NR	805	4	NR	935	0	NR
420	32	NR	550	603	NR	680	183	NR	810	3	NR	940	0	NR
425	55	NR	555	619	NR	685	159	NR	815	3	NR	945	0	NR
430	95	NR	560	640	NR	690	136	NR	820	2	NR	950	0	NR
435	164	NR	565	666	NR	695	117	NR	825	2	NR	955	0	NR
440	273	NR	570	689	NR	700	100	NR	830	2	NR	960	0	NR
445	480	NR	575	718	NR	705	85	NR	835	2	NR	965	0	NR
450	835	NR	580	743	NR	710	73	NR	840	1	NR	970	0	NR
455	998	NR	585	764	NR	715	63	NR	845	1	NR	975	0	NR
460	735	NR	590	781	NR	720	54	NR	850	1	NR	980	0	NR
465	533	NR	595	789	NR	725	46	NR	855	1	NR	985	0	NR
470	435	NR	600	787	NR	730	39	NR	860	1	NR	990	0	NR
475	320	NR	605	775	NR	735	33	NR	865	1	NR	995	0	NR
480	254	NR	610	755	NR	740	28	NR	870	1	NR	1000	0	NR
485	245	NR	615	725	NR	745	24	NR	875	1	NR			

REPORT NUMBER: SP3-2602-684-3

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.73**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	258	NR	620	689	NR	750	21	NR	880	1	NR
365	0	NR	495	283	NR	625	645	NR	755	18	NR	885	1	NR
370	0	NR	500	331	NR	630	600	NR	760	15	NR	890	1	NR
375	0	NR	505	383	NR	635	550	NR	765	13	NR	895	0	NR
380	0	NR	510	428	NR	640	501	NR	770	11	NR	900	0	NR
385	0	NR	515	469	NR	645	450	NR	775	9	NR	905	0	NR
390	1	NR	520	502	NR	650	404	NR	780	8	NR	910	0	NR
395	3	NR	525	526	NR	655	359	NR	785	7	NR	915	0	NR
400	4	NR	530	543	NR	660	317	NR	790	6	NR	920	0	NR
405	7	NR	535	559	NR	665	278	NR	795	5	NR	925	0	NR
410	10	NR	540	573	NR	670	243	NR	800	4	NR	930	0	NR
415	18	NR	545	587	NR	675	212	NR	805	4	NR	935	0	NR
420	32	NR	550	603	NR	680	183	NR	810	3	NR	940	0	NR
425	55	NR	555	619	NR	685	159	NR	815	3	NR	945	0	NR
430	95	NR	560	640	NR	690	136	NR	820	2	NR	950	0	NR
435	164	NR	565	666	NR	695	117	NR	825	2	NR	955	0	NR
440	273	NR	570	689	NR	700	100	NR	830	2	NR	960	0	NR
445	480	NR	575	718	NR	705	85	NR	835	2	NR	965	0	NR
450	835	NR	580	743	NR	710	73	NR	840	1	NR	970	0	NR
455	998	NR	585	764	NR	715	63	NR	845	1	NR	975	0	NR
460	735	NR	590	781	NR	720	54	NR	850	1	NR	980	0	NR
465	533	NR	595	789	NR	725	46	NR	855	1	NR	985	0	NR
470	435	NR	600	787	NR	730	39	NR	860	1	NR	990	0	NR
475	320	NR	605	775	NR	735	33	NR	865	1	NR	995	0	NR
480	254	NR	610	755	NR	740	28	NR	870	1	NR	1000	0	NR
485	245	NR	615	725	NR	745	24	NR	875	1	NR			

REPORT NUMBER: SP3-2602-684-3

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 3.62**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	258	NR	620	689	NR	750	21	NR	880	1	NR
365	0	NR	495	283	NR	625	645	NR	755	18	NR	885	1	NR
370	0	NR	500	331	NR	630	600	NR	760	15	NR	890	1	NR
375	0	NR	505	383	NR	635	550	NR	765	13	NR	895	0	NR
380	0	NR	510	428	NR	640	501	NR	770	11	NR	900	0	NR
385	0	NR	515	469	NR	645	450	NR	775	9	NR	905	0	NR
390	1	NR	520	502	NR	650	404	NR	780	8	NR	910	0	NR
395	3	NR	525	526	NR	655	359	NR	785	7	NR	915	0	NR
400	4	NR	530	543	NR	660	317	NR	790	6	NR	920	0	NR
405	7	NR	535	559	NR	665	278	NR	795	5	NR	925	0	NR
410	10	NR	540	573	NR	670	243	NR	800	4	NR	930	0	NR
415	18	NR	545	587	NR	675	212	NR	805	4	NR	935	0	NR
420	32	NR	550	603	NR	680	183	NR	810	3	NR	940	0	NR
425	55	NR	555	619	NR	685	159	NR	815	3	NR	945	0	NR
430	95	NR	560	640	NR	690	136	NR	820	2	NR	950	0	NR
435	164	NR	565	666	NR	695	117	NR	825	2	NR	955	0	NR
440	273	NR	570	689	NR	700	100	NR	830	2	NR	960	0	NR
445	480	NR	575	718	NR	705	85	NR	835	2	NR	965	0	NR
450	835	NR	580	743	NR	710	73	NR	840	1	NR	970	0	NR
455	998	NR	585	764	NR	715	63	NR	845	1	NR	975	0	NR
460	735	NR	590	781	NR	720	54	NR	850	1	NR	980	0	NR
465	533	NR	595	789	NR	725	46	NR	855	1	NR	985	0	NR
470	435	NR	600	787	NR	730	39	NR	860	1	NR	990	0	NR
475	320	NR	605	775	NR	735	33	NR	865	1	NR	995	0	NR
480	254	NR	610	755	NR	740	28	NR	870	1	NR	1000	0	NR
485	245	NR	615	725	NR	745	24	NR	875	1	NR			


REPORT NUMBER: SP3-2602-684-3

TM-30-18


Summary


R_f = 83.8
R_g = 95.3
CIE R_a = 84.8
R_9 = 16.8


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP3-2602-684-3

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 84	CES51 = 92	CES76 = 77
CES02 = 61	CES27 = 90	CES52 = 93	CES77 = 82
CES03 = 31	CES28 = 91	CES53 = 89	CES78 = 76
CES04 = 70	CES29 = 91	CES54 = 88	CES79 = 92
CES05 = 48	CES30 = 88	CES55 = 84	CES80 = 89
CES06 = 51	CES31 = 93	CES56 = 84	CES81 = 80
CES07 = 41	CES32 = 84	CES57 = 82	CES82 = 95
CES08 = 40	CES33 = 97	CES58 = 82	CES83 = 96
CES09 = 29	CES34 = 87	CES59 = 91	CES84 = 90
CES10 = 74	CES35 = 93	CES60 = 88	CES85 = 77
CES11 = 57	CES36 = 76	CES61 = 85	CES86 = 75
CES12 = 63	CES37 = 92	CES62 = 77	CES87 = 85
CES13 = 43	CES38 = 82	CES63 = 83	CES88 = 91
CES14 = 74	CES39 = 98	CES64 = 75	CES89 = 79
CES15 = 71	CES40 = 97	CES65 = 76	CES90 = 91
CES16 = 47	CES41 = 95	CES66 = 71	CES91 = 66
CES17 = 49	CES42 = 93	CES67 = 70	CES92 = 65
CES18 = 56	CES43 = 90	CES68 = 76	CES93 = 78
CES19 = 71	CES44 = 99	CES69 = 80	CES94 = 65
CES20 = 65	CES45 = 95	CES70 = 73	CES95 = 73
CES21 = 86	CES46 = 92	CES71 = 65	CES96 = 85
CES22 = 78	CES47 = 94	CES72 = 88	CES97 = 90
CES23 = 91	CES48 = 84	CES73 = 68	CES98 = 87
CES24 = 90	CES49 = 91	CES74 = 89	CES99 = 80
CES25 = 71	CES50 = 93	CES75 = 70	





REPORT NUMBER: SP3-2602-684-3

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP3-2602-684-3

TM-30-18

Measure Comparisons





(END OF REPORT)