Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: METALUX

Report Number: P1594681

Luminaire Tested: FLXB-4860-W-MED-5000K

Issue Date: 10/2/2026

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-2019
Report Number:	P1594681
	TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (A2601781A001)
Test Lab:	INNOVATION CENTER
Issue Date:	10/2/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	METALUX
Catalog Number:	FLXB-4860-W-MED-5000K
Description:	4860 FlexBay Linear High bay at W beam, MED lumen, 5000K CCT settings
Light Source:	-
Ballast/Driver:	-

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	53663.0 lumens
Efficiency:	N/A
Efficacy:	155.8 lumens/watt
Spacing Criteria (0/90/45):	1.28 / 1.33 / 1.41
Luminous Opening:	Rectangular (W 1.04' x L: 2.12' x H: 0')
CIE Type:	Direct


Input Watts (W):	344.5
Input Voltage (V):	NR
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	NR
Total Harmonic Distortion (THDi):	NR
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594681
CATALOG NUMBER: FLXB-4860-W-MED-5000K

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594681
CATALOG NUMBER: FLXB-4860-W-MED-5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87
2	101	94	87	82	98	92	86	81	88	83	79	85	81	78	82	79	76	74
3	93	83	75	69	90	81	74	69	78	72	67	76	71	66	73	69	65	63
4	85	74	65	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54
5	78	66	57	51	76	65	57	51	63	56	50	61	55	50	59	54	49	47
6	72	60	51	45	70	59	50	45	57	50	44	55	49	44	54	48	43	41
7	67	54	46	40	65	53	45	39	52	44	39	50	44	39	49	43	39	37
8	62	49	41	35	61	49	41	35	47	40	35	46	40	35	45	39	35	33
9	58	45	37	32	57	45	37	32	43	36	32	42	36	31	41	36	31	29
10	55	42	34	29	53	41	34	29	40	33	29	39	33	29	38	33	28	27

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	99519	99519	99519	99519
5°	99643	99655	99643	99655
10°	99722	99679	99722	99679
15°	99736	99528	99736	99528
20°	99599	99596	99599	99596
25°	99609	99960	99609	99960
30°	99296	101828	99296	101828
35°	98663	104413	98663	104413
40°	97590	100810	97590	100810
45°	96358	91197	96358	91197
50°	93920	85677	93920	85677
55°	90385	75790	90385	75790
60°	84424	62786	84424	62786
65°	76179	42354	76179	42354
70°	64727	20024	64727	20024
75°	52295	8252	52295	8252
80°	34510	4618	34510	4618
85°	21954	4000	21954	4000

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 60°
Vertical Angle: 45.5°
Luminance: 100167 cd/sqm

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594681
CATALOG NUMBER: FLXB-4860-W-MED-5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1942.2	3.6
10°-20°	5590.3	10.4
20°-30°	8570.9	16.0
30°-40°	10612.5	19.8
40°-50°	10839.7	20.2
50°-60°	8845.7	16.5
60°-70°	5421.1	10.1
70°-80°	1629.6	3.0
80°-90°	179.4	0.3
90°-100°	2.4	0.0
100°-110°	1.0	0.0
110°-120°	2.9	0.0
120°-130°	4.7	0.0
130°-140°	5.7	0.0
140°-150°	5.6	0.0
150°-160°	4.8	0.0
160°-170°	3.2	0.0
170°-180°	1.2	0.0
0°-30°	16103.3	30.0
0°-40°	26715.9	49.8
0°-60°	46401.3	86.5
0°-90°	53631.4	99.9
90°-120°	6.3	0.0
90°-150°	22.3	0.0
90°-180°	32.0	0.1
0°-180°	53663.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	20466	20466	20466	20466	20466	
5°	20414	20416	20414	20416	20414	1941
15°	19812	19771	19812	19771	19812	5594
25°	18565	18631	18565	18631	18565	8561
35°	16621	17589	16621	17589	16621	10404
45°	14012	13262	14012	13262	14012	10817
55°	10662	8940	10662	8940	10662	9543
65°	6621	3681	6621	3681	6621	6610
75°	2784	439	2784	439	2784	2906
85°	394	72	394	72	394	456
90°	48	14	48	14	48	32
95°	1	0	1	0	1	1
105°	1	1	1	1	1	2
115°	3	2	3	2	3	3
125°	6	4	6	4	6	5
135°	7	7	7	7	7	6
145°	9	9	9	9	9	6
155°	10	10	10	10	10	5
165°	11	11	11	11	11	3
175°	12	12	12	12	12	1
180°	12	12	12	12	12	

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594681
CATALOG NUMBER: FLXB-4860-W-MED-5000K

CANDELA DISTRIBUTION (FULL):

	0°	30°	60°	90°	120°	150°	180°	210°	240°	270°	300°
0°	20466.2	20466.2	20466.2	20466.2	20466.2	*20466.2*	20466.2	20466.2	20466.2	20466.2	20466.2
0.5°	20466.2	20466.2	20466.2	20466.2	20466.2	*20466.2*	20466.2	20466.2	20466.2	20466.2	20466.2
1°	20487.8	20489.7	20498.9	20503.3	20499.6	*20511.3*	20487.8	20489.7	20498.9	20503.3	20499.6
1.5°	20480.4	20478.6	20498.9	20481.0	20494.0	*20498.9*	20480.4	20478.6	20498.9	20481.0	20494.0
2°	*20458.8*	*20478.6*	*20465.0*	*20482.9*	*20494.0*	*20515.6*	*20458.8*	*20478.6*	*20465.0*	*20482.9*	*20494.0*
2.5°	20453.8	20471.1	20465.0	20484.7	20482.9	*20515.6*	20453.8	20471.1	20465.0	20484.7	20482.9
3°	20460.6	20471.1	20476.1	20453.8	20482.9	*20471.8*	20460.6	20471.1	20476.1	20453.8	20482.9
3.5°	20446.4	20450.1	20476.1	20463.1	20466.2	*20474.9*	20446.4	20450.1	20476.1	20463.1	20466.2
4°	20433.5	20445.2	20435.3	20444.6	20466.2	*20476.7*	20433.5	20445.2	20435.3	20444.6	20466.2
4.5°	20401.3	20423.6	20435.3	20423.6	20439.6	*20454.5*	20401.3	20423.6	20435.3	20423.6	20439.6
5°	20413.7	20416.8	20418.6	20416.2	20439.6	*20444.0*	20413.7	20416.8	20418.6	20416.2	20439.6
5.5°	20405.0	20404.4	20408.8	20416.8	20410.6	*20427.3*	20405.0	20404.4	20408.8	20416.8	20410.6
6°	20386.5	20392.7	20392.7	20383.4	20378.5	*20408.8*	20386.5	20392.7	20392.7	20383.4	20378.5
6.5°	20347.0	20368.6	20340.8	20366.7	20378.5	*20395.2*	20347.0	20368.6	20340.8	20366.7	20378.5
7°	20350.1	20332.8	20340.8	20355.6	20339.6	*20392.7*	20350.1	20332.8	20340.8	20355.6	20339.6
7.5°	20327.2	20332.8	20321.7	20337.1	20339.6	*20326.6*	20327.2	20332.8	20321.7	20337.1	20339.6
8°	20284.0	20292.0	20321.7	20289.5	20298.2	*20326.6*	20284.0	20292.0	20321.7	20289.5	20298.2
8.5°	20265.4	20292.0	20252.5	20261.7	20298.2	*20310.5*	20265.4	20292.0	20252.5	20261.7	20298.2
9°	20222.2	20248.1	20252.5	20226.5	20247.5	*20271.6*	20222.2	20248.1	20252.5	20226.5	20247.5
9.5°	20219.7	20227.1	20219.1	20196.3	20247.5	*20241.3*	20219.7	20227.1	20219.1	20196.3	20247.5
10°	20196.3	20192.5	20189.5	20187.6	20188.2	*20218.5*	20196.3	20192.5	20189.5	20187.6	20188.2
10.5°	20164.8	20169.1	20153.6	20141.3	20128.3	*20193.2*	20164.8	20169.1	20153.6	20141.3	20128.3
11°	20109.8	20133.2	20079.5	20105.4	20128.3	*20161.0*	20109.8	20133.2	20079.5	20105.4	20128.3
11.5°	20101.1	20108.5	20079.5	20083.2	20058.5	*20139.4*	20101.1	20108.5	20079.5	20083.2	20058.5
12°	20070.9	20068.4	20023.3	20056.7	20058.5	*20094.3*	20070.9	20068.4	20023.3	20056.7	20058.5
12.5°	20043.1	19997.3	20023.3	20002.3	19986.8	*20047.4*	20043.1	19997.3	20023.3	20002.3	19986.8
13°	19990.5	19997.3	19922.6	19941.1	19986.8	*20004.1*	19990.5	19997.3	19922.6	19941.1	19986.8
13.5°	19965.8	19922.0	19922.6	19892.3	19905.3	*20004.1*	19965.8	19922.0	19922.6	19892.3	19905.3
14°	19894.8	19922.0	19864.5	19846.0	19905.3	*19897.9*	19894.8	19922.0	19864.5	19846.0	19905.3
14.5°	19854.0	19839.2	19864.5	19821.3	19825.0	*19863.9*	19854.0	19839.2	19864.5	19821.3	19825.0
15°	19812.0	19801.5	19765.7	19770.6	19825.0	*19829.3*	19812.0	19801.5	19765.7	19770.6	19825.0
15.5°	19745.3	19754.6	19710.7	19718.7	19737.3	*19778.7*	19745.3	19754.6	19710.7	19718.7	19737.3
16°	19724.3	19713.2	19679.2	19684.8	19647.1	*19737.9*	19724.3	19713.2	19679.2	19684.8	19647.1
16.5°	19682.3	19658.2	19598.3	19652.0	19647.1	*19681.7*	19682.3	19658.2	19598.3	19652.0	19647.1
17°	19637.2	19558.7	19598.3	19587.8	19556.9	*19624.9*	19637.2	19558.7	19598.3	19587.8	19556.9
17.5°	19569.2	19558.7	19477.8	19546.4	19556.9	*19548.2*	19569.2	19558.7	19477.8	19546.4	19556.9
18°	19477.2	19459.9	19477.8	19509.9	19457.4	*19548.2*	19477.2	19459.9	19477.8	19509.9	19457.4
18.5°	19438.9	19459.9	19401.2	19399.4	19410.5	*19412.3*	19438.9	19459.9	19401.2	19399.4	19410.5
19°	19380.2	19350.0	19401.2	19366.0	19355.5	*19367.9*	19380.2	19350.0	19401.2	19366.0	19355.5
19.5°	19326.5	19303.0	19280.8	19366.0	19355.5	*19325.3*	19326.5	19303.0	19280.8	19366.0	19355.5
20°	19247.4	19237.5	19220.2	19246.8	19242.5	*19258.5*	19247.4	19237.5	19220.2	19246.8	19242.5
20.5°	19213.4	19181.3	19181.9	19196.8	19242.5	*19197.4*	19213.4	19181.3	19181.9	19196.8	19242.5
21°	19157.2	19118.3	19072.0	19159.1	19131.9	*19135.6*	19157.2	19118.3	19072.0	19159.1	19131.9
21.5°	19095.4	19062.1	19072.0	19091.1	19017.6	*19070.7*	19095.4	19062.1	19072.0	19091.1	19017.6
22°	19010.2	18989.2	18941.6	19031.2	19017.6	*19011.4*	19010.2	18989.2	18941.6	19031.2	19017.6

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594681
CATALOG NUMBER: FLXB-4860-W-MED-5000K

CANDELA DISTRIBUTION (continued):

	0°	30°	60°	90°	120°	150°	180°	210°	240°	270°	300°
22.5°	18968.2	18865.6	18941.6	18988.6	18895.9	*18960.8*	18968.2	18865.6	18941.6	18988.6	18895.9
23°	18900.2	18865.6	18834.8	18928.7	18895.9	*18800.2*	18900.2	18865.6	18834.8	18928.7	18895.9
23.5°	18765.6	18735.9	18834.8	18809.4	18774.8	*18800.2*	18765.6	18735.9	18834.8	18809.4	18774.8
24°	18705.0	18735.9	18685.3	18760.6	18774.8	*18690.8*	18705.0	18735.9	18685.3	18760.6	18774.8
24.5°	18614.8	18596.9	18685.3	18688.4	18641.4	*18607.4*	18614.8	18596.9	18685.3	18688.4	18641.4
25°	18565.4	18527.1	18571.6	18630.9	18641.4	*18528.4*	18565.4	18527.1	18571.6	18630.9	18641.4
25.5°	18493.8	18447.4	18503.7	18583.3	18511.7	*18460.4*	18493.8	18447.4	18503.7	18583.3	18511.7
26°	18419.0	18373.3	18427.7	18520.3	18374.6	*18390.0*	18419.0	18373.3	18427.7	18520.3	18374.6
26.5°	18320.8	18296.1	18291.2	18451.8	18374.6	*18310.3*	18320.8	18296.1	18291.2	18451.8	18374.6
27°	18264.6	18224.4	18291.2	18433.9	18238.6	*18243.0*	18264.6	18224.4	18291.2	18433.9	18238.6
27.5°	18187.4	18144.8	18171.3	18377.0	18238.6	*18063.8*	18187.4	18144.8	18171.3	18377.0	18238.6
28°	18112.6	17984.1	18171.3	18338.1	18117.0	*18063.8*	18112.6	17984.1	18171.3	18338.1	18117.0
28.5°	18014.4	17984.1	18007.0	18260.9	18117.0	*17926.1*	18014.4	17984.1	18007.0	18260.9	18117.0
29°	17844.5	17822.3	18007.0	18207.8	17989.7	*17926.1*	17844.5	17822.3	18007.0	18207.8	17989.7
29.5°	17775.3	17822.3	17900.1	18169.5	17989.7	*17735.2*	17775.3	17822.3	17900.1	18169.5	17989.7
30°	17684.5	17649.3	17900.1	18135.5	17868.0	*17581.4*	17684.5	17649.3	17900.1	18135.5	17868.0
30.5°	17596.8	17564.7	17752.5	18104.6	17868.0	*17581.4*	17596.8	17564.7	17752.5	18104.6	17868.0
31°	17482.5	17478.8	17752.5	18054.6	17743.8	*17487.5*	17482.5	17478.8	17752.5	18054.6	17743.8
31.5°	17412.1	17389.9	17629.6	18058.3	17619.1	*17404.1*	17412.1	17389.9	17629.6	18058.3	17619.1
32°	17320.7	17300.3	17519.0	18027.4	17619.1	*17308.3*	17320.7	17300.3	17519.0	18027.4	17619.1
32.5°	17226.2	17110.7	17519.0	17881.6	17515.9	*17212.0*	17226.2	17110.7	17519.0	17881.6	17515.9
33°	17110.0	17110.7	17390.5	17881.6	17515.9	*17047.0*	17110.0	17110.7	17390.5	17881.6	17515.9
33.5°	16919.8	17020.5	17390.5	17791.4	17382.5	*17047.0*	16919.8	17020.5	17390.5	17791.4	17382.5
34°	16831.4	16931.5	17311.4	17714.8	17382.5	*16832.7*	16831.4	16931.5	17311.4	17714.8	17382.5
34.5°	16722.7	16732.0	17311.4	17657.4	17241.0	*16745.0*	16722.7	16732.0	17311.4	17657.4	17241.0
35°	16620.8	16640.6	17155.8	17589.4	17241.0	*16661.0*	16620.8	16640.6	17155.8	17589.4	17241.0
35.5°	16494.8	16540.5	17030.4	17551.7	17110.7	*16555.3*	16494.8	16540.5	17030.4	17551.7	17110.7
36°	16407.7	16441.7	16985.9	17367.0	17048.9	*16455.9*	16407.7	16441.7	16985.9	17367.0	17048.9
36.5°	16303.3	16349.6	16915.5	17299.7	16972.9	*16360.7*	16303.3	16349.6	16915.5	17299.7	16972.9
37°	16192.7	16248.9	16820.3	17073.6	16796.2	*16262.5*	16192.7	16248.9	16820.3	17073.6	16796.2
37.5°	16061.1	16156.3	16662.2	17014.3	16796.2	*16171.1*	16061.1	16156.3	16662.2	17014.3	16796.2
38°	15966.6	15962.9	16662.2	16785.1	16719.0	*16086.5*	15966.6	15962.9	16662.2	16785.1	16719.0
38.5°	15851.1	15962.9	16538.6	16438.6	16719.0	*15837.5*	15851.1	15962.9	16538.6	16438.6	16719.0
39°	15618.2	15749.8	16538.6	16324.9	16567.1	*15837.5*	15618.2	15749.8	16538.6	16324.9	16567.1
39.5°	15507.6	15749.8	16346.5	16087.7	16567.1	*15757.8*	15507.6	15749.8	16346.5	16087.7	16567.1
40°	15374.2	15543.5	16346.5	15881.4	16248.3	*15659.6*	15374.2	15543.5	16346.5	15881.4	16248.3
40.5°	15271.7	15438.4	16193.3	15654.0	16248.3	*15444.6*	15271.7	15438.4	16193.3	15654.0	16248.3
41°	15151.2	15322.3	16006.2	15408.8	15993.2	*15444.6*	15151.2	15322.3	16006.2	15408.8	15993.2
41.5°	15030.7	15222.2	15938.8	15181.5	15706.6	*15246.9*	15030.7	15222.2	15938.8	15181.5	15706.6
42°	14887.4	15095.6	15649.7	14889.9	15706.6	*15246.9*	14887.4	15095.6	15649.7	14889.9	15706.6
42.5°	14781.8	14998.0	15649.7	14688.5	15339.0	*15028.9*	14781.8	14998.0	15649.7	14688.5	15339.0
43°	14656.4	14862.7	15313.1	14444.5	15339.0	*14904.1*	14656.4	14862.7	15313.1	14444.5	15339.0
43.5°	14392.6	14600.8	15313.1	14215.3	14932.5	*14776.2*	14392.6	14600.8	15313.1	14215.3	14932.5
44°	14392.6	14600.8	14856.5	13745.2	14932.5	*14668.8*	14392.6	14600.8	14856.5	13745.2	14932.5
44.5°	14129.5	14309.2	14856.5	13499.4	14511.9	*14511.9*	14129.5	14309.2	14856.5	13499.4	14511.9

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594681
CATALOG NUMBER: FLXB-4860-W-MED-5000K

CANDELA DISTRIBUTION (continued):

	0°	30°	60°	90°	120°	150°	180°	210°	240°	270°	300°
45°	14012.1	14199.3	14438.3	13261.6	14511.9	*14172.1*	14012.1	14199.3	14438.3	13261.6	14511.9
45.5°	14012.1	13997.3	14438.3	13046.6	14078.8	*14172.1*	14012.1	13997.3	14438.3	13046.6	14078.8
46°	13739.1	13872.5	13955.9	12941.6	14078.8	*13821.2*	13739.1	13872.5	13955.9	12941.6	14078.8
46.5°	13584.0	13656.3	13719.3	12711.8	13566.1	*13821.2*	13584.0	13656.3	13719.3	12711.8	13566.1
47°	13463.5	13512.4	13231.3	12632.1	13087.4	*13421.5*	13463.5	13512.4	13231.3	12632.1	13087.4
47.5°	13319.0	13308.5	12991.6	12410.3	13087.4	*13225.7*	13319.0	13308.5	12991.6	12410.3	13087.4
48°	13180.0	12958.9	12991.6	12164.5	12631.5	*13017.5*	13180.0	12958.9	12991.6	12164.5	12631.5
48.5°	13012.6	12958.9	12518.4	12164.5	12631.5	*12822.3*	13012.6	12958.9	12518.4	12164.5	12631.5
49°	12719.2	12619.1	12518.4	11787.6	12165.7	*12619.1*	12719.2	12619.1	12518.4	11787.6	12165.7
49.5°	12583.3	12619.1	12081.7	11497.3	12165.7	*12391.2*	12583.3	12619.1	12081.7	11497.3	12165.7
50°	12415.3	12257.7	12081.7	11325.6	11667.8	*12202.1*	12415.3	12257.7	12081.7	11325.6	11667.8
50.5°	12272.6	12060.7	11605.4	11009.3	11667.8	*11820.4*	12272.6	12060.7	11605.4	11009.3	11667.8
51°	12092.8	11886.5	11323.7	10965.4	11193.4	*11820.4*	12092.8	11886.5	11323.7	10965.4	11193.4
51.5°	11958.1	11679.5	11090.8	10719.6	10930.2	*11443.6*	11958.1	11679.5	11090.8	10719.6	10930.2
52°	11792.6	11503.5	10845.0	10643.6	10703.5	*11443.6*	11792.6	11503.5	10845.0	10643.6	10703.5
52.5°	11643.1	11295.9	10563.3	10297.7	10295.2	*11085.3*	11643.1	11295.9	10563.3	10297.7	10295.2
53°	11460.8	11117.4	10080.2	10247.6	10295.2	*11085.3*	11460.8	11117.4	10080.2	10247.6	10295.2
53.5°	11321.2	10741.8	10080.2	9968.4	9992.5	*10730.1*	11321.2	10741.8	10080.2	9968.4	9992.5
54°	11152.6	10741.8	9707.1	9700.3	9992.5	*10542.9*	11152.6	10741.8	9707.1	9700.3	9992.5
54.5°	10818.4	10365.0	9707.1	9159.2	9662.6	*10374.3*	10818.4	10365.0	9707.1	9159.2	9662.6
55°	10661.5	10365.0	9459.4	8939.9	9662.6	*10204.4*	10661.5	10365.0	9459.4	8939.9	9662.6
55.5°	10473.1	10025.8	9459.4	8684.7	9374.1	*10051.2*	10473.1	10025.8	9459.4	8684.7	9374.1
56°	10318.7	9838.7	9236.4	8495.1	9374.1	*9765.8*	10318.7	9838.7	9236.4	8495.1	9374.1
56.5°	10136.4	9724.4	9017.7	8244.9	9101.1	*9765.8*	10136.4	9724.4	9017.7	8244.9	9101.1
57°	9965.9	9544.0	8915.2	8109.6	8692.2	*9527.3*	9965.9	9544.0	8915.2	8109.6	8692.2
57.5°	9766.4	9414.3	8649.5	7765.6	8692.2	*9527.3*	9766.4	9414.3	8649.5	7765.6	8692.2
58°	9602.7	9232.1	8649.5	7579.6	8125.1	*9212.3*	9602.7	9232.1	8649.5	7579.6	8125.1
58.5°	9416.8	9073.3	8094.2	7302.9	8125.1	*9048.0*	9416.8	9073.3	8094.2	7302.9	8125.1
59°	9048.0	8718.7	8094.2	7090.4	7630.3	*8873.2*	9048.0	8718.7	8094.2	7090.4	7630.3
59.5°	9048.0	8718.7	7417.2	6635.1	7630.3	*8800.9*	9048.0	8718.7	7417.2	6635.1	7630.3
60°	8681.0	8367.8	7417.2	6456.0	7108.3	*8621.7*	8681.0	8367.8	7417.2	6456.0	7108.3
60.5°	8508.7	8181.3	6848.8	6116.2	7108.3	*8401.8*	8508.7	8181.3	6848.8	6116.2	7108.3
61°	8317.2	8026.9	6848.8	5985.9	6535.6	*8401.8*	8317.2	8026.9	6848.8	5985.9	6535.6
61.5°	8136.8	7841.5	6408.4	5670.2	6535.6	*8098.5*	8136.8	7841.5	6408.4	5670.2	6535.6
62°	7936.1	7710.6	6176.1	5553.4	6055.0	*8098.5*	7936.1	7710.6	6176.1	5553.4	6055.0
62.5°	7761.2	7530.2	5919.8	5553.4	5669.0	*7734.1*	7761.2	7530.2	5919.8	5553.4	5669.0
63°	7571.0	7360.9	5528.7	5334.1	5669.0	*7734.1*	7571.0	7360.9	5528.7	5334.1	5669.0
63.5°	7382.6	7000.2	5528.7	4814.0	5205.7	*7336.2*	7382.6	7000.2	5528.7	4814.0	5205.7
64°	7186.1	7000.2	5096.9	4524.9	5205.7	*7174.4*	7186.1	7000.2	5096.9	4524.9	5205.7
64.5°	6811.2	6714.8	4889.4	3929.4	4719.5	*6965.6*	6811.2	6714.8	4889.4	3929.4	4719.5
65°	6620.9	6714.8	4569.4	3681.1	4719.5	*6817.3*	6620.9	6714.8	4569.4	3681.1	4719.5
65.5°	6435.0	6318.2	4569.4	3363.6	4265.5	*6587.5*	6435.0	6318.2	4569.4	3363.6	4265.5
66°	6241.6	6150.2	4132.0	3120.8	4265.5	*6166.2*	6241.6	6150.2	4132.0	3120.8	4265.5
66.5°	6049.5	5916.7	3875.1	2837.9	3804.6	*6166.2*	6049.5	5916.7	3875.1	2837.9	3804.6
67°	5862.9	5718.4	3655.8	2642.1	3362.3	*5688.7*	5862.9	5718.4	3655.8	2642.1	3362.3

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594681
CATALOG NUMBER: FLXB-4860-W-MED-5000K

CANDELA DISTRIBUTION (continued):

	0°	30°	60°	90°	120°	150°	180°	210°	240°	270°	300°
67.5°	5485.5	5494.8	3425.3	2403.6	3362.3	5688.7	5485.5	5494.8	3425.3	2403.6	3362.3
68°	5485.5	5355.2	3180.7	2258.4	2879.9	5235.3	5485.5	5355.2	3180.7	2258.4	2879.9
68.5°	5294.6	5118.6	2717.4	2015.1	2879.9	5235.3	5294.6	5118.6	2717.4	2015.1	2879.9
69°	5107.4	4670.1	2717.4	1907.6	2455.5	4802.9	5107.4	4670.1	2717.4	1907.6	2455.5
69.5°	4924.6	4670.1	2330.7	1584.5	2455.5	4570.0	4924.6	4670.1	2330.7	1584.5	2455.5
70°	4552.7	4235.2	2330.7	1408.4	2070.6	4308.7	4552.7	4235.2	2330.7	1408.4	2070.6
70.5°	4353.2	4017.1	1908.8	1285.5	2070.6	3789.2	4353.2	4017.1	1908.8	1285.5	2070.6
71°	4169.7	3789.2	1908.8	1134.2	1691.4	3789.2	4169.7	3789.2	1908.8	1134.2	1691.4
71.5°	3972.0	3588.4	1531.4	1045.2	1691.4	3294.4	3972.0	3588.4	1531.4	1045.2	1691.4
72°	3808.3	3377.2	1448.6	923.5	1364.0	3294.4	3808.3	3377.2	1448.6	923.5	1364.0
72.5°	3612.5	3176.4	1233.0	877.2	1092.2	2847.8	3612.5	3176.4	1233.0	877.2	1092.2
73°	3449.4	2989.2	977.3	750.5	1092.2	2847.8	3449.4	2989.2	977.3	750.5	1092.2
73.5°	3264.1	2758.8	977.3	718.4	873.5	2424.0	3264.1	2758.8	977.3	718.4	873.5
74°	3113.4	2603.8	801.8	598.0	873.5	2205.9	3113.4	2603.8	801.8	598.0	873.5
74.5°	2783.5	2222.0	801.8	564.6	745.6	2048.4	2783.5	2222.0	801.8	564.6	745.6
75°	2783.5	2222.0	687.5	439.2	745.6	1863.1	2783.5	2222.0	687.5	439.2	745.6
75.5°	2467.9	1861.9	687.5	387.9	630.1	1712.4	2467.9	1861.9	687.5	387.9	630.1
76°	2284.4	1643.8	561.5	355.8	630.1	1546.8	2284.4	1643.8	561.5	355.8	630.1
76.5°	2168.9	1501.7	561.5	328.6	497.9	1398.6	2168.9	1501.7	561.5	328.6	497.9
77°	1987.3	1318.2	450.9	313.2	497.9	1089.1	1987.3	1318.2	450.9	313.2	497.9
77.5°	1887.8	1195.3	407.1	272.4	394.7	1089.1	1887.8	1195.3	407.1	272.4	394.7
78°	1711.7	1039.0	368.2	266.2	332.3	804.9	1711.7	1039.0	368.2	266.2	332.3
78.5°	1632.1	963.7	304.5	232.9	332.3	804.9	1632.1	963.7	304.5	232.9	332.3
79°	1460.3	761.1	304.5	227.3	289.1	573.3	1460.3	761.1	304.5	227.3	289.1
79.5°	1395.5	761.1	257.0	195.2	289.1	456.5	1395.5	761.1	257.0	195.2	289.1
80°	1232.4	586.8	257.0	164.9	234.1	404.6	1232.4	586.8	257.0	164.9	234.1
80.5°	1026.1	586.8	194.6	153.8	234.1	325.5	1026.1	586.8	194.6	153.8	234.1
81°	987.8	429.3	194.6	147.6	170.5	294.0	987.8	429.3	194.6	147.6	170.5
81.5°	837.0	320.6	154.4	140.8	170.5	224.2	837.0	320.6	154.4	140.8	170.5
82°	809.9	299.0	145.8	136.5	142.7	224.2	809.9	299.0	145.8	136.5	142.7
82.5°	675.2	225.5	135.9	127.9	126.6	177.9	675.2	225.5	135.9	127.9	126.6
83°	656.0	209.4	118.6	117.4	126.6	177.9	656.0	209.4	118.6	117.4	126.6
83.5°	531.9	166.2	118.6	102.5	102.5	142.1	531.9	166.2	118.6	102.5	102.5
84°	518.9	154.4	90.8	92.7	102.5	142.1	518.9	154.4	90.8	92.7	102.5
84.5°	410.8	119.8	90.8	80.9	76.0	111.2	410.8	119.8	90.8	80.9	76.0
85°	393.5	119.8	68.0	71.7	76.0	95.1	393.5	119.8	68.0	71.7	76.0
85.5°	286.6	87.7	68.0	63.0	64.9	85.2	286.6	87.7	68.0	63.0	64.9
86°	210.6	87.7	58.1	59.9	64.9	61.8	210.6	87.7	58.1	59.9	64.9
86.5°	210.6	61.8	58.1	44.5	53.7	61.8	210.6	61.8	58.1	44.5	53.7
87°	150.7	49.4	41.4	38.3	53.7	40.2	150.7	49.4	41.4	38.3	53.7
87.5°	150.7	44.5	35.2	24.7	34.0	40.2	150.7	44.5	35.2	24.7	34.0
88°	105.0	34.0	20.4	19.1	17.9	23.5	105.0	34.0	20.4	19.1	17.9
88.5°	105.0	32.7	15.4	17.3	17.9	23.5	105.0	32.7	15.4	17.3	17.9
89°	71.7	21.0	15.4	16.7	15.4	8.6	71.7	21.0	15.4	16.7	15.4
89.5°	71.7	21.0	11.7	13.6	15.4	5.6	71.7	21.0	11.7	13.6	15.4

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594681
CATALOG NUMBER: FLXB-4860-W-MED-5000K

CANDELA DISTRIBUTION (continued):

	0°	30°	60°	90°	120°	150°	180°	210°	240°	270°	300°
90°	48.2	9.3	11.7	13.6	11.1	5.6	48.2	9.3	11.7	13.6	11.1
90.5°	31.5	9.3	4.9	7.4	11.1	0.6	31.5	9.3	4.9	7.4	11.1
91°	31.5	6.2	4.9	1.9	4.3	0.6	31.5	6.2	4.9	1.9	4.3
91.5°	18.5	1.2	0.6	1.9	4.3	0.6	18.5	1.2	0.6	1.9	4.3
92°	18.5	0.6	0.6	0.6	0.6	0.6	18.5	0.6	0.6	0.6	0.6
92.5°	8.0	0.6	0.6	0.6	0.6	0.6	8.0	0.6	0.6	0.6	0.6
93°	8.0	0.6	0.6	0.6	0.6	0.6	8.0	0.6	0.6	0.6	0.6
93.5°	1.2	0.6	0.6	0.6	0.6	0.6	1.2	0.6	0.6	0.6	0.6
94°	1.2	0.6	0.6	0.0	0.6	0.6	1.2	0.6	0.6	0.0	0.6
94.5°	0.6	0.6	0.6	0.0	0.0	0.6	0.6	0.6	0.6	0.0	0.0
95°	0.6	0.6	0.0	0.0	0.0	0.6	0.6	0.6	0.0	0.0	0.0
95.5°	0.6	0.6	0.0	0.0	0.0	0.6	0.6	0.6	0.0	0.0	0.0
96°	0.6	0.6	0.0	0.0	0.0	0.6	0.6	0.6	0.0	0.0	0.0
96.5°	0.6	0.6	0.0	0.0	0.0	0.6	0.6	0.6	0.0	0.0	0.0
97°	0.6	0.6	0.0	0.0	0.0	0.6	0.6	0.6	0.0	0.0	0.0
97.5°	0.6	0.6	0.0	0.0	0.0	0.6	0.6	0.6	0.0	0.0	0.0
98°	0.6	0.6	0.0	0.0	0.0	0.6	0.6	0.6	0.0	0.0	0.0
98.5°	0.6	0.6	0.0	0.0	0.0	0.6	0.6	0.6	0.0	0.0	0.0
99°	0.6	0.6	0.0	0.0	0.0	0.6	0.6	0.6	0.0	0.0	0.0
99.5°	0.6	0.6	0.0	0.0	0.0	0.6	0.6	0.6	0.0	0.0	0.0
100°	1.2	0.6	0.0	0.0	0.0	0.6	1.2	0.6	0.0	0.0	0.0
100.5°	1.2	0.6	0.0	0.0	0.0	0.6	1.2	0.6	0.0	0.0	0.0
101°	1.2	0.6	0.0	0.0	0.0	0.6	1.2	0.6	0.0	0.0	0.0
101.5°	1.2	0.6	0.0	0.0	0.0	0.6	1.2	0.6	0.0	0.0	0.0
102°	1.2	0.6	0.0	0.6	0.0	0.6	1.2	0.6	0.0	0.6	0.0
102.5°	1.2	0.6	0.0	0.6	0.0	0.6	1.2	0.6	0.0	0.6	0.0
103°	1.2	0.6	0.0	0.6	0.0	0.6	1.2	0.6	0.0	0.6	0.0
103.5°	1.2	0.6	0.0	0.6	0.0	0.6	1.2	0.6	0.0	0.6	0.0
104°	1.2	0.6	1.2	0.6	0.0	0.6	1.2	0.6	1.2	0.6	0.0
104.5°	1.2	1.2	1.2	0.6	0.6	0.6	1.2	1.2	1.2	0.6	0.6
105°	1.2	1.2	1.2	0.6	0.6	1.2	1.2	1.2	1.2	0.6	0.6
105.5°	1.9	1.9	1.2	0.6	0.6	1.2	1.9	1.9	1.2	0.6	0.6
106°	1.9	1.9	1.2	0.6	0.6	1.2	1.9	1.9	1.2	0.6	0.6
106.5°	1.9	1.9	1.2	0.6	1.2	1.2	1.9	1.9	1.2	0.6	1.2
107°	1.9	1.9	1.2	0.6	1.2	1.9	1.9	1.9	1.2	0.6	1.2
107.5°	1.9	1.9	1.2	0.6	1.2	1.9	1.9	1.9	1.2	0.6	1.2
108°	1.9	1.9	1.2	0.6	1.2	1.9	1.9	1.9	1.2	0.6	1.2
108.5°	1.9	1.9	1.2	0.6	1.2	1.9	1.9	1.9	1.2	0.6	1.2
109°	1.9	1.9	1.2	0.6	1.2	1.9	1.9	1.9	1.2	0.6	1.2
109.5°	1.9	1.9	1.2	0.6	1.2	1.9	1.9	1.9	1.2	0.6	1.2
110°	1.9	2.5	1.2	1.2	1.9	1.9	1.9	2.5	1.2	1.2	1.9
110.5°	2.5	2.5	1.9	1.2	1.9	1.9	2.5	2.5	1.9	1.2	1.9
111°	2.5	2.5	1.9	1.9	1.9	1.9	2.5	2.5	1.9	1.9	1.9
111.5°	3.1	2.5	1.9	1.9	1.9	1.9	3.1	2.5	1.9	1.9	1.9
112°	3.1	3.1	1.9	1.9	1.9	1.9	3.1	3.1	1.9	1.9	1.9

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594681
CATALOG NUMBER: FLXB-4860-W-MED-5000K

CANDELA DISTRIBUTION (continued):

	0°	30°	60°	90°	120°	150°	180°	210°	240°	270°	300°
112.5°	3.1	3.1	2.5	1.9	1.9	3.1	3.1	3.1	2.5	1.9	1.9
113°	3.1	3.1	2.5	1.9	1.9	3.1	3.1	3.1	2.5	1.9	1.9
113.5°	3.1	3.1	2.5	1.9	1.9	3.1	3.1	3.1	2.5	1.9	1.9
114°	3.1	3.1	2.5	1.9	2.5	3.1	3.1	3.1	2.5	1.9	2.5
114.5°	3.1	3.1	2.5	1.9	3.1	3.1	3.1	3.1	2.5	1.9	3.1
115°	3.1	3.1	3.1	1.9	3.1	3.1	3.1	3.1	3.1	1.9	3.1
115.5°	3.7	3.1	3.1	2.5	3.1	3.1	3.7	3.1	3.1	2.5	3.1
116°	3.7	3.1	3.1	2.5	3.1	3.1	3.7	3.1	3.1	2.5	3.1
116.5°	3.7	3.7	3.1	3.1	3.1	3.1	3.7	3.7	3.1	3.1	3.1
117°	3.7	3.7	3.1	3.1	3.1	3.1	3.7	3.7	3.1	3.1	3.1
117.5°	3.7	3.7	3.1	3.1	3.1	3.1	3.7	3.7	3.1	3.1	3.1
118°	3.7	3.7	3.1	3.1	3.1	4.3	3.7	3.7	3.1	3.1	3.1
118.5°	3.7	3.7	3.1	3.1	3.1	4.3	3.7	3.7	3.1	3.1	3.1
119°	4.3	4.3	3.1	3.1	3.1	4.3	4.3	4.3	3.1	3.1	3.1
119.5°	4.3	4.3	4.3	3.1	3.1	4.3	4.3	4.3	4.3	3.1	3.1
120°	4.3	4.3	4.3	3.7	4.3	4.3	4.3	4.3	4.3	3.7	4.3
120.5°	4.3	4.3	4.3	3.7	4.3	4.3	4.3	4.3	4.3	3.7	4.3
121°	4.3	4.9	4.3	3.7	4.3	4.3	4.3	4.9	4.3	3.7	4.3
121.5°	4.9	4.9	4.3	3.7	4.3	4.3	4.9	4.9	4.3	3.7	4.3
122°	4.9	4.9	4.3	4.3	4.3	4.3	4.9	4.9	4.3	4.3	4.3
122.5°	4.9	4.9	4.3	4.3	4.3	4.3	4.9	4.9	4.3	4.3	4.3
123°	4.9	4.9	4.3	4.3	4.3	4.3	4.9	4.9	4.3	4.3	4.3
123.5°	4.9	4.9	4.3	4.3	4.3	5.6	4.9	4.9	4.3	4.3	4.3
124°	4.9	4.9	4.9	4.3	4.9	5.6	4.9	4.9	4.9	4.3	4.9
124.5°	5.6	5.6	5.6	4.3	5.6	5.6	5.6	5.6	5.6	4.3	5.6
125°	5.6	5.6	5.6	4.3	5.6	5.6	5.6	5.6	5.6	4.3	5.6
125.5°	5.6	5.6	5.6	4.9	5.6	5.6	5.6	5.6	5.6	4.9	5.6
126°	5.6	5.6	5.6	4.9	5.6	5.6	5.6	5.6	5.6	4.9	5.6
126.5°	5.6	6.2	5.6	5.6	5.6	5.6	5.6	6.2	5.6	5.6	5.6
127°	5.6	6.2	5.6	5.6	5.6	5.6	5.6	6.2	5.6	5.6	5.6
127.5°	5.6	6.2	5.6	5.6	5.6	5.6	5.6	6.2	5.6	5.6	5.6
128°	6.2	6.2	5.6	5.6	5.6	6.2	6.2	6.2	5.6	5.6	5.6
128.5°	6.2	6.2	6.2	5.6	5.6	6.2	6.2	6.2	6.2	5.6	5.6
129°	6.2	6.2	6.8	6.2	6.2	6.8	6.2	6.2	6.8	6.2	6.2
129.5°	6.2	6.2	6.8	6.2	6.2	6.8	6.2	6.2	6.8	6.2	6.2
130°	6.2	6.8	6.8	6.2	6.8	6.8	6.2	6.8	6.8	6.2	6.8
130.5°	6.2	6.8	6.8	6.2	6.8	6.8	6.2	6.8	6.8	6.2	6.8
131°	6.8	6.8	6.8	6.2	6.8	6.8	6.8	6.8	6.8	6.2	6.8
131.5°	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8
132°	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8
132.5°	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8
133°	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8
133.5°	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8
134°	6.8	7.4	7.4	6.8	6.8	6.8	6.8	7.4	7.4	6.8	6.8
134.5°	7.4	7.4	7.4	7.4	6.8	7.4	7.4	7.4	7.4	7.4	6.8

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594681
CATALOG NUMBER: FLXB-4860-W-MED-5000K

CANDELA DISTRIBUTION (continued):

	0°	30°	60°	90°	120°	150°	180°	210°	240°	270°	300°
135°	7.4	7.4	7.4	7.4	6.8	7.4	7.4	7.4	7.4	7.4	6.8
135.5°	7.4	7.4	7.4	7.4	7.4	7.4	7.4	7.4	7.4	7.4	7.4
136°	7.4	7.4	8.0	7.4	7.4	8.0	7.4	7.4	8.0	7.4	7.4
136.5°	7.4	8.0	8.0	7.4	8.0	8.0	7.4	8.0	8.0	7.4	8.0
137°	7.4	8.0	8.0	8.0	8.0	8.0	7.4	8.0	8.0	8.0	8.0
137.5°	7.4	8.0	8.0	7.4	8.0	8.0	7.4	8.0	8.0	7.4	8.0
138°	8.0	8.0	8.0	7.4	8.0	8.0	8.0	8.0	8.0	7.4	8.0
138.5°	8.0	8.0	8.0	8.0	8.0	8.0	8.0	8.0	8.0	8.0	8.0
139°	8.0	8.0	8.0	8.0	8.0	8.0	8.0	8.0	8.0	8.0	8.0
139.5°	8.0	8.6	8.0	8.0	8.0	8.0	8.0	8.6	8.0	8.0	8.0
140°	8.0	8.6	8.0	8.0	8.0	8.0	8.0	8.6	8.0	8.0	8.0
140.5°	8.0	8.6	8.0	8.0	8.0	8.0	8.0	8.6	8.0	8.0	8.0
141°	8.6	8.6	8.0	8.6	8.0	8.0	8.6	8.6	8.0	8.6	8.0
141.5°	8.6	8.6	8.6	8.6	8.0	8.0	8.6	8.6	8.6	8.6	8.0
142°	8.6	8.6	8.6	8.6	8.0	8.6	8.6	8.6	8.6	8.6	8.0
142.5°	8.6	8.6	9.3	8.6	8.0	8.6	8.6	8.6	9.3	8.6	8.0
143°	8.6	8.6	9.3	8.6	9.3	8.6	8.6	8.6	9.3	8.6	9.3
143.5°	8.6	8.6	9.3	8.6	9.3	9.3	8.6	8.6	9.3	8.6	9.3
144°	8.6	8.6	9.3	9.3	9.3	9.3	8.6	8.6	9.3	9.3	9.3
144.5°	8.6	9.3	9.3	9.3	9.3	9.3	8.6	9.3	9.3	9.3	9.3
145°	8.6	9.3	9.3	9.3	9.3	9.3	8.6	9.3	9.3	9.3	9.3
145.5°	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3
146°	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3
146.5°	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3
147°	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3
147.5°	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3
148°	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3
148.5°	9.3	9.9	9.3	9.3	9.3	9.3	9.3	9.9	9.3	9.3	9.3
149°	9.3	9.9	9.9	9.3	9.3	9.3	9.3	9.9	9.9	9.3	9.3
149.5°	9.3	9.9	10.5	9.3	9.3	9.3	9.3	9.9	10.5	9.3	9.3
150°	9.3	9.9	9.9	9.9	9.9	9.3	9.3	9.9	9.9	9.9	9.9
150.5°	9.3	9.9	9.9	9.9	9.9	9.3	9.3	9.9	9.9	9.9	9.9
151°	9.9	9.9	9.9	9.9	10.5	9.9	9.9	9.9	9.9	9.9	10.5
151.5°	9.9	9.9	10.5	9.9	10.5	10.5	9.9	9.9	10.5	9.9	10.5
152°	9.9	10.5	10.5	10.5	10.5	10.5	9.9	10.5	10.5	10.5	10.5
152.5°	9.9	10.5	10.5	10.5	10.5	10.5	9.9	10.5	10.5	10.5	10.5
153°	9.9	10.5	10.5	10.5	10.5	10.5	9.9	10.5	10.5	10.5	10.5
153.5°	10.5	10.5	10.5	10.5	10.5	10.5	10.5	10.5	10.5	10.5	10.5
154°	10.5	10.5	10.5	10.5	10.5	10.5	10.5	10.5	10.5	10.5	10.5
154.5°	10.5	10.5	10.5	10.5	10.5	10.5	10.5	10.5	10.5	10.5	10.5
155°	10.5	10.5	10.5	10.5	10.5	10.5	10.5	10.5	10.5	10.5	10.5
155.5°	10.5	10.5	10.5	10.5	10.5	10.5	10.5	10.5	10.5	10.5	10.5
156°	10.5	11.1	10.5	10.5	10.5	10.5	10.5	11.1	10.5	10.5	10.5
156.5°	10.5	10.5	10.5	11.1	10.5	10.5	10.5	10.5	10.5	11.1	10.5
157°	10.5	10.5	10.5	11.1	10.5	10.5	10.5	10.5	10.5	11.1	10.5

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594681
CATALOG NUMBER: FLXB-4860-W-MED-5000K

CANDELA DISTRIBUTION (continued):

	0°	30°	60°	90°	120°	150°	180°	210°	240°	270°	300°
157.5°	10.5	11.1	10.5	11.1	10.5	10.5	10.5	11.1	10.5	11.1	10.5
158°	10.5	11.1	11.1	11.1	10.5	10.5	10.5	11.1	11.1	11.1	10.5
158.5°	10.5	11.1	11.1	11.1	11.1	11.1	10.5	11.1	11.1	11.1	11.1
159°	10.5	11.1	11.1	11.1	11.1	11.1	10.5	11.1	11.1	11.1	11.1
159.5°	10.5	11.1	11.1	11.1	11.1	11.1	10.5	11.1	11.1	11.1	11.1
160°	10.5	11.1	11.1	11.1	11.1	11.1	10.5	11.1	11.1	11.1	11.1
160.5°	10.5	11.1	11.1	11.1	11.1	11.1	10.5	11.1	11.1	11.1	11.1
161°	10.5	11.1	11.1	11.1	11.1	11.1	10.5	11.1	11.1	11.1	11.1
161.5°	10.5	11.1	11.1	11.1	11.1	11.1	10.5	11.1	11.1	11.1	11.1
162°	10.5	11.1	11.1	11.1	11.1	11.1	10.5	11.1	11.1	11.1	11.1
162.5°	10.5	11.1	11.7	11.1	11.1	11.1	10.5	11.1	11.7	11.1	11.1
163°	11.1	11.7	11.7	11.1	11.1	11.1	11.1	11.7	11.7	11.1	11.1
163.5°	11.1	11.1	11.7	11.7	11.1	11.1	11.1	11.1	11.7	11.7	11.1
164°	11.1	11.1	11.7	12.4	11.1	11.1	11.1	11.1	11.7	12.4	11.1
164.5°	11.1	11.1	11.7	11.7	11.1	11.1	11.1	11.1	11.7	11.7	11.1
165°	11.1	11.1	11.7	11.1	11.7	11.1	11.1	11.1	11.7	11.1	11.7
165.5°	11.7	11.7	11.7	11.7	11.7	11.1	11.7	11.7	11.7	11.7	11.7
166°	11.7	11.7	11.7	12.4	11.7	11.1	11.7	11.7	11.7	12.4	11.7
166.5°	11.1	11.7	11.7	11.7	11.7	11.1	11.1	11.7	11.7	11.7	11.7
167°	11.1	11.7	11.7	11.7	11.7	11.1	11.1	11.7	11.7	11.7	11.7
167.5°	11.7	11.7	11.7	12.4	12.4	11.1	11.7	11.7	11.7	12.4	12.4
168°	11.1	11.7	11.7	12.4	12.4	11.7	11.1	11.7	11.7	12.4	12.4
168.5°	11.1	12.4	11.7	12.4	11.7	11.7	11.1	12.4	11.7	12.4	11.7
169°	11.7	12.4	12.4	12.4	11.7	11.7	11.7	12.4	12.4	12.4	11.7
169.5°	11.7	12.4	12.4	12.4	12.4	11.7	11.7	12.4	12.4	12.4	12.4
170°	11.7	12.4	11.7	12.4	11.7	11.7	11.7	12.4	11.7	12.4	11.7
170.5°	11.7	12.4	11.7	12.4	11.7	11.7	11.7	12.4	11.7	12.4	11.7
171°	11.7	12.4	12.4	12.4	12.4	12.4	11.7	12.4	12.4	12.4	12.4
171.5°	11.7	12.4	12.4	12.4	12.4	12.4	11.7	12.4	12.4	12.4	12.4
172°	11.7	12.4	12.4	12.4	12.4	11.7	11.7	12.4	12.4	12.4	12.4
172.5°	11.7	12.4	12.4	12.4	12.4	11.7	11.7	12.4	12.4	12.4	12.4
173°	11.7	12.4	12.4	12.4	12.4	11.7	11.7	12.4	12.4	12.4	12.4
173.5°	11.7	12.4	12.4	12.4	12.4	11.7	11.7	12.4	12.4	12.4	12.4
174°	11.7	12.4	12.4	12.4	12.4	11.7	11.7	12.4	12.4	12.4	12.4
174.5°	11.7	12.4	12.4	12.4	12.4	12.4	11.7	12.4	12.4	12.4	12.4
175°	11.7	11.7	12.4	12.4	12.4	12.4	11.7	11.7	12.4	12.4	12.4
175.5°	11.7	11.7	12.4	12.4	12.4	11.7	11.7	11.7	12.4	12.4	12.4
176°	11.7	12.4	12.4	12.4	12.4	11.7	11.7	12.4	12.4	12.4	12.4
176.5°	11.7	12.4	12.4	12.4	12.4	12.4	11.7	12.4	12.4	12.4	12.4
177°	11.7	12.4	12.4	12.4	12.4	12.4	11.7	12.4	12.4	12.4	12.4
177.5°	11.1	12.4	12.4	12.4	12.4	11.7	11.1	12.4	12.4	12.4	12.4
178°	11.1	12.4	12.4	12.4	12.4	11.7	11.1	12.4	12.4	12.4	12.4
178.5°	11.1	12.4	12.4	12.4	12.4	12.4	11.1	12.4	12.4	12.4	12.4
179°	12.4	12.4	12.4	12.4	12.4	12.4	12.4	12.4	12.4	12.4	12.4
179.5°	12.4	12.4	12.4	12.4	12.4	12.4	12.4	12.4	12.4	12.4	12.4

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594681
CATALOG NUMBER: FLXB-4860-W-MED-5000K

CANDELA DISTRIBUTION (continued):

	0°	30°	60°	90°	120°	150°	180°	210°	240°	270°	300°
180°	12.4	12.4	12.4	12.4	12.4	*12.4*	12.4	12.4	12.4	12.4	12.4

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594681
CATALOG NUMBER: FLXB-4860-W-MED-5000K

CANDELA DISTRIBUTION (continued):

	330°	360°
0°	20466.2	20466.2
0.5°	20466.2	20466.2
1°	20511.3	20487.8
1.5°	20498.9	20480.4
2°	*20515.6*	*20458.8*
2.5°	20515.6	20453.8
3°	20471.8	20460.6
3.5°	20474.9	20446.4
4°	20476.7	20433.5
4.5°	20454.5	20401.3
5°	20444.0	20413.7
5.5°	20427.3	20405.0
6°	20408.8	20386.5
6.5°	20395.2	20347.0
7°	20392.7	20350.1
7.5°	20326.6	20327.2
8°	20326.6	20284.0
8.5°	20310.5	20265.4
9°	20271.6	20222.2
9.5°	20241.3	20219.7
10°	20218.5	20196.3
10.5°	20193.2	20164.8
11°	20161.0	20109.8
11.5°	20139.4	20101.1
12°	20094.3	20070.9
12.5°	20047.4	20043.1
13°	20004.1	19990.5
13.5°	20004.1	19965.8
14°	19897.9	19894.8
14.5°	19863.9	19854.0
15°	19829.3	19812.0
15.5°	19778.7	19745.3
16°	19737.9	19724.3
16.5°	19681.7	19682.3
17°	19624.9	19637.2
17.5°	19548.2	19569.2
18°	19548.2	19477.2
18.5°	19412.3	19438.9
19°	19367.9	19380.2
19.5°	19325.3	19326.5
20°	19258.5	19247.4
20.5°	19197.4	19213.4
21°	19135.6	19157.2
21.5°	19070.7	19095.4
22°	19011.4	19010.2

TEST NUMBER: P1594681
CATALOG NUMBER: FLXB-4860-W-MED-5000K

CANDELA DISTRIBUTION (continued):

	330°	360°
22.5°	18960.8	18968.2
23°	18800.2	18900.2
23.5°	18800.2	18765.6
24°	18690.8	18705.0
24.5°	18607.4	18614.8
25°	18528.4	18565.4
25.5°	18460.4	18493.8
26°	18390.0	18419.0
26.5°	18310.3	18320.8
27°	18243.0	18264.6
27.5°	18063.8	18187.4
28°	18063.8	18112.6
28.5°	17926.1	18014.4
29°	17926.1	17844.5
29.5°	17735.2	17775.3
30°	17581.4	17684.5
30.5°	17581.4	17596.8
31°	17487.5	17482.5
31.5°	17404.1	17412.1
32°	17308.3	17320.7
32.5°	17212.0	17226.2
33°	17047.0	17110.0
33.5°	17047.0	16919.8
34°	16832.7	16831.4
34.5°	16745.0	16722.7
35°	16661.0	16620.8
35.5°	16555.3	16494.8
36°	16455.9	16407.7
36.5°	16360.7	16303.3
37°	16262.5	16192.7
37.5°	16171.1	16061.1
38°	16086.5	15966.6
38.5°	15837.5	15851.1
39°	15837.5	15618.2
39.5°	15757.8	15507.6
40°	15659.6	15374.2
40.5°	15444.6	15271.7
41°	15444.6	15151.2
41.5°	15246.9	15030.7
42°	15246.9	14887.4
42.5°	15028.9	14781.8
43°	14904.1	14656.4
43.5°	14776.2	14392.6
44°	14668.8	14392.6
44.5°	14511.9	14129.5

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594681
CATALOG NUMBER: FLXB-4860-W-MED-5000K

CANDELA DISTRIBUTION (continued):

	330°	360°
45°	14172.1	14012.1
45.5°	14172.1	14012.1
46°	13821.2	13739.1
46.5°	13821.2	13584.0
47°	13421.5	13463.5
47.5°	13225.7	13319.0
48°	13017.5	13180.0
48.5°	12822.3	13012.6
49°	12619.1	12719.2
49.5°	12391.2	12583.3
50°	12202.1	12415.3
50.5°	11820.4	12272.6
51°	11820.4	12092.8
51.5°	11443.6	11958.1
52°	11443.6	11792.6
52.5°	11085.3	11643.1
53°	11085.3	11460.8
53.5°	10730.1	11321.2
54°	10542.9	11152.6
54.5°	10374.3	10818.4
55°	10204.4	10661.5
55.5°	10051.2	10473.1
56°	9765.8	10318.7
56.5°	9765.8	10136.4
57°	9527.3	9965.9
57.5°	9527.3	9766.4
58°	9212.3	9602.7
58.5°	9048.0	9416.8
59°	8873.2	9048.0
59.5°	8800.9	9048.0
60°	8621.7	8681.0
60.5°	8401.8	8508.7
61°	8401.8	8317.2
61.5°	8098.5	8136.8
62°	8098.5	7936.1
62.5°	7734.1	7761.2
63°	7734.1	7571.0
63.5°	7336.2	7382.6
64°	7174.4	7186.1
64.5°	6965.6	6811.2
65°	6817.3	6620.9
65.5°	6587.5	6435.0
66°	6166.2	6241.6
66.5°	6166.2	6049.5
67°	5688.7	5862.9

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594681
CATALOG NUMBER: FLXB-4860-W-MED-5000K

CANDELA DISTRIBUTION (continued):

	330°	360°
67.5°	5688.7	5485.5
68°	5235.3	5485.5
68.5°	5235.3	5294.6
69°	4802.9	5107.4
69.5°	4570.0	4924.6
70°	4308.7	4552.7
70.5°	3789.2	4353.2
71°	3789.2	4169.7
71.5°	3294.4	3972.0
72°	3294.4	3808.3
72.5°	2847.8	3612.5
73°	2847.8	3449.4
73.5°	2424.0	3264.1
74°	2205.9	3113.4
74.5°	2048.4	2783.5
75°	1863.1	2783.5
75.5°	1712.4	2467.9
76°	1546.8	2284.4
76.5°	1398.6	2168.9
77°	1089.1	1987.3
77.5°	1089.1	1887.8
78°	804.9	1711.7
78.5°	804.9	1632.1
79°	573.3	1460.3
79.5°	456.5	1395.5
80°	404.6	1232.4
80.5°	325.5	1026.1
81°	294.0	987.8
81.5°	224.2	837.0
82°	224.2	809.9
82.5°	177.9	675.2
83°	177.9	656.0
83.5°	142.1	531.9
84°	142.1	518.9
84.5°	111.2	410.8
85°	95.1	393.5
85.5°	85.2	286.6
86°	61.8	210.6
86.5°	61.8	210.6
87°	40.2	150.7
87.5°	40.2	150.7
88°	23.5	105.0
88.5°	23.5	105.0
89°	8.6	71.7
89.5°	5.6	71.7

TEST NUMBER: P1594681
CATALOG NUMBER: FLXB-4860-W-MED-5000K

CANDELA DISTRIBUTION (continued):

	330°	360°
90°	5.6	48.2
90.5°	0.6	31.5
91°	0.6	31.5
91.5°	0.6	18.5
92°	0.6	18.5
92.5°	0.6	8.0
93°	0.6	8.0
93.5°	0.6	1.2
94°	0.6	1.2
94.5°	0.6	0.6
95°	0.6	0.6
95.5°	0.6	0.6
96°	0.6	0.6
96.5°	0.6	0.6
97°	0.6	0.6
97.5°	0.6	0.6
98°	0.6	0.6
98.5°	0.6	0.6
99°	0.6	0.6
99.5°	0.6	0.6
100°	0.6	1.2
100.5°	0.6	1.2
101°	0.6	1.2
101.5°	0.6	1.2
102°	0.6	1.2
102.5°	0.6	1.2
103°	0.6	1.2
103.5°	0.6	1.2
104°	0.6	1.2
104.5°	0.6	1.2
105°	1.2	1.2
105.5°	1.2	1.9
106°	1.2	1.9
106.5°	1.2	1.9
107°	1.9	1.9
107.5°	1.9	1.9
108°	1.9	1.9
108.5°	1.9	1.9
109°	1.9	1.9
109.5°	1.9	1.9
110°	1.9	1.9
110.5°	1.9	2.5
111°	1.9	2.5
111.5°	1.9	3.1
112°	1.9	3.1

TEST NUMBER: P1594681
CATALOG NUMBER: FLXB-4860-W-MED-5000K

CANDELA DISTRIBUTION (continued):

	330°	360°
112.5°	3.1	3.1
113°	3.1	3.1
113.5°	3.1	3.1
114°	3.1	3.1
114.5°	3.1	3.1
115°	3.1	3.1
115.5°	3.1	3.7
116°	3.1	3.7
116.5°	3.1	3.7
117°	3.1	3.7
117.5°	3.1	3.7
118°	4.3	3.7
118.5°	4.3	3.7
119°	4.3	4.3
119.5°	4.3	4.3
120°	4.3	4.3
120.5°	4.3	4.3
121°	4.3	4.3
121.5°	4.3	4.9
122°	4.3	4.9
122.5°	4.3	4.9
123°	4.3	4.9
123.5°	5.6	4.9
124°	5.6	4.9
124.5°	5.6	5.6
125°	5.6	5.6
125.5°	5.6	5.6
126°	5.6	5.6
126.5°	5.6	5.6
127°	5.6	5.6
127.5°	5.6	5.6
128°	6.2	6.2
128.5°	6.2	6.2
129°	6.8	6.2
129.5°	6.8	6.2
130°	6.8	6.2
130.5°	6.8	6.2
131°	6.8	6.8
131.5°	6.8	6.8
132°	6.8	6.8
132.5°	6.8	6.8
133°	6.8	6.8
133.5°	6.8	6.8
134°	6.8	6.8
134.5°	7.4	7.4

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594681
CATALOG NUMBER: FLXB-4860-W-MED-5000K

CANDELA DISTRIBUTION (continued):

	330°	360°
135°	7.4	7.4
135.5°	7.4	7.4
136°	8.0	7.4
136.5°	8.0	7.4
137°	8.0	7.4
137.5°	8.0	7.4
138°	8.0	8.0
138.5°	8.0	8.0
139°	8.0	8.0
139.5°	8.0	8.0
140°	8.0	8.0
140.5°	8.0	8.0
141°	8.0	8.6
141.5°	8.0	8.6
142°	8.6	8.6
142.5°	8.6	8.6
143°	8.6	8.6
143.5°	9.3	8.6
144°	9.3	8.6
144.5°	9.3	8.6
145°	9.3	8.6
145.5°	9.3	9.3
146°	9.3	9.3
146.5°	9.3	9.3
147°	9.3	9.3
147.5°	9.3	9.3
148°	9.3	9.3
148.5°	9.3	9.3
149°	9.3	9.3
149.5°	9.3	9.3
150°	9.3	9.3
150.5°	9.3	9.3
151°	9.9	9.9
151.5°	10.5	9.9
152°	10.5	9.9
152.5°	10.5	9.9
153°	10.5	9.9
153.5°	10.5	10.5
154°	10.5	10.5
154.5°	10.5	10.5
155°	10.5	10.5
155.5°	10.5	10.5
156°	10.5	10.5
156.5°	10.5	10.5
157°	10.5	10.5

TEST NUMBER: P1594681
CATALOG NUMBER: FLXB-4860-W-MED-5000K

CANDELA DISTRIBUTION (continued):

	330°	360°
157.5°	10.5	10.5
158°	10.5	10.5
158.5°	11.1	10.5
159°	11.1	10.5
159.5°	11.1	10.5
160°	11.1	10.5
160.5°	11.1	10.5
161°	11.1	10.5
161.5°	11.1	10.5
162°	11.1	10.5
162.5°	11.1	10.5
163°	11.1	11.1
163.5°	11.1	11.1
164°	11.1	11.1
164.5°	11.1	11.1
165°	11.1	11.1
165.5°	11.1	11.7
166°	11.1	11.7
166.5°	11.1	11.1
167°	11.1	11.1
167.5°	11.1	11.7
168°	11.7	11.1
168.5°	11.7	11.1
169°	11.7	11.7
169.5°	11.7	11.7
170°	11.7	11.7
170.5°	11.7	11.7
171°	12.4	11.7
171.5°	12.4	11.7
172°	11.7	11.7
172.5°	11.7	11.7
173°	11.7	11.7
173.5°	11.7	11.7
174°	11.7	11.7
174.5°	12.4	11.7
175°	12.4	11.7
175.5°	11.7	11.7
176°	11.7	11.7
176.5°	12.4	11.7
177°	12.4	11.7
177.5°	11.7	11.1
178°	11.7	11.1
178.5°	12.4	11.1
179°	12.4	12.4
179.5°	12.4	12.4

TEST NUMBER: P1594681
CATALOG NUMBER: FLXB-4860-W-MED-5000K

CANDELA DISTRIBUTION (continued):

	330°	360°
180°	12.4	12.4

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594681
CATALOG NUMBER: FLXB-4860-W-MED-5000K

CIE UGR TABLE:

Reflectances:											
	Ceiling	0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
	Wall	0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
	Reference plane	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room Dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	28.0	29.6	28.4	29.9	30.2	27.0	28.6	27.4	28.9	29.2
	3H	29.5	30.9	29.9	31.2	31.6	27.4	28.8	27.8	29.1	29.5
	4H	29.8	31.1	30.2	31.5	31.9	27.4	28.7	27.8	29.0	29.4
	6H	30.0	31.2	30.4	31.5	31.9	27.3	28.5	27.7	28.9	29.3
	8H	30.0	31.1	30.4	31.5	31.9	27.3	28.4	27.7	28.8	29.2
	12H	30.0	31.1	30.4	31.5	31.9	27.3	28.4	27.7	28.7	29.2
4H	2H	28.4	29.7	28.8	30.1	30.4	27.6	28.9	28.0	29.2	29.6
	3H	30.0	31.1	30.4	31.5	31.9	28.0	29.1	28.4	29.5	29.9
	4H	30.4	31.4	30.8	31.8	32.2	28.0	28.9	28.4	29.4	29.8
	6H	30.6	31.4	31.0	31.9	32.3	27.9	28.8	28.4	29.2	29.7
	8H	30.6	31.4	31.1	31.8	32.3	27.9	28.7	28.4	29.1	29.6
	12H	30.6	31.3	31.1	31.8	32.2	27.9	28.6	28.4	29.1	29.5
8H	4H	30.4	31.1	30.8	31.6	32.1	28.1	28.9	28.5	29.3	29.8
	6H	30.5	31.2	31.0	31.7	32.2	28.0	28.7	28.5	29.2	29.6
	8H	30.6	31.1	31.1	31.6	32.1	28.0	28.6	28.5	29.1	29.6
	12H	30.6	31.1	31.1	31.6	32.1	28.0	28.5	28.5	29.0	29.5
12H	4H	30.3	31.0	30.8	31.5	32.0	28.1	28.8	28.5	29.2	29.7
	6H	30.5	31.1	31.0	31.5	32.1	28.0	28.6	28.5	29.0	29.6
	8H	30.5	31.0	31.0	31.5	32.1	28.0	28.5	28.5	29.0	29.5

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP3-2602-684-4

Test Date: 02/20/2026

Luminaire Tested: HLBX-2436-W-HI-5000K

Data in this report applies to families of products including HLBX-2436*

Report Generated By FNC07603 / LDUCLS01DT01661
Version: v7.05


Test Information

Test Method:	LM-79-2019
Report Number:	SP3-2602-684-4
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP3 - 3M SPHERE
Measurement Geometry:	4π
Issue Date:	02/27/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	Metalux
Catalog Number:	**HLBX-2436-W-HI-5000K**
Description:	LDS HLBX 2436 W beam, HI lumen, 5000K CCT settings

Spectral Parameters

CCT (K):	5117	CRI (Ra):	84.6		
CIE u':	0.2117	R1:	84.3	R9:	16.1
CIE v':	0.4808	R2:	90.8	R10:	76.0
Duv:	-0.0020	R3:	92.9	R11:	82.6
CIE x:	0.3416	R4:	83.6	R12:	61.4
CIE y:	0.3449	R5:	84.0	R13:	86.4
CIE z:	0.3135	R6:	84.9	R14:	96.3
Peak Wavelength (nm):	454	R7:	86.7	R15:	80.3
Dominant Wavelength (nm):	574	R8:	69.3		
Purity:	5.96999				

Rf:	83.2
Rg:	95.8




Test Conditions

Stabilization Time:	24M
Operation Time:	1H 24M
Sphere Temperature (°C):	25.0


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	3M SPHERE IN02505	1/10/2026	7/10/2026
Power Meter	XITRON INXT2011006	10/21/2025	10/21/2026
AC Power Source	CHROMA 61604 IN6064A	10/20/2025	10/20/2026
DC Power Source	EYSIGHT N5770A IN0534	10/20/2025	10/20/2026
Sphere Thermometer	TANDD IN4036E	10/21/2025	10/21/2026

REPORT NUMBER: SP3-2602-684-4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 5117K
CIE x = 0.3416
CIE y = 0.3449
Duv = -0.0020

Point lies inside the ANSI 5000K 7-step quadrangle

REPORT NUMBER: SP3-2602-684-4

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	228	NR	620	445	NR	750	13	NR	880	0	NR
365	0	NR	495	248	NR	625	413	NR	755	11	NR	885	1	NR
370	0	NR	500	288	NR	630	382	NR	760	10	NR	890	0	NR
375	0	NR	505	333	NR	635	348	NR	765	8	NR	895	0	NR
380	0	NR	510	371	NR	640	316	NR	770	7	NR	900	0	NR
385	1	NR	515	406	NR	645	283	NR	775	6	NR	905	0	NR
390	2	NR	520	432	NR	650	253	NR	780	5	NR	910	0	NR
395	4	NR	525	450	NR	655	225	NR	785	5	NR	915	0	NR
400	6	NR	530	463	NR	660	198	NR	790	4	NR	920	0	NR
405	8	NR	535	474	NR	665	174	NR	795	3	NR	925	0	NR
410	12	NR	540	481	NR	670	152	NR	800	3	NR	930	0	NR
415	21	NR	545	488	NR	675	132	NR	805	3	NR	935	0	NR
420	38	NR	550	495	NR	680	114	NR	810	2	NR	940	0	NR
425	66	NR	555	501	NR	685	100	NR	815	2	NR	945	0	NR
430	112	NR	560	509	NR	690	85	NR	820	2	NR	950	0	NR
435	192	NR	565	519	NR	695	73	NR	825	1	NR	955	0	NR
440	312	NR	570	525	NR	700	63	NR	830	1	NR	960	0	NR
445	533	NR	575	536	NR	705	54	NR	835	1	NR	965	0	NR
450	876	NR	580	543	NR	710	46	NR	840	1	NR	970	0	NR
455	991	NR	585	546	NR	715	40	NR	845	1	NR	975	0	NR
460	722	NR	590	547	NR	720	34	NR	850	1	NR	980	0	NR
465	519	NR	595	543	NR	725	29	NR	855	1	NR	985	0	NR
470	411	NR	600	532	NR	730	25	NR	860	1	NR	990	0	NR
475	297	NR	605	517	NR	735	21	NR	865	1	NR	995	0	NR
480	233	NR	610	497	NR	740	18	NR	870	1	NR	1000	0	NR
485	220	NR	615	472	NR	745	16	NR	875	1	NR			

REPORT NUMBER: SP3-2602-684-4

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 2**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	228	NR	620	445	NR	750	13	NR	880	0	NR
365	0	NR	495	248	NR	625	413	NR	755	11	NR	885	1	NR
370	0	NR	500	288	NR	630	382	NR	760	10	NR	890	0	NR
375	0	NR	505	333	NR	635	348	NR	765	8	NR	895	0	NR
380	0	NR	510	371	NR	640	316	NR	770	7	NR	900	0	NR
385	1	NR	515	406	NR	645	283	NR	775	6	NR	905	0	NR
390	2	NR	520	432	NR	650	253	NR	780	5	NR	910	0	NR
395	4	NR	525	450	NR	655	225	NR	785	5	NR	915	0	NR
400	6	NR	530	463	NR	660	198	NR	790	4	NR	920	0	NR
405	8	NR	535	474	NR	665	174	NR	795	3	NR	925	0	NR
410	12	NR	540	481	NR	670	152	NR	800	3	NR	930	0	NR
415	21	NR	545	488	NR	675	132	NR	805	3	NR	935	0	NR
420	38	NR	550	495	NR	680	114	NR	810	2	NR	940	0	NR
425	66	NR	555	501	NR	685	100	NR	815	2	NR	945	0	NR
430	112	NR	560	509	NR	690	85	NR	820	2	NR	950	0	NR
435	192	NR	565	519	NR	695	73	NR	825	1	NR	955	0	NR
440	312	NR	570	525	NR	700	63	NR	830	1	NR	960	0	NR
445	533	NR	575	536	NR	705	54	NR	835	1	NR	965	0	NR
450	876	NR	580	543	NR	710	46	NR	840	1	NR	970	0	NR
455	991	NR	585	546	NR	715	40	NR	845	1	NR	975	0	NR
460	722	NR	590	547	NR	720	34	NR	850	1	NR	980	0	NR
465	519	NR	595	543	NR	725	29	NR	855	1	NR	985	0	NR
470	411	NR	600	532	NR	730	25	NR	860	1	NR	990	0	NR
475	297	NR	605	517	NR	735	21	NR	865	1	NR	995	0	NR
480	233	NR	610	497	NR	740	18	NR	870	1	NR	1000	0	NR
485	220	NR	615	472	NR	745	16	NR	875	1	NR			

REPORT NUMBER: SP3-2602-684-4

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 4.33**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	228	NR	620	445	NR	750	13	NR	880	0	NR
365	0	NR	495	248	NR	625	413	NR	755	11	NR	885	1	NR
370	0	NR	500	288	NR	630	382	NR	760	10	NR	890	0	NR
375	0	NR	505	333	NR	635	348	NR	765	8	NR	895	0	NR
380	0	NR	510	371	NR	640	316	NR	770	7	NR	900	0	NR
385	1	NR	515	406	NR	645	283	NR	775	6	NR	905	0	NR
390	2	NR	520	432	NR	650	253	NR	780	5	NR	910	0	NR
395	4	NR	525	450	NR	655	225	NR	785	5	NR	915	0	NR
400	6	NR	530	463	NR	660	198	NR	790	4	NR	920	0	NR
405	8	NR	535	474	NR	665	174	NR	795	3	NR	925	0	NR
410	12	NR	540	481	NR	670	152	NR	800	3	NR	930	0	NR
415	21	NR	545	488	NR	675	132	NR	805	3	NR	935	0	NR
420	38	NR	550	495	NR	680	114	NR	810	2	NR	940	0	NR
425	66	NR	555	501	NR	685	100	NR	815	2	NR	945	0	NR
430	112	NR	560	509	NR	690	85	NR	820	2	NR	950	0	NR
435	192	NR	565	519	NR	695	73	NR	825	1	NR	955	0	NR
440	312	NR	570	525	NR	700	63	NR	830	1	NR	960	0	NR
445	533	NR	575	536	NR	705	54	NR	835	1	NR	965	0	NR
450	876	NR	580	543	NR	710	46	NR	840	1	NR	970	0	NR
455	991	NR	585	546	NR	715	40	NR	845	1	NR	975	0	NR
460	722	NR	590	547	NR	720	34	NR	850	1	NR	980	0	NR
465	519	NR	595	543	NR	725	29	NR	855	1	NR	985	0	NR
470	411	NR	600	532	NR	730	25	NR	860	1	NR	990	0	NR
475	297	NR	605	517	NR	735	21	NR	865	1	NR	995	0	NR
480	233	NR	610	497	NR	740	18	NR	870	1	NR	1000	0	NR
485	220	NR	615	472	NR	745	16	NR	875	1	NR			


REPORT NUMBER: SP3-2602-684-4

TM-30-18


Summary


R_f = 83.2
R_g = 95.8
CIE R_a = 84.6
R_9 = 16.1


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP3-2602-684-4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 85	CES26 = 80	CES51 = 92	CES76 = 72
CES02 = 60	CES27 = 92	CES52 = 94	CES77 = 79
CES03 = 30	CES28 = 89	CES53 = 89	CES78 = 71
CES04 = 69	CES29 = 88	CES54 = 89	CES79 = 90
CES05 = 47	CES30 = 92	CES55 = 86	CES80 = 87
CES06 = 50	CES31 = 89	CES56 = 85	CES81 = 84
CES07 = 40	CES32 = 80	CES57 = 83	CES82 = 94
CES08 = 39	CES33 = 96	CES58 = 83	CES83 = 96
CES09 = 29	CES34 = 83	CES59 = 91	CES84 = 89
CES10 = 73	CES35 = 90	CES60 = 88	CES85 = 79
CES11 = 56	CES36 = 80	CES61 = 85	CES86 = 79
CES12 = 62	CES37 = 88	CES62 = 79	CES87 = 85
CES13 = 42	CES38 = 87	CES63 = 82	CES88 = 91
CES14 = 74	CES39 = 99	CES64 = 75	CES89 = 80
CES15 = 71	CES40 = 96	CES65 = 75	CES90 = 91
CES16 = 46	CES41 = 96	CES66 = 70	CES91 = 69
CES17 = 49	CES42 = 89	CES67 = 68	CES92 = 67
CES18 = 56	CES43 = 89	CES68 = 75	CES93 = 80
CES19 = 71	CES44 = 99	CES69 = 79	CES94 = 66
CES20 = 64	CES45 = 94	CES70 = 71	CES95 = 73
CES21 = 85	CES46 = 92	CES71 = 62	CES96 = 85
CES22 = 77	CES47 = 95	CES72 = 88	CES97 = 91
CES23 = 91	CES48 = 87	CES73 = 65	CES98 = 87
CES24 = 90	CES49 = 91	CES74 = 89	CES99 = 79
CES25 = 71	CES50 = 93	CES75 = 66	





REPORT NUMBER: SP3-2602-684-4

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP3-2602-684-4

TM-30-18

Measure Comparisons





(END OF REPORT)