

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: METALUX

Report Number: P1433742

Luminaire Tested: EHBR1-18-UNV-TASM-L940-UPL24

Issue Date: 3/20/2026

Test Information

Test Method: LM-79-2019
Report Number: P1433742
REPORT IS A COMBINATION OF REPORTS P1431679 AND P1431635
Test Lab: INNOVATION CENTER
Issue Date: 3/20/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: METALUX
Catalog Number: EHBR1-18-UNV-TASM-L940-UPL24
Description: Elevate Round Highbay at, 18000 lumens, 4000K 90CRI LEDs with TASM lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 19364.2 lumens
Efficiency: N/A
Efficacy: 174.1 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.84 / 0.9
Luminous Opening: Vertical Cylinder (Dia: 1.71' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 111.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1433742
CATALOG NUMBER: EHBR1-18-UNV-TASM-L940-UPL24

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° ··· 90°-270° - · 135°-315°



TEST NUMBER: P1433742

CATALOG NUMBER: EHBR1-18-UNV-TASM-L940-UPL24

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	116	116	116	116	112	112	112	112	105	105	105	98	98	98	91	91	91	88			88
1	109	105	102	99	105	102	99	97	96	94	92	90	88	87	85	84	82				80
2	102	96	91	87	98	93	89	85	88	84	81	83	80	78	79	76	74				72
3	95	88	82	77	92	85	80	75	81	76	73	77	73	70	73	70	68				65
4	90	80	74	69	87	79	72	68	75	70	66	71	67	64	68	65	62				60
5	84	74	67	62	81	73	66	62	69	64	60	66	62	58	64	60	57				55
6	79	69	62	57	77	67	61	56	65	59	55	62	57	54	60	56	52				50
7	75	64	57	52	72	63	56	52	60	55	51	58	53	50	56	52	49				47
8	71	60	53	48	69	59	52	48	57	51	47	55	50	46	53	48	45				44
9	67	56	49	45	65	55	49	44	53	48	44	51	46	43	50	45	42				41
10	63	53	46	42	62	52	46	42	50	45	41	48	44	40	47	43	40				38

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	71808	71808	71808	71808
5°	71370	76139	71370	67667
10°	70493	78094	70493	64041
15°	68412	72573	68412	59156
20°	63982	58194	63982	52692
25°	56630	40320	56630	44158
30°	45981	26231	45981	33039
35°	32979	16987	32979	21995
40°	21322	11709	21322	13871
45°	13529	9069	13529	9883
50°	10046	7707	10046	8232
55°	8203	7021	8203	7267
60°	7103	6688	7103	6729
65°	6475	6450	6475	6423
70°	6137	6319	6137	6237
75°	5738	6114	5738	5931
80°	5041	5771	5041	5397
85°	3262	4120	3262	3931

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 19020 cd/sqm



TEST NUMBER: P1433742
 CATALOG NUMBER: EHBR1-18-UNV-TASM-L940-UPL24

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1453.9	7.5
10°-20°	3955.5	20.4
20°-30°	4639.0	24.0
30°-40°	3226.1	16.7
40°-50°	1603.2	8.3
50°-60°	958.9	5.0
60°-70°	674.9	3.5
70°-80°	434.8	2.2
80°-90°	142.1	0.7
90°-100°	60.5	0.3
100°-110°	396.1	2.0
110°-120°	731.9	3.8
120°-130°	434.8	2.2
130°-140°	262.7	1.4
140°-150°	181.5	0.9
150°-160°	118.2	0.6
160°-170°	67.6	0.3
170°-180°	22.4	0.1
0°-30°	10048.5	51.9
0°-40°	13274.6	68.6
0°-60°	15836.7	81.8
0°-90°	17088.5	88.2
90°-120°	1188.5	6.1
90°-150°	2067.5	10.7
90°-180°	2276.0	11.8
0°-180°	19364.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	15291	15291	15291	15291	15291	
5°	15239	16257	15239	14448	15239	1446
15°	14352	15226	14352	12411	14352	4011
25°	11309	8052	11309	8818	11309	5120
35°	6053	3118	6053	4037	6053	3779
45°	2189	1467	2189	1599	2189	1791
55°	1108	949	1108	982	1108	1014
65°	676	673	676	670	676	679
75°	404	431	404	418	404	424
85°	112	142	112	135	112	125
90°	17	19	17	17	17	13
95°	32	30	32	28	32	34
105°	182	92	182	138	182	245
115°	779	665	779	633	779	710
125°	498	522	498	457	498	459
135°	315	363	315	334	315	250
145°	284	297	284	276	284	178
155°	253	263	253	245	253	118
165°	237	244	237	232	237	67
175°	235	239	235	231	235	22
180°	235	235	235	235	235	



TEST NUMBER: P1433742
 CATALOG NUMBER: EHBR1-18-UNV-TASM-L940-UPL24

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
0°	15290.9	15290.9	15290.9	15290.9	15290.9	15290.9	15290.9	15290.9	15290.9	15290.9	15290.9
2.5°	15282.0	15479.6	15639.5	15745.1	15797.3	15745.1	15639.5	15479.6	15282.0	15085.6	14950.6
5°	15238.7	15634.4	15969.6	16188.9	16256.9	16188.9	15969.6	15634.4	15238.7	14864.9	14616.8
7.5°	15135.2	15751.7	16249.8	16505.8	16568.3	16505.8	16249.8	15751.7	15135.2	14605.9	14292.6
10°	14977.2	15825.7	16401.2	16584.6	16592.1	16584.6	16401.2	15825.7	14977.2	14264.2	13894.6
12.5°	14725.2	15799.3	16350.4	16290.2	16153.3	16290.2	16350.4	15799.3	14725.2	13846.7	13380.5
15°	14352.5	15643.0	16029.0	15538.9	15225.5	15538.9	16029.0	15643.0	14352.5	13282.9	12742.2
17.5°	13827.2	15350.5	15358.0	14388.6	13797.3	14388.6	15358.0	15350.5	13827.2	12593.6	11998.1
20°	13150.2	14881.5	14434.2	12661.1	11960.6	12661.1	14434.2	14881.5	13150.2	11778.8	11194.5
22.5°	12301.5	14249.0	13147.6	10923.2	9967.5	10923.2	13147.6	14249.0	12301.5	10831.1	10223.0
25°	11308.9	13473.9	11763.6	9029.6	8051.9	9029.6	11763.6	13473.9	11308.9	9702.0	9152.0
27.5°	10141.2	12491.6	10289.8	7378.6	6476.6	7378.6	10289.8	12491.6	10141.2	8536.2	7974.5
30°	8844.4	11232.3	8756.1	5876.2	5045.5	5876.2	8756.1	11232.3	8844.4	7226.4	6723.5
32.5°	7392.4	9998.0	7283.1	4708.4	4004.8	4708.4	7283.1	9998.0	7392.4	5976.5	5451.0
35°	6052.8	8453.6	5955.1	3699.7	3117.8	3699.7	5955.1	8453.6	6052.8	4796.7	4280.5
37.5°	4750.2	6994.4	4747.1	2979.1	2529.0	2979.1	4747.1	6994.4	4750.2	3729.2	3310.2
40°	3695.7	5469.0	3719.4	2378.1	2029.5	2378.1	3719.4	5469.0	3695.7	2837.4	2569.4
42.5°	2800.2	4181.9	2923.5	1951.8	1723.8	1951.8	2923.5	4181.9	2800.2	2235.6	2034.9
45°	2188.9	3077.4	2282.9	1646.7	1467.4	1646.7	2282.9	3077.4	2188.9	1800.4	1665.6
47.5°	1782.6	2378.4	1850.2	1412.4	1286.8	1412.4	1850.2	2378.4	1782.6	1522.8	1421.9
50°	1497.2	1825.0	1536.3	1232.9	1148.6	1232.9	1536.3	1825.0	1497.2	1304.0	1236.7
52.5°	1286.2	1488.4	1308.3	1098.8	1042.0	1098.8	1308.3	1488.4	1286.2	1140.9	1099.1
55°	1108.5	1251.3	1137.7	988.1	948.8	988.1	1137.7	1251.3	1108.5	1015.3	984.4
57.5°	973.5	1061.4	988.1	893.7	867.6	893.7	988.1	1061.4	973.5	903.5	886.8
60°	853.9	919.3	871.9	811.5	804.0	811.5	871.9	919.3	853.9	812.9	802.0
62.5°	761.8	803.1	771.0	737.5	730.9	737.5	771.0	803.1	761.8	730.3	732.3
65°	675.8	714.2	689.0	671.0	673.2	671.0	689.0	714.2	675.8	661.2	664.4
67.5°	609.3	629.3	618.4	608.2	610.7	608.2	618.4	629.3	609.3	594.9	599.8
70°	538.5	560.0	548.8	550.2	554.5	550.2	548.8	560.0	538.5	534.2	537.9
72.5°	470.8	487.4	483.7	487.2	491.7	487.2	483.7	487.4	470.8	470.2	470.5
75°	404.2	416.9	418.6	423.5	430.7	423.5	418.6	416.9	404.2	400.0	405.2
77.5°	331.8	346.1	351.5	358.1	368.7	358.1	351.5	346.1	331.8	334.6	337.2
80°	265.2	271.9	283.9	288.7	303.6	288.7	283.9	271.9	265.2	260.4	264.1
82.5°	194.2	200.1	210.5	219.6	228.3	219.6	210.5	200.1	194.2	191.8	192.1
85°	112.1	121.3	128.2	139.1	141.6	139.1	128.2	121.3	112.1	114.7	112.1
87.5°	39.3	42.1	48.2	52.5	52.7	52.5	48.2	42.1	39.3	40.2	36.4
90°	16.7	28.2	48.7	26.8	18.7	26.8	48.7	28.2	16.7	29.3	45.7
92.5°	21.7	38.3	68.8	35.7	25.0	35.7	68.8	38.3	21.7	38.0	73.3
95°	32.0	47.1	87.8	39.4	30.0	39.4	87.8	47.1	32.0	50.7	102.3
97.5°	49.7	58.5	99.0	42.0	36.3	42.0	99.0	58.5	49.7	62.0	117.4
100°	66.1	66.1	180.9	48.3	41.4	48.3	180.9	66.1	66.1	76.1	182.9
102.5°	100.1	129.3	419.1	96.5	50.2	96.5	419.1	129.3	100.1	142.8	388.1
105°	181.9	295.5	737.8	248.8	92.0	248.8	737.8	295.5	181.9	299.0	691.6
107.5°	344.3	551.1	950.6	490.6	214.2	490.6	950.6	551.1	344.3	529.5	912.2
110°	550.8	770.2	1037.4	671.9	433.2	671.9	1037.4	770.2	550.8	727.1	956.2



TEST NUMBER: P1433742

CATALOG NUMBER: EHBR1-18-UNV-TASM-L940-UPL24

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
112.5°	717.0	858.3	1013.5	744.9	599.4	744.9	1013.5	858.3	717.0	802.6	916.0
115°	779.0	845.7	905.2	742.4	664.9	742.4	905.2	845.7	779.0	783.8	817.8
117.5°	752.6	774.0	781.8	697.2	668.7	697.2	781.8	774.0	752.6	704.7	694.4
120°	679.5	670.7	658.7	630.4	630.9	630.4	658.7	670.7	679.5	615.4	579.8
122.5°	587.9	569.0	556.7	562.6	579.3	562.6	556.7	569.0	587.9	523.7	496.9
125°	498.5	479.6	485.2	504.8	521.6	504.8	485.2	479.6	498.5	444.7	438.1
127.5°	423.2	414.4	433.6	455.7	470.0	455.7	433.6	414.4	423.2	389.2	396.5
130°	369.4	371.6	397.1	415.6	424.7	415.6	397.1	371.6	369.4	353.0	370.3
132.5°	335.8	345.5	369.8	385.7	391.0	385.7	369.8	345.5	335.8	331.0	352.1
135°	314.6	329.1	351.1	361.5	363.2	361.5	351.1	329.1	314.6	316.1	335.8
137.5°	302.3	316.9	333.5	341.6	339.4	341.6	333.5	316.9	302.3	306.3	321.1
140°	295.1	309.6	317.1	326.5	324.5	326.5	317.1	309.6	295.1	297.6	308.8
142.5°	287.8	301.0	304.8	311.6	309.4	311.6	304.8	301.0	287.8	290.3	297.8
145°	284.2	294.0	291.2	300.4	297.1	300.4	291.2	294.0	284.2	285.3	289.3
147.5°	277.9	285.3	281.5	289.3	286.1	289.3	281.5	285.3	277.9	277.9	279.5
150°	270.6	275.7	270.4	279.5	278.7	279.5	270.4	275.7	270.6	269.4	270.9
152.5°	260.9	265.9	260.9	271.2	270.3	271.2	260.9	265.9	260.9	259.6	261.1
155°	252.7	255.2	252.7	263.0	263.3	263.0	252.7	255.2	252.7	252.4	252.9
157.5°	246.9	248.5	247.2	256.4	256.7	256.4	247.2	248.5	246.9	246.9	247.2
160°	241.8	244.3	243.3	251.2	251.5	251.2	243.3	244.3	241.8	242.8	243.1
162.5°	239.8	239.8	239.2	247.0	247.5	247.0	239.2	239.8	239.8	239.8	241.1
165°	236.9	238.1	236.2	241.8	243.7	241.8	236.2	238.1	236.9	237.8	237.8
167.5°	236.2	235.0	235.5	240.2	242.0	240.2	235.5	235.0	236.2	237.2	237.2
170°	233.9	234.2	233.7	238.2	240.1	238.2	233.7	234.2	233.9	235.2	236.2
172.5°	234.9	234.9	233.2	236.5	239.6	236.5	233.2	234.9	234.9	235.8	237.0
175°	235.4	234.5	233.7	235.9	239.0	235.9	233.7	234.5	235.4	235.1	235.1
177.5°	234.2	234.8	235.3	237.4	241.8	237.4	235.3	234.8	234.2	235.1	235.1
180°	234.8	234.8	234.8	234.8	234.8	234.8	234.8	234.8	234.8	234.8	234.8



TEST NUMBER: P1433742

CATALOG NUMBER: EHBR1-18-UNV-TASM-L940-UPL24

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
0°	15290.9	15290.9	15290.9	15290.9	15290.9	15290.9
2.5°	14846.8	14837.0	14846.8	14950.6	15085.6	15282.0
5°	14501.8	14448.0	14501.8	14616.8	14864.9	15238.7
7.5°	14100.1	14068.9	14100.1	14292.6	14605.9	15135.2
10°	13677.2	13606.4	13677.2	13894.6	14264.2	14977.2
12.5°	13156.0	13062.1	13156.0	13380.5	13846.7	14725.2
15°	12493.0	12410.7	12493.0	12742.2	13282.9	14352.5
17.5°	11781.7	11707.1	11781.7	11998.1	12593.6	13827.2
20°	10888.2	10829.7	10888.2	11194.5	11778.8	13150.2
22.5°	9950.9	9896.1	9950.9	10223.0	10831.1	12301.5
25°	8848.1	8818.3	8848.1	9152.0	9702.0	11308.9
27.5°	7656.5	7605.8	7656.5	7974.5	8536.2	10141.2
30°	6439.1	6355.0	6439.1	6723.5	7226.4	8844.4
32.5°	5248.2	5187.8	5248.2	5451.0	5976.5	7392.4
35°	4097.4	4036.8	4097.4	4280.5	4796.7	6052.8
37.5°	3192.8	3085.8	3192.8	3310.2	3729.2	4750.2
40°	2421.4	2404.2	2421.4	2569.4	2837.4	3695.7
42.5°	1971.3	1924.5	1971.3	2034.9	2235.6	2800.2
45°	1617.4	1599.1	1617.4	1665.6	1800.4	2188.9
47.5°	1390.9	1399.0	1390.9	1421.9	1522.8	1782.6
50°	1222.0	1226.9	1222.0	1236.7	1304.0	1497.2
52.5°	1097.6	1093.3	1097.6	1099.1	1140.9	1286.2
55°	987.5	982.0	987.5	984.4	1015.3	1108.5
57.5°	891.1	895.1	891.1	886.8	903.5	973.5
60°	805.1	808.9	805.1	802.0	812.9	853.9
62.5°	732.6	734.9	732.6	732.3	730.3	761.8
65°	667.8	670.4	667.8	664.4	661.2	675.8
67.5°	605.8	605.8	605.8	599.8	594.9	609.3
70°	547.6	547.3	547.6	537.9	534.2	538.5
72.5°	477.7	484.5	477.7	470.5	470.2	470.8
75°	409.7	417.8	409.7	405.2	400.0	404.2
77.5°	340.9	353.3	340.9	337.2	334.6	331.8
80°	270.4	283.9	270.4	264.1	260.4	265.2
82.5°	199.8	209.9	199.8	192.1	191.8	194.2
85°	119.0	135.1	119.0	112.1	114.7	112.1
87.5°	38.1	48.7	38.1	36.4	40.2	39.3
90°	26.7	16.7	26.7	45.7	29.3	16.7
92.5°	40.6	24.2	40.6	73.3	38.0	21.7
95°	46.9	27.9	46.9	102.3	50.7	32.0
97.5°	51.9	35.8	51.9	117.4	62.0	49.7
100°	60.7	47.1	60.7	182.9	76.1	66.1
102.5°	128.8	79.8	128.8	388.1	142.8	100.1
105°	271.0	137.8	271.0	691.6	299.0	181.9
107.5°	485.1	238.5	485.1	912.2	529.5	344.3
110°	643.7	445.0	643.7	956.2	727.1	550.8



TEST NUMBER: P1433742

CATALOG NUMBER: EHBR1-18-UNV-TASM-L940-UPL24

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
112.5°	691.6	601.2	691.6	916.0	802.6	717.0
115°	665.1	632.7	665.1	817.8	783.8	779.0
117.5°	607.2	611.3	607.2	694.4	704.7	752.6
120°	540.4	566.0	540.4	579.8	615.4	679.5
122.5°	479.1	509.2	479.1	496.9	523.7	587.9
125°	426.1	456.7	426.1	438.1	444.7	498.5
127.5°	389.6	410.1	389.6	396.5	389.2	423.2
130°	360.9	378.6	360.9	370.3	353.0	369.4
132.5°	341.1	352.4	341.1	352.1	331.0	335.8
135°	323.7	333.5	323.7	335.8	316.1	314.6
137.5°	308.9	317.4	308.9	321.1	306.3	302.3
140°	295.7	303.0	295.7	308.8	297.6	295.1
142.5°	282.1	287.2	282.1	297.8	290.3	287.8
145°	272.6	276.4	272.6	289.3	285.3	284.2
147.5°	264.4	266.9	264.4	279.5	277.9	277.9
150°	256.1	258.6	256.1	270.9	269.4	270.6
152.5°	247.6	250.4	247.6	261.1	259.6	260.9
155°	241.9	244.7	241.9	252.9	252.4	252.7
157.5°	238.7	240.6	238.7	247.2	246.9	246.9
160°	235.8	237.3	235.8	243.1	242.8	241.8
162.5°	232.5	234.1	232.5	241.1	239.8	239.8
165°	231.9	232.2	231.9	237.8	237.8	236.9
167.5°	230.9	232.2	230.9	237.2	237.2	236.2
170°	231.1	231.4	231.1	236.2	235.2	233.9
172.5°	231.7	232.0	231.7	237.0	235.8	234.9
175°	231.1	231.4	231.1	235.1	235.1	235.4
177.5°	232.6	232.9	232.6	235.1	235.1	234.2
180°	234.8	234.8	234.8	234.8	234.8	234.8



TEST NUMBER: P1433742
 CATALOG NUMBER: EHBR1-18-UNV-TASM-L940-UPL24

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.09	16.12	15.65	16.67	17.27	14.40	15.44	14.97	15.99	16.59
	3H	16.63	17.55	17.21	18.11	18.76	16.25	17.17	16.83	17.73	18.38
	4H	17.26	18.13	17.86	18.70	19.36	17.03	17.89	17.63	18.46	19.12
	6H	17.74	18.54	18.35	19.12	19.79	17.67	18.46	18.28	19.05	19.72
	8H	17.89	18.64	18.52	19.25	19.93	17.89	18.64	18.51	19.25	19.92
	12H	17.96	18.68	18.59	19.28	19.98	18.01	18.73	18.64	19.33	20.03
4H	2H	15.49	16.36	16.10	16.93	17.59	14.97	15.84	15.57	16.41	17.07
	3H	17.29	18.00	17.90	18.62	19.30	17.03	17.74	17.64	18.36	19.03
	4H	18.06	18.71	18.69	19.33	20.04	17.93	18.58	18.56	19.20	19.91
	6H	18.67	19.23	19.33	19.88	20.60	18.70	19.26	19.35	19.91	20.63
	8H	18.87	19.39	19.53	20.03	20.77	18.97	19.49	19.63	20.14	20.87
	12H	18.97	19.43	19.65	20.11	20.84	19.14	19.60	19.81	20.27	21.01
8H	4H	18.31	18.83	18.96	19.47	20.20	18.21	18.73	18.87	19.37	20.11
	6H	19.05	19.47	19.73	20.16	20.90	19.11	19.53	19.80	20.23	20.96
	8H	19.32	19.70	20.02	20.39	21.15	19.47	19.84	20.17	20.54	21.29
	12H	19.49	19.82	20.19	20.50	21.32	19.71	20.04	20.41	20.72	21.55
12H	4H	18.32	18.77	18.99	19.45	20.18	18.22	18.68	18.89	19.35	20.09
	6H	19.09	19.47	19.80	20.17	20.92	19.16	19.54	19.86	20.23	20.99
	8H	19.41	19.74	20.11	20.42	21.24	19.56	19.89	20.26	20.57	21.39

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2506-472-6

Test Date: 08/01/2025

Luminaire Tested: EHBR-60-L935-N

Data in this report applies to families of products including EHBR-60-L935-N

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2506-472-6
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 08/05/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Metalux
 Catalog Number: **EHBR-60-L935-N**
 Description: Elevate Round Highbay at, 60000 lumens, 3500K 90CRI LEDs with N lens

Spectral Parameters

CCT (K): 3406
 CIE u': 0.2394
 CIE v': 0.5094
 Duv: -0.0028
 CIE x: 0.4076
 CIE y: 0.3856
 CIE z: 0.2068
 Peak Wavelength (nm): 630
 Dominant Wavelength (nm): 582
 Purity: 38.0517
 Rf: 91.3
 Rg: 100

CRI (Ra):	94.6		
R1:	96.6	R9:	63.8
R2:	98.4	R10:	94.7
R3:	98.1	R11:	96.6
R4:	95.8	R12:	80.9
R5:	96.2	R13:	97.4
R6:	95.4	R14:	98.3
R7:	91.8	R15:	93.1
R8:	84.4		



Test Conditions

Stabilization Time: 35M
 Operation Time: 1H 35M
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP1-2506-472-6

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2506-472-6

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2506-472-6

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)
360	0	NR	490	140	NR	620	338	NR	750	8	NR	880	0	NR
365	0	NR	495	159	NR	625	339	NR	755	7	NR	885	0	NR
370	0	NR	500	182	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	202	NR	635	653	NR	765	5	NR	895	0	NR
380	0	NR	510	216	NR	640	222	NR	770	4	NR	900	0	NR
385	0	NR	515	228	NR	645	214	NR	775	3	NR	905	0	NR
390	0	NR	520	236	NR	650	185	NR	780	3	NR	910	0	NR
395	1	NR	525	242	NR	655	157	NR	785	3	NR	915	0	NR
400	2	NR	530	248	NR	660	133	NR	790	2	NR	920	0	NR
405	3	NR	535	253	NR	665	113	NR	795	2	NR	925	0	NR
410	4	NR	540	258	NR	670	103	NR	800	2	NR	930	0	NR
415	7	NR	545	264	NR	675	85	NR	805	1	NR	935	0	NR
420	13	NR	550	270	NR	680	72	NR	810	1	NR	940	0	NR
425	22	NR	555	278	NR	685	62	NR	815	1	NR	945	0	NR
430	38	NR	560	286	NR	690	53	NR	820	1	NR	950	0	NR
435	65	NR	565	295	NR	695	45	NR	825	1	NR	955	0	NR
440	108	NR	570	303	NR	700	39	NR	830	1	NR	960	0	NR
445	193	NR	575	311	NR	705	33	NR	835	1	NR	965	0	NR
450	312	NR	580	319	NR	710	28	NR	840	1	NR	970	0	NR
455	300	NR	585	326	NR	715	24	NR	845	0	NR	975	0	NR
460	214	NR	590	332	NR	720	20	NR	850	0	NR	980	0	NR
465	184	NR	595	333	NR	725	17	NR	855	0	NR	985	0	NR
470	153	NR	600	336	NR	730	15	NR	860	0	NR	990	0	NR
475	122	NR	605	337	NR	735	12	NR	865	0	NR	995	0	NR
480	115	NR	610	367	NR	740	10	NR	870	0	NR	1000	0	NR
485	125	NR	615	390	NR	745	9	NR	875	0	NR			

REPORT NUMBER: SP1-2506-472-6

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.62

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	140	NR	620	338	NR	750	8	NR	880	0	NR
365	0	NR	495	159	NR	625	339	NR	755	7	NR	885	0	NR
370	0	NR	500	182	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	202	NR	635	653	NR	765	5	NR	895	0	NR
380	0	NR	510	216	NR	640	222	NR	770	4	NR	900	0	NR
385	0	NR	515	228	NR	645	214	NR	775	3	NR	905	0	NR
390	0	NR	520	236	NR	650	185	NR	780	3	NR	910	0	NR
395	1	NR	525	242	NR	655	157	NR	785	3	NR	915	0	NR
400	2	NR	530	248	NR	660	133	NR	790	2	NR	920	0	NR
405	3	NR	535	253	NR	665	113	NR	795	2	NR	925	0	NR
410	4	NR	540	258	NR	670	103	NR	800	2	NR	930	0	NR
415	7	NR	545	264	NR	675	85	NR	805	1	NR	935	0	NR
420	13	NR	550	270	NR	680	72	NR	810	1	NR	940	0	NR
425	22	NR	555	278	NR	685	62	NR	815	1	NR	945	0	NR
430	38	NR	560	286	NR	690	53	NR	820	1	NR	950	0	NR
435	65	NR	565	295	NR	695	45	NR	825	1	NR	955	0	NR
440	108	NR	570	303	NR	700	39	NR	830	1	NR	960	0	NR
445	193	NR	575	311	NR	705	33	NR	835	1	NR	965	0	NR
450	312	NR	580	319	NR	710	28	NR	840	1	NR	970	0	NR
455	300	NR	585	326	NR	715	24	NR	845	0	NR	975	0	NR
460	214	NR	590	332	NR	720	20	NR	850	0	NR	980	0	NR
465	184	NR	595	333	NR	725	17	NR	855	0	NR	985	0	NR
470	153	NR	600	336	NR	730	15	NR	860	0	NR	990	0	NR
475	122	NR	605	337	NR	735	12	NR	865	0	NR	995	0	NR
480	115	NR	610	367	NR	740	10	NR	870	0	NR	1000	0	NR
485	125	NR	615	390	NR	745	9	NR	875	0	NR			

REPORT NUMBER: SP1-2506-472-6

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 3.3

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	140	NR	620	338	NR	750	8	NR	880	0	NR
365	0	NR	495	159	NR	625	339	NR	755	7	NR	885	0	NR
370	0	NR	500	182	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	202	NR	635	653	NR	765	5	NR	895	0	NR
380	0	NR	510	216	NR	640	222	NR	770	4	NR	900	0	NR
385	0	NR	515	228	NR	645	214	NR	775	3	NR	905	0	NR
390	0	NR	520	236	NR	650	185	NR	780	3	NR	910	0	NR
395	1	NR	525	242	NR	655	157	NR	785	3	NR	915	0	NR
400	2	NR	530	248	NR	660	133	NR	790	2	NR	920	0	NR
405	3	NR	535	253	NR	665	113	NR	795	2	NR	925	0	NR
410	4	NR	540	258	NR	670	103	NR	800	2	NR	930	0	NR
415	7	NR	545	264	NR	675	85	NR	805	1	NR	935	0	NR
420	13	NR	550	270	NR	680	72	NR	810	1	NR	940	0	NR
425	22	NR	555	278	NR	685	62	NR	815	1	NR	945	0	NR
430	38	NR	560	286	NR	690	53	NR	820	1	NR	950	0	NR
435	65	NR	565	295	NR	695	45	NR	825	1	NR	955	0	NR
440	108	NR	570	303	NR	700	39	NR	830	1	NR	960	0	NR
445	193	NR	575	311	NR	705	33	NR	835	1	NR	965	0	NR
450	312	NR	580	319	NR	710	28	NR	840	1	NR	970	0	NR
455	300	NR	585	326	NR	715	24	NR	845	0	NR	975	0	NR
460	214	NR	590	332	NR	720	20	NR	850	0	NR	980	0	NR
465	184	NR	595	333	NR	725	17	NR	855	0	NR	985	0	NR
470	153	NR	600	336	NR	730	15	NR	860	0	NR	990	0	NR
475	122	NR	605	337	NR	735	12	NR	865	0	NR	995	0	NR
480	115	NR	610	367	NR	740	10	NR	870	0	NR	1000	0	NR
485	125	NR	615	390	NR	745	9	NR	875	0	NR			

Summary

$R_f = 91.3$
 $R_g = 100$
 $CIE R_a = 94.6$
 $R_9 = 63.8$



Color Vector Graphics




Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 94	CES51 = 97	CES76 = 90
CES02 = 63	CES27 = 92	CES52 = 98	CES77 = 86
CES03 = 31	CES28 = 97	CES53 = 98	CES78 = 86
CES04 = 70	CES29 = 97	CES54 = 93	CES79 = 90
CES05 = 50	CES30 = 92	CES55 = 92	CES80 = 91
CES06 = 51	CES31 = 97	CES56 = 96	CES81 = 74
CES07 = 43	CES32 = 89	CES57 = 94	CES82 = 96
CES08 = 41	CES33 = 99	CES58 = 95	CES83 = 94
CES09 = 29	CES34 = 94	CES59 = 98	CES84 = 95
CES10 = 75	CES35 = 97	CES60 = 92	CES85 = 79
CES11 = 58	CES36 = 81	CES61 = 93	CES86 = 79
CES12 = 64	CES37 = 96	CES62 = 86	CES87 = 92
CES13 = 44	CES38 = 87	CES63 = 94	CES88 = 98
CES14 = 74	CES39 = 99	CES64 = 91	CES89 = 84
CES15 = 72	CES40 = 97	CES65 = 90	CES90 = 96
CES16 = 48	CES41 = 96	CES66 = 89	CES91 = 75
CES17 = 49	CES42 = 94	CES67 = 88	CES92 = 76
CES18 = 56	CES43 = 93	CES68 = 89	CES93 = 86
CES19 = 71	CES44 = 99	CES69 = 90	CES94 = 74
CES20 = 67	CES45 = 97	CES70 = 88	CES95 = 83
CES21 = 86	CES46 = 97	CES71 = 83	CES96 = 92
CES22 = 78	CES47 = 91	CES72 = 94	CES97 = 96
CES23 = 91	CES48 = 91	CES73 = 83	CES98 = 95
CES24 = 90	CES49 = 96	CES74 = 90	CES99 = 92
CES25 = 71	CES50 = 98	CES75 = 85	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)