

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: METALUX

Report Number: P1433840

Luminaire Tested: EHBR1-36-UNV-TASM-L940-UPL36

Issue Date: 3/20/2026

Test Information

Test Method: LM-79-2019
Report Number: P1433840
REPORT IS A COMBINATION OF REPORTS P1431777 AND P1431635
Test Lab: INNOVATION CENTER
Issue Date: 3/20/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: METALUX
Catalog Number: EHBR1-36-UNV-TASM-L940-UPL36
Description: Elevate Round Highbay at, 36000 lumens, 4000K 90CRI LEDs with TASM lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 37035.6 lumens
Efficiency: N/A
Efficacy: 168.5 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.84 / 0.9
Luminous Opening: Vertical Cylinder (Dia: 1.71' x H: 0.1')
CIE Type: Direct

Input Watts (W): 219.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1433840
CATALOG NUMBER: EHBR1-36-UNV-TASM-L940-UPL36

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - · - · 90°-270° - · - · 135°-315°



TEST NUMBER: P1433840

CATALOG NUMBER: EHBR1-36-UNV-TASM-L940-UPL36

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|----|----|----|----|----|----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 |
| RCR | | | | | | | | | | | | | | | | | | | | |
| 0 | 117 | 117 | 117 | 117 | 113 | 113 | 113 | 113 | 106 | 106 | 106 | 99 | 99 | 99 | 93 | 93 | 93 | 93 | 91 | |
| 1 | 110 | 106 | 103 | 100 | 106 | 103 | 100 | 98 | 97 | 95 | 93 | 92 | 90 | 89 | 87 | 86 | 84 | 84 | 82 | |
| 2 | 103 | 97 | 92 | 87 | 99 | 94 | 89 | 86 | 89 | 86 | 82 | 85 | 82 | 79 | 81 | 78 | 76 | 76 | 74 | |
| 3 | 96 | 88 | 82 | 77 | 93 | 86 | 81 | 76 | 82 | 78 | 74 | 78 | 75 | 71 | 75 | 72 | 69 | 69 | 67 | |
| 4 | 90 | 81 | 75 | 70 | 88 | 79 | 73 | 69 | 76 | 71 | 67 | 73 | 68 | 65 | 70 | 66 | 63 | 63 | 61 | |
| 5 | 85 | 75 | 68 | 63 | 82 | 73 | 67 | 62 | 70 | 65 | 61 | 68 | 63 | 60 | 65 | 61 | 58 | 58 | 56 | |
| 6 | 80 | 70 | 63 | 58 | 78 | 68 | 62 | 57 | 66 | 60 | 56 | 63 | 58 | 55 | 61 | 57 | 54 | 54 | 52 | |
| 7 | 75 | 65 | 58 | 53 | 73 | 64 | 57 | 53 | 61 | 56 | 52 | 59 | 54 | 51 | 57 | 53 | 50 | 50 | 48 | |
| 8 | 71 | 60 | 54 | 49 | 69 | 59 | 53 | 49 | 58 | 52 | 48 | 56 | 51 | 47 | 54 | 50 | 46 | 46 | 45 | |
| 9 | 67 | 57 | 50 | 46 | 66 | 56 | 50 | 45 | 54 | 48 | 45 | 52 | 47 | 44 | 51 | 47 | 43 | 43 | 42 | |
| 10 | 64 | 53 | 47 | 43 | 62 | 52 | 46 | 42 | 51 | 45 | 42 | 50 | 45 | 41 | 48 | 44 | 41 | 41 | 39 | |

AVERAGE LUMINANCE (cd/sqm):

| | 0° | 90° | 180° | 270° |
|-----|--------|--------|--------|--------|
| 0° | 141138 | 141138 | 141138 | 141138 |
| 5° | 140280 | 149652 | 140280 | 133000 |
| 10° | 138555 | 153494 | 138555 | 125873 |
| 15° | 134464 | 142644 | 134464 | 116273 |
| 20° | 125757 | 114381 | 125757 | 103566 |
| 25° | 111305 | 79250 | 111305 | 86793 |
| 30° | 90376 | 51558 | 90376 | 64939 |
| 35° | 64820 | 33390 | 64820 | 43231 |
| 40° | 41908 | 23014 | 41908 | 27264 |
| 45° | 26590 | 17827 | 26590 | 19426 |
| 50° | 19747 | 15149 | 19747 | 16181 |
| 55° | 16122 | 13800 | 16122 | 14283 |
| 60° | 13961 | 13145 | 13961 | 13225 |
| 65° | 12726 | 12677 | 12726 | 12623 |
| 70° | 12061 | 12421 | 12061 | 12262 |
| 75° | 11280 | 12017 | 11280 | 11658 |
| 80° | 9909 | 11345 | 9909 | 10607 |
| 85° | 6410 | 8100 | 6410 | 7722 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 37385 cd/sqm



TEST NUMBER: P1433840
 CATALOG NUMBER: EHBR1-36-UNV-TASM-L940-UPL36

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 2857.7 | 7.7 |
| 10°-20° | 7774.6 | 21.0 |
| 20°-30° | 9118.0 | 24.6 |
| 30°-40° | 6341.0 | 17.1 |
| 40°-50° | 3151.2 | 8.5 |
| 50°-60° | 1884.7 | 5.1 |
| 60°-70° | 1326.6 | 3.6 |
| 70°-80° | 854.5 | 2.3 |
| 80°-90° | 277.5 | 0.7 |
| 90°-100° | 91.9 | 0.2 |
| 100°-110° | 599.8 | 1.6 |
| 110°-120° | 1108.1 | 3.0 |
| 120°-130° | 658.6 | 1.8 |
| 130°-140° | 398.3 | 1.1 |
| 140°-150° | 275.6 | 0.7 |
| 150°-160° | 179.9 | 0.5 |
| 160°-170° | 103.3 | 0.3 |
| 170°-180° | 34.4 | 0.1 |
| 0°-30° | 19750.3 | 53.3 |
| 0°-40° | 26091.3 | 70.4 |
| 0°-60° | 31127.2 | 84.0 |
| 0°-90° | 33585.8 | 90.7 |
| 90°-120° | 1799.8 | 4.9 |
| 90°-150° | 3132.3 | 8.5 |
| 90°-180° | 3450.0 | 9.3 |
| 0°-180° | 37035.6 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | 90° | 180° | 270° | 360° | Flux |
|------|-------|-------|-------|-------|-------|-------|
| 0° | 30054 | 30054 | 30054 | 30054 | 30054 | |
| 5° | 29952 | 31953 | 29952 | 28398 | 29952 | 2842 |
| 15° | 28210 | 29926 | 28210 | 24393 | 28210 | 7884 |
| 25° | 22228 | 15826 | 22228 | 17332 | 22228 | 10063 |
| 35° | 11897 | 6128 | 11897 | 7934 | 11897 | 7427 |
| 45° | 4302 | 2884 | 4302 | 3143 | 4302 | 3521 |
| 55° | 2179 | 1865 | 2179 | 1930 | 2179 | 1992 |
| 65° | 1328 | 1323 | 1328 | 1318 | 1328 | 1334 |
| 75° | 795 | 846 | 795 | 821 | 795 | 834 |
| 85° | 220 | 278 | 220 | 265 | 220 | 245 |
| 90° | 25 | 29 | 25 | 25 | 25 | 22 |
| 95° | 49 | 46 | 49 | 42 | 49 | 52 |
| 105° | 276 | 140 | 276 | 209 | 276 | 371 |
| 115° | 1179 | 1007 | 1179 | 958 | 1179 | 1075 |
| 125° | 755 | 791 | 755 | 692 | 755 | 695 |
| 135° | 477 | 551 | 477 | 505 | 477 | 378 |
| 145° | 432 | 451 | 432 | 420 | 432 | 271 |
| 155° | 384 | 401 | 384 | 373 | 384 | 180 |
| 165° | 362 | 373 | 362 | 355 | 362 | 103 |
| 175° | 361 | 367 | 361 | 355 | 361 | 34 |
| 180° | 360 | 360 | 360 | 360 | 360 | |



TEST NUMBER: P1433840
 CATALOG NUMBER: EHBR1-36-UNV-TASM-L940-UPL36

CANDELA DISTRIBUTION (FULL):

| | 0° | 22.5° | 45° | 67.5° | 90° | 112.5° | 135° | 157.5° | 180° | 202.5° | 225° |
|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0° | 30054.4 | 30054.4 | 30054.4 | 30054.4 | 30054.4 | 30054.4 | 30054.4 | 30054.4 | 30054.4 | 30054.4 | 30054.4 |
| 2.5° | 30036.9 | 30425.2 | 30739.7 | 30947.1 | 31049.6 | 30947.1 | 30739.7 | 30425.2 | 30036.9 | 29650.8 | 29385.4 |
| 5° | 29951.9 | 30729.6 | 31388.4 | 31819.5 | 31953.0 | 31819.5 | 31388.4 | 30729.6 | 29951.9 | 29217.0 | 28729.4 |
| 7.5° | 29748.4 | 30960.1 | 31939.0 | 32442.2 | 32565.1 | 32442.2 | 31939.0 | 30960.1 | 29748.4 | 28708.0 | 28092.1 |
| 10° | 29437.9 | 31105.4 | 32236.5 | 32597.2 | 32611.9 | 32597.2 | 32236.5 | 31105.4 | 29437.9 | 28036.3 | 27309.8 |
| 12.5° | 28942.5 | 31053.6 | 32136.8 | 32018.4 | 31749.6 | 32018.4 | 32136.8 | 31053.6 | 28942.5 | 27215.7 | 26299.3 |
| 15° | 28209.9 | 30746.5 | 31505.0 | 30541.9 | 29925.9 | 30541.9 | 31505.0 | 30746.5 | 28209.9 | 26107.8 | 25044.9 |
| 17.5° | 27177.4 | 30171.6 | 30186.3 | 28280.9 | 27118.8 | 28280.9 | 30186.3 | 30171.6 | 27177.4 | 24752.9 | 23582.4 |
| 20° | 25846.8 | 29249.7 | 28370.5 | 24885.4 | 23508.6 | 24885.4 | 28370.5 | 29249.7 | 25846.8 | 23151.3 | 22002.8 |
| 22.5° | 24178.6 | 28006.4 | 25841.7 | 21469.6 | 19591.2 | 21469.6 | 25841.7 | 28006.4 | 24178.6 | 21288.7 | 20093.4 |
| 25° | 22227.6 | 26483.1 | 23121.4 | 17747.9 | 15826.1 | 17747.9 | 23121.4 | 26483.1 | 22227.6 | 19069.4 | 17988.5 |
| 27.5° | 19932.8 | 24552.3 | 20224.7 | 14502.8 | 12729.8 | 14502.8 | 20224.7 | 24552.3 | 19932.8 | 16777.9 | 15673.9 |
| 30° | 17383.8 | 22077.1 | 17210.2 | 11549.7 | 9917.1 | 11549.7 | 17210.2 | 22077.1 | 17383.8 | 14203.6 | 13215.0 |
| 32.5° | 14529.9 | 19651.0 | 14315.1 | 9254.3 | 7871.3 | 9254.3 | 14315.1 | 19651.0 | 14529.9 | 11746.9 | 10713.9 |
| 35° | 11896.8 | 16615.6 | 11704.7 | 7271.7 | 6128.2 | 7271.7 | 11704.7 | 16615.6 | 11896.8 | 9427.9 | 8413.5 |
| 37.5° | 9336.6 | 13747.6 | 9330.4 | 5855.5 | 4970.6 | 5855.5 | 9330.4 | 13747.6 | 9336.6 | 7329.7 | 6506.3 |
| 40° | 7263.8 | 10749.4 | 7310.5 | 4674.3 | 3988.9 | 4674.3 | 7310.5 | 10749.4 | 7263.8 | 5577.0 | 5050.1 |
| 42.5° | 5503.8 | 8219.6 | 5746.1 | 3836.2 | 3388.1 | 3836.2 | 5746.1 | 8219.6 | 5503.8 | 4394.1 | 3999.6 |
| 45° | 4302.2 | 6048.7 | 4487.1 | 3236.5 | 2884.4 | 3236.5 | 4487.1 | 6048.7 | 4302.2 | 3538.7 | 3273.7 |
| 47.5° | 3503.7 | 4674.8 | 3636.7 | 2776.1 | 2529.3 | 2776.1 | 3636.7 | 4674.8 | 3503.7 | 2993.1 | 2794.8 |
| 50° | 2943.0 | 3587.1 | 3019.6 | 2423.3 | 2257.7 | 2423.3 | 3019.6 | 3587.1 | 2943.0 | 2563.1 | 2430.7 |
| 52.5° | 2528.1 | 2925.5 | 2571.5 | 2159.6 | 2048.0 | 2159.6 | 2571.5 | 2925.5 | 2528.1 | 2242.5 | 2160.1 |
| 55° | 2178.7 | 2459.4 | 2236.2 | 1942.0 | 1864.9 | 1942.0 | 2236.2 | 2459.4 | 2178.7 | 1995.6 | 1934.7 |
| 57.5° | 1913.3 | 2086.3 | 1942.0 | 1756.6 | 1705.4 | 1756.6 | 1942.0 | 2086.3 | 1913.3 | 1775.8 | 1743.1 |
| 60° | 1678.3 | 1806.8 | 1713.8 | 1594.9 | 1580.3 | 1594.9 | 1713.8 | 1806.8 | 1678.3 | 1597.7 | 1576.3 |
| 62.5° | 1497.4 | 1578.6 | 1515.4 | 1449.5 | 1436.5 | 1449.5 | 1515.4 | 1578.6 | 1497.4 | 1435.4 | 1439.4 |
| 65° | 1328.3 | 1403.8 | 1354.2 | 1318.7 | 1323.2 | 1318.7 | 1354.2 | 1403.8 | 1328.3 | 1299.6 | 1305.8 |
| 67.5° | 1197.5 | 1237.0 | 1215.6 | 1195.3 | 1200.4 | 1195.3 | 1215.6 | 1237.0 | 1197.5 | 1169.4 | 1179.0 |
| 70° | 1058.3 | 1100.6 | 1078.7 | 1081.5 | 1089.9 | 1081.5 | 1078.7 | 1100.6 | 1058.3 | 1050.0 | 1057.2 |
| 72.5° | 925.4 | 958.1 | 950.7 | 957.5 | 966.5 | 957.5 | 950.7 | 958.1 | 925.4 | 924.3 | 924.8 |
| 75° | 794.6 | 819.4 | 822.8 | 832.4 | 846.5 | 832.4 | 822.8 | 819.4 | 794.6 | 786.2 | 796.3 |
| 77.5° | 652.1 | 680.2 | 690.9 | 703.9 | 724.7 | 703.9 | 690.9 | 680.2 | 652.1 | 657.6 | 662.8 |
| 80° | 521.3 | 534.3 | 558.0 | 567.5 | 596.8 | 567.5 | 558.0 | 534.3 | 521.3 | 511.8 | 519.0 |
| 82.5° | 381.5 | 393.3 | 413.7 | 431.7 | 448.6 | 431.7 | 413.7 | 393.3 | 381.5 | 377.0 | 377.6 |
| 85° | 220.3 | 238.4 | 251.9 | 273.3 | 278.4 | 273.3 | 251.9 | 238.4 | 220.3 | 225.5 | 220.3 |
| 87.5° | 77.2 | 82.8 | 94.7 | 103.1 | 103.7 | 103.1 | 94.7 | 82.8 | 77.2 | 78.9 | 71.6 |
| 90° | 25.3 | 43.0 | 74.1 | 41.5 | 29.3 | 41.5 | 74.1 | 43.0 | 25.3 | 44.3 | 69.1 |
| 92.5° | 33.0 | 58.3 | 104.6 | 54.8 | 38.8 | 54.8 | 104.6 | 58.3 | 33.0 | 57.8 | 111.1 |
| 95° | 48.7 | 71.6 | 133.1 | 60.6 | 46.4 | 60.6 | 133.1 | 71.6 | 48.7 | 76.8 | 154.9 |
| 97.5° | 75.5 | 88.8 | 150.3 | 64.4 | 55.9 | 64.4 | 150.3 | 88.8 | 75.5 | 93.9 | 177.8 |
| 100° | 100.2 | 100.2 | 274.2 | 73.9 | 63.5 | 73.9 | 274.2 | 100.2 | 100.2 | 115.4 | 276.9 |
| 102.5° | 151.7 | 196.0 | 634.9 | 146.8 | 76.9 | 146.8 | 634.9 | 196.0 | 151.7 | 216.4 | 587.5 |
| 105° | 275.5 | 447.6 | 1117.0 | 377.4 | 140.3 | 377.4 | 1117.0 | 447.6 | 275.5 | 452.8 | 1046.7 |
| 107.5° | 521.3 | 834.4 | 1439.0 | 743.3 | 325.1 | 743.3 | 1439.0 | 834.4 | 521.3 | 801.5 | 1380.8 |
| 110° | 833.8 | 1166.0 | 1570.6 | 1017.7 | 656.7 | 1017.7 | 1570.6 | 1166.0 | 833.8 | 1100.6 | 1447.5 |



TEST NUMBER: P1433840
 CATALOG NUMBER: EHBR1-36-UNV-TASM-L940-UPL36

CANDELA DISTRIBUTION (continued):

| | 0° | 22.5° | 45° | 67.5° | 90° | 112.5° | 135° | 157.5° | 180° | 202.5° | 225° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 112.5° | 1085.4 | 1299.4 | 1534.3 | 1128.2 | 908.3 | 1128.2 | 1534.3 | 1299.4 | 1085.4 | 1215.0 | 1386.5 |
| 115° | 1179.4 | 1280.4 | 1370.5 | 1124.4 | 1007.4 | 1124.4 | 1370.5 | 1280.4 | 1179.4 | 1186.4 | 1237.9 |
| 117.5° | 1139.3 | 1171.7 | 1183.7 | 1055.8 | 1013.1 | 1055.8 | 1183.7 | 1171.7 | 1139.3 | 1066.9 | 1051.1 |
| 120° | 1028.8 | 1015.5 | 997.5 | 954.8 | 956.0 | 954.8 | 997.5 | 1015.5 | 1028.8 | 931.6 | 877.7 |
| 122.5° | 890.3 | 861.7 | 843.1 | 852.5 | 877.8 | 852.5 | 843.1 | 861.7 | 890.3 | 793.0 | 752.5 |
| 125° | 754.9 | 726.4 | 735.1 | 764.8 | 790.7 | 764.8 | 735.1 | 726.4 | 754.9 | 673.6 | 663.5 |
| 127.5° | 641.2 | 627.8 | 657.0 | 690.4 | 712.5 | 690.4 | 657.0 | 627.8 | 641.2 | 589.7 | 600.6 |
| 130° | 559.8 | 563.0 | 601.8 | 630.1 | 644.0 | 630.1 | 601.8 | 563.0 | 559.8 | 535.0 | 561.1 |
| 132.5° | 508.9 | 523.6 | 560.4 | 584.9 | 593.2 | 584.9 | 560.4 | 523.6 | 508.9 | 501.8 | 533.6 |
| 135° | 477.1 | 498.8 | 532.3 | 548.1 | 551.3 | 548.1 | 532.3 | 498.8 | 477.1 | 479.5 | 508.9 |
| 137.5° | 458.6 | 480.3 | 505.6 | 518.2 | 515.0 | 518.2 | 505.6 | 480.3 | 458.6 | 464.8 | 487.2 |
| 140° | 447.7 | 469.5 | 480.8 | 495.4 | 492.7 | 495.4 | 480.8 | 469.5 | 447.7 | 451.5 | 468.6 |
| 142.5° | 436.9 | 456.7 | 462.4 | 473.1 | 469.8 | 473.1 | 462.4 | 456.7 | 436.9 | 440.8 | 452.1 |
| 145° | 431.7 | 446.4 | 442.0 | 455.9 | 451.4 | 455.9 | 442.0 | 446.4 | 431.7 | 433.1 | 439.4 |
| 147.5° | 422.2 | 433.1 | 427.3 | 439.4 | 434.8 | 439.4 | 427.3 | 433.1 | 422.2 | 422.2 | 424.6 |
| 150° | 411.3 | 419.0 | 410.8 | 424.6 | 423.9 | 424.6 | 410.8 | 419.0 | 411.3 | 409.5 | 411.9 |
| 152.5° | 396.7 | 404.2 | 396.7 | 412.4 | 411.1 | 412.4 | 396.7 | 404.2 | 396.7 | 394.7 | 397.3 |
| 155° | 384.4 | 388.2 | 384.4 | 400.2 | 400.8 | 400.2 | 384.4 | 388.2 | 384.4 | 383.8 | 385.0 |
| 157.5° | 376.0 | 378.5 | 376.6 | 390.5 | 391.0 | 390.5 | 376.6 | 378.5 | 376.0 | 376.0 | 376.6 |
| 160° | 368.7 | 372.6 | 371.2 | 383.2 | 383.7 | 383.2 | 371.2 | 372.6 | 368.7 | 370.0 | 370.6 |
| 162.5° | 366.0 | 366.0 | 365.3 | 377.2 | 378.3 | 377.2 | 365.3 | 366.0 | 366.0 | 366.0 | 367.9 |
| 165° | 362.0 | 363.9 | 361.2 | 370.0 | 373.0 | 370.0 | 361.2 | 363.9 | 362.0 | 363.3 | 363.3 |
| 167.5° | 361.2 | 359.3 | 360.5 | 367.9 | 371.0 | 367.9 | 360.5 | 359.3 | 361.2 | 362.6 | 362.6 |
| 170° | 357.9 | 358.6 | 357.8 | 365.2 | 368.3 | 365.2 | 357.8 | 358.6 | 357.9 | 359.9 | 361.2 |
| 172.5° | 359.7 | 359.7 | 357.6 | 363.1 | 368.0 | 363.1 | 357.6 | 359.7 | 359.7 | 361.1 | 363.0 |
| 175° | 360.8 | 359.5 | 358.7 | 362.3 | 367.3 | 362.3 | 358.7 | 359.5 | 360.8 | 360.3 | 360.3 |
| 177.5° | 359.0 | 360.1 | 361.2 | 364.7 | 371.6 | 364.7 | 361.2 | 360.1 | 359.0 | 360.3 | 360.3 |
| 180° | 360.1 | 360.1 | 360.1 | 360.1 | 360.1 | 360.1 | 360.1 | 360.1 | 360.1 | 360.1 | 360.1 |



TEST NUMBER: P1433840

CATALOG NUMBER: EHBR1-36-UNV-TASM-L940-UPL36

CANDELA DISTRIBUTION (continued):

| | 247.5° | 270° | 292.5° | 315° | 337.5° | 360° |
|--------|---------|---------|---------|---------|---------|---------|
| 0° | 30054.4 | 30054.4 | 30054.4 | 30054.4 | 30054.4 | 30054.4 |
| 2.5° | 29181.5 | 29162.3 | 29181.5 | 29385.4 | 29650.8 | 30036.9 |
| 5° | 28503.4 | 28397.5 | 28503.4 | 28729.4 | 29217.0 | 29951.9 |
| 7.5° | 27714.0 | 27652.5 | 27714.0 | 28092.1 | 28708.0 | 29748.4 |
| 10° | 26882.6 | 26743.5 | 26882.6 | 27309.8 | 28036.3 | 29437.9 |
| 12.5° | 25858.1 | 25673.8 | 25858.1 | 26299.3 | 27215.7 | 28942.5 |
| 15° | 24555.1 | 24393.4 | 24555.1 | 25044.9 | 26107.8 | 28209.9 |
| 17.5° | 23156.9 | 23010.4 | 23156.9 | 23582.4 | 24752.9 | 27177.4 |
| 20° | 21400.8 | 21285.9 | 21400.8 | 22002.8 | 23151.3 | 25846.8 |
| 22.5° | 19558.5 | 19450.9 | 19558.5 | 20093.4 | 21288.7 | 24178.6 |
| 25° | 17391.0 | 17332.4 | 17391.0 | 17988.5 | 19069.4 | 22227.6 |
| 27.5° | 15048.9 | 14949.2 | 15048.9 | 15673.9 | 16777.9 | 19932.8 |
| 30° | 12656.0 | 12490.9 | 12656.0 | 13215.0 | 14203.6 | 17383.8 |
| 32.5° | 10315.5 | 10196.6 | 10315.5 | 10713.9 | 11746.9 | 14529.9 |
| 35° | 8053.3 | 7934.5 | 8053.3 | 8413.5 | 9427.9 | 11896.8 |
| 37.5° | 6275.3 | 6065.1 | 6275.3 | 6506.3 | 7329.7 | 9336.6 |
| 40° | 4759.3 | 4725.5 | 4759.3 | 5050.1 | 5577.0 | 7263.8 |
| 42.5° | 3874.5 | 3782.7 | 3874.5 | 3999.6 | 4394.1 | 5503.8 |
| 45° | 3179.1 | 3143.0 | 3179.1 | 3273.7 | 3538.7 | 4302.2 |
| 47.5° | 2733.8 | 2749.7 | 2733.8 | 2794.8 | 2993.1 | 3503.7 |
| 50° | 2401.9 | 2411.5 | 2401.9 | 2430.7 | 2563.1 | 2943.0 |
| 52.5° | 2157.3 | 2148.8 | 2157.3 | 2160.1 | 2242.5 | 2528.1 |
| 55° | 1940.9 | 1930.2 | 1940.9 | 1934.7 | 1995.6 | 2178.7 |
| 57.5° | 1751.6 | 1759.4 | 1751.6 | 1743.1 | 1775.8 | 1913.3 |
| 60° | 1582.5 | 1589.9 | 1582.5 | 1576.3 | 1597.7 | 1678.3 |
| 62.5° | 1440.0 | 1444.4 | 1440.0 | 1439.4 | 1435.4 | 1497.4 |
| 65° | 1312.5 | 1317.6 | 1312.5 | 1305.8 | 1299.6 | 1328.3 |
| 67.5° | 1190.8 | 1190.8 | 1190.8 | 1179.0 | 1169.4 | 1197.5 |
| 70° | 1076.4 | 1075.9 | 1076.4 | 1057.2 | 1050.0 | 1058.3 |
| 72.5° | 938.9 | 952.4 | 938.9 | 924.8 | 924.3 | 925.4 |
| 75° | 805.3 | 821.2 | 805.3 | 796.3 | 786.2 | 794.6 |
| 77.5° | 670.0 | 694.4 | 670.0 | 662.8 | 657.6 | 652.1 |
| 80° | 531.4 | 558.0 | 531.4 | 519.0 | 511.8 | 521.3 |
| 82.5° | 392.8 | 412.5 | 392.8 | 377.6 | 377.0 | 381.5 |
| 85° | 233.8 | 265.4 | 233.8 | 220.3 | 225.5 | 220.3 |
| 87.5° | 75.0 | 95.8 | 75.0 | 71.6 | 78.9 | 77.2 |
| 90° | 40.6 | 25.3 | 40.6 | 69.1 | 44.3 | 25.3 |
| 92.5° | 61.6 | 36.8 | 61.6 | 111.1 | 57.8 | 33.0 |
| 95° | 71.1 | 42.5 | 71.1 | 154.9 | 76.8 | 48.7 |
| 97.5° | 78.7 | 54.5 | 78.7 | 177.8 | 93.9 | 75.5 |
| 100° | 92.0 | 71.6 | 92.0 | 276.9 | 115.4 | 100.2 |
| 102.5° | 194.9 | 121.2 | 194.9 | 587.5 | 216.4 | 151.7 |
| 105° | 410.3 | 208.8 | 410.3 | 1046.7 | 452.8 | 275.5 |
| 107.5° | 734.2 | 361.3 | 734.2 | 1380.8 | 801.5 | 521.3 |
| 110° | 974.3 | 673.8 | 974.3 | 1447.5 | 1100.6 | 833.8 |



TEST NUMBER: P1433840

CATALOG NUMBER: EHBR1-36-UNV-TASM-L940-UPL36

CANDELA DISTRIBUTION (continued):

| | 247.5° | 270° | 292.5° | 315° | 337.5° | 360° |
|--------|--------|-------|--------|--------|--------|--------|
| 112.5° | 1046.7 | 910.1 | 1046.7 | 1386.5 | 1215.0 | 1085.4 |
| 115° | 1006.7 | 957.7 | 1006.7 | 1237.9 | 1186.4 | 1179.4 |
| 117.5° | 919.1 | 925.3 | 919.1 | 1051.1 | 1066.9 | 1139.3 |
| 120° | 818.1 | 856.7 | 818.1 | 877.7 | 931.6 | 1028.8 |
| 122.5° | 725.3 | 770.9 | 725.3 | 752.5 | 793.0 | 890.3 |
| 125° | 645.2 | 691.5 | 645.2 | 663.5 | 673.6 | 754.9 |
| 127.5° | 589.9 | 621.0 | 589.9 | 600.6 | 589.7 | 641.2 |
| 130° | 546.7 | 573.3 | 546.7 | 561.1 | 535.0 | 559.8 |
| 132.5° | 516.8 | 533.9 | 516.8 | 533.6 | 501.8 | 508.9 |
| 135° | 490.6 | 505.3 | 490.6 | 508.9 | 479.5 | 477.1 |
| 137.5° | 468.3 | 481.1 | 468.3 | 487.2 | 464.8 | 458.6 |
| 140° | 448.5 | 459.4 | 448.5 | 468.6 | 451.5 | 447.7 |
| 142.5° | 428.1 | 435.7 | 428.1 | 452.1 | 440.8 | 436.9 |
| 145° | 414.0 | 419.8 | 414.0 | 439.4 | 433.1 | 431.7 |
| 147.5° | 401.8 | 405.6 | 401.8 | 424.6 | 422.2 | 422.2 |
| 150° | 389.6 | 393.4 | 389.6 | 411.9 | 409.5 | 411.3 |
| 152.5° | 376.9 | 381.2 | 376.9 | 397.3 | 394.7 | 396.7 |
| 155° | 368.4 | 372.8 | 368.4 | 385.0 | 383.8 | 384.4 |
| 157.5° | 363.8 | 366.8 | 363.8 | 376.6 | 376.0 | 376.0 |
| 160° | 359.8 | 362.2 | 359.8 | 370.6 | 370.0 | 368.7 |
| 162.5° | 355.1 | 357.7 | 355.1 | 367.9 | 366.0 | 366.0 |
| 165° | 354.4 | 355.0 | 354.4 | 363.3 | 363.3 | 362.0 |
| 167.5° | 353.0 | 355.0 | 353.0 | 362.6 | 362.6 | 361.2 |
| 170° | 353.6 | 354.1 | 353.6 | 361.2 | 359.9 | 357.9 |
| 172.5° | 354.8 | 355.3 | 354.8 | 363.0 | 361.1 | 359.7 |
| 175° | 354.0 | 354.6 | 354.0 | 360.3 | 360.3 | 360.8 |
| 177.5° | 356.4 | 357.0 | 356.4 | 360.3 | 360.3 | 359.0 |
| 180° | 360.1 | 360.1 | 360.1 | 360.1 | 360.1 | 360.1 |



TEST NUMBER: P1433840
 CATALOG NUMBER: EHBR1-36-UNV-TASM-L940-UPL36

CIE UGR TABLE:

| Reflectances: | | | | | | | | | | | |
|-----------------|------|------------------|-------|-------|-------|-------|----------------|-------|-------|-------|-------|
| Ceiling | | 0.7 | 0.7 | 0.5 | 0.5 | 0.3 | 0.7 | 0.7 | 0.5 | 0.5 | 0.3 |
| Wall | | 0.5 | 0.3 | 0.5 | 0.3 | 0.3 | 0.5 | 0.3 | 0.5 | 0.3 | 0.3 |
| Reference plane | | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 |
| Room dimensions | | Viewed crosswise | | | | | Viewed endwise | | | | |
| X=2H | Y=2H | 17.63 | 18.70 | 18.15 | 19.20 | 19.74 | 16.95 | 18.01 | 17.47 | 18.52 | 19.06 |
| | 3H | 19.17 | 20.12 | 19.71 | 20.64 | 21.23 | 18.79 | 19.74 | 19.33 | 20.26 | 20.85 |
| | 4H | 19.81 | 20.70 | 20.37 | 21.23 | 21.84 | 19.57 | 20.46 | 20.13 | 20.99 | 21.60 |
| | 6H | 20.29 | 21.10 | 20.86 | 21.65 | 22.27 | 20.21 | 21.03 | 20.79 | 21.58 | 22.19 |
| | 8H | 20.44 | 21.21 | 21.02 | 21.78 | 22.40 | 20.43 | 21.21 | 21.02 | 21.77 | 22.40 |
| | 12H | 20.51 | 21.25 | 21.10 | 21.80 | 22.45 | 20.56 | 21.30 | 21.15 | 21.86 | 22.50 |
| 4H | 2H | 18.04 | 18.93 | 18.60 | 19.46 | 20.07 | 17.52 | 18.41 | 18.08 | 18.94 | 19.54 |
| | 3H | 19.83 | 20.57 | 20.41 | 21.15 | 21.77 | 19.57 | 20.31 | 20.15 | 20.88 | 21.51 |
| | 4H | 20.61 | 21.27 | 21.20 | 21.85 | 22.51 | 20.48 | 21.14 | 21.07 | 21.73 | 22.39 |
| | 6H | 21.22 | 21.79 | 21.84 | 22.40 | 23.08 | 21.25 | 21.82 | 21.87 | 22.43 | 23.11 |
| | 8H | 21.42 | 21.95 | 22.04 | 22.56 | 23.24 | 21.52 | 22.05 | 22.14 | 22.66 | 23.34 |
| | 12H | 21.52 | 21.99 | 22.16 | 22.63 | 23.32 | 21.69 | 22.16 | 22.32 | 22.80 | 23.48 |
| 8H | 4H | 20.86 | 21.39 | 21.48 | 22.00 | 22.68 | 20.76 | 21.29 | 21.38 | 21.90 | 22.58 |
| | 6H | 21.60 | 22.03 | 22.25 | 22.68 | 23.37 | 21.66 | 22.09 | 22.31 | 22.75 | 23.44 |
| | 8H | 21.87 | 22.25 | 22.54 | 22.92 | 23.62 | 22.01 | 22.40 | 22.68 | 23.07 | 23.77 |
| | 12H | 22.04 | 22.38 | 22.70 | 23.02 | 23.80 | 22.26 | 22.60 | 22.93 | 23.25 | 24.02 |
| 12H | 4H | 20.86 | 21.33 | 21.50 | 21.97 | 22.66 | 20.77 | 21.24 | 21.40 | 21.88 | 22.56 |
| | 6H | 21.64 | 22.03 | 22.31 | 22.69 | 23.39 | 21.71 | 22.09 | 22.38 | 22.76 | 23.46 |
| | 8H | 21.96 | 22.29 | 22.62 | 22.94 | 23.71 | 22.11 | 22.45 | 22.77 | 23.09 | 23.87 |

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2506-472-6

Test Date: 08/01/2025

Luminaire Tested: EHBR-60-L935-N

Data in this report applies to families of products including EHBR-60-L935-N

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2506-472-6
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 08/05/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Metalux
 Catalog Number: **EHBR-60-L935-N**
 Description: Elevate Round Highbay at, 60000 lumens, 3500K 90CRI LEDs with N lens

Spectral Parameters

CCT (K): 3406
 CIE u': 0.2394
 CIE v': 0.5094
 Duv: -0.0028
 CIE x: 0.4076
 CIE y: 0.3856
 CIE z: 0.2068
 Peak Wavelength (nm): 630
 Dominant Wavelength (nm): 582
 Purity: 38.0517
 Rf: 91.3
 Rg: 100

| | | | |
|-----------|------|------|------|
| CRI (Ra): | 94.6 | | |
| R1: | 96.6 | R9: | 63.8 |
| R2: | 98.4 | R10: | 94.7 |
| R3: | 98.1 | R11: | 96.6 |
| R4: | 95.8 | R12: | 80.9 |
| R5: | 96.2 | R13: | 97.4 |
| R6: | 95.4 | R14: | 98.3 |
| R7: | 91.8 | R15: | 93.1 |
| R8: | 84.4 | | |



Test Conditions

Stabilization Time: 35M
 Operation Time: 1H 35M
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP1-2506-472-6

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | 76INCH SPHERE IN0058 | 6/16/2025 | 12/16/2025 |
| Power Meter | XITRON INXT2011004 | 1/21/2025 | 1/21/2026 |
| AC Power Source | CHROMA 61603 IN0063 | 10/22/2024 | 10/22/2025 |
| DC Power Source | AGILENT E3634A IN0208 | 10/22/2024 | 10/22/2025 |
| Sphere Thermometer | ONSET IN0085 | 10/22/2024 | 10/22/2025 |
| Room Thermometer | ONSET IN0046 | 10/22/2024 | 10/22/2025 |

REPORT NUMBER: SP1-2506-472-6

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2506-472-6

Photopic Flux vs. Wavelength



Photopic Lumens: NR

| λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360 | 0 | NR | 490 | 140 | NR | 620 | 338 | NR | 750 | 8 | NR | 880 | 0 | NR |
| 365 | 0 | NR | 495 | 159 | NR | 625 | 339 | NR | 755 | 7 | NR | 885 | 0 | NR |
| 370 | 0 | NR | 500 | 182 | NR | 630 | 1000 | NR | 760 | 5 | NR | 890 | 0 | NR |
| 375 | 0 | NR | 505 | 202 | NR | 635 | 653 | NR | 765 | 5 | NR | 895 | 0 | NR |
| 380 | 0 | NR | 510 | 216 | NR | 640 | 222 | NR | 770 | 4 | NR | 900 | 0 | NR |
| 385 | 0 | NR | 515 | 228 | NR | 645 | 214 | NR | 775 | 3 | NR | 905 | 0 | NR |
| 390 | 0 | NR | 520 | 236 | NR | 650 | 185 | NR | 780 | 3 | NR | 910 | 0 | NR |
| 395 | 1 | NR | 525 | 242 | NR | 655 | 157 | NR | 785 | 3 | NR | 915 | 0 | NR |
| 400 | 2 | NR | 530 | 248 | NR | 660 | 133 | NR | 790 | 2 | NR | 920 | 0 | NR |
| 405 | 3 | NR | 535 | 253 | NR | 665 | 113 | NR | 795 | 2 | NR | 925 | 0 | NR |
| 410 | 4 | NR | 540 | 258 | NR | 670 | 103 | NR | 800 | 2 | NR | 930 | 0 | NR |
| 415 | 7 | NR | 545 | 264 | NR | 675 | 85 | NR | 805 | 1 | NR | 935 | 0 | NR |
| 420 | 13 | NR | 550 | 270 | NR | 680 | 72 | NR | 810 | 1 | NR | 940 | 0 | NR |
| 425 | 22 | NR | 555 | 278 | NR | 685 | 62 | NR | 815 | 1 | NR | 945 | 0 | NR |
| 430 | 38 | NR | 560 | 286 | NR | 690 | 53 | NR | 820 | 1 | NR | 950 | 0 | NR |
| 435 | 65 | NR | 565 | 295 | NR | 695 | 45 | NR | 825 | 1 | NR | 955 | 0 | NR |
| 440 | 108 | NR | 570 | 303 | NR | 700 | 39 | NR | 830 | 1 | NR | 960 | 0 | NR |
| 445 | 193 | NR | 575 | 311 | NR | 705 | 33 | NR | 835 | 1 | NR | 965 | 0 | NR |
| 450 | 312 | NR | 580 | 319 | NR | 710 | 28 | NR | 840 | 1 | NR | 970 | 0 | NR |
| 455 | 300 | NR | 585 | 326 | NR | 715 | 24 | NR | 845 | 0 | NR | 975 | 0 | NR |
| 460 | 214 | NR | 590 | 332 | NR | 720 | 20 | NR | 850 | 0 | NR | 980 | 0 | NR |
| 465 | 184 | NR | 595 | 333 | NR | 725 | 17 | NR | 855 | 0 | NR | 985 | 0 | NR |
| 470 | 153 | NR | 600 | 336 | NR | 730 | 15 | NR | 860 | 0 | NR | 990 | 0 | NR |
| 475 | 122 | NR | 605 | 337 | NR | 735 | 12 | NR | 865 | 0 | NR | 995 | 0 | NR |
| 480 | 115 | NR | 610 | 367 | NR | 740 | 10 | NR | 870 | 0 | NR | 1000 | 0 | NR |
| 485 | 125 | NR | 615 | 390 | NR | 745 | 9 | NR | 875 | 0 | NR | | | |

REPORT NUMBER: SP1-2506-472-6

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.62

| λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360 | 0 | NR | 490 | 140 | NR | 620 | 338 | NR | 750 | 8 | NR | 880 | 0 | NR |
| 365 | 0 | NR | 495 | 159 | NR | 625 | 339 | NR | 755 | 7 | NR | 885 | 0 | NR |
| 370 | 0 | NR | 500 | 182 | NR | 630 | 1000 | NR | 760 | 5 | NR | 890 | 0 | NR |
| 375 | 0 | NR | 505 | 202 | NR | 635 | 653 | NR | 765 | 5 | NR | 895 | 0 | NR |
| 380 | 0 | NR | 510 | 216 | NR | 640 | 222 | NR | 770 | 4 | NR | 900 | 0 | NR |
| 385 | 0 | NR | 515 | 228 | NR | 645 | 214 | NR | 775 | 3 | NR | 905 | 0 | NR |
| 390 | 0 | NR | 520 | 236 | NR | 650 | 185 | NR | 780 | 3 | NR | 910 | 0 | NR |
| 395 | 1 | NR | 525 | 242 | NR | 655 | 157 | NR | 785 | 3 | NR | 915 | 0 | NR |
| 400 | 2 | NR | 530 | 248 | NR | 660 | 133 | NR | 790 | 2 | NR | 920 | 0 | NR |
| 405 | 3 | NR | 535 | 253 | NR | 665 | 113 | NR | 795 | 2 | NR | 925 | 0 | NR |
| 410 | 4 | NR | 540 | 258 | NR | 670 | 103 | NR | 800 | 2 | NR | 930 | 0 | NR |
| 415 | 7 | NR | 545 | 264 | NR | 675 | 85 | NR | 805 | 1 | NR | 935 | 0 | NR |
| 420 | 13 | NR | 550 | 270 | NR | 680 | 72 | NR | 810 | 1 | NR | 940 | 0 | NR |
| 425 | 22 | NR | 555 | 278 | NR | 685 | 62 | NR | 815 | 1 | NR | 945 | 0 | NR |
| 430 | 38 | NR | 560 | 286 | NR | 690 | 53 | NR | 820 | 1 | NR | 950 | 0 | NR |
| 435 | 65 | NR | 565 | 295 | NR | 695 | 45 | NR | 825 | 1 | NR | 955 | 0 | NR |
| 440 | 108 | NR | 570 | 303 | NR | 700 | 39 | NR | 830 | 1 | NR | 960 | 0 | NR |
| 445 | 193 | NR | 575 | 311 | NR | 705 | 33 | NR | 835 | 1 | NR | 965 | 0 | NR |
| 450 | 312 | NR | 580 | 319 | NR | 710 | 28 | NR | 840 | 1 | NR | 970 | 0 | NR |
| 455 | 300 | NR | 585 | 326 | NR | 715 | 24 | NR | 845 | 0 | NR | 975 | 0 | NR |
| 460 | 214 | NR | 590 | 332 | NR | 720 | 20 | NR | 850 | 0 | NR | 980 | 0 | NR |
| 465 | 184 | NR | 595 | 333 | NR | 725 | 17 | NR | 855 | 0 | NR | 985 | 0 | NR |
| 470 | 153 | NR | 600 | 336 | NR | 730 | 15 | NR | 860 | 0 | NR | 990 | 0 | NR |
| 475 | 122 | NR | 605 | 337 | NR | 735 | 12 | NR | 865 | 0 | NR | 995 | 0 | NR |
| 480 | 115 | NR | 610 | 367 | NR | 740 | 10 | NR | 870 | 0 | NR | 1000 | 0 | NR |
| 485 | 125 | NR | 615 | 390 | NR | 745 | 9 | NR | 875 | 0 | NR | | | |

REPORT NUMBER: SP1-2506-472-6

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 3.3

| λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360 | 0 | NR | 490 | 140 | NR | 620 | 338 | NR | 750 | 8 | NR | 880 | 0 | NR |
| 365 | 0 | NR | 495 | 159 | NR | 625 | 339 | NR | 755 | 7 | NR | 885 | 0 | NR |
| 370 | 0 | NR | 500 | 182 | NR | 630 | 1000 | NR | 760 | 5 | NR | 890 | 0 | NR |
| 375 | 0 | NR | 505 | 202 | NR | 635 | 653 | NR | 765 | 5 | NR | 895 | 0 | NR |
| 380 | 0 | NR | 510 | 216 | NR | 640 | 222 | NR | 770 | 4 | NR | 900 | 0 | NR |
| 385 | 0 | NR | 515 | 228 | NR | 645 | 214 | NR | 775 | 3 | NR | 905 | 0 | NR |
| 390 | 0 | NR | 520 | 236 | NR | 650 | 185 | NR | 780 | 3 | NR | 910 | 0 | NR |
| 395 | 1 | NR | 525 | 242 | NR | 655 | 157 | NR | 785 | 3 | NR | 915 | 0 | NR |
| 400 | 2 | NR | 530 | 248 | NR | 660 | 133 | NR | 790 | 2 | NR | 920 | 0 | NR |
| 405 | 3 | NR | 535 | 253 | NR | 665 | 113 | NR | 795 | 2 | NR | 925 | 0 | NR |
| 410 | 4 | NR | 540 | 258 | NR | 670 | 103 | NR | 800 | 2 | NR | 930 | 0 | NR |
| 415 | 7 | NR | 545 | 264 | NR | 675 | 85 | NR | 805 | 1 | NR | 935 | 0 | NR |
| 420 | 13 | NR | 550 | 270 | NR | 680 | 72 | NR | 810 | 1 | NR | 940 | 0 | NR |
| 425 | 22 | NR | 555 | 278 | NR | 685 | 62 | NR | 815 | 1 | NR | 945 | 0 | NR |
| 430 | 38 | NR | 560 | 286 | NR | 690 | 53 | NR | 820 | 1 | NR | 950 | 0 | NR |
| 435 | 65 | NR | 565 | 295 | NR | 695 | 45 | NR | 825 | 1 | NR | 955 | 0 | NR |
| 440 | 108 | NR | 570 | 303 | NR | 700 | 39 | NR | 830 | 1 | NR | 960 | 0 | NR |
| 445 | 193 | NR | 575 | 311 | NR | 705 | 33 | NR | 835 | 1 | NR | 965 | 0 | NR |
| 450 | 312 | NR | 580 | 319 | NR | 710 | 28 | NR | 840 | 1 | NR | 970 | 0 | NR |
| 455 | 300 | NR | 585 | 326 | NR | 715 | 24 | NR | 845 | 0 | NR | 975 | 0 | NR |
| 460 | 214 | NR | 590 | 332 | NR | 720 | 20 | NR | 850 | 0 | NR | 980 | 0 | NR |
| 465 | 184 | NR | 595 | 333 | NR | 725 | 17 | NR | 855 | 0 | NR | 985 | 0 | NR |
| 470 | 153 | NR | 600 | 336 | NR | 730 | 15 | NR | 860 | 0 | NR | 990 | 0 | NR |
| 475 | 122 | NR | 605 | 337 | NR | 735 | 12 | NR | 865 | 0 | NR | 995 | 0 | NR |
| 480 | 115 | NR | 610 | 367 | NR | 740 | 10 | NR | 870 | 0 | NR | 1000 | 0 | NR |
| 485 | 125 | NR | 615 | 390 | NR | 745 | 9 | NR | 875 | 0 | NR | | | |

Summary

$R_f = 91.3$
 $R_g = 100$
 $CIE R_a = 94.6$
 $R_9 = 63.8$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 94 | CES51 = 97 | CES76 = 90 |
| CES02 = 63 | CES27 = 92 | CES52 = 98 | CES77 = 86 |
| CES03 = 31 | CES28 = 97 | CES53 = 98 | CES78 = 86 |
| CES04 = 70 | CES29 = 97 | CES54 = 93 | CES79 = 90 |
| CES05 = 50 | CES30 = 92 | CES55 = 92 | CES80 = 91 |
| CES06 = 51 | CES31 = 97 | CES56 = 96 | CES81 = 74 |
| CES07 = 43 | CES32 = 89 | CES57 = 94 | CES82 = 96 |
| CES08 = 41 | CES33 = 99 | CES58 = 95 | CES83 = 94 |
| CES09 = 29 | CES34 = 94 | CES59 = 98 | CES84 = 95 |
| CES10 = 75 | CES35 = 97 | CES60 = 92 | CES85 = 79 |
| CES11 = 58 | CES36 = 81 | CES61 = 93 | CES86 = 79 |
| CES12 = 64 | CES37 = 96 | CES62 = 86 | CES87 = 92 |
| CES13 = 44 | CES38 = 87 | CES63 = 94 | CES88 = 98 |
| CES14 = 74 | CES39 = 99 | CES64 = 91 | CES89 = 84 |
| CES15 = 72 | CES40 = 97 | CES65 = 90 | CES90 = 96 |
| CES16 = 48 | CES41 = 96 | CES66 = 89 | CES91 = 75 |
| CES17 = 49 | CES42 = 94 | CES67 = 88 | CES92 = 76 |
| CES18 = 56 | CES43 = 93 | CES68 = 89 | CES93 = 86 |
| CES19 = 71 | CES44 = 99 | CES69 = 90 | CES94 = 74 |
| CES20 = 67 | CES45 = 97 | CES70 = 88 | CES95 = 83 |
| CES21 = 86 | CES46 = 97 | CES71 = 83 | CES96 = 92 |
| CES22 = 78 | CES47 = 91 | CES72 = 94 | CES97 = 96 |
| CES23 = 91 | CES48 = 91 | CES73 = 83 | CES98 = 95 |
| CES24 = 90 | CES49 = 96 | CES74 = 90 | CES99 = 92 |
| CES25 = 71 | CES50 = 98 | CES75 = 85 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)