

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: METALUX

Report Number: P1433968

Luminaire Tested: EHBR1-60-UNV-TASM-L940-UPL36

Issue Date: 3/20/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1433968  
REPORT IS A COMBINATION OF REPORTS P1431905 AND P1431635  
Test Lab: INNOVATION CENTER  
Issue Date: 3/20/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: METALUX  
Catalog Number: EHBR1-60-UNV-TASM-L940-UPL36  
Description: Elevate Round Highbay at, 60000 lumens, 4000K 90CRI LEDs with TASM lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 58764.6 lumens  
Efficiency: N/A  
Efficacy: 163.8 lumens/watt  
Spacing Criteria (0/90/45): 0.99 / 0.84 / 0.9  
Luminous Opening: Vertical Cylinder (Dia: 1.71' x H: 0.1')  
CIE Type: Direct  
  
Input Watts (W): 358.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1433968  
CATALOG NUMBER: EHBR1-60-UNV-TASM-L940-UPL36

### Luminous Intensity Polar Plot



— 0°-180°    - - 45°-225°    - - - 90°-270°    - · - 135°-315°



TEST NUMBER: P1433968

CATALOG NUMBER: EHBR1-60-UNV-TASM-L940-UPL36

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	118	118	118	118	114	114	114	114	108	108	108	102	102	102	97	97	97	97	97	97	94
1	110	107	104	101	107	104	101	99	99	97	95	94	93	91	90	89	87	87	87	87	85
2	103	97	93	88	101	95	91	87	91	87	84	87	84	81	83	81	79	79	79	79	77
3	97	89	83	78	94	87	82	77	84	79	75	80	77	73	77	74	72	72	72	72	70
4	91	82	76	71	89	81	74	70	78	72	68	75	70	67	72	68	65	65	65	65	64
5	86	76	69	64	84	75	68	64	72	67	62	70	65	61	67	63	60	60	60	60	58
6	81	70	64	59	79	69	63	58	67	62	57	65	60	56	63	59	56	56	56	56	54
7	76	66	59	54	74	65	58	54	63	57	53	61	56	52	59	55	52	52	52	52	50
8	72	61	55	50	70	61	54	50	59	53	49	57	52	49	56	51	48	48	48	48	46
9	68	58	51	47	67	57	51	46	55	50	46	54	49	45	53	48	45	45	45	45	43
10	65	54	48	43	64	53	47	43	52	47	43	51	46	42	50	45	42	42	42	42	41

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	232397	232397	232397	232397
5°	230982	246415	230982	218995
10°	228142	252741	228142	207261
15°	221406	234875	221406	191453
20°	207071	188338	207071	170531
25°	183274	130491	183274	142912
30°	148811	84894	148811	106927
35°	106733	54979	106733	71184
40°	69006	37895	69006	44892
45°	43784	29354	43784	31986
50°	32515	24943	32515	26643
55°	26547	22722	26547	23518
60°	22987	21644	22987	21775
65°	20955	20874	20955	20785
70°	19861	20453	19861	20188
75°	18574	19786	18574	19193
80°	16315	18680	16315	17463
85°	10559	13337	10559	12715

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 22.5°  
 Vertical Angle: 45°  
 Luminance: 61558 cd/sqm



TEST NUMBER: P1433968  
 CATALOG NUMBER: EHBR1-60-UNV-TASM-L940-UPL36

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	4705.5	8.0
10°-20°	12801.5	21.8
20°-30°	15013.6	25.5
30°-40°	10441.0	17.8
40°-50°	5188.7	8.8
50°-60°	3103.4	5.3
60°-70°	2184.3	3.7
70°-80°	1407.0	2.4
80°-90°	453.0	0.8
90°-100°	92.9	0.2
100°-110°	601.1	1.0
110°-120°	1109.4	1.9
120°-130°	660.2	1.1
130°-140°	400.4	0.7
140°-150°	278.1	0.5
150°-160°	182.7	0.3
160°-170°	106.1	0.2
170°-180°	35.6	0.1
0°-30°	32520.6	55.3
0°-40°	42961.6	73.1
0°-60°	51253.7	87.2
0°-90°	55298.0	94.1
90°-120°	1803.4	3.1
90°-150°	3142.2	5.3
90°-180°	3467.0	5.9
0°-180°	58764.6	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	49487	49487	49487	49487	49487	
5°	49318	52614	49318	46759	49318	4680
15°	46450	49276	46450	40166	46450	12981
25°	36600	26059	36600	28539	36600	16570
35°	19589	10091	19589	13065	19589	12229
45°	7084	4749	7084	5175	7084	5797
55°	3588	3071	3588	3178	3588	3281
65°	2187	2179	2187	2170	2187	2197
75°	1308	1394	1308	1352	1308	1373
85°	363	458	363	437	363	403
90°	26	32	26	26	26	29
95°	50	49	50	43	50	52
105°	276	144	276	210	276	372
115°	1180	1011	1180	958	1180	1076
125°	756	794	756	693	756	697
135°	480	555	480	507	480	381
145°	436	456	436	424	436	273
155°	390	407	390	380	390	182
165°	372	385	372	365	372	106
175°	374	383	374	367	374	35
180°	374	374	374	374	374	



TEST NUMBER: P1433968  
 CATALOG NUMBER: EHBR1-60-UNV-TASM-L940-UPL36

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
0°	49487.2	49487.2	49487.2	49487.2	49487.2	49487.2	49487.2	49487.2	49487.2	49487.2	49487.2
2.5°	49458.4	50097.8	50615.6	50957.0	51125.9	50957.0	50615.6	50097.8	49458.4	48822.7	48385.7
5°	49318.3	50598.8	51683.6	52393.5	52613.5	52393.5	51683.6	50598.8	49318.3	48108.2	47305.5
7.5°	48983.2	50978.4	52590.3	53418.9	53621.3	53418.9	52590.3	50978.4	48983.2	47270.2	46256.0
10°	48472.0	51217.8	53080.3	53674.1	53698.2	53674.1	53080.3	51217.8	48472.0	46164.2	44968.0
12.5°	47656.3	51132.5	52916.0	52721.1	52278.5	52721.1	52916.0	51132.5	47656.3	44813.0	43304.1
15°	46449.9	50626.7	51875.7	50289.9	49275.6	50289.9	51875.7	50626.7	46449.9	42988.7	41238.6
17.5°	44749.9	49680.2	49704.3	46566.8	44653.4	46566.8	49704.3	49680.2	44749.9	40757.8	38830.4
20°	42559.0	48162.0	46714.4	40975.9	38708.9	40975.9	46714.4	48162.0	42559.0	38120.6	36229.4
22.5°	39812.2	46115.0	42550.7	35351.6	32258.6	35351.6	42550.7	46115.0	39812.2	35053.6	33085.5
25°	36599.6	43606.7	38071.4	29223.3	26059.0	29223.3	38071.4	43606.7	36599.6	31399.4	29619.5
27.5°	32821.0	40427.5	33301.7	23880.1	20960.7	23880.1	33301.7	40427.5	32821.0	27626.3	25808.5
30°	28623.8	36351.9	28338.1	19017.6	16329.3	19017.6	28338.1	36351.9	28623.8	23387.4	21759.7
32.5°	23924.7	32357.0	23571.1	15238.0	12960.8	15238.0	23571.1	32357.0	23924.7	19342.4	17641.5
35°	19589.3	27359.0	19272.8	11973.4	10090.7	11973.4	19272.8	27359.0	19589.3	15523.8	13853.5
37.5°	15373.5	22636.7	15363.3	9641.5	8184.6	9641.5	15363.3	22636.7	15373.5	12069.0	10713.3
40°	11960.5	17699.9	12037.5	7696.5	6568.1	7696.5	12037.5	17699.9	11960.5	9183.0	8315.4
42.5°	9062.5	13534.3	9461.5	6316.7	5578.9	6316.7	9461.5	13534.3	9062.5	7235.3	6585.7
45°	7084.0	9959.8	7388.4	5329.3	4749.3	5329.3	7388.4	9959.8	7084.0	5826.7	5390.5
47.5°	5769.1	7697.4	5988.2	4571.1	4164.6	4571.1	5988.2	7697.4	5769.1	4928.4	4601.8
50°	4845.8	5906.4	4972.0	3990.2	3717.4	3990.2	4972.0	5906.4	4845.8	4220.4	4002.3
52.5°	4162.8	4817.1	4234.2	3555.9	3372.2	3555.9	4234.2	4817.1	4162.8	3692.4	3556.8
55°	3587.5	4049.6	3682.1	3197.8	3070.6	3197.8	3682.1	4049.6	3587.5	3285.9	3185.7
57.5°	3150.5	3435.4	3197.8	2892.5	2808.0	2892.5	3197.8	3435.4	3150.5	2924.0	2870.2
60°	2763.4	2975.0	2822.0	2626.1	2602.0	2626.1	2822.0	2975.0	2763.4	2630.8	2595.5
62.5°	2465.6	2599.2	2495.3	2386.7	2365.4	2386.7	2495.3	2599.2	2465.6	2363.5	2370.0
65°	2187.2	2311.5	2229.9	2171.4	2178.8	2171.4	2229.9	2311.5	2187.2	2139.9	2150.1
67.5°	1971.9	2036.9	2001.6	1968.2	1976.6	1968.2	2001.6	2036.9	1971.9	1925.5	1941.3
70°	1742.7	1812.3	1776.1	1780.7	1794.6	1780.7	1776.1	1812.3	1742.7	1728.8	1740.9
72.5°	1523.7	1577.6	1565.4	1576.6	1591.4	1576.6	1565.4	1577.6	1523.7	1521.8	1522.8
75°	1308.4	1349.2	1354.8	1370.6	1393.8	1370.6	1354.8	1349.2	1308.4	1294.5	1311.2
77.5°	1073.6	1120.0	1137.6	1159.1	1193.3	1159.1	1137.6	1120.0	1073.6	1082.9	1091.2
80°	858.3	879.7	918.7	934.4	982.7	934.4	918.7	879.7	858.3	842.6	854.7
82.5°	628.2	647.7	681.1	710.8	738.7	710.8	681.1	647.7	628.2	620.8	621.7
85°	362.9	392.5	414.8	450.1	458.4	450.1	414.8	392.5	362.9	371.2	362.9
87.5°	127.2	136.4	155.9	169.8	170.8	169.8	155.9	136.4	127.2	129.9	117.9
90°	25.7	43.8	75.2	43.7	32.2	43.7	75.2	43.8	25.7	44.7	69.5
92.5°	33.4	59.1	105.7	57.0	41.7	57.0	105.7	59.1	33.4	58.1	111.4
95°	49.5	72.4	134.3	62.8	49.4	62.8	134.3	72.4	49.5	77.1	155.3
97.5°	76.2	89.5	151.4	66.6	58.9	66.6	151.4	89.5	76.2	94.3	178.1
100°	101.0	101.0	275.3	76.1	66.5	76.1	275.3	101.0	101.0	116.2	277.3
102.5°	152.4	197.1	636.4	149.4	79.8	149.4	636.4	197.1	152.4	217.2	587.9
105°	276.2	448.7	1118.5	380.0	143.7	380.0	1118.5	448.7	276.2	453.5	1047.1
107.5°	522.1	835.5	1440.5	745.9	328.5	745.9	1440.5	835.5	522.1	802.2	1381.5
110°	834.6	1167.1	1572.1	1020.3	660.1	1020.3	1572.1	1167.1	834.6	1101.4	1448.2



TEST NUMBER: P1433968  
 CATALOG NUMBER: EHBR1-60-UNV-TASM-L940-UPL36

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
112.5°	1086.1	1300.5	1535.8	1130.8	911.6	1130.8	1535.8	1300.5	1086.1	1215.7	1387.2
115°	1180.5	1281.5	1371.9	1127.0	1010.7	1127.0	1371.9	1281.5	1180.5	1187.1	1238.6
117.5°	1140.4	1172.8	1185.1	1058.4	1016.4	1058.4	1185.1	1172.8	1140.4	1068.0	1051.8
120°	1029.9	1016.6	999.4	957.5	959.3	957.5	999.4	1016.6	1029.9	932.8	878.4
122.5°	891.8	863.2	845.0	855.4	881.2	855.4	845.0	863.2	891.8	794.5	753.6
125°	756.4	727.9	737.3	767.8	794.4	767.8	737.3	727.9	756.4	675.4	665.0
127.5°	643.0	629.7	659.2	693.4	716.2	693.4	659.2	629.7	643.0	591.6	602.1
130°	562.1	564.9	604.0	633.4	647.7	633.4	604.0	564.9	562.1	537.3	563.0
132.5°	511.5	525.8	563.0	588.6	597.2	588.6	563.0	525.8	511.5	504.8	536.3
135°	480.1	501.0	535.3	551.4	555.3	551.4	535.3	501.0	480.1	482.9	511.5
137.5°	461.9	482.9	508.6	521.9	519.0	521.9	508.6	482.9	461.9	468.5	490.5
140°	451.4	472.4	483.8	499.1	497.1	499.1	483.8	472.4	451.4	455.2	472.3
142.5°	440.9	460.0	465.7	477.1	474.2	477.1	465.7	460.0	440.9	444.8	456.1
145°	436.1	450.5	445.7	460.0	456.0	460.0	445.7	450.5	436.1	437.1	443.7
147.5°	426.6	437.1	431.4	443.7	439.8	443.7	431.4	437.1	426.6	426.6	429.3
150°	416.0	423.6	415.1	429.3	429.3	429.3	415.1	423.6	416.0	414.1	416.9
152.5°	401.7	409.3	401.7	417.8	416.9	417.8	401.7	409.3	401.7	399.8	402.7
155°	390.2	394.0	390.2	406.4	407.3	406.4	390.2	394.0	390.2	389.2	391.1
157.5°	382.5	385.4	383.5	397.7	398.7	397.7	383.5	385.4	382.5	382.5	383.5
160°	376.8	380.6	379.6	391.9	392.9	391.9	379.6	380.6	376.8	377.7	378.6
162.5°	374.8	374.8	374.8	387.1	389.0	387.1	374.8	374.8	374.8	374.8	376.7
165°	371.9	373.8	371.8	381.3	385.0	381.3	371.8	373.8	371.9	372.8	372.8
167.5°	371.8	370.0	371.8	380.3	384.1	380.3	371.8	370.0	371.8	372.8	372.8
170°	368.9	369.9	369.9	378.3	382.1	378.3	369.9	369.9	368.9	370.9	371.8
172.5°	371.7	371.7	370.7	377.2	382.9	377.2	370.7	371.7	371.7	372.8	374.6
175°	373.6	372.7	372.5	377.2	382.9	377.2	372.5	372.7	373.6	372.7	372.7
177.5°	371.7	373.6	375.4	380.0	387.7	380.0	375.4	373.6	371.7	372.7	372.7
180°	373.6	373.6	373.6	373.6	373.6	373.6	373.6	373.6	373.6	373.6	373.6



TEST NUMBER: P1433968

CATALOG NUMBER: EHBR1-60-UNV-TASM-L940-UPL36

**CANDELA DISTRIBUTION (continued):**

	247.5°	270°	292.5°	315°	337.5°	360°
0°	49487.2	49487.2	49487.2	49487.2	49487.2	49487.2
2.5°	48049.7	48018.2	48049.7	48385.7	48822.7	49458.4
5°	46933.4	46758.9	46933.4	47305.5	48108.2	49318.3
7.5°	45633.3	45532.1	45633.3	46256.0	47270.2	48983.2
10°	44264.6	44035.4	44264.6	44968.0	46164.2	48472.0
12.5°	42577.5	42274.1	42577.5	43304.1	44813.0	47656.3
15°	40432.1	40165.8	40432.1	41238.6	42988.7	46449.9
17.5°	38129.8	37888.6	38129.8	38830.4	40757.8	44749.9
20°	35238.3	35049.0	35238.3	36229.4	38120.6	42559.0
22.5°	32204.9	32027.6	32204.9	33085.5	35053.6	39812.2
25°	28635.9	28539.4	28635.9	29619.5	31399.4	36599.6
27.5°	24779.3	24615.0	24779.3	25808.5	27626.3	32821.0
30°	20839.2	20567.3	20839.2	21759.7	23387.4	28623.8
32.5°	16985.4	16789.6	16985.4	17641.5	19342.4	23924.7
35°	13260.6	13064.8	13260.6	13853.5	15523.8	19589.3
37.5°	10332.8	9986.7	10332.8	10713.3	12069.0	15373.5
40°	7836.6	7780.9	7836.6	8315.4	9183.0	11960.5
42.5°	6379.7	6228.4	6379.7	6585.7	7235.3	9062.5
45°	5234.6	5175.2	5234.6	5390.5	5826.7	7084.0
47.5°	4501.5	4527.5	4501.5	4601.8	4928.4	5769.1
50°	3954.9	3970.8	3954.9	4002.3	4220.4	4845.8
52.5°	3552.3	3538.3	3552.3	3556.8	3692.4	4162.8
55°	3195.9	3178.2	3195.9	3185.7	3285.9	3587.5
57.5°	2884.1	2897.0	2884.1	2870.2	2924.0	3150.5
60°	2605.7	2617.7	2605.7	2595.5	2630.8	2763.4
62.5°	2370.9	2378.4	2370.9	2370.0	2363.5	2465.6
65°	2161.2	2169.5	2161.2	2150.1	2139.9	2187.2
67.5°	1960.7	1960.7	1960.7	1941.3	1925.5	1971.9
70°	1772.4	1771.4	1772.4	1740.9	1728.8	1742.7
72.5°	1546.0	1568.2	1546.0	1522.8	1521.8	1523.7
75°	1326.0	1352.0	1326.0	1311.2	1294.5	1308.4
77.5°	1103.3	1143.2	1103.3	1091.2	1082.9	1073.6
80°	875.1	918.7	875.1	854.7	842.6	858.3
82.5°	646.7	679.3	646.7	621.7	620.8	628.2
85°	385.1	437.0	385.1	362.9	371.2	362.9
87.5°	123.4	157.7	123.4	117.9	129.9	127.2
90°	41.0	25.7	41.0	69.5	44.7	25.7
92.5°	62.0	37.2	62.0	111.4	58.1	33.4
95°	71.5	42.9	71.5	155.3	77.1	49.5
97.5°	79.1	55.2	79.1	178.1	94.3	76.2
100°	92.4	72.4	92.4	277.3	116.2	101.0
102.5°	195.3	122.0	195.3	587.9	217.2	152.4
105°	410.7	209.5	410.7	1047.1	453.5	276.2
107.5°	734.6	362.0	734.6	1381.5	802.2	522.1
110°	974.7	674.5	974.7	1448.2	1101.4	834.6



TEST NUMBER: P1433968

CATALOG NUMBER: EHBR1-60-UNV-TASM-L940-UPL36

**CANDELA DISTRIBUTION (continued):**

	247.5°	270°	292.5°	315°	337.5°	360°
112.5°	1047.1	910.9	1047.1	1387.2	1215.7	1086.1
115°	1007.1	958.5	1007.1	1238.6	1187.1	1180.5
117.5°	919.4	926.1	919.4	1051.8	1068.0	1140.4
120°	818.5	857.5	818.5	878.4	932.8	1029.9
122.5°	726.0	771.7	726.0	753.6	794.5	891.8
125°	645.9	692.6	645.9	665.0	675.4	756.4
127.5°	590.7	622.2	590.7	602.1	591.6	643.0
130°	547.8	574.5	547.8	563.0	537.3	562.1
132.5°	518.3	535.4	518.3	536.3	504.8	511.5
135°	492.5	506.8	492.5	511.5	482.9	480.1
137.5°	470.6	483.0	470.6	490.5	468.5	461.9
140°	451.5	462.0	451.5	472.3	455.2	451.4
142.5°	431.4	439.1	431.4	456.1	444.8	440.9
145°	418.0	423.8	418.0	443.7	437.1	436.1
147.5°	406.5	410.3	406.5	429.3	426.6	426.6
150°	395.0	398.8	395.0	416.9	414.1	416.0
152.5°	382.6	387.4	382.6	402.7	399.8	401.7
155°	374.9	379.6	374.9	391.1	389.2	390.2
157.5°	371.1	374.8	371.1	383.5	382.5	382.5
160°	368.2	371.0	368.2	378.6	377.7	376.8
162.5°	364.3	367.2	364.3	376.7	374.8	374.8
165°	364.3	365.2	364.3	372.8	372.8	371.9
167.5°	363.2	365.2	363.2	372.8	372.8	371.8
170°	364.2	365.1	364.2	371.8	370.9	368.9
172.5°	366.0	367.0	366.0	374.6	372.8	371.7
175°	366.0	367.0	366.0	372.7	372.7	373.6
177.5°	368.8	369.8	368.8	372.7	372.7	371.7
180°	373.6	373.6	373.6	373.6	373.6	373.6



TEST NUMBER: P1433968  
 CATALOG NUMBER: EHBR1-60-UNV-TASM-L940-UPL36

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	19.63	20.75	20.10	21.18	21.65	18.95	20.07	19.42	20.50	20.97
	3H	21.18	22.17	21.66	22.63	23.14	20.80	21.79	21.28	22.24	22.76
	4H	21.81	22.74	22.32	23.21	23.74	21.58	22.51	22.09	22.98	23.51
	6H	22.30	23.15	22.82	23.64	24.17	22.22	23.07	22.74	23.56	24.10
	8H	22.45	23.25	22.98	23.76	24.31	22.44	23.25	22.98	23.76	24.30
	12H	22.52	23.29	23.06	23.79	24.36	22.57	23.34	23.11	23.84	24.41
4H	2H	20.05	20.97	20.55	21.44	21.97	19.52	20.45	20.03	20.92	21.45
	3H	21.84	22.61	22.36	23.13	23.67	21.58	22.35	22.10	22.87	23.41
	4H	22.62	23.31	23.16	23.84	24.42	22.49	23.18	23.03	23.71	24.29
	6H	23.23	23.83	23.80	24.38	24.99	23.26	23.85	23.83	24.41	25.01
	8H	23.43	23.98	24.00	24.54	25.15	23.53	24.09	24.10	24.64	25.25
	12H	23.54	24.02	24.12	24.61	25.22	23.70	24.19	24.29	24.78	25.39
8H	4H	22.87	23.42	23.44	23.98	24.58	22.77	23.32	23.34	23.88	24.49
	6H	23.61	24.06	24.21	24.66	25.28	23.67	24.12	24.27	24.73	25.34
	8H	23.88	24.28	24.50	24.90	25.52	24.03	24.43	24.65	25.04	25.67
	12H	24.05	24.40	24.67	25.00	25.70	24.28	24.63	24.89	25.22	25.93
12H	4H	22.88	23.37	23.46	23.95	24.56	22.78	23.27	23.37	23.86	24.47
	6H	23.65	24.05	24.27	24.67	25.30	23.72	24.12	24.34	24.74	25.36
	8H	23.97	24.32	24.58	24.92	25.62	24.12	24.47	24.74	25.07	25.77

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2506-472-6

Test Date: 08/01/2025

Luminaire Tested: EHBR-60-L935-N

Data in this report applies to families of products including EHBR-60-L935-N

**Test Information**

Test Method: LM-79-2019  
 Report Number: SP1-2506-472-6  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry: 4π  
 Issue Date: 08/05/2025  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: Metalux  
 Catalog Number: **EHBR-60-L935-N**  
 Description: Elevate Round Highbay at, 60000 lumens, 3500K 90CRI LEDs with N lens

**Spectral Parameters**

CCT (K): 3406  
 CIE u': 0.2394  
 CIE v': 0.5094  
 Duv: -0.0028  
 CIE x: 0.4076  
 CIE y: 0.3856  
 CIE z: 0.2068  
 Peak Wavelength (nm): 630  
 Dominant Wavelength (nm): 582  
 Purity: 38.0517  
 Rf: 91.3  
 Rg: 100

CRI (Ra):	94.6		
R1:	96.6	R9:	63.8
R2:	98.4	R10:	94.7
R3:	98.1	R11:	96.6
R4:	95.8	R12:	80.9
R5:	96.2	R13:	97.4
R6:	95.4	R14:	98.3
R7:	91.8	R15:	93.1
R8:	84.4		



**Test Conditions**


Stabilization Time: 35M  
 Operation Time: 1H 35M  
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP1-2506-472-6

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2506-472-6

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2506-472-6

**Photopic Flux vs. Wavelength**



**Photopic Lumens: NR**

λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)
360	0	NR	490	140	NR	620	338	NR	750	8	NR	880	0	NR
365	0	NR	495	159	NR	625	339	NR	755	7	NR	885	0	NR
370	0	NR	500	182	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	202	NR	635	653	NR	765	5	NR	895	0	NR
380	0	NR	510	216	NR	640	222	NR	770	4	NR	900	0	NR
385	0	NR	515	228	NR	645	214	NR	775	3	NR	905	0	NR
390	0	NR	520	236	NR	650	185	NR	780	3	NR	910	0	NR
395	1	NR	525	242	NR	655	157	NR	785	3	NR	915	0	NR
400	2	NR	530	248	NR	660	133	NR	790	2	NR	920	0	NR
405	3	NR	535	253	NR	665	113	NR	795	2	NR	925	0	NR
410	4	NR	540	258	NR	670	103	NR	800	2	NR	930	0	NR
415	7	NR	545	264	NR	675	85	NR	805	1	NR	935	0	NR
420	13	NR	550	270	NR	680	72	NR	810	1	NR	940	0	NR
425	22	NR	555	278	NR	685	62	NR	815	1	NR	945	0	NR
430	38	NR	560	286	NR	690	53	NR	820	1	NR	950	0	NR
435	65	NR	565	295	NR	695	45	NR	825	1	NR	955	0	NR
440	108	NR	570	303	NR	700	39	NR	830	1	NR	960	0	NR
445	193	NR	575	311	NR	705	33	NR	835	1	NR	965	0	NR
450	312	NR	580	319	NR	710	28	NR	840	1	NR	970	0	NR
455	300	NR	585	326	NR	715	24	NR	845	0	NR	975	0	NR
460	214	NR	590	332	NR	720	20	NR	850	0	NR	980	0	NR
465	184	NR	595	333	NR	725	17	NR	855	0	NR	985	0	NR
470	153	NR	600	336	NR	730	15	NR	860	0	NR	990	0	NR
475	122	NR	605	337	NR	735	12	NR	865	0	NR	995	0	NR
480	115	NR	610	367	NR	740	10	NR	870	0	NR	1000	0	NR
485	125	NR	615	390	NR	745	9	NR	875	0	NR			

REPORT NUMBER: SP1-2506-472-6

**Scotopic Flux vs. Wavelength**



**Scotopic Lumens: NR**

**S/P: 1.62**

λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)
360	0	NR	490	140	NR	620	338	NR	750	8	NR	880	0	NR
365	0	NR	495	159	NR	625	339	NR	755	7	NR	885	0	NR
370	0	NR	500	182	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	202	NR	635	653	NR	765	5	NR	895	0	NR
380	0	NR	510	216	NR	640	222	NR	770	4	NR	900	0	NR
385	0	NR	515	228	NR	645	214	NR	775	3	NR	905	0	NR
390	0	NR	520	236	NR	650	185	NR	780	3	NR	910	0	NR
395	1	NR	525	242	NR	655	157	NR	785	3	NR	915	0	NR
400	2	NR	530	248	NR	660	133	NR	790	2	NR	920	0	NR
405	3	NR	535	253	NR	665	113	NR	795	2	NR	925	0	NR
410	4	NR	540	258	NR	670	103	NR	800	2	NR	930	0	NR
415	7	NR	545	264	NR	675	85	NR	805	1	NR	935	0	NR
420	13	NR	550	270	NR	680	72	NR	810	1	NR	940	0	NR
425	22	NR	555	278	NR	685	62	NR	815	1	NR	945	0	NR
430	38	NR	560	286	NR	690	53	NR	820	1	NR	950	0	NR
435	65	NR	565	295	NR	695	45	NR	825	1	NR	955	0	NR
440	108	NR	570	303	NR	700	39	NR	830	1	NR	960	0	NR
445	193	NR	575	311	NR	705	33	NR	835	1	NR	965	0	NR
450	312	NR	580	319	NR	710	28	NR	840	1	NR	970	0	NR
455	300	NR	585	326	NR	715	24	NR	845	0	NR	975	0	NR
460	214	NR	590	332	NR	720	20	NR	850	0	NR	980	0	NR
465	184	NR	595	333	NR	725	17	NR	855	0	NR	985	0	NR
470	153	NR	600	336	NR	730	15	NR	860	0	NR	990	0	NR
475	122	NR	605	337	NR	735	12	NR	865	0	NR	995	0	NR
480	115	NR	610	367	NR	740	10	NR	870	0	NR	1000	0	NR
485	125	NR	615	390	NR	745	9	NR	875	0	NR			

REPORT NUMBER: SP1-2506-472-6

Melanopic Flux vs. Wavelength




Melanopic Lumens: NR

M/P: 3.3

λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)
360	0	NR	490	140	NR	620	338	NR	750	8	NR	880	0	NR
365	0	NR	495	159	NR	625	339	NR	755	7	NR	885	0	NR
370	0	NR	500	182	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	202	NR	635	653	NR	765	5	NR	895	0	NR
380	0	NR	510	216	NR	640	222	NR	770	4	NR	900	0	NR
385	0	NR	515	228	NR	645	214	NR	775	3	NR	905	0	NR
390	0	NR	520	236	NR	650	185	NR	780	3	NR	910	0	NR
395	1	NR	525	242	NR	655	157	NR	785	3	NR	915	0	NR
400	2	NR	530	248	NR	660	133	NR	790	2	NR	920	0	NR
405	3	NR	535	253	NR	665	113	NR	795	2	NR	925	0	NR
410	4	NR	540	258	NR	670	103	NR	800	2	NR	930	0	NR
415	7	NR	545	264	NR	675	85	NR	805	1	NR	935	0	NR
420	13	NR	550	270	NR	680	72	NR	810	1	NR	940	0	NR
425	22	NR	555	278	NR	685	62	NR	815	1	NR	945	0	NR
430	38	NR	560	286	NR	690	53	NR	820	1	NR	950	0	NR
435	65	NR	565	295	NR	695	45	NR	825	1	NR	955	0	NR
440	108	NR	570	303	NR	700	39	NR	830	1	NR	960	0	NR
445	193	NR	575	311	NR	705	33	NR	835	1	NR	965	0	NR
450	312	NR	580	319	NR	710	28	NR	840	1	NR	970	0	NR
455	300	NR	585	326	NR	715	24	NR	845	0	NR	975	0	NR
460	214	NR	590	332	NR	720	20	NR	850	0	NR	980	0	NR
465	184	NR	595	333	NR	725	17	NR	855	0	NR	985	0	NR
470	153	NR	600	336	NR	730	15	NR	860	0	NR	990	0	NR
475	122	NR	605	337	NR	735	12	NR	865	0	NR	995	0	NR
480	115	NR	610	367	NR	740	10	NR	870	0	NR	1000	0	NR
485	125	NR	615	390	NR	745	9	NR	875	0	NR			

**Summary**

$R_f = 91.3$   
 $R_g = 100$   
 $CIE R_a = 94.6$   
 $R_9 = 63.8$



**Color Vector Graphics**



**Individual Sample Fidelity Index ( $R_{f,i}$ )**


CES01 = 86	CES26 = 94	CES51 = 97	CES76 = 90
CES02 = 63	CES27 = 92	CES52 = 98	CES77 = 86
CES03 = 31	CES28 = 97	CES53 = 98	CES78 = 86
CES04 = 70	CES29 = 97	CES54 = 93	CES79 = 90
CES05 = 50	CES30 = 92	CES55 = 92	CES80 = 91
CES06 = 51	CES31 = 97	CES56 = 96	CES81 = 74
CES07 = 43	CES32 = 89	CES57 = 94	CES82 = 96
CES08 = 41	CES33 = 99	CES58 = 95	CES83 = 94
CES09 = 29	CES34 = 94	CES59 = 98	CES84 = 95
CES10 = 75	CES35 = 97	CES60 = 92	CES85 = 79
CES11 = 58	CES36 = 81	CES61 = 93	CES86 = 79
CES12 = 64	CES37 = 96	CES62 = 86	CES87 = 92
CES13 = 44	CES38 = 87	CES63 = 94	CES88 = 98
CES14 = 74	CES39 = 99	CES64 = 91	CES89 = 84
CES15 = 72	CES40 = 97	CES65 = 90	CES90 = 96
CES16 = 48	CES41 = 96	CES66 = 89	CES91 = 75
CES17 = 49	CES42 = 94	CES67 = 88	CES92 = 76
CES18 = 56	CES43 = 93	CES68 = 89	CES93 = 86
CES19 = 71	CES44 = 99	CES69 = 90	CES94 = 74
CES20 = 67	CES45 = 97	CES70 = 88	CES95 = 83
CES21 = 86	CES46 = 97	CES71 = 83	CES96 = 92
CES22 = 78	CES47 = 91	CES72 = 94	CES97 = 96
CES23 = 91	CES48 = 91	CES73 = 83	CES98 = 95
CES24 = 90	CES49 = 96	CES74 = 90	CES99 = 92
CES25 = 71	CES50 = 98	CES75 = 85	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)