

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: METALUX

Report Number: P1444808

Luminaire Tested: EHBR1-24-UNV-TA-L940-UPL40

Issue Date: 5/1/2026

Test Information

Test Method: LM-79-2019
Report Number: P1444808
REPORT IS A COMBINATION OF REPORTS P1444356 AND P1431635
Test Lab: INNOVATION CENTER
Issue Date: 5/1/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: METALUX
Catalog Number: EHBR1-24-UNV-TA-L940-UPL40
Description: Elevate Round Highbay at, 24000 lumens, 4000K 90CRI LEDs with TA lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 26651.6 lumens
Efficiency: N/A
Efficacy: 167.7 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 0.77 / 0.88
Luminous Opening: Vertical Cylinder (Dia: 1.71' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 158.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1444808
CATALOG NUMBER: EHBR1-24-UNV-TA-L940-UPL40

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - · - 90°-270° - · - 135°-315°



TEST NUMBER: P1444808
 CATALOG NUMBER: EHBR1-24-UNV-TA-L940-UPL40

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	116	116	116	116	111	111	111	111	103	103	103	96	96	96	89	89	89	89	89	89	86
1	108	105	102	99	104	101	99	96	95	93	91	89	87	85	83	82	80	80	80	80	78
2	102	96	91	86	98	93	88	84	87	83	80	82	79	77	77	75	73	73	73	73	70
3	95	87	81	77	92	85	80	75	80	76	72	76	72	69	72	69	67	67	67	67	64
4	89	80	74	69	86	78	72	68	74	69	65	71	66	63	67	64	61	61	61	61	59
5	84	74	68	63	81	72	66	62	69	64	60	66	61	58	63	59	56	56	56	56	54
6	79	69	62	57	77	67	61	56	64	59	55	61	57	53	59	55	52	52	52	52	50
7	75	64	57	53	72	63	56	52	60	55	51	58	53	49	55	51	48	48	48	48	46
8	71	60	53	49	68	59	52	48	56	51	47	54	49	46	52	48	45	45	45	45	43
9	67	56	50	45	65	55	49	45	53	48	44	51	46	43	49	45	42	42	42	42	40
10	63	53	46	42	62	52	46	42	50	45	41	48	43	40	47	42	39	39	39	39	38

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	93446	93446	93446	93446
5°	93898	96636	92584	97902
10°	94682	101461	92412	100790
15°	95147	91973	92250	88270
20°	94163	68517	91081	63394
25°	89129	43333	86184	39317
30°	77861	26040	74845	23798
35°	59922	16340	56475	14475
40°	37906	10250	34681	9632
45°	19538	7985	19214	7854
50°	11454	7102	11103	6992
55°	8775	6720	8451	6660
60°	7425	6865	7110	6775
65°	6975	7168	6706	6924
70°	6813	7507	6473	7224
75°	7285	7961	6892	7609
80°	7539	8814	6836	8046
85°	7099	8507	5738	7283

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 25°
 Vertical Angle: 45°
 Luminance: 29900 cd/sqm



TEST NUMBER: P1444808
 CATALOG NUMBER: EHBR1-24-UNV-TA-L940-UPL40

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1961.1	7.4
10°-20°	5516.6	20.7
20°-30°	6283.0	23.6
30°-40°	4516.0	16.9
40°-50°	2082.8	7.8
50°-60°	996.7	3.7
60°-70°	727.2	2.7
70°-80°	552.5	2.1
80°-90°	257.7	1.0
90°-100°	103.3	0.4
100°-110°	635.8	2.4
110°-120°	1175.5	4.4
120°-130°	708.1	2.7
130°-140°	440.9	1.7
140°-150°	315.6	1.2
150°-160°	212.5	0.8
160°-170°	124.5	0.5
170°-180°	41.9	0.2
0°-30°	13760.7	51.6
0°-40°	18276.7	68.6
0°-60°	21356.1	80.1
0°-90°	22893.6	85.9
90°-120°	1914.5	7.2
90°-150°	3379.1	12.7
90°-180°	3758.0	14.1
0°-180°	26651.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	19899	19899	19899	19899	19899	
5°	20049	20633	19768	20904	20049	1916
15°	19961	19296	19354	18519	19961	5624
25°	17799	8654	17211	7852	17799	8069
35°	10998	2999	10365	2657	10998	6750
45°	3161	1292	3109	1271	3161	2689
55°	1186	908	1142	900	1186	1095
65°	728	748	700	723	728	727
75°	513	561	486	536	513	534
85°	244	292	197	250	244	229
90°	81	99	34	39	81	48
95°	48	54	48	54	48	46
105°	225	294	149	294	225	300
115°	1021	1247	1070	1248	1021	942
125°	752	804	854	805	752	685
135°	570	520	616	522	570	446
145°	489	487	522	490	489	309
155°	444	452	475	454	444	207
165°	431	434	448	436	431	123
175°	435	440	443	441	435	42
180°	440	440	440	440	440	



TEST NUMBER: P1444808
 CATALOG NUMBER: EHBR1-24-UNV-TA-L940-UPL40

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6
2.5°	19974.7	19973.1	19972.7	19971.3	19970.9	19970.9	19970.3	19968.7	19967.7	19965.4	19962.7
5°	20048.7	20047.9	20048.5	20048.5	20047.1	20044.1	20039.2	20033.2	20025.7	20018.6	20012.3
7.5°	20106.1	20107.5	20109.3	20108.9	20104.5	20097.3	20087.3	20081.7	20085.0	20095.8	20120.6
10°	20116.6	20125.1	20128.4	20127.4	20118.7	20112.5	20114.9	20135.9	20178.0	20233.9	20310.4
12.5°	20075.8	20086.3	20085.9	20082.4	20074.0	20082.6	20113.1	20175.8	20265.8	20376.2	20505.7
15°	19961.3	19974.9	19970.9	19966.5	19960.9	19988.9	20049.9	20158.9	20297.9	20453.5	20612.9
17.5°	19738.9	19755.3	19747.3	19742.2	19737.5	19790.1	19894.9	20054.5	20229.6	20405.6	20556.7
20°	19353.2	19364.2	19345.2	19336.3	19343.9	19447.0	19601.4	19805.2	19989.7	20156.2	20259.4
22.5°	18723.7	18737.4	18701.8	18697.7	18741.6	18900.1	19095.4	19323.3	19496.5	19628.6	19668.3
25°	17799.0	17812.4	17770.1	17795.4	17870.2	18086.0	18318.6	18562.3	18710.2	18808.0	18781.0
27.5°	16550.8	16563.0	16522.8	16574.5	16692.7	16976.4	17250.1	17514.5	17646.3	17714.8	17627.9
30°	14976.5	15001.9	14954.5	15026.5	15207.0	15575.3	15888.8	16185.3	16316.7	16368.9	16233.8
32.5°	13106.7	13142.9	13090.6	13197.9	13449.6	13892.0	14248.2	14579.5	14724.8	14784.4	14631.8
35°	10997.9	11049.8	10989.8	11150.7	11461.3	11953.9	12348.4	12718.2	12890.3	12974.7	12820.9
37.5°	8763.6	8813.1	8780.7	8995.3	9336.3	9846.8	10249.6	10648.6	10843.0	10969.6	10848.4
40°	6570.1	6615.3	6639.9	6885.4	7206.2	7687.4	8074.2	8468.9	8686.4	8845.3	8770.5
42.5°	4637.2	4682.8	4766.3	5003.2	5270.7	5669.0	6000.4	6354.8	6562.5	6732.1	6703.2
45°	3161.1	3214.1	3318.7	3512.6	3706.1	3991.8	4235.2	4510.7	4680.5	4835.8	4837.7
47.5°	2215.2	2252.3	2345.8	2478.3	2604.3	2962.1	2976.8	3112.3	3226.4	3342.5	3357.5
50°	1707.1	1729.6	1779.2	1852.9	1924.4	2017.3	2102.3	2200.5	2270.7	2334.3	2349.5
52.5°	1403.2	1417.4	1442.7	1482.6	1524.1	1574.6	1620.0	1674.0	1712.2	1746.3	1753.4
55°	1185.9	1197.7	1235.3	1242.8	1290.2	1299.5	1319.6	1352.5	1374.6	1395.0	1400.2
57.5°	1022.0	1030.5	1038.5	1055.6	1070.2	1091.4	1108.5	1132.0	1146.0	1160.7	1162.0
60°	892.6	898.9	904.5	916.3	926.2	941.0	952.8	968.8	978.9	989.9	991.2
62.5°	796.4	800.8	804.6	812.4	819.5	830.8	840.2	853.6	862.9	871.5	873.4
65°	728.0	731.2	733.7	739.5	745.7	755.4	763.9	774.8	781.7	788.2	789.6
67.5°	667.3	670.4	672.9	678.3	682.6	689.8	695.5	703.7	708.9	714.1	714.2
70°	597.8	600.7	602.7	607.7	611.2	617.3	621.9	629.3	634.5	640.4	641.9
72.5°	549.8	551.4	554.0	558.6	563.5	570.1	576.2	583.9	590.3	596.3	598.9
75°	513.2	515.2	516.9	520.8	524.1	529.7	534.3	541.3	546.9	553.4	556.6
77.5°	460.4	462.7	464.1	468.1	470.9	476.4	479.7	485.9	490.6	496.5	499.4
80°	396.6	398.7	399.8	403.5	405.7	410.7	414.0	420.1	423.9	429.8	433.3
82.5°	325.9	327.9	328.5	332.0	333.2	337.3	339.8	345.9	350.7	358.3	363.6
85°	244.0	244.7	246.0	245.0	250.0	250.3	255.9	256.9	264.3	266.3	274.6
87.5°	149.2	151.4	152.5	155.9	157.4	160.8	161.8	165.5	167.4	171.5	173.5
90°	81.3	86.0	88.3	93.6	96.0	100.7	102.8	108.2	110.5	115.9	119.8
92.5°	41.5	44.3	47.1	50.3	53.2	56.6	59.6	62.8	65.8	69.0	74.8
95°	47.5	50.9	54.2	57.6	60.9	64.2	67.5	70.9	74.3	77.6	87.4
97.5°	60.0	62.9	65.8	68.7	71.6	74.5	77.4	80.3	83.2	86.0	97.6
100°	78.6	81.1	83.6	86.0	88.4	90.9	93.4	95.8	98.3	100.7	122.2
102.5°	131.6	140.3	149.1	157.7	166.4	175.1	183.8	192.5	201.2	209.9	255.6
105°	225.0	248.6	272.3	295.8	319.5	343.1	366.8	390.2	413.8	437.5	512.0
107.5°	386.7	430.4	474.1	517.9	561.6	605.2	648.9	692.6	736.2	779.8	855.4
110°	717.6	752.7	787.9	823.1	858.3	893.5	928.7	963.7	998.9	1034.0	1089.3



TEST NUMBER: P1444808
 CATALOG NUMBER: EHBR1-24-UNV-TA-L940-UPL40

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	968.4	984.4	1000.4	1016.3	1032.3	1048.2	1064.1	1080.1	1096.1	1111.8	1151.4
115°	1020.8	1026.5	1032.3	1037.8	1043.5	1049.1	1054.8	1060.3	1066.1	1071.5	1098.4
117.5°	989.4	988.5	987.7	986.8	985.9	985.0	984.1	983.1	982.1	981.2	996.3
120°	920.0	915.2	910.7	905.8	901.1	896.3	891.7	886.8	882.0	877.1	883.8
122.5°	832.9	827.2	821.8	815.9	810.3	804.5	798.9	792.8	787.2	781.4	784.2
125°	752.0	746.3	740.8	735.0	729.1	723.4	717.6	711.7	705.9	699.9	701.6
127.5°	681.3	677.5	673.6	669.5	665.6	661.4	657.4	653.2	649.2	644.9	645.5
130°	635.0	631.6	628.1	624.4	620.8	617.1	613.5	609.6	606.0	602.1	603.1
132.5°	596.6	594.3	592.0	589.4	586.9	584.1	581.6	578.7	576.2	573.5	574.6
135°	570.4	568.1	566.1	563.7	561.4	558.9	556.5	553.9	551.4	548.8	550.3
137.5°	547.9	545.9	544.0	541.9	539.8	537.4	535.2	532.9	530.7	528.2	529.6
140°	527.2	525.5	523.7	521.8	520.0	517.9	515.9	513.8	511.8	509.6	511.2
142.5°	504.4	503.0	501.8	500.3	498.9	497.2	495.7	494.0	492.5	490.8	492.8
145°	489.1	488.1	487.1	485.8	484.5	483.2	481.9	480.4	479.1	477.7	480.0
147.5°	475.7	474.9	474.0	473.2	472.3	471.0	470.0	468.9	467.9	466.8	468.9
150°	463.9	463.1	462.4	461.5	460.6	459.5	458.5	457.5	456.4	455.3	457.5
152.5°	451.8	450.9	450.2	449.4	448.5	447.4	446.5	445.5	444.5	443.5	445.3
155°	443.9	443.1	442.3	441.5	440.7	439.6	438.7	437.8	436.8	435.8	437.4
157.5°	438.4	437.8	437.2	436.6	436.0	435.3	434.5	433.9	433.1	432.5	433.6
160°	435.1	434.5	434.0	433.3	432.7	431.9	431.4	430.6	430.0	429.3	430.2
162.5°	432.0	431.4	430.8	430.1	429.5	428.7	428.1	427.5	426.9	426.2	427.4
165°	430.8	430.4	430.0	429.8	429.4	429.0	428.7	428.2	427.8	427.3	428.2
167.5°	433.5	432.9	432.5	431.9	431.3	430.7	430.1	429.6	429.0	428.4	429.2
170°	433.7	433.3	433.0	432.8	432.6	432.3	432.0	431.7	431.4	431.2	431.8
172.5°	435.3	435.0	434.8	434.7	434.4	434.2	434.1	433.8	433.7	433.3	434.2
175°	434.6	434.3	434.2	434.1	434.0	433.9	433.8	433.6	433.6	433.4	433.9
177.5°	437.3	437.2	437.2	437.2	437.2	437.1	437.0	436.8	436.8	436.8	437.2
180°	439.9	439.9	439.9	439.9	439.9	439.9	439.9	439.9	439.9	439.9	439.9



TEST NUMBER: P1444808
 CATALOG NUMBER: EHBR1-24-UNV-TA-L940-UPL40

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6
2.5°	19960.9	19958.5	19955.1	19950.9	19947.3	19943.1	19933.1	19930.2	19933.5	19935.7	19940.3
5°	20008.3	20009.7	20010.2	20019.3	20027.1	20046.7	20199.8	20260.6	20307.6	20337.5	20382.8
7.5°	20151.3	20197.3	20242.8	20304.0	20356.8	20428.1	20695.9	20810.0	20891.0	20949.3	21021.0
10°	20393.6	20494.1	20588.2	20698.6	20793.4	20902.0	21151.3	21262.4	21332.5	21383.6	21431.2
12.5°	20637.7	20777.0	20902.9	21025.7	21128.3	21222.5	21310.2	21349.1	21352.4	21354.1	21328.7
15°	20764.9	20898.0	21009.0	21090.1	21150.5	21177.1	21026.2	20947.0	20847.0	20764.5	20628.9
17.5°	20684.6	20764.5	20812.4	20807.7	20782.8	20699.3	20271.7	20036.5	19803.1	19592.7	19316.7
20°	20327.9	20321.8	20280.2	20162.0	20019.8	19798.6	19065.5	18642.6	18233.6	17874.5	17438.8
22.5°	19664.2	19559.8	19414.3	19159.7	18876.9	18490.4	17439.8	16817.7	16248.5	15745.6	15182.2
25°	18702.7	18487.9	18219.4	17815.2	17375.7	16811.9	15517.2	14743.4	14059.8	13467.1	12817.1
27.5°	17472.1	17148.4	16755.0	16195.5	15600.1	14877.9	13442.4	12588.5	11854.8	11219.2	10527.4
30°	16015.1	15594.3	15086.1	14391.9	13673.7	12854.6	11398.7	10533.7	9791.0	9137.2	8444.9
32.5°	14368.7	13875.7	13280.3	12501.1	11724.4	10882.2	9476.1	8638.9	7929.4	7300.5	6673.8
35°	12552.7	12024.1	11394.1	10599.4	9827.4	9008.5	7718.4	6963.5	6337.0	5781.0	5275.1
37.5°	10604.7	10085.7	9487.0	8738.0	8022.0	7280.1	6166.8	5534.3	5008.5	4547.1	4156.4
40°	8579.4	8125.3	7607.2	6959.6	6348.6	5730.7	4816.9	4314.7	3899.9	3548.0	3255.2
42.5°	6578.9	6226.9	5829.7	5317.9	4850.4	4379.9	3676.6	3304.5	2997.2	2743.9	2536.9
45°	4773.3	4537.8	4271.3	3915.6	3592.1	3263.9	2763.3	2501.8	2301.7	2138.3	2000.2
47.5°	3336.8	3200.2	3191.8	2863.0	2625.8	2425.2	2102.6	1937.5	1814.9	1715.9	1628.5
50°	2343.3	2277.2	2195.1	2077.8	1967.7	1854.3	1657.9	1558.0	1486.2	1426.2	1370.9
52.5°	1751.8	1717.5	1673.8	1611.5	1551.8	1488.0	1363.7	1300.1	1277.6	1221.8	1178.0
55°	1399.2	1379.5	1354.6	1318.1	1281.8	1267.2	1160.7	1113.5	1083.6	1061.6	1038.0
57.5°	1162.2	1147.6	1132.8	1108.0	1087.0	1061.6	1005.1	980.8	963.0	950.1	933.8
60°	991.4	982.6	974.3	959.8	948.4	934.7	898.9	885.2	875.9	868.1	857.7
62.5°	875.0	870.5	866.2	858.5	852.7	845.3	820.7	814.2	809.5	805.6	799.3
65°	791.0	787.8	785.4	780.3	777.4	773.0	751.9	747.5	744.7	743.2	739.5
67.5°	714.7	711.3	709.7	706.1	704.9	702.2	684.9	682.4	681.5	682.0	680.6
70°	643.3	641.9	642.6	642.0	643.7	644.1	633.7	633.6	634.7	637.0	637.2
72.5°	600.5	600.5	601.3	601.7	603.2	604.0	595.3	594.9	595.3	597.0	597.1
75°	559.8	560.5	562.7	563.5	565.2	565.6	554.1	552.8	552.8	554.4	554.0
77.5°	503.5	505.9	510.1	512.3	515.9	516.5	503.6	502.1	502.2	503.6	502.3
80°	439.6	444.2	450.9	455.6	461.0	463.2	449.9	446.7	443.8	443.4	440.7
82.5°	371.6	377.3	385.3	389.5	395.4	396.7	374.5	370.2	367.8	368.0	365.6
85°	283.7	288.0	295.2	297.7	301.3	300.9	275.6	264.8	267.7	263.1	266.6
87.5°	177.9	180.5	185.0	185.6	187.4	187.0	161.5	156.4	154.9	155.0	153.2
90°	126.6	130.9	137.5	140.1	145.3	147.6	129.6	129.8	125.8	124.5	119.7
92.5°	81.0	86.8	92.8	98.7	104.6	110.7	114.2	119.4	113.4	107.0	101.1
95°	97.3	107.0	116.8	126.7	136.5	146.3	156.1	165.9	156.8	147.6	138.4
97.5°	109.2	120.8	132.4	144.0	155.6	167.2	178.8	190.4	180.6	170.6	160.8
100°	143.9	165.6	187.1	208.8	230.3	251.9	273.6	295.2	276.2	257.2	238.2
102.5°	301.5	347.5	393.3	439.3	485.1	531.1	577.2	623.1	579.5	535.8	492.2
105°	586.4	660.8	735.3	809.5	883.9	958.4	1033.0	1107.4	1037.8	968.1	898.5
107.5°	930.8	1006.4	1081.8	1157.2	1232.8	1308.3	1384.1	1459.6	1391.7	1323.7	1255.8
110°	1144.4	1199.5	1254.7	1309.8	1365.0	1420.0	1475.6	1530.9	1490.1	1449.3	1408.6



TEST NUMBER: P1444808
 CATALOG NUMBER: EHBR1-24-UNV-TA-L940-UPL40

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	1190.8	1230.4	1269.9	1309.3	1348.7	1388.2	1428.4	1468.0	1447.6	1427.2	1406.9
115°	1125.0	1151.8	1178.4	1205.1	1231.8	1258.5	1286.0	1312.9	1306.4	1300.1	1293.8
117.5°	1011.3	1026.4	1041.5	1056.5	1071.4	1086.6	1102.6	1117.8	1119.1	1120.5	1122.0
120°	890.2	896.8	903.2	909.8	916.2	922.7	930.4	937.1	942.9	948.7	954.5
122.5°	786.8	789.5	792.1	794.8	797.3	800.0	804.0	807.1	811.1	815.4	819.5
125°	703.0	704.6	706.0	707.5	708.8	710.4	713.5	715.2	715.9	716.3	717.0
127.5°	646.1	646.7	647.2	647.8	648.1	648.8	651.0	652.0	650.1	648.1	646.1
130°	604.1	605.0	605.9	607.0	607.9	608.8	611.6	613.1	609.3	605.6	601.7
132.5°	575.8	576.9	578.0	579.3	580.4	581.5	584.7	586.3	582.0	577.5	573.1
135°	551.5	553.0	554.3	555.6	556.9	558.5	562.0	563.9	559.8	555.5	551.3
137.5°	530.9	532.3	533.6	535.1	536.4	537.9	541.8	543.7	540.4	537.0	533.9
140°	512.8	514.4	516.0	517.6	519.2	521.0	525.2	527.4	524.9	522.4	519.8
142.5°	494.7	496.9	499.1	501.2	503.3	505.6	510.4	513.2	511.4	509.4	507.7
145°	482.2	484.6	487.0	489.5	491.8	494.3	499.7	502.9	501.9	500.7	499.5
147.5°	470.8	473.0	475.2	477.4	479.6	482.1	487.5	490.5	490.0	489.3	488.7
150°	459.5	461.7	464.0	466.2	468.6	471.0	476.9	480.2	479.7	479.1	478.5
152.5°	447.4	449.3	451.3	453.4	455.5	457.7	464.5	467.7	467.2	466.6	466.2
155°	438.9	440.6	442.1	443.8	445.4	447.3	454.1	457.1	456.9	456.6	456.3
157.5°	434.8	435.8	436.9	438.2	439.6	440.8	447.7	450.4	450.1	449.9	449.6
160°	431.3	432.2	433.0	434.1	435.1	436.1	443.1	445.5	445.3	445.0	444.8
162.5°	428.6	429.9	431.0	432.2	433.4	434.7	441.8	444.7	444.1	443.6	443.3
165°	428.9	429.7	430.4	431.3	432.0	432.8	439.3	441.5	441.4	441.1	440.9
167.5°	430.0	430.9	431.6	432.6	433.3	434.3	440.4	442.5	442.3	442.1	442.0
170°	432.4	433.2	433.7	434.5	435.2	436.0	441.0	442.8	442.6	442.0	441.7
172.5°	434.8	435.7	436.4	437.1	437.9	438.7	443.0	444.8	444.5	444.1	443.6
175°	434.4	435.0	435.5	436.3	436.8	437.5	440.9	442.1	442.0	441.9	441.7
177.5°	437.7	438.0	438.4	438.9	439.4	439.7	441.9	442.6	442.6	442.6	442.5
180°	439.9	439.9	439.9	439.9	439.9	439.9	439.9	439.9	439.9	439.9	439.9



TEST NUMBER: P1444808
 CATALOG NUMBER: EHBR1-24-UNV-TA-L940-UPL40

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6
2.5°	19941.3	19948.3	19949.3	19957.5	19956.9	19966.7	19965.1	19973.1	19968.4	19974.9	19969.5
5°	20409.7	20452.1	20474.4	20515.9	20528.9	20566.1	20576.5	20610.3	20611.7	20638.6	20632.5
7.5°	21071.9	21134.5	21171.6	21222.9	21248.9	21291.5	21310.4	21342.0	21352.1	21377.2	21379.1
10°	21467.3	21497.7	21518.9	21533.2	21546.3	21552.4	21559.6	21557.6	21559.6	21556.8	21562.8
12.5°	21311.8	21267.3	21238.0	21182.5	21150.2	21088.7	21058.5	20999.5	20978.0	20927.3	20920.0
15°	20524.1	20369.3	20260.0	20101.1	20001.1	19844.7	19753.2	19612.2	19547.7	19435.5	19406.1
17.5°	19088.4	18801.2	18579.0	18293.8	18096.0	17829.6	17662.0	17441.4	17320.6	17142.7	17081.2
20°	17075.6	16650.6	16317.3	15920.1	15635.9	15281.8	15055.1	14769.2	14603.2	14384.7	14296.2
22.5°	14712.5	14183.5	13767.1	13297.9	12955.0	12560.4	12288.8	11979.4	11798.8	11561.5	11456.4
25°	12276.9	11693.5	11230.6	10736.3	10374.0	9978.4	9706.7	9402.8	9215.9	8990.6	8886.2
27.5°	9947.5	9356.9	8909.5	8449.9	8117.6	7760.7	7515.5	7250.2	7084.3	6892.0	6793.7
30°	7891.8	7370.9	6990.2	6608.8	6332.3	6042.5	5838.7	5618.8	5473.3	5308.6	5215.1
32.5°	6217.0	5814.9	5516.7	5214.1	4987.8	4745.6	4569.5	4375.6	4244.2	4097.2	4012.4
35°	4923.7	4611.3	4373.5	4124.4	3930.1	3723.7	3568.6	3401.2	3283.3	3156.7	3083.5
37.5°	3890.3	3641.8	3446.2	3239.2	3079.6	2908.6	2851.0	2658.8	2536.8	2435.7	2365.7
40°	3053.1	2855.6	2693.7	2535.4	2405.1	2275.5	2171.5	2068.8	1990.0	1917.7	1867.7
42.5°	2384.3	2241.1	2122.8	2007.0	1911.9	1817.5	1742.1	1671.4	1618.3	1571.0	1538.8
45°	1895.3	1797.0	1714.8	1633.1	1566.1	1503.0	1452.2	1407.2	1372.9	1344.5	1324.3
47.5°	1557.1	1489.7	1431.8	1376.6	1331.1	1289.9	1255.9	1244.8	1207.9	1183.0	1173.6
50°	1323.3	1282.6	1238.5	1197.9	1167.5	1137.4	1115.3	1093.7	1079.9	1068.4	1065.0
52.5°	1148.8	1117.7	1093.2	1067.5	1047.4	1025.9	1010.7	996.3	988.8	982.8	982.0
55°	1019.1	997.3	981.1	963.9	951.9	939.2	931.4	923.7	920.5	917.4	917.7
57.5°	920.9	906.4	895.9	884.7	878.2	872.1	870.2	868.2	869.2	869.7	871.4
60°	849.4	840.0	833.4	826.9	824.2	822.3	823.8	825.4	828.9	831.7	834.2
62.5°	794.6	789.2	786.0	782.5	782.2	782.4	785.3	788.2	792.6	795.8	798.2
65°	738.2	735.1	734.0	731.9	732.9	733.7	737.2	739.4	743.7	746.3	749.4
67.5°	681.2	680.5	681.1	681.1	683.1	684.9	688.2	690.7	694.4	696.8	699.3
70°	639.1	639.4	641.0	641.3	643.4	644.5	647.5	649.1	652.4	654.4	657.5
72.5°	598.1	597.5	597.8	596.9	597.7	597.4	599.0	599.8	602.6	604.2	607.8
75°	554.6	552.7	552.3	550.3	550.4	548.9	549.7	549.6	551.4	552.2	554.8
77.5°	501.9	498.8	497.3	494.1	494.0	492.7	494.1	494.8	498.1	499.6	502.6
80°	438.9	434.1	431.8	428.0	428.7	428.5	431.7	434.1	438.2	438.9	442.7
82.5°	364.8	359.9	357.6	353.7	354.7	354.7	357.7	358.2	361.7	363.2	367.5
85°	261.2	263.1	257.9	258.3	257.1	259.2	261.2	263.7	266.6	271.4	275.1
87.5°	153.8	153.2	155.0	155.2	157.9	159.3	163.6	166.0	170.8	174.6	181.3
90°	117.6	112.7	111.9	108.8	109.1	106.0	106.6	103.6	104.7	103.2	105.1
92.5°	94.5	88.4	81.9	75.8	69.4	63.5	60.3	57.7	54.5	52.0	48.6
95°	129.3	120.1	111.0	101.8	92.7	83.6	80.2	76.9	73.5	70.2	66.9
97.5°	151.0	141.1	131.4	121.5	111.6	101.8	99.6	97.4	95.1	92.9	90.6
100°	219.2	200.2	181.3	162.2	143.3	124.3	122.5	120.7	119.0	117.2	115.3
102.5°	448.7	405.3	361.8	318.2	274.6	231.0	223.5	215.9	208.3	200.7	193.1
105°	828.7	759.0	689.3	619.7	550.1	480.4	459.7	438.8	418.0	397.3	376.6
107.5°	1187.8	1119.9	1052.0	984.1	916.2	848.3	815.5	782.7	749.7	716.9	684.2
110°	1367.7	1326.8	1286.2	1245.4	1204.8	1164.1	1132.7	1101.5	1070.2	1038.9	1007.6



TEST NUMBER: P1444808
 CATALOG NUMBER: EHBR1-24-UNV-TA-L940-UPL40

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	1386.6	1366.3	1345.9	1325.6	1305.4	1285.1	1269.8	1254.6	1239.5	1224.2	1208.8
115°	1287.3	1281.1	1274.7	1268.4	1262.3	1256.0	1254.8	1253.9	1252.8	1251.9	1250.8
117.5°	1123.4	1124.8	1126.1	1127.7	1129.2	1130.6	1138.8	1147.0	1155.3	1163.8	1172.1
120°	960.2	966.1	971.8	977.7	983.5	989.4	1000.4	1011.5	1022.6	1033.8	1045.2
122.5°	823.6	827.8	831.9	836.1	840.3	844.5	855.4	866.5	877.5	888.7	900.0
125°	717.4	717.9	718.4	718.9	719.4	720.1	729.2	738.3	747.6	756.9	766.1
127.5°	644.1	642.0	640.0	638.2	636.0	634.2	639.7	645.2	650.8	656.4	662.0
130°	597.9	594.1	590.2	586.5	582.6	578.8	581.2	583.5	585.9	588.3	590.8
132.5°	568.5	564.1	559.5	555.1	550.6	546.0	546.3	546.6	546.9	547.2	547.7
135°	547.1	543.0	538.6	534.3	529.9	525.8	525.0	524.1	523.2	522.5	521.7
137.5°	530.6	527.2	523.9	520.6	517.2	513.8	512.3	511.2	509.8	508.8	507.5
140°	517.2	514.5	511.8	509.2	506.6	504.0	502.8	501.9	500.9	499.9	498.9
142.5°	505.7	503.8	501.9	500.1	498.2	496.3	495.2	494.1	493.2	492.3	491.3
145°	498.4	497.2	496.1	494.9	493.7	492.7	491.8	491.1	490.3	489.7	489.1
147.5°	488.2	487.4	486.8	486.1	485.4	484.7	484.2	483.9	483.3	483.1	482.6
150°	477.9	477.3	476.6	476.2	475.3	474.8	474.6	474.5	474.2	474.2	474.0
152.5°	465.5	465.0	464.3	463.9	463.1	462.6	462.4	462.4	462.2	462.2	461.9
155°	455.9	455.7	455.3	455.0	454.5	454.4	454.0	453.6	453.3	453.0	452.6
157.5°	449.3	449.1	448.7	448.5	448.0	447.7	447.5	447.2	446.8	446.5	446.2
160°	444.5	444.3	443.9	443.6	443.4	443.1	442.5	442.0	441.4	441.0	440.4
162.5°	442.7	442.2	441.7	441.2	440.6	440.2	439.8	439.5	439.2	438.9	438.5
165°	440.6	440.3	440.0	439.7	439.5	439.2	438.6	438.2	437.6	437.1	436.5
167.5°	441.6	441.4	441.1	440.9	440.6	440.2	439.8	439.3	438.8	438.2	437.7
170°	441.3	440.8	440.4	439.9	439.5	439.0	438.5	438.0	437.5	437.0	436.5
172.5°	443.4	443.0	442.5	442.3	441.7	441.3	440.9	440.5	440.1	439.6	439.3
175°	441.6	441.6	441.5	441.2	441.2	441.0	440.9	440.9	440.7	440.6	440.4
177.5°	442.5	442.4	442.4	442.3	442.3	442.3	442.0	441.7	441.4	441.1	440.9
180°	439.9	439.9	439.9	439.9	439.9	439.9	439.9	439.9	439.9	439.9	439.9



TEST NUMBER: P1444808
 CATALOG NUMBER: EHBR1-24-UNV-TA-L940-UPL40

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6
2.5°	19975.1	19970.1	19972.5	19963.1	19965.4	19954.1	19953.1	19940.3	19939.1	19927.1	19922.5
5°	20651.5	20640.3	20652.9	20633.3	20637.2	20611.7	20609.6	20576.7	20565.3	20524.2	20506.5
7.5°	21394.8	21390.6	21398.2	21381.9	21381.4	21358.6	21349.3	21319.8	21301.5	21258.3	21230.7
10°	21557.6	21561.4	21555.2	21556.8	21547.9	21545.4	21536.4	21530.6	21515.8	21504.6	21488.1
12.5°	20881.4	20885.5	20859.7	20876.0	20863.2	20893.4	20890.8	20926.4	20931.9	20976.8	20993.9
15°	19318.7	19313.9	19264.3	19295.5	19278.8	19345.0	19359.9	19448.9	19496.5	19611.0	19681.2
17.5°	16957.9	16945.1	16875.5	16913.5	16894.1	16991.7	17024.5	17167.0	17255.8	17440.1	17571.5
20°	14143.8	14119.3	14037.8	14082.2	14062.4	14173.2	14220.0	14392.2	14506.7	14750.9	14924.6
22.5°	11294.6	11256.0	11176.2	11217.7	11198.8	11313.8	11374.6	11547.4	11678.6	11929.3	12132.0
25°	8736.1	8701.8	8624.5	8653.6	8646.6	8743.8	8797.9	8961.3	9090.3	9329.0	9522.5
27.5°	6663.2	6627.4	6557.7	6578.3	6571.2	6654.0	6705.1	6841.5	6952.5	7153.5	7323.4
30°	5099.7	5056.6	4997.4	5008.8	5004.0	5071.0	5118.6	5233.6	5328.8	5498.7	5645.0
32.5°	3908.9	3865.6	3811.3	3816.6	3809.4	3862.0	3901.3	4001.2	4084.1	4228.6	4356.0
35°	2990.9	3041.5	2925.5	2999.0	2922.5	3034.8	2994.4	3056.9	3128.2	3249.9	3356.2
37.5°	2299.3	2264.0	2234.1	2230.9	2230.7	2256.8	2287.6	2347.7	2410.5	2501.2	2594.8
40°	1822.0	1797.2	1778.0	1776.6	1778.0	1796.5	1819.2	1860.8	1906.8	1971.9	2040.7
42.5°	1511.2	1494.7	1483.1	1482.3	1486.0	1499.1	1514.9	1539.6	1569.5	1611.7	1658.9
45°	1307.9	1298.8	1292.4	1292.0	1293.7	1300.5	1309.6	1325.0	1344.0	1370.3	1400.2
47.5°	1165.3	1163.2	1159.1	1159.2	1157.4	1160.2	1161.2	1169.9	1179.9	1199.8	1238.8
50°	1061.5	1061.5	1058.7	1058.5	1055.9	1055.7	1053.5	1057.0	1061.7	1074.0	1086.4
52.5°	979.4	979.2	976.1	975.5	972.7	972.5	970.7	972.0	972.6	978.9	986.3
55°	915.2	913.4	909.4	908.1	907.1	908.6	907.9	908.0	907.1	909.8	912.0
57.5°	869.2	866.7	863.0	861.9	861.6	863.5	863.5	862.9	859.4	857.1	853.8
60°	832.8	830.3	826.3	825.3	825.8	828.5	828.3	826.1	821.0	816.5	811.2
62.5°	797.0	796.0	793.9	793.7	793.1	793.6	791.7	789.4	784.3	779.5	773.8
65°	749.0	749.6	748.0	748.2	746.4	746.1	743.3	741.0	735.8	731.5	725.7
67.5°	699.2	699.6	698.3	698.3	697.3	697.5	695.8	693.7	689.3	685.8	681.3
70°	658.1	659.1	658.4	658.7	657.5	657.0	654.4	652.2	647.8	644.9	640.8
72.5°	608.9	611.2	611.1	611.6	609.9	608.9	605.8	603.1	599.1	596.7	593.6
75°	555.8	558.7	559.5	560.8	558.2	556.9	553.5	551.4	548.1	546.7	544.5
77.5°	504.0	507.2	510.2	513.0	509.0	505.3	500.9	497.7	492.9	491.1	487.7
80°	445.8	451.4	458.1	463.7	456.4	449.1	441.9	436.6	430.3	427.7	423.6
82.5°	369.9	375.5	379.5	383.0	378.0	372.6	365.7	361.0	354.2	351.7	346.9
85°	281.0	288.2	290.4	292.4	289.1	286.2	279.7	270.9	266.6	259.9	256.5
87.5°	184.8	189.1	189.9	190.5	188.6	187.2	183.0	178.9	171.5	166.2	159.8
90°	102.9	103.6	100.0	98.9	98.4	100.4	98.1	98.7	94.6	94.2	90.7
92.5°	45.9	42.9	40.0	37.1	40.3	42.9	46.1	48.6	51.9	54.5	57.7
95°	63.5	60.2	56.8	53.5	56.2	58.8	61.5	64.2	66.8	69.5	72.2
97.5°	88.4	86.2	83.9	81.7	83.3	84.9	86.4	87.9	89.5	91.1	92.7
100°	113.6	111.8	110.0	108.3	108.3	108.3	108.3	108.3	108.3	108.3	108.3
102.5°	185.5	177.9	170.3	162.8	167.9	173.0	178.1	183.3	188.5	193.6	198.8
105°	355.8	335.0	314.3	293.6	313.6	333.7	353.7	373.9	393.9	414.2	434.2
107.5°	651.3	618.5	585.7	552.9	589.6	626.2	662.8	699.4	735.9	772.5	809.3
110°	976.4	945.2	913.9	882.7	921.6	960.3	999.2	1037.9	1076.9	1115.6	1154.6



TEST NUMBER: P1444808
 CATALOG NUMBER: EHBR1-24-UNV-TA-L940-UPL40

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	1193.6	1178.5	1163.3	1148.2	1173.1	1198.1	1223.1	1248.2	1273.3	1298.3	1323.3
115°	1249.9	1249.0	1248.1	1247.2	1259.0	1270.9	1282.7	1294.6	1306.4	1318.3	1330.3
117.5°	1180.4	1188.8	1197.3	1205.7	1209.6	1213.4	1217.2	1221.0	1225.0	1228.9	1232.8
120°	1056.5	1067.7	1079.0	1090.4	1088.8	1087.2	1085.7	1084.2	1082.9	1081.4	1080.1
122.5°	911.1	922.4	933.8	945.1	941.7	938.4	935.1	931.8	928.7	925.5	922.3
125°	775.7	785.0	794.6	804.1	800.7	797.4	794.1	791.0	787.7	784.5	781.6
127.5°	667.9	673.8	679.5	685.5	683.9	682.3	681.1	679.5	678.2	676.9	675.8
130°	593.5	596.2	599.0	601.6	602.0	602.5	603.1	603.7	604.5	605.2	606.0
132.5°	548.4	548.9	549.6	550.3	552.1	553.9	555.9	557.9	560.0	562.0	564.5
135°	521.2	520.7	520.1	519.9	522.6	525.2	528.0	530.8	533.8	536.9	540.0
137.5°	506.5	505.5	504.7	503.7	506.4	509.1	511.8	514.7	517.6	520.7	524.0
140°	498.1	497.3	496.8	496.0	498.7	501.3	504.0	506.9	509.9	513.0	516.0
142.5°	490.6	489.8	489.1	488.6	490.8	493.3	495.9	498.4	501.2	503.9	506.7
145°	488.5	487.9	487.4	487.1	488.7	490.5	492.5	494.3	496.4	498.2	500.6
147.5°	482.3	482.0	481.8	481.7	483.0	484.3	485.7	487.0	488.6	490.0	491.6
150°	474.0	473.8	473.9	473.9	474.8	475.6	476.5	477.4	478.4	479.3	480.5
152.5°	462.1	461.9	462.1	462.1	462.8	463.6	464.5	465.3	466.3	467.1	468.3
155°	452.5	452.3	452.0	451.8	452.1	452.5	452.9	453.2	453.7	454.1	454.5
157.5°	446.1	445.8	445.6	445.3	445.3	445.4	445.5	445.6	445.8	445.9	446.1
160°	440.0	439.5	439.0	438.6	438.9	439.1	439.4	439.6	439.9	440.3	440.6
162.5°	438.3	438.1	437.8	437.5	437.3	437.0	436.9	436.7	436.5	436.3	436.3
165°	436.0	435.5	435.1	434.5	434.5	434.6	434.5	434.5	434.6	434.6	434.7
167.5°	437.2	436.7	436.2	435.7	435.4	434.8	434.5	434.1	433.7	433.3	433.1
170°	436.1	435.6	435.2	434.8	434.6	434.4	434.3	434.1	434.1	434.0	434.0
172.5°	438.8	438.4	438.0	437.7	437.5	437.3	437.3	437.2	437.0	437.0	437.0
175°	440.3	440.2	440.1	439.9	439.6	439.4	439.2	439.0	438.7	438.4	438.2
177.5°	440.6	440.3	440.0	439.8	439.7	439.7	439.7	439.7	439.7	439.6	439.6
180°	439.9	439.9	439.9	439.9	439.9	439.9	439.9	439.9	439.9	439.9	439.9



TEST NUMBER: P1444808
 CATALOG NUMBER: EHBR1-24-UNV-TA-L940-UPL40

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6
2.5°	19909.6	19904.4	19890.6	19883.8	19871.1	19864.6	19854.7	19848.2	19840.2	19834.3	19831.2
5°	20461.3	20435.8	20384.8	20353.4	20298.2	20262.0	20207.3	20167.1	20110.7	20068.9	20015.6
7.5°	21178.9	21139.9	21074.5	21025.0	20947.9	20889.0	20802.4	20733.3	20637.7	20558.3	20460.7
10°	21471.2	21448.3	21419.0	21387.1	21344.5	21302.5	21243.5	21183.3	21103.1	21023.2	20919.0
12.5°	21039.3	21060.7	21103.1	21122.8	21155.2	21166.1	21181.1	21174.1	21160.9	21128.3	21081.1
15°	19816.2	19905.8	20047.3	20145.3	20282.6	20378.9	20506.5	20588.5	20683.1	20739.5	20793.2
17.5°	17804.2	17977.5	18227.4	18426.7	18694.3	18911.9	19178.5	19387.9	19629.8	19815.3	20012.8
20°	15227.2	15469.9	15814.9	16107.8	16495.5	16824.3	17245.6	17598.5	18010.1	18353.2	18723.7
22.5°	12453.7	12739.1	13134.3	13487.7	13950.7	14364.3	14892.1	15358.7	15915.2	16413.7	16965.2
25°	9837.2	10116.9	10519.5	10885.3	11385.3	11840.8	12417.4	12952.8	13598.5	14200.7	14892.1
27.5°	7593.3	7841.8	8195.8	8525.0	8982.8	9430.1	10015.3	10586.1	11275.2	11922.4	12667.5
30°	5864.1	6065.9	6349.4	6614.3	6981.8	7347.6	7868.9	8396.7	9082.4	9753.1	10517.0
32.5°	4544.6	4716.5	4953.2	5168.2	5451.4	5727.2	6111.1	6532.9	7134.4	7776.8	8515.4
35°	3518.0	3665.1	3866.5	4051.8	4284.6	4503.7	4790.1	5091.2	5550.2	6090.5	6751.5
37.5°	2804.7	2864.7	3008.5	3160.2	3353.7	3533.6	3757.7	3980.4	4308.8	4735.1	5275.1
40°	2133.0	2228.2	2345.2	2464.8	2611.2	2755.5	3001.4	3119.7	3335.9	3642.0	4061.0
42.5°	1721.0	1788.0	1870.4	1953.5	2055.6	2156.0	2280.4	2407.0	2568.6	2775.9	3074.1
45°	1440.2	1483.8	1536.9	1592.4	1659.4	1727.9	1811.2	1898.1	2007.7	2135.1	2316.2
47.5°	1252.6	1276.7	1311.4	1349.2	1395.1	1442.7	1496.8	1552.1	1620.2	1695.8	1798.9
50°	1106.1	1126.3	1153.2	1178.4	1210.2	1258.8	1280.4	1310.9	1351.8	1396.4	1454.0
52.5°	1000.1	1013.5	1030.5	1045.0	1065.1	1083.2	1107.2	1128.2	1156.5	1183.3	1220.5
55°	917.7	922.5	932.1	941.4	955.3	967.8	984.2	998.0	1016.1	1032.0	1055.5
57.5°	853.9	854.3	858.8	863.6	872.6	880.4	891.7	900.7	913.3	923.4	937.5
60°	808.1	805.7	806.5	808.3	813.2	818.4	825.6	831.5	839.4	845.1	853.0
62.5°	770.0	766.2	765.3	764.8	767.3	769.2	773.1	776.0	780.4	783.0	787.1
65°	721.8	717.4	715.6	713.5	714.2	713.6	715.1	715.2	717.5	718.0	720.4
67.5°	678.1	674.4	672.1	669.3	668.1	666.1	665.2	663.2	663.0	661.4	661.0
70°	638.4	634.6	632.8	630.2	628.9	626.2	624.6	621.3	619.4	616.4	614.7
72.5°	592.2	590.2	589.6	587.9	587.4	585.9	585.3	582.9	581.6	579.0	577.6
75°	544.1	542.4	542.2	540.4	540.4	538.6	538.1	535.7	534.5	531.9	530.8
77.5°	486.7	484.2	483.5	481.4	481.9	481.0	481.8	480.0	479.1	476.5	475.7
80°	422.1	418.9	417.6	414.9	415.6	414.3	415.6	415.4	416.4	414.3	413.9
82.5°	345.5	342.0	341.4	339.5	340.7	340.9	343.6	342.1	342.7	340.8	341.6
85°	251.5	248.8	245.1	244.7	242.2	244.7	241.5	243.6	240.2	242.6	239.3
87.5°	155.9	150.5	147.6	143.7	142.2	138.4	136.9	134.2	135.0	133.7	134.4
90°	91.4	88.6	90.6	90.0	92.7	92.5	96.1	96.8	100.6	101.4	105.5
92.5°	60.3	63.2	68.6	74.1	79.3	84.6	90.0	95.5	100.7	106.2	111.4
95°	74.8	77.5	84.7	91.8	98.9	106.1	113.3	120.5	127.6	134.7	141.9
97.5°	94.3	95.9	103.0	110.1	117.3	124.5	131.5	138.9	146.1	153.2	160.3
100°	108.3	108.4	128.7	149.0	169.2	189.6	209.9	230.2	250.5	270.8	291.1
102.5°	203.9	209.1	260.4	311.7	363.1	414.4	465.6	517.1	568.4	619.8	671.3
105°	454.4	474.5	552.7	631.1	709.4	787.8	866.2	944.7	1022.9	1101.4	1179.7
107.5°	845.8	882.5	953.3	1024.1	1094.8	1165.7	1236.4	1307.2	1378.0	1448.8	1519.8
110°	1193.3	1232.3	1279.7	1327.0	1374.5	1421.9	1469.3	1516.7	1564.2	1611.7	1659.3



TEST NUMBER: P1444808
 CATALOG NUMBER: EHBR1-24-UNV-TA-L940-UPL40

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	1348.3	1373.4	1401.0	1428.6	1456.3	1483.8	1511.5	1539.1	1566.8	1594.5	1622.3
115°	1342.2	1354.2	1364.9	1375.6	1386.2	1396.9	1407.7	1418.5	1429.4	1440.1	1451.0
117.5°	1236.7	1240.8	1242.3	1243.9	1245.4	1247.2	1248.9	1250.6	1252.4	1254.2	1255.9
120°	1078.7	1077.4	1075.4	1073.5	1071.6	1069.8	1068.0	1066.2	1064.5	1062.7	1061.0
122.5°	919.2	916.2	914.3	912.5	910.7	909.0	907.3	905.7	904.1	902.4	900.7
125°	778.5	775.6	777.0	778.3	779.8	781.3	782.7	784.4	785.8	787.3	788.9
127.5°	674.5	673.5	677.3	681.3	685.2	689.2	693.1	697.2	701.2	705.3	709.3
130°	606.9	607.9	612.9	618.1	623.2	628.4	633.5	638.7	643.9	649.1	654.2
132.5°	566.6	569.0	573.7	578.7	583.6	588.6	593.6	598.6	603.5	608.6	613.4
135°	543.1	546.5	550.9	555.4	559.8	564.5	568.9	573.5	577.9	582.5	586.8
137.5°	526.9	530.3	533.8	537.4	540.8	544.5	548.2	551.8	555.3	558.9	562.4
140°	519.2	522.5	524.2	526.4	528.3	530.3	532.2	534.2	536.1	538.2	540.0
142.5°	509.6	512.7	513.7	514.9	516.2	517.6	518.7	520.0	521.2	522.4	523.4
145°	502.6	505.0	504.9	504.9	505.0	505.0	504.9	505.0	504.9	504.9	504.8
147.5°	493.3	495.0	494.5	494.3	494.0	493.6	493.3	493.0	492.6	492.3	491.9
150°	481.6	482.8	482.0	481.6	480.7	480.2	479.4	478.9	478.1	477.6	476.7
152.5°	469.2	470.3	469.4	468.8	468.0	467.3	466.4	465.8	464.9	464.2	463.5
155°	454.9	455.5	455.0	454.6	454.3	453.8	453.3	453.2	452.9	452.4	452.1
157.5°	446.3	446.4	446.2	445.9	445.7	445.4	445.2	445.0	445.0	444.9	444.9
160°	440.8	441.2	440.9	440.7	440.5	440.2	440.0	439.8	439.7	439.7	439.7
162.5°	436.0	435.9	435.7	435.5	435.3	435.1	434.9	435.0	434.8	434.8	434.8
165°	434.9	435.1	434.5	434.1	433.8	433.4	433.0	432.7	432.6	432.3	432.1
167.5°	432.8	432.7	432.7	432.7	432.7	432.7	432.8	433.1	433.2	433.5	433.6
170°	433.9	434.0	433.7	433.5	433.3	433.2	433.0	432.8	432.8	432.7	432.6
172.5°	437.0	437.0	436.6	436.1	435.7	435.3	434.8	434.5	434.1	433.8	433.3
175°	437.9	437.7	437.5	437.2	437.0	436.7	436.5	436.1	435.9	435.6	435.5
177.5°	439.6	439.4	439.3	439.3	439.3	439.2	439.2	439.1	439.1	439.1	438.9
180°	439.9	439.9	439.9	439.9	439.9	439.9	439.9	439.9	439.9	439.9	439.9



TEST NUMBER: P1444808
 CATALOG NUMBER: EHBR1-24-UNV-TA-L940-UPL40

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6
2.5°	19827.2	19826.9	19825.0	19825.9	19826.3	19827.7	19829.4	19831.2	19831.5	19833.0	19833.2
5°	19975.5	19926.5	19890.3	19850.3	19820.3	19793.3	19775.3	19761.0	19755.5	19756.8	19760.2
7.5°	20377.9	20276.6	20193.1	20098.1	20018.9	19935.1	19865.5	19799.4	19751.3	19715.4	19695.3
10°	20819.4	20696.1	20578.1	20440.7	20310.2	20171.2	20045.1	19918.2	19812.4	19720.4	19653.0
12.5°	21015.4	20928.2	20826.2	20696.5	20556.9	20396.4	20234.2	20060.5	19898.7	19748.7	19627.7
15°	20807.9	20808.1	20770.9	20708.6	20611.7	20483.4	20329.0	20147.8	19957.1	19762.4	19584.6
17.5°	20149.4	20273.6	20342.8	20386.5	20373.0	20325.8	20227.4	20088.3	19910.5	19703.2	19486.2
20°	19018.4	19311.5	19520.5	19708.4	19813.7	19883.6	19876.7	19820.0	19693.4	19517.1	19291.2
22.5°	17434.3	17926.2	18314.3	18676.2	18930.0	19136.6	19234.7	19276.4	19219.0	19096.2	18884.0
25°	15510.0	16178.9	16749.6	17303.5	17719.0	18076.1	18290.6	18441.8	18453.8	18389.7	18200.3
27.5°	13371.9	14161.4	14883.7	15619.9	16204.1	16717.4	17054.3	17300.8	17379.1	17368.9	17196.9
30°	11236.5	12065.3	12861.5	13719.9	14442.9	15098.7	15543.7	15877.1	16005.6	16030.2	15864.8
32.5°	9219.8	10037.1	10831.1	11728.5	12524.2	13275.8	13801.5	14197.5	14346.9	14382.1	14200.7
35°	7389.5	8143.5	8898.1	9767.9	10559.0	11337.3	11891.2	12305.8	12445.4	12468.9	12258.9
37.5°	5802.4	6444.8	7102.3	7882.7	8609.2	9340.2	9866.4	10256.1	10357.8	10351.4	10113.9
40°	4466.0	4965.5	5493.7	6136.3	6740.3	7358.1	7802.5	8124.7	8178.1	8138.6	7888.9
42.5°	3358.2	3718.9	4101.9	4581.6	5029.7	5492.1	5815.4	6054.6	6062.2	5999.7	5775.6
45°	2501.8	2853.8	3014.4	3304.4	3593.0	3900.5	4097.9	4245.7	4222.8	4167.8	3997.5
47.5°	1907.3	2042.4	2185.9	2365.7	2533.9	2882.8	2857.0	3094.2	2923.3	3039.9	2783.4
50°	1514.6	1590.1	1667.5	1762.9	1850.7	1941.9	1998.9	2041.4	2035.9	2017.7	1968.5
52.5°	1288.5	1311.9	1350.0	1404.2	1453.3	1502.6	1535.1	1561.4	1562.0	1554.5	1529.8
55°	1076.9	1106.6	1133.9	1169.4	1229.8	1239.1	1285.7	1276.2	1279.9	1266.9	1280.2
57.5°	949.5	966.8	982.1	1003.3	1020.7	1041.1	1053.1	1064.7	1063.6	1061.1	1048.4
60°	859.3	868.8	877.3	889.6	899.2	910.7	916.3	922.1	920.2	915.9	904.6
62.5°	789.6	795.6	800.5	808.4	814.3	821.4	824.2	826.7	824.2	820.2	810.3
65°	720.9	724.8	727.9	733.9	738.0	744.1	746.5	748.9	746.6	743.5	735.8
67.5°	659.0	659.3	659.0	661.5	662.8	666.4	667.5	669.3	666.6	663.9	657.5
70°	612.0	611.1	609.9	610.9	611.1	612.8	613.1	612.8	609.7	604.9	597.9
72.5°	575.3	574.8	573.9	574.7	574.7	576.3	575.9	575.0	571.1	566.5	559.5
75°	528.1	527.8	526.0	526.0	524.5	525.1	523.1	522.1	517.7	513.9	507.7
77.5°	472.9	472.0	469.4	468.4	465.6	464.4	460.9	459.1	454.6	451.6	446.3
80°	411.2	410.3	406.9	405.1	400.7	397.9	392.6	389.5	384.4	381.4	376.3
82.5°	339.9	340.2	337.0	334.6	328.3	323.5	316.4	312.6	307.0	304.0	298.7
85°	241.8	238.3	240.1	240.0	236.0	231.8	226.0	222.0	217.3	214.5	210.7
87.5°	132.6	133.4	132.5	131.6	128.8	126.7	122.2	119.8	116.4	114.7	111.9
90°	98.6	95.0	88.4	85.0	78.3	73.7	66.5	62.4	55.6	53.8	49.9
92.5°	105.4	99.4	93.5	87.3	81.5	75.5	69.4	63.4	57.4	55.2	53.4
95°	133.2	124.5	115.8	107.0	98.4	89.6	81.1	72.3	63.6	61.9	60.1
97.5°	150.1	139.8	129.6	119.4	109.1	98.8	88.7	78.4	68.2	67.1	66.0
100°	267.6	244.0	220.4	196.8	173.2	149.5	126.0	102.3	78.7	77.4	76.0
102.5°	614.0	556.6	499.4	442.2	385.0	327.7	270.4	213.0	155.8	147.5	139.3
105°	1093.1	1006.4	919.8	833.1	746.4	659.6	573.1	486.2	399.6	371.7	343.9
107.5°	1438.3	1356.8	1275.2	1193.8	1112.3	1030.9	949.3	867.7	786.2	737.1	688.1
110°	1594.5	1529.8	1465.1	1400.4	1335.7	1271.0	1206.1	1141.5	1076.7	1034.3	992.2



TEST NUMBER: P1444808
 CATALOG NUMBER: EHBR1-24-UNV-TA-L940-UPL40

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	1574.9	1527.2	1479.9	1432.4	1384.9	1337.4	1290.0	1242.3	1194.7	1169.0	1143.3
115°	1422.4	1393.6	1365.0	1336.4	1307.6	1278.9	1250.3	1221.3	1192.6	1179.0	1165.3
117.5°	1241.1	1226.3	1211.7	1196.9	1182.1	1167.2	1152.4	1137.5	1122.6	1117.8	1112.9
120°	1056.5	1051.8	1047.1	1042.4	1037.7	1033.0	1028.3	1023.5	1018.7	1019.0	1019.4
122.5°	902.2	903.6	905.1	906.3	907.8	909.0	910.5	911.7	913.0	916.4	919.7
125°	792.8	796.7	800.7	804.6	808.3	812.2	816.1	819.8	823.9	827.1	830.6
127.5°	713.8	718.1	722.6	727.0	731.3	735.6	740.1	744.2	748.7	751.6	754.7
130°	658.1	661.7	665.6	669.2	673.0	676.7	680.4	684.1	687.8	690.1	692.3
132.5°	616.7	620.1	623.4	626.6	630.1	633.2	636.6	639.9	643.3	644.8	646.4
135°	589.4	591.7	594.1	596.3	599.0	601.3	603.7	606.1	608.6	609.5	610.5
137.5°	564.3	566.3	568.2	570.1	572.0	574.0	576.0	578.0	580.1	580.2	580.7
140°	542.1	544.2	546.2	548.3	550.5	552.6	554.8	557.0	559.3	559.5	559.8
142.5°	525.1	526.6	528.1	529.7	531.4	532.9	534.7	536.5	538.3	538.6	538.9
145°	506.8	508.7	510.6	512.6	514.5	516.7	518.9	521.0	523.2	523.2	523.3
147.5°	493.5	495.2	496.9	498.6	500.4	502.1	504.1	506.0	507.9	507.9	507.9
150°	478.7	480.5	482.3	484.2	486.2	488.3	490.2	492.4	494.7	495.1	495.4
152.5°	465.5	467.5	469.5	471.7	473.9	476.2	478.5	480.7	483.1	483.4	483.8
155°	454.2	456.1	458.3	460.4	462.7	464.8	467.0	469.3	471.5	472.2	472.6
157.5°	446.7	448.5	450.4	452.3	454.3	456.2	458.2	460.1	462.3	462.7	463.1
160°	441.3	442.9	444.6	446.3	448.0	449.7	451.5	453.2	455.0	455.4	455.9
162.5°	436.4	438.1	439.7	441.3	443.2	444.8	446.5	448.2	450.0	450.4	450.8
165°	433.3	434.4	435.7	436.8	438.1	439.2	440.5	441.7	443.0	443.5	444.2
167.5°	434.6	435.4	436.3	437.1	438.2	439.2	440.2	441.0	442.1	442.5	443.1
170°	433.5	434.2	435.1	435.9	436.9	437.8	438.6	439.5	440.5	440.9	441.5
172.5°	433.9	434.3	435.0	435.5	436.1	436.7	437.2	437.9	438.4	439.2	439.7
175°	435.7	436.0	436.3	436.6	436.8	437.2	437.5	438.0	438.2	438.7	439.3
177.5°	439.1	439.4	439.6	439.7	440.2	440.4	440.7	440.9	441.2	441.9	442.5
180°	439.9	439.9	439.9	439.9	439.9	439.9	439.9	439.9	439.9	439.9	439.9



TEST NUMBER: P1444808
 CATALOG NUMBER: EHBR1-24-UNV-TA-L940-UPL40

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6
2.5°	19832.6	19832.3	19831.7	19830.8	19829.9	19830.4	19831.3	19833.6	19837.5	19843.3	19850.9
5°	19762.9	19767.0	19769.2	19769.6	19767.5	19766.3	19768.2	19773.6	19784.6	19803.1	19827.9
7.5°	19690.0	19694.9	19702.6	19708.4	19709.4	19708.0	19708.4	19716.9	19737.2	19773.2	19823.5
10°	19612.0	19597.2	19605.0	19619.2	19630.6	19632.7	19634.1	19644.2	19673.8	19728.2	19809.0
12.5°	19540.0	19493.1	19484.1	19496.9	19514.2	19519.7	19518.2	19522.5	19557.3	19629.1	19741.8
15°	19445.3	19357.0	19326.9	19330.2	19351.5	19359.1	19353.5	19345.0	19378.9	19466.5	19612.5
17.5°	19292.1	19149.7	19094.3	19091.8	19116.8	19123.4	19109.7	19083.2	19116.4	19225.9	19407.1
20°	19059.1	18849.0	18744.5	18727.9	18755.1	18747.1	18719.7	18679.7	18723.5	18856.5	19072.0
22.5°	18640.3	18374.1	18195.7	18138.1	18170.5	18148.9	18109.0	18057.8	18115.9	18267.1	18507.1
25°	17955.9	17648.3	17404.1	17267.0	17292.8	17254.2	17210.8	17148.6	17218.0	17391.5	17655.7
27.5°	16950.0	16594.7	16292.1	16065.2	16073.5	16022.8	15972.8	15892.4	15979.0	16184.5	16482.4
30°	15612.4	15201.3	14832.6	14524.4	14496.9	14447.7	14396.3	14290.9	14399.3	14645.2	14993.3
32.5°	13932.6	13476.1	13050.2	12660.5	12586.9	12538.9	12493.3	12371.9	12513.9	12800.5	13200.5
35°	11968.1	11481.9	11020.2	10575.0	10453.2	10405.2	10365.2	10248.9	10426.0	10738.1	11170.1
37.5°	9811.8	9315.1	8856.7	8400.2	8228.1	8163.0	8134.0	8057.8	8262.1	8570.7	9004.4
40°	7598.2	7136.3	6725.4	6322.1	6125.9	6026.3	6011.1	5997.2	6194.8	6462.5	6856.3
42.5°	5527.4	5154.7	4837.8	4529.7	4351.9	4215.8	4215.7	4257.1	4434.9	4635.4	4939.0
45°	3823.5	3573.4	3371.4	3165.5	3220.6	2949.3	3108.7	3026.9	3114.9	3244.1	3441.5
47.5°	2628.3	2491.8	2380.8	2265.8	2181.9	2101.9	2108.9	2160.5	2243.3	2320.0	2422.7
50°	1915.6	1846.1	1789.5	1729.8	1688.0	1652.7	1654.8	1677.1	1720.7	1761.1	1814.8
52.5°	1501.0	1462.6	1431.9	1398.9	1377.0	1359.5	1360.4	1371.3	1394.8	1417.9	1448.7
55°	1237.1	1232.6	1192.6	1163.0	1151.7	1139.9	1142.0	1146.3	1162.3	1175.8	1196.2
57.5°	1036.7	1018.8	1006.8	991.3	984.1	975.8	977.7	979.3	990.0	999.0	1013.7
60°	895.2	882.5	874.1	863.4	858.7	853.5	854.7	855.6	862.4	868.4	878.9
62.5°	801.2	789.8	782.5	774.3	770.9	767.4	768.2	768.5	772.8	777.2	785.1
65°	729.1	720.1	713.9	706.8	703.4	699.7	700.0	700.0	703.7	706.8	712.8
67.5°	652.8	646.0	642.0	636.4	634.1	630.4	630.3	629.0	631.4	632.7	636.7
70°	591.6	584.7	579.7	574.3	571.3	568.0	568.0	568.1	570.9	573.7	579.0
72.5°	553.8	547.2	542.7	538.0	535.1	532.3	531.9	531.6	533.6	535.1	538.6
75°	503.6	498.4	495.8	491.3	489.2	485.9	485.5	484.0	484.9	485.3	487.8
77.5°	442.9	438.0	435.8	431.4	429.5	425.9	425.6	424.0	424.7	424.2	426.2
80°	373.7	369.2	368.0	364.3	363.4	360.1	359.6	357.6	358.2	356.6	357.4
82.5°	296.4	292.3	291.4	288.0	288.0	285.0	284.8	281.8	281.8	279.2	275.1
85°	208.8	205.7	204.5	201.7	200.9	198.4	197.2	194.3	193.3	191.5	190.9
87.5°	110.2	108.3	106.6	105.3	102.8	98.5	98.1	95.0	95.3	93.2	93.3
90°	48.4	44.9	43.4	40.1	38.5	35.8	34.3	35.3	36.8	37.8	39.3
92.5°	51.3	49.4	47.3	45.4	43.3	41.4	39.3	41.4	43.3	45.4	47.3
95°	58.3	56.6	54.7	52.9	51.1	49.4	47.6	49.4	51.1	53.0	54.8
97.5°	64.8	63.7	62.6	61.5	60.4	59.3	58.1	59.3	60.5	61.6	62.7
100°	74.7	73.4	72.0	70.7	69.4	68.0	66.7	68.2	69.6	70.9	72.2
102.5°	131.1	122.9	114.6	106.4	98.1	89.9	81.6	89.9	98.1	106.5	114.7
105°	315.9	288.2	260.3	232.4	204.5	176.6	148.8	176.7	204.6	232.5	260.5
107.5°	639.1	590.2	541.1	492.1	443.0	394.0	344.9	394.0	443.1	492.1	541.2
110°	949.8	907.5	865.2	822.9	780.5	738.2	695.8	738.3	780.7	823.1	865.5



TEST NUMBER: P1444808
 CATALOG NUMBER: EHBR1-24-UNV-TA-L940-UPL40

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	1117.6	1091.8	1066.0	1040.3	1014.5	988.7	962.8	988.8	1014.7	1040.6	1066.5
115°	1151.8	1138.0	1124.5	1110.7	1097.0	1083.3	1069.5	1083.5	1097.4	1111.2	1125.1
117.5°	1108.0	1103.2	1098.2	1093.3	1088.3	1083.4	1078.4	1083.6	1088.7	1093.9	1099.0
120°	1019.7	1020.1	1020.3	1020.6	1020.9	1021.1	1021.3	1021.5	1021.5	1021.5	1021.4
122.5°	923.0	926.3	929.6	932.9	936.0	939.2	942.3	939.5	936.6	933.8	930.7
125°	833.8	837.3	840.6	844.0	847.1	850.5	853.5	850.9	848.0	845.1	842.0
127.5°	757.7	760.6	763.6	766.6	769.4	772.2	774.8	772.6	770.1	767.7	765.2
130°	694.4	696.7	698.7	700.9	702.7	704.7	706.5	705.1	703.5	702.2	700.4
132.5°	647.9	649.5	651.0	652.4	653.7	655.0	656.2	655.5	654.7	653.8	652.8
135°	611.4	612.4	613.1	614.1	614.8	615.5	615.9	616.0	615.7	615.5	615.1
137.5°	580.9	581.2	581.4	581.5	581.6	581.5	581.4	582.1	582.6	583.2	583.4
140°	560.1	560.5	560.7	560.9	561.0	561.0	560.9	561.6	562.1	562.4	562.7
142.5°	539.1	539.4	539.6	539.9	539.9	540.0	539.8	540.4	540.9	541.3	541.7
145°	523.4	523.4	523.3	523.3	523.1	522.9	522.5	523.5	524.1	524.8	525.4
147.5°	508.0	508.1	507.8	507.7	507.6	507.4	507.0	507.8	508.5	509.1	509.8
150°	495.8	496.3	496.5	496.8	497.0	497.1	497.1	497.6	498.0	498.2	498.3
152.5°	484.2	484.5	484.7	484.9	485.2	485.2	485.3	485.7	486.2	486.5	486.7
155°	473.1	473.6	474.0	474.5	474.8	475.1	475.4	475.7	476.0	476.1	476.3
157.5°	463.6	464.1	464.4	464.9	465.2	465.6	465.9	466.3	466.6	466.8	466.9
160°	456.2	456.8	457.1	457.5	457.9	458.3	458.6	458.9	459.2	459.4	459.7
162.5°	451.2	451.7	451.8	452.3	452.7	453.1	453.3	453.7	454.0	454.3	454.5
165°	444.7	445.3	445.9	446.5	447.1	447.7	448.1	448.3	448.2	448.3	448.3
167.5°	443.6	444.2	444.7	445.3	445.7	446.4	446.8	446.9	446.9	446.9	446.8
170°	441.9	442.4	442.9	443.5	443.9	444.5	444.9	444.9	444.8	444.9	444.8
172.5°	440.3	441.0	441.7	442.4	442.9	443.6	444.2	444.1	443.7	443.6	443.1
175°	439.7	440.4	440.9	441.6	442.0	442.6	443.3	442.8	442.6	442.3	442.0
177.5°	443.4	444.2	445.0	445.6	446.4	447.0	447.7	447.1	446.5	445.9	445.2
180°	439.9	439.9	439.9	439.9	439.9	439.9	439.9	439.9	439.9	439.9	439.9



TEST NUMBER: P1444808
 CATALOG NUMBER: EHBR1-24-UNV-TA-L940-UPL40

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6
2.5°	19861.5	19871.4	19886.6	19900.4	19921.1	19937.5	19962.1	19980.7	20008.4	20026.5	20056.6
5°	19863.2	19902.1	19953.2	20003.1	20063.0	20117.4	20185.0	20242.7	20310.6	20366.1	20435.6
7.5°	19891.3	19966.3	20056.1	20146.6	20248.9	20344.6	20452.5	20550.1	20656.9	20747.2	20845.9
10°	19912.1	20027.6	20160.0	20293.2	20433.4	20563.6	20695.1	20808.8	20915.0	21002.4	21079.5
12.5°	19883.9	20043.1	20213.0	20377.0	20532.9	20667.7	20780.8	20868.2	20928.6	20969.5	20979.1
15°	19788.4	19980.1	20164.7	20328.0	20457.4	20557.2	20608.8	20633.0	20607.1	20563.9	20469.3
17.5°	19610.0	19812.1	19977.3	20106.1	20174.4	20201.5	20158.8	20084.3	19938.9	19777.4	19544.3
20°	19283.0	19471.3	19591.0	19661.4	19643.0	19575.4	19413.9	19217.6	18927.2	18617.8	18209.5
22.5°	18709.3	18873.9	18937.7	18943.0	18831.4	18662.1	18370.7	18034.0	17576.0	17099.8	16514.2
25°	17848.2	17992.3	18002.5	17945.8	17741.6	17467.2	17039.4	16563.2	15940.7	15306.2	14572.3
27.5°	16680.3	16818.6	16784.7	16679.1	16395.6	16028.4	15480.8	14865.4	14098.1	13348.7	12536.9
30°	15212.3	15360.1	15320.4	15184.8	14847.6	14413.7	13769.3	13054.3	12202.4	11401.9	10579.3
32.5°	13455.4	13642.4	13614.9	13486.0	13134.2	12669.7	11970.5	11212.3	10340.7	9551.9	8751.7
35°	11458.5	11685.4	11697.2	11613.0	11286.3	10827.3	10136.9	9402.9	8568.1	7823.8	7084.5
37.5°	9307.0	9570.1	9624.3	9601.5	9330.8	8925.5	8296.5	7638.1	6898.5	6246.2	5614.0
40°	7143.7	7410.0	7502.4	7529.9	7330.1	7016.2	6500.0	5968.6	5365.6	4837.0	4335.0
42.5°	5170.8	5407.0	5496.2	5552.4	5427.8	5218.4	4841.9	4456.0	4014.2	3633.0	3267.5
45°	3591.2	3758.3	3826.2	3882.7	3814.8	3696.8	3458.9	3217.5	2926.0	2676.9	2441.0
47.5°	2510.9	2602.9	2647.8	2675.2	2648.9	2587.4	2457.9	2318.1	2153.5	2007.9	1867.9
50°	1861.1	1910.2	1933.5	1949.4	1930.3	1896.0	1825.9	1749.8	1659.4	1577.0	1496.4
52.5°	1474.9	1502.9	1516.9	1525.5	1514.5	1493.5	1452.7	1407.6	1353.4	1302.4	1275.7
55°	1242.4	1241.0	1273.3	1257.7	1273.3	1238.5	1231.2	1181.6	1136.6	1104.8	1070.6
57.5°	1024.6	1039.3	1045.4	1052.4	1047.8	1041.5	1024.2	1006.5	982.7	962.9	941.7
60°	886.9	898.9	905.7	912.6	912.2	909.8	899.8	889.2	874.3	862.4	849.7
62.5°	792.1	802.5	809.2	815.7	816.4	815.4	807.8	800.5	790.3	782.9	774.0
65°	717.5	724.8	729.4	734.6	734.3	732.9	726.0	719.9	711.6	706.4	699.9
67.5°	639.4	644.9	648.4	653.4	654.4	654.7	650.8	648.1	644.0	642.5	640.2
70°	583.9	590.6	596.3	602.5	605.9	607.5	605.9	604.5	602.0	601.0	599.3
72.5°	541.8	547.5	551.9	557.6	560.8	563.1	561.8	561.0	558.9	558.6	557.5
75°	489.6	493.5	496.0	500.3	502.0	504.1	503.2	503.6	503.0	504.7	504.6
77.5°	426.9	429.8	430.9	434.0	434.3	436.8	437.5	440.5	442.6	447.4	449.9
80°	356.2	358.0	358.0	361.2	362.6	367.0	369.0	374.0	376.3	380.5	380.9
82.5°	276.7	274.6	276.7	275.4	279.4	284.3	285.0	289.2	290.1	292.8	290.7
85°	189.1	189.0	187.4	187.6	186.3	187.0	186.2	187.0	186.3	186.3	184.5
87.5°	90.6	91.5	89.4	90.1	88.2	89.1	87.4	88.7	86.7	87.0	84.0
90°	40.6	42.0	43.2	44.7	46.5	50.3	54.2	58.0	62.2	66.1	70.2
92.5°	49.4	51.4	53.5	55.4	57.5	63.5	69.5	75.6	81.7	87.6	93.6
95°	56.6	58.4	60.2	62.1	63.9	72.6	81.3	90.0	98.8	107.4	116.2
97.5°	63.9	65.0	66.1	67.3	68.5	78.7	89.0	99.2	109.5	119.8	130.0
100°	73.7	75.0	76.3	77.7	79.0	102.7	126.3	149.9	173.6	197.2	220.9
102.5°	123.1	131.3	139.6	147.9	156.1	213.4	270.8	328.1	385.3	442.7	499.9
105°	288.3	316.2	344.2	372.1	400.0	486.7	573.5	660.3	747.0	833.6	920.5
107.5°	590.4	639.5	688.6	737.7	786.8	868.4	949.9	1031.5	1113.1	1194.7	1276.1
110°	907.9	950.2	992.7	1035.1	1077.4	1142.3	1207.1	1271.9	1336.7	1401.5	1466.2



TEST NUMBER: P1444808
 CATALOG NUMBER: EHBR1-24-UNV-TA-L940-UPL40

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	1092.4	1118.3	1144.1	1169.8	1195.7	1243.3	1291.1	1338.6	1386.2	1433.7	1481.3
115°	1138.8	1152.5	1166.3	1180.0	1193.8	1222.6	1251.5	1280.4	1309.1	1337.9	1366.7
117.5°	1104.1	1109.1	1114.2	1119.0	1124.0	1139.0	1153.9	1168.8	1183.8	1198.7	1213.7
120°	1021.3	1021.1	1020.9	1020.6	1020.4	1025.2	1030.2	1035.0	1039.8	1044.6	1049.3
122.5°	927.7	924.5	921.5	918.3	915.2	913.9	912.6	911.3	910.2	908.9	907.7
125°	838.9	835.7	832.6	829.4	826.1	822.4	818.6	814.8	811.1	807.4	803.5
127.5°	762.6	759.8	757.1	754.2	751.4	747.0	742.9	738.5	734.3	730.0	725.8
130°	698.6	696.7	695.0	692.8	690.9	687.1	683.6	679.9	676.3	672.6	669.0
132.5°	651.7	650.5	649.3	647.9	646.6	643.2	640.1	636.9	633.7	630.4	627.3
135°	614.7	614.0	613.6	612.8	612.2	609.8	607.5	605.2	602.9	600.5	598.2
137.5°	583.7	583.7	583.8	583.8	583.8	581.9	580.0	578.2	576.3	574.5	572.6
140°	563.0	563.1	563.2	563.2	563.2	561.1	559.1	557.1	555.1	552.9	551.0
142.5°	541.8	542.0	542.1	542.1	542.2	540.6	539.2	537.7	536.1	534.6	533.2
145°	525.8	526.2	526.7	526.8	527.3	525.3	523.5	521.4	519.7	517.7	515.9
147.5°	510.4	510.8	511.3	511.7	512.1	510.4	509.0	507.3	505.8	504.0	502.6
150°	498.6	498.7	498.8	498.9	498.9	497.1	495.4	493.8	492.1	490.2	488.6
152.5°	487.0	487.2	487.3	487.5	487.7	485.9	484.1	482.1	480.3	478.3	476.4
155°	476.4	476.4	476.5	476.5	476.5	474.8	473.0	471.1	469.4	467.5	465.7
157.5°	467.1	467.2	467.4	467.5	467.6	466.0	464.4	462.9	461.4	459.7	458.1
160°	459.9	460.0	460.2	460.3	460.4	459.1	457.9	456.4	455.3	453.7	452.3
162.5°	454.7	454.9	455.1	455.2	455.3	454.0	452.8	451.5	450.2	448.6	447.3
165°	448.4	448.2	448.2	448.0	447.9	447.0	446.3	445.3	444.5	443.5	442.6
167.5°	446.9	446.7	446.7	446.5	446.4	445.8	445.4	444.7	444.0	443.3	442.6
170°	444.8	444.6	444.6	444.4	444.3	443.6	443.1	442.4	442.0	441.0	440.4
172.5°	442.9	442.5	442.3	442.0	441.6	441.1	440.7	440.3	439.9	439.5	439.0
175°	441.6	441.2	440.9	440.6	440.2	440.1	439.8	439.7	439.5	439.3	439.0
177.5°	444.7	444.1	443.4	442.8	442.3	442.1	441.9	441.7	441.6	441.3	441.1
180°	439.9	439.9	439.9	439.9	439.9	439.9	439.9	439.9	439.9	439.9	439.9



TEST NUMBER: P1444808
 CATALOG NUMBER: EHBR1-24-UNV-TA-L940-UPL40

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6
2.5°	20075.3	19951.3	19934.9	19943.6	19964.3	19972.0	19994.3	20000.5	20022.9	20028.5	20050.1
5°	20489.5	20325.6	20333.8	20373.2	20432.9	20468.4	20527.0	20557.7	20613.7	20639.1	20689.7
7.5°	20926.3	20797.6	20837.7	20904.2	20985.7	21042.2	21112.7	21158.5	21219.3	21256.9	21305.5
10°	21140.7	21105.5	21149.7	21201.9	21248.5	21284.9	21314.7	21338.7	21354.3	21369.0	21375.4
12.5°	20977.6	21032.1	21039.6	21034.5	21003.8	20980.2	20927.3	20891.4	20827.6	20788.7	20712.9
15°	20372.5	20492.5	20426.0	20325.4	20178.2	20055.5	19882.2	19753.2	19572.8	19450.3	19269.2
17.5°	19310.7	19462.2	19289.1	19056.3	18760.2	18506.9	18191.5	17941.1	17627.5	17399.3	17106.7
20°	17816.0	17957.5	17648.7	17262.8	16804.8	16419.3	15964.8	15602.1	15179.7	14865.4	14486.3
22.5°	15954.8	16055.6	15620.6	15100.5	14516.9	14035.3	13491.8	13057.0	12574.9	12215.7	11811.3
25°	13895.8	13923.0	13401.2	12801.9	12151.5	11610.4	11030.0	10572.9	10081.2	9717.2	9320.4
27.5°	11817.6	11777.7	11213.7	10578.3	9894.2	9331.6	8765.7	8337.3	7906.7	7578.8	7236.8
30°	9856.1	9759.5	9173.8	8520.7	7856.7	7352.5	6882.6	6538.6	6196.1	5935.9	5661.4
32.5°	8057.3	7921.0	7351.0	6739.2	6179.5	5790.5	5442.0	5181.7	4905.1	4685.3	4455.0
35°	6464.1	6318.9	5813.9	5295.2	4871.7	4584.8	4311.0	4097.5	3862.6	3677.1	3477.2
37.5°	5096.8	4977.8	4554.7	4146.6	3826.2	3603.9	3379.5	3205.0	3010.9	2929.4	2715.7
40°	3934.7	3851.5	3520.8	3219.9	2979.3	2874.9	2647.2	2484.0	2339.0	2219.4	2103.6
42.5°	3069.1	3039.7	2717.8	2483.1	2313.7	2182.2	2055.2	1952.3	1851.9	1769.5	1691.6
45°	2252.3	2229.0	2086.0	1950.6	1835.2	1743.2	1657.5	1586.6	1521.0	1466.7	1417.2
47.5°	1753.8	1746.4	1664.1	1580.1	1507.4	1448.3	1392.6	1345.6	1302.1	1265.8	1254.0
50°	1426.4	1425.5	1377.3	1325.4	1273.6	1239.5	1203.9	1176.1	1148.2	1126.5	1103.4
52.5°	1212.1	1206.8	1174.2	1142.2	1111.5	1089.0	1066.3	1048.6	1030.0	1016.6	1002.3
55°	1043.4	1048.9	1030.1	1011.0	991.7	977.8	961.9	950.2	937.4	928.9	920.4
57.5°	926.3	933.6	923.7	912.9	901.2	892.1	881.1	873.0	864.5	859.1	854.0
60°	841.2	849.1	845.1	839.7	832.4	827.0	820.0	815.5	810.1	807.0	804.2
62.5°	768.9	778.9	777.5	774.8	770.2	767.2	763.4	761.3	757.7	756.4	755.1
65°	696.8	708.0	707.8	706.5	704.0	703.0	700.7	700.2	698.4	699.1	699.0
67.5°	640.0	649.8	652.0	653.5	653.4	654.0	653.7	654.8	654.8	656.2	657.0
70°	599.1	605.9	607.5	609.1	609.6	610.9	610.9	611.7	611.5	612.7	612.8
72.5°	557.8	566.6	568.3	569.6	569.6	570.9	570.2	570.0	568.2	567.8	566.6
75°	506.3	517.7	520.2	521.8	522.1	523.1	521.6	520.7	517.7	516.5	514.5
77.5°	452.5	464.4	466.2	466.8	465.8	466.0	462.7	460.5	456.8	455.2	453.2
80°	382.5	400.0	401.4	400.3	397.5	397.2	394.0	391.9	387.4	385.9	384.1
82.5°	291.0	311.5	314.4	315.7	313.5	314.1	311.0	309.8	305.7	304.9	302.2
85°	183.8	204.3	207.7	207.2	205.0	204.4	202.6	203.3	202.9	203.9	204.6
87.5°	84.4	104.3	109.1	107.5	107.3	105.9	102.8	103.9	105.8	107.0	107.1
90°	74.1	83.9	87.8	84.9	79.9	76.8	72.1	69.2	64.9	62.0	57.7
92.5°	99.7	105.6	111.7	106.3	101.0	95.6	90.3	84.8	79.6	74.1	68.8
95°	124.8	133.4	142.1	134.9	127.7	120.6	113.4	106.3	99.1	92.0	84.9
97.5°	140.2	150.4	160.5	153.3	146.3	139.0	131.8	124.7	117.6	110.3	103.2
100°	244.5	267.8	291.4	271.1	250.7	230.5	210.2	189.8	169.5	149.2	128.8
102.5°	557.1	614.3	671.4	620.0	568.7	517.3	466.0	414.7	363.3	311.8	260.6
105°	1007.0	1093.6	1180.1	1101.7	1023.2	944.9	866.4	788.1	709.7	631.3	552.9
107.5°	1357.7	1438.7	1520.1	1449.2	1378.4	1307.6	1236.7	1166.0	1095.1	1024.3	953.4
110°	1531.1	1595.1	1659.7	1612.1	1564.7	1517.1	1469.7	1422.2	1374.7	1327.3	1280.0



TEST NUMBER: P1444808
 CATALOG NUMBER: EHBR1-24-UNV-TA-L940-UPL40

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	1528.7	1575.5	1622.7	1594.9	1567.3	1539.5	1512.0	1484.1	1456.6	1428.9	1401.4
115°	1395.3	1423.2	1451.6	1440.6	1429.9	1419.0	1408.2	1397.5	1386.7	1375.9	1365.2
117.5°	1228.5	1242.1	1256.6	1254.8	1253.1	1251.2	1249.5	1247.7	1246.1	1244.4	1242.7
120°	1054.2	1057.5	1061.9	1063.6	1065.3	1067.0	1068.8	1070.6	1072.3	1074.1	1076.0
122.5°	906.3	903.5	901.7	903.3	905.0	906.6	908.3	909.8	911.6	913.3	915.1
125°	799.7	794.3	789.9	788.4	787.0	785.4	783.8	782.2	780.8	779.3	777.9
127.5°	721.5	715.4	710.7	706.7	702.6	698.5	694.4	690.4	686.5	682.4	678.6
130°	665.4	659.9	655.7	650.5	645.4	640.1	635.0	629.9	624.7	619.5	614.4
132.5°	624.0	618.8	615.1	610.1	605.3	600.3	595.4	590.4	585.4	580.4	575.6
135°	595.9	591.4	588.6	584.0	579.9	575.3	570.8	566.3	561.9	557.3	553.0
137.5°	570.7	566.5	564.2	560.7	557.3	553.8	550.3	546.6	543.1	539.4	536.1
140°	548.9	544.5	541.9	540.1	538.3	536.3	534.5	532.5	530.7	528.8	526.8
142.5°	531.6	527.5	525.4	524.3	523.3	522.1	521.1	520.0	518.8	517.4	516.3
145°	514.0	509.3	506.8	506.8	507.1	507.1	507.2	507.3	507.4	507.3	507.4
147.5°	500.9	496.2	494.0	494.3	494.8	495.2	495.7	496.0	496.5	496.8	497.3
150°	486.8	481.5	478.8	479.5	480.2	480.9	481.7	482.3	483.1	483.8	484.5
152.5°	474.5	468.2	465.2	465.9	466.8	467.5	468.2	469.1	469.9	470.9	471.6
155°	463.7	457.0	453.8	454.1	454.5	454.7	455.1	455.6	456.0	456.4	457.0
157.5°	456.4	449.5	446.5	446.4	446.6	446.7	447.0	447.2	447.5	447.7	448.0
160°	451.0	444.2	441.4	441.3	441.5	441.6	441.7	441.8	442.1	442.3	442.6
162.5°	445.9	439.2	436.5	436.4	436.5	436.5	436.6	436.7	436.8	436.9	437.3
165°	441.6	436.0	433.7	433.9	434.1	434.3	434.6	435.0	435.4	435.6	436.1
167.5°	441.8	436.8	435.2	434.9	434.7	434.4	434.4	434.1	434.1	434.1	434.1
170°	439.6	435.7	434.1	434.1	434.4	434.4	434.4	434.7	434.8	434.8	435.1
172.5°	438.5	435.6	434.4	434.9	435.4	435.6	436.1	436.5	436.9	437.3	437.8
175°	438.8	437.0	436.6	436.6	436.8	437.0	437.3	437.5	437.8	438.0	438.4
177.5°	441.0	440.4	440.0	440.0	440.0	440.0	440.0	440.0	440.0	440.1	440.1
180°	439.9	439.9	439.9	439.9	439.9	439.9	439.9	439.9	439.9	439.9	439.9



TEST NUMBER: P1444808
 CATALOG NUMBER: EHBR1-24-UNV-TA-L940-UPL40

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6
2.5°	20054.1	20077.5	20075.8	20097.6	20096.5	20117.0	20112.9	20130.7	20126.6	20141.8	20133.0
5°	20712.0	20756.4	20771.1	20811.3	20819.6	20855.4	20856.2	20884.8	20881.3	20903.6	20891.8
7.5°	21334.2	21375.8	21395.4	21426.6	21442.2	21468.0	21478.2	21499.4	21504.4	21517.0	21516.6
10°	21386.8	21386.6	21396.4	21392.0	21400.7	21395.7	21406.3	21402.5	21418.2	21414.2	21426.0
12.5°	20680.1	20610.0	20584.4	20521.5	20507.7	20453.5	20457.4	20422.8	20439.5	20418.1	20454.5
15°	19161.4	18998.8	18918.4	18776.9	18732.5	18620.7	18611.7	18537.4	18557.4	18518.6	18575.4
17.5°	16917.3	16661.2	16520.6	16314.0	16232.1	16073.9	16042.2	15946.6	15961.4	15913.3	15981.8
20°	14241.6	13932.1	13754.8	13515.9	13409.4	13220.9	13170.9	13063.9	13077.3	13029.4	13107.0
22.5°	11535.4	11211.4	11011.3	10760.9	10624.9	10447.6	10394.4	10287.0	10293.0	10248.1	10322.7
25°	9048.5	8737.9	8543.7	8316.1	8198.1	8035.6	7979.7	7883.2	7888.7	7851.6	7918.5
27.5°	6999.6	6744.8	6582.3	6391.6	6285.8	6152.2	6097.7	6016.6	6016.3	5989.1	6045.1
30°	5469.9	5257.2	5111.2	4945.3	4845.9	4725.2	4672.6	4600.0	4596.8	4577.5	4622.0
32.5°	4282.8	4093.7	3960.5	3814.4	3725.2	3621.7	3571.8	3513.5	3508.2	3490.7	3527.2
35°	3329.3	3170.0	3055.5	2932.5	2941.6	2789.0	2814.3	2695.7	2663.6	2656.6	2683.7
37.5°	2573.2	2449.8	2356.8	2264.6	2202.3	2137.8	2103.0	2071.8	2068.3	2065.3	2084.3
40°	2014.1	1927.8	1860.1	1797.0	1754.0	1714.6	1692.9	1675.8	1671.7	1669.4	1680.9
42.5°	1630.1	1571.9	1528.3	1489.7	1463.6	1442.2	1430.3	1420.8	1417.6	1417.6	1424.4
45°	1377.3	1341.8	1313.8	1289.9	1273.2	1280.5	1258.9	1270.2	1255.3	1270.8	1260.5
47.5°	1212.8	1182.7	1165.3	1148.3	1138.3	1130.2	1130.5	1130.6	1133.8	1134.3	1137.6
50°	1086.0	1068.6	1056.5	1045.7	1040.5	1036.2	1037.6	1038.7	1041.9	1042.0	1044.5
52.5°	992.1	980.7	973.4	966.7	964.3	961.9	962.9	962.5	963.9	963.1	965.1
55°	915.7	910.3	908.1	905.6	905.9	905.3	905.7	903.2	901.7	900.0	901.6
57.5°	853.0	852.3	853.9	854.9	857.8	858.8	859.4	856.6	853.9	851.5	852.9
60°	804.8	805.9	809.7	812.9	817.0	818.9	820.0	818.5	816.5	814.5	815.7
62.5°	757.1	758.9	763.5	766.9	772.0	774.6	777.5	777.6	778.3	777.6	778.4
65°	701.8	704.0	708.1	711.0	715.7	718.0	720.9	721.5	723.1	722.7	724.1
67.5°	659.7	661.8	665.3	668.0	672.1	674.5	677.0	677.2	677.8	677.7	679.0
70°	614.9	615.9	619.0	621.3	625.4	627.8	630.8	631.7	633.5	633.9	635.3
72.5°	567.1	566.6	568.5	569.5	572.7	574.5	578.4	580.4	583.5	584.3	585.4
75°	515.0	514.6	516.8	517.7	520.3	522.3	526.5	529.2	534.0	536.0	535.5
77.5°	454.8	455.9	460.0	462.3	465.8	468.2	473.6	478.0	486.8	490.6	486.7
80°	387.4	388.5	392.8	394.9	399.6	402.5	408.6	413.7	421.6	423.3	421.1
82.5°	304.6	304.8	308.7	310.3	316.4	320.8	328.5	332.5	337.3	336.7	336.0
85°	207.7	210.5	215.3	220.1	227.4	234.5	241.9	247.8	243.6	250.3	242.8
87.5°	111.0	110.7	117.2	116.2	126.5	132.5	138.8	141.8	145.2	144.5	144.6
90°	55.1	52.3	51.2	48.3	47.7	44.6	44.6	41.6	42.0	38.7	43.3
92.5°	63.4	60.6	57.6	54.8	51.8	48.9	45.9	43.0	40.2	37.3	40.2
95°	77.7	75.0	72.4	69.6	66.9	64.3	61.6	58.9	56.3	53.6	56.9
97.5°	96.1	94.5	92.9	91.4	89.8	88.2	86.6	85.2	83.6	82.0	84.2
100°	108.5	108.5	108.5	108.5	108.4	108.4	108.4	108.4	108.4	108.4	110.2
102.5°	209.2	204.0	198.9	193.8	188.7	183.4	178.3	173.2	168.1	162.9	170.5
105°	474.6	454.5	434.3	414.3	394.2	374.1	354.0	334.0	313.9	293.8	314.6
107.5°	882.7	846.0	809.4	772.8	736.1	699.6	663.0	626.3	589.8	553.2	586.0
110°	1232.5	1193.6	1154.8	1115.9	1077.1	1038.1	999.4	960.5	921.8	882.9	914.1



TEST NUMBER: P1444808
 CATALOG NUMBER: EHBR1-24-UNV-TA-L940-UPL40

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	1373.7	1348.6	1323.5	1298.4	1273.4	1248.3	1223.3	1198.4	1173.4	1148.4	1163.6
115°	1354.4	1342.5	1330.6	1318.7	1306.7	1294.9	1283.0	1271.1	1259.3	1247.5	1248.4
117.5°	1241.1	1237.1	1233.1	1229.2	1225.3	1221.4	1217.5	1213.7	1209.9	1206.1	1197.6
120°	1077.9	1079.2	1080.5	1081.8	1083.3	1084.8	1086.1	1087.6	1089.2	1090.8	1079.4
122.5°	916.8	919.9	922.9	926.1	929.2	932.4	935.6	938.9	942.3	945.6	934.3
125°	776.4	779.4	782.4	785.5	788.5	791.7	794.9	798.2	801.5	804.9	795.3
127.5°	674.6	675.8	676.8	678.1	679.3	680.7	682.2	683.5	685.1	686.8	680.8
130°	609.3	608.4	607.4	606.7	605.8	605.1	604.5	604.0	603.4	603.1	600.4
132.5°	570.6	568.4	566.1	563.7	561.6	559.6	557.6	555.7	553.9	552.2	551.3
135°	548.4	545.2	541.9	539.0	535.8	532.9	529.9	527.3	524.5	521.9	522.3
137.5°	532.5	529.4	526.1	523.0	520.0	517.2	514.2	511.4	508.8	506.2	507.0
140°	524.9	521.6	518.5	515.5	512.5	509.5	506.6	504.0	501.1	498.7	499.3
142.5°	515.2	512.5	509.4	506.7	503.9	501.2	498.7	496.3	493.6	491.3	492.0
145°	507.5	505.3	503.2	501.0	499.1	497.2	495.2	493.4	491.6	490.0	490.3
147.5°	497.6	496.1	494.3	492.9	491.3	489.9	488.5	487.3	485.9	484.6	484.7
150°	485.2	484.2	483.2	482.1	481.2	480.3	479.3	478.5	477.7	476.8	476.7
152.5°	472.4	471.5	470.5	469.5	468.7	467.8	466.9	466.2	465.5	464.6	464.5
155°	457.4	457.0	456.5	456.2	455.8	455.5	455.0	454.9	454.5	454.3	454.4
157.5°	448.2	448.2	447.9	447.9	447.7	447.7	447.5	447.7	447.4	447.6	447.7
160°	443.0	442.6	442.3	442.1	441.8	441.4	441.2	441.0	440.9	440.6	440.9
162.5°	437.5	437.7	437.8	438.0	438.2	438.3	438.5	438.8	439.0	439.3	439.5
165°	436.6	436.5	436.3	436.2	436.2	436.1	436.0	436.1	436.0	436.1	436.5
167.5°	434.0	434.2	434.4	434.7	434.9	435.4	435.6	436.0	436.5	436.9	437.3
170°	435.2	435.2	435.2	435.2	435.2	435.3	435.4	435.5	435.5	435.7	436.0
172.5°	438.2	438.2	438.1	438.2	438.1	438.2	438.2	438.2	438.2	438.3	438.5
175°	438.4	438.8	439.1	439.3	439.5	439.7	439.9	440.1	440.4	440.6	440.6
177.5°	440.1	440.2	440.2	440.2	440.2	440.3	440.3	440.3	440.3	440.2	440.4
180°	439.9	439.9	439.9	439.9	439.9	439.9	439.9	439.9	439.9	439.9	439.9



TEST NUMBER: P1444808
 CATALOG NUMBER: EHBR1-24-UNV-TA-L940-UPL40

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6
2.5°	20147.8	20137.6	20148.0	20137.5	20148.0	20135.5	20143.9	20130.3	20133.8	20119.7	20123.4
5°	20909.6	20893.5	20902.0	20881.2	20883.4	20855.4	20855.0	20822.6	20814.0	20777.0	20760.8
7.5°	21525.6	21520.4	21523.2	21509.8	21508.3	21489.2	21480.2	21453.4	21436.5	21402.5	21379.2
10°	21428.0	21443.8	21447.8	21463.8	21467.2	21483.0	21486.4	21502.2	21505.5	21517.2	21517.4
12.5°	20452.8	20506.1	20518.8	20584.7	20612.4	20687.7	20728.2	20811.3	20860.6	20943.4	20994.3
15°	18573.8	18666.1	18702.9	18831.5	18902.7	19052.8	19147.2	19319.5	19441.2	19624.4	19755.0
17.5°	15987.9	16116.8	16175.0	16349.4	16463.2	16684.8	16844.5	17107.4	17308.8	17600.9	17832.4
20°	13120.3	13263.6	13342.6	13541.6	13675.8	13934.7	14134.2	14457.2	14726.6	15096.9	15413.4
22.5°	10346.1	10482.4	10570.1	10772.5	10923.7	11193.8	11416.7	11757.6	12059.5	12476.7	12856.2
25°	7943.9	8068.8	8148.1	8331.1	8473.1	8721.3	8934.1	9262.0	9557.4	9975.9	10365.1
27.5°	6072.9	6177.6	6254.0	6410.1	6535.4	6745.9	6928.6	7199.7	7454.2	7816.2	8162.8
30°	4649.4	4742.2	4816.5	4952.4	5068.5	5250.9	5411.7	5639.4	5850.0	6138.1	6413.8
32.5°	3552.9	3632.8	3699.0	3818.0	3923.3	4087.6	4232.5	4432.0	4612.8	4857.1	5084.0
35°	2708.9	2866.1	2854.9	3019.1	3045.5	3163.4	3292.6	3467.1	3627.3	3834.9	4028.1
37.5°	2102.6	2146.8	2194.1	2266.7	2342.9	2450.2	2559.4	2772.6	2850.7	3007.7	3167.6
40°	1695.5	1725.4	1756.6	1805.7	1859.1	1934.7	2014.1	2115.9	2220.1	2347.4	2477.3
42.5°	1433.4	1450.3	1470.2	1499.0	1531.9	1579.9	1633.1	1702.0	1774.5	1864.1	1955.5
45°	1280.6	1272.6	1278.6	1294.1	1313.9	1343.0	1376.6	1419.3	1466.4	1524.5	1586.3
47.5°	1138.3	1141.5	1143.3	1151.7	1162.3	1181.9	1202.2	1231.2	1287.2	1304.2	1337.9
50°	1044.3	1045.8	1045.3	1049.6	1054.9	1067.7	1080.8	1100.5	1120.0	1146.0	1170.8
52.5°	965.5	967.6	967.3	970.1	973.0	981.0	989.4	1003.3	1016.1	1032.6	1046.8
55°	903.1	906.2	907.4	909.8	911.1	915.3	918.7	925.3	930.7	940.1	948.8
57.5°	855.3	859.4	861.4	862.1	860.5	860.3	859.2	860.6	861.7	866.7	871.6
60°	817.6	821.0	821.4	821.0	817.9	815.7	812.1	811.0	810.4	812.9	815.5
62.5°	778.2	779.3	778.6	777.6	774.0	771.9	768.2	766.9	765.6	767.3	768.7
65°	723.6	724.6	723.6	723.1	719.9	718.1	715.0	714.0	712.2	712.7	712.4
67.5°	679.3	680.3	679.5	678.7	676.5	675.4	673.1	671.7	669.6	668.7	667.2
70°	635.1	635.9	634.6	633.9	631.4	630.4	628.2	627.8	626.1	625.8	624.0
72.5°	584.3	584.3	582.6	582.1	580.2	580.1	579.3	580.1	580.0	580.9	580.5
75°	532.3	531.6	529.4	529.0	527.6	528.2	527.3	528.5	528.7	530.6	530.9
77.5°	480.3	477.5	473.3	471.3	468.5	468.2	466.6	467.6	467.2	469.5	470.4
80°	414.5	411.1	405.7	403.2	399.9	399.3	397.9	399.3	398.6	401.2	403.0
82.5°	330.9	328.0	322.4	320.4	316.5	316.9	315.3	316.9	316.7	320.5	322.7
85°	244.7	242.9	237.1	232.0	226.3	223.0	219.8	219.2	218.2	219.8	221.1
87.5°	141.3	139.6	135.1	132.2	122.2	122.6	118.7	118.5	117.6	116.6	118.7
90°	44.2	48.3	49.3	53.2	54.5	58.8	60.3	64.5	66.0	70.5	72.5
92.5°	43.0	45.9	48.8	51.8	54.7	57.6	60.5	63.4	69.6	75.6	82.1
95°	60.3	63.6	67.0	70.2	73.6	77.0	80.3	83.7	92.8	101.9	111.1
97.5°	86.5	88.7	90.9	93.2	95.4	97.6	99.9	102.1	111.9	121.8	131.5
100°	112.0	113.8	115.5	117.4	119.2	120.9	122.7	124.5	143.6	162.5	181.5
102.5°	178.1	185.7	193.3	200.9	208.5	216.0	223.7	231.2	274.8	318.3	361.9
105°	335.3	356.1	376.9	397.5	418.3	439.1	459.9	480.6	550.3	619.9	689.7
107.5°	618.8	651.6	684.4	717.2	750.0	782.9	815.7	848.5	916.5	984.4	1052.3
110°	945.3	976.6	1007.9	1039.3	1070.5	1101.8	1133.0	1164.4	1205.1	1245.8	1286.5



TEST NUMBER: P1444808
 CATALOG NUMBER: EHBR1-24-UNV-TA-L940-UPL40

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	1178.8	1193.9	1209.2	1224.5	1239.7	1254.9	1270.2	1285.6	1305.9	1326.1	1346.4
115°	1249.3	1250.3	1251.2	1252.2	1253.2	1254.2	1255.4	1256.4	1262.8	1269.0	1275.3
117.5°	1189.2	1180.9	1172.5	1164.2	1155.9	1147.7	1139.4	1131.3	1129.8	1128.3	1126.9
120°	1068.3	1057.0	1045.8	1034.4	1023.3	1012.1	1001.1	990.2	984.4	978.6	972.8
122.5°	923.1	911.9	900.7	889.4	878.4	867.4	856.5	845.6	841.5	837.2	833.1
125°	785.9	776.5	767.2	757.9	748.7	739.5	730.5	721.4	720.9	720.3	719.9
127.5°	675.0	669.2	663.4	657.8	652.2	646.7	641.3	635.8	637.8	639.9	641.9
130°	597.7	595.0	592.6	589.9	587.7	585.4	583.0	580.8	584.7	588.4	592.3
132.5°	550.9	550.2	549.9	549.3	549.1	548.7	548.6	548.3	552.8	557.2	561.8
135°	522.8	523.3	524.1	524.7	525.6	526.4	527.4	528.1	532.5	536.6	541.1
137.5°	508.0	509.0	510.0	511.2	512.5	513.7	515.1	516.3	519.7	523.0	526.3
140°	500.1	500.7	501.6	502.5	503.6	504.4	505.6	506.6	509.4	511.8	514.5
142.5°	492.8	493.4	494.2	495.2	496.2	496.9	498.1	498.9	500.9	502.7	504.7
145°	490.9	491.3	492.0	492.5	493.2	493.9	494.6	495.3	496.5	497.5	498.6
147.5°	485.0	485.3	485.7	485.9	486.4	486.8	487.2	487.5	488.3	488.9	489.5
150°	476.7	476.7	476.9	476.8	477.1	477.3	477.4	477.6	478.1	478.7	479.3
152.5°	464.6	464.6	464.6	464.6	464.7	464.8	464.8	465.0	465.5	466.1	466.7
155°	454.5	454.8	455.1	455.4	455.8	455.9	456.2	456.5	456.9	457.2	457.5
157.5°	447.9	448.1	448.5	448.6	449.0	449.2	449.5	449.7	450.1	450.4	450.6
160°	441.5	442.0	442.3	442.9	443.5	443.8	444.4	444.9	445.1	445.4	445.7
162.5°	439.8	440.1	440.4	440.6	440.9	441.2	441.4	441.7	442.3	442.7	443.3
165°	437.1	437.5	438.1	438.5	439.1	439.6	440.0	440.5	440.8	441.0	441.2
167.5°	437.9	438.2	438.8	439.3	439.8	440.2	440.8	441.2	441.5	441.6	442.0
170°	436.5	436.9	437.4	437.8	438.3	438.6	439.2	439.6	440.0	440.5	440.9
172.5°	438.9	439.3	439.7	439.9	440.4	440.8	441.2	441.5	441.9	442.3	442.6
175°	440.6	440.6	440.7	440.8	440.9	440.9	440.9	441.0	441.1	441.2	441.2
177.5°	440.7	440.9	441.0	441.3	441.5	441.7	442.0	442.2	442.2	442.2	442.2
180°	439.9	439.9	439.9	439.9	439.9	439.9	439.9	439.9	439.9	439.9	439.9



TEST NUMBER: P1444808
 CATALOG NUMBER: EHBR1-24-UNV-TA-L940-UPL40

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6
2.5°	20109.3	20110.1	20093.9	20093.0	20077.8	20075.9	20061.1	20056.6	20044.5	20040.3	20028.0
5°	20719.3	20699.6	20653.9	20627.1	20582.0	20552.1	20503.3	20471.4	20424.3	20388.8	20341.4
7.5°	21336.4	21305.7	21254.5	21212.9	21150.3	21100.4	21027.1	20967.1	20887.7	20819.0	20735.7
10°	21517.4	21512.6	21499.6	21480.6	21451.4	21418.7	21368.9	21316.9	21247.3	21171.8	21079.1
12.5°	21072.1	21120.1	21185.7	21224.6	21271.9	21292.6	21312.0	21307.1	21294.3	21256.1	21202.6
15°	19944.1	20079.2	20258.2	20396.8	20556.3	20672.2	20800.3	20880.0	20959.6	20996.3	21018.9
17.5°	18149.8	18405.6	18726.4	18992.2	19299.0	19545.4	19815.4	20018.7	20227.8	20377.6	20513.1
20°	15845.0	16215.7	16669.4	17070.2	17536.3	17941.3	18385.1	18749.5	19125.2	19418.9	19697.0
22.5°	13345.1	13785.3	14333.7	14841.9	15442.7	15982.7	16591.9	17122.2	17675.7	18138.3	18585.5
25°	10886.7	11369.5	11969.3	12536.2	13216.7	13844.7	14567.3	15228.1	15943.6	16564.9	17178.6
27.5°	8642.0	9116.0	9728.3	10331.8	11051.3	11720.6	12494.7	13222.8	14037.6	14788.8	15557.5
30°	6797.0	7199.0	7748.0	8332.5	9042.3	9723.3	10505.8	11254.7	12102.2	12922.6	13788.3
32.5°	5385.1	5691.3	6123.0	6617.2	7272.1	7920.3	8665.4	9388.3	10222.9	11051.6	11952.1
35°	4276.7	4515.6	4844.7	5230.4	5784.9	6343.8	7002.8	7660.2	8438.9	9225.2	10100.4
37.5°	3372.5	3566.2	3824.0	4113.8	4558.5	5017.1	5557.5	6102.6	6779.1	7476.2	8269.4
40°	2633.5	2790.5	2991.0	3207.2	3543.0	3896.4	4314.4	4737.0	5280.6	5850.3	6506.7
42.5°	2068.8	2184.6	2326.3	2484.2	2797.5	2985.2	3268.6	3574.3	3973.9	4387.5	4881.0
45°	1661.4	1740.4	1838.7	1944.6	2090.1	2249.2	2443.3	2646.8	3026.5	3212.7	3512.9
47.5°	1387.5	1440.5	1503.0	1569.7	1655.5	1748.0	1863.2	1980.9	2133.1	2290.8	2475.8
50°	1202.9	1256.9	1278.3	1312.9	1362.5	1415.4	1480.3	1545.2	1626.8	1709.6	1804.8
52.5°	1066.0	1083.6	1107.0	1128.9	1159.7	1219.8	1239.3	1273.3	1319.0	1363.8	1413.8
55°	961.5	972.8	988.1	1001.3	1019.9	1037.7	1063.4	1085.9	1116.5	1143.4	1176.7
57.5°	880.0	887.3	897.8	906.6	918.6	928.7	943.7	955.9	973.5	988.8	1008.9
60°	820.9	825.7	832.8	838.5	846.2	851.4	858.9	864.6	873.9	881.6	892.9
62.5°	772.6	775.0	779.7	783.0	787.9	790.6	794.5	797.0	802.1	806.1	812.3
65°	714.6	715.2	718.3	719.7	723.5	724.9	728.2	729.4	733.6	736.5	742.0
67.5°	667.2	665.8	665.8	664.7	665.3	664.2	664.4	663.2	665.0	665.8	670.0
70°	623.7	621.9	621.3	619.4	618.7	616.7	616.1	614.2	614.0	613.4	614.9
72.5°	581.5	581.0	581.2	579.8	579.6	578.2	578.3	577.3	578.4	578.7	580.7
75°	532.9	533.1	534.0	532.7	533.1	532.0	532.3	531.3	531.9	531.6	533.6
77.5°	473.7	475.1	477.7	477.2	478.0	476.7	477.3	475.7	476.2	475.1	475.9
80°	407.2	410.2	413.7	413.5	415.0	414.0	415.3	413.8	414.5	412.7	412.3
82.5°	328.2	330.7	334.5	334.6	337.8	338.5	342.0	341.9	344.1	342.7	341.6
85°	224.4	226.1	229.4	231.1	234.4	236.5	240.0	241.4	238.9	243.4	239.8
87.5°	117.2	121.6	119.1	124.7	123.4	129.2	127.9	133.2	132.2	136.8	136.2
90°	77.8	80.2	85.7	88.2	94.4	97.4	97.5	93.9	93.9	90.5	90.5
92.5°	88.1	94.7	100.9	107.1	113.4	119.7	113.8	108.1	102.2	96.5	90.6
95°	120.2	129.4	138.5	147.7	156.8	165.9	156.1	146.4	136.6	126.8	116.9
97.5°	141.3	151.2	161.0	170.8	180.7	190.5	178.9	167.3	155.7	144.2	132.6
100°	200.4	219.5	238.4	257.4	276.4	295.4	273.9	252.2	230.6	209.0	187.3
102.5°	405.5	449.0	492.6	536.1	579.6	623.2	577.3	531.6	485.6	439.6	393.7
105°	759.3	829.0	898.7	968.4	1038.0	1107.8	1033.4	959.0	884.5	810.2	735.7
107.5°	1120.3	1188.0	1256.1	1324.0	1392.0	1460.0	1384.5	1309.1	1233.6	1158.0	1082.6
110°	1327.3	1368.1	1408.9	1449.7	1490.4	1531.3	1476.2	1421.0	1366.0	1310.7	1255.6



TEST NUMBER: P1444808
 CATALOG NUMBER: EHBR1-24-UNV-TA-L940-UPL40

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	1366.7	1387.1	1407.3	1427.8	1448.1	1468.6	1429.1	1389.6	1350.0	1310.6	1271.0
115°	1281.8	1288.0	1294.4	1300.9	1307.1	1313.5	1286.8	1260.1	1233.4	1206.8	1179.9
117.5°	1125.5	1124.2	1122.7	1121.5	1120.0	1118.7	1103.7	1088.6	1073.5	1058.4	1043.3
120°	967.0	961.3	955.5	949.8	944.0	938.2	931.7	925.3	918.6	912.1	905.5
122.5°	829.0	824.9	820.8	816.7	812.4	808.2	805.5	803.0	800.1	797.5	794.6
125°	719.3	718.9	718.3	717.8	717.3	716.7	715.1	713.6	712.1	710.7	709.0
127.5°	643.8	645.9	647.8	649.7	651.7	653.6	653.0	652.4	651.8	651.2	650.5
130°	596.1	600.0	603.7	607.4	611.1	615.0	613.8	612.8	611.8	610.8	609.7
132.5°	566.3	570.6	575.1	579.7	583.9	588.3	587.0	585.9	584.5	583.4	582.1
135°	545.2	549.4	553.5	557.9	561.9	566.0	564.4	563.1	561.5	560.2	558.6
137.5°	529.5	533.0	536.2	539.4	542.6	545.9	544.3	542.9	541.3	540.0	538.4
140°	517.0	519.6	522.0	524.7	527.0	529.6	527.9	526.1	524.3	522.6	520.8
142.5°	506.4	508.4	510.1	511.9	513.7	515.6	513.2	510.9	508.7	506.4	504.2
145°	499.7	501.0	502.0	503.1	504.0	505.1	502.5	500.1	497.4	495.0	492.3
147.5°	490.0	490.8	491.2	491.8	492.3	492.9	490.4	488.1	485.7	483.2	480.8
150°	479.7	480.4	480.8	481.3	481.8	482.4	479.8	477.4	474.9	472.3	470.0
152.5°	467.2	467.7	468.2	468.6	469.1	469.5	467.1	465.0	462.6	460.2	457.9
155°	457.6	458.0	458.2	458.5	458.6	458.7	456.7	455.0	453.0	451.1	449.1
157.5°	450.8	451.1	451.4	451.5	451.7	451.8	450.4	449.0	447.5	446.0	444.4
160°	445.9	446.2	446.4	446.5	446.7	446.8	445.6	444.4	443.2	441.9	440.5
162.5°	443.6	444.1	444.6	445.0	445.4	445.8	444.2	442.8	441.4	439.8	438.2
165°	441.5	441.7	441.9	442.2	442.2	442.4	441.4	440.4	439.3	438.3	437.3
167.5°	442.1	442.3	442.5	442.7	442.8	443.0	442.0	441.0	439.9	438.9	437.8
170°	441.2	441.6	442.1	442.3	442.7	443.0	442.2	441.4	440.5	439.7	438.8
172.5°	443.0	443.4	443.6	443.9	444.2	444.6	443.6	442.8	442.0	441.1	440.2
175°	441.2	441.3	441.5	441.5	441.5	441.6	440.9	440.3	439.6	439.0	438.2
177.5°	442.2	442.2	442.2	442.1	442.1	442.1	441.6	441.1	440.8	440.3	439.7
180°	439.9	439.9	439.9	439.9	439.9	439.9	439.9	439.9	439.9	439.9	439.9



TEST NUMBER: P1444808
 CATALOG NUMBER: EHBR1-24-UNV-TA-L940-UPL40

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6	19898.6
2.5°	20023.7	20014.9	20009.3	20002.2	19997.8	19992.3	19988.3	19984.7	19981.9	19979.4	19977.5
5°	20305.2	20260.4	20225.7	20188.1	20157.2	20126.3	20102.6	20082.9	20069.3	20059.2	20053.1
7.5°	20663.7	20581.7	20508.9	20432.2	20363.4	20295.8	20237.6	20187.4	20149.6	20125.2	20110.4
10°	20983.8	20874.2	20765.6	20651.5	20543.3	20438.3	20341.4	20256.1	20188.6	20143.8	20117.6
12.5°	21127.3	21033.9	20923.1	20799.2	20666.5	20532.3	20401.5	20283.4	20184.4	20118.0	20079.6
15°	21000.9	20962.6	20887.4	20791.2	20665.3	20526.5	20372.9	20228.5	20095.7	20009.5	19959.6
17.5°	20589.7	20643.3	20637.5	20600.7	20510.3	20393.4	20236.9	20074.7	19908.6	19793.5	19730.6
20°	19895.9	20064.3	20149.6	20193.5	20157.9	20082.2	19940.5	19775.9	19582.2	19431.9	19340.1
22.5°	18921.0	19218.1	19403.3	19538.8	19567.5	19541.7	19416.5	19260.0	19044.1	18863.4	18727.9
25°	17665.8	18101.1	18393.8	18623.2	18712.3	18735.3	18628.8	18473.1	18232.5	18022.0	17835.9
27.5°	16187.4	16753.0	17143.8	17452.1	17591.1	17651.5	17553.5	17394.7	17110.0	16858.7	16615.6
30°	14523.1	15194.1	15664.5	16034.2	16203.7	16283.5	16179.3	16002.0	15670.8	15368.4	15062.3
32.5°	12741.6	13476.0	13988.6	14390.0	14558.1	14633.1	14496.9	14297.7	13914.8	13558.6	13201.5
35°	10876.5	11617.7	12134.7	12525.3	12666.2	12711.5	12537.2	12307.0	11882.9	11491.9	11102.6
37.5°	8973.3	9662.9	10132.8	10483.4	10570.6	10578.5	10368.6	10114.3	9668.5	9283.0	8895.4
40°	7086.7	7668.3	8047.6	8328.3	8358.5	8331.5	8103.4	7847.5	7430.4	7085.1	6744.8
42.5°	5309.5	5748.5	6019.2	6211.6	6200.1	6146.8	5937.6	5717.7	5373.5	5110.5	4842.7
45°	3787.0	4076.5	4234.8	4347.3	4311.2	4260.3	4097.5	3943.4	3709.5	3539.6	3359.7
47.5°	2630.9	2976.6	2916.4	3136.5	2946.9	3072.1	2811.3	2667.6	2543.5	2453.2	2351.5
50°	1883.5	1962.7	2001.0	2027.1	2013.2	1994.0	1947.1	1905.2	1848.6	1807.2	1759.0
52.5°	1454.6	1494.2	1515.9	1531.5	1528.5	1521.5	1501.1	1482.3	1455.8	1438.4	1417.2
55°	1232.1	1232.7	1272.5	1255.5	1280.7	1251.1	1262.8	1230.0	1235.3	1207.0	1188.1
57.5°	1023.8	1040.1	1047.4	1054.4	1052.5	1051.2	1043.3	1039.3	1030.4	1027.7	1021.4
60°	900.6	909.1	910.9	914.1	911.3	910.3	904.2	901.9	896.0	894.8	890.7
62.5°	816.1	820.4	820.4	820.4	816.9	813.5	806.6	803.0	798.0	796.8	794.4
65°	745.6	750.1	750.8	751.7	749.2	746.5	740.5	736.6	731.3	729.4	726.6
67.5°	672.8	677.6	679.2	681.7	680.2	679.6	675.5	674.0	670.5	669.7	667.2
70°	615.6	617.6	617.5	617.4	614.1	611.3	606.5	604.2	600.6	599.9	597.5
72.5°	581.6	583.0	582.2	580.9	576.7	572.4	566.8	562.7	558.0	555.0	551.7
75°	533.7	535.6	534.5	533.6	529.8	527.0	522.6	520.3	517.0	516.0	513.7
77.5°	475.0	475.9	473.9	473.7	470.9	469.1	465.7	465.1	462.7	462.7	460.5
80°	409.6	409.1	406.0	405.4	402.5	401.7	399.1	399.3	397.3	398.2	396.6
82.5°	337.0	335.2	331.1	330.0	326.6	326.4	324.6	326.1	324.9	326.6	325.6
85°	241.5	242.0	240.3	240.3	239.3	239.6	239.4	240.6	240.7	242.3	242.2
87.5°	134.6	136.6	136.2	138.0	137.9	139.9	140.6	143.5	143.8	146.6	146.6
90°	87.1	87.3	83.8	84.1	82.5	84.3	83.1	84.9	83.4	84.8	82.5
92.5°	84.9	79.0	73.3	67.5	64.6	61.5	58.9	55.6	52.9	49.8	46.9
95°	107.1	97.4	87.5	77.7	74.3	70.9	67.5	64.2	60.9	57.6	54.2
97.5°	121.0	109.4	97.8	86.2	83.3	80.4	77.4	74.5	71.6	68.7	65.8
100°	165.6	144.0	122.4	100.7	98.3	95.8	93.4	90.9	88.4	86.0	83.6
102.5°	347.9	301.9	255.9	210.0	201.3	192.6	183.9	175.1	166.4	157.7	149.1
105°	661.3	586.8	512.3	437.8	414.1	390.5	366.9	343.2	319.6	295.9	272.3
107.5°	1007.0	931.4	855.8	780.2	736.6	692.9	649.1	605.3	561.7	517.9	474.1
110°	1200.4	1145.2	1089.9	1034.6	999.6	964.3	929.0	893.8	858.7	823.4	788.1



TEST NUMBER: P1444808
 CATALOG NUMBER: EHBR1-24-UNV-TA-L940-UPL40

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	1231.5	1191.9	1152.4	1112.7	1096.8	1080.7	1064.8	1048.8	1032.7	1016.6	1000.7
115°	1153.2	1126.4	1099.6	1072.6	1067.1	1061.3	1055.6	1049.9	1044.2	1038.4	1032.6
117.5°	1028.3	1013.1	997.9	982.7	983.5	984.3	985.3	986.1	986.7	987.4	988.2
120°	898.9	892.1	885.6	879.0	883.8	888.4	893.2	897.6	902.2	906.7	911.2
122.5°	792.0	789.1	786.5	783.5	789.3	795.0	800.6	806.1	811.6	817.0	822.5
125°	707.5	705.8	704.3	702.6	708.3	714.0	719.6	725.2	730.7	736.1	741.5
127.5°	649.9	649.3	648.6	647.9	652.0	655.8	659.7	663.4	667.3	670.9	674.4
130°	608.6	607.6	606.6	605.5	609.0	612.5	616.1	619.4	622.8	625.9	629.1
132.5°	580.9	579.6	578.4	577.1	579.7	581.9	584.4	586.6	588.9	590.8	593.0
135°	557.3	555.6	554.3	552.7	555.0	557.2	559.5	561.4	563.5	565.2	567.2
137.5°	537.0	535.4	533.9	532.3	534.4	536.3	538.2	540.1	541.8	543.6	545.1
140°	519.2	517.3	515.7	513.8	515.6	517.3	519.0	520.5	522.2	523.5	524.9
142.5°	502.0	499.5	497.5	495.1	496.4	497.5	498.8	499.8	500.9	501.9	502.8
145°	489.8	487.2	484.6	482.1	483.1	483.9	484.9	485.9	486.5	487.2	488.0
147.5°	478.5	476.0	473.6	471.0	471.9	472.5	473.0	473.6	474.3	474.8	475.1
150°	467.4	464.8	462.4	459.8	460.4	461.0	461.4	462.0	462.6	462.9	463.3
152.5°	455.5	453.2	450.7	448.3	448.9	449.3	449.7	450.1	450.5	450.9	451.2
155°	447.2	445.1	443.2	441.0	441.6	442.0	442.3	442.7	443.0	443.3	443.6
157.5°	442.8	441.2	439.7	438.1	438.2	438.3	438.4	438.4	438.5	438.6	438.6
160°	439.3	437.9	436.5	435.1	435.1	435.3	435.4	435.3	435.4	435.3	435.3
162.5°	436.7	435.2	433.6	431.9	431.9	432.2	432.2	432.2	432.2	432.2	432.2
165°	436.3	435.1	434.0	432.7	432.6	432.5	432.4	432.1	431.9	431.6	431.4
167.5°	436.7	435.5	434.3	433.0	433.2	433.4	433.4	433.5	433.5	433.5	433.5
170°	438.0	436.9	436.1	435.1	435.0	434.9	434.8	434.6	434.4	434.2	434.1
172.5°	439.3	438.3	437.5	436.4	436.4	436.3	436.2	436.1	435.8	435.7	435.6
175°	437.5	436.8	436.0	435.4	435.3	435.3	435.2	435.1	434.9	434.9	434.7
177.5°	439.3	438.9	438.3	437.9	437.8	437.8	437.7	437.6	437.6	437.6	437.5
180°	439.9	439.9	439.9	439.9	439.9	439.9	439.9	439.9	439.9	439.9	439.9



TEST NUMBER: P1444808
 CATALOG NUMBER: EHBR1-24-UNV-TA-L940-UPL40

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	19898.6	19898.6
2.5°	19975.7	19974.7
5°	20049.9	20048.7
7.5°	20106.4	20106.1
10°	20113.1	20116.6
12.5°	20073.0	20075.8
15°	19955.8	19961.3
17.5°	19731.7	19738.9
20°	19345.7	19353.2
22.5°	18720.7	18723.7
25°	17811.9	17799.0
27.5°	16572.9	16550.8
30°	14997.9	14976.5
32.5°	13120.1	13106.7
35°	11006.4	10997.9
37.5°	8780.9	8763.6
40°	6620.4	6570.1
42.5°	4725.5	4637.2
45°	3265.7	3161.1
47.5°	2279.8	2215.2
50°	1728.0	1707.1
52.5°	1408.1	1403.2
55°	1188.0	1185.9
57.5°	1022.8	1022.0
60°	892.9	892.6
62.5°	796.0	796.4
65°	727.8	728.0
67.5°	667.8	667.3
70°	598.4	597.8
72.5°	550.6	549.8
75°	513.7	513.2
77.5°	461.3	460.4
80°	397.6	396.6
82.5°	327.1	325.9
85°	244.0	244.0
87.5°	149.2	149.2
90°	83.8	81.3
92.5°	44.2	41.5
95°	50.9	47.5
97.5°	62.9	60.0
100°	81.1	78.6
102.5°	140.3	131.6
105°	248.7	225.0
107.5°	430.4	386.7
110°	752.9	717.6



TEST NUMBER: P1444808
CATALOG NUMBER: EHBR1-24-UNV-TA-L940-UPL40

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	984.5	968.4
115°	1026.6	1020.8
117.5°	988.8	989.4
120°	915.5	920.0
122.5°	827.6	832.9
125°	746.7	752.0
127.5°	678.0	681.3
130°	631.8	635.0
132.5°	594.8	596.6
135°	568.8	570.4
137.5°	546.4	547.9
140°	526.1	527.2
142.5°	503.6	504.4
145°	488.6	489.1
147.5°	475.2	475.7
150°	463.6	463.9
152.5°	451.4	451.8
155°	443.7	443.9
157.5°	438.5	438.4
160°	435.2	435.1
162.5°	432.1	432.0
165°	431.1	430.8
167.5°	433.4	433.5
170°	433.8	433.7
172.5°	435.5	435.3
175°	434.6	434.6
177.5°	437.5	437.3
180°	439.9	439.9

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2506-472-7

Test Date: 08/04/2025

Luminaire Tested: EHBR-60-L940-N

Data in this report applies to families of products including EHBR-60-L940-N

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2506-472-7
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 08/05/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Metalux
 Catalog Number: **EHBR-60-L940-N**
 Description: Elevate Round Highbay at, 60000 lumens, 4000K 90CRI LEDs with N lens

Spectral Parameters

CCT (K): 3963
 CIE u': 0.2267
 CIE v': 0.5003
 Duv: -0.0016
 CIE x: 0.3810
 CIE y: 0.3738
 CIE z: 0.2453
 Peak Wavelength (nm): 630
 Dominant Wavelength (nm): 580
 Purity: 26.49712
 Rf: 90.7
 Rg: 101

CRI (Ra):	93.4		
R1:	95.2	R9:	66.4
R2:	95.1	R10:	86.6
R3:	93.3	R11:	94.4
R4:	94.5	R12:	75.4
R5:	94.2	R13:	95.0
R6:	92.9	R14:	95.4
R7:	94.0	R15:	92.8
R8:	87.7		



Test Conditions


Stabilization Time: 44M
 Operation Time: 1H 44M
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP1-2506-472-7


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2506-472-7

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2506-472-7

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	141	NR	620	276	NR	750	5	NR	880	0	NR
365	0	NR	495	167	NR	625	279	NR	755	4	NR	885	0	NR
370	0	NR	500	193	NR	630	1000	NR	760	4	NR	890	0	NR
375	0	NR	505	215	NR	635	628	NR	765	3	NR	895	0	NR
380	0	NR	510	230	NR	640	164	NR	770	3	NR	900	0	NR
385	0	NR	515	243	NR	645	161	NR	775	2	NR	905	0	NR
390	1	NR	520	251	NR	650	137	NR	780	2	NR	910	0	NR
395	2	NR	525	256	NR	655	111	NR	785	2	NR	915	0	NR
400	3	NR	530	262	NR	660	92	NR	790	1	NR	920	0	NR
405	4	NR	535	267	NR	665	76	NR	795	1	NR	925	0	NR
410	6	NR	540	271	NR	670	71	NR	800	1	NR	930	0	NR
415	11	NR	545	276	NR	675	56	NR	805	1	NR	935	0	NR
420	20	NR	550	280	NR	680	47	NR	810	1	NR	940	0	NR
425	37	NR	555	285	NR	685	40	NR	815	1	NR	945	0	NR
430	63	NR	560	290	NR	690	34	NR	820	1	NR	950	0	NR
435	108	NR	565	294	NR	695	29	NR	825	1	NR	955	0	NR
440	186	NR	570	296	NR	700	25	NR	830	0	NR	960	0	NR
445	323	NR	575	298	NR	705	21	NR	835	0	NR	965	0	NR
450	403	NR	580	299	NR	710	18	NR	840	0	NR	970	0	NR
455	293	NR	585	298	NR	715	15	NR	845	0	NR	975	0	NR
460	214	NR	590	296	NR	720	13	NR	850	0	NR	980	0	NR
465	180	NR	595	288	NR	725	11	NR	855	0	NR	985	0	NR
470	132	NR	600	286	NR	730	9	NR	860	0	NR	990	0	NR
475	109	NR	605	282	NR	735	8	NR	865	0	NR	995	0	NR
480	110	NR	610	311	NR	740	7	NR	870	0	NR	1000	0	NR
485	121	NR	615	334	NR	745	6	NR	875	0	NR			

REPORT NUMBER: SP1-2506-472-7

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.76

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	141	NR	620	276	NR	750	5	NR	880	0	NR
365	0	NR	495	167	NR	625	279	NR	755	4	NR	885	0	NR
370	0	NR	500	193	NR	630	1000	NR	760	4	NR	890	0	NR
375	0	NR	505	215	NR	635	628	NR	765	3	NR	895	0	NR
380	0	NR	510	230	NR	640	164	NR	770	3	NR	900	0	NR
385	0	NR	515	243	NR	645	161	NR	775	2	NR	905	0	NR
390	1	NR	520	251	NR	650	137	NR	780	2	NR	910	0	NR
395	2	NR	525	256	NR	655	111	NR	785	2	NR	915	0	NR
400	3	NR	530	262	NR	660	92	NR	790	1	NR	920	0	NR
405	4	NR	535	267	NR	665	76	NR	795	1	NR	925	0	NR
410	6	NR	540	271	NR	670	71	NR	800	1	NR	930	0	NR
415	11	NR	545	276	NR	675	56	NR	805	1	NR	935	0	NR
420	20	NR	550	280	NR	680	47	NR	810	1	NR	940	0	NR
425	37	NR	555	285	NR	685	40	NR	815	1	NR	945	0	NR
430	63	NR	560	290	NR	690	34	NR	820	1	NR	950	0	NR
435	108	NR	565	294	NR	695	29	NR	825	1	NR	955	0	NR
440	186	NR	570	296	NR	700	25	NR	830	0	NR	960	0	NR
445	323	NR	575	298	NR	705	21	NR	835	0	NR	965	0	NR
450	403	NR	580	299	NR	710	18	NR	840	0	NR	970	0	NR
455	293	NR	585	298	NR	715	15	NR	845	0	NR	975	0	NR
460	214	NR	590	296	NR	720	13	NR	850	0	NR	980	0	NR
465	180	NR	595	288	NR	725	11	NR	855	0	NR	985	0	NR
470	132	NR	600	286	NR	730	9	NR	860	0	NR	990	0	NR
475	109	NR	605	282	NR	735	8	NR	865	0	NR	995	0	NR
480	110	NR	610	311	NR	740	7	NR	870	0	NR	1000	0	NR
485	121	NR	615	334	NR	745	6	NR	875	0	NR			

REPORT NUMBER: SP1-2506-472-7

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 3.64

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	141	NR	620	276	NR	750	5	NR	880	0	NR
365	0	NR	495	167	NR	625	279	NR	755	4	NR	885	0	NR
370	0	NR	500	193	NR	630	1000	NR	760	4	NR	890	0	NR
375	0	NR	505	215	NR	635	628	NR	765	3	NR	895	0	NR
380	0	NR	510	230	NR	640	164	NR	770	3	NR	900	0	NR
385	0	NR	515	243	NR	645	161	NR	775	2	NR	905	0	NR
390	1	NR	520	251	NR	650	137	NR	780	2	NR	910	0	NR
395	2	NR	525	256	NR	655	111	NR	785	2	NR	915	0	NR
400	3	NR	530	262	NR	660	92	NR	790	1	NR	920	0	NR
405	4	NR	535	267	NR	665	76	NR	795	1	NR	925	0	NR
410	6	NR	540	271	NR	670	71	NR	800	1	NR	930	0	NR
415	11	NR	545	276	NR	675	56	NR	805	1	NR	935	0	NR
420	20	NR	550	280	NR	680	47	NR	810	1	NR	940	0	NR
425	37	NR	555	285	NR	685	40	NR	815	1	NR	945	0	NR
430	63	NR	560	290	NR	690	34	NR	820	1	NR	950	0	NR
435	108	NR	565	294	NR	695	29	NR	825	1	NR	955	0	NR
440	186	NR	570	296	NR	700	25	NR	830	0	NR	960	0	NR
445	323	NR	575	298	NR	705	21	NR	835	0	NR	965	0	NR
450	403	NR	580	299	NR	710	18	NR	840	0	NR	970	0	NR
455	293	NR	585	298	NR	715	15	NR	845	0	NR	975	0	NR
460	214	NR	590	296	NR	720	13	NR	850	0	NR	980	0	NR
465	180	NR	595	288	NR	725	11	NR	855	0	NR	985	0	NR
470	132	NR	600	286	NR	730	9	NR	860	0	NR	990	0	NR
475	109	NR	605	282	NR	735	8	NR	865	0	NR	995	0	NR
480	110	NR	610	311	NR	740	7	NR	870	0	NR	1000	0	NR
485	121	NR	615	334	NR	745	6	NR	875	0	NR			

Summary

$R_f = 90.7$
 $R_g = 101$
 $CIE R_a = 93.4$
 $R_9 = 66.4$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 90	CES51 = 99	CES76 = 83
CES02 = 62	CES27 = 93	CES52 = 97	CES77 = 87
CES03 = 31	CES28 = 94	CES53 = 95	CES78 = 79
CES04 = 69	CES29 = 91	CES54 = 96	CES79 = 94
CES05 = 49	CES30 = 98	CES55 = 95	CES80 = 91
CES06 = 50	CES31 = 92	CES56 = 95	CES81 = 80
CES07 = 42	CES32 = 84	CES57 = 94	CES82 = 96
CES08 = 41	CES33 = 95	CES58 = 95	CES83 = 95
CES09 = 29	CES34 = 90	CES59 = 98	CES84 = 93
CES10 = 74	CES35 = 94	CES60 = 93	CES85 = 82
CES11 = 57	CES36 = 84	CES61 = 93	CES86 = 84
CES12 = 63	CES37 = 92	CES62 = 90	CES87 = 90
CES13 = 43	CES38 = 93	CES63 = 92	CES88 = 97
CES14 = 74	CES39 = 98	CES64 = 91	CES89 = 84
CES15 = 71	CES40 = 96	CES65 = 88	CES90 = 99
CES16 = 47	CES41 = 98	CES66 = 88	CES91 = 74
CES17 = 49	CES42 = 89	CES67 = 87	CES92 = 78
CES18 = 56	CES43 = 89	CES68 = 87	CES93 = 87
CES19 = 71	CES44 = 99	CES69 = 88	CES94 = 75
CES20 = 66	CES45 = 93	CES70 = 84	CES95 = 83
CES21 = 85	CES46 = 95	CES71 = 80	CES96 = 91
CES22 = 78	CES47 = 92	CES72 = 93	CES97 = 93
CES23 = 91	CES48 = 96	CES73 = 78	CES98 = 93
CES24 = 90	CES49 = 93	CES74 = 92	CES99 = 94
CES25 = 71	CES50 = 99	CES75 = 81	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)