

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: METALUX

Report Number: P1431683

Luminaire Tested: EHBR1-18-UNV-TASM-L950

Issue Date: 3/13/2026

Test Information

Test Method: LM-79-2019
Report Number: P1431683
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2601-654-4)
Test Lab: INNOVATION CENTER
Issue Date: 3/13/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: METALUX
Catalog Number: EHBR1-18-UNV-TASM-L950
Description: Elevate Round Highbay at, 18000 lumens, 5000K 90CRI LEDs with TASM lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 17051.1 lumens
Efficiency: N/A
Efficacy: 180.1 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.84 / 0.9
Luminous Opening: Circular (Dia: 1.71' x H: 0')
CIE Type: Direct

Input Watts (W): 94.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1431683
CATALOG NUMBER: EHBR1-18-UNV-TASM-L950

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - · - · 90°-270° - · - · 135°-315°



TEST NUMBER: P1431683
 CATALOG NUMBER: EHBR1-18-UNV-TASM-L950

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 102 | 102 | 102 | 100 |
| 1 | 112 | 108 | 105 | 103 | 109 | 106 | 104 | 101 | 102 | 100 | 98 | 98 | 97 | 95 | 95 | 93 | 92 | 92 | 92 | 92 | 90 |
| 2 | 105 | 99 | 94 | 90 | 103 | 97 | 93 | 89 | 94 | 90 | 87 | 91 | 88 | 85 | 88 | 85 | 83 | 83 | 83 | 83 | 81 |
| 3 | 99 | 91 | 85 | 80 | 96 | 89 | 84 | 79 | 87 | 82 | 78 | 84 | 80 | 77 | 82 | 78 | 76 | 76 | 76 | 76 | 74 |
| 4 | 93 | 84 | 77 | 72 | 91 | 83 | 77 | 72 | 80 | 75 | 71 | 78 | 74 | 70 | 76 | 72 | 69 | 69 | 69 | 69 | 67 |
| 5 | 87 | 78 | 71 | 66 | 86 | 77 | 70 | 65 | 75 | 69 | 65 | 73 | 68 | 64 | 71 | 67 | 64 | 64 | 64 | 64 | 62 |
| 6 | 82 | 72 | 65 | 60 | 81 | 71 | 65 | 60 | 70 | 64 | 60 | 68 | 63 | 59 | 67 | 62 | 59 | 59 | 59 | 59 | 57 |
| 7 | 78 | 67 | 60 | 56 | 76 | 67 | 60 | 56 | 65 | 59 | 55 | 64 | 59 | 55 | 63 | 58 | 55 | 55 | 55 | 55 | 53 |
| 8 | 74 | 63 | 56 | 52 | 72 | 62 | 56 | 52 | 61 | 55 | 51 | 60 | 55 | 51 | 59 | 54 | 51 | 51 | 51 | 51 | 49 |
| 9 | 70 | 59 | 53 | 48 | 69 | 59 | 52 | 48 | 58 | 52 | 48 | 57 | 51 | 48 | 56 | 51 | 47 | 47 | 47 | 47 | 46 |
| 10 | 66 | 56 | 49 | 45 | 65 | 55 | 49 | 45 | 54 | 49 | 45 | 54 | 48 | 45 | 53 | 48 | 45 | 45 | 45 | 45 | 43 |

AVERAGE LUMINANCE (cd/sqm):

| | 0° | 90° | 180° | 270° |
|-----|-------|-------|-------|-------|
| 0° | 71613 | 71613 | 71613 | 71613 |
| 5° | 71641 | 76427 | 71641 | 67923 |
| 10° | 71225 | 78905 | 71225 | 64706 |
| 15° | 69589 | 73821 | 69589 | 60174 |
| 20° | 65539 | 59610 | 65539 | 53974 |
| 25° | 58438 | 41609 | 58438 | 45568 |
| 30° | 47829 | 27285 | 47829 | 34367 |
| 35° | 34606 | 17826 | 34606 | 23080 |
| 40° | 22594 | 12408 | 22594 | 14699 |
| 45° | 14498 | 9719 | 14498 | 10591 |
| 50° | 10909 | 8369 | 10909 | 8939 |
| 55° | 9051 | 7747 | 9051 | 8019 |
| 60° | 7997 | 7531 | 7997 | 7577 |
| 65° | 7489 | 7461 | 7489 | 7429 |
| 70° | 7373 | 7593 | 7373 | 7495 |
| 75° | 7314 | 7793 | 7314 | 7559 |
| 80° | 7153 | 8189 | 7153 | 7656 |
| 85° | 6024 | 7608 | 6024 | 7258 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 20382 cd/sqm



TEST NUMBER: P1431683
 CATALOG NUMBER: EHBR1-18-UNV-TASM-L950

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 1450.0 | 8.5 |
| 10°-20° | 3944.8 | 23.1 |
| 20°-30° | 4626.4 | 27.1 |
| 30°-40° | 3217.4 | 18.9 |
| 40°-50° | 1598.9 | 9.4 |
| 50°-60° | 956.3 | 5.6 |
| 60°-70° | 673.1 | 3.9 |
| 70°-80° | 433.6 | 2.5 |
| 80°-90° | 137.7 | 0.8 |
| 90°-100° | 0.8 | 0.0 |
| 100°-110° | 1.0 | 0.0 |
| 110°-120° | 1.0 | 0.0 |
| 120°-130° | 1.2 | 0.0 |
| 130°-140° | 1.7 | 0.0 |
| 140°-150° | 2.0 | 0.0 |
| 150°-160° | 2.2 | 0.0 |
| 160°-170° | 2.2 | 0.0 |
| 170°-180° | 0.9 | 0.0 |
| 0°-30° | 10021.1 | 58.8 |
| 0°-40° | 13238.5 | 77.6 |
| 0°-60° | 15793.7 | 92.6 |
| 0°-90° | 17038.1 | 99.9 |
| 90°-120° | 2.7 | 0.0 |
| 90°-150° | 7.6 | 0.0 |
| 90°-180° | 13.0 | 0.1 |
| 0°-180° | 17051.1 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | 90° | 180° | 270° | 360° | Flux |
|------|-------|-------|-------|-------|-------|------|
| 0° | 15249 | 15249 | 15249 | 15249 | 15249 | |
| 5° | 15197 | 16213 | 15197 | 14409 | 15197 | 1442 |
| 15° | 14314 | 15184 | 14314 | 12377 | 14314 | 4000 |
| 25° | 11278 | 8030 | 11278 | 8794 | 11278 | 5106 |
| 35° | 6036 | 3109 | 6036 | 4026 | 6036 | 3768 |
| 45° | 2183 | 1463 | 2183 | 1595 | 2183 | 1786 |
| 55° | 1106 | 946 | 1106 | 979 | 1106 | 1011 |
| 65° | 674 | 671 | 674 | 669 | 674 | 677 |
| 75° | 403 | 430 | 403 | 417 | 403 | 423 |
| 85° | 112 | 141 | 112 | 135 | 112 | 124 |
| 90° | 0 | 2 | 0 | 0 | 0 | 5 |
| 95° | 1 | 2 | 1 | 0 | 1 | 0 |
| 105° | 1 | 3 | 1 | 1 | 1 | 1 |
| 115° | 1 | 3 | 1 | 1 | 1 | 1 |
| 125° | 1 | 3 | 1 | 1 | 1 | 1 |
| 135° | 2 | 3 | 2 | 1 | 2 | 2 |
| 145° | 3 | 4 | 3 | 3 | 3 | 2 |
| 155° | 5 | 5 | 5 | 5 | 5 | 2 |
| 165° | 8 | 10 | 8 | 8 | 8 | 2 |
| 175° | 10 | 12 | 10 | 10 | 10 | 1 |
| 180° | 11 | 11 | 11 | 11 | 11 | |



TEST NUMBER: P1431683
 CATALOG NUMBER: EHBR1-18-UNV-TASM-L950

CANDELA DISTRIBUTION (FULL):

| | 0° | 22.5° | 45° | 67.5° | 90° | 112.5° | 135° | 157.5° | 180° | 202.5° | 225° |
|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0° | 15249.4 | 15249.4 | 15249.4 | 15249.4 | 15249.4 | 15249.4 | 15249.4 | 15249.4 | 15249.4 | 15249.4 | 15249.4 |
| 2.5° | 15240.4 | 15437.5 | 15597.0 | 15702.3 | 15754.3 | 15702.3 | 15597.0 | 15437.5 | 15240.4 | 15044.6 | 14910.0 |
| 5° | 15197.3 | 15591.9 | 15926.2 | 16144.9 | 16212.7 | 16144.9 | 15926.2 | 15591.9 | 15197.3 | 14824.5 | 14577.1 |
| 7.5° | 15094.1 | 15708.9 | 16205.6 | 16460.9 | 16523.3 | 16460.9 | 16205.6 | 15708.9 | 15094.1 | 14566.2 | 14253.7 |
| 10° | 14936.5 | 15782.7 | 16356.6 | 16539.5 | 16547.0 | 16539.5 | 16356.6 | 15782.7 | 14936.5 | 14225.4 | 13856.8 |
| 12.5° | 14685.2 | 15756.4 | 16306.0 | 16245.9 | 16109.4 | 16245.9 | 16306.0 | 15756.4 | 14685.2 | 13809.0 | 13344.1 |
| 15° | 14313.5 | 15600.5 | 15985.4 | 15496.7 | 15184.1 | 15496.7 | 15985.4 | 15600.5 | 14313.5 | 13246.8 | 12707.6 |
| 17.5° | 13789.6 | 15308.8 | 15316.3 | 14349.5 | 13759.8 | 14349.5 | 15316.3 | 15308.8 | 13789.6 | 12559.4 | 11965.5 |
| 20° | 13114.4 | 14841.0 | 14394.9 | 12626.7 | 11928.1 | 12626.7 | 14394.9 | 14841.0 | 13114.4 | 11746.8 | 11164.0 |
| 22.5° | 12268.0 | 14210.2 | 13111.8 | 10893.5 | 9940.4 | 10893.5 | 13111.8 | 14210.2 | 12268.0 | 10801.7 | 10195.2 |
| 25° | 11278.1 | 13437.3 | 11731.6 | 9005.1 | 8030.1 | 9005.1 | 11731.6 | 13437.3 | 11278.1 | 9675.6 | 9127.2 |
| 27.5° | 10113.7 | 12457.7 | 10261.9 | 7358.6 | 6459.0 | 7358.6 | 10261.9 | 12457.7 | 10113.7 | 8513.0 | 7952.8 |
| 30° | 8820.4 | 11201.8 | 8732.3 | 5860.2 | 5031.8 | 5860.2 | 8732.3 | 11201.8 | 8820.4 | 7206.8 | 6705.2 |
| 32.5° | 7372.3 | 9970.8 | 7263.3 | 4695.6 | 3993.9 | 4695.6 | 7263.3 | 9970.8 | 7372.3 | 5960.3 | 5436.2 |
| 35° | 6036.4 | 8430.6 | 5938.9 | 3689.6 | 3109.4 | 3689.6 | 5938.9 | 8430.6 | 6036.4 | 4783.6 | 4268.9 |
| 37.5° | 4737.3 | 6975.4 | 4734.2 | 2971.0 | 2522.1 | 2971.0 | 4734.2 | 6975.4 | 4737.3 | 3719.1 | 3301.2 |
| 40° | 3685.6 | 5454.2 | 3709.3 | 2371.7 | 2024.0 | 2371.7 | 3709.3 | 5454.2 | 3685.6 | 2829.7 | 2562.4 |
| 42.5° | 2792.5 | 4170.5 | 2915.6 | 1946.5 | 1719.1 | 1946.5 | 2915.6 | 4170.5 | 2792.5 | 2229.5 | 2029.4 |
| 45° | 2183.0 | 3069.0 | 2276.7 | 1642.2 | 1463.4 | 1642.2 | 2276.7 | 3069.0 | 2183.0 | 1795.5 | 1661.1 |
| 47.5° | 1777.8 | 2371.9 | 1845.2 | 1408.5 | 1283.3 | 1408.5 | 1845.2 | 2371.9 | 1777.8 | 1518.6 | 1418.0 |
| 50° | 1493.2 | 1820.0 | 1532.1 | 1229.6 | 1145.5 | 1229.6 | 1532.1 | 1820.0 | 1493.2 | 1300.5 | 1233.3 |
| 52.5° | 1282.7 | 1484.4 | 1304.8 | 1095.8 | 1039.1 | 1095.8 | 1304.8 | 1484.4 | 1282.7 | 1137.8 | 1096.1 |
| 55° | 1105.5 | 1247.9 | 1134.6 | 985.4 | 946.2 | 985.4 | 1134.6 | 1247.9 | 1105.5 | 1012.5 | 981.7 |
| 57.5° | 970.8 | 1058.5 | 985.4 | 891.3 | 865.3 | 891.3 | 985.4 | 1058.5 | 970.8 | 901.1 | 884.4 |
| 60° | 851.5 | 916.8 | 869.6 | 809.3 | 801.8 | 809.3 | 869.6 | 916.8 | 851.5 | 810.7 | 799.8 |
| 62.5° | 759.7 | 800.9 | 768.9 | 735.5 | 728.9 | 735.5 | 768.9 | 800.9 | 759.7 | 728.3 | 730.3 |
| 65° | 674.0 | 712.3 | 687.2 | 669.1 | 671.4 | 669.1 | 687.2 | 712.3 | 674.0 | 659.4 | 662.6 |
| 67.5° | 607.6 | 627.6 | 616.7 | 606.5 | 609.0 | 606.5 | 616.7 | 627.6 | 607.6 | 593.3 | 598.2 |
| 70° | 537.0 | 558.5 | 547.3 | 548.7 | 553.0 | 548.7 | 547.3 | 558.5 | 537.0 | 532.8 | 536.5 |
| 72.5° | 469.5 | 486.1 | 482.4 | 485.8 | 490.4 | 485.8 | 482.4 | 486.1 | 469.5 | 468.9 | 469.2 |
| 75° | 403.1 | 415.8 | 417.5 | 422.4 | 429.5 | 422.4 | 417.5 | 415.8 | 403.1 | 398.9 | 404.1 |
| 77.5° | 330.9 | 345.2 | 350.6 | 357.2 | 367.7 | 357.2 | 350.6 | 345.2 | 330.9 | 333.7 | 336.2 |
| 80° | 264.5 | 271.1 | 283.1 | 287.9 | 302.8 | 287.9 | 283.1 | 271.1 | 264.5 | 259.7 | 263.4 |
| 82.5° | 193.6 | 199.6 | 209.9 | 219.0 | 227.6 | 219.0 | 209.9 | 199.6 | 193.6 | 191.3 | 191.6 |
| 85° | 111.8 | 121.0 | 127.8 | 138.7 | 141.2 | 138.7 | 127.8 | 121.0 | 111.8 | 114.4 | 111.8 |
| 87.5° | 39.2 | 42.0 | 48.0 | 52.3 | 52.6 | 52.3 | 48.0 | 42.0 | 39.2 | 40.0 | 36.3 |
| 90° | 0.3 | 0.6 | 0.8 | 1.7 | 2.3 | 1.7 | 0.8 | 0.6 | 0.3 | 0.3 | 0.3 |
| 92.5° | 0.3 | 0.6 | 0.8 | 1.7 | 2.3 | 1.7 | 0.8 | 0.6 | 0.3 | 0.3 | 0.3 |
| 95° | 0.6 | 0.6 | 0.8 | 1.7 | 2.3 | 1.7 | 0.8 | 0.6 | 0.6 | 0.3 | 0.3 |
| 97.5° | 0.6 | 0.6 | 0.8 | 1.7 | 2.3 | 1.7 | 0.8 | 0.6 | 0.6 | 0.3 | 0.3 |
| 100° | 0.6 | 0.6 | 0.8 | 1.7 | 2.3 | 1.7 | 0.8 | 0.6 | 0.6 | 0.6 | 0.3 |
| 102.5° | 0.6 | 0.8 | 1.1 | 2.0 | 2.3 | 2.0 | 1.1 | 0.8 | 0.6 | 0.6 | 0.3 |
| 105° | 0.6 | 0.8 | 1.1 | 2.0 | 2.6 | 2.0 | 1.1 | 0.8 | 0.6 | 0.6 | 0.3 |
| 107.5° | 0.6 | 0.8 | 1.1 | 2.0 | 2.6 | 2.0 | 1.1 | 0.8 | 0.6 | 0.6 | 0.6 |
| 110° | 0.6 | 0.8 | 1.1 | 2.0 | 2.6 | 2.0 | 1.1 | 0.8 | 0.6 | 0.6 | 0.6 |



TEST NUMBER: P1431683
 CATALOG NUMBER: EHBR1-18-UNV-TASM-L950

CANDELA DISTRIBUTION (continued):

| | 0° | 22.5° | 45° | 67.5° | 90° | 112.5° | 135° | 157.5° | 180° | 202.5° | 225° |
|--------|------|-------|------|-------|------|--------|------|--------|------|--------|------|
| 112.5° | 0.6 | 0.8 | 1.1 | 2.0 | 2.6 | 2.0 | 1.1 | 0.8 | 0.6 | 0.6 | 0.6 |
| 115° | 0.8 | 0.8 | 1.1 | 2.0 | 2.6 | 2.0 | 1.1 | 0.8 | 0.8 | 0.6 | 0.6 |
| 117.5° | 0.8 | 0.8 | 1.1 | 2.0 | 2.6 | 2.0 | 1.1 | 0.8 | 0.8 | 0.8 | 0.6 |
| 120° | 0.8 | 0.8 | 1.4 | 2.0 | 2.6 | 2.0 | 1.4 | 0.8 | 0.8 | 0.8 | 0.6 |
| 122.5° | 1.1 | 1.1 | 1.4 | 2.3 | 2.6 | 2.3 | 1.4 | 1.1 | 1.1 | 1.1 | 0.8 |
| 125° | 1.1 | 1.1 | 1.7 | 2.3 | 2.9 | 2.3 | 1.7 | 1.1 | 1.1 | 1.4 | 1.1 |
| 127.5° | 1.4 | 1.4 | 1.7 | 2.3 | 2.9 | 2.3 | 1.7 | 1.4 | 1.4 | 1.4 | 1.1 |
| 130° | 1.7 | 1.4 | 1.7 | 2.6 | 2.9 | 2.6 | 1.7 | 1.4 | 1.7 | 1.7 | 1.4 |
| 132.5° | 2.0 | 1.7 | 2.0 | 2.9 | 3.2 | 2.9 | 2.0 | 1.7 | 2.0 | 2.3 | 2.0 |
| 135° | 2.3 | 1.7 | 2.3 | 2.6 | 3.2 | 2.6 | 2.3 | 1.7 | 2.3 | 2.6 | 2.0 |
| 137.5° | 2.6 | 2.0 | 2.3 | 2.9 | 3.2 | 2.9 | 2.3 | 2.0 | 2.6 | 2.9 | 2.6 |
| 140° | 2.9 | 2.3 | 2.3 | 2.9 | 3.4 | 2.9 | 2.3 | 2.3 | 2.9 | 2.9 | 2.9 |
| 142.5° | 3.2 | 2.6 | 2.6 | 3.2 | 3.4 | 3.2 | 2.6 | 2.6 | 3.2 | 3.2 | 3.2 |
| 145° | 3.4 | 3.2 | 2.9 | 3.2 | 3.7 | 3.2 | 2.9 | 3.2 | 3.4 | 3.2 | 3.4 |
| 147.5° | 3.4 | 3.2 | 3.2 | 3.4 | 4.0 | 3.4 | 3.2 | 3.2 | 3.4 | 3.4 | 3.7 |
| 150° | 3.7 | 3.7 | 3.4 | 3.7 | 4.3 | 3.7 | 3.4 | 3.7 | 3.7 | 3.7 | 4.0 |
| 152.5° | 4.0 | 4.0 | 4.0 | 4.3 | 4.6 | 4.3 | 4.0 | 4.0 | 4.0 | 4.0 | 4.3 |
| 155° | 4.6 | 4.6 | 4.6 | 4.8 | 5.1 | 4.8 | 4.6 | 4.6 | 4.6 | 4.3 | 4.8 |
| 157.5° | 5.1 | 5.4 | 5.4 | 5.8 | 6.0 | 5.8 | 5.4 | 5.4 | 5.1 | 5.1 | 5.4 |
| 160° | 6.3 | 6.3 | 6.6 | 6.9 | 7.2 | 6.9 | 6.6 | 6.3 | 6.3 | 6.0 | 6.3 |
| 162.5° | 6.9 | 6.9 | 7.4 | 7.7 | 8.3 | 7.7 | 7.4 | 6.9 | 6.9 | 6.9 | 6.9 |
| 165° | 7.7 | 7.7 | 8.3 | 8.8 | 9.5 | 8.8 | 8.3 | 7.7 | 7.7 | 7.4 | 7.4 |
| 167.5° | 8.3 | 8.3 | 8.8 | 9.8 | 10.3 | 9.8 | 8.8 | 8.3 | 8.3 | 8.0 | 8.0 |
| 170° | 8.5 | 8.8 | 9.5 | 10.3 | 10.9 | 10.3 | 9.5 | 8.8 | 8.5 | 8.5 | 8.3 |
| 172.5° | 9.5 | 9.5 | 10.3 | 11.1 | 11.7 | 11.1 | 10.3 | 9.5 | 9.5 | 9.1 | 9.1 |
| 175° | 10.0 | 10.3 | 10.9 | 11.7 | 12.3 | 11.7 | 10.9 | 10.3 | 10.0 | 9.8 | 9.8 |
| 177.5° | 10.0 | 10.6 | 11.1 | 12.0 | 12.5 | 12.0 | 11.1 | 10.6 | 10.0 | 9.8 | 9.8 |
| 180° | 10.6 | 10.6 | 10.6 | 10.6 | 10.6 | 10.6 | 10.6 | 10.6 | 10.6 | 10.6 | 10.6 |



TEST NUMBER: P1431683
 CATALOG NUMBER: EHBR1-18-UNV-TASM-L950

CANDELA DISTRIBUTION (continued):

| | 247.5° | 270° | 292.5° | 315° | 337.5° | 360° |
|--------|---------|---------|---------|---------|---------|---------|
| 0° | 15249.4 | 15249.4 | 15249.4 | 15249.4 | 15249.4 | 15249.4 |
| 2.5° | 14806.5 | 14796.7 | 14806.5 | 14910.0 | 15044.6 | 15240.4 |
| 5° | 14462.4 | 14408.7 | 14462.4 | 14577.1 | 14824.5 | 15197.3 |
| 7.5° | 14061.8 | 14030.6 | 14061.8 | 14253.7 | 14566.2 | 15094.1 |
| 10° | 13640.0 | 13569.4 | 13640.0 | 13856.8 | 14225.4 | 14936.5 |
| 12.5° | 13120.2 | 13026.6 | 13120.2 | 13344.1 | 13809.0 | 14685.2 |
| 15° | 12459.0 | 12377.0 | 12459.0 | 12707.6 | 13246.8 | 14313.5 |
| 17.5° | 11749.7 | 11675.2 | 11749.7 | 11965.5 | 12559.4 | 13789.6 |
| 20° | 10858.6 | 10800.3 | 10858.6 | 11164.0 | 11746.8 | 13114.4 |
| 22.5° | 9923.9 | 9869.2 | 9923.9 | 10195.2 | 10801.7 | 12268.0 |
| 25° | 8824.1 | 8794.3 | 8824.1 | 9127.2 | 9675.6 | 11278.1 |
| 27.5° | 7635.6 | 7585.1 | 7635.6 | 7952.8 | 8513.0 | 10113.7 |
| 30° | 6421.6 | 6337.8 | 6421.6 | 6705.2 | 7206.8 | 8820.4 |
| 32.5° | 5234.0 | 5173.7 | 5234.0 | 5436.2 | 5960.3 | 7372.3 |
| 35° | 4086.2 | 4025.9 | 4086.2 | 4268.9 | 4783.6 | 6036.4 |
| 37.5° | 3184.1 | 3077.4 | 3184.1 | 3301.2 | 3719.1 | 4737.3 |
| 40° | 2414.9 | 2397.7 | 2414.9 | 2562.4 | 2829.7 | 3685.6 |
| 42.5° | 1965.9 | 1919.3 | 1965.9 | 2029.4 | 2229.5 | 2792.5 |
| 45° | 1613.0 | 1594.7 | 1613.0 | 1661.1 | 1795.5 | 2183.0 |
| 47.5° | 1387.2 | 1395.2 | 1387.2 | 1418.0 | 1518.6 | 1777.8 |
| 50° | 1218.7 | 1223.6 | 1218.7 | 1233.3 | 1300.5 | 1493.2 |
| 52.5° | 1094.6 | 1090.3 | 1094.6 | 1096.1 | 1137.8 | 1282.7 |
| 55° | 984.8 | 979.4 | 984.8 | 981.7 | 1012.5 | 1105.5 |
| 57.5° | 888.7 | 892.7 | 888.7 | 884.4 | 901.1 | 970.8 |
| 60° | 802.9 | 806.7 | 802.9 | 799.8 | 810.7 | 851.5 |
| 62.5° | 730.6 | 732.9 | 730.6 | 730.3 | 728.3 | 759.7 |
| 65° | 666.0 | 668.6 | 666.0 | 662.6 | 659.4 | 674.0 |
| 67.5° | 604.2 | 604.2 | 604.2 | 598.2 | 593.3 | 607.6 |
| 70° | 546.1 | 545.9 | 546.1 | 536.5 | 532.8 | 537.0 |
| 72.5° | 476.4 | 483.2 | 476.4 | 469.2 | 468.9 | 469.5 |
| 75° | 408.6 | 416.6 | 408.6 | 404.1 | 398.9 | 403.1 |
| 77.5° | 340.0 | 352.3 | 340.0 | 336.2 | 333.7 | 330.9 |
| 80° | 269.6 | 283.1 | 269.6 | 263.4 | 259.7 | 264.5 |
| 82.5° | 199.3 | 209.3 | 199.3 | 191.6 | 191.3 | 193.6 |
| 85° | 118.6 | 134.7 | 118.6 | 111.8 | 114.4 | 111.8 |
| 87.5° | 38.0 | 48.6 | 38.0 | 36.3 | 40.0 | 39.2 |
| 90° | 0.3 | 0.3 | 0.3 | 0.3 | 0.3 | 0.3 |
| 92.5° | 0.3 | 0.3 | 0.3 | 0.3 | 0.3 | 0.3 |
| 95° | 0.3 | 0.3 | 0.3 | 0.3 | 0.3 | 0.6 |
| 97.5° | 0.3 | 0.6 | 0.3 | 0.3 | 0.3 | 0.6 |
| 100° | 0.3 | 0.6 | 0.3 | 0.3 | 0.6 | 0.6 |
| 102.5° | 0.3 | 0.6 | 0.3 | 0.3 | 0.6 | 0.6 |
| 105° | 0.3 | 0.6 | 0.3 | 0.3 | 0.6 | 0.6 |
| 107.5° | 0.3 | 0.6 | 0.3 | 0.6 | 0.6 | 0.6 |
| 110° | 0.3 | 0.6 | 0.3 | 0.6 | 0.6 | 0.6 |



TEST NUMBER: P1431683
 CATALOG NUMBER: EHBR1-18-UNV-TASM-L950

CANDELA DISTRIBUTION (continued):

| | 247.5° | 270° | 292.5° | 315° | 337.5° | 360° |
|--------|--------|------|--------|------|--------|------|
| 112.5° | 0.3 | 0.6 | 0.3 | 0.6 | 0.6 | 0.6 |
| 115° | 0.3 | 0.6 | 0.3 | 0.6 | 0.6 | 0.8 |
| 117.5° | 0.3 | 0.6 | 0.3 | 0.6 | 0.8 | 0.8 |
| 120° | 0.3 | 0.6 | 0.3 | 0.6 | 0.8 | 0.8 |
| 122.5° | 0.6 | 0.6 | 0.6 | 0.8 | 1.1 | 1.1 |
| 125° | 0.6 | 0.8 | 0.6 | 1.1 | 1.4 | 1.1 |
| 127.5° | 0.6 | 0.8 | 0.6 | 1.1 | 1.4 | 1.4 |
| 130° | 0.8 | 0.8 | 0.8 | 1.4 | 1.7 | 1.7 |
| 132.5° | 1.1 | 1.1 | 1.1 | 2.0 | 2.3 | 2.0 |
| 135° | 1.4 | 1.1 | 1.4 | 2.0 | 2.6 | 2.3 |
| 137.5° | 1.7 | 1.4 | 1.7 | 2.6 | 2.9 | 2.6 |
| 140° | 2.3 | 2.0 | 2.3 | 2.9 | 2.9 | 2.9 |
| 142.5° | 2.6 | 2.6 | 2.6 | 3.2 | 3.2 | 3.2 |
| 145° | 3.2 | 3.2 | 3.2 | 3.4 | 3.2 | 3.4 |
| 147.5° | 3.7 | 3.7 | 3.7 | 3.7 | 3.4 | 3.4 |
| 150° | 4.3 | 4.3 | 4.3 | 4.0 | 3.7 | 3.7 |
| 152.5° | 4.6 | 4.8 | 4.6 | 4.3 | 4.0 | 4.0 |
| 155° | 5.1 | 5.4 | 5.1 | 4.8 | 4.3 | 4.6 |
| 157.5° | 5.8 | 6.3 | 5.8 | 5.4 | 5.1 | 5.1 |
| 160° | 6.6 | 6.9 | 6.6 | 6.3 | 6.0 | 6.3 |
| 162.5° | 7.2 | 7.4 | 7.2 | 6.9 | 6.9 | 6.9 |
| 165° | 7.7 | 8.0 | 7.7 | 7.4 | 7.4 | 7.7 |
| 167.5° | 8.0 | 8.0 | 8.0 | 8.0 | 8.0 | 8.3 |
| 170° | 8.3 | 8.5 | 8.3 | 8.3 | 8.5 | 8.5 |
| 172.5° | 8.8 | 9.1 | 8.8 | 9.1 | 9.1 | 9.5 |
| 175° | 9.5 | 9.8 | 9.5 | 9.8 | 9.8 | 10.0 |
| 177.5° | 9.8 | 10.0 | 9.8 | 9.8 | 9.8 | 10.0 |
| 180° | 10.6 | 10.6 | 10.6 | 10.6 | 10.6 | 10.6 |



TEST NUMBER: P1431683
 CATALOG NUMBER: EHBR1-18-UNV-TASM-L950

CIE UGR TABLE:

| Reflectances: | | | | | | | | | | | |
|-----------------|------|------------------|-------|-------|-------|-------|----------------|-------|-------|-------|-------|
| Ceiling | | 0.7 | 0.7 | 0.5 | 0.5 | 0.3 | 0.7 | 0.7 | 0.5 | 0.5 | 0.3 |
| Wall | | 0.5 | 0.3 | 0.5 | 0.3 | 0.3 | 0.5 | 0.3 | 0.5 | 0.3 | 0.3 |
| Reference plane | | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 |
| Room dimensions | | Viewed crosswise | | | | | Viewed endwise | | | | |
| X=2H | Y=2H | 16.49 | 17.70 | 16.86 | 18.01 | 18.33 | 15.81 | 17.02 | 16.18 | 17.33 | 17.65 |
| | 3H | 18.13 | 19.20 | 18.51 | 19.54 | 19.90 | 17.76 | 18.83 | 18.14 | 19.17 | 19.53 |
| | 4H | 18.83 | 19.84 | 19.24 | 20.19 | 20.58 | 18.62 | 19.62 | 19.02 | 19.97 | 20.36 |
| | 6H | 19.41 | 20.33 | 19.82 | 20.70 | 21.10 | 19.37 | 20.29 | 19.79 | 20.66 | 21.06 |
| | 8H | 19.61 | 20.48 | 20.04 | 20.87 | 21.28 | 19.66 | 20.53 | 20.09 | 20.92 | 21.33 |
| | 12H | 19.73 | 20.56 | 20.17 | 20.95 | 21.38 | 19.85 | 20.68 | 20.29 | 21.07 | 21.50 |
| 4H | 2H | 16.95 | 17.95 | 17.36 | 18.31 | 18.69 | 16.44 | 17.44 | 16.85 | 17.79 | 18.18 |
| | 3H | 18.86 | 19.69 | 19.28 | 20.09 | 20.50 | 18.62 | 19.44 | 19.03 | 19.85 | 20.25 |
| | 4H | 19.72 | 20.46 | 20.16 | 20.88 | 21.33 | 19.61 | 20.35 | 20.05 | 20.78 | 21.22 |
| | 6H | 20.44 | 21.08 | 20.91 | 21.53 | 22.00 | 20.51 | 21.15 | 20.97 | 21.60 | 22.07 |
| | 8H | 20.70 | 21.30 | 21.17 | 21.75 | 22.22 | 20.85 | 21.45 | 21.33 | 21.90 | 22.37 |
| | 12H | 20.87 | 21.40 | 21.36 | 21.88 | 22.36 | 21.10 | 21.63 | 21.59 | 22.11 | 22.59 |
| 8H | 4H | 20.03 | 20.62 | 20.50 | 21.07 | 21.55 | 19.95 | 20.55 | 20.43 | 21.00 | 21.47 |
| | 6H | 20.91 | 21.39 | 21.41 | 21.89 | 22.37 | 21.01 | 21.49 | 21.51 | 21.99 | 22.47 |
| | 8H | 21.26 | 21.69 | 21.78 | 22.21 | 22.70 | 21.45 | 21.89 | 21.98 | 22.41 | 22.90 |
| | 12H | 21.52 | 21.89 | 22.03 | 22.39 | 22.97 | 21.81 | 22.19 | 22.33 | 22.69 | 23.26 |
| 12H | 4H | 20.06 | 20.58 | 20.55 | 21.07 | 21.55 | 19.98 | 20.51 | 20.47 | 20.99 | 21.47 |
| | 6H | 20.98 | 21.41 | 21.50 | 21.93 | 22.42 | 21.08 | 21.51 | 21.61 | 22.03 | 22.53 |
| | 8H | 21.39 | 21.77 | 21.91 | 22.27 | 22.84 | 21.60 | 21.97 | 22.11 | 22.47 | 23.05 |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2506-472-8

Test Date: 08/04/2025

Luminaire Tested: EHBR-60-L950-N

Data in this report applies to families of products including EHBR-60-L950-N

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2506-472-8
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 08/05/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Metalux
 Catalog Number: **EHBR-60-L950-N**
 Description: Elevate Round Highbay at, 60000 lumens, 5000K 90CRI LEDs with N lens

Spectral Parameters

CCT (K): 4901
 CIE u': 0.2131
 CIE v': 0.4853
 Duv: -0.0008
 CIE x: 0.3477
 CIE y: 0.3520
 CIE z: 0.3003
 Peak Wavelength (nm): 630
 Dominant Wavelength (nm): 574
 Purity: 9.953987
 Rf: 90.7
 Rg: 100.5

| | | | |
|-----------|------|------|------|
| CRI (Ra): | 94.3 | | |
| R1: | 95.8 | R9: | 72.3 |
| R2: | 96.5 | R10: | 89.1 |
| R3: | 94.4 | R11: | 94.9 |
| R4: | 95.3 | R12: | 68.4 |
| R5: | 94.1 | R13: | 96.4 |
| R6: | 92.5 | R14: | 96.4 |
| R7: | 95.5 | R15: | 93.9 |
| R8: | 90.1 | | |



Test Conditions

Stabilization Time: 35M
 Operation Time: 1H 35M
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP1-2506-472-8

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | 76INCH SPHERE IN0058 | 6/16/2025 | 12/16/2025 |
| Power Meter | XITRON INXT2011004 | 1/21/2025 | 1/21/2026 |
| AC Power Source | CHROMA 61603 IN0063 | 10/22/2024 | 10/22/2025 |
| DC Power Source | AGILENT E3634A IN0208 | 10/22/2024 | 10/22/2025 |
| Sphere Thermometer | ONSET IN0085 | 10/22/2024 | 10/22/2025 |
| Room Thermometer | ONSET IN0046 | 10/22/2024 | 10/22/2025 |

REPORT NUMBER: SP1-2506-472-8

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 5000K 4-step quadrangle

REPORT NUMBER: SP1-2506-472-8

Photopic Flux vs. Wavelength




Photopic Lumens: NR

| λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360 | 0 | NR | 490 | 221 | NR | 620 | 326 | NR | 750 | 7 | NR | 880 | 0 | NR |
| 365 | 0 | NR | 495 | 250 | NR | 625 | 325 | NR | 755 | 6 | NR | 885 | 0 | NR |
| 370 | 0 | NR | 500 | 284 | NR | 630 | 1000 | NR | 760 | 5 | NR | 890 | 0 | NR |
| 375 | 0 | NR | 505 | 311 | NR | 635 | 643 | NR | 765 | 4 | NR | 895 | 0 | NR |
| 380 | 0 | NR | 510 | 329 | NR | 640 | 206 | NR | 770 | 4 | NR | 900 | 0 | NR |
| 385 | 1 | NR | 515 | 344 | NR | 645 | 199 | NR | 775 | 3 | NR | 905 | 0 | NR |
| 390 | 2 | NR | 520 | 353 | NR | 650 | 172 | NR | 780 | 3 | NR | 910 | 0 | NR |
| 395 | 3 | NR | 525 | 357 | NR | 655 | 143 | NR | 785 | 2 | NR | 915 | 0 | NR |
| 400 | 5 | NR | 530 | 362 | NR | 660 | 122 | NR | 790 | 2 | NR | 920 | 0 | NR |
| 405 | 6 | NR | 535 | 365 | NR | 665 | 102 | NR | 795 | 2 | NR | 925 | 0 | NR |
| 410 | 9 | NR | 540 | 367 | NR | 670 | 94 | NR | 800 | 2 | NR | 930 | 0 | NR |
| 415 | 15 | NR | 545 | 369 | NR | 675 | 76 | NR | 805 | 1 | NR | 935 | 0 | NR |
| 420 | 26 | NR | 550 | 370 | NR | 680 | 65 | NR | 810 | 1 | NR | 940 | 0 | NR |
| 425 | 47 | NR | 555 | 372 | NR | 685 | 56 | NR | 815 | 1 | NR | 945 | 0 | NR |
| 430 | 81 | NR | 560 | 372 | NR | 690 | 48 | NR | 820 | 1 | NR | 950 | 0 | NR |
| 435 | 143 | NR | 565 | 371 | NR | 695 | 41 | NR | 825 | 1 | NR | 955 | 0 | NR |
| 440 | 243 | NR | 570 | 370 | NR | 700 | 35 | NR | 830 | 1 | NR | 960 | 0 | NR |
| 445 | 434 | NR | 575 | 367 | NR | 705 | 30 | NR | 835 | 1 | NR | 965 | 0 | NR |
| 450 | 675 | NR | 580 | 365 | NR | 710 | 25 | NR | 840 | 1 | NR | 970 | 0 | NR |
| 455 | 615 | NR | 585 | 361 | NR | 715 | 22 | NR | 845 | 0 | NR | 975 | 0 | NR |
| 460 | 418 | NR | 590 | 356 | NR | 720 | 19 | NR | 850 | 0 | NR | 980 | 0 | NR |
| 465 | 344 | NR | 595 | 348 | NR | 725 | 16 | NR | 855 | 0 | NR | 985 | 0 | NR |
| 470 | 272 | NR | 600 | 343 | NR | 730 | 13 | NR | 860 | 0 | NR | 990 | 0 | NR |
| 475 | 206 | NR | 605 | 337 | NR | 735 | 11 | NR | 865 | 0 | NR | 995 | 0 | NR |
| 480 | 190 | NR | 610 | 362 | NR | 740 | 10 | NR | 870 | 0 | NR | 1000 | 0 | NR |
| 485 | 202 | NR | 615 | 381 | NR | 745 | 8 | NR | 875 | 0 | NR | | | |

REPORT NUMBER: SP1-2506-472-8

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 2.04

| λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360 | 0 | NR | 490 | 221 | NR | 620 | 326 | NR | 750 | 7 | NR | 880 | 0 | NR |
| 365 | 0 | NR | 495 | 250 | NR | 625 | 325 | NR | 755 | 6 | NR | 885 | 0 | NR |
| 370 | 0 | NR | 500 | 284 | NR | 630 | 1000 | NR | 760 | 5 | NR | 890 | 0 | NR |
| 375 | 0 | NR | 505 | 311 | NR | 635 | 643 | NR | 765 | 4 | NR | 895 | 0 | NR |
| 380 | 0 | NR | 510 | 329 | NR | 640 | 206 | NR | 770 | 4 | NR | 900 | 0 | NR |
| 385 | 1 | NR | 515 | 344 | NR | 645 | 199 | NR | 775 | 3 | NR | 905 | 0 | NR |
| 390 | 2 | NR | 520 | 353 | NR | 650 | 172 | NR | 780 | 3 | NR | 910 | 0 | NR |
| 395 | 3 | NR | 525 | 357 | NR | 655 | 143 | NR | 785 | 2 | NR | 915 | 0 | NR |
| 400 | 5 | NR | 530 | 362 | NR | 660 | 122 | NR | 790 | 2 | NR | 920 | 0 | NR |
| 405 | 6 | NR | 535 | 365 | NR | 665 | 102 | NR | 795 | 2 | NR | 925 | 0 | NR |
| 410 | 9 | NR | 540 | 367 | NR | 670 | 94 | NR | 800 | 2 | NR | 930 | 0 | NR |
| 415 | 15 | NR | 545 | 369 | NR | 675 | 76 | NR | 805 | 1 | NR | 935 | 0 | NR |
| 420 | 26 | NR | 550 | 370 | NR | 680 | 65 | NR | 810 | 1 | NR | 940 | 0 | NR |
| 425 | 47 | NR | 555 | 372 | NR | 685 | 56 | NR | 815 | 1 | NR | 945 | 0 | NR |
| 430 | 81 | NR | 560 | 372 | NR | 690 | 48 | NR | 820 | 1 | NR | 950 | 0 | NR |
| 435 | 143 | NR | 565 | 371 | NR | 695 | 41 | NR | 825 | 1 | NR | 955 | 0 | NR |
| 440 | 243 | NR | 570 | 370 | NR | 700 | 35 | NR | 830 | 1 | NR | 960 | 0 | NR |
| 445 | 434 | NR | 575 | 367 | NR | 705 | 30 | NR | 835 | 1 | NR | 965 | 0 | NR |
| 450 | 675 | NR | 580 | 365 | NR | 710 | 25 | NR | 840 | 1 | NR | 970 | 0 | NR |
| 455 | 615 | NR | 585 | 361 | NR | 715 | 22 | NR | 845 | 0 | NR | 975 | 0 | NR |
| 460 | 418 | NR | 590 | 356 | NR | 720 | 19 | NR | 850 | 0 | NR | 980 | 0 | NR |
| 465 | 344 | NR | 595 | 348 | NR | 725 | 16 | NR | 855 | 0 | NR | 985 | 0 | NR |
| 470 | 272 | NR | 600 | 343 | NR | 730 | 13 | NR | 860 | 0 | NR | 990 | 0 | NR |
| 475 | 206 | NR | 605 | 337 | NR | 735 | 11 | NR | 865 | 0 | NR | 995 | 0 | NR |
| 480 | 190 | NR | 610 | 362 | NR | 740 | 10 | NR | 870 | 0 | NR | 1000 | 0 | NR |
| 485 | 202 | NR | 615 | 381 | NR | 745 | 8 | NR | 875 | 0 | NR | | | |

REPORT NUMBER: SP1-2506-472-8

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 4.41


| λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360 | 0 | NR | 490 | 221 | NR | 620 | 326 | NR | 750 | 7 | NR | 880 | 0 | NR |
| 365 | 0 | NR | 495 | 250 | NR | 625 | 325 | NR | 755 | 6 | NR | 885 | 0 | NR |
| 370 | 0 | NR | 500 | 284 | NR | 630 | 1000 | NR | 760 | 5 | NR | 890 | 0 | NR |
| 375 | 0 | NR | 505 | 311 | NR | 635 | 643 | NR | 765 | 4 | NR | 895 | 0 | NR |
| 380 | 0 | NR | 510 | 329 | NR | 640 | 206 | NR | 770 | 4 | NR | 900 | 0 | NR |
| 385 | 1 | NR | 515 | 344 | NR | 645 | 199 | NR | 775 | 3 | NR | 905 | 0 | NR |
| 390 | 2 | NR | 520 | 353 | NR | 650 | 172 | NR | 780 | 3 | NR | 910 | 0 | NR |
| 395 | 3 | NR | 525 | 357 | NR | 655 | 143 | NR | 785 | 2 | NR | 915 | 0 | NR |
| 400 | 5 | NR | 530 | 362 | NR | 660 | 122 | NR | 790 | 2 | NR | 920 | 0 | NR |
| 405 | 6 | NR | 535 | 365 | NR | 665 | 102 | NR | 795 | 2 | NR | 925 | 0 | NR |
| 410 | 9 | NR | 540 | 367 | NR | 670 | 94 | NR | 800 | 2 | NR | 930 | 0 | NR |
| 415 | 15 | NR | 545 | 369 | NR | 675 | 76 | NR | 805 | 1 | NR | 935 | 0 | NR |
| 420 | 26 | NR | 550 | 370 | NR | 680 | 65 | NR | 810 | 1 | NR | 940 | 0 | NR |
| 425 | 47 | NR | 555 | 372 | NR | 685 | 56 | NR | 815 | 1 | NR | 945 | 0 | NR |
| 430 | 81 | NR | 560 | 372 | NR | 690 | 48 | NR | 820 | 1 | NR | 950 | 0 | NR |
| 435 | 143 | NR | 565 | 371 | NR | 695 | 41 | NR | 825 | 1 | NR | 955 | 0 | NR |
| 440 | 243 | NR | 570 | 370 | NR | 700 | 35 | NR | 830 | 1 | NR | 960 | 0 | NR |
| 445 | 434 | NR | 575 | 367 | NR | 705 | 30 | NR | 835 | 1 | NR | 965 | 0 | NR |
| 450 | 675 | NR | 580 | 365 | NR | 710 | 25 | NR | 840 | 1 | NR | 970 | 0 | NR |
| 455 | 615 | NR | 585 | 361 | NR | 715 | 22 | NR | 845 | 0 | NR | 975 | 0 | NR |
| 460 | 418 | NR | 590 | 356 | NR | 720 | 19 | NR | 850 | 0 | NR | 980 | 0 | NR |
| 465 | 344 | NR | 595 | 348 | NR | 725 | 16 | NR | 855 | 0 | NR | 985 | 0 | NR |
| 470 | 272 | NR | 600 | 343 | NR | 730 | 13 | NR | 860 | 0 | NR | 990 | 0 | NR |
| 475 | 206 | NR | 605 | 337 | NR | 735 | 11 | NR | 865 | 0 | NR | 995 | 0 | NR |
| 480 | 190 | NR | 610 | 362 | NR | 740 | 10 | NR | 870 | 0 | NR | 1000 | 0 | NR |
| 485 | 202 | NR | 615 | 381 | NR | 745 | 8 | NR | 875 | 0 | NR | | | |

Summary

$R_f = 90.7$
 $R_g = 100.5$
 CIE $R_a = 94.3$
 $R_9 = 72.3$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 91 | CES51 = 98 | CES76 = 83 |
| CES02 = 61 | CES27 = 92 | CES52 = 98 | CES77 = 87 |
| CES03 = 31 | CES28 = 94 | CES53 = 97 | CES78 = 80 |
| CES04 = 69 | CES29 = 94 | CES54 = 93 | CES79 = 94 |
| CES05 = 48 | CES30 = 93 | CES55 = 92 | CES80 = 91 |
| CES06 = 50 | CES31 = 95 | CES56 = 95 | CES81 = 84 |
| CES07 = 41 | CES32 = 86 | CES57 = 94 | CES82 = 96 |
| CES08 = 40 | CES33 = 99 | CES58 = 94 | CES83 = 96 |
| CES09 = 29 | CES34 = 90 | CES59 = 97 | CES84 = 93 |
| CES10 = 73 | CES35 = 94 | CES60 = 92 | CES85 = 83 |
| CES11 = 56 | CES36 = 81 | CES61 = 92 | CES86 = 86 |
| CES12 = 62 | CES37 = 92 | CES62 = 86 | CES87 = 91 |
| CES13 = 43 | CES38 = 88 | CES63 = 92 | CES88 = 98 |
| CES14 = 74 | CES39 = 99 | CES64 = 89 | CES89 = 87 |
| CES15 = 71 | CES40 = 97 | CES65 = 88 | CES90 = 98 |
| CES16 = 47 | CES41 = 97 | CES66 = 85 | CES91 = 73 |
| CES17 = 48 | CES42 = 90 | CES67 = 84 | CES92 = 79 |
| CES18 = 56 | CES43 = 91 | CES68 = 86 | CES93 = 87 |
| CES19 = 70 | CES44 = 99 | CES69 = 87 | CES94 = 78 |
| CES20 = 65 | CES45 = 95 | CES70 = 83 | CES95 = 83 |
| CES21 = 85 | CES46 = 97 | CES71 = 77 | CES96 = 92 |
| CES22 = 77 | CES47 = 95 | CES72 = 92 | CES97 = 95 |
| CES23 = 91 | CES48 = 93 | CES73 = 77 | CES98 = 95 |
| CES24 = 90 | CES49 = 95 | CES74 = 92 | CES99 = 94 |
| CES25 = 70 | CES50 = 98 | CES75 = 79 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)