

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: METALUX

Report Number: P1431843

Luminaire Tested: EHBR1-48-UNV-TASM-L950

Issue Date: 3/13/2026

Test Information

Test Method: LM-79-2019
Report Number: P1431843
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2601-654-4)
Test Lab: INNOVATION CENTER
Issue Date: 3/13/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: METALUX
Catalog Number: EHBR1-48-UNV-TASM-L950
Description: Elevate Round Highbay at, 48000 lumens, 5000K 90CRI LEDs with TASM lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 44107.9 lumens
Efficiency: N/A
Efficacy: 170.6 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.84 / 0.9
Luminous Opening: Circular (Dia: 1.71' x H: 0')
CIE Type: Direct

Input Watts (W): 258.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1431843
CATALOG NUMBER: EHBR1-48-UNV-TASM-L950

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - - - 90°-270° - · - 135°-315°



TEST NUMBER: P1431843
 CATALOG NUMBER: EHBR1-48-UNV-TASM-L950

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100
1	112	108	105	103	109	106	104	101	102	100	98	98	97	95	95	93	92	90	90	90
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81	81	81
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74	74	74
4	93	84	77	72	91	83	77	72	80	75	71	78	74	70	76	72	69	67	67	67
5	87	78	71	66	86	77	70	65	75	69	65	73	68	64	71	67	64	62	62	62
6	82	72	65	60	81	71	65	60	70	64	60	68	63	59	67	62	59	57	57	57
7	78	67	60	56	76	67	60	56	65	59	55	64	59	55	63	58	55	53	53	53
8	74	63	56	52	72	62	56	52	61	55	51	60	55	51	59	54	51	49	49	49
9	70	59	53	48	69	59	52	48	58	52	48	57	51	48	56	51	47	46	46	46
10	66	56	49	45	65	55	49	45	54	49	45	54	48	45	53	48	45	43	43	43

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	185247	185247	185247	185247
5°	185320	197702	185320	175703
10°	184246	204112	184246	167382
15°	180011	190962	180011	155658
20°	169537	154200	169537	139621
25°	151168	107632	151168	117877
30°	123724	70582	123724	88901
35°	89518	46112	89518	59703
40°	58446	32096	58446	38022
45°	37502	25143	37502	27397
50°	28220	21649	28220	23124
55°	23413	20040	23413	20742
60°	20689	19480	20689	19599
65°	19374	19299	19374	19217
70°	19073	19643	19073	19389
75°	18923	20158	18923	19556
80°	18503	21183	18503	19804
85°	15583	19688	15583	18772

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 52726 cd/sqm



TEST NUMBER: P1431843
 CATALOG NUMBER: EHBR1-48-UNV-TASM-L950

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	3750.8	8.5
10°-20°	10204.3	23.1
20°-30°	11967.6	27.1
30°-40°	8322.7	18.9
40°-50°	4136.0	9.4
50°-60°	2473.8	5.6
60°-70°	1741.1	3.9
70°-80°	1121.6	2.5
80°-90°	356.2	0.8
90°-100°	2.1	0.0
100°-110°	2.5	0.0
110°-120°	2.5	0.0
120°-130°	3.2	0.0
130°-140°	4.3	0.0
140°-150°	5.2	0.0
150°-160°	5.8	0.0
160°-170°	5.7	0.0
170°-180°	2.4	0.0
0°-30°	25922.7	58.8
0°-40°	34245.4	77.6
0°-60°	40855.2	92.6
0°-90°	44074.1	99.9
90°-120°	7.1	0.0
90°-150°	19.8	0.0
90°-180°	34.0	0.1
0°-180°	44107.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	39447	39447	39447	39447	39447	
5°	39312	41939	39312	37272	39312	3731
15°	37026	39278	37026	32017	37026	10347
25°	29174	20772	29174	22749	29174	13208
35°	15615	8043	15615	10414	15615	9748
45°	5647	3786	5647	4125	5647	4621
55°	2860	2448	2860	2533	2860	2615
65°	1744	1737	1744	1729	1744	1751
75°	1043	1111	1043	1078	1043	1095
85°	289	365	289	348	289	322
90°	1	6	1	1	1	14
95°	2	6	2	1	2	1
105°	2	7	2	2	2	2
115°	2	7	2	2	2	2
125°	3	7	3	2	3	3
135°	6	8	6	3	6	5
145°	9	10	9	8	9	5
155°	12	13	12	14	12	6
165°	20	24	20	21	20	5
175°	26	32	26	25	26	2
180°	27	27	27	27	27	



TEST NUMBER: P1431843
 CATALOG NUMBER: EHBR1-48-UNV-TASM-L950

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
0°	39447.0	39447.0	39447.0	39447.0	39447.0	39447.0	39447.0	39447.0	39447.0	39447.0	39447.0
2.5°	39424.2	39933.8	40346.5	40618.7	40753.4	40618.7	40346.5	39933.8	39424.2	38917.4	38569.0
5°	39312.5	40333.2	41197.9	41763.8	41939.1	41763.8	41197.9	40333.2	39312.5	38347.9	37708.1
7.5°	39045.4	40635.7	41920.6	42581.1	42742.4	42581.1	41920.6	40635.7	39045.4	37679.9	36871.4
10°	38637.9	40826.6	42311.1	42784.6	42803.8	42784.6	42311.1	40826.6	38637.9	36798.2	35844.8
12.5°	37987.7	40758.6	42180.2	42024.8	41672.1	42024.8	42180.2	40758.6	37987.7	35721.3	34518.5
15°	37026.0	40355.4	41351.1	40086.9	39278.4	40086.9	41351.1	40355.4	37026.0	34267.0	32872.0
17.5°	35670.9	39600.9	39620.1	37119.2	35594.0	37119.2	39620.1	39600.9	35670.9	32488.8	30952.4
20°	33924.6	38390.8	37236.8	32662.6	30855.5	32662.6	37236.8	38390.8	33924.6	30386.6	28879.1
22.5°	31735.0	36759.0	33917.9	28179.3	25714.0	28179.3	33917.9	36759.0	31735.0	27941.9	26373.0
25°	29174.2	34759.6	30347.4	23294.4	20772.0	23294.4	30347.4	34759.6	29174.2	25028.9	23610.3
27.5°	26162.2	32225.5	26545.3	19035.2	16708.2	19035.2	26545.3	32225.5	26162.2	22021.4	20572.3
30°	22816.5	28976.7	22588.7	15159.2	13016.3	15159.2	22588.7	28976.7	22816.5	18642.5	17345.1
32.5°	19070.7	25792.3	18788.9	12146.5	10331.3	12146.5	18788.9	25792.3	19070.7	15418.2	14062.3
35°	15614.9	21808.3	15362.7	9544.2	8043.4	9544.2	15362.7	21808.3	15614.9	12374.3	11042.9
37.5°	12254.5	18044.0	12246.4	7685.4	6524.1	7685.4	12246.4	18044.0	12254.5	9620.4	8539.8
40°	9533.9	14108.9	9595.3	6135.0	5235.6	6135.0	9595.3	14108.9	9533.9	7320.0	6628.4
42.5°	7223.9	10788.4	7541.9	5035.1	4447.0	5035.1	7541.9	10788.4	7223.9	5767.4	5249.6
45°	5646.8	7939.1	5889.5	4248.1	3785.8	4248.1	5889.5	7939.1	5646.8	4644.5	4296.9
47.5°	4598.6	6135.8	4773.2	3643.7	3319.7	3643.7	4773.2	6135.8	4598.6	3928.5	3668.1
50°	3862.7	4708.1	3963.2	3180.6	2963.2	3180.6	3963.2	4708.1	3862.7	3364.1	3190.3
52.5°	3318.2	3839.7	3375.2	2834.5	2688.0	2834.5	3375.2	3839.7	3318.2	2943.2	2835.3
55°	2859.6	3228.0	2935.1	2549.0	2447.7	2549.0	2935.1	3228.0	2859.6	2619.3	2539.4
57.5°	2511.3	2738.4	2549.0	2305.6	2238.3	2305.6	2549.0	2738.4	2511.3	2330.8	2287.9
60°	2202.8	2371.5	2249.4	2093.3	2074.1	2093.3	2249.4	2371.5	2202.8	2097.0	2069.0
62.5°	1965.4	2071.9	1989.0	1902.5	1885.5	1902.5	1989.0	2071.9	1965.4	1884.0	1889.2
65°	1743.5	1842.6	1777.5	1730.8	1736.8	1730.8	1777.5	1842.6	1743.5	1705.8	1713.8
67.5°	1571.9	1623.6	1595.5	1568.9	1575.6	1568.9	1595.5	1623.6	1571.9	1534.9	1547.4
70°	1389.1	1444.6	1415.8	1419.5	1430.6	1419.5	1415.8	1444.6	1389.1	1378.1	1387.6
72.5°	1214.5	1257.5	1247.9	1256.7	1268.6	1256.7	1247.9	1257.5	1214.5	1213.1	1213.8
75°	1042.9	1075.5	1079.9	1092.5	1111.0	1092.5	1079.9	1075.5	1042.9	1031.9	1045.2
77.5°	855.8	892.8	906.9	923.9	951.2	923.9	906.9	892.8	855.8	863.2	869.8
80°	684.2	701.2	732.3	744.9	783.3	744.9	732.3	701.2	684.2	671.7	681.2
82.5°	500.8	516.3	543.0	566.6	588.8	566.6	543.0	516.3	500.8	494.8	495.6
85°	289.2	312.9	330.7	358.7	365.4	358.7	330.7	312.9	289.2	295.9	289.2
87.5°	101.4	108.7	124.2	135.4	136.1	135.4	124.2	108.7	101.4	103.6	93.9
90°	0.7	1.5	2.2	4.5	5.9	4.5	2.2	1.5	0.7	0.7	0.7
92.5°	0.7	1.5	2.2	4.5	5.9	4.5	2.2	1.5	0.7	0.7	0.7
95°	1.5	1.5	2.2	4.5	5.9	4.5	2.2	1.5	1.5	0.7	0.7
97.5°	1.5	1.5	2.2	4.5	5.9	4.5	2.2	1.5	1.5	0.7	0.7
100°	1.5	1.5	2.2	4.5	5.9	4.5	2.2	1.5	1.5	1.5	0.7
102.5°	1.5	2.2	3.0	5.2	5.9	5.2	3.0	2.2	1.5	1.5	0.7
105°	1.5	2.2	3.0	5.2	6.7	5.2	3.0	2.2	1.5	1.5	0.7
107.5°	1.5	2.2	3.0	5.2	6.7	5.2	3.0	2.2	1.5	1.5	1.5
110°	1.5	2.2	3.0	5.2	6.7	5.2	3.0	2.2	1.5	1.5	1.5



TEST NUMBER: P1431843
 CATALOG NUMBER: EHBR1-48-UNV-TASM-L950

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
112.5°	1.5	2.2	3.0	5.2	6.7	5.2	3.0	2.2	1.5	1.5	1.5
115°	2.2	2.2	3.0	5.2	6.7	5.2	3.0	2.2	2.2	1.5	1.5
117.5°	2.2	2.2	3.0	5.2	6.7	5.2	3.0	2.2	2.2	2.2	1.5
120°	2.2	2.2	3.7	5.2	6.7	5.2	3.7	2.2	2.2	2.2	1.5
122.5°	3.0	3.0	3.7	5.9	6.7	5.9	3.7	3.0	3.0	3.0	2.2
125°	3.0	3.0	4.5	5.9	7.4	5.9	4.5	3.0	3.0	3.7	3.0
127.5°	3.7	3.7	4.5	5.9	7.4	5.9	4.5	3.7	3.7	3.7	3.0
130°	4.5	3.7	4.5	6.7	7.4	6.7	4.5	3.7	4.5	4.5	3.7
132.5°	5.2	4.5	5.2	7.4	8.2	7.4	5.2	4.5	5.2	5.9	5.2
135°	5.9	4.5	5.9	6.7	8.2	6.7	5.9	4.5	5.9	6.7	5.2
137.5°	6.7	5.2	5.9	7.4	8.2	7.4	5.9	5.2	6.7	7.4	6.7
140°	7.4	5.9	5.9	7.4	8.9	7.4	5.9	5.9	7.4	7.4	7.4
142.5°	8.2	6.7	6.7	8.2	8.9	8.2	6.7	6.7	8.2	8.2	8.2
145°	8.9	8.2	7.4	8.2	9.6	8.2	7.4	8.2	8.9	8.2	8.9
147.5°	8.9	8.2	8.2	8.9	10.3	8.9	8.2	8.2	8.9	8.9	9.6
150°	9.6	9.6	8.9	9.6	11.1	9.6	8.9	9.6	9.6	9.6	10.3
152.5°	10.3	10.3	10.3	11.1	11.8	11.1	10.3	10.3	10.3	10.3	11.1
155°	11.8	11.8	11.8	12.5	13.3	12.5	11.8	11.8	11.8	11.1	12.5
157.5°	13.3	14.0	14.0	14.8	15.5	14.8	14.0	14.0	13.3	13.3	14.0
160°	16.3	16.3	17.0	17.7	18.5	17.7	17.0	16.3	16.3	15.5	16.3
162.5°	17.7	17.7	19.2	20.0	21.5	20.0	19.2	17.7	17.7	17.7	17.7
165°	20.0	20.0	21.5	22.9	24.4	22.9	21.5	20.0	20.0	19.2	19.2
167.5°	21.5	21.5	22.9	25.2	26.7	25.2	22.9	21.5	21.5	20.7	20.7
170°	22.2	22.9	24.4	26.7	28.2	26.7	24.4	22.9	22.2	22.2	21.5
172.5°	24.4	24.4	26.7	28.8	30.3	28.8	26.7	24.4	24.4	23.7	23.7
175°	25.9	26.7	28.2	30.3	31.8	30.3	28.2	26.7	25.9	25.2	25.2
177.5°	25.9	27.4	28.8	31.0	32.5	31.0	28.8	27.4	25.9	25.2	25.2
180°	27.4	27.4	27.4	27.4	27.4	27.4	27.4	27.4	27.4	27.4	27.4



TEST NUMBER: P1431843
 CATALOG NUMBER: EHBR1-48-UNV-TASM-L950

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
0°	39447.0	39447.0	39447.0	39447.0	39447.0	39447.0
2.5°	38301.2	38276.2	38301.2	38569.0	38917.4	39424.2
5°	37411.4	37272.3	37411.4	37708.1	38347.9	39312.5
7.5°	36375.1	36294.5	36375.1	36871.4	37679.9	39045.4
10°	35284.0	35101.4	35284.0	35844.8	36798.2	38637.9
12.5°	33939.3	33697.5	33939.3	34518.5	35721.3	37987.7
15°	32229.1	32016.9	32229.1	32872.0	34267.0	37026.0
17.5°	30394.0	30201.7	30394.0	30952.4	32488.8	35670.9
20°	28089.1	27938.2	28089.1	28879.1	30386.6	33924.6
22.5°	25671.0	25529.7	25671.0	26373.0	27941.9	31735.0
25°	22826.2	22749.3	22826.2	23610.3	25028.9	29174.2
27.5°	19752.0	19621.1	19752.0	20572.3	22021.4	26162.2
30°	16611.3	16394.6	16611.3	17345.1	18642.5	22816.5
32.5°	13539.3	13383.2	13539.3	14062.3	15418.2	19070.7
35°	10570.3	10414.2	10570.3	11042.9	12374.3	15614.9
37.5°	8236.5	7960.6	8236.5	8539.8	9620.4	12254.5
40°	6246.7	6202.3	6246.7	6628.4	7320.0	9533.9
42.5°	5085.4	4964.8	5085.4	5249.6	5767.4	7223.9
45°	4172.7	4125.3	4172.7	4296.9	4644.5	5646.8
47.5°	3588.2	3609.0	3588.2	3668.1	3928.5	4598.6
50°	3152.6	3165.1	3152.6	3190.3	3364.1	3862.7
52.5°	2831.6	2820.4	2831.6	2835.3	2943.2	3318.2
55°	2547.5	2533.4	2547.5	2539.4	2619.3	2859.6
57.5°	2299.0	2309.3	2299.0	2287.9	2330.8	2511.3
60°	2077.0	2086.7	2077.0	2069.0	2097.0	2202.8
62.5°	1889.9	1895.9	1889.9	1889.2	1884.0	1965.4
65°	1722.8	1729.4	1722.8	1713.8	1705.8	1743.5
67.5°	1563.0	1563.0	1563.0	1547.4	1534.9	1571.9
70°	1412.8	1412.1	1412.8	1387.6	1378.1	1389.1
72.5°	1232.3	1250.1	1232.3	1213.8	1213.1	1214.5
75°	1057.1	1077.8	1057.1	1045.2	1031.9	1042.9
77.5°	879.5	911.3	879.5	869.8	863.2	855.8
80°	697.5	732.3	697.5	681.2	671.7	684.2
82.5°	515.6	541.5	515.6	495.6	494.8	500.8
85°	307.0	348.4	307.0	289.2	295.9	289.2
87.5°	98.4	125.7	98.4	93.9	103.6	101.4
90°	0.7	0.7	0.7	0.7	0.7	0.7
92.5°	0.7	0.7	0.7	0.7	0.7	0.7
95°	0.7	0.7	0.7	0.7	0.7	1.5
97.5°	0.7	1.5	0.7	0.7	0.7	1.5
100°	0.7	1.5	0.7	0.7	1.5	1.5
102.5°	0.7	1.5	0.7	0.7	1.5	1.5
105°	0.7	1.5	0.7	0.7	1.5	1.5
107.5°	0.7	1.5	0.7	1.5	1.5	1.5
110°	0.7	1.5	0.7	1.5	1.5	1.5



TEST NUMBER: P1431843
 CATALOG NUMBER: EHBR1-48-UNV-TASM-L950

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
112.5°	0.7	1.5	0.7	1.5	1.5	1.5
115°	0.7	1.5	0.7	1.5	1.5	2.2
117.5°	0.7	1.5	0.7	1.5	2.2	2.2
120°	0.7	1.5	0.7	1.5	2.2	2.2
122.5°	1.5	1.5	1.5	2.2	3.0	3.0
125°	1.5	2.2	1.5	3.0	3.7	3.0
127.5°	1.5	2.2	1.5	3.0	3.7	3.7
130°	2.2	2.2	2.2	3.7	4.5	4.5
132.5°	3.0	3.0	3.0	5.2	5.9	5.2
135°	3.7	3.0	3.7	5.2	6.7	5.9
137.5°	4.5	3.7	4.5	6.7	7.4	6.7
140°	5.9	5.2	5.9	7.4	7.4	7.4
142.5°	6.7	6.7	6.7	8.2	8.2	8.2
145°	8.2	8.2	8.2	8.9	8.2	8.9
147.5°	9.6	9.6	9.6	9.6	8.9	8.9
150°	11.1	11.1	11.1	10.3	9.6	9.6
152.5°	11.8	12.5	11.8	11.1	10.3	10.3
155°	13.3	14.0	13.3	12.5	11.1	11.8
157.5°	14.8	16.3	14.8	14.0	13.3	13.3
160°	17.0	17.7	17.0	16.3	15.5	16.3
162.5°	18.5	19.2	18.5	17.7	17.7	17.7
165°	20.0	20.7	20.0	19.2	19.2	20.0
167.5°	20.7	20.7	20.7	20.7	20.7	21.5
170°	21.5	22.2	21.5	21.5	22.2	22.2
172.5°	22.9	23.7	22.9	23.7	23.7	24.4
175°	24.4	25.2	24.4	25.2	25.2	25.9
177.5°	25.2	25.9	25.2	25.2	25.2	25.9
180°	27.4	27.4	27.4	27.4	27.4	27.4



TEST NUMBER: P1431843
 CATALOG NUMBER: EHBR1-48-UNV-TASM-L950

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	19.79	21.00	20.16	21.31	21.63	19.11	20.32	19.48	20.63	20.95
	3H	21.43	22.50	21.81	22.84	23.21	21.06	22.13	21.44	22.47	22.84
	4H	22.14	23.14	22.54	23.49	23.88	21.92	22.92	22.33	23.27	23.66
	6H	22.71	23.63	23.13	24.00	24.40	22.67	23.59	23.09	23.97	24.36
	8H	22.91	23.78	23.35	24.18	24.58	22.96	23.83	23.39	24.22	24.63
	12H	23.03	23.87	23.47	24.25	24.68	23.16	23.99	23.59	24.37	24.80
4H	2H	20.25	21.26	20.66	21.61	22.00	19.74	20.74	20.15	21.10	21.48
	3H	22.16	22.99	22.58	23.40	23.80	21.92	22.74	22.33	23.15	23.56
	4H	23.02	23.76	23.46	24.18	24.63	22.92	23.65	23.35	24.08	24.52
	6H	23.75	24.38	24.21	24.83	25.30	23.81	24.45	24.28	24.90	25.37
	8H	24.00	24.60	24.48	25.05	25.52	24.16	24.75	24.63	25.20	25.67
	12H	24.17	24.70	24.66	25.18	25.66	24.41	24.93	24.89	25.42	25.89
8H	4H	23.33	23.93	23.80	24.38	24.85	23.26	23.85	23.73	24.30	24.77
	6H	24.21	24.69	24.71	25.19	25.68	24.31	24.79	24.81	25.29	25.78
	8H	24.56	24.99	25.08	25.51	26.00	24.76	25.19	25.28	25.71	26.20
	12H	24.82	25.20	25.34	25.69	26.27	25.11	25.49	25.63	25.99	26.56
12H	4H	23.36	23.88	23.85	24.37	24.85	23.29	23.81	23.77	24.30	24.77
	6H	24.28	24.71	24.80	25.23	25.72	24.38	24.81	24.91	25.33	25.83
	8H	24.69	25.07	25.21	25.57	26.14	24.90	25.28	25.42	25.77	26.35

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2506-472-8

Test Date: 08/04/2025

Luminaire Tested: EHBR-60-L950-N

Data in this report applies to families of products including EHBR-60-L950-N

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2506-472-8
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 08/05/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Metalux
 Catalog Number: **EHBR-60-L950-N**
 Description: Elevate Round Highbay at, 60000 lumens, 5000K 90CRI LEDs with N lens

Spectral Parameters

CCT (K): 4901
 CIE u': 0.2131
 CIE v': 0.4853
 Duv: -0.0008
 CIE x: 0.3477
 CIE y: 0.3520
 CIE z: 0.3003
 Peak Wavelength (nm): 630
 Dominant Wavelength (nm): 574
 Purity: 9.953987
 Rf: 90.7
 Rg: 100.5

CRI (Ra):	94.3		
R1:	95.8	R9:	72.3
R2:	96.5	R10:	89.1
R3:	94.4	R11:	94.9
R4:	95.3	R12:	68.4
R5:	94.1	R13:	96.4
R6:	92.5	R14:	96.4
R7:	95.5	R15:	93.9
R8:	90.1		



Test Conditions

Stabilization Time: 35M
 Operation Time: 1H 35M
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP1-2506-472-8

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2506-472-8

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 5000K 4-step quadrangle

REPORT NUMBER: SP1-2506-472-8

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)
360	0	NR	490	221	NR	620	326	NR	750	7	NR	880	0	NR
365	0	NR	495	250	NR	625	325	NR	755	6	NR	885	0	NR
370	0	NR	500	284	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	311	NR	635	643	NR	765	4	NR	895	0	NR
380	0	NR	510	329	NR	640	206	NR	770	4	NR	900	0	NR
385	1	NR	515	344	NR	645	199	NR	775	3	NR	905	0	NR
390	2	NR	520	353	NR	650	172	NR	780	3	NR	910	0	NR
395	3	NR	525	357	NR	655	143	NR	785	2	NR	915	0	NR
400	5	NR	530	362	NR	660	122	NR	790	2	NR	920	0	NR
405	6	NR	535	365	NR	665	102	NR	795	2	NR	925	0	NR
410	9	NR	540	367	NR	670	94	NR	800	2	NR	930	0	NR
415	15	NR	545	369	NR	675	76	NR	805	1	NR	935	0	NR
420	26	NR	550	370	NR	680	65	NR	810	1	NR	940	0	NR
425	47	NR	555	372	NR	685	56	NR	815	1	NR	945	0	NR
430	81	NR	560	372	NR	690	48	NR	820	1	NR	950	0	NR
435	143	NR	565	371	NR	695	41	NR	825	1	NR	955	0	NR
440	243	NR	570	370	NR	700	35	NR	830	1	NR	960	0	NR
445	434	NR	575	367	NR	705	30	NR	835	1	NR	965	0	NR
450	675	NR	580	365	NR	710	25	NR	840	1	NR	970	0	NR
455	615	NR	585	361	NR	715	22	NR	845	0	NR	975	0	NR
460	418	NR	590	356	NR	720	19	NR	850	0	NR	980	0	NR
465	344	NR	595	348	NR	725	16	NR	855	0	NR	985	0	NR
470	272	NR	600	343	NR	730	13	NR	860	0	NR	990	0	NR
475	206	NR	605	337	NR	735	11	NR	865	0	NR	995	0	NR
480	190	NR	610	362	NR	740	10	NR	870	0	NR	1000	0	NR
485	202	NR	615	381	NR	745	8	NR	875	0	NR			

REPORT NUMBER: SP1-2506-472-8

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 2.04

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	221	NR	620	326	NR	750	7	NR	880	0	NR
365	0	NR	495	250	NR	625	325	NR	755	6	NR	885	0	NR
370	0	NR	500	284	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	311	NR	635	643	NR	765	4	NR	895	0	NR
380	0	NR	510	329	NR	640	206	NR	770	4	NR	900	0	NR
385	1	NR	515	344	NR	645	199	NR	775	3	NR	905	0	NR
390	2	NR	520	353	NR	650	172	NR	780	3	NR	910	0	NR
395	3	NR	525	357	NR	655	143	NR	785	2	NR	915	0	NR
400	5	NR	530	362	NR	660	122	NR	790	2	NR	920	0	NR
405	6	NR	535	365	NR	665	102	NR	795	2	NR	925	0	NR
410	9	NR	540	367	NR	670	94	NR	800	2	NR	930	0	NR
415	15	NR	545	369	NR	675	76	NR	805	1	NR	935	0	NR
420	26	NR	550	370	NR	680	65	NR	810	1	NR	940	0	NR
425	47	NR	555	372	NR	685	56	NR	815	1	NR	945	0	NR
430	81	NR	560	372	NR	690	48	NR	820	1	NR	950	0	NR
435	143	NR	565	371	NR	695	41	NR	825	1	NR	955	0	NR
440	243	NR	570	370	NR	700	35	NR	830	1	NR	960	0	NR
445	434	NR	575	367	NR	705	30	NR	835	1	NR	965	0	NR
450	675	NR	580	365	NR	710	25	NR	840	1	NR	970	0	NR
455	615	NR	585	361	NR	715	22	NR	845	0	NR	975	0	NR
460	418	NR	590	356	NR	720	19	NR	850	0	NR	980	0	NR
465	344	NR	595	348	NR	725	16	NR	855	0	NR	985	0	NR
470	272	NR	600	343	NR	730	13	NR	860	0	NR	990	0	NR
475	206	NR	605	337	NR	735	11	NR	865	0	NR	995	0	NR
480	190	NR	610	362	NR	740	10	NR	870	0	NR	1000	0	NR
485	202	NR	615	381	NR	745	8	NR	875	0	NR			

REPORT NUMBER: SP1-2506-472-8

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 4.41

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	221	NR	620	326	NR	750	7	NR	880	0	NR
365	0	NR	495	250	NR	625	325	NR	755	6	NR	885	0	NR
370	0	NR	500	284	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	311	NR	635	643	NR	765	4	NR	895	0	NR
380	0	NR	510	329	NR	640	206	NR	770	4	NR	900	0	NR
385	1	NR	515	344	NR	645	199	NR	775	3	NR	905	0	NR
390	2	NR	520	353	NR	650	172	NR	780	3	NR	910	0	NR
395	3	NR	525	357	NR	655	143	NR	785	2	NR	915	0	NR
400	5	NR	530	362	NR	660	122	NR	790	2	NR	920	0	NR
405	6	NR	535	365	NR	665	102	NR	795	2	NR	925	0	NR
410	9	NR	540	367	NR	670	94	NR	800	2	NR	930	0	NR
415	15	NR	545	369	NR	675	76	NR	805	1	NR	935	0	NR
420	26	NR	550	370	NR	680	65	NR	810	1	NR	940	0	NR
425	47	NR	555	372	NR	685	56	NR	815	1	NR	945	0	NR
430	81	NR	560	372	NR	690	48	NR	820	1	NR	950	0	NR
435	143	NR	565	371	NR	695	41	NR	825	1	NR	955	0	NR
440	243	NR	570	370	NR	700	35	NR	830	1	NR	960	0	NR
445	434	NR	575	367	NR	705	30	NR	835	1	NR	965	0	NR
450	675	NR	580	365	NR	710	25	NR	840	1	NR	970	0	NR
455	615	NR	585	361	NR	715	22	NR	845	0	NR	975	0	NR
460	418	NR	590	356	NR	720	19	NR	850	0	NR	980	0	NR
465	344	NR	595	348	NR	725	16	NR	855	0	NR	985	0	NR
470	272	NR	600	343	NR	730	13	NR	860	0	NR	990	0	NR
475	206	NR	605	337	NR	735	11	NR	865	0	NR	995	0	NR
480	190	NR	610	362	NR	740	10	NR	870	0	NR	1000	0	NR
485	202	NR	615	381	NR	745	8	NR	875	0	NR			

Summary

$R_f = 90.7$
 $R_g = 100.5$
 CIE $R_a = 94.3$
 $R_9 = 72.3$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 85	CES26 = 91	CES51 = 98	CES76 = 83
CES02 = 61	CES27 = 92	CES52 = 98	CES77 = 87
CES03 = 31	CES28 = 94	CES53 = 97	CES78 = 80
CES04 = 69	CES29 = 94	CES54 = 93	CES79 = 94
CES05 = 48	CES30 = 93	CES55 = 92	CES80 = 91
CES06 = 50	CES31 = 95	CES56 = 95	CES81 = 84
CES07 = 41	CES32 = 86	CES57 = 94	CES82 = 96
CES08 = 40	CES33 = 99	CES58 = 94	CES83 = 96
CES09 = 29	CES34 = 90	CES59 = 97	CES84 = 93
CES10 = 73	CES35 = 94	CES60 = 92	CES85 = 83
CES11 = 56	CES36 = 81	CES61 = 92	CES86 = 86
CES12 = 62	CES37 = 92	CES62 = 86	CES87 = 91
CES13 = 43	CES38 = 88	CES63 = 92	CES88 = 98
CES14 = 74	CES39 = 99	CES64 = 89	CES89 = 87
CES15 = 71	CES40 = 97	CES65 = 88	CES90 = 98
CES16 = 47	CES41 = 97	CES66 = 85	CES91 = 73
CES17 = 48	CES42 = 90	CES67 = 84	CES92 = 79
CES18 = 56	CES43 = 91	CES68 = 86	CES93 = 87
CES19 = 70	CES44 = 99	CES69 = 87	CES94 = 78
CES20 = 65	CES45 = 95	CES70 = 83	CES95 = 83
CES21 = 85	CES46 = 97	CES71 = 77	CES96 = 92
CES22 = 77	CES47 = 95	CES72 = 92	CES97 = 95
CES23 = 91	CES48 = 93	CES73 = 77	CES98 = 95
CES24 = 90	CES49 = 95	CES74 = 92	CES99 = 94
CES25 = 70	CES50 = 98	CES75 = 79	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)