Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: METALUX

Report Number: P1594575

Luminaire Tested: FLXB-1224-N-MED-4000K

Issue Date: 10/2/2026

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-2019
Report Number:	P1594575
	TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (A2601782A001)
Test Lab:	INNOVATION CENTER
Issue Date:	10/2/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	METALUX
Catalog Number:	FLXB-1224-N-MED-4000K
Description:	1224 FlexBay Linear High bay at N beam, MED lumen, 4000K CCT settings
Light Source:	-
Ballast/Driver:	-

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	18876.0 lumens
Efficiency:	N/A
Efficacy:	168.2 lumens/watt
Spacing Criteria (0/90/45):	1.53 / 1 / 1.06
Luminous Opening:	Rectangular (W 1.04' x L: 1.19' x H: 0')
CIE Type:	Direct


Input Watts (W):	112.2
Input Voltage (V):	NR
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	NR
Total Harmonic Distortion (THDi):	NR
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594575
CATALOG NUMBER: FLXB-1224-N-MED-4000K

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594575
CATALOG NUMBER: FLXB-1224-N-MED-4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	91	90
2	104	98	92	88	102	96	91	87	93	89	85	89	86	83	87	84	81	80
3	97	89	82	77	95	87	81	76	84	79	75	82	78	74	79	76	73	71
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64
5	84	74	67	61	83	73	66	61	71	65	60	69	64	60	67	63	59	57
6	79	68	61	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47
8	70	58	51	46	68	58	51	46	56	50	46	55	49	45	54	49	45	43
9	66	54	47	42	64	54	47	42	52	46	42	51	46	42	51	45	42	40
10	62	50	44	39	61	50	43	39	49	43	39	48	43	39	47	42	38	37

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	100878	100878	100878	100878
5°	101309	100828	101309	100828
10°	102476	100364	102476	100364
15°	104554	98628	104554	98628
20°	107450	94379	107450	94379
25°	111578	85615	111578	85615
30°	116991	63851	116991	63851
35°	123606	29634	123606	29634
40°	130858	9254	130858	9254
45°	135400	6414	135400	6414
50°	137474	6303	137474	6303
55°	128352	6214	128352	6214
60°	115102	6571	115102	6571
65°	89853	6368	89853	6368
70°	67646	6531	67646	6531
75°	41474	5056	41474	5056
80°	27300	3648	27300	3648
85°	13109	1667	13109	1667

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 50°
Luminance: 137474 cd/sqm

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594575
CATALOG NUMBER: FLXB-1224-N-MED-4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1099.8	5.8
10°-20°	3174.7	16.8
20°-30°	4700.5	24.9
30°-40°	4390.2	23.3
40°-50°	2484.8	13.2
50°-60°	1560.1	8.3
60°-70°	984.0	5.2
70°-80°	413.7	2.2
80°-90°	68.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	8975.0	47.5
0°-40°	13365.2	70.8
0°-60°	17410.2	92.2
0°-90°	18876.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	18876.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	11593	11593	11593	11593	11593	
5°	11598	11543	11598	11543	11598	1107
15°	11606	10948	11606	10948	11606	3289
25°	11622	8917	11622	8917	11622	5381
35°	11636	2790	11636	2790	11636	7295
45°	11003	521	11003	521	11003	8454
55°	8461	410	8461	410	8461	7536
65°	4364	309	4364	309	4364	4399
75°	1234	150	1234	150	1234	1430
85°	131	17	131	17	131	204
90°	15	2	15	2	15	

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594575
CATALOG NUMBER: FLXB-1224-N-MED-4000K

CANDELA DISTRIBUTION (FULL):

	0°	30°	60°	90°	120°	150°	180°	210°	240°	270°	300°
0°	11593.2	11593.2	11593.2	11593.2	11593.2	11593.2	11593.2	11593.2	11593.2	11593.2	11593.2
0.5°	11593.2	11593.2	11593.2	11593.2	11593.2	11593.2	11593.2	11593.2	11593.2	11593.2	11593.2
1°	11615.1	11604.8	11590.5	11631.8	11499.1	11590.0	11615.1	11604.8	11590.5	11631.8	11499.1
1.5°	11615.1	11610.2	11593.9	11603.3	11499.1	11609.2	11615.1	11610.2	11593.9	11603.3	11499.1
2°	11588.0	11618.0	11567.9	11603.3	11499.1	11604.8	11588.0	11618.0	11567.9	11603.3	11499.1
2.5°	11588.0	11618.0	11556.6	11592.0	11499.1	11604.8	11588.0	11618.0	11556.6	11592.0	11499.1
3°	11613.1	11606.7	11562.0	11592.0	11499.1	11605.2	11613.1	11606.7	11562.0	11592.0	11499.1
3.5°	11613.1	11601.3	11552.1	11578.2	11462.2	11605.2	11613.1	11601.3	11552.1	11578.2	11462.2
4°	11591.5	11618.0	11539.8	11578.2	11526.1	11590.5	11591.5	11618.0	11539.8	11578.2	11526.1
4.5°	11591.5	11611.6	11499.5	11552.1	11533.5	11604.3	11591.5	11611.6	11499.5	11552.1	11533.5
5°	11598.4	11595.4	11517.7	11543.3	11498.5	11585.6	11598.4	11595.4	11517.7	11543.3	11498.5
5.5°	11608.7	11575.3	11526.6	11535.9	11498.5	11555.6	11608.7	11575.3	11526.6	11535.9	11498.5
6°	11608.7	11580.2	11507.4	11527.6	11470.5	11577.7	11608.7	11580.2	11507.4	11527.6	11470.5
6.5°	11586.1	11585.1	11473.5	11504.4	11475.9	11592.0	11586.1	11585.1	11473.5	11504.4	11475.9
7°	11586.1	11586.6	11477.4	11471.5	11466.6	11580.2	11586.1	11586.6	11477.4	11471.5	11466.6
7.5°	11613.1	11554.1	11460.7	11471.5	11444.5	11556.1	11613.1	11554.1	11460.7	11471.5	11444.5
8°	11613.1	11554.1	11433.6	11446.9	11388.9	11556.1	11613.1	11554.1	11433.6	11446.9	11388.9
8.5°	11588.0	11566.4	11409.1	11446.9	11400.7	11545.3	11588.0	11566.4	11409.1	11446.9	11400.7
9°	11607.2	11566.9	11358.9	11384.0	11398.7	11556.6	11607.2	11566.9	11358.9	11384.0	11398.7
9.5°	11597.9	11541.3	11372.7	11370.2	11326.5	11532.5	11597.9	11541.3	11372.7	11370.2	11326.5
10°	11597.9	11515.3	11370.2	11358.9	11326.5	11497.1	11597.9	11515.3	11370.2	11358.9	11326.5
10.5°	11603.3	11531.5	11338.3	11319.6	11299.4	11517.7	11603.3	11531.5	11338.3	11319.6	11299.4
11°	11602.8	11542.3	11281.2	11281.7	11299.4	11517.7	11602.8	11542.3	11281.2	11281.7	11299.4
11.5°	11585.1	11533.0	11284.7	11241.4	11246.8	11503.5	11585.1	11533.0	11284.7	11241.4	11246.8
12°	11613.6	11507.4	11263.0	11241.4	11225.2	11484.3	11613.6	11507.4	11263.0	11241.4	11225.2
12.5°	11613.6	11497.1	11250.3	11166.2	11168.6	11484.3	11613.6	11497.1	11250.3	11166.2	11168.6
13°	11583.6	11493.1	11199.6	11166.2	11168.6	11464.6	11583.6	11493.1	11199.6	11166.2	11168.6
13.5°	11583.6	11493.1	11174.6	11082.1	11138.7	11464.6	11583.6	11493.1	11174.6	11082.1	11138.7
14°	11608.7	11466.6	11110.6	11082.1	11105.7	11450.9	11608.7	11466.6	11110.6	11082.1	11105.7
14.5°	11608.7	11439.6	11077.2	11007.9	11045.7	11416.4	11608.7	11439.6	11077.2	11007.9	11045.7
15°	11606.2	11456.7	11057.0	10948.4	10991.6	11426.3	11606.2	11456.7	11057.0	10948.4	10991.6
15.5°	11594.9	11453.3	10991.6	10899.7	10991.6	11426.3	11594.9	11453.3	10991.6	10899.7	10991.6
16°	11594.9	11430.7	10980.3	10845.6	10898.2	11400.2	11594.9	11430.7	10980.3	10845.6	10898.2
16.5°	11620.0	11399.2	10941.5	10816.6	10869.7	11366.8	11620.0	11399.2	10941.5	10816.6	10869.7
17°	11620.0	11388.4	10916.9	10759.6	10793.0	11378.1	11620.0	11388.4	10916.9	10759.6	10793.0
17.5°	11588.5	11400.7	10845.6	10685.3	10785.6	11351.1	11588.5	11400.7	10845.6	10685.3	10785.6
18°	11588.5	11400.7	10737.0	10558.5	10729.6	11351.1	11588.5	11400.7	10737.0	10558.5	10729.6
18.5°	11615.6	11350.6	10719.3	10558.5	10682.9	11309.3	11615.6	11350.6	10719.3	10558.5	10682.9
19°	11615.6	11320.1	10655.8	10480.3	10587.0	11309.3	11615.6	11320.1	10655.8	10480.3	10587.0
19.5°	11603.8	11340.2	10604.2	10383.0	10577.2	11277.8	11603.8	11340.2	10604.2	10383.0	10577.2
20°	11603.8	11333.8	10509.8	10192.2	10501.9	11261.1	11603.8	11333.8	10509.8	10192.2	10501.9
20.5°	11600.3	11307.3	10487.2	10192.2	10455.7	11240.4	11600.3	11307.3	10487.2	10192.2	10455.7
21°	11623.4	11261.1	10415.9	10032.4	10356.4	11191.3	11623.4	11261.1	10415.9	10032.4	10356.4
21.5°	11623.4	11251.7	10368.7	9894.7	10216.8	11202.6	11623.4	11251.7	10368.7	9894.7	10216.8
22°	11595.4	11236.5	10266.9	9785.1	10185.8	11173.1	11595.4	11236.5	10266.9	9785.1	10185.8

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594575
CATALOG NUMBER: FLXB-1224-N-MED-4000K

CANDELA DISTRIBUTION (continued):

	0°	30°	60°	90°	120°	150°	180°	210°	240°	270°	300°
22.5°	11595.4	11228.6	10219.7	9657.8	10085.5	11155.4	11595.4	11228.6	10219.7	9657.8	10085.5
23°	11630.8	11180.4	10112.1	9558.4	10023.1	11104.2	11630.8	11180.4	10112.1	9558.4	10023.1
23.5°	11630.8	11180.4	9951.8	9375.5	9882.5	11104.2	11630.8	11180.4	9951.8	9375.5	9882.5
24°	11614.6	11135.2	9868.2	9267.9	9843.6	11044.7	11614.6	11135.2	9868.2	9267.9	9843.6
24.5°	11614.6	11108.2	9732.0	9059.9	9723.1	11018.7	11614.6	11108.2	9732.0	9059.9	9723.1
25°	11621.5	11076.2	9663.7	8917.3	9492.1	10991.2	11621.5	11076.2	9663.7	8917.3	9492.1
25.5°	11621.5	11019.7	9540.7	8552.5	9492.1	10928.7	11621.5	11019.7	9540.7	8552.5	9492.1
26°	11649.5	11003.4	9437.0	8552.5	9254.1	10926.7	11649.5	11003.4	9437.0	8552.5	9254.1
26.5°	11614.1	10978.4	9280.2	8107.5	9254.1	10872.2	11614.1	10978.4	9280.2	8107.5	9254.1
27°	11614.1	10946.4	9167.1	7843.0	8994.5	10852.0	11614.1	10946.4	9167.1	7843.0	8994.5
27.5°	11646.1	10892.8	9008.8	7683.7	8873.1	10777.3	11646.1	10892.8	9008.8	7683.7	8873.1
28°	11646.1	10848.1	8884.9	7385.3	8665.1	10694.2	11646.1	10848.1	8884.9	7385.3	8665.1
28.5°	11631.8	10751.7	8707.9	7207.8	8551.0	10675.0	11631.8	10751.7	8707.9	7207.8	8551.0
29°	11631.8	10751.7	8316.5	6900.5	8342.1	10675.0	11631.8	10751.7	8316.5	6900.5	8342.1
29.5°	11643.6	10623.9	8130.2	6685.7	8172.9	10568.3	11643.6	10623.9	8130.2	6685.7	8172.9
30°	11643.6	10553.6	7925.6	6354.8	7918.3	10478.4	11643.6	10553.6	7925.6	6354.8	7918.3
30.5°	11655.4	10485.7	7678.3	6142.9	7469.4	10455.2	11655.4	10485.7	7678.3	6142.9	7469.4
31°	11629.8	10437.0	7422.6	5517.9	7469.4	10383.5	11629.8	10437.0	7422.6	5517.9	7469.4
31.5°	11629.8	10334.3	7155.2	5517.9	6956.6	10322.5	11629.8	10334.3	7155.2	5517.9	6956.6
32°	11664.7	10255.6	6896.1	4874.3	6697.9	10226.1	11664.7	10255.6	6896.1	4874.3	6697.9
32.5°	11664.7	10131.2	6608.4	4455.5	6373.9	10168.1	11664.7	10131.2	6608.4	4455.5	6373.9
33°	11631.8	9901.1	6321.8	4175.7	6105.5	9989.6	11631.8	9901.1	6321.8	4175.7	6105.5
33.5°	11631.8	9901.1	5700.9	3764.2	5776.1	9989.6	11631.8	9901.1	5700.9	3764.2	5776.1
34°	11637.7	9650.9	5376.4	3461.3	5478.1	9792.5	11637.7	9650.9	5376.4	3461.3	5478.1
34.5°	11637.7	9546.6	5060.7	3461.3	5122.2	9792.5	11637.7	9546.6	5060.7	3461.3	5122.2
35°	11636.2	9348.5	4692.9	2789.7	4830.1	9568.8	11636.2	9348.5	4692.9	2789.7	4830.1
35.5°	11636.2	9262.5	4344.8	2206.1	4468.7	9441.4	11636.2	9262.5	4344.8	2206.1	4468.7
36°	11603.8	8991.1	3951.0	2206.1	3790.7	9289.5	11603.8	8991.1	3951.0	2206.1	3790.7
36.5°	11622.0	8873.6	3604.9	1734.6	3790.7	9129.7	11622.0	8873.6	3604.9	1734.6	3790.7
37°	11622.0	8560.9	3165.3	1649.0	3157.5	8977.3	11622.0	8560.9	3165.3	1649.0	3157.5
37.5°	11574.8	8458.6	2826.1	1334.9	2767.6	8800.3	11574.8	8458.6	2826.1	1334.9	2767.6
38°	11574.8	8102.6	2353.1	1310.3	2585.2	8609.0	11574.8	8102.6	2353.1	1310.3	2585.2
38.5°	11565.9	7550.5	1983.4	1025.6	2140.7	8173.4	11565.9	7550.5	1983.4	1025.6	2140.7
39°	11565.9	7550.5	1543.8	1020.2	2037.9	8173.4	11565.9	7550.5	1543.8	1020.2	2037.9
39.5°	11520.2	6968.8	1219.3	813.2	1591.0	7662.1	11520.2	6968.8	1219.3	813.2	1591.0
40°	11520.2	6807.1	1057.6	814.7	1138.7	7402.0	11520.2	6807.1	1057.6	814.7	1138.7
40.5°	11458.7	6329.2	750.8	683.9	1120.5	7050.5	11458.7	6329.2	750.8	683.9	1120.5
41°	11464.6	6131.5	750.8	618.0	1120.5	6726.5	11464.6	6131.5	750.8	618.0	1120.5
41.5°	11419.9	5644.8	583.6	618.0	825.5	6354.8	11419.9	5644.8	583.6	618.0	825.5
42°	11296.5	5431.4	583.6	586.1	825.5	5987.0	11296.5	5431.4	583.6	586.1	825.5
42.5°	11296.5	4968.3	522.1	582.1	639.7	5564.7	11296.5	4968.3	522.1	582.1	639.7
43°	11239.0	4711.6	522.1	564.9	536.9	4703.7	11239.0	4711.6	522.1	564.9	536.9
43.5°	11239.0	4306.0	508.4	554.6	530.0	4703.7	11239.0	4306.0	508.4	554.6	530.0
44°	11115.5	3714.0	501.0	535.4	501.0	3798.1	11115.5	3714.0	501.0	535.4	501.0
44.5°	11115.5	3714.0	497.6	521.2	497.6	3798.1	11115.5	3714.0	497.6	521.2	497.6

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594575
CATALOG NUMBER: FLXB-1224-N-MED-4000K

CANDELA DISTRIBUTION (continued):

	0°	30°	60°	90°	120°	150°	180°	210°	240°	270°	300°
45°	11003.0	3194.3	488.2	521.2	490.2	2929.3	11003.0	3194.3	488.2	521.2	490.2
45.5°	11003.0	2789.7	488.2	503.5	487.2	2581.2	11003.0	2789.7	488.2	503.5	487.2
46°	10876.1	2675.6	478.9	503.5	478.4	2161.4	10876.1	2675.6	478.9	503.5	478.4
46.5°	10699.6	2250.8	478.9	487.7	478.4	1908.6	10699.6	2250.8	478.9	487.7	478.4
47°	10699.6	2174.1	469.5	487.7	472.5	1542.4	10699.6	2174.1	469.5	487.7	472.5
47.5°	10557.0	1758.7	469.5	482.3	465.6	1349.6	10557.0	1758.7	469.5	482.3	465.6
48°	10557.0	1707.1	463.6	477.4	459.2	1109.2	10557.0	1707.1	463.6	477.4	459.2
48.5°	10355.9	1310.8	463.6	478.9	456.3	810.8	10355.9	1310.8	463.6	478.9	456.3
49°	10355.9	1310.8	455.8	474.0	451.3	810.8	10355.9	1310.8	455.8	474.0	451.3
49.5°	10155.3	1017.2	458.7	471.0	450.9	613.6	10155.3	1017.2	458.7	471.0	450.9
50°	10155.3	804.4	458.7	465.6	449.4	578.2	10155.3	804.4	458.7	465.6	449.4
50.5°	9933.6	790.6	466.6	457.3	454.3	516.2	9933.6	790.6	466.6	457.3	454.3
51°	9933.6	620.5	466.6	443.5	455.3	501.0	9933.6	620.5	466.6	443.5	455.3
51.5°	9666.6	608.7	469.5	443.5	467.1	459.7	9666.6	608.7	469.5	443.5	467.1
52°	9418.8	488.2	469.5	441.0	467.1	449.4	9418.8	488.2	469.5	441.0	467.1
52.5°	9418.8	476.9	463.1	438.1	465.1	424.3	9418.8	476.9	463.1	438.1	465.1
53°	9090.4	421.4	463.1	434.1	458.7	416.9	9090.4	421.4	463.1	434.1	458.7
53.5°	9090.4	413.0	439.5	423.3	449.9	402.2	9090.4	413.0	439.5	423.3	449.9
54°	8791.9	380.0	429.7	422.8	432.7	383.5	8791.9	380.0	429.7	422.8	432.7
54.5°	8791.9	380.0	415.5	410.0	419.9	383.5	8791.9	380.0	415.5	410.0	419.9
55°	8460.6	359.9	394.3	409.6	404.6	365.8	8460.6	359.9	394.3	409.6	404.6
55.5°	8460.6	353.0	394.3	399.2	398.2	358.4	8460.6	353.0	394.3	399.2	398.2
56°	8097.2	347.1	381.5	395.8	383.0	348.1	8097.2	347.1	381.5	395.8	383.0
56.5°	8097.2	339.7	381.5	390.9	383.0	339.7	8097.2	339.7	381.5	390.9	383.0
57°	7755.0	335.8	375.6	390.9	374.2	331.4	7755.0	335.8	375.6	390.9	374.2
57.5°	7366.6	328.4	375.6	392.4	373.2	322.5	7366.6	328.4	375.6	392.4	373.2
58°	7366.6	328.4	369.2	388.9	369.2	315.6	7366.6	328.4	369.2	388.9	369.2
58.5°	7000.3	327.0	369.2	389.4	362.4	301.9	7000.3	327.0	369.2	389.4	362.4
59°	7000.3	327.0	359.9	383.0	358.4	301.9	7000.3	327.0	359.9	383.0	358.4
59.5°	6613.9	324.5	351.5	377.6	355.5	288.6	6613.9	324.5	351.5	377.6	355.5
60°	6613.9	324.5	351.5	377.6	354.0	288.6	6613.9	324.5	351.5	377.6	354.0
60.5°	6230.4	315.6	349.6	368.7	346.6	280.7	6230.4	315.6	349.6	368.7	346.6
61°	6230.4	307.3	349.6	358.9	344.7	274.3	6230.4	307.3	349.6	358.9	344.7
61.5°	5856.2	305.8	350.1	352.0	345.6	276.8	5856.2	305.8	350.1	352.0	345.6
62°	5462.4	298.0	350.1	350.1	345.6	271.9	5462.4	298.0	350.1	350.1	345.6
62.5°	5462.4	292.0	346.6	339.7	338.7	277.8	5462.4	292.0	346.6	339.7	338.7
63°	5093.1	285.2	346.6	327.4	338.3	275.3	5093.1	285.2	346.6	327.4	338.3
63.5°	5093.1	281.2	328.4	327.4	331.9	276.3	5093.1	281.2	328.4	327.4	331.9
64°	4721.0	275.3	328.4	318.6	325.0	268.9	4721.0	275.3	328.4	318.6	325.0
64.5°	4721.0	275.3	309.8	318.6	320.1	268.9	4721.0	275.3	309.8	318.6	320.1
65°	4364.0	277.8	295.5	309.3	305.8	270.4	4364.0	277.8	295.5	309.3	305.8
65.5°	4364.0	275.3	295.5	309.3	303.4	274.8	4364.0	275.3	295.5	309.3	303.4
66°	4019.4	294.5	290.1	302.4	292.5	269.4	4019.4	294.5	290.1	302.4	292.5
66.5°	4019.4	293.0	290.1	299.9	292.5	275.3	4019.4	293.0	290.1	299.9	292.5
67°	3653.6	328.4	285.7	294.5	280.7	271.4	3653.6	328.4	285.7	294.5	280.7

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594575
CATALOG NUMBER: FLXB-1224-N-MED-4000K

CANDELA DISTRIBUTION (continued):

	0°	30°	60°	90°	120°	150°	180°	210°	240°	270°	300°
67.5°	3321.7	336.3	285.7	289.1	280.7	278.3	3321.7	336.3	285.7	289.1	280.7
68°	3321.7	369.2	276.8	284.2	271.4	280.3	3321.7	369.2	276.8	284.2	271.4
68.5°	2974.6	369.2	276.8	271.9	270.9	294.5	2974.6	369.2	276.8	271.9	270.9
69°	2974.6	347.6	265.0	271.9	266.5	294.5	2974.6	347.6	265.0	271.9	266.5
69.5°	2658.9	307.3	260.1	256.7	259.6	312.7	2658.9	307.3	260.1	256.7	259.6
70°	2658.9	307.3	254.7	256.7	248.8	312.7	2658.9	307.3	254.7	256.7	248.8
70.5°	2369.3	291.6	238.0	236.5	243.9	342.7	2369.3	291.6	238.0	236.5	243.9
71°	2369.3	295.5	238.0	236.5	232.1	356.9	2369.3	295.5	238.0	236.5	232.1
71.5°	2087.6	281.2	215.8	225.7	216.3	383.0	2087.6	281.2	215.8	225.7	216.3
72°	2013.9	284.2	215.8	221.2	216.3	386.0	2013.9	284.2	215.8	221.2	216.3
72.5°	1843.2	271.4	191.7	213.4	193.7	375.6	1843.2	271.4	191.7	213.4	193.7
73°	1618.1	272.9	191.7	201.1	193.7	379.1	1618.1	272.9	191.7	201.1	193.7
73.5°	1618.1	261.1	179.5	201.1	167.7	338.7	1618.1	261.1	179.5	201.1	167.7
74°	1418.9	264.0	179.5	189.8	155.4	298.0	1418.9	264.0	179.5	189.8	155.4
74.5°	1418.9	264.0	166.7	189.8	149.0	298.0	1418.9	264.0	166.7	189.8	149.0
75°	1233.6	265.0	145.0	150.4	145.5	267.5	1233.6	265.0	145.0	150.4	145.5
75.5°	1233.6	271.4	145.0	150.4	140.1	267.5	1233.6	271.4	145.0	150.4	140.1
76°	1066.4	257.6	132.8	121.4	136.7	243.9	1066.4	257.6	132.8	121.4	136.7
76.5°	953.3	246.8	132.8	113.6	130.8	230.1	953.3	246.8	132.8	113.6	130.8
77°	922.8	247.3	121.4	111.6	115.0	215.8	922.8	247.3	121.4	111.6	115.0
77.5°	783.7	228.6	121.4	102.3	115.0	206.5	783.7	228.6	121.4	102.3	115.0
78°	783.7	211.4	107.2	96.4	99.8	208.5	783.7	211.4	107.2	96.4	99.8
78.5°	659.3	195.7	107.2	81.1	93.9	199.1	659.3	195.7	107.2	81.1	93.9
79°	659.3	175.5	87.0	81.1	88.5	186.8	659.3	175.5	87.0	81.1	88.5
79.5°	544.8	162.3	87.0	72.8	81.1	163.7	544.8	162.3	87.0	72.8	81.1
80°	544.8	150.4	64.4	72.8	74.7	163.7	544.8	150.4	64.4	72.8	74.7
80.5°	448.9	132.3	53.1	56.0	62.9	151.4	448.9	132.3	53.1	56.0	62.9
81°	448.9	121.4	53.1	56.0	58.5	143.6	448.9	121.4	53.1	56.0	58.5
81.5°	365.8	111.1	40.8	44.2	46.7	130.8	365.8	111.1	40.8	44.2	46.7
82°	365.8	104.7	40.8	42.8	44.2	114.6	365.8	104.7	40.8	42.8	44.2
82.5°	291.6	99.8	29.0	39.3	37.4	92.9	291.6	99.8	29.0	39.3	37.4
83°	229.6	90.5	29.0	31.0	37.4	80.1	229.6	90.5	29.0	31.0	37.4
83.5°	229.6	88.0	24.6	29.0	26.0	67.3	229.6	88.0	24.6	29.0	26.0
84°	175.5	78.7	24.6	20.7	20.2	49.7	175.5	78.7	24.6	20.7	20.2
84.5°	175.5	76.7	20.2	20.7	17.2	49.7	175.5	76.7	20.2	20.7	17.2
85°	131.3	67.9	16.2	16.7	14.7	29.0	131.3	67.9	16.2	16.7	14.7
85.5°	131.3	51.6	13.3	16.7	14.3	29.0	131.3	51.6	13.3	16.7	14.3
86°	95.9	51.1	6.4	14.3	12.3	16.2	95.9	51.1	6.4	14.3	12.3
86.5°	95.9	38.4	6.4	14.3	11.3	12.3	95.9	38.4	6.4	14.3	11.3
87°	69.8	38.4	5.4	10.3	6.9	9.8	69.8	38.4	5.4	10.3	6.9
87.5°	69.8	29.0	5.4	4.9	6.9	5.9	69.8	29.0	5.4	4.9	6.9
88°	50.2	29.0	3.9	4.9	3.9	3.4	50.2	29.0	3.9	4.9	3.9
88.5°	35.4	19.2	3.9	3.4	3.4	2.9	35.4	19.2	3.9	3.4	3.4
89°	35.4	19.2	2.0	3.4	3.4	2.9	35.4	19.2	2.0	3.4	3.4
89.5°	24.6	10.8	2.0	2.9	2.5	2.0	24.6	10.8	2.0	2.9	2.5

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594575
CATALOG NUMBER: FLXB-1224-N-MED-4000K

CANDELA DISTRIBUTION (continued):

	0°	30°	60°	90°	120°	150°	180°	210°	240°	270°	300°
90°	*15.2*	6.4	1.0	2.0	1.5	1.5	15.2	6.4	1.0	2.0	1.5

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594575
CATALOG NUMBER: FLXB-1224-N-MED-4000K

CANDELA DISTRIBUTION (continued):

	330°	360°
0°	11593.2	11593.2
0.5°	11593.2	11593.2
1°	11590.0	11615.1
1.5°	11609.2	11615.1
2°	11604.8	11588.0
2.5°	11604.8	11588.0
3°	11605.2	11613.1
3.5°	11605.2	11613.1
4°	11590.5	11591.5
4.5°	11604.3	11591.5
5°	11585.6	11598.4
5.5°	11555.6	11608.7
6°	11577.7	11608.7
6.5°	11592.0	11586.1
7°	11580.2	11586.1
7.5°	11556.1	11613.1
8°	11556.1	11613.1
8.5°	11545.3	11588.0
9°	11556.6	11607.2
9.5°	11532.5	11597.9
10°	11497.1	11597.9
10.5°	11517.7	11603.3
11°	11517.7	11602.8
11.5°	11503.5	11585.1
12°	11484.3	11613.6
12.5°	11484.3	11613.6
13°	11464.6	11583.6
13.5°	11464.6	11583.6
14°	11450.9	11608.7
14.5°	11416.4	11608.7
15°	11426.3	11606.2
15.5°	11426.3	11594.9
16°	11400.2	11594.9
16.5°	11366.8	11620.0
17°	11378.1	11620.0
17.5°	11351.1	11588.5
18°	11351.1	11588.5
18.5°	11309.3	11615.6
19°	11309.3	11615.6
19.5°	11277.8	11603.8
20°	11261.1	11603.8
20.5°	11240.4	11600.3
21°	11191.3	11623.4
21.5°	11202.6	11623.4
22°	11173.1	11595.4

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594575
CATALOG NUMBER: FLXB-1224-N-MED-4000K

CANDELA DISTRIBUTION (continued):

	330°	360°
22.5°	11155.4	11595.4
23°	11104.2	11630.8
23.5°	11104.2	11630.8
24°	11044.7	11614.6
24.5°	11018.7	11614.6
25°	10991.2	11621.5
25.5°	10928.7	11621.5
26°	10926.7	11649.5
26.5°	10872.2	11614.1
27°	10852.0	11614.1
27.5°	10777.3	11646.1
28°	10694.2	11646.1
28.5°	10675.0	11631.8
29°	10675.0	11631.8
29.5°	10568.3	11643.6
30°	10478.4	11643.6
30.5°	10455.2	11655.4
31°	10383.5	11629.8
31.5°	10322.5	11629.8
32°	*10226.1*	*11664.7*
32.5°	10168.1	11664.7
33°	9989.6	11631.8
33.5°	9989.6	11631.8
34°	9792.5	11637.7
34.5°	9792.5	11637.7
35°	9568.8	11636.2
35.5°	9441.4	11636.2
36°	9289.5	11603.8
36.5°	9129.7	11622.0
37°	8977.3	11622.0
37.5°	8800.3	11574.8
38°	8609.0	11574.8
38.5°	8173.4	11565.9
39°	8173.4	11565.9
39.5°	7662.1	11520.2
40°	7402.0	11520.2
40.5°	7050.5	11458.7
41°	6726.5	11464.6
41.5°	6354.8	11419.9
42°	5987.0	11296.5
42.5°	5564.7	11296.5
43°	4703.7	11239.0
43.5°	4703.7	11239.0
44°	3798.1	11115.5
44.5°	3798.1	11115.5

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594575
CATALOG NUMBER: FLXB-1224-N-MED-4000K

CANDELA DISTRIBUTION (continued):

	330°	360°
45°	2929.3	11003.0
45.5°	2581.2	11003.0
46°	2161.4	10876.1
46.5°	1908.6	10699.6
47°	1542.4	10699.6
47.5°	1349.6	10557.0
48°	1109.2	10557.0
48.5°	810.8	10355.9
49°	810.8	10355.9
49.5°	613.6	10155.3
50°	578.2	10155.3
50.5°	516.2	9933.6
51°	501.0	9933.6
51.5°	459.7	9666.6
52°	449.4	9418.8
52.5°	424.3	9418.8
53°	416.9	9090.4
53.5°	402.2	9090.4
54°	383.5	8791.9
54.5°	383.5	8791.9
55°	365.8	8460.6
55.5°	358.4	8460.6
56°	348.1	8097.2
56.5°	339.7	8097.2
57°	331.4	7755.0
57.5°	322.5	7366.6
58°	315.6	7366.6
58.5°	301.9	7000.3
59°	301.9	7000.3
59.5°	288.6	6613.9
60°	288.6	6613.9
60.5°	280.7	6230.4
61°	274.3	6230.4
61.5°	276.8	5856.2
62°	271.9	5462.4
62.5°	277.8	5462.4
63°	275.3	5093.1
63.5°	276.3	5093.1
64°	268.9	4721.0
64.5°	268.9	4721.0
65°	270.4	4364.0
65.5°	274.8	4364.0
66°	269.4	4019.4
66.5°	275.3	4019.4
67°	271.4	3653.6

TEST NUMBER: P1594575
CATALOG NUMBER: FLXB-1224-N-MED-4000K

CANDELA DISTRIBUTION (continued):

	330°	360°
67.5°	278.3	3321.7
68°	280.3	3321.7
68.5°	294.5	2974.6
69°	294.5	2974.6
69.5°	312.7	2658.9
70°	312.7	2658.9
70.5°	342.7	2369.3
71°	356.9	2369.3
71.5°	383.0	2087.6
72°	386.0	2013.9
72.5°	375.6	1843.2
73°	379.1	1618.1
73.5°	338.7	1618.1
74°	298.0	1418.9
74.5°	298.0	1418.9
75°	267.5	1233.6
75.5°	267.5	1233.6
76°	243.9	1066.4
76.5°	230.1	953.3
77°	215.8	922.8
77.5°	206.5	783.7
78°	208.5	783.7
78.5°	199.1	659.3
79°	186.8	659.3
79.5°	163.7	544.8
80°	163.7	544.8
80.5°	151.4	448.9
81°	143.6	448.9
81.5°	130.8	365.8
82°	114.6	365.8
82.5°	92.9	291.6
83°	80.1	229.6
83.5°	67.3	229.6
84°	49.7	175.5
84.5°	49.7	175.5
85°	29.0	131.3
85.5°	29.0	131.3
86°	16.2	95.9
86.5°	12.3	95.9
87°	9.8	69.8
87.5°	5.9	69.8
88°	3.4	50.2
88.5°	2.9	35.4
89°	2.9	35.4
89.5°	2.0	24.6

TEST NUMBER: P1594575
CATALOG NUMBER: FLXB-1224-N-MED-4000K

CANDELA DISTRIBUTION (continued):

	330°	360°
90°	1.5	15.2

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594575
CATALOG NUMBER: FLXB-1224-N-MED-4000K

CIE UGR TABLE:

Reflectances:											
	Ceiling	0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
	Wall	0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
	Reference plane	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room Dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	26.1	27.4	26.5	27.7	28.0	11.6	12.9	12.0	13.3	13.6
	3H	28.0	29.2	28.4	29.5	29.9	13.9	15.0	14.3	15.4	15.7
	4H	28.5	29.5	28.9	29.9	30.3	14.6	15.7	15.0	16.0	16.4
	6H	28.6	29.6	29.1	30.0	30.4	14.9	15.8	15.3	16.2	16.6
	8H	28.7	29.6	29.1	30.0	30.4	14.9	15.8	15.3	16.2	16.6
	12H	28.7	29.5	29.1	29.9	30.4	14.9	15.8	15.3	16.1	16.6
4H	2H	25.9	27.0	26.3	27.3	27.7	12.3	13.3	12.7	13.7	14.1
	3H	27.8	28.7	28.2	29.1	29.5	14.7	15.6	15.1	16.0	16.4
	4H	28.3	29.1	28.7	29.5	30.0	15.5	16.3	15.9	16.7	17.1
	6H	28.6	29.2	29.0	29.7	30.2	15.8	16.5	16.3	17.0	17.4
	8H	28.6	29.2	29.1	29.7	30.2	15.9	16.5	16.3	16.9	17.4
	12H	28.6	29.2	29.1	29.7	30.1	15.8	16.4	16.3	16.9	17.4
8H	4H	28.2	28.8	28.7	29.3	29.7	16.1	16.7	16.6	17.2	17.7
	6H	28.4	29.0	29.0	29.5	29.9	16.5	17.0	17.0	17.5	18.0
	8H	28.5	29.0	29.0	29.5	30.0	16.5	17.0	17.0	17.5	18.0
	12H	28.5	28.9	29.0	29.4	30.0	16.5	16.9	17.0	17.4	18.0
12H	4H	28.1	28.7	28.6	29.2	29.7	16.3	16.8	16.8	17.3	17.8
	6H	28.4	28.9	28.9	29.3	29.9	16.7	17.1	17.2	17.6	18.1
	8H	28.5	28.9	29.0	29.4	29.9	16.7	17.1	17.2	17.6	18.2

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP3-2602-684-3

Test Date: 02/20/2026

Luminaire Tested: HLBX-2436-W-HI-4000K

Data in this report applies to families of products including HLBX-2436*

Report Generated By FNC07603 / LDUCLS01DT01661
Version: v7.05


Test Information

Test Method:	LM-79-2019
Report Number:	SP3-2602-684-3
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP3 - 3M SPHERE
Measurement Geometry:	4π
Issue Date:	02/27/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	Metalux
Catalog Number:	**HLBX-2436-W-HI-4000K**
Description:	LDS HLBX 2436 W beam, HI lumen, 4000K CCT settings

Spectral Parameters

CCT (K):	4000
CIE u':	0.2271
CIE v':	0.4972
Duv:	-0.0036
CIE x:	0.3780
CIE y:	0.3677
CIE z:	0.2543
Peak Wavelength (nm):	454
Dominant Wavelength (nm):	581
Purity:	23.78071
Rf:	83.8
Rg:	95.3

CRI (Ra):	84.8
R1:	84.5
R2:	92.5
R3:	95.4
R4:	82.5
R5:	84.0
R6:	87.9
R7:	85.2
R8:	66.3
R9:	16.8
R10:	80.6
R11:	81.5
R12:	62.9
R13:	87.1
R14:	98.1
R15:	79.5



Test Conditions


Stabilization Time:	22M
Operation Time:	1H 22M
Sphere Temperature (°C):	25.0

REPORT NUMBER: SP3-2602-684-3


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	3M SPHERE IN02505	1/10/2026	7/10/2026
Power Meter	XITRON INXT2011006	10/21/2025	10/21/2026
AC Power Source	CHROMA 61604 IN6064A	10/20/2025	10/20/2026
DC Power Source	EYSIGHT N5770A IN0534	10/20/2025	10/20/2026
Sphere Thermometer	TANDD IN4036E	10/21/2025	10/21/2026

REPORT NUMBER: SP3-2602-684-3

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 4000K
CIE x = 0.3780
CIE y = 0.3677
Duv = -0.0036

Point lies inside the ANSI 4000K 7-step quadrangle

REPORT NUMBER: SP3-2602-684-3

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	258	NR	620	689	NR	750	21	NR	880	1	NR
365	0	NR	495	283	NR	625	645	NR	755	18	NR	885	1	NR
370	0	NR	500	331	NR	630	600	NR	760	15	NR	890	1	NR
375	0	NR	505	383	NR	635	550	NR	765	13	NR	895	0	NR
380	0	NR	510	428	NR	640	501	NR	770	11	NR	900	0	NR
385	0	NR	515	469	NR	645	450	NR	775	9	NR	905	0	NR
390	1	NR	520	502	NR	650	404	NR	780	8	NR	910	0	NR
395	3	NR	525	526	NR	655	359	NR	785	7	NR	915	0	NR
400	4	NR	530	543	NR	660	317	NR	790	6	NR	920	0	NR
405	7	NR	535	559	NR	665	278	NR	795	5	NR	925	0	NR
410	10	NR	540	573	NR	670	243	NR	800	4	NR	930	0	NR
415	18	NR	545	587	NR	675	212	NR	805	4	NR	935	0	NR
420	32	NR	550	603	NR	680	183	NR	810	3	NR	940	0	NR
425	55	NR	555	619	NR	685	159	NR	815	3	NR	945	0	NR
430	95	NR	560	640	NR	690	136	NR	820	2	NR	950	0	NR
435	164	NR	565	666	NR	695	117	NR	825	2	NR	955	0	NR
440	273	NR	570	689	NR	700	100	NR	830	2	NR	960	0	NR
445	480	NR	575	718	NR	705	85	NR	835	2	NR	965	0	NR
450	835	NR	580	743	NR	710	73	NR	840	1	NR	970	0	NR
455	998	NR	585	764	NR	715	63	NR	845	1	NR	975	0	NR
460	735	NR	590	781	NR	720	54	NR	850	1	NR	980	0	NR
465	533	NR	595	789	NR	725	46	NR	855	1	NR	985	0	NR
470	435	NR	600	787	NR	730	39	NR	860	1	NR	990	0	NR
475	320	NR	605	775	NR	735	33	NR	865	1	NR	995	0	NR
480	254	NR	610	755	NR	740	28	NR	870	1	NR	1000	0	NR
485	245	NR	615	725	NR	745	24	NR	875	1	NR			

REPORT NUMBER: SP3-2602-684-3

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.73**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	258	NR	620	689	NR	750	21	NR	880	1	NR
365	0	NR	495	283	NR	625	645	NR	755	18	NR	885	1	NR
370	0	NR	500	331	NR	630	600	NR	760	15	NR	890	1	NR
375	0	NR	505	383	NR	635	550	NR	765	13	NR	895	0	NR
380	0	NR	510	428	NR	640	501	NR	770	11	NR	900	0	NR
385	0	NR	515	469	NR	645	450	NR	775	9	NR	905	0	NR
390	1	NR	520	502	NR	650	404	NR	780	8	NR	910	0	NR
395	3	NR	525	526	NR	655	359	NR	785	7	NR	915	0	NR
400	4	NR	530	543	NR	660	317	NR	790	6	NR	920	0	NR
405	7	NR	535	559	NR	665	278	NR	795	5	NR	925	0	NR
410	10	NR	540	573	NR	670	243	NR	800	4	NR	930	0	NR
415	18	NR	545	587	NR	675	212	NR	805	4	NR	935	0	NR
420	32	NR	550	603	NR	680	183	NR	810	3	NR	940	0	NR
425	55	NR	555	619	NR	685	159	NR	815	3	NR	945	0	NR
430	95	NR	560	640	NR	690	136	NR	820	2	NR	950	0	NR
435	164	NR	565	666	NR	695	117	NR	825	2	NR	955	0	NR
440	273	NR	570	689	NR	700	100	NR	830	2	NR	960	0	NR
445	480	NR	575	718	NR	705	85	NR	835	2	NR	965	0	NR
450	835	NR	580	743	NR	710	73	NR	840	1	NR	970	0	NR
455	998	NR	585	764	NR	715	63	NR	845	1	NR	975	0	NR
460	735	NR	590	781	NR	720	54	NR	850	1	NR	980	0	NR
465	533	NR	595	789	NR	725	46	NR	855	1	NR	985	0	NR
470	435	NR	600	787	NR	730	39	NR	860	1	NR	990	0	NR
475	320	NR	605	775	NR	735	33	NR	865	1	NR	995	0	NR
480	254	NR	610	755	NR	740	28	NR	870	1	NR	1000	0	NR
485	245	NR	615	725	NR	745	24	NR	875	1	NR			

REPORT NUMBER: SP3-2602-684-3

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 3.62**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	258	NR	620	689	NR	750	21	NR	880	1	NR
365	0	NR	495	283	NR	625	645	NR	755	18	NR	885	1	NR
370	0	NR	500	331	NR	630	600	NR	760	15	NR	890	1	NR
375	0	NR	505	383	NR	635	550	NR	765	13	NR	895	0	NR
380	0	NR	510	428	NR	640	501	NR	770	11	NR	900	0	NR
385	0	NR	515	469	NR	645	450	NR	775	9	NR	905	0	NR
390	1	NR	520	502	NR	650	404	NR	780	8	NR	910	0	NR
395	3	NR	525	526	NR	655	359	NR	785	7	NR	915	0	NR
400	4	NR	530	543	NR	660	317	NR	790	6	NR	920	0	NR
405	7	NR	535	559	NR	665	278	NR	795	5	NR	925	0	NR
410	10	NR	540	573	NR	670	243	NR	800	4	NR	930	0	NR
415	18	NR	545	587	NR	675	212	NR	805	4	NR	935	0	NR
420	32	NR	550	603	NR	680	183	NR	810	3	NR	940	0	NR
425	55	NR	555	619	NR	685	159	NR	815	3	NR	945	0	NR
430	95	NR	560	640	NR	690	136	NR	820	2	NR	950	0	NR
435	164	NR	565	666	NR	695	117	NR	825	2	NR	955	0	NR
440	273	NR	570	689	NR	700	100	NR	830	2	NR	960	0	NR
445	480	NR	575	718	NR	705	85	NR	835	2	NR	965	0	NR
450	835	NR	580	743	NR	710	73	NR	840	1	NR	970	0	NR
455	998	NR	585	764	NR	715	63	NR	845	1	NR	975	0	NR
460	735	NR	590	781	NR	720	54	NR	850	1	NR	980	0	NR
465	533	NR	595	789	NR	725	46	NR	855	1	NR	985	0	NR
470	435	NR	600	787	NR	730	39	NR	860	1	NR	990	0	NR
475	320	NR	605	775	NR	735	33	NR	865	1	NR	995	0	NR
480	254	NR	610	755	NR	740	28	NR	870	1	NR	1000	0	NR
485	245	NR	615	725	NR	745	24	NR	875	1	NR			


REPORT NUMBER: SP3-2602-684-3

TM-30-18


Summary


R_f = 83.8
R_g = 95.3
CIE R_a = 84.8
R_9 = 16.8


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP3-2602-684-3

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 84	CES51 = 92	CES76 = 77
CES02 = 61	CES27 = 90	CES52 = 93	CES77 = 82
CES03 = 31	CES28 = 91	CES53 = 89	CES78 = 76
CES04 = 70	CES29 = 91	CES54 = 88	CES79 = 92
CES05 = 48	CES30 = 88	CES55 = 84	CES80 = 89
CES06 = 51	CES31 = 93	CES56 = 84	CES81 = 80
CES07 = 41	CES32 = 84	CES57 = 82	CES82 = 95
CES08 = 40	CES33 = 97	CES58 = 82	CES83 = 96
CES09 = 29	CES34 = 87	CES59 = 91	CES84 = 90
CES10 = 74	CES35 = 93	CES60 = 88	CES85 = 77
CES11 = 57	CES36 = 76	CES61 = 85	CES86 = 75
CES12 = 63	CES37 = 92	CES62 = 77	CES87 = 85
CES13 = 43	CES38 = 82	CES63 = 83	CES88 = 91
CES14 = 74	CES39 = 98	CES64 = 75	CES89 = 79
CES15 = 71	CES40 = 97	CES65 = 76	CES90 = 91
CES16 = 47	CES41 = 95	CES66 = 71	CES91 = 66
CES17 = 49	CES42 = 93	CES67 = 70	CES92 = 65
CES18 = 56	CES43 = 90	CES68 = 76	CES93 = 78
CES19 = 71	CES44 = 99	CES69 = 80	CES94 = 65
CES20 = 65	CES45 = 95	CES70 = 73	CES95 = 73
CES21 = 86	CES46 = 92	CES71 = 65	CES96 = 85
CES22 = 78	CES47 = 94	CES72 = 88	CES97 = 90
CES23 = 91	CES48 = 84	CES73 = 68	CES98 = 87
CES24 = 90	CES49 = 91	CES74 = 89	CES99 = 80
CES25 = 71	CES50 = 93	CES75 = 70	





REPORT NUMBER: SP3-2602-684-3

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP3-2602-684-3

TM-30-18

Measure Comparisons





(END OF REPORT)