Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: METALUX

Report Number: P1594655

Luminaire Tested: FLXB-4860-N-HI-4000K

Issue Date: 10/2/2026

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-2019
Report Number:	P1594655
	TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (A2601781A001)
Test Lab:	INNOVATION CENTER
Issue Date:	10/2/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	METALUX
Catalog Number:	FLXB-4860-N-HI-4000K
Description:	4860 FlexBay Linear High bay at N beam, HI lumen, 4000K CCT settings
Light Source:	-
Ballast/Driver:	-

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	61444.0 lumens
Efficiency:	N/A
Efficacy:	165.1 lumens/watt
Spacing Criteria (0/90/45):	1.51 / 0.92 / 0.99
Luminous Opening:	Rectangular (W 1.04' x L: 2.12' x H: 0')
CIE Type:	Direct


Input Watts (W):	372.1
Input Voltage (V):	NR
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	NR
Total Harmonic Distortion (THDi):	NR
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594655
CATALOG NUMBER: FLXB-4860-N-HI-4000K

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594655
CATALOG NUMBER: FLXB-4860-N-HI-4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	95	93	92	90
2	104	98	93	88	102	96	91	87	93	89	85	90	86	83	87	84	82	80
3	97	89	83	78	95	87	82	77	85	80	76	82	78	74	80	76	73	71
4	91	81	74	69	89	80	73	68	78	72	68	76	71	67	74	69	66	64
5	85	74	67	62	83	73	67	62	71	66	61	70	64	60	68	63	60	58
6	80	69	61	56	78	68	61	56	66	60	55	65	59	55	63	58	54	53
7	75	63	56	51	73	63	56	51	61	55	51	60	54	50	59	54	50	48
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	42	41
10	63	51	44	40	62	51	44	40	50	44	40	49	43	40	48	43	39	38

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	201395	201395	201395	201395
5°	201910	200624	201910	200624
10°	204345	196338	204345	196338
15°	208509	188713	208509	188713
20°	214400	173667	214400	173667
25°	222225	146023	222225	146023
30°	232410	91052	232410	91052
35°	244345	31927	244345	31927
40°	254466	14497	254466	14497
45°	259877	14590	259877	14590
50°	255928	14312	255928	14312
55°	227810	14607	227810	14607
60°	196805	14719	196805	14719
65°	145069	14848	145069	14848
70°	107783	15370	107783	15370
75°	64487	10029	64487	10029
80°	39355	5867	39355	5867
85°	18093	1506	18093	1506

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 46°
Luminance: 260089 cd/sqm

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594655
CATALOG NUMBER: FLXB-4860-N-HI-4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	3909.1	6.4
10°-20°	11064.5	18.0
20°-30°	15504.4	25.2
30°-40°	13270.9	21.6
40°-50°	7786.1	12.7
50°-60°	5193.3	8.5
60°-70°	3172.9	5.2
70°-80°	1352.5	2.2
80°-90°	189.3	0.3
90°-100°	1.1	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	30478.0	49.6
0°-40°	43748.8	71.2
0°-60°	56728.2	92.3
0°-90°	61442.9	100.0
90°-120°	1.1	0.0
90°-150°	1.1	0.0
90°-180°	1.0	0.0
0°-180°	61444.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	41417	41417	41417	41417	41417	
5°	41365	41102	41365	41102	41365	3949
15°	41419	37487	41419	37487	41419	11738
25°	41419	27216	41419	27216	41419	19174
35°	41162	5378	41162	5378	41162	25759
45°	37791	2122	37791	2122	37791	28967
55°	26872	1723	26872	1723	26872	24002
65°	12608	1290	12608	1290	12608	12935
75°	3432	534	3432	534	3432	4062
85°	324	27	324	27	324	488
90°	54	0	54	0	54	35
95°	0	0	0	0	0	0
105°	0	0	0	0	0	0
115°	0	0	0	0	0	0
125°	0	0	0	0	0	0
135°	0	0	0	0	0	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594655
CATALOG NUMBER: FLXB-4860-N-HI-4000K

CANDELA DISTRIBUTION (FULL):

	0°	30°	60°	90°	120°	150°	180°	210°	240°	270°	300°
0°	41417.1	41417.1	41417.1	41417.1	41417.1	41417.1	41417.1	41417.1	41417.1	41417.1	41417.1
0.5°	41417.1	41417.1	41417.1	41417.1	41417.1	41417.1	41417.1	41417.1	41417.1	41417.1	41417.1
1°	41358.3	41581.3	41324.5	41540.7	41196.1	41452.9	41358.3	41581.3	41324.5	41540.7	41196.1
1.5°	41338.0	41608.3	41263.7	41540.7	41108.3	41446.1	41338.0	41608.3	41263.7	41540.7	41108.3
2°	41392.1	41608.3	41263.7	41459.6	41047.5	41473.1	41392.1	41608.3	41263.7	41459.6	41047.5
2.5°	41392.1	41588.0	41196.1	41473.1	41047.5	41446.1	41392.1	41588.0	41196.1	41473.1	41047.5
3°	41338.0	41588.0	41196.1	41385.3	41006.9	41412.3	41338.0	41588.0	41196.1	41385.3	41006.9
3.5°	41338.0	41547.5	41135.3	41385.3	41027.2	41398.8	41338.0	41547.5	41135.3	41385.3	41027.2
4°	41378.6	41561.0	41135.3	41256.9	40898.8	41358.3	41378.6	41561.0	41135.3	41256.9	40898.8
4.5°	41365.0	41554.2	41020.4	41256.9	40905.6	41398.8	41365.0	41554.2	41020.4	41256.9	40905.6
5°	41365.0	41534.0	41020.4	41101.5	40405.6	41317.7	41365.0	41534.0	41020.4	41101.5	40405.6
5.5°	41365.0	41466.4	40946.1	41006.9	40432.6	41297.5	41365.0	41466.4	40946.1	41006.9	40432.6
6°	41351.5	41479.9	40736.7	40919.1	40432.6	41277.2	41351.5	41479.9	40736.7	40919.1	40432.6
6.5°	41398.8	41466.4	40736.7	40709.6	40412.3	41290.7	41398.8	41466.4	40736.7	40709.6	40412.3
7°	41398.8	41378.6	40621.8	40709.6	40412.3	41196.1	41398.8	41378.6	40621.8	40709.6	40412.3
7.5°	41344.8	41378.6	40621.8	40486.7	40405.6	41196.1	41344.8	41378.6	40621.8	40486.7	40405.6
8°	41344.8	41311.0	40432.6	40486.7	40229.9	41128.6	41344.8	41311.0	40432.6	40486.7	40229.9
8.5°	41398.8	41311.0	40432.6	40229.9	40196.1	41061.0	41398.8	41311.0	40432.6	40229.9	40196.1
9°	41378.6	41270.4	40196.1	40229.9	39966.4	41081.3	41378.6	41270.4	40196.1	40229.9	39966.4
9.5°	41371.8	41236.7	40196.1	39939.4	39966.4	40993.4	41371.8	41236.7	40196.1	39939.4	39966.4
10°	41385.3	41162.3	40013.7	39763.7	39729.9	40939.4	41385.3	41162.3	40013.7	39763.7	39729.9
10.5°	41385.3	41155.6	39682.6	39520.4	39729.9	40892.1	41385.3	41155.6	39682.6	39520.4	39729.9
11°	41385.3	41121.8	39682.6	39297.5	39432.6	40905.6	41385.3	41121.8	39682.6	39297.5	39432.6
11.5°	41398.8	41061.0	39452.9	39297.5	39432.6	40790.7	41398.8	41061.0	39452.9	39297.5	39432.6
12°	41365.0	40986.7	39452.9	38925.8	39162.3	40763.7	41365.0	40986.7	39452.9	38925.8	39162.3
12.5°	41365.0	40892.1	39135.3	38709.6	38905.6	40702.9	41365.0	40892.1	39135.3	38709.6	38905.6
13°	41425.9	40838.0	39135.3	38466.4	38804.2	40655.6	41425.9	40838.0	39135.3	38466.4	38804.2
13.5°	41425.9	40804.2	39061.0	38250.2	38561.0	40540.7	41425.9	40804.2	39061.0	38250.2	38561.0
14°	41385.3	40729.9	38804.2	38000.2	38479.9	40439.4	41385.3	40729.9	38804.2	38000.2	38479.9
14.5°	41405.6	40635.3	38459.6	37736.6	38074.5	40371.8	41405.6	40635.3	38459.6	37736.6	38074.5
15°	41419.1	40621.8	38459.6	37486.6	38074.5	40290.7	41419.1	40621.8	38459.6	37486.6	38074.5
15.5°	41412.3	40574.5	38027.2	36919.1	37628.5	40284.0	41412.3	40574.5	38027.2	36919.1	37628.5
16°	41419.1	40574.5	37621.8	36601.5	37628.5	40135.3	41419.1	40574.5	37621.8	36601.5	37628.5
16.5°	41412.3	40378.6	37621.8	36304.2	37486.6	40061.0	41412.3	40378.6	37621.8	36304.2	37486.6
17°	41398.8	40250.2	37108.3	35925.8	37182.6	39979.9	41398.8	40250.2	37108.3	35925.8	37182.6
17.5°	41446.1	40250.2	37108.3	35581.2	36635.3	39932.6	41446.1	40250.2	37108.3	35581.2	36635.3
18°	41446.1	40101.5	36594.7	35209.6	36256.9	39723.1	41446.1	40101.5	36594.7	35209.6	36256.9
18.5°	41398.8	39966.4	36594.7	34865.0	36081.2	39601.5	41398.8	39966.4	36594.7	34865.0	36081.2
19°	41398.8	39878.6	36020.4	34419.1	35439.3	39513.7	41398.8	39878.6	36020.4	34419.1	35439.3
19.5°	41446.1	39804.2	36020.4	34027.2	35439.3	39371.8	41446.1	39804.2	36020.4	34027.2	35439.3
20°	41432.6	39804.2	35358.3	33561.0	34750.1	39331.3	41432.6	39804.2	35358.3	33561.0	34750.1
20.5°	41432.6	39682.6	35358.3	33135.3	34750.1	39148.8	41432.6	39682.6	35358.3	33135.3	34750.1
21°	41432.6	39466.4	34702.8	32148.8	34013.7	38898.8	41432.6	39466.4	34702.8	32148.8	34013.7
21.5°	41425.9	39365.0	33892.0	31567.7	34013.7	38898.8	41425.9	39365.0	33892.0	31567.7	34013.7
22°	41432.6	39270.4	33892.0	31060.9	33169.1	38817.7	41432.6	39270.4	33892.0	31060.9	33169.1

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594655
CATALOG NUMBER: FLXB-4860-N-HI-4000K

CANDELA DISTRIBUTION (continued):

	0°	30°	60°	90°	120°	150°	180°	210°	240°	270°	300°
22.5°	41452.9	38986.7	33067.7	30446.1	31635.3	38608.3	41452.9	38986.7	33067.7	30446.1	31635.3
23°	41412.3	38986.7	33067.7	29919.0	31317.7	38500.2	41412.3	38986.7	33067.7	29919.0	31317.7
23.5°	41412.3	38702.9	32142.0	29196.1	31317.7	38169.1	41412.3	38702.9	32142.0	29196.1	31317.7
24°	41466.4	38702.9	32142.0	28608.2	30925.8	37946.1	41466.4	38702.9	32142.0	28608.2	30925.8
24.5°	41432.6	38398.8	31115.0	27844.7	30520.4	37831.2	41432.6	38398.8	31115.0	27844.7	30520.4
25°	41419.1	38182.6	31115.0	27216.3	30520.4	37581.2	41419.1	38182.6	31115.0	27216.3	30520.4
25.5°	41425.9	37993.4	30040.7	25655.5	29385.3	37392.1	41425.9	37993.4	30040.7	25655.5	29385.3
26°	41432.6	37804.2	28790.7	25655.5	28628.5	37169.1	41432.6	37804.2	28790.7	25655.5	28628.5
26.5°	41425.9	37635.3	28790.7	23905.5	28108.2	37013.7	41425.9	37635.3	28790.7	23905.5	28108.2
27°	41439.4	37378.5	27500.1	22750.1	27290.7	36702.9	41439.4	37378.5	27500.1	22750.1	27290.7
27.5°	41392.1	37162.3	27500.1	21986.6	26750.1	36486.6	41392.1	37162.3	27500.1	21986.6	26750.1
28°	41392.1	36709.6	26027.1	20689.3	25851.5	35979.9	41392.1	36709.6	26027.1	20689.3	25851.5
28.5°	41446.1	36709.6	26027.1	19831.2	24256.9	35979.9	41446.1	36709.6	26027.1	19831.2	24256.9
29°	41446.1	36189.3	24432.5	18459.5	24256.9	35405.6	41446.1	36189.3	24432.5	18459.5	24256.9
29.5°	41392.1	35831.2	24432.5	17567.6	22527.1	35061.0	41392.1	35831.2	24432.5	17567.6	22527.1
30°	41392.1	35547.4	22702.8	16216.3	21756.8	34743.4	41392.1	35547.4	22702.8	16216.3	21756.8
30.5°	41405.6	35169.1	22702.8	15236.6	20608.2	34371.8	41405.6	35169.1	22702.8	15236.6	20608.2
31°	41365.0	34905.6	20743.3	12885.2	19750.1	34081.2	41365.0	34905.6	20743.3	12885.2	19750.1
31.5°	41371.8	34452.8	18587.9	11736.5	18614.9	33621.8	41371.8	34452.8	18587.9	11736.5	18614.9
32°	41317.7	34135.3	18587.9	10669.0	17648.7	33229.9	41317.7	34135.3	18587.9	10669.0	17648.7
32.5°	41317.7	33311.0	16229.8	9662.2	16594.7	32783.9	41317.7	33311.0	16229.8	9662.2	16594.7
33°	41311.0	33311.0	16229.8	8601.4	14493.3	32371.8	41311.0	33311.0	16229.8	8601.4	14493.3
33.5°	41311.0	32351.5	13817.6	7777.1	14493.3	31351.5	41311.0	32351.5	13817.6	7777.1	14493.3
34°	41189.4	32351.5	13817.6	6804.1	12324.4	30770.4	41189.4	32351.5	13817.6	6804.1	12324.4
34.5°	41189.4	31243.4	11304.1	6277.1	10837.9	30196.1	41189.4	31243.4	11304.1	6277.1	10837.9
35°	41162.3	30439.3	11304.1	5378.4	10155.4	29547.4	41162.3	30439.3	11304.1	5378.4	10155.4
35.5°	41047.5	30013.6	8939.2	5060.8	8655.4	28925.8	41047.5	30013.6	8939.2	5060.8	8655.4
36°	41047.5	29054.2	8939.2	4229.7	8175.7	28169.0	41047.5	29054.2	8939.2	4229.7	8175.7
36.5°	40919.1	28533.9	6905.4	3351.4	6824.4	27385.2	40919.1	28533.9	6905.4	3351.4	6824.4
37°	40905.6	27439.3	5263.5	3236.5	6567.6	26560.9	40905.6	27439.3	5263.5	3236.5	6567.6
37.5°	40770.4	26905.5	5263.5	2777.0	5364.9	25682.5	40770.4	26905.5	5263.5	2777.0	5364.9
38°	40777.2	25000.1	4006.8	2702.7	5223.0	24675.8	40777.2	25000.1	4006.8	2702.7	5223.0
38.5°	40534.0	25000.1	4006.8	2459.5	4067.6	23662.3	40534.0	25000.1	4006.8	2459.5	4067.6
39°	40534.0	22932.5	3135.1	2405.4	4067.6	21365.0	40534.0	22932.5	3135.1	2405.4	4067.6
39.5°	40351.5	22932.5	3135.1	2283.8	3175.7	20101.4	40351.5	22932.5	3135.1	2283.8	3175.7
40°	40088.0	18669.0	2648.7	2283.8	2689.2	18729.8	40088.0	18669.0	2648.7	2283.8	2689.2
40.5°	40047.5	18669.0	2648.7	2202.7	2675.7	17500.1	40047.5	18669.0	2648.7	2202.7	2675.7
41°	39777.2	17723.1	2337.8	2189.2	2391.9	15973.0	39777.2	17723.1	2337.8	2189.2	2391.9
41.5°	39743.4	17723.1	2168.9	2189.2	2385.1	14858.2	39743.4	17723.1	2168.9	2189.2	2385.1
42°	39412.3	16648.7	2168.9	2175.7	2216.2	13398.7	39412.3	16648.7	2168.9	2175.7	2216.2
42.5°	39378.5	15290.6	2054.1	2175.7	2202.7	12304.1	39378.5	15290.6	2054.1	2175.7	2202.7
43°	38905.6	12905.5	2054.1	2168.9	2101.4	10844.6	38905.6	12905.5	2054.1	2168.9	2101.4
43.5°	38905.6	11608.2	1979.7	2148.7	2006.8	8277.1	38905.6	11608.2	1979.7	2148.7	2006.8
44°	38432.6	10750.0	1979.7	2148.7	2000.0	8277.1	38432.6	10750.0	1979.7	2148.7	2000.0
44.5°	38432.6	9635.2	1918.9	2108.1	2000.0	6040.6	38432.6	9635.2	1918.9	2108.1	2000.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594655
CATALOG NUMBER: FLXB-4860-N-HI-4000K

CANDELA DISTRIBUTION (continued):

	0°	30°	60°	90°	120°	150°	180°	210°	240°	270°	300°
45°	37790.7	9067.6	1918.9	2121.6	1932.4	5216.2	37790.7	9067.6	1918.9	2121.6	1932.4
45.5°	37290.7	7547.3	1905.4	2067.6	1912.2	4432.5	37290.7	7547.3	1905.4	2067.6	1912.2
46°	37155.6	7547.3	1905.4	2074.3	1918.9	3946.0	37155.6	7547.3	1905.4	2074.3	1918.9
46.5°	36574.5	6196.0	1871.6	2040.5	1905.4	3446.0	36574.5	6196.0	1871.6	2040.5	1905.4
47°	36398.8	6196.0	1837.8	2020.3	1912.2	3196.0	36398.8	6196.0	1837.8	2020.3	1912.2
47.5°	35797.4	4891.9	1837.8	1993.3	1898.7	2804.1	35797.4	4891.9	1837.8	1993.3	1898.7
48°	35594.7	3851.4	1824.3	1986.5	1905.4	2668.9	35594.7	3851.4	1824.3	1986.5	1905.4
48.5°	34783.9	3682.4	1824.3	1946.0	1891.9	2391.9	34783.9	3682.4	1824.3	1946.0	1891.9
49°	34783.9	2932.4	1824.3	1932.4	1891.9	2148.7	34783.9	2932.4	1824.3	1932.4	1891.9
49.5°	33831.2	2797.3	1824.3	1891.9	1871.6	2094.6	33831.2	2797.3	1824.3	1891.9	1871.6
50°	33831.2	2317.6	1844.6	1891.9	1885.1	1959.5	33831.2	2317.6	1844.6	1891.9	1885.1
50.5°	32885.3	2317.6	1844.6	1891.9	1844.6	1912.2	32885.3	2317.6	1844.6	1891.9	1844.6
51°	32148.8	2094.6	1864.9	1864.9	1864.9	1804.1	32148.8	2094.6	1864.9	1864.9	1864.9
51.5°	31790.7	2013.5	1851.4	1858.1	1824.3	1756.8	31790.7	2013.5	1851.4	1858.1	1824.3
52°	31040.7	1824.3	1864.9	1817.6	1831.1	1668.9	31040.7	1824.3	1864.9	1817.6	1831.1
52.5°	30628.5	1824.3	1804.1	1790.5	1810.8	1621.6	30628.5	1824.3	1804.1	1790.5	1810.8
53°	29425.8	1696.0	1804.1	1783.8	1797.3	1554.1	29425.8	1696.0	1804.1	1783.8	1797.3
53.5°	29425.8	1635.1	1729.7	1763.5	1777.0	1506.8	29425.8	1635.1	1729.7	1763.5	1777.0
54°	28142.0	1587.8	1729.7	1756.8	1716.2	1446.0	28142.0	1587.8	1729.7	1756.8	1716.2
54.5°	28142.0	1540.5	1655.4	1743.3	1716.2	1351.4	28142.0	1540.5	1655.4	1743.3	1716.2
55°	26871.7	1500.0	1655.4	1723.0	1621.6	1317.6	26871.7	1500.0	1655.4	1723.0	1621.6
55.5°	26128.5	1418.9	1601.4	1702.7	1587.8	1277.0	26128.5	1418.9	1601.4	1702.7	1587.8
56°	25513.6	1418.9	1574.3	1689.2	1567.6	1243.2	25513.6	1418.9	1574.3	1689.2	1567.6
56.5°	24817.7	1337.8	1547.3	1655.4	1547.3	1216.2	24817.7	1337.8	1547.3	1655.4	1547.3
57°	24196.1	1337.8	1513.5	1655.4	1547.3	1196.0	24196.1	1337.8	1513.5	1655.4	1547.3
57.5°	23520.4	1277.0	1513.5	1614.9	1540.5	1168.9	23520.4	1277.0	1513.5	1614.9	1540.5
58°	22871.7	1277.0	1479.7	1601.4	1533.8	1155.4	22871.7	1277.0	1479.7	1601.4	1533.8
58.5°	21533.9	1223.0	1479.7	1567.6	1513.5	1135.1	21533.9	1223.0	1479.7	1567.6	1513.5
59°	21533.9	1189.2	1452.7	1554.1	1506.8	1155.4	21533.9	1189.2	1452.7	1554.1	1506.8
59.5°	20236.6	1196.0	1452.7	1520.3	1459.5	1155.4	20236.6	1196.0	1452.7	1520.3	1459.5
60°	20236.6	1175.7	1418.9	1513.5	1439.2	1175.7	20236.6	1175.7	1418.9	1513.5	1439.2
60.5°	18898.7	1162.2	1418.9	1500.0	1412.2	1168.9	18898.7	1162.2	1418.9	1500.0	1412.2
61°	18371.7	1135.1	1398.7	1466.2	1412.2	1168.9	18371.7	1135.1	1398.7	1466.2	1412.2
61.5°	17614.9	1135.1	1398.7	1459.5	1385.1	1168.9	17614.9	1135.1	1398.7	1459.5	1385.1
62°	17094.7	1121.6	1358.1	1439.2	1358.1	1182.4	17094.7	1121.6	1358.1	1439.2	1358.1
62.5°	16317.6	1121.6	1317.6	1439.2	1324.3	1175.7	16317.6	1121.6	1317.6	1439.2	1324.3
63°	15817.6	1108.1	1317.6	1418.9	1317.6	1168.9	15817.6	1108.1	1317.6	1418.9	1317.6
63.5°	15054.1	1108.1	1283.8	1378.4	1297.3	1175.7	15054.1	1108.1	1283.8	1378.4	1297.3
64°	13824.4	1108.1	1283.8	1337.8	1270.3	1141.9	13824.4	1108.1	1283.8	1337.8	1270.3
64.5°	13824.4	1101.4	1223.0	1317.6	1270.3	1128.4	13824.4	1101.4	1223.0	1317.6	1270.3
65°	12608.2	1101.4	1223.0	1290.5	1236.5	1128.4	12608.2	1101.4	1223.0	1290.5	1236.5
65.5°	12175.7	1148.7	1175.7	1263.5	1196.0	1114.9	12175.7	1148.7	1175.7	1263.5	1196.0
66°	11473.0	1148.7	1175.7	1256.8	1175.7	1114.9	11473.0	1148.7	1175.7	1256.8	1175.7
66.5°	11074.4	1256.8	1135.1	1236.5	1148.7	1128.4	11074.4	1256.8	1135.1	1236.5	1148.7
67°	10398.7	1256.8	1108.1	1216.2	1114.9	1141.9	10398.7	1256.8	1108.1	1216.2	1114.9

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594655
CATALOG NUMBER: FLXB-4860-N-HI-4000K

CANDELA DISTRIBUTION (continued):

	0°	30°	60°	90°	120°	150°	180°	210°	240°	270°	300°
67.5°	10020.3	1364.9	1108.1	1175.7	1101.4	1216.2	10020.3	1364.9	1108.1	1175.7	1101.4
68°	9378.4	1364.9	1060.8	1162.2	1074.3	1250.0	9378.4	1364.9	1060.8	1162.2	1074.3
68.5°	8452.7	1418.9	1060.8	1128.4	1060.8	1385.1	8452.7	1418.9	1060.8	1128.4	1060.8
69°	8452.7	1446.0	1027.0	1114.9	1027.0	1412.2	8452.7	1446.0	1027.0	1114.9	1027.0
69.5°	7581.1	1371.6	1027.0	1094.6	993.2	1439.2	7581.1	1371.6	1027.0	1094.6	993.2
70°	7581.1	1385.1	986.5	1081.1	993.2	1459.5	7581.1	1385.1	986.5	1081.1	993.2
70.5°	6770.3	1304.1	986.5	1060.8	939.2	1466.2	6770.3	1304.1	986.5	1060.8	939.2
71°	6520.3	1236.5	912.2	1033.8	912.2	1378.4	6520.3	1236.5	912.2	1033.8	912.2
71.5°	6006.8	1236.5	912.2	1006.8	885.1	1297.3	6006.8	1236.5	912.2	1006.8	885.1
72°	5790.6	1216.2	837.8	898.7	844.6	1209.5	5790.6	1216.2	837.8	898.7	844.6
72.5°	5297.3	1216.2	790.5	831.1	777.0	1128.4	5297.3	1216.2	790.5	831.1	777.0
73°	5108.1	1175.7	790.5	810.8	756.8	1013.5	5108.1	1175.7	790.5	810.8	756.8
73.5°	4628.4	1175.7	709.5	790.5	689.2	1013.5	4628.4	1175.7	709.5	790.5	689.2
74°	4000.0	1202.7	709.5	668.9	621.6	1006.8	4000.0	1202.7	709.5	668.9	621.6
74.5°	4000.0	1243.2	621.6	628.4	621.6	1006.8	4000.0	1243.2	621.6	628.4	621.6
75°	3432.4	1209.5	621.6	533.8	581.1	979.7	3432.4	1209.5	621.6	533.8	581.1
75.5°	3432.4	1081.1	547.3	527.0	554.1	952.7	3432.4	1081.1	547.3	527.0	554.1
76°	2918.9	1047.3	547.3	493.2	527.0	871.6	2918.9	1047.3	547.3	493.2	527.0
76.5°	2831.1	912.2	500.0	459.5	506.8	831.1	2831.1	912.2	500.0	459.5	506.8
77°	2466.2	912.2	500.0	439.2	445.9	810.8	2466.2	912.2	500.0	439.2	445.9
77.5°	2378.4	817.6	432.4	364.9	398.7	790.5	2378.4	817.6	432.4	364.9	398.7
78°	2054.1	783.8	317.6	351.4	358.1	770.3	2054.1	783.8	317.6	351.4	358.1
78.5°	2006.8	743.2	317.6	310.8	317.6	729.7	2006.8	743.2	317.6	310.8	317.6
79°	1716.2	695.9	270.3	297.3	270.3	695.9	1716.2	695.9	270.3	297.3	270.3
79.5°	1405.4	628.4	270.3	243.2	250.0	662.2	1405.4	628.4	270.3	243.2	250.0
80°	1405.4	601.4	229.7	209.5	250.0	581.1	1405.4	601.4	229.7	209.5	250.0
80.5°	1141.9	560.8	229.7	175.7	209.5	533.8	1141.9	560.8	229.7	175.7	209.5
81°	1114.9	479.7	155.4	155.4	175.7	459.5	1114.9	479.7	155.4	155.4	175.7
81.5°	912.2	479.7	155.4	141.9	168.9	405.4	912.2	479.7	155.4	141.9	168.9
82°	891.9	405.4	108.1	94.6	114.9	371.6	891.9	405.4	108.1	94.6	114.9
82.5°	716.2	405.4	87.8	94.6	108.1	317.6	716.2	405.4	87.8	94.6	108.1
83°	702.7	331.1	87.8	60.8	87.8	270.3	702.7	331.1	87.8	60.8	87.8
83.5°	560.8	331.1	54.1	47.3	74.3	223.0	560.8	331.1	54.1	47.3	74.3
84°	425.7	243.2	54.1	40.5	60.8	182.4	425.7	243.2	54.1	40.5	60.8
84.5°	425.7	189.2	33.8	33.8	60.8	155.4	425.7	189.2	33.8	33.8	60.8
85°	324.3	182.4	33.8	27.0	40.5	128.4	324.3	182.4	33.8	27.0	40.5
85.5°	324.3	121.6	20.3	27.0	40.5	47.3	324.3	121.6	20.3	27.0	40.5
86°	229.7	121.6	20.3	13.5	27.0	33.8	229.7	121.6	20.3	13.5	27.0
86.5°	229.7	81.1	13.5	13.5	20.3	20.3	229.7	81.1	13.5	13.5	20.3
87°	182.4	81.1	13.5	0.0	20.3	6.8	182.4	81.1	13.5	0.0	20.3
87.5°	182.4	47.3	0.0	0.0	6.8	0.0	182.4	47.3	0.0	0.0	6.8
88°	128.4	13.5	0.0	0.0	6.8	0.0	128.4	13.5	0.0	0.0	6.8
88.5°	128.4	13.5	0.0	0.0	0.0	0.0	128.4	13.5	0.0	0.0	0.0
89°	87.8	13.5	0.0	0.0	0.0	0.0	87.8	13.5	0.0	0.0	0.0
89.5°	54.1	0.0	0.0	0.0	0.0	0.0	54.1	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594655
CATALOG NUMBER: FLXB-4860-N-HI-4000K

CANDELA DISTRIBUTION (continued):

	0°	30°	60°	90°	120°	150°	180°	210°	240°	270°	300°
90°	54.1	0.0	0.0	0.0	0.0	0.0	54.1	0.0	0.0	0.0	0.0
90.5°	33.8	0.0	0.0	0.0	0.0	0.0	33.8	0.0	0.0	0.0	0.0
91°	33.8	0.0	0.0	0.0	0.0	0.0	33.8	0.0	0.0	0.0	0.0
91.5°	13.5	0.0	0.0	0.0	0.0	0.0	13.5	0.0	0.0	0.0	0.0
92°	13.5	0.0	0.0	0.0	0.0	0.0	13.5	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
93°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
93.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
94°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
94.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
96°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
96.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
98°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
98.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
99°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
99.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
101°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
101.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
103°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
103.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
104°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
104.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
106°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
106.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
108°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
108.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
109°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
109.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
111°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
111.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
112°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594655
CATALOG NUMBER: FLXB-4860-N-HI-4000K

CANDELA DISTRIBUTION (continued):

	0°	30°	60°	90°	120°	150°	180°	210°	240°	270°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
113°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
113.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
114°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
114.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
116°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
116.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
118°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
118.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
119°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
119.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
121°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
121.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
123°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
123.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
124°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
124.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
126°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
126.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
128°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
128.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
129°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
129.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
131°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
131.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
133°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
133.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
134°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
134.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594655
CATALOG NUMBER: FLXB-4860-N-HI-4000K

CANDELA DISTRIBUTION (continued):

	0°	30°	60°	90°	120°	150°	180°	210°	240°	270°	300°
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
136°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
136.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
138°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
138.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
139°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
139.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
141°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
141.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
143°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
143.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
144°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
144.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
146°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
146.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
148°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
148.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
149°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
149.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
151°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
151.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
153°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
153.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
154°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
154.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
156°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
156.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594655
CATALOG NUMBER: FLXB-4860-N-HI-4000K

CANDELA DISTRIBUTION (continued):

	0°	30°	60°	90°	120°	150°	180°	210°	240°	270°	300°
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
158°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
158.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
159°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
159.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
161°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
161.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
163°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
163.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
164°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
164.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
166°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
166.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
168°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
168.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
169°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
169.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
171°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
171.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
173°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
173.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
174°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
174.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
176°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
176.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
178°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
178.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
179°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
179.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594655
CATALOG NUMBER: FLXB-4860-N-HI-4000K

CANDELA DISTRIBUTION (continued):

	0°	30°	60°	90°	120°	150°	180°	210°	240°	270°	300°
180°	0.0	*0.0*	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1594655
CATALOG NUMBER: FLXB-4860-N-HI-4000K

CANDELA DISTRIBUTION (continued):

	330°	360°
0°	41417.1	41417.1
0.5°	41417.1	41417.1
1°	41452.9	41358.3
1.5°	*41446.1*	*41338.0*
2°	41473.1	41392.1
2.5°	41446.1	41392.1
3°	41412.3	41338.0
3.5°	41398.8	41338.0
4°	41358.3	41378.6
4.5°	41398.8	41365.0
5°	41317.7	41365.0
5.5°	41297.5	41365.0
6°	41277.2	41351.5
6.5°	41290.7	41398.8
7°	41196.1	41398.8
7.5°	41196.1	41344.8
8°	41128.6	41344.8
8.5°	41061.0	41398.8
9°	41081.3	41378.6
9.5°	40993.4	41371.8
10°	40939.4	41385.3
10.5°	40892.1	41385.3
11°	40905.6	41385.3
11.5°	40790.7	41398.8
12°	40763.7	41365.0
12.5°	40702.9	41365.0
13°	40655.6	41425.9
13.5°	40540.7	41425.9
14°	40439.4	41385.3
14.5°	40371.8	41405.6
15°	40290.7	41419.1
15.5°	40284.0	41412.3
16°	40135.3	41419.1
16.5°	40061.0	41412.3
17°	39979.9	41398.8
17.5°	39932.6	41446.1
18°	39723.1	41446.1
18.5°	39601.5	41398.8
19°	39513.7	41398.8
19.5°	39371.8	41446.1
20°	39331.3	41432.6
20.5°	39148.8	41432.6
21°	38898.8	41432.6
21.5°	38898.8	41425.9
22°	38817.7	41432.6

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594655
CATALOG NUMBER: FLXB-4860-N-HI-4000K

CANDELA DISTRIBUTION (continued):

	330°	360°
22.5°	38608.3	41452.9
23°	38500.2	41412.3
23.5°	38169.1	41412.3
24°	37946.1	41466.4
24.5°	37831.2	41432.6
25°	37581.2	41419.1
25.5°	37392.1	41425.9
26°	37169.1	41432.6
26.5°	37013.7	41425.9
27°	36702.9	41439.4
27.5°	36486.6	41392.1
28°	35979.9	41392.1
28.5°	35979.9	41446.1
29°	35405.6	41446.1
29.5°	35061.0	41392.1
30°	34743.4	41392.1
30.5°	34371.8	41405.6
31°	34081.2	41365.0
31.5°	33621.8	41371.8
32°	33229.9	41317.7
32.5°	32783.9	41317.7
33°	32371.8	41311.0
33.5°	31351.5	41311.0
34°	30770.4	41189.4
34.5°	30196.1	41189.4
35°	29547.4	41162.3
35.5°	28925.8	41047.5
36°	28169.0	41047.5
36.5°	27385.2	40919.1
37°	26560.9	40905.6
37.5°	25682.5	40770.4
38°	24675.8	40777.2
38.5°	23662.3	40534.0
39°	21365.0	40534.0
39.5°	20101.4	40351.5
40°	18729.8	40088.0
40.5°	17500.1	40047.5
41°	15973.0	39777.2
41.5°	14858.2	39743.4
42°	13398.7	39412.3
42.5°	12304.1	39378.5
43°	10844.6	38905.6
43.5°	8277.1	38905.6
44°	8277.1	38432.6
44.5°	6040.6	38432.6

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594655
CATALOG NUMBER: FLXB-4860-N-HI-4000K

CANDELA DISTRIBUTION (continued):

	330°	360°
45°	5216.2	37790.7
45.5°	4432.5	37290.7
46°	3946.0	37155.6
46.5°	3446.0	36574.5
47°	3196.0	36398.8
47.5°	2804.1	35797.4
48°	2668.9	35594.7
48.5°	2391.9	34783.9
49°	2148.7	34783.9
49.5°	2094.6	33831.2
50°	1959.5	33831.2
50.5°	1912.2	32885.3
51°	1804.1	32148.8
51.5°	1756.8	31790.7
52°	1668.9	31040.7
52.5°	1621.6	30628.5
53°	1554.1	29425.8
53.5°	1506.8	29425.8
54°	1446.0	28142.0
54.5°	1351.4	28142.0
55°	1317.6	26871.7
55.5°	1277.0	26128.5
56°	1243.2	25513.6
56.5°	1216.2	24817.7
57°	1196.0	24196.1
57.5°	1168.9	23520.4
58°	1155.4	22871.7
58.5°	1135.1	21533.9
59°	1155.4	21533.9
59.5°	1155.4	20236.6
60°	1175.7	20236.6
60.5°	1168.9	18898.7
61°	1168.9	18371.7
61.5°	1168.9	17614.9
62°	1182.4	17094.7
62.5°	1175.7	16317.6
63°	1168.9	15817.6
63.5°	1175.7	15054.1
64°	1141.9	13824.4
64.5°	1128.4	13824.4
65°	1128.4	12608.2
65.5°	1114.9	12175.7
66°	1114.9	11473.0
66.5°	1128.4	11074.4
67°	1141.9	10398.7

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594655
CATALOG NUMBER: FLXB-4860-N-HI-4000K

CANDELA DISTRIBUTION (continued):

	330°	360°
67.5°	1216.2	10020.3
68°	1250.0	9378.4
68.5°	1385.1	8452.7
69°	1412.2	8452.7
69.5°	1439.2	7581.1
70°	1459.5	7581.1
70.5°	1466.2	6770.3
71°	1378.4	6520.3
71.5°	1297.3	6006.8
72°	1209.5	5790.6
72.5°	1128.4	5297.3
73°	1013.5	5108.1
73.5°	1013.5	4628.4
74°	1006.8	4000.0
74.5°	1006.8	4000.0
75°	979.7	3432.4
75.5°	952.7	3432.4
76°	871.6	2918.9
76.5°	831.1	2831.1
77°	810.8	2466.2
77.5°	790.5	2378.4
78°	770.3	2054.1
78.5°	729.7	2006.8
79°	695.9	1716.2
79.5°	662.2	1405.4
80°	581.1	1405.4
80.5°	533.8	1141.9
81°	459.5	1114.9
81.5°	405.4	912.2
82°	371.6	891.9
82.5°	317.6	716.2
83°	270.3	702.7
83.5°	223.0	560.8
84°	182.4	425.7
84.5°	155.4	425.7
85°	128.4	324.3
85.5°	47.3	324.3
86°	33.8	229.7
86.5°	20.3	229.7
87°	6.8	182.4
87.5°	0.0	182.4
88°	0.0	128.4
88.5°	0.0	128.4
89°	0.0	87.8
89.5°	0.0	54.1

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594655
CATALOG NUMBER: FLXB-4860-N-HI-4000K

CANDELA DISTRIBUTION (continued):

	330°	360°
90°	0.0	54.1
90.5°	0.0	33.8
91°	0.0	33.8
91.5°	0.0	13.5
92°	0.0	13.5
92.5°	0.0	0.0
93°	0.0	0.0
93.5°	0.0	0.0
94°	0.0	0.0
94.5°	0.0	0.0
95°	0.0	0.0
95.5°	0.0	0.0
96°	0.0	0.0
96.5°	0.0	0.0
97°	0.0	0.0
97.5°	0.0	0.0
98°	0.0	0.0
98.5°	0.0	0.0
99°	0.0	0.0
99.5°	0.0	0.0
100°	0.0	0.0
100.5°	0.0	0.0
101°	0.0	0.0
101.5°	0.0	0.0
102°	0.0	0.0
102.5°	0.0	0.0
103°	0.0	0.0
103.5°	0.0	0.0
104°	0.0	0.0
104.5°	0.0	0.0
105°	0.0	0.0
105.5°	0.0	0.0
106°	0.0	0.0
106.5°	0.0	0.0
107°	0.0	0.0
107.5°	0.0	0.0
108°	0.0	0.0
108.5°	0.0	0.0
109°	0.0	0.0
109.5°	0.0	0.0
110°	0.0	0.0
110.5°	0.0	0.0
111°	0.0	0.0
111.5°	0.0	0.0
112°	0.0	0.0

TEST NUMBER: P1594655
CATALOG NUMBER: FLXB-4860-N-HI-4000K

CANDELA DISTRIBUTION (continued):

	330°	360°
112.5°	0.0	0.0
113°	0.0	0.0
113.5°	0.0	0.0
114°	0.0	0.0
114.5°	0.0	0.0
115°	0.0	0.0
115.5°	0.0	0.0
116°	0.0	0.0
116.5°	0.0	0.0
117°	0.0	0.0
117.5°	0.0	0.0
118°	0.0	0.0
118.5°	0.0	0.0
119°	0.0	0.0
119.5°	0.0	0.0
120°	0.0	0.0
120.5°	0.0	0.0
121°	0.0	0.0
121.5°	0.0	0.0
122°	0.0	0.0
122.5°	0.0	0.0
123°	0.0	0.0
123.5°	0.0	0.0
124°	0.0	0.0
124.5°	0.0	0.0
125°	0.0	0.0
125.5°	0.0	0.0
126°	0.0	0.0
126.5°	0.0	0.0
127°	0.0	0.0
127.5°	0.0	0.0
128°	0.0	0.0
128.5°	0.0	0.0
129°	0.0	0.0
129.5°	0.0	0.0
130°	0.0	0.0
130.5°	0.0	0.0
131°	0.0	0.0
131.5°	0.0	0.0
132°	0.0	0.0
132.5°	0.0	0.0
133°	0.0	0.0
133.5°	0.0	0.0
134°	0.0	0.0
134.5°	0.0	0.0

TEST NUMBER: P1594655
CATALOG NUMBER: FLXB-4860-N-HI-4000K

CANDELA DISTRIBUTION (continued):

	330°	360°
135°	0.0	0.0
135.5°	0.0	0.0
136°	0.0	0.0
136.5°	0.0	0.0
137°	0.0	0.0
137.5°	0.0	0.0
138°	0.0	0.0
138.5°	0.0	0.0
139°	0.0	0.0
139.5°	0.0	0.0
140°	0.0	0.0
140.5°	0.0	0.0
141°	0.0	0.0
141.5°	0.0	0.0
142°	0.0	0.0
142.5°	0.0	0.0
143°	0.0	0.0
143.5°	0.0	0.0
144°	0.0	0.0
144.5°	0.0	0.0
145°	0.0	0.0
145.5°	0.0	0.0
146°	0.0	0.0
146.5°	0.0	0.0
147°	0.0	0.0
147.5°	0.0	0.0
148°	0.0	0.0
148.5°	0.0	0.0
149°	0.0	0.0
149.5°	0.0	0.0
150°	0.0	0.0
150.5°	0.0	0.0
151°	0.0	0.0
151.5°	0.0	0.0
152°	0.0	0.0
152.5°	0.0	0.0
153°	0.0	0.0
153.5°	0.0	0.0
154°	0.0	0.0
154.5°	0.0	0.0
155°	0.0	0.0
155.5°	0.0	0.0
156°	0.0	0.0
156.5°	0.0	0.0
157°	0.0	0.0

TEST NUMBER: P1594655
CATALOG NUMBER: FLXB-4860-N-HI-4000K

CANDELA DISTRIBUTION (continued):

	330°	360°
157.5°	0.0	0.0
158°	0.0	0.0
158.5°	0.0	0.0
159°	0.0	0.0
159.5°	0.0	0.0
160°	0.0	0.0
160.5°	0.0	0.0
161°	0.0	0.0
161.5°	0.0	0.0
162°	0.0	0.0
162.5°	0.0	0.0
163°	0.0	0.0
163.5°	0.0	0.0
164°	0.0	0.0
164.5°	0.0	0.0
165°	0.0	0.0
165.5°	0.0	0.0
166°	0.0	0.0
166.5°	0.0	0.0
167°	0.0	0.0
167.5°	0.0	0.0
168°	0.0	0.0
168.5°	0.0	0.0
169°	0.0	0.0
169.5°	0.0	0.0
170°	0.0	0.0
170.5°	0.0	0.0
171°	0.0	0.0
171.5°	0.0	0.0
172°	0.0	0.0
172.5°	0.0	0.0
173°	0.0	0.0
173.5°	0.0	0.0
174°	0.0	0.0
174.5°	0.0	0.0
175°	0.0	0.0
175.5°	0.0	0.0
176°	0.0	0.0
176.5°	0.0	0.0
177°	0.0	0.0
177.5°	0.0	0.0
178°	0.0	0.0
178.5°	0.0	0.0
179°	0.0	0.0
179.5°	0.0	0.0

TEST NUMBER: P1594655
CATALOG NUMBER: FLXB-4860-N-HI-4000K

CANDELA DISTRIBUTION (continued):

	330°	360°
180°	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594655
CATALOG NUMBER: FLXB-4860-N-HI-4000K

CIE UGR TABLE:

Reflectances:											
	Ceiling	0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
	Wall	0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
	Reference plane	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room Dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	28.1	29.4	28.4	29.7	30.0	15.3	16.6	15.7	16.9	17.2
	3H	29.7	30.9	30.1	31.2	31.6	17.5	18.7	17.9	19.0	19.3
	4H	30.1	31.2	30.5	31.5	31.9	18.1	19.1	18.5	19.5	19.9
	6H	30.3	31.2	30.7	31.6	32.0	18.2	19.2	18.7	19.6	20.0
	8H	30.3	31.2	30.7	31.6	32.0	18.2	19.2	18.7	19.5	20.0
	12H	30.2	31.1	30.7	31.5	31.9	18.2	19.1	18.6	19.5	19.9
4H	2H	27.9	28.9	28.3	29.3	29.7	15.9	17.0	16.3	17.3	17.7
	3H	29.5	30.4	29.9	30.8	31.2	18.3	19.2	18.7	19.6	20.0
	4H	30.0	30.8	30.4	31.2	31.6	18.9	19.7	19.4	20.1	20.6
	6H	30.2	30.9	30.7	31.3	31.8	19.2	19.8	19.6	20.3	20.8
	8H	30.2	30.9	30.7	31.3	31.8	19.2	19.8	19.6	20.2	20.7
	12H	30.2	30.8	30.7	31.3	31.7	19.1	19.7	19.6	20.2	20.6
8H	4H	29.9	30.5	30.3	30.9	31.4	19.5	20.1	20.0	20.6	21.0
	6H	30.1	30.6	30.6	31.1	31.6	19.7	20.2	20.2	20.7	21.2
	8H	30.1	30.6	30.7	31.1	31.6	19.7	20.2	20.3	20.7	21.2
	12H	30.1	30.5	30.7	31.0	31.6	19.7	20.1	20.2	20.6	21.2
12H	4H	29.8	30.4	30.3	30.9	31.3	19.6	20.1	20.1	20.6	21.1
	6H	30.1	30.5	30.6	31.0	31.5	19.9	20.3	20.4	20.8	21.3
	8H	30.1	30.5	30.6	31.0	31.6	19.9	20.3	20.4	20.8	21.3

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP3-2602-684-3

Test Date: 02/20/2026

Luminaire Tested: HLBX-2436-W-HI-4000K

Data in this report applies to families of products including HLBX-2436*

Report Generated By FNC07603 / LDUCLS01DT01661
Version: v7.05


Test Information

Test Method:	LM-79-2019
Report Number:	SP3-2602-684-3
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP3 - 3M SPHERE
Measurement Geometry:	4π
Issue Date:	02/27/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	Metalux
Catalog Number:	**HLBX-2436-W-HI-4000K**
Description:	LDS HLBX 2436 W beam, HI lumen, 4000K CCT settings

Spectral Parameters

CCT (K):	4000
CIE u':	0.2271
CIE v':	0.4972
Duv:	-0.0036
CIE x:	0.3780
CIE y:	0.3677
CIE z:	0.2543
Peak Wavelength (nm):	454
Dominant Wavelength (nm):	581
Purity:	23.78071
Rf:	83.8
Rg:	95.3

CRI (Ra):	84.8
R1:	84.5
R2:	92.5
R3:	95.4
R4:	82.5
R5:	84.0
R6:	87.9
R7:	85.2
R8:	66.3
R9:	16.8
R10:	80.6
R11:	81.5
R12:	62.9
R13:	87.1
R14:	98.1
R15:	79.5



Test Conditions


Stabilization Time:	22M
Operation Time:	1H 22M
Sphere Temperature (°C):	25.0

REPORT NUMBER: SP3-2602-684-3


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	3M SPHERE IN02505	1/10/2026	7/10/2026
Power Meter	XITRON INXT2011006	10/21/2025	10/21/2026
AC Power Source	CHROMA 61604 IN6064A	10/20/2025	10/20/2026
DC Power Source	EYSIGHT N5770A IN0534	10/20/2025	10/20/2026
Sphere Thermometer	TANDD IN4036E	10/21/2025	10/21/2026

REPORT NUMBER: SP3-2602-684-3

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 4000K
CIE x = 0.3780
CIE y = 0.3677
Duv = -0.0036

Point lies inside the ANSI 4000K 7-step quadrangle

REPORT NUMBER: SP3-2602-684-3

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	258	NR	620	689	NR	750	21	NR	880	1	NR
365	0	NR	495	283	NR	625	645	NR	755	18	NR	885	1	NR
370	0	NR	500	331	NR	630	600	NR	760	15	NR	890	1	NR
375	0	NR	505	383	NR	635	550	NR	765	13	NR	895	0	NR
380	0	NR	510	428	NR	640	501	NR	770	11	NR	900	0	NR
385	0	NR	515	469	NR	645	450	NR	775	9	NR	905	0	NR
390	1	NR	520	502	NR	650	404	NR	780	8	NR	910	0	NR
395	3	NR	525	526	NR	655	359	NR	785	7	NR	915	0	NR
400	4	NR	530	543	NR	660	317	NR	790	6	NR	920	0	NR
405	7	NR	535	559	NR	665	278	NR	795	5	NR	925	0	NR
410	10	NR	540	573	NR	670	243	NR	800	4	NR	930	0	NR
415	18	NR	545	587	NR	675	212	NR	805	4	NR	935	0	NR
420	32	NR	550	603	NR	680	183	NR	810	3	NR	940	0	NR
425	55	NR	555	619	NR	685	159	NR	815	3	NR	945	0	NR
430	95	NR	560	640	NR	690	136	NR	820	2	NR	950	0	NR
435	164	NR	565	666	NR	695	117	NR	825	2	NR	955	0	NR
440	273	NR	570	689	NR	700	100	NR	830	2	NR	960	0	NR
445	480	NR	575	718	NR	705	85	NR	835	2	NR	965	0	NR
450	835	NR	580	743	NR	710	73	NR	840	1	NR	970	0	NR
455	998	NR	585	764	NR	715	63	NR	845	1	NR	975	0	NR
460	735	NR	590	781	NR	720	54	NR	850	1	NR	980	0	NR
465	533	NR	595	789	NR	725	46	NR	855	1	NR	985	0	NR
470	435	NR	600	787	NR	730	39	NR	860	1	NR	990	0	NR
475	320	NR	605	775	NR	735	33	NR	865	1	NR	995	0	NR
480	254	NR	610	755	NR	740	28	NR	870	1	NR	1000	0	NR
485	245	NR	615	725	NR	745	24	NR	875	1	NR			

REPORT NUMBER: SP3-2602-684-3

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.73**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	258	NR	620	689	NR	750	21	NR	880	1	NR
365	0	NR	495	283	NR	625	645	NR	755	18	NR	885	1	NR
370	0	NR	500	331	NR	630	600	NR	760	15	NR	890	1	NR
375	0	NR	505	383	NR	635	550	NR	765	13	NR	895	0	NR
380	0	NR	510	428	NR	640	501	NR	770	11	NR	900	0	NR
385	0	NR	515	469	NR	645	450	NR	775	9	NR	905	0	NR
390	1	NR	520	502	NR	650	404	NR	780	8	NR	910	0	NR
395	3	NR	525	526	NR	655	359	NR	785	7	NR	915	0	NR
400	4	NR	530	543	NR	660	317	NR	790	6	NR	920	0	NR
405	7	NR	535	559	NR	665	278	NR	795	5	NR	925	0	NR
410	10	NR	540	573	NR	670	243	NR	800	4	NR	930	0	NR
415	18	NR	545	587	NR	675	212	NR	805	4	NR	935	0	NR
420	32	NR	550	603	NR	680	183	NR	810	3	NR	940	0	NR
425	55	NR	555	619	NR	685	159	NR	815	3	NR	945	0	NR
430	95	NR	560	640	NR	690	136	NR	820	2	NR	950	0	NR
435	164	NR	565	666	NR	695	117	NR	825	2	NR	955	0	NR
440	273	NR	570	689	NR	700	100	NR	830	2	NR	960	0	NR
445	480	NR	575	718	NR	705	85	NR	835	2	NR	965	0	NR
450	835	NR	580	743	NR	710	73	NR	840	1	NR	970	0	NR
455	998	NR	585	764	NR	715	63	NR	845	1	NR	975	0	NR
460	735	NR	590	781	NR	720	54	NR	850	1	NR	980	0	NR
465	533	NR	595	789	NR	725	46	NR	855	1	NR	985	0	NR
470	435	NR	600	787	NR	730	39	NR	860	1	NR	990	0	NR
475	320	NR	605	775	NR	735	33	NR	865	1	NR	995	0	NR
480	254	NR	610	755	NR	740	28	NR	870	1	NR	1000	0	NR
485	245	NR	615	725	NR	745	24	NR	875	1	NR			

REPORT NUMBER: SP3-2602-684-3

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 3.62**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	258	NR	620	689	NR	750	21	NR	880	1	NR
365	0	NR	495	283	NR	625	645	NR	755	18	NR	885	1	NR
370	0	NR	500	331	NR	630	600	NR	760	15	NR	890	1	NR
375	0	NR	505	383	NR	635	550	NR	765	13	NR	895	0	NR
380	0	NR	510	428	NR	640	501	NR	770	11	NR	900	0	NR
385	0	NR	515	469	NR	645	450	NR	775	9	NR	905	0	NR
390	1	NR	520	502	NR	650	404	NR	780	8	NR	910	0	NR
395	3	NR	525	526	NR	655	359	NR	785	7	NR	915	0	NR
400	4	NR	530	543	NR	660	317	NR	790	6	NR	920	0	NR
405	7	NR	535	559	NR	665	278	NR	795	5	NR	925	0	NR
410	10	NR	540	573	NR	670	243	NR	800	4	NR	930	0	NR
415	18	NR	545	587	NR	675	212	NR	805	4	NR	935	0	NR
420	32	NR	550	603	NR	680	183	NR	810	3	NR	940	0	NR
425	55	NR	555	619	NR	685	159	NR	815	3	NR	945	0	NR
430	95	NR	560	640	NR	690	136	NR	820	2	NR	950	0	NR
435	164	NR	565	666	NR	695	117	NR	825	2	NR	955	0	NR
440	273	NR	570	689	NR	700	100	NR	830	2	NR	960	0	NR
445	480	NR	575	718	NR	705	85	NR	835	2	NR	965	0	NR
450	835	NR	580	743	NR	710	73	NR	840	1	NR	970	0	NR
455	998	NR	585	764	NR	715	63	NR	845	1	NR	975	0	NR
460	735	NR	590	781	NR	720	54	NR	850	1	NR	980	0	NR
465	533	NR	595	789	NR	725	46	NR	855	1	NR	985	0	NR
470	435	NR	600	787	NR	730	39	NR	860	1	NR	990	0	NR
475	320	NR	605	775	NR	735	33	NR	865	1	NR	995	0	NR
480	254	NR	610	755	NR	740	28	NR	870	1	NR	1000	0	NR
485	245	NR	615	725	NR	745	24	NR	875	1	NR			


REPORT NUMBER: SP3-2602-684-3

TM-30-18


Summary


R_f = 83.8
R_g = 95.3
CIE R_a = 84.8
R_9 = 16.8


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP3-2602-684-3

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 84	CES51 = 92	CES76 = 77
CES02 = 61	CES27 = 90	CES52 = 93	CES77 = 82
CES03 = 31	CES28 = 91	CES53 = 89	CES78 = 76
CES04 = 70	CES29 = 91	CES54 = 88	CES79 = 92
CES05 = 48	CES30 = 88	CES55 = 84	CES80 = 89
CES06 = 51	CES31 = 93	CES56 = 84	CES81 = 80
CES07 = 41	CES32 = 84	CES57 = 82	CES82 = 95
CES08 = 40	CES33 = 97	CES58 = 82	CES83 = 96
CES09 = 29	CES34 = 87	CES59 = 91	CES84 = 90
CES10 = 74	CES35 = 93	CES60 = 88	CES85 = 77
CES11 = 57	CES36 = 76	CES61 = 85	CES86 = 75
CES12 = 63	CES37 = 92	CES62 = 77	CES87 = 85
CES13 = 43	CES38 = 82	CES63 = 83	CES88 = 91
CES14 = 74	CES39 = 98	CES64 = 75	CES89 = 79
CES15 = 71	CES40 = 97	CES65 = 76	CES90 = 91
CES16 = 47	CES41 = 95	CES66 = 71	CES91 = 66
CES17 = 49	CES42 = 93	CES67 = 70	CES92 = 65
CES18 = 56	CES43 = 90	CES68 = 76	CES93 = 78
CES19 = 71	CES44 = 99	CES69 = 80	CES94 = 65
CES20 = 65	CES45 = 95	CES70 = 73	CES95 = 73
CES21 = 86	CES46 = 92	CES71 = 65	CES96 = 85
CES22 = 78	CES47 = 94	CES72 = 88	CES97 = 90
CES23 = 91	CES48 = 84	CES73 = 68	CES98 = 87
CES24 = 90	CES49 = 91	CES74 = 89	CES99 = 80
CES25 = 71	CES50 = 93	CES75 = 70	





REPORT NUMBER: SP3-2602-684-3

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP3-2602-684-3

TM-30-18

Measure Comparisons





(END OF REPORT)