Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: METALUX

Report Number: P1594660

Luminaire Tested: FLXB-4860-N-LOW-4000K

Issue Date: 10/2/2026

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-2019
Report Number:	P1594660
	TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (A2601781A001)
Test Lab:	INNOVATION CENTER
Issue Date:	10/2/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	METALUX
Catalog Number:	FLXB-4860-N-LOW-4000K
Description:	4860 FlexBay Linear High bay at N beam, LOW lumen, 4000K CCT settings
Light Source:	-
Ballast/Driver:	-

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	49741.0 lumens
Efficiency:	N/A
Efficacy:	170.5 lumens/watt
Spacing Criteria (0/90/45):	1.51 / 0.92 / 0.99
Luminous Opening:	Rectangular (W 1.04' x L: 2.12' x H: 0')
CIE Type:	Direct


Input Watts (W):	291.7
Input Voltage (V):	NR
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	NR
Total Harmonic Distortion (THDi):	NR
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	28.75 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594660
CATALOG NUMBER: FLXB-4860-N-LOW-4000K

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594660
CATALOG NUMBER: FLXB-4860-N-LOW-4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	95	93	92	90
2	104	98	93	88	102	96	91	87	93	89	85	90	86	83	87	84	82	80
3	97	89	83	78	95	87	82	77	85	80	76	82	78	74	80	76	73	71
4	91	81	74	69	89	80	73	68	78	72	68	76	71	67	74	69	66	64
5	85	74	67	62	83	73	67	62	71	66	61	70	64	60	68	63	60	58
6	80	69	61	56	78	68	61	56	66	60	55	65	59	55	63	58	54	53
7	75	63	56	51	73	63	56	51	61	55	51	60	54	50	59	54	50	48
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	42	41
10	63	51	44	40	62	51	44	40	50	44	40	49	43	40	48	43	39	38

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	163036	163036	163036	163036
5°	163453	162412	163453	162412
10°	165424	158942	165424	158942
15°	168796	152769	168796	152769
20°	173564	140589	173564	140589
25°	179899	118211	179899	118211
30°	188144	73709	188144	73709
35°	197806	25846	197806	25846
40°	205999	11736	205999	11736
45°	210380	11811	210380	11811
50°	207183	11586	207183	11586
55°	184420	11825	184420	11825
60°	159320	11915	159320	11915
65°	117437	12020	117437	12020
70°	87254	12443	87254	12443
75°	52205	8118	52205	8118
80°	31859	4749	31859	4749
85°	14651	1222	14651	1222

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 46°
Luminance: 210551 cd/sqm

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594660
CATALOG NUMBER: FLXB-4860-N-LOW-4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	3164.5	6.4
10°-20°	8957.1	18.0
20°-30°	12551.3	25.2
30°-40°	10743.2	21.6
40°-50°	6303.1	12.7
50°-60°	4204.1	8.5
60°-70°	2568.6	5.2
70°-80°	1094.9	2.2
80°-90°	153.2	0.3
90°-100°	0.9	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	24673.0	49.6
0°-40°	35416.2	71.2
0°-60°	45923.4	92.3
0°-90°	49740.1	100.0
90°-120°	0.9	0.0
90°-150°	0.9	0.0
90°-180°	1.0	0.0
0°-180°	49741.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	33528	33528	33528	33528	33528	
5°	33486	33273	33486	33273	33486	3197
15°	33530	30347	33530	30347	33530	9503
25°	33530	22032	33530	22032	33530	15522
35°	33322	4354	33322	4354	33322	20853
45°	30593	1718	30593	1718	30593	23450
55°	21754	1395	21754	1395	21754	19430
65°	10207	1045	10207	1045	10207	10471
75°	2779	432	2779	432	2779	3288
85°	263	22	263	22	263	395
90°	44	0	44	0	44	28
95°	0	0	0	0	0	0
105°	0	0	0	0	0	0
115°	0	0	0	0	0	0
125°	0	0	0	0	0	0
135°	0	0	0	0	0	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594660
CATALOG NUMBER: FLXB-4860-N-LOW-4000K

CANDELA DISTRIBUTION (FULL):

	0°	30°	60°	90°	120°	150°	180°	210°	240°	270°	300°
0°	33528.5	33528.5	33528.5	33528.5	33528.5	33528.5	33528.5	33528.5	33528.5	33528.5	33528.5
0.5°	33528.5	33528.5	33528.5	33528.5	33528.5	33528.5	33528.5	33528.5	33528.5	33528.5	33528.5
1°	33480.9	33661.4	33453.6	33628.6	33349.7	33557.5	33480.9	33661.4	33453.6	33628.6	33349.7
1.5°	33464.5	33683.3	33404.4	33628.6	33278.5	33552.0	33464.5	33683.3	33404.4	33628.6	33278.5
2°	33508.3	33683.3	33404.4	33563.0	33229.3	33573.9	33508.3	33683.3	33404.4	33563.0	33229.3
2.5°	33508.3	33666.9	33349.7	33573.9	33229.3	33552.0	33508.3	33666.9	33349.7	33573.9	33229.3
3°	33464.5	33666.9	33349.7	33502.8	33196.5	33524.7	33464.5	33666.9	33349.7	33502.8	33196.5
3.5°	33464.5	33634.1	33300.4	33502.8	33212.9	33513.7	33464.5	33634.1	33300.4	33502.8	33212.9
4°	33497.3	33645.0	33300.4	33398.9	33109.0	33480.9	33497.3	33645.0	33300.4	33398.9	33109.0
4.5°	33486.4	33639.6	33207.4	33398.9	33114.5	33513.8	33486.4	33639.6	33207.4	33398.9	33114.5
5°	33486.4	33623.1	33207.4	33273.1	32709.7	33448.1	33486.4	33623.1	33207.4	33273.1	32709.7
5.5°	33486.4	33568.4	33147.3	33196.5	32731.6	33431.7	33486.4	33568.4	33147.3	33196.5	32731.6
6°	33475.5	33579.4	32977.7	33125.4	32731.6	33415.3	33475.5	33579.4	32977.7	33125.4	32731.6
6.5°	33513.7	33568.4	32977.7	32955.8	32715.2	33426.2	33513.7	33568.4	32977.7	32955.8	32715.2
7°	33513.7	33497.3	32884.7	32955.8	32715.2	33349.7	33513.7	33497.3	32884.7	32955.8	32715.2
7.5°	33470.0	33497.3	32884.7	32775.3	32709.7	33349.7	33470.0	33497.3	32884.7	32775.3	32709.7
8°	33470.0	33442.6	32731.6	32775.3	32567.5	33295.0	33470.0	33442.6	32731.6	32775.3	32567.5
8.5°	33513.7	33442.6	32731.6	32567.5	32540.1	33240.3	33513.7	33442.6	32731.6	32567.5	32540.1
9°	33497.3	33409.8	32540.1	32567.5	32354.1	33256.7	33497.3	33409.8	32540.1	32567.5	32354.1
9.5°	33491.9	33382.5	32540.1	32332.3	32354.1	33185.6	33491.9	33382.5	32540.1	32332.3	32354.1
10°	33502.8	33322.3	32392.4	32190.1	32162.7	33141.8	33502.8	33322.3	32392.4	32190.1	32162.7
10.5°	33502.8	33316.8	32124.4	31993.1	32162.7	33103.5	33502.8	33316.8	32124.4	31993.1	32162.7
11°	33502.8	33289.5	32124.4	31812.6	31922.0	33114.5	33502.8	33289.5	32124.4	31812.6	31922.0
11.5°	33513.8	33240.3	31938.4	31812.6	31922.0	33021.5	33513.8	33240.3	31938.4	31812.6	31922.0
12°	33486.4	33180.1	31938.4	31511.8	31703.2	32999.6	33486.4	33180.1	31938.4	31511.8	31703.2
12.5°	33486.4	33103.5	31681.4	31336.8	31495.4	32950.4	33486.4	33103.5	31681.4	31336.8	31495.4
13°	33535.6	33059.8	31681.4	31139.8	31413.3	32912.1	33535.6	33059.8	31681.4	31139.8	31413.3
13.5°	33535.6	33032.4	31621.2	30964.8	31216.4	32819.1	33535.6	33032.4	31621.2	30964.8	31216.4
14°	33502.8	32972.2	31413.3	30762.4	31150.8	32737.0	33502.8	32972.2	31413.3	30762.4	31150.8
14.5°	33519.2	32895.7	31134.4	30549.1	30822.6	32682.3	33519.2	32895.7	31134.4	30549.1	30822.6
15°	33530.2	32884.7	31134.4	30346.7	30822.6	32616.7	33530.2	32884.7	31134.4	30346.7	30822.6
15.5°	33524.7	32846.4	30784.3	29887.2	30461.6	32611.2	33524.7	32846.4	30784.3	29887.2	30461.6
16°	33530.2	32846.4	30456.1	29630.2	30461.6	32490.9	33530.2	32846.4	30456.1	29630.2	30461.6
16.5°	33524.7	32687.8	30456.1	29389.5	30346.7	32430.7	33524.7	32687.8	30456.1	29389.5	30346.7
17°	33513.8	32583.9	30040.4	29083.2	30100.6	32365.1	33513.8	32583.9	30040.4	29083.2	30100.6
17.5°	33552.0	32583.9	30040.4	28804.2	29657.5	32326.8	33552.0	32583.9	30040.4	28804.2	29657.5
18°	33552.0	32463.5	29624.7	28503.4	29351.2	32157.2	33552.0	32463.5	29624.7	28503.4	29351.2
18.5°	33513.7	32354.1	29624.7	28224.4	29209.0	32058.8	33513.7	32354.1	29624.7	28224.4	29209.0
19°	33513.7	32283.0	29159.8	27863.4	28689.3	31987.7	33513.7	32283.0	29159.8	27863.4	28689.3
19.5°	33552.0	32222.9	29159.8	27546.2	28689.3	31872.8	33552.0	32222.9	29159.8	27546.2	28689.3
20°	33541.1	32222.9	28623.7	27168.7	28131.4	31840.0	33541.1	32222.9	28623.7	27168.7	28131.4
20.5°	33541.1	32124.4	28623.7	26824.1	28131.4	31692.3	33541.1	32124.4	28623.7	26824.1	28131.4
21°	33541.1	31949.4	28093.1	26025.5	27535.2	31489.9	33541.1	31949.4	28093.1	26025.5	27535.2
21.5°	33535.6	31867.3	27436.8	25555.1	27535.2	31489.9	33535.6	31867.3	27436.8	25555.1	27535.2
22°	33541.1	31790.7	27436.8	25144.9	26851.5	31424.3	33541.1	31790.7	27436.8	25144.9	26851.5

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594660
CATALOG NUMBER: FLXB-4860-N-LOW-4000K

CANDELA DISTRIBUTION (continued):

	0°	30°	60°	90°	120°	150°	180°	210°	240°	270°	300°
22.5°	33557.5	31561.0	26769.4	24647.1	25609.8	31254.7	33557.5	31561.0	26769.4	24647.1	25609.8
23°	33524.7	31561.0	26769.4	24220.5	25352.7	31167.2	33524.7	31561.0	26769.4	24220.5	25352.7
23.5°	33524.7	31331.3	26020.1	23635.2	25352.7	30899.2	33524.7	31331.3	26020.1	23635.2	25352.7
24°	33568.4	31331.3	26020.1	23159.3	25035.5	30718.7	33568.4	31331.3	26020.1	23159.3	25035.5
24.5°	33541.1	31085.1	25188.6	22541.2	24707.3	30625.7	33541.1	31085.1	25188.6	22541.2	24707.3
25°	33530.2	30910.1	25188.6	22032.5	24707.3	30423.3	33530.2	30910.1	25188.6	22032.5	24707.3
25.5°	33535.6	30757.0	24318.9	20769.0	23788.4	30270.1	33535.6	30757.0	24318.9	20769.0	23788.4
26°	33541.1	30603.8	23307.0	20769.0	23175.7	30089.6	33541.1	30603.8	23307.0	20769.0	23175.7
26.5°	33535.6	30467.0	23307.0	19352.3	22754.6	29963.8	33535.6	30467.0	23307.0	19352.3	22754.6
27°	33546.6	30259.2	22262.3	18417.0	22092.7	29712.2	33546.6	30259.2	22262.3	18417.0	22092.7
27.5°	33508.3	30084.2	22262.3	17798.9	21655.1	29537.2	33508.3	30084.2	22262.3	17798.9	21655.1
28°	33508.3	29717.7	21069.8	16748.7	20927.6	29126.9	33508.3	29717.7	21069.8	16748.7	20927.6
28.5°	33552.0	29717.7	21069.8	16054.0	19636.7	29126.9	33552.0	29717.7	21069.8	16054.0	19636.7
29°	33552.0	29296.5	19779.0	14943.6	19636.7	28662.0	33552.0	29296.5	19779.0	14943.6	19636.7
29.5°	33508.3	29006.6	19779.0	14221.6	18236.5	28383.0	33508.3	29006.6	19779.0	14221.6	18236.5
30°	33508.3	28776.9	18378.7	13127.6	17612.9	28125.9	33508.3	28776.9	18378.7	13127.6	17612.9
30.5°	33519.2	28470.6	18378.7	12334.5	16683.0	27825.1	33519.2	28470.6	18378.7	12334.5	16683.0
31°	33486.4	28257.2	16792.4	10431.0	15988.4	27589.9	33486.4	28257.2	16792.4	10431.0	15988.4
31.5°	33491.9	27890.7	15047.5	9501.1	15069.4	27218.0	33491.9	27890.7	15047.5	9501.1	15069.4
32°	33448.1	27633.7	15047.5	8636.9	14287.2	26900.7	33448.1	27633.7	15047.5	8636.9	14287.2
32.5°	33448.1	26966.3	13138.6	7821.9	13433.9	26539.7	33448.1	26966.3	13138.6	7821.9	13433.9
33°	33442.6	26966.3	13138.6	6963.1	11732.8	26206.0	33442.6	26966.3	13138.6	6963.1	11732.8
33.5°	33442.6	26189.6	11185.8	6295.8	11732.8	25380.1	33442.6	26189.6	11185.8	6295.8	11732.8
34°	33344.2	26189.6	11185.8	5508.1	9977.0	24909.7	33344.2	26189.6	11185.8	5508.1	9977.0
34.5°	33344.2	25292.6	9151.1	5081.5	8773.6	24444.7	33344.2	25292.6	9151.1	5081.5	8773.6
35°	33322.3	24641.7	9151.1	4354.0	8221.2	23919.6	33322.3	24641.7	9151.1	4354.0	8221.2
35.5°	33229.3	24297.1	7236.6	4096.9	7006.9	23416.4	33229.3	24297.1	7236.6	4096.9	7006.9
36°	33229.3	23520.3	7236.6	3424.1	6618.5	22803.8	33229.3	23520.3	7236.6	3424.1	6618.5
36.5°	33125.4	23099.2	5590.2	2713.0	5524.5	22169.3	33125.4	23099.2	5590.2	2713.0	5524.5
37°	33114.5	22213.0	4261.0	2620.1	5316.7	21502.0	33114.5	22213.0	4261.0	2620.1	5316.7
37.5°	33005.1	21780.9	4261.0	2248.1	4343.1	20790.9	33005.1	21780.9	4261.0	2248.1	4343.1
38°	33010.5	20238.4	3243.6	2187.9	4228.2	19975.9	33010.5	20238.4	3243.6	2187.9	4228.2
38.5°	32813.6	20238.4	3243.6	1991.0	3292.8	19155.4	32813.6	20238.4	3243.6	1991.0	3292.8
39°	32813.6	18564.7	2538.0	1947.3	3292.8	17295.7	32813.6	18564.7	2538.0	1947.3	3292.8
39.5°	32665.9	18564.7	2538.0	1848.8	2570.8	16272.8	32665.9	18564.7	2538.0	1848.8	2570.8
40°	32452.6	15113.2	2144.2	1848.8	2177.0	15162.4	32452.6	15113.2	2144.2	1848.8	2177.0
40.5°	32419.8	15113.2	2144.2	1783.2	2166.1	14166.9	32419.8	15113.2	2144.2	1783.2	2166.1
41°	32201.0	14347.4	1892.6	1772.2	1936.3	12930.7	32201.0	14347.4	1892.6	1772.2	1936.3
41.5°	32173.6	14347.4	1755.8	1772.2	1930.9	12028.2	32173.6	14347.4	1755.8	1772.2	1930.9
42°	31905.6	13477.7	1755.8	1761.3	1794.1	10846.7	31905.6	13477.7	1755.8	1761.3	1794.1
42.5°	31878.3	12378.3	1662.8	1761.3	1783.2	9960.6	31878.3	12378.3	1662.8	1761.3	1783.2
43°	31495.4	10447.4	1662.8	1755.8	1701.1	8779.1	31495.4	10447.4	1662.8	1755.8	1701.1
43.5°	31495.4	9397.2	1602.7	1739.4	1624.5	6700.6	31495.4	9397.2	1602.7	1739.4	1624.5
44°	31112.5	8702.5	1602.7	1739.4	1619.1	6700.6	31112.5	8702.5	1602.7	1739.4	1619.1
44.5°	31112.5	7800.0	1553.4	1706.6	1619.1	4890.0	31112.5	7800.0	1553.4	1706.6	1619.1

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594660
CATALOG NUMBER: FLXB-4860-N-LOW-4000K

CANDELA DISTRIBUTION (continued):

	0°	30°	60°	90°	120°	150°	180°	210°	240°	270°	300°
45°	30592.9	7340.5	1553.4	1717.5	1564.4	4222.7	30592.9	7340.5	1553.4	1717.5	1564.4
45.5°	30188.1	6109.8	1542.5	1673.8	1548.0	3588.2	30188.1	6109.8	1542.5	1673.8	1548.0
46°	30078.7	6109.8	1542.5	1679.2	1553.4	3194.4	30078.7	6109.8	1542.5	1679.2	1553.4
46.5°	29608.3	5015.8	1515.1	1651.9	1542.5	2789.6	29608.3	5015.8	1515.1	1651.9	1542.5
47°	29466.1	5015.8	1487.8	1635.5	1548.0	2587.2	29466.1	5015.8	1487.8	1635.5	1548.0
47.5°	28979.2	3960.2	1487.8	1613.6	1537.0	2270.0	28979.2	3960.2	1487.8	1613.6	1537.0
48°	28815.2	3117.8	1476.9	1608.1	1542.5	2160.6	28815.2	3117.8	1476.9	1608.1	1542.5
48.5°	28158.8	2981.1	1476.9	1575.3	1531.6	1936.3	28158.8	2981.1	1476.9	1575.3	1531.6
49°	28158.8	2373.9	1476.9	1564.4	1531.6	1739.4	28158.8	2373.9	1476.9	1564.4	1531.6
49.5°	27387.5	2264.5	1476.9	1531.6	1515.1	1695.7	27387.5	2264.5	1476.9	1531.6	1515.1
50°	27387.5	1876.2	1493.3	1531.6	1526.1	1586.3	27387.5	1876.2	1493.3	1531.6	1526.1
50.5°	26621.7	1876.2	1493.3	1531.6	1493.3	1548.0	26621.7	1876.2	1493.3	1531.6	1493.3
51°	26025.5	1695.7	1509.7	1509.7	1509.7	1460.4	26025.5	1695.7	1509.7	1509.7	1509.7
51.5°	25735.6	1630.0	1498.7	1504.2	1476.9	1422.2	25735.6	1630.0	1498.7	1504.2	1476.9
52°	25128.5	1476.9	1509.7	1471.4	1482.3	1351.1	25128.5	1476.9	1509.7	1471.4	1482.3
52.5°	24794.8	1476.9	1460.4	1449.5	1465.9	1312.8	24794.8	1476.9	1460.4	1449.5	1465.9
53°	23821.2	1372.9	1460.4	1444.0	1455.0	1258.1	23821.2	1372.9	1460.4	1444.0	1455.0
53.5°	23821.2	1323.7	1400.3	1427.6	1438.6	1219.8	23821.2	1323.7	1400.3	1427.6	1438.6
54°	22781.9	1285.4	1400.3	1422.2	1389.3	1170.5	22781.9	1285.4	1400.3	1422.2	1389.3
54.5°	22781.9	1247.1	1340.1	1411.2	1389.3	1094.0	22781.9	1247.1	1340.1	1411.2	1389.3
55°	21753.6	1214.3	1340.1	1394.8	1312.8	1066.6	21753.6	1214.3	1340.1	1394.8	1312.8
55.5°	21151.9	1148.7	1296.4	1378.4	1285.4	1033.8	21151.9	1148.7	1296.4	1378.4	1285.4
56°	20654.1	1148.7	1274.5	1367.5	1269.0	1006.5	20654.1	1148.7	1274.5	1367.5	1269.0
56.5°	20090.8	1083.0	1252.6	1340.1	1252.6	984.6	20090.8	1083.0	1252.6	1340.1	1252.6
57°	19587.5	1083.0	1225.2	1340.1	1252.6	968.2	19587.5	1083.0	1225.2	1340.1	1252.6
57.5°	19040.5	1033.8	1225.2	1307.3	1247.1	946.3	19040.5	1033.8	1225.2	1307.3	1247.1
58°	18515.4	1033.8	1197.9	1296.4	1241.7	935.3	18515.4	1033.8	1197.9	1296.4	1241.7
58.5°	17432.4	990.0	1197.9	1269.0	1225.2	918.9	17432.4	990.0	1197.9	1269.0	1225.2
59°	17432.4	962.7	1176.0	1258.1	1219.8	935.3	17432.4	962.7	1176.0	1258.1	1219.8
59.5°	16382.2	968.2	1176.0	1230.7	1181.5	935.3	16382.2	968.2	1176.0	1230.7	1181.5
60°	16382.2	951.8	1148.7	1225.2	1165.1	951.8	16382.2	951.8	1148.7	1225.2	1165.1
60.5°	15299.2	940.8	1148.7	1214.3	1143.2	946.3	15299.2	940.8	1148.7	1214.3	1143.2
61°	14872.5	918.9	1132.3	1187.0	1143.2	946.3	14872.5	918.9	1132.3	1187.0	1143.2
61.5°	14259.9	918.9	1132.3	1181.5	1121.3	946.3	14259.9	918.9	1132.3	1181.5	1121.3
62°	13838.7	908.0	1099.4	1165.1	1099.4	957.2	13838.7	908.0	1099.4	1165.1	1099.4
62.5°	13209.7	908.0	1066.6	1165.1	1072.1	951.8	13209.7	908.0	1066.6	1165.1	1072.1
63°	12804.9	897.1	1066.6	1148.7	1066.6	946.3	12804.9	897.1	1066.6	1148.7	1066.6
63.5°	12186.8	897.1	1039.3	1115.8	1050.2	951.8	12186.8	897.1	1039.3	1115.8	1050.2
64°	11191.3	897.1	1039.3	1083.0	1028.3	924.4	11191.3	897.1	1039.3	1083.0	1028.3
64.5°	11191.3	891.6	990.0	1066.6	1028.3	913.5	11191.3	891.6	990.0	1066.6	1028.3
65°	10206.7	891.6	990.0	1044.7	1001.0	913.5	10206.7	891.6	990.0	1044.7	1001.0
65.5°	9856.7	929.9	951.8	1022.9	968.2	902.5	9856.7	929.9	951.8	1022.9	968.2
66°	9287.8	929.9	951.8	1017.4	951.8	902.5	9287.8	929.9	951.8	1017.4	951.8
66.5°	8965.1	1017.4	918.9	1001.0	929.9	913.5	8965.1	1017.4	918.9	1001.0	929.9
67°	8418.1	1017.4	897.1	984.6	902.5	924.4	8418.1	1017.4	897.1	984.6	902.5

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594660
CATALOG NUMBER: FLXB-4860-N-LOW-4000K

CANDELA DISTRIBUTION (continued):

	0°	30°	60°	90°	120°	150°	180°	210°	240°	270°	300°
67.5°	8111.8	1104.9	897.1	951.8	891.6	984.6	8111.8	1104.9	897.1	951.8	891.6
68°	7592.1	1104.9	858.8	940.8	869.7	1011.9	7592.1	1104.9	858.8	940.8	869.7
68.5°	6842.8	1148.7	858.8	913.5	858.8	1121.3	6842.8	1148.7	858.8	913.5	858.8
69°	6842.8	1170.5	831.4	902.5	831.4	1143.2	6842.8	1170.5	831.4	902.5	831.4
69.5°	6137.2	1110.4	831.4	886.1	804.1	1165.1	6137.2	1110.4	831.4	886.1	804.1
70°	6137.2	1121.3	798.6	875.2	804.1	1181.5	6137.2	1121.3	798.6	875.2	804.1
70.5°	5480.8	1055.7	798.6	858.8	760.3	1187.0	5480.8	1055.7	798.6	858.8	760.3
71°	5278.4	1001.0	738.4	836.9	738.4	1115.8	5278.4	1001.0	738.4	836.9	738.4
71.5°	4862.7	1001.0	738.4	815.0	716.5	1050.2	4862.7	1001.0	738.4	815.0	716.5
72°	4687.7	984.6	678.3	727.5	683.7	979.1	4687.7	984.6	678.3	727.5	683.7
72.5°	4288.4	984.6	640.0	672.8	629.0	913.5	4288.4	984.6	640.0	672.8	629.0
73°	4135.2	951.8	640.0	656.4	612.6	820.5	4135.2	951.8	640.0	656.4	612.6
73.5°	3746.8	951.8	574.3	640.0	557.9	820.5	3746.8	951.8	574.3	640.0	557.9
74°	3238.1	973.6	574.3	541.5	503.2	815.0	3238.1	973.6	574.3	541.5	503.2
74.5°	3238.1	1006.5	503.2	508.7	503.2	815.0	3238.1	1006.5	503.2	508.7	503.2
75°	2778.7	979.1	503.2	432.1	470.4	793.1	2778.7	979.1	503.2	432.1	470.4
75.5°	2778.7	875.2	443.1	426.6	448.5	771.2	2778.7	875.2	443.1	426.6	448.5
76°	2363.0	847.8	443.1	399.3	426.6	705.6	2363.0	847.8	443.1	399.3	426.6
76.5°	2291.9	738.4	404.8	371.9	410.2	672.8	2291.9	738.4	404.8	371.9	410.2
77°	1996.5	738.4	404.8	355.5	361.0	656.4	1996.5	738.4	404.8	355.5	361.0
77.5°	1925.4	661.9	350.1	295.4	322.7	640.0	1925.4	661.9	350.1	295.4	322.7
78°	1662.8	634.5	257.1	284.4	289.9	623.6	1662.8	634.5	257.1	284.4	289.9
78.5°	1624.5	601.7	257.1	251.6	257.1	590.7	1624.5	601.7	257.1	251.6	257.1
79°	1389.3	563.4	218.8	240.7	218.8	563.4	1389.3	563.4	218.8	240.7	218.8
79.5°	1137.7	508.7	218.8	196.9	202.4	536.0	1137.7	508.7	218.8	196.9	202.4
80°	1137.7	486.8	186.0	169.6	202.4	470.4	1137.7	486.8	186.0	169.6	202.4
80.5°	924.4	454.0	186.0	142.2	169.6	432.1	924.4	454.0	186.0	142.2	169.6
81°	902.5	388.4	125.8	125.8	142.2	371.9	902.5	388.4	125.8	125.8	142.2
81.5°	738.4	388.4	125.8	114.9	136.7	328.2	738.4	388.4	125.8	114.9	136.7
82°	722.0	328.2	87.5	76.6	93.0	300.8	722.0	328.2	87.5	76.6	93.0
82.5°	579.8	328.2	71.1	76.6	87.5	257.1	579.8	328.2	71.1	76.6	87.5
83°	568.9	268.0	71.1	49.2	71.1	218.8	568.9	268.0	71.1	49.2	71.1
83.5°	454.0	268.0	43.8	38.3	60.2	180.5	454.0	268.0	43.8	38.3	60.2
84°	344.6	196.9	43.8	32.8	49.2	147.7	344.6	196.9	43.8	32.8	49.2
84.5°	344.6	153.2	27.3	27.3	49.2	125.8	344.6	153.2	27.3	27.3	49.2
85°	262.6	147.7	27.3	21.9	32.8	103.9	262.6	147.7	27.3	21.9	32.8
85.5°	262.6	98.5	16.4	21.9	32.8	38.3	262.6	98.5	16.4	21.9	32.8
86°	186.0	98.5	16.4	10.9	21.9	27.3	186.0	98.5	16.4	10.9	21.9
86.5°	186.0	65.6	10.9	10.9	16.4	16.4	186.0	65.6	10.9	10.9	16.4
87°	147.7	65.6	10.9	0.0	16.4	5.5	147.7	65.6	10.9	0.0	16.4
87.5°	147.7	38.3	0.0	0.0	5.5	0.0	147.7	38.3	0.0	0.0	5.5
88°	103.9	10.9	0.0	0.0	5.5	0.0	103.9	10.9	0.0	0.0	5.5
88.5°	103.9	10.9	0.0	0.0	0.0	0.0	103.9	10.9	0.0	0.0	0.0
89°	71.1	10.9	0.0	0.0	0.0	0.0	71.1	10.9	0.0	0.0	0.0
89.5°	43.8	0.0	0.0	0.0	0.0	0.0	43.8	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594660
CATALOG NUMBER: FLXB-4860-N-LOW-4000K

CANDELA DISTRIBUTION (continued):

	0°	30°	60°	90°	120°	150°	180°	210°	240°	270°	300°
90°	43.8	0.0	0.0	0.0	0.0	0.0	43.8	0.0	0.0	0.0	0.0
90.5°	27.3	0.0	0.0	0.0	0.0	0.0	27.3	0.0	0.0	0.0	0.0
91°	27.3	0.0	0.0	0.0	0.0	0.0	27.3	0.0	0.0	0.0	0.0
91.5°	10.9	0.0	0.0	0.0	0.0	0.0	10.9	0.0	0.0	0.0	0.0
92°	10.9	0.0	0.0	0.0	0.0	0.0	10.9	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
93°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
93.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
94°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
94.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
96°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
96.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
98°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
98.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
99°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
99.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
101°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
101.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
103°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
103.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
104°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
104.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
106°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
106.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
108°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
108.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
109°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
109.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
111°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
111.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
112°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594660
CATALOG NUMBER: FLXB-4860-N-LOW-4000K

CANDELA DISTRIBUTION (continued):

	0°	30°	60°	90°	120°	150°	180°	210°	240°	270°	300°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
113°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
113.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
114°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
114.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
116°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
116.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
118°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
118.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
119°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
119.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
121°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
121.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
123°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
123.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
124°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
124.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
126°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
126.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
128°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
128.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
129°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
129.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
131°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
131.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
133°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
133.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
134°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
134.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594660
CATALOG NUMBER: FLXB-4860-N-LOW-4000K

CANDELA DISTRIBUTION (continued):

	0°	30°	60°	90°	120°	150°	180°	210°	240°	270°	300°
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
136°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
136.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
138°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
138.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
139°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
139.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
141°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
141.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
143°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
143.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
144°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
144.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
146°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
146.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
148°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
148.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
149°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
149.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
151°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
151.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
153°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
153.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
154°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
154.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
156°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
156.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594660
CATALOG NUMBER: FLXB-4860-N-LOW-4000K

CANDELA DISTRIBUTION (continued):

	0°	30°	60°	90°	120°	150°	180°	210°	240°	270°	300°
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
158°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
158.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
159°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
159.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
161°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
161.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
163°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
163.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
164°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
164.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
166°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
166.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
168°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
168.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
169°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
169.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
171°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
171.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
173°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
173.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
174°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
174.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
176°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
176.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
178°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
178.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
179°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
179.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594660
CATALOG NUMBER: FLXB-4860-N-LOW-4000K

CANDELA DISTRIBUTION (continued):

	0°	30°	60°	90°	120°	150°	180°	210°	240°	270°	300°
180°	0.0	*0.0*	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1594660
CATALOG NUMBER: FLXB-4860-N-LOW-4000K

CANDELA DISTRIBUTION (continued):

	330°	360°
0°	33528.5	33528.5
0.5°	33528.5	33528.5
1°	33557.5	33480.9
1.5°	*33552.0*	*33464.5*
2°	33573.9	33508.3
2.5°	33552.0	33508.3
3°	33524.7	33464.5
3.5°	33513.7	33464.5
4°	33480.9	33497.3
4.5°	33513.8	33486.4
5°	33448.1	33486.4
5.5°	33431.7	33486.4
6°	33415.3	33475.5
6.5°	33426.2	33513.7
7°	33349.7	33513.7
7.5°	33349.7	33470.0
8°	33295.0	33470.0
8.5°	33240.3	33513.7
9°	33256.7	33497.3
9.5°	33185.6	33491.9
10°	33141.8	33502.8
10.5°	33103.5	33502.8
11°	33114.5	33502.8
11.5°	33021.5	33513.8
12°	32999.6	33486.4
12.5°	32950.4	33486.4
13°	32912.1	33535.6
13.5°	32819.1	33535.6
14°	32737.0	33502.8
14.5°	32682.3	33519.2
15°	32616.7	33530.2
15.5°	32611.2	33524.7
16°	32490.9	33530.2
16.5°	32430.7	33524.7
17°	32365.1	33513.8
17.5°	32326.8	33552.0
18°	32157.2	33552.0
18.5°	32058.8	33513.7
19°	31987.7	33513.7
19.5°	31872.8	33552.0
20°	31840.0	33541.1
20.5°	31692.3	33541.1
21°	31489.9	33541.1
21.5°	31489.9	33535.6
22°	31424.3	33541.1

TEST NUMBER: P1594660
CATALOG NUMBER: FLXB-4860-N-LOW-4000K

CANDELA DISTRIBUTION (continued):

	330°	360°
22.5°	31254.7	33557.5
23°	31167.2	33524.7
23.5°	30899.2	33524.7
24°	30718.7	33568.4
24.5°	30625.7	33541.1
25°	30423.3	33530.2
25.5°	30270.1	33535.6
26°	30089.6	33541.1
26.5°	29963.8	33535.6
27°	29712.2	33546.6
27.5°	29537.2	33508.3
28°	29126.9	33508.3
28.5°	29126.9	33552.0
29°	28662.0	33552.0
29.5°	28383.0	33508.3
30°	28125.9	33508.3
30.5°	27825.1	33519.2
31°	27589.9	33486.4
31.5°	27218.0	33491.9
32°	26900.7	33448.1
32.5°	26539.7	33448.1
33°	26206.0	33442.6
33.5°	25380.1	33442.6
34°	24909.7	33344.2
34.5°	24444.7	33344.2
35°	23919.6	33322.3
35.5°	23416.4	33229.3
36°	22803.8	33229.3
36.5°	22169.3	33125.4
37°	21502.0	33114.5
37.5°	20790.9	33005.1
38°	19975.9	33010.5
38.5°	19155.4	32813.6
39°	17295.7	32813.6
39.5°	16272.8	32665.9
40°	15162.4	32452.6
40.5°	14166.9	32419.8
41°	12930.7	32201.0
41.5°	12028.2	32173.6
42°	10846.7	31905.6
42.5°	9960.6	31878.3
43°	8779.1	31495.4
43.5°	6700.6	31495.4
44°	6700.6	31112.5
44.5°	4890.0	31112.5

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594660
CATALOG NUMBER: FLXB-4860-N-LOW-4000K

CANDELA DISTRIBUTION (continued):

	330°	360°
45°	4222.7	30592.9
45.5°	3588.2	30188.1
46°	3194.4	30078.7
46.5°	2789.6	29608.3
47°	2587.2	29466.1
47.5°	2270.0	28979.2
48°	2160.6	28815.2
48.5°	1936.3	28158.8
49°	1739.4	28158.8
49.5°	1695.7	27387.5
50°	1586.3	27387.5
50.5°	1548.0	26621.7
51°	1460.4	26025.5
51.5°	1422.2	25735.6
52°	1351.1	25128.5
52.5°	1312.8	24794.8
53°	1258.1	23821.2
53.5°	1219.8	23821.2
54°	1170.5	22781.9
54.5°	1094.0	22781.9
55°	1066.6	21753.6
55.5°	1033.8	21151.9
56°	1006.5	20654.1
56.5°	984.6	20090.8
57°	968.2	19587.5
57.5°	946.3	19040.5
58°	935.3	18515.4
58.5°	918.9	17432.4
59°	935.3	17432.4
59.5°	935.3	16382.2
60°	951.8	16382.2
60.5°	946.3	15299.2
61°	946.3	14872.5
61.5°	946.3	14259.9
62°	957.2	13838.7
62.5°	951.8	13209.7
63°	946.3	12804.9
63.5°	951.8	12186.8
64°	924.4	11191.3
64.5°	913.5	11191.3
65°	913.5	10206.7
65.5°	902.5	9856.7
66°	902.5	9287.8
66.5°	913.5	8965.1
67°	924.4	8418.1

TEST NUMBER: P1594660
CATALOG NUMBER: FLXB-4860-N-LOW-4000K

CANDELA DISTRIBUTION (continued):

	330°	360°
67.5°	984.6	8111.8
68°	1011.9	7592.1
68.5°	1121.3	6842.8
69°	1143.2	6842.8
69.5°	1165.1	6137.2
70°	1181.5	6137.2
70.5°	1187.0	5480.8
71°	1115.8	5278.4
71.5°	1050.2	4862.7
72°	979.1	4687.7
72.5°	913.5	4288.4
73°	820.5	4135.2
73.5°	820.5	3746.8
74°	815.0	3238.1
74.5°	815.0	3238.1
75°	793.1	2778.7
75.5°	771.2	2778.7
76°	705.6	2363.0
76.5°	672.8	2291.9
77°	656.4	1996.5
77.5°	640.0	1925.4
78°	623.6	1662.8
78.5°	590.7	1624.5
79°	563.4	1389.3
79.5°	536.0	1137.7
80°	470.4	1137.7
80.5°	432.1	924.4
81°	371.9	902.5
81.5°	328.2	738.4
82°	300.8	722.0
82.5°	257.1	579.8
83°	218.8	568.9
83.5°	180.5	454.0
84°	147.7	344.6
84.5°	125.8	344.6
85°	103.9	262.6
85.5°	38.3	262.6
86°	27.3	186.0
86.5°	16.4	186.0
87°	5.5	147.7
87.5°	0.0	147.7
88°	0.0	103.9
88.5°	0.0	103.9
89°	0.0	71.1
89.5°	0.0	43.8

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594660
CATALOG NUMBER: FLXB-4860-N-LOW-4000K

CANDELA DISTRIBUTION (continued):

	330°	360°
90°	0.0	43.8
90.5°	0.0	27.3
91°	0.0	27.3
91.5°	0.0	10.9
92°	0.0	10.9
92.5°	0.0	0.0
93°	0.0	0.0
93.5°	0.0	0.0
94°	0.0	0.0
94.5°	0.0	0.0
95°	0.0	0.0
95.5°	0.0	0.0
96°	0.0	0.0
96.5°	0.0	0.0
97°	0.0	0.0
97.5°	0.0	0.0
98°	0.0	0.0
98.5°	0.0	0.0
99°	0.0	0.0
99.5°	0.0	0.0
100°	0.0	0.0
100.5°	0.0	0.0
101°	0.0	0.0
101.5°	0.0	0.0
102°	0.0	0.0
102.5°	0.0	0.0
103°	0.0	0.0
103.5°	0.0	0.0
104°	0.0	0.0
104.5°	0.0	0.0
105°	0.0	0.0
105.5°	0.0	0.0
106°	0.0	0.0
106.5°	0.0	0.0
107°	0.0	0.0
107.5°	0.0	0.0
108°	0.0	0.0
108.5°	0.0	0.0
109°	0.0	0.0
109.5°	0.0	0.0
110°	0.0	0.0
110.5°	0.0	0.0
111°	0.0	0.0
111.5°	0.0	0.0
112°	0.0	0.0

TEST NUMBER: P1594660
CATALOG NUMBER: FLXB-4860-N-LOW-4000K

CANDELA DISTRIBUTION (continued):

	330°	360°
112.5°	0.0	0.0
113°	0.0	0.0
113.5°	0.0	0.0
114°	0.0	0.0
114.5°	0.0	0.0
115°	0.0	0.0
115.5°	0.0	0.0
116°	0.0	0.0
116.5°	0.0	0.0
117°	0.0	0.0
117.5°	0.0	0.0
118°	0.0	0.0
118.5°	0.0	0.0
119°	0.0	0.0
119.5°	0.0	0.0
120°	0.0	0.0
120.5°	0.0	0.0
121°	0.0	0.0
121.5°	0.0	0.0
122°	0.0	0.0
122.5°	0.0	0.0
123°	0.0	0.0
123.5°	0.0	0.0
124°	0.0	0.0
124.5°	0.0	0.0
125°	0.0	0.0
125.5°	0.0	0.0
126°	0.0	0.0
126.5°	0.0	0.0
127°	0.0	0.0
127.5°	0.0	0.0
128°	0.0	0.0
128.5°	0.0	0.0
129°	0.0	0.0
129.5°	0.0	0.0
130°	0.0	0.0
130.5°	0.0	0.0
131°	0.0	0.0
131.5°	0.0	0.0
132°	0.0	0.0
132.5°	0.0	0.0
133°	0.0	0.0
133.5°	0.0	0.0
134°	0.0	0.0
134.5°	0.0	0.0

TEST NUMBER: P1594660
CATALOG NUMBER: FLXB-4860-N-LOW-4000K

CANDELA DISTRIBUTION (continued):

	330°	360°
135°	0.0	0.0
135.5°	0.0	0.0
136°	0.0	0.0
136.5°	0.0	0.0
137°	0.0	0.0
137.5°	0.0	0.0
138°	0.0	0.0
138.5°	0.0	0.0
139°	0.0	0.0
139.5°	0.0	0.0
140°	0.0	0.0
140.5°	0.0	0.0
141°	0.0	0.0
141.5°	0.0	0.0
142°	0.0	0.0
142.5°	0.0	0.0
143°	0.0	0.0
143.5°	0.0	0.0
144°	0.0	0.0
144.5°	0.0	0.0
145°	0.0	0.0
145.5°	0.0	0.0
146°	0.0	0.0
146.5°	0.0	0.0
147°	0.0	0.0
147.5°	0.0	0.0
148°	0.0	0.0
148.5°	0.0	0.0
149°	0.0	0.0
149.5°	0.0	0.0
150°	0.0	0.0
150.5°	0.0	0.0
151°	0.0	0.0
151.5°	0.0	0.0
152°	0.0	0.0
152.5°	0.0	0.0
153°	0.0	0.0
153.5°	0.0	0.0
154°	0.0	0.0
154.5°	0.0	0.0
155°	0.0	0.0
155.5°	0.0	0.0
156°	0.0	0.0
156.5°	0.0	0.0
157°	0.0	0.0

TEST NUMBER: P1594660
CATALOG NUMBER: FLXB-4860-N-LOW-4000K

CANDELA DISTRIBUTION (continued):

	330°	360°
157.5°	0.0	0.0
158°	0.0	0.0
158.5°	0.0	0.0
159°	0.0	0.0
159.5°	0.0	0.0
160°	0.0	0.0
160.5°	0.0	0.0
161°	0.0	0.0
161.5°	0.0	0.0
162°	0.0	0.0
162.5°	0.0	0.0
163°	0.0	0.0
163.5°	0.0	0.0
164°	0.0	0.0
164.5°	0.0	0.0
165°	0.0	0.0
165.5°	0.0	0.0
166°	0.0	0.0
166.5°	0.0	0.0
167°	0.0	0.0
167.5°	0.0	0.0
168°	0.0	0.0
168.5°	0.0	0.0
169°	0.0	0.0
169.5°	0.0	0.0
170°	0.0	0.0
170.5°	0.0	0.0
171°	0.0	0.0
171.5°	0.0	0.0
172°	0.0	0.0
172.5°	0.0	0.0
173°	0.0	0.0
173.5°	0.0	0.0
174°	0.0	0.0
174.5°	0.0	0.0
175°	0.0	0.0
175.5°	0.0	0.0
176°	0.0	0.0
176.5°	0.0	0.0
177°	0.0	0.0
177.5°	0.0	0.0
178°	0.0	0.0
178.5°	0.0	0.0
179°	0.0	0.0
179.5°	0.0	0.0

TEST NUMBER: P1594660
CATALOG NUMBER: FLXB-4860-N-LOW-4000K

CANDELA DISTRIBUTION (continued):

	330°	360°
180°	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1594660
CATALOG NUMBER: FLXB-4860-N-LOW-4000K

CIE UGR TABLE:

Reflectances:											
	Ceiling	0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
	Wall	0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
	Reference plane	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room Dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	27.3	28.6	27.7	28.9	29.3	14.6	15.9	15.0	16.2	16.5
	3H	29.0	30.1	29.4	30.5	30.8	16.8	17.9	17.2	18.2	18.6
	4H	29.4	30.4	29.8	30.8	31.2	17.3	18.4	17.7	18.7	19.1
	6H	29.5	30.5	29.9	30.9	31.3	17.5	18.5	17.9	18.9	19.2
	8H	29.5	30.5	30.0	30.9	31.3	17.5	18.4	17.9	18.8	19.2
	12H	29.5	30.4	29.9	30.8	31.2	17.5	18.3	17.9	18.7	19.2
4H	2H	27.1	28.2	27.5	28.5	28.9	15.2	16.2	15.6	16.6	17.0
	3H	28.8	29.7	29.2	30.1	30.5	17.6	18.4	18.0	18.9	19.3
	4H	29.2	30.0	29.7	30.5	30.9	18.2	19.0	18.6	19.4	19.8
	6H	29.5	30.2	29.9	30.6	31.1	18.4	19.1	18.9	19.6	20.0
	8H	29.5	30.1	30.0	30.6	31.0	18.4	19.1	18.9	19.5	20.0
	12H	29.5	30.0	30.0	30.5	31.0	18.4	18.9	18.9	19.4	19.9
8H	4H	29.1	29.8	29.6	30.2	30.7	18.8	19.4	19.2	19.8	20.3
	6H	29.4	29.9	29.9	30.4	30.9	19.0	19.5	19.5	20.0	20.5
	8H	29.4	29.9	29.9	30.4	30.9	19.0	19.5	19.5	20.0	20.5
	12H	29.4	29.8	29.9	30.3	30.9	19.0	19.4	19.5	19.9	20.4
12H	4H	29.1	29.6	29.6	30.1	30.6	18.9	19.4	19.3	19.9	20.4
	6H	29.3	29.8	29.9	30.2	30.8	19.1	19.6	19.7	20.0	20.6
	8H	29.4	29.8	29.9	30.3	30.8	19.1	19.5	19.7	20.0	20.6

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP3-2602-684-3

Test Date: 02/20/2026

Luminaire Tested: HLBX-2436-W-HI-4000K

Data in this report applies to families of products including HLBX-2436*

Report Generated By FNC07603 / LDUCLS01DT01661
Version: v7.05


Test Information

Test Method:	LM-79-2019
Report Number:	SP3-2602-684-3
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP3 - 3M SPHERE
Measurement Geometry:	4π
Issue Date:	02/27/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	Metalux
Catalog Number:	**HLBX-2436-W-HI-4000K**
Description:	LDS HLBX 2436 W beam, HI lumen, 4000K CCT settings

Spectral Parameters

CCT (K):	4000
CIE u':	0.2271
CIE v':	0.4972
Duv:	-0.0036
CIE x:	0.3780
CIE y:	0.3677
CIE z:	0.2543
Peak Wavelength (nm):	454
Dominant Wavelength (nm):	581
Purity:	23.78071
Rf:	83.8
Rg:	95.3

CRI (Ra):	84.8
R1:	84.5
R2:	92.5
R3:	95.4
R4:	82.5
R5:	84.0
R6:	87.9
R7:	85.2
R8:	66.3
R9:	16.8
R10:	80.6
R11:	81.5
R12:	62.9
R13:	87.1
R14:	98.1
R15:	79.5



Test Conditions


Stabilization Time:	22M
Operation Time:	1H 22M
Sphere Temperature (°C):	25.0

REPORT NUMBER: SP3-2602-684-3


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	3M SPHERE IN02505	1/10/2026	7/10/2026
Power Meter	XITRON INXT2011006	10/21/2025	10/21/2026
AC Power Source	CHROMA 61604 IN6064A	10/20/2025	10/20/2026
DC Power Source	EYSIGHT N5770A IN0534	10/20/2025	10/20/2026
Sphere Thermometer	TANDD IN4036E	10/21/2025	10/21/2026

REPORT NUMBER: SP3-2602-684-3

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 4000K
CIE x = 0.3780
CIE y = 0.3677
Duv = -0.0036

Point lies inside the ANSI 4000K 7-step quadrangle

REPORT NUMBER: SP3-2602-684-3

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	258	NR	620	689	NR	750	21	NR	880	1	NR
365	0	NR	495	283	NR	625	645	NR	755	18	NR	885	1	NR
370	0	NR	500	331	NR	630	600	NR	760	15	NR	890	1	NR
375	0	NR	505	383	NR	635	550	NR	765	13	NR	895	0	NR
380	0	NR	510	428	NR	640	501	NR	770	11	NR	900	0	NR
385	0	NR	515	469	NR	645	450	NR	775	9	NR	905	0	NR
390	1	NR	520	502	NR	650	404	NR	780	8	NR	910	0	NR
395	3	NR	525	526	NR	655	359	NR	785	7	NR	915	0	NR
400	4	NR	530	543	NR	660	317	NR	790	6	NR	920	0	NR
405	7	NR	535	559	NR	665	278	NR	795	5	NR	925	0	NR
410	10	NR	540	573	NR	670	243	NR	800	4	NR	930	0	NR
415	18	NR	545	587	NR	675	212	NR	805	4	NR	935	0	NR
420	32	NR	550	603	NR	680	183	NR	810	3	NR	940	0	NR
425	55	NR	555	619	NR	685	159	NR	815	3	NR	945	0	NR
430	95	NR	560	640	NR	690	136	NR	820	2	NR	950	0	NR
435	164	NR	565	666	NR	695	117	NR	825	2	NR	955	0	NR
440	273	NR	570	689	NR	700	100	NR	830	2	NR	960	0	NR
445	480	NR	575	718	NR	705	85	NR	835	2	NR	965	0	NR
450	835	NR	580	743	NR	710	73	NR	840	1	NR	970	0	NR
455	998	NR	585	764	NR	715	63	NR	845	1	NR	975	0	NR
460	735	NR	590	781	NR	720	54	NR	850	1	NR	980	0	NR
465	533	NR	595	789	NR	725	46	NR	855	1	NR	985	0	NR
470	435	NR	600	787	NR	730	39	NR	860	1	NR	990	0	NR
475	320	NR	605	775	NR	735	33	NR	865	1	NR	995	0	NR
480	254	NR	610	755	NR	740	28	NR	870	1	NR	1000	0	NR
485	245	NR	615	725	NR	745	24	NR	875	1	NR			

REPORT NUMBER: SP3-2602-684-3

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.73**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	258	NR	620	689	NR	750	21	NR	880	1	NR
365	0	NR	495	283	NR	625	645	NR	755	18	NR	885	1	NR
370	0	NR	500	331	NR	630	600	NR	760	15	NR	890	1	NR
375	0	NR	505	383	NR	635	550	NR	765	13	NR	895	0	NR
380	0	NR	510	428	NR	640	501	NR	770	11	NR	900	0	NR
385	0	NR	515	469	NR	645	450	NR	775	9	NR	905	0	NR
390	1	NR	520	502	NR	650	404	NR	780	8	NR	910	0	NR
395	3	NR	525	526	NR	655	359	NR	785	7	NR	915	0	NR
400	4	NR	530	543	NR	660	317	NR	790	6	NR	920	0	NR
405	7	NR	535	559	NR	665	278	NR	795	5	NR	925	0	NR
410	10	NR	540	573	NR	670	243	NR	800	4	NR	930	0	NR
415	18	NR	545	587	NR	675	212	NR	805	4	NR	935	0	NR
420	32	NR	550	603	NR	680	183	NR	810	3	NR	940	0	NR
425	55	NR	555	619	NR	685	159	NR	815	3	NR	945	0	NR
430	95	NR	560	640	NR	690	136	NR	820	2	NR	950	0	NR
435	164	NR	565	666	NR	695	117	NR	825	2	NR	955	0	NR
440	273	NR	570	689	NR	700	100	NR	830	2	NR	960	0	NR
445	480	NR	575	718	NR	705	85	NR	835	2	NR	965	0	NR
450	835	NR	580	743	NR	710	73	NR	840	1	NR	970	0	NR
455	998	NR	585	764	NR	715	63	NR	845	1	NR	975	0	NR
460	735	NR	590	781	NR	720	54	NR	850	1	NR	980	0	NR
465	533	NR	595	789	NR	725	46	NR	855	1	NR	985	0	NR
470	435	NR	600	787	NR	730	39	NR	860	1	NR	990	0	NR
475	320	NR	605	775	NR	735	33	NR	865	1	NR	995	0	NR
480	254	NR	610	755	NR	740	28	NR	870	1	NR	1000	0	NR
485	245	NR	615	725	NR	745	24	NR	875	1	NR			

REPORT NUMBER: SP3-2602-684-3

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 3.62**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	258	NR	620	689	NR	750	21	NR	880	1	NR
365	0	NR	495	283	NR	625	645	NR	755	18	NR	885	1	NR
370	0	NR	500	331	NR	630	600	NR	760	15	NR	890	1	NR
375	0	NR	505	383	NR	635	550	NR	765	13	NR	895	0	NR
380	0	NR	510	428	NR	640	501	NR	770	11	NR	900	0	NR
385	0	NR	515	469	NR	645	450	NR	775	9	NR	905	0	NR
390	1	NR	520	502	NR	650	404	NR	780	8	NR	910	0	NR
395	3	NR	525	526	NR	655	359	NR	785	7	NR	915	0	NR
400	4	NR	530	543	NR	660	317	NR	790	6	NR	920	0	NR
405	7	NR	535	559	NR	665	278	NR	795	5	NR	925	0	NR
410	10	NR	540	573	NR	670	243	NR	800	4	NR	930	0	NR
415	18	NR	545	587	NR	675	212	NR	805	4	NR	935	0	NR
420	32	NR	550	603	NR	680	183	NR	810	3	NR	940	0	NR
425	55	NR	555	619	NR	685	159	NR	815	3	NR	945	0	NR
430	95	NR	560	640	NR	690	136	NR	820	2	NR	950	0	NR
435	164	NR	565	666	NR	695	117	NR	825	2	NR	955	0	NR
440	273	NR	570	689	NR	700	100	NR	830	2	NR	960	0	NR
445	480	NR	575	718	NR	705	85	NR	835	2	NR	965	0	NR
450	835	NR	580	743	NR	710	73	NR	840	1	NR	970	0	NR
455	998	NR	585	764	NR	715	63	NR	845	1	NR	975	0	NR
460	735	NR	590	781	NR	720	54	NR	850	1	NR	980	0	NR
465	533	NR	595	789	NR	725	46	NR	855	1	NR	985	0	NR
470	435	NR	600	787	NR	730	39	NR	860	1	NR	990	0	NR
475	320	NR	605	775	NR	735	33	NR	865	1	NR	995	0	NR
480	254	NR	610	755	NR	740	28	NR	870	1	NR	1000	0	NR
485	245	NR	615	725	NR	745	24	NR	875	1	NR			


REPORT NUMBER: SP3-2602-684-3

TM-30-18


Summary


R_f = 83.8
R_g = 95.3
CIE R_a = 84.8
R_9 = 16.8


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP3-2602-684-3

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 84	CES51 = 92	CES76 = 77
CES02 = 61	CES27 = 90	CES52 = 93	CES77 = 82
CES03 = 31	CES28 = 91	CES53 = 89	CES78 = 76
CES04 = 70	CES29 = 91	CES54 = 88	CES79 = 92
CES05 = 48	CES30 = 88	CES55 = 84	CES80 = 89
CES06 = 51	CES31 = 93	CES56 = 84	CES81 = 80
CES07 = 41	CES32 = 84	CES57 = 82	CES82 = 95
CES08 = 40	CES33 = 97	CES58 = 82	CES83 = 96
CES09 = 29	CES34 = 87	CES59 = 91	CES84 = 90
CES10 = 74	CES35 = 93	CES60 = 88	CES85 = 77
CES11 = 57	CES36 = 76	CES61 = 85	CES86 = 75
CES12 = 63	CES37 = 92	CES62 = 77	CES87 = 85
CES13 = 43	CES38 = 82	CES63 = 83	CES88 = 91
CES14 = 74	CES39 = 98	CES64 = 75	CES89 = 79
CES15 = 71	CES40 = 97	CES65 = 76	CES90 = 91
CES16 = 47	CES41 = 95	CES66 = 71	CES91 = 66
CES17 = 49	CES42 = 93	CES67 = 70	CES92 = 65
CES18 = 56	CES43 = 90	CES68 = 76	CES93 = 78
CES19 = 71	CES44 = 99	CES69 = 80	CES94 = 65
CES20 = 65	CES45 = 95	CES70 = 73	CES95 = 73
CES21 = 86	CES46 = 92	CES71 = 65	CES96 = 85
CES22 = 78	CES47 = 94	CES72 = 88	CES97 = 90
CES23 = 91	CES48 = 84	CES73 = 68	CES98 = 87
CES24 = 90	CES49 = 91	CES74 = 89	CES99 = 80
CES25 = 71	CES50 = 93	CES75 = 70	





REPORT NUMBER: SP3-2602-684-3

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP3-2602-684-3

TM-30-18

Measure Comparisons





(END OF REPORT)