

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: METALUX

Report Number: P830583

Luminaire Tested: **OHBL-48SE-W-UNV-L730-CD**

Issue Date: 5/3/2024



Test Information

Test Method: LM-79-08
Report Number: P830583
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-285-4)
Test Lab: INNOVATION CENTER
Issue Date: 5/3/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: METALUX
Catalog Number: OHBL-48SE-W-UNV-L730-CD
Description: 48000 LUMEN OHBL SE LED LUMINAIRE WITH 70CRI, 3000K LEDS AND WIDE LENS
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 47904.0 lumens
Efficiency: N/A
Efficacy: 165.9 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.58 / 1.62
Luminous Opening: Rectangular w/ Sides (W: 1.67' x L: 3.78' x H: 0.17')
CIE Type: Direct

Input Watts (W): 288.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P830583

CATALOG NUMBER: OHBL-48SE-W-UNV-L730-CD

Luminous Intensity Polar Plot





TEST NUMBER: P830583

CATALOG NUMBER: OHBL-48SE-W-UNV-L730-CD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		110	110	110		105	105	105		100	100	100
1	109	104	100	96		106	102	98	95		97	94	91		93	90	88		89	87	85
2	99	91	85	79		96	89	83	78		85	80	76		82	77	74		78	75	72
3	90	80	72	66		88	78	71	65		75	69	64		72	67	62		69	65	61
4	83	71	62	56		80	69	61	55		67	60	54		64	58	53		62	57	52
5	76	63	54	48		74	62	54	47		60	52	47		57	51	46		55	50	45
6	70	57	48	41		68	56	47	41		54	46	41		52	45	40		50	44	40
7	65	51	43	36		63	50	42	36		49	41	36		47	40	35		45	40	35
8	60	47	38	32		58	46	38	32		44	37	32		43	36	31		42	36	31
9	56	43	34	29		55	42	34	29		41	34	28		39	33	28		38	32	28
10	52	39	31	26		51	39	31	26		38	31	26		36	30	26		35	30	25

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	27326	27326	27326
5°	27072	27288	27504
10°	26732	27246	27402
15°	26210	26796	26393
20°	25496	25874	24971
25°	24540	24759	24339
30°	23269	23930	26040
35°	21818	24373	30281
40°	20135	26396	34763
45°	18375	29941	37072
50°	16539	33108	34182
55°	14814	33065	25831
60°	13058	27973	15578
65°	11203	19314	9270
70°	9102	12484	6531
75°	6924	8945	5839
80°	4971	7854	6196
85°	3374	8625	8616



TEST NUMBER: P830583

CATALOG NUMBER: OHBL-48SE-W-UNV-L730-CD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1528.9	3.2
10°-20°	4329.4	9.0
20°-30°	6335.3	13.2
30°-40°	8227.7	17.2
40°-50°	10047.0	21.0
50°-60°	8848.0	18.5
60°-70°	4610.7	9.6
70°-80°	1977.3	4.1
80°-90°	949.6	2.0
90°-100°	446.1	0.9
100°-110°	277.3	0.6
110°-120°	163.9	0.3
120°-130°	89.1	0.2
130°-140°	44.7	0.1
140°-150°	21.5	0.0
150°-160°	7.5	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	12193.5	25.5
0°-40°	20421.2	42.6
0°-60°	39316.2	82.1
0°-90°	46853.8	97.8
90°-120°	887.3	1.9
90°-150°	1042.7	2.2
90°-180°	1050.0	2.2
0°-180°	47904.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	15999	15999	15999	15999	15999	
5°	15851	15971	16058	16199	16182	###
15°	14998	15419	15568	15450	15326	4223
25°	13289	14000	13762	13503	13517	6099
35°	10787	11926	12523	14604	15540	6723
45°	7943	9993	13659	16538	16883	6124
55°	5288	8754	12720	11153	9914	4746
65°	3034	6065	5823	3238	2786	3002
75°	1222	2837	1871	1281	1215	1332
85°	259	1011	953	932	942	289
90°	4	366	628	718	735	18
95°	7	214	500	587	604	5
105°	14	121	324	390	397	15
115°	21	69	200	245	252	21
125°	24	34	117	152	155	21
135°	21	21	55	93	97	16
145°	28	21	24	45	52	16
155°	28	28	21	21	21	9
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	



TEST NUMBER: P830583

CATALOG NUMBER: OHBL-48SE-W-UNV-L730-CD

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	15999.1	15999.1	15999.1	15999.1	15999.1
2.5°	15930.0	15999.1	16002.5	16099.2	16088.8
5°	15850.6	15971.4	16057.7	16199.3	16182.0
7.5°	15719.5	15909.3	16061.2	16216.5	16202.7
10°	15533.1	15792.0	15992.2	16119.9	16078.5
12.5°	15291.4	15633.2	15829.9	15857.5	15778.1
15°	14998.0	15419.2	15567.6	15450.2	15326.0
17.5°	14666.7	15160.3	15212.1	14956.6	14801.3
20°	14252.5	14815.1	14763.3	14411.2	14238.6
22.5°	13793.4	14435.4	14269.7	13900.4	13734.7
25°	13289.4	14000.5	13762.3	13503.4	13517.2
27.5°	12699.1	13506.9	13275.6	13393.0	13613.9
30°	12098.5	12989.1	12847.6	13531.0	13966.0
32.5°	11439.2	12457.5	12585.2	13934.9	14646.0
35°	10786.9	11925.9	12523.1	14604.5	15540.0
37.5°	10065.4	11387.5	12623.2	15377.7	16358.0
40°	9364.7	10862.8	12851.0	16071.5	16900.0
42.5°	8650.2	10393.3	13234.2	16482.3	17127.8
45°	7942.6	9992.9	13658.7	16537.5	16882.7
47.5°	7235.0	9654.7	13952.1	16099.2	15940.4
50°	6551.5	9354.4	13972.9	15046.4	14397.4
52.5°	5912.9	9078.2	13593.2	13368.8	12360.9
55°	5288.1	8753.7	12719.9	11152.7	9913.5
57.5°	4718.6	8305.0	11373.7	8771.0	7417.9
60°	4114.5	7697.5	9634.0	6416.9	5350.3
62.5°	3558.8	6941.6	7683.7	4466.6	3845.3
65°	3034.1	6064.8	5823.2	3237.8	2785.6
67.5°	2478.4	5157.0	4297.5	2361.0	2071.1
70°	2043.5	4314.7	3199.8	1836.4	1667.2
72.5°	1598.2	3513.9	2392.1	1491.2	1398.0
75°	1221.9	2837.4	1870.9	1280.6	1215.0
77.5°	900.9	2243.7	1505.0	1132.2	1070.1
80°	631.7	1767.3	1259.9	1011.4	987.2
82.5°	424.6	1366.9	1073.5	963.1	966.5
85°	258.9	1011.4	952.7	932.0	942.3
87.5°	124.3	718.0	818.1	849.1	859.5
90°	3.5	365.9	628.2	718.0	735.2
92.5°	0.0	279.6	552.3	642.0	659.3
95°	6.9	214.0	500.5	586.8	604.1
97.5°	6.9	176.0	448.7	538.5	548.8
100°	10.4	151.9	400.4	486.7	497.1
102.5°	10.4	134.6	359.0	434.9	441.8
105°	13.8	120.8	324.5	390.1	397.0



TEST NUMBER: P830583

CATALOG NUMBER: OHBL-48SE-W-UNV-L730-CD

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	20.7	82.8	227.8	276.1	283.0
115°	20.7	69.0	200.2	245.1	252.0
117.5°	24.2	62.1	176.0	217.5	220.9
120°	24.2	51.8	151.9	193.3	196.8
122.5°	24.2	41.4	134.6	172.6	176.0
125°	24.2	34.5	117.4	151.9	155.3
127.5°	20.7	24.2	100.1	134.6	138.1
130°	20.7	20.7	82.8	117.4	124.3
132.5°	20.7	20.7	69.0	103.6	110.5
135°	20.7	20.7	55.2	93.2	96.7
137.5°	20.7	20.7	44.9	79.4	86.3
140°	20.7	20.7	34.5	69.0	72.5
142.5°	24.2	20.7	31.1	58.7	62.1
145°	27.6	20.7	24.2	44.9	51.8
147.5°	27.6	24.2	24.2	38.0	41.4
150°	27.6	27.6	20.7	27.6	34.5
152.5°	27.6	27.6	20.7	20.7	27.6
155°	27.6	27.6	20.7	20.7	20.7
157.5°	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180° - - 45°-225° - - - 90°-270°







107.5°	17.3	107.0	290.0	348.6	355.5
110°	17.3	93.2	255.4	310.7	317.6



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

METALUX

Report Number: SP1-2307-100-1

Test Date: 07/27/2023

Luminaire Tested: OHB-15SE-N-UNV-L730-CD

Data in this report applies to families of products including OHB-15SE-N-UNV-L730-CD.

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2307-100-1
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 08/04/2023
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: METALUX
 Catalog Number: **OHB-15SE-N-UNV-L730-CD**
 Description: 15000 LUMEN OHB SE LED LUMINAIRE WITH 70CRI, 3000K LEDS AND NARROW LENS

LENS

Spectral Parameters

CCT (K):	3069	CRI (Ra):	71.3		
CIE u':	0.2485	R1:	67.4	R9:	-35.7
CIE v':	0.5185	R2:	83.0	R10:	60.6
Duv:	-0.0010	R3:	94.0	R11:	58.9
CIE x:	0.4306	R4:	65.2	R12:	49.5
CIE y:	0.3993	R5:	66.6	R13:	70.5
CIE z:	0.1702	R6:	76.0	R14:	97.0
Peak Wavelength (nm):	596	R7:	76.4		
Dominant Wavelength (nm):	582	R8:	41.9		
Purity:	49.5				
Rf:	74.9				
Rg:	92.7				



Test Conditions

Stabilization Time: 23M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.7/57%
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2307-100-1

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	2/9/2023	8/9/2023
Power Meter	XITRON 2801 IN0071	11/29/2022	11/29/2023
AC Power Source	CHROMA 61603 IN0063	11/28/2022	11/28/2023
DC Power Source	AGILENT E3634A IN0208	11/28/2022	11/28/2023
Sphere Thermometer	ONSET IN0085	11/28/2022	11/28/2023
Room Thermometer	ONSET IN0046	11/28/2022	11/28/2023

REPORT NUMBER: SP1-2307-100-1

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2307-100-1

Photopic Flux vs. Wavelength




#####

λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)
360	6099	NR	490	40168	NR	620	253019	NR	750	11053	NR	880	4764	NR
365	5425	NR	495	46535	NR	625	234501	NR	755	10436	NR	885	4069	NR
370	5467	NR	500	57902	NR	630	214134	NR	760	9340	NR	890	5470	NR
375	5866	NR	505	75040	NR	635	194074	NR	765	9223	NR	895	5625	NR
380	5693	NR	510	92426	NR	640	175837	NR	770	7875	NR	900	5662	NR
385	5528	NR	515	109218	NR	645	158182	NR	775	6995	NR	905	4976	NR
390	5323	NR	520	124301	NR	650	139770	NR	780	6291	NR	910	3243	NR
395	4691	NR	525	136616	NR	655	124825	NR	785	5894	NR	915	4005	NR
400	4292	NR	530	148525	NR	660	109765	NR	790	5176	NR	920	4854	NR
405	4106	NR	535	158686	NR	665	95251	NR	795	5191	NR	925	3999	NR
410	4555	NR	540	170513	NR	670	82640	NR	800	4961	NR	930	4856	NR
415	6579	NR	545	182793	NR	675	71832	NR	805	5762	NR	935	5652	NR
420	11281	NR	550	196628	NR	680	62184	NR	810	5247	NR	940	7244	NR
425	19782	NR	555	213600	NR	685	53604	NR	815	5570	NR	945	6266	NR
430	32934	NR	560	232241	NR	690	46370	NR	820	5470	NR	950	6258	NR
435	52004	NR	565	250545	NR	695	40048	NR	825	5780	NR	955	6166	NR
440	77987	NR	570	269608	NR	700	35148	NR	830	4151	NR	960	4813	NR
445	117241	NR	575	286007	NR	705	30717	NR	835	5899	NR	965	6539	NR
450	171397	NR	580	300402	NR	710	27137	NR	840	5774	NR	970	2930	NR
455	188676	NR	585	310093	NR	715	24655	NR	845	4055	NR	975	3170	NR
460	142860	NR	590	313605	NR	720	21845	NR	850	4767	NR	980	3959	NR
465	100906	NR	595	314960	NR	725	19116	NR	855	4780	NR	985	6920	NR
470	78130	NR	600	311387	NR	730	16889	NR	860	5148	NR	990	2710	NR
475	57660	NR	605	301618	NR	735	14825	NR	865	6865	NR	995	5566	NR
480	43089	NR	610	288042	NR	740	13154	NR	870	5392	NR	1000	0	NR
485	38569	NR	615	270953	NR	745	11725	NR	875	6166	NR			

REPORT NUMBER: SP1-2307-100-1

Scotopic Flux vs. Wavelength



Scotopic Lumens: 18956.8

S/P: 1.25

λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)
360	6099	NR	490	40168	NR	620	253019	NR	750	11053	NR	880	4764	NR
365	5425	NR	495	46535	NR	625	234501	NR	755	10436	NR	885	4069	NR
370	5467	NR	500	57902	NR	630	214134	NR	760	9340	NR	890	5470	NR
375	5866	NR	505	75040	NR	635	194074	NR	765	9223	NR	895	5625	NR
380	5693	NR	510	92426	NR	640	175837	NR	770	7875	NR	900	5662	NR
385	5528	NR	515	109218	NR	645	158182	NR	775	6995	NR	905	4976	NR
390	5323	NR	520	124301	NR	650	139770	NR	780	6291	NR	910	3243	NR
395	4691	NR	525	136616	NR	655	124825	NR	785	5894	NR	915	4005	NR
400	4292	NR	530	148525	NR	660	109765	NR	790	5176	NR	920	4854	NR
405	4106	NR	535	158686	NR	665	95251	NR	795	5191	NR	925	3999	NR
410	4555	NR	540	170513	NR	670	82640	NR	800	4961	NR	930	4856	NR
415	6579	NR	545	182793	NR	675	71832	NR	805	5762	NR	935	5652	NR
420	11281	NR	550	196628	NR	680	62184	NR	810	5247	NR	940	7244	NR
425	19782	NR	555	213600	NR	685	53604	NR	815	5570	NR	945	6266	NR
430	32934	NR	560	232241	NR	690	46370	NR	820	5470	NR	950	6258	NR
435	52004	NR	565	250545	NR	695	40048	NR	825	5780	NR	955	6166	NR
440	77987	NR	570	269608	NR	700	35148	NR	830	4151	NR	960	4813	NR
445	117241	NR	575	286007	NR	705	30717	NR	835	5899	NR	965	6539	NR
450	171397	NR	580	300402	NR	710	27137	NR	840	5774	NR	970	2930	NR
455	188676	NR	585	310093	NR	715	24655	NR	845	4055	NR	975	3170	NR
460	142860	NR	590	313605	NR	720	21845	NR	850	4767	NR	980	3959	NR
465	100906	NR	595	314960	NR	725	19116	NR	855	4780	NR	985	6920	NR
470	78130	NR	600	311387	NR	730	16889	NR	860	5148	NR	990	2710	NR
475	57660	NR	605	301618	NR	735	14825	NR	865	6865	NR	995	5566	NR
480	43089	NR	610	288042	NR	740	13154	NR	870	5392	NR	1000	0	NR
485	38569	NR	615	270953	NR	745	11725	NR	875	6166	NR			

REPORT NUMBER: SP1-2307-100-1

Melanopic Flux vs. Wavelength



Melanopic Lumens: 7042.8

M/P: 0.47

λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)
360	6099	NR	490	40168	NR	620	253019	NR	750	11053	NR	880	4764	NR
365	5425	NR	495	46535	NR	625	234501	NR	755	10436	NR	885	4069	NR
370	5467	NR	500	57902	NR	630	214134	NR	760	9340	NR	890	5470	NR
375	5866	NR	505	75040	NR	635	194074	NR	765	9223	NR	895	5625	NR
380	5693	NR	510	92426	NR	640	175837	NR	770	7875	NR	900	5662	NR
385	5528	NR	515	109218	NR	645	158182	NR	775	6995	NR	905	4976	NR
390	5323	NR	520	124301	NR	650	139770	NR	780	6291	NR	910	3243	NR
395	4691	NR	525	136616	NR	655	124825	NR	785	5894	NR	915	4005	NR
400	4292	NR	530	148525	NR	660	109765	NR	790	5176	NR	920	4854	NR
405	4106	NR	535	158686	NR	665	95251	NR	795	5191	NR	925	3999	NR
410	4555	NR	540	170513	NR	670	82640	NR	800	4961	NR	930	4856	NR
415	6579	NR	545	182793	NR	675	71832	NR	805	5762	NR	935	5652	NR
420	11281	NR	550	196628	NR	680	62184	NR	810	5247	NR	940	7244	NR
425	19782	NR	555	213600	NR	685	53604	NR	815	5570	NR	945	6266	NR
430	32934	NR	560	232241	NR	690	46370	NR	820	5470	NR	950	6258	NR
435	52004	NR	565	250545	NR	695	40048	NR	825	5780	NR	955	6166	NR
440	77987	NR	570	269608	NR	700	35148	NR	830	4151	NR	960	4813	NR
445	117241	NR	575	286007	NR	705	30717	NR	835	5899	NR	965	6539	NR
450	171397	NR	580	300402	NR	710	27137	NR	840	5774	NR	970	2930	NR
455	188676	NR	585	310093	NR	715	24655	NR	845	4055	NR	975	3170	NR
460	142860	NR	590	313605	NR	720	21845	NR	850	4767	NR	980	3959	NR
465	100906	NR	595	314960	NR	725	19116	NR	855	4780	NR	985	6920	NR
470	78130	NR	600	311387	NR	730	16889	NR	860	5148	NR	990	2710	NR
475	57660	NR	605	301618	NR	735	14825	NR	865	6865	NR	995	5566	NR
480	43089	NR	610	288042	NR	740	13154	NR	870	5392	NR	1000	0	NR
485	38569	NR	615	270953	NR	745	11725	NR	875	6166	NR			

REPORT NUMBER: SP1-2307-100-1

TM-30-18

Summary

$R_f = 74.9$
 $R_g = 92.7$
 $CIE R_a = 71.3$
 $R_g = -35.7$



Color Vector Graphics



REPORT NUMBER: SP1-2307-100-1

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)




CES01 = 86	CES26 = 67	CES51 = 85	CES76 = 60
CES02 = 62	CES27 = 90	CES52 = 83	CES77 = 76
CES03 = 31	CES28 = 85	CES53 = 77	CES78 = 64
CES04 = 71	CES29 = 73	CES54 = 85	CES79 = 86
CES05 = 49	CES30 = 90	CES55 = 82	CES80 = 85
CES06 = 51	CES31 = 76	CES56 = 74	CES81 = 72
CES07 = 41	CES32 = 67	CES57 = 73	CES82 = 93
CES08 = 40	CES33 = 84	CES58 = 73	CES83 = 92
CES09 = 29	CES34 = 77	CES59 = 83	CES84 = 87
CES10 = 76	CES35 = 88	CES60 = 88	CES85 = 74
CES11 = 59	CES36 = 89	CES61 = 79	CES86 = 64
CES12 = 65	CES37 = 85	CES62 = 85	CES87 = 77
CES13 = 43	CES38 = 98	CES63 = 76	CES88 = 80
CES14 = 74	CES39 = 98	CES64 = 62	CES89 = 67
CES15 = 71	CES40 = 94	CES65 = 64	CES90 = 81
CES16 = 47	CES41 = 97	CES66 = 57	CES91 = 76
CES17 = 50	CES42 = 88	CES67 = 55	CES92 = 55
CES18 = 56	CES43 = 80	CES68 = 64	CES93 = 72
CES19 = 73	CES44 = 99	CES69 = 73	CES94 = 49
CES20 = 66	CES45 = 86	CES70 = 60	CES95 = 66
CES21 = 87	CES46 = 83	CES71 = 56	CES96 = 76
CES22 = 79	CES47 = 91	CES72 = 84	CES97 = 81
CES23 = 92	CES48 = 76	CES73 = 53	CES98 = 76
CES24 = 91	CES49 = 80	CES74 = 93	CES99 = 64
CES25 = 73	CES50 = 85	CES75 = 61	



REPORT NUMBER: SP1-2307-100-1

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-2307-100-1

TM-30-18

Measure Comparisons



(END OF REPORT)