

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: METALUX

Report Number: P828638

Luminaire Tested: **OHBL-24HE-N-UNV-L950-CD-UPL36**

Issue Date: 5/3/2024



Test Information

Test Method: LM-79-08
Report Number: P828638
REPORT IS A COMBINATION OF REPORTS P826302 AND G3-2310-221-2
Test Lab: INNOVATION CENTER
Issue Date: 5/3/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: METALUX
Catalog Number: OHBL-24HE-N-UNV-L950-CD-UPL36
Description:
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 23994.1 lumens
Efficiency: N/A
Efficacy: 148.3 lumens/watt
Spacing Criteria (0/90/45): 1.47 / 0.53 / 0.78
Luminous Opening: Rectangular w/ Sides (W: 3.78' x L: 1.8' x H: 0.17')
CIE Type: Semi-Direct

Input Watts (W): 161.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P828638

CATALOG NUMBER: OHBL-24HE-N-UNV-L950-CD-UPL36

Luminous Intensity Polar Plot





TEST NUMBER: P828638

CATALOG NUMBER: OHBL-24HE-N-UNV-L950-CD-UPL36

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	115	115	115	115	111	111	111	111	102	102	102	95	95	95	87	87	87	84		
1	106	101	98	94	102	98	94	91	91	88	85	84	82	80	78	76	75	72		
2	97	90	84	79	93	87	81	76	81	76	72	75	72	68	70	67	65	62		
3	90	80	73	67	86	77	71	65	72	67	62	68	63	59	63	59	56	54		
4	83	72	64	58	79	70	62	57	65	59	54	61	56	52	57	53	50	47		
5	77	65	57	51	74	63	56	50	59	53	48	56	50	46	52	48	44	42		
6	71	59	51	45	68	57	50	44	54	48	43	51	46	41	48	43	40	38		
7	66	54	46	41	64	53	45	40	50	43	39	47	41	37	44	40	36	34		
8	62	50	42	37	60	48	41	36	46	40	35	44	38	34	41	36	33	31		
9	58	46	39	33	56	45	38	33	43	36	32	40	35	31	38	34	30	28		
10	55	43	35	31	53	42	35	30	40	34	29	38	32	29	36	31	28	26		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22373	22373	22373
5°	22234	20384	19036
10°	22390	17178	15338
15°	22729	14698	12652
20°	23263	12434	10286
25°	23955	10297	9061
30°	24659	8875	8466
35°	25034	8093	8117
40°	24457	7315	7755
45°	22344	6615	7236
50°	18700	5849	6855
55°	14072	5128	6168
60°	9744	4403	5986
65°	6453	3798	5966
70°	4313	3571	6414
75°	2898	3694	7107
80°	1889	4111	7780
85°	985	5188	9276



TEST NUMBER: P828638

CATALOG NUMBER: OHBL-24HE-N-UNV-L950-CD-UPL36

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1190.9	5.0
10°-20°	2801.5	11.7
20°-30°	3511.6	14.6
30°-40°	3726.3	15.5
40°-50°	3369.1	14.0
50°-60°	2442.8	10.2
60°-70°	1533.0	6.4
70°-80°	1014.5	4.2
80°-90°	591.1	2.5
90°-100°	522.3	2.2
100°-110°	1278.8	5.3
110°-120°	1017.3	4.2
120°-130°	482.8	2.0
130°-140°	241.7	1.0
140°-150°	140.3	0.6
150°-160°	80.1	0.3
160°-170°	38.3	0.2
170°-180°	11.7	0.0
0°-30°	7504.0	31.3
0°-40°	11230.3	46.8
0°-60°	17042.2	71.0
0°-90°	20180.9	84.1
90°-120°	2818.4	11.7
90°-150°	3683.2	15.4
90°-180°	3813.0	15.9
0°-180°	23994.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	14147	14147	14147	14147	14147	
5°	14119	13757	12949	12348	12037	###
15°	14226	11596	9210	8190	7819	4035
25°	14321	8966	6167	5473	5300	6616
35°	13808	5961	4476	4336	4334	8584
45°	10916	3776	3244	3322	3378	8315
55°	5779	2340	2117	2296	2378	5221
65°	2067	1357	1225	1570	1745	2151
75°	638	731	823	1278	1354	711
85°	112	303	602	837	769	134
90°	7	169	404	554	559	12
95°	59	197	450	600	633	205
105°	1295	1341	1429	1193	1114	1231
115°	910	925	1041	1085	1080	920
125°	457	478	544	556	546	429
135°	274	283	308	329	330	217
145°	206	211	218	232	231	131
155°	169	176	180	183	180	77
165°	131	133	134	135	136	38
175°	120	120	121	121	122	12
180°	118	118	118	118	118	



TEST NUMBER: P828638

CATALOG NUMBER: OHBL-24HE-N-UNV-L950-CD-UPL36

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	14147.1	14147.1	14147.1	14147.1	14147.1
2.5°	14117.5	14036.7	13785.0	13631.4	13502.2
5°	14118.8	13756.6	12948.8	12348.3	12037.2
7.5°	14139.1	13333.9	11878.4	11001.8	10659.8
10°	14170.0	12810.1	10879.3	9944.9	9625.7
12.5°	14192.9	12220.4	10000.1	9040.0	8690.0
15°	14226.5	11595.6	9209.7	8190.4	7818.8
17.5°	14257.5	11007.2	8428.7	7363.8	6950.3
20°	14288.4	10373.0	7647.8	6550.5	6209.8
22.5°	14318.1	9703.9	6885.7	5919.0	5686.1
25°	14320.8	8966.0	6166.7	5473.3	5299.6
27.5°	14285.8	8201.2	5583.7	5100.3	4992.6
30°	14225.2	7459.3	5131.3	4831.1	4754.3
32.5°	14074.4	6702.6	4781.2	4571.2	4526.8
35°	13807.8	5960.7	4475.6	4335.6	4334.2
37.5°	13387.7	5302.3	4144.4	4120.1	4149.8
40°	12767.0	4726.0	3830.6	3895.3	3895.3
42.5°	11939.0	4225.2	3546.6	3612.5	3595.0
45°	10915.6	3775.5	3243.5	3321.7	3378.2
47.5°	9729.4	3379.6	2933.9	3084.7	3162.8
50°	8439.5	3002.5	2651.2	2843.7	2932.5
52.5°	7087.7	2653.8	2375.1	2596.0	2667.3
55°	5778.9	2340.1	2116.6	2295.7	2377.8
57.5°	4594.1	2041.2	1863.5	2033.1	2202.8
60°	3574.8	1784.0	1625.2	1867.5	2037.2
62.5°	2730.6	1555.2	1401.6	1712.7	1882.3
65°	2066.8	1357.2	1225.3	1570.0	1745.0
67.5°	1557.9	1186.2	1087.9	1466.3	1637.3
70°	1170.1	1020.6	977.5	1401.6	1555.2
72.5°	864.4	868.5	890.0	1345.1	1462.2
75°	638.3	731.1	822.7	1277.7	1354.5
77.5°	456.5	605.9	762.1	1197.0	1223.9
80°	316.4	494.1	698.8	1090.6	1067.8
82.5°	197.9	395.9	642.3	973.5	910.2
85°	111.7	302.9	601.8	837.4	768.8
87.5°	49.8	226.2	526.4	653.0	609.9
90°	7.0	169.2	403.5	554.0	559.0
92.5°	24.4	157.2	388.7	533.1	551.8
95°	59.3	196.7	450.5	600.0	632.8
97.5°	331.9	427.6	591.6	750.3	787.4
100°	706.2	786.4	820.8	916.7	947.6
102.5°	1103.2	1173.1	1120.1	1049.6	1034.3
105°	1295.0	1340.8	1428.6	1192.6	1113.8



TEST NUMBER: P828638

CATALOG NUMBER: OHBL-24HE-N-UNV-L950-CD-UPL36

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1065.5	1100.5	1213.4	1254.3	1233.2
115°	910.3	925.1	1041.1	1084.9	1080.3
117.5°	782.2	793.6	896.2	926.4	918.1
120°	660.4	676.6	766.1	782.2	775.2
122.5°	550.0	573.0	646.3	660.5	647.9
125°	457.0	478.0	543.7	556.0	546.0
127.5°	393.0	400.9	457.5	472.0	470.7
130°	340.0	349.6	391.5	412.1	410.4
132.5°	302.1	311.8	344.7	366.1	368.7
135°	274.3	283.1	307.5	329.0	329.9
137.5°	251.7	260.9	276.9	298.8	299.7
140°	232.6	240.5	253.8	273.4	273.4
142.5°	218.2	224.8	234.6	250.7	250.7
145°	205.7	211.4	218.4	231.8	231.4
147.5°	195.3	201.5	207.1	214.8	214.2
150°	185.7	192.3	195.8	201.6	201.1
152.5°	177.0	183.6	187.1	190.7	190.2
155°	169.2	175.8	179.8	182.8	180.1
157.5°	146.1	148.7	151.3	152.2	152.2
160°	140.8	142.6	145.2	145.2	146.1
162.5°	135.6	137.4	139.1	140.0	140.8
165°	131.3	133.0	133.9	134.8	135.6
167.5°	127.8	128.7	129.5	130.4	130.4
170°	124.3	125.2	126.1	126.1	126.9
172.5°	121.7	122.6	123.5	123.5	123.5
175°	120.0	120.0	120.9	120.9	121.7
177.5°	118.2	119.1	119.1	119.1	120.0
180°	118.2	118.2	118.2	118.2	118.2



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180° - - 45°-225° - - - 90°-270°







107.5°	1307.1	1354.2	1472.3	1381.6	1239.7
110°	1208.4	1257.5	1374.9	1375.1	1315.8



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

METALUX

Report Number: SP1-2307-100-9

Test Date: 08/01/2023

Luminaire Tested: OHB-15SE-N-UNV-L950-CD

Data in this report applies to families of products including OHB-15SE-N-UNV-L950-CD.

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2307-100-9
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 08/04/2023
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: METALUX
 Catalog Number: **OHB-15SE-N-UNV-L950-CD**
 Description: 15000 LUMEN OHB SE LED LUMINAIRE WITH 90CRI, 5000K LEDS AND NARROW LENS

LENS

Spectral Parameters

CCT (K):	5013	CRI (Ra):	92.0		
CIE u':	0.2111	R1:	92.6	R9:	62.7
CIE v':	0.4847	R2:	96.7	R10:	90.0
Duv:	0.0002	R3:	96.5	R11:	89.8
CIE x:	0.3447	R4:	90.1	R12:	69.9
CIE y:	0.3517	R5:	91.1	R13:	94.5
CIE z:	0.3036	R6:	92.0	R14:	98.3
Peak Wavelength (nm):	455	R7:	92.4		
Dominant Wavelength (nm):	572	R8:	84.9		
Purity:	9.1				
Rf:	88.9				
Rg:	97.2				



Test Conditions

Stabilization Time: 26M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.7/57%
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2307-100-9

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	2/9/2023	8/9/2023
Power Meter	XITRON 2801 IN0071	11/29/2022	11/29/2023
AC Power Source	CHROMA 61603 IN0063	11/28/2022	11/28/2023
DC Power Source	AGILENT E3634A IN0208	11/28/2022	11/28/2023
Sphere Thermometer	ONSET IN0085	11/28/2022	11/28/2023
Room Thermometer	ONSET IN0046	11/28/2022	11/28/2023

REPORT NUMBER: SP1-2307-100-9

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 5000K 4-step quadrangle

REPORT NUMBER: SP1-2307-100-9

Photopic Flux vs. Wavelength



#####

λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)
360	6694	NR	490	112019	NR	620	173132	NR	750	14981	NR	880	5536	NR
365	5354	NR	495	119136	NR	625	169860	NR	755	13480	NR	885	6938	NR
370	5722	NR	500	127627	NR	630	163982	NR	760	11900	NR	890	5411	NR
375	6251	NR	505	139687	NR	635	158304	NR	765	10671	NR	895	4784	NR
380	6177	NR	510	148127	NR	640	151433	NR	770	9643	NR	900	5872	NR
385	5889	NR	515	155327	NR	645	144044	NR	775	8310	NR	905	5214	NR
390	5252	NR	520	161724	NR	650	134971	NR	780	7378	NR	910	5425	NR
395	5012	NR	525	166350	NR	655	126523	NR	785	7348	NR	915	5372	NR
400	4505	NR	530	170827	NR	660	117624	NR	790	6731	NR	920	5263	NR
405	4163	NR	535	174287	NR	665	107737	NR	795	6603	NR	925	5581	NR
410	4931	NR	540	177402	NR	670	97796	NR	800	6333	NR	930	7934	NR
415	6887	NR	545	179468	NR	675	88146	NR	805	5919	NR	935	6835	NR
420	10750	NR	550	180621	NR	680	80008	NR	810	5757	NR	940	4871	NR
425	18574	NR	555	182239	NR	685	71588	NR	815	6226	NR	945	6554	NR
430	31943	NR	560	184077	NR	690	63388	NR	820	5694	NR	950	6239	NR
435	54504	NR	565	184113	NR	695	56106	NR	825	5621	NR	955	4562	NR
440	91570	NR	570	183843	NR	700	49976	NR	830	5832	NR	960	3863	NR
445	155007	NR	575	183242	NR	705	44326	NR	835	5478	NR	965	4898	NR
450	253466	NR	580	182759	NR	710	39116	NR	840	5675	NR	970	7576	NR
455	316705	NR	585	182781	NR	715	34755	NR	845	4960	NR	975	6056	NR
460	273954	NR	590	181075	NR	720	30900	NR	850	5274	NR	980	3439	NR
465	214019	NR	595	181315	NR	725	27349	NR	855	5470	NR	985	3623	NR
470	175153	NR	600	181289	NR	730	23954	NR	860	6539	NR	990	4301	NR
475	140894	NR	605	180053	NR	735	21526	NR	865	6378	NR	995	7368	NR
480	115223	NR	610	177907	NR	740	18965	NR	870	5702	NR	1000	10668	NR
485	108577	NR	615	175575	NR	745	17153	NR	875	4933	NR			

REPORT NUMBER: SP1-2307-100-9

Scotopic Flux vs. Wavelength



Scotopic Lumens: 26039.5

S/P: 2.08

λ (nm)	Power (μW/nm)	Lumens (Φ/nm)	λ (nm)	Power (μW/nm)	Lumens (Φ/nm)	λ (nm)	Power (μW/nm)	Lumens (Φ/nm)	λ (nm)	Power (μW/nm)	Lumens (Φ/nm)	λ (nm)	Power (μW/nm)	Lumens (Φ/nm)
360	6694	NR	490	112019	NR	620	173132	NR	750	14981	NR	880	5536	NR
365	5354	NR	495	119136	NR	625	169860	NR	755	13480	NR	885	6938	NR
370	5722	NR	500	127627	NR	630	163982	NR	760	11900	NR	890	5411	NR
375	6251	NR	505	139687	NR	635	158304	NR	765	10671	NR	895	4784	NR
380	6177	NR	510	148127	NR	640	151433	NR	770	9643	NR	900	5872	NR
385	5889	NR	515	155327	NR	645	144044	NR	775	8310	NR	905	5214	NR
390	5252	NR	520	161724	NR	650	134971	NR	780	7378	NR	910	5425	NR
395	5012	NR	525	166350	NR	655	126523	NR	785	7348	NR	915	5372	NR
400	4505	NR	530	170827	NR	660	117624	NR	790	6731	NR	920	5263	NR
405	4163	NR	535	174287	NR	665	107737	NR	795	6603	NR	925	5581	NR
410	4931	NR	540	177402	NR	670	97796	NR	800	6333	NR	930	7934	NR
415	6887	NR	545	179468	NR	675	88146	NR	805	5919	NR	935	6835	NR
420	10750	NR	550	180621	NR	680	80008	NR	810	5757	NR	940	4871	NR
425	18574	NR	555	182239	NR	685	71588	NR	815	6226	NR	945	6554	NR
430	31943	NR	560	184077	NR	690	63388	NR	820	5694	NR	950	6239	NR
435	54504	NR	565	184113	NR	695	56106	NR	825	5621	NR	955	4562	NR
440	91570	NR	570	183843	NR	700	49976	NR	830	5832	NR	960	3863	NR
445	155007	NR	575	183242	NR	705	44326	NR	835	5478	NR	965	4898	NR
450	253466	NR	580	182759	NR	710	39116	NR	840	5675	NR	970	7576	NR
455	316705	NR	585	182781	NR	715	34755	NR	845	4960	NR	975	6056	NR
460	273954	NR	590	181075	NR	720	30900	NR	850	5274	NR	980	3439	NR
465	214019	NR	595	181315	NR	725	27349	NR	855	5470	NR	985	3623	NR
470	175153	NR	600	181289	NR	730	23954	NR	860	6539	NR	990	4301	NR
475	140894	NR	605	180053	NR	735	21526	NR	865	6378	NR	995	7368	NR
480	115223	NR	610	177907	NR	740	18965	NR	870	5702	NR	1000	10668	NR
485	108577	NR	615	175575	NR	745	17153	NR	875	4933	NR			

REPORT NUMBER: SP1-2307-100-9

Melanopic Flux vs. Wavelength



Melanopic Lumens: 11248.3 M/P: 0.9

λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)
360	6694	NR	490	112019	NR	620	173132	NR	750	14981	NR	880	5536	NR
365	5354	NR	495	119136	NR	625	169860	NR	755	13480	NR	885	6938	NR
370	5722	NR	500	127627	NR	630	163982	NR	760	11900	NR	890	5411	NR
375	6251	NR	505	139687	NR	635	158304	NR	765	10671	NR	895	4784	NR
380	6177	NR	510	148127	NR	640	151433	NR	770	9643	NR	900	5872	NR
385	5889	NR	515	155327	NR	645	144044	NR	775	8310	NR	905	5214	NR
390	5252	NR	520	161724	NR	650	134971	NR	780	7378	NR	910	5425	NR
395	5012	NR	525	166350	NR	655	126523	NR	785	7348	NR	915	5372	NR
400	4505	NR	530	170827	NR	660	117624	NR	790	6731	NR	920	5263	NR
405	4163	NR	535	174287	NR	665	107737	NR	795	6603	NR	925	5581	NR
410	4931	NR	540	177402	NR	670	97796	NR	800	6333	NR	930	7934	NR
415	6887	NR	545	179468	NR	675	88146	NR	805	5919	NR	935	6835	NR
420	10750	NR	550	180621	NR	680	80008	NR	810	5757	NR	940	4871	NR
425	18574	NR	555	182239	NR	685	71588	NR	815	6226	NR	945	6554	NR
430	31943	NR	560	184077	NR	690	63388	NR	820	5694	NR	950	6239	NR
435	54504	NR	565	184113	NR	695	56106	NR	825	5621	NR	955	4562	NR
440	91570	NR	570	183843	NR	700	49976	NR	830	5832	NR	960	3863	NR
445	155007	NR	575	183242	NR	705	44326	NR	835	5478	NR	965	4898	NR
450	253466	NR	580	182759	NR	710	39116	NR	840	5675	NR	970	7576	NR
455	316705	NR	585	182781	NR	715	34755	NR	845	4960	NR	975	6056	NR
460	273954	NR	590	181075	NR	720	30900	NR	850	5274	NR	980	3439	NR
465	214019	NR	595	181315	NR	725	27349	NR	855	5470	NR	985	3623	NR
470	175153	NR	600	181289	NR	730	23954	NR	860	6539	NR	990	4301	NR
475	140894	NR	605	180053	NR	735	21526	NR	865	6378	NR	995	7368	NR
480	115223	NR	610	177907	NR	740	18965	NR	870	5702	NR	1000	10668	NR
485	108577	NR	615	175575	NR	745	17153	NR	875	4933	NR			

REPORT NUMBER: SP1-2307-100-9


TM-30-18

Summary

$R_f = 88.9$
 $R_g = 97.2$
 $CIE R_a = 92.0$
 $R_9 = 62.7$



Color Vector Graphics



REPORT NUMBER: SP1-2307-100-9

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 85	CES26 = 93	CES51 = 92	CES76 = 85
CES02 = 61	CES27 = 89	CES52 = 95	CES77 = 86
CES03 = 31	CES28 = 95	CES53 = 92	CES78 = 84
CES04 = 69	CES29 = 94	CES54 = 89	CES79 = 95
CES05 = 48	CES30 = 83	CES55 = 86	CES80 = 93
CES06 = 50	CES31 = 96	CES56 = 88	CES81 = 89
CES07 = 41	CES32 = 93	CES57 = 85	CES82 = 97
CES08 = 40	CES33 = 92	CES58 = 85	CES83 = 97
CES09 = 29	CES34 = 93	CES59 = 94	CES84 = 92
CES10 = 73	CES35 = 96	CES60 = 89	CES85 = 83
CES11 = 56	CES36 = 76	CES61 = 88	CES86 = 88
CES12 = 62	CES37 = 95	CES62 = 78	CES87 = 91
CES13 = 42	CES38 = 78	CES63 = 87	CES88 = 95
CES14 = 74	CES39 = 97	CES64 = 81	CES89 = 88
CES15 = 71	CES40 = 97	CES65 = 84	CES90 = 93
CES16 = 46	CES41 = 92	CES66 = 78	CES91 = 70
CES17 = 49	CES42 = 96	CES67 = 77	CES92 = 78
CES18 = 56	CES43 = 95	CES68 = 82	CES93 = 86
CES19 = 70	CES44 = 99	CES69 = 84	CES94 = 81
CES20 = 65	CES45 = 97	CES70 = 81	CES95 = 81
CES21 = 85	CES46 = 95	CES71 = 73	CES96 = 92
CES22 = 77	CES47 = 91	CES72 = 91	CES97 = 94
CES23 = 91	CES48 = 85	CES73 = 77	CES98 = 92
CES24 = 90	CES49 = 95	CES74 = 89	CES99 = 90
CES25 = 70	CES50 = 93	CES75 = 77	



REPORT NUMBER: SP1-2307-100-9

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-2307-100-9

TM-30-18

Measure Comparisons



(END OF REPORT)