

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: METALUX

Report Number: P828085

Luminaire Tested: **OHBL-30SE-W-UNV-L935-CD-UPL15**

Issue Date: 5/3/2024



Test Information

Test Method: LM-79-08
Report Number: P828085
REPORT IS A COMBINATION OF REPORTS P826130 AND G3-2310-221-10
Test Lab: INNOVATION CENTER
Issue Date: 5/3/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: METALUX
Catalog Number: OHBL-30SE-W-UNV-L935-CD-UPL15
Description:
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 25684.4 lumens
Efficiency: N/A
Efficacy: 139.4 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.58 / 1.62
Luminous Opening: Rectangular w/ Sides (W: 3.78' x L: 1.67' x H: 0.17')
CIE Type: Direct

Input Watts (W): 184.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P828085

CATALOG NUMBER: OHBL-30SE-W-UNV-L935-CD-UPL15

Luminous Intensity Polar Plot





TEST NUMBER: P828085

CATALOG NUMBER: OHBL-30SE-W-UNV-L935-CD-UPL15

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	117	117	117	117	114	114	114	114	107	107	107	101	101	101	96	96	96	96	96	93
1	108	103	99	95	104	100	96	93	95	92	89	90	87	85	85	83	81	81	81	79
2	98	90	84	78	95	88	82	77	83	78	74	79	75	71	75	72	69	69	69	66
3	90	79	71	65	86	77	70	64	73	67	62	70	64	60	66	62	58	58	58	56
4	82	70	62	55	79	68	60	54	65	58	53	62	56	51	59	54	50	50	50	48
5	75	63	54	47	73	61	53	47	58	51	45	55	49	44	53	48	43	43	43	41
6	69	56	47	41	67	55	47	41	52	45	40	50	44	39	48	42	38	38	38	36
7	64	51	42	36	62	50	41	36	47	40	35	45	39	34	43	38	33	33	33	31
8	59	46	38	32	58	45	37	32	43	36	31	41	35	30	40	34	30	30	30	28
9	55	42	34	28	54	41	34	28	40	33	28	38	32	27	37	31	27	27	27	25
10	52	39	31	26	50	38	30	25	37	30	25	35	29	25	34	28	24	24	24	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13929	13929	13929
5°	13732	13910	14088
10°	13494	13888	14105
15°	13165	13659	13653
20°	12741	13189	12984
25°	12197	12621	12723
30°	11499	12198	13692
35°	10714	12424	16022
40°	9819	13455	18522
45°	8890	15262	19909
50°	7929	16876	18527
55°	7024	16855	14156
60°	6106	14259	8655
65°	5147	9845	5243
70°	4080	6364	3785
75°	2993	4560	3509
80°	2021	4004	3959
85°	1207	4396	6259



TEST NUMBER: P828085

CATALOG NUMBER: OHBL-30SE-W-UNV-L935-CD-UPL15

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	779.3	3.0
10°-20°	2206.8	8.6
20°-30°	3229.3	12.6
30°-40°	4193.9	16.3
40°-50°	5121.3	19.9
50°-60°	4510.1	17.6
60°-70°	2350.3	9.2
70°-80°	1007.9	3.9
80°-90°	487.2	1.9
90°-100°	348.8	1.4
100°-110°	561.8	2.2
110°-120°	444.9	1.7
120°-130°	218.8	0.9
130°-140°	109.5	0.4
140°-150°	61.3	0.2
150°-160°	33.2	0.1
160°-170°	15.2	0.1
170°-180°	4.6	0.0
0°-30°	6215.5	24.2
0°-40°	10409.4	40.5
0°-60°	20040.9	78.0
0°-90°	23886.2	93.0
90°-120°	1355.5	5.3
90°-150°	1745.1	6.8
90°-180°	1798.0	7.0
0°-180°	25684.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	8155	8155	8155	8155	8155	
5°	8080	8141	8185	8257	8248	766
15°	7645	7860	7935	7876	7812	2153
25°	6774	7136	7015	6883	6890	3109
35°	5498	6079	6384	7444	7921	3427
45°	4049	5094	6962	8430	8606	3122
55°	2696	4462	6484	5685	5053	2419
65°	1547	3091	2968	1650	1420	1530
75°	623	1446	954	653	619	679
85°	132	516	486	475	480	147
90°	4	205	344	398	411	11
95°	27	169	344	417	445	86
105°	534	582	609	512	490	507
115°	374	398	469	490	486	378
125°	188	203	251	267	268	177
135°	115	118	138	159	162	91
145°	90	88	92	104	107	57
155°	75	76	74	74	75	33
165°	52	52	53	53	53	15
175°	48	48	48	48	48	5
180°	48	48	48	48	48	



TEST NUMBER: P828085

CATALOG NUMBER: OHBL-30SE-W-UNV-L935-CD-UPL15

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	8155.2	8155.2	8155.2	8155.2	8155.2
2.5°	8120.1	8155.2	8157.0	8206.3	8201.0
5°	8079.6	8141.2	8185.2	8257.3	8248.5
7.5°	8012.8	8109.5	8186.9	8266.2	8259.1
10°	7917.8	8049.7	8151.8	8216.8	8195.8
12.5°	7794.6	7968.8	8069.1	8083.2	8042.7
15°	7645.0	7859.7	7935.3	7875.5	7812.2
17.5°	7476.1	7727.8	7754.1	7623.9	7544.8
20°	7265.0	7551.8	7525.4	7345.9	7257.9
22.5°	7030.9	7358.2	7273.8	7085.5	7001.1
25°	6774.1	7136.5	7015.1	6883.2	6890.2
27.5°	6473.2	6884.9	6767.0	6826.8	6939.5
30°	6167.1	6621.0	6548.8	6897.3	7118.9
32.5°	5831.0	6350.0	6415.2	7103.1	7465.6
35°	5498.4	6079.1	6383.5	7444.4	7921.2
37.5°	5130.7	5804.6	6434.5	7838.6	8338.2
40°	4773.5	5537.2	6550.6	8192.3	8614.5
42.5°	4409.3	5297.8	6745.9	8401.6	8730.7
45°	4048.6	5093.8	6962.3	8429.8	8605.8
47.5°	3687.9	4921.3	7111.9	8206.3	8125.3
50°	3339.5	4768.2	7122.4	7669.7	7338.8
52.5°	3014.0	4627.5	6928.9	6814.5	6300.8
55°	2695.6	4462.1	6483.8	5684.9	5053.2
57.5°	2405.3	4233.3	5797.6	4470.9	3781.2
60°	2097.3	3923.7	4910.8	3270.9	2727.2
62.5°	1814.1	3538.3	3916.7	2276.8	1960.1
65°	1546.6	3091.4	2968.2	1650.4	1419.9
67.5°	1263.3	2628.7	2190.6	1203.5	1055.7
70°	1041.6	2199.3	1631.1	936.1	849.8
72.5°	814.7	1791.2	1219.3	760.1	712.6
75°	622.8	1446.3	953.7	652.8	619.3
77.5°	459.3	1143.7	767.2	577.1	545.4
80°	322.0	900.8	642.3	515.5	503.2
82.5°	216.4	696.8	547.2	490.9	492.7
85°	132.0	515.5	485.6	475.1	480.3
87.5°	63.3	366.0	417.0	432.8	438.1
90°	4.2	204.8	344.4	397.7	410.6
92.5°	8.3	165.8	319.8	380.6	397.8
95°	26.8	169.1	344.3	417.4	445.4
97.5°	141.8	245.6	398.8	470.3	490.6
100°	286.1	380.8	453.2	509.8	520.8
102.5°	456.9	505.2	505.5	511.7	510.2
105°	534.5	581.6	608.8	512.2	489.8



TEST NUMBER: P828085

CATALOG NUMBER: OHBL-30SE-W-UNV-L935-CD-UPL15

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	434.8	472.3	538.7	548.2	536.8
115°	373.9	398.5	468.8	489.9	485.9
117.5°	324.0	341.7	403.1	422.5	422.6
120°	272.3	289.8	341.6	361.0	361.9
122.5°	227.3	242.8	294.4	311.3	312.2
125°	188.2	203.4	250.7	266.6	267.5
127.5°	160.6	168.2	213.5	231.1	231.2
130°	140.6	144.8	181.4	199.8	203.3
132.5°	126.4	129.8	158.5	176.9	181.3
135°	114.8	118.1	138.2	159.2	161.8
137.5°	106.4	108.1	123.7	142.2	146.5
140°	98.1	100.6	110.1	128.5	131.1
142.5°	94.0	93.9	100.8	116.6	118.3
145°	89.9	88.1	91.5	103.7	107.2
147.5°	85.8	85.7	87.3	94.3	96.9
150°	81.6	83.3	80.6	84.9	88.4
152.5°	78.3	79.1	77.2	77.2	81.6
155°	74.9	75.8	73.9	73.9	74.8
157.5°	58.3	59.2	60.0	60.8	60.8
160°	55.8	56.7	57.5	57.5	58.3
162.5°	54.2	55.0	55.0	55.8	55.8
165°	52.5	52.5	53.3	53.3	53.3
167.5°	50.8	50.8	51.7	51.7	52.5
170°	49.2	50.0	50.0	50.0	50.8
172.5°	48.3	48.3	49.2	49.2	49.2
175°	47.5	47.5	47.5	48.3	48.3
177.5°	46.7	47.5	47.5	47.5	47.5
180°	47.5	47.5	47.5	47.5	47.5



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180° - - 45°-225° - - - 90°-270°







107.5°	536.3	582.9	637.0	554.4	497.1
110°	495.5	538.3	599.3	585.0	536.8



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

METALUX

Report Number: SP1-2307-100-7

Test Date: 07/28/2023

Luminaire Tested: OHB-15SE-N-UNV-L935-CD

Data in this report applies to families of products including OHB-15SE-N-UNV-L935-CD.

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2307-100-7
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 08/04/2023
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: METALUX
 Catalog Number: **OHB-15SE-N-UNV-L935-CD**
 Description: 15000 LUMEN OHB SE LED LUMINAIRE WITH 90CRI, 3500K LEDS AND NARROW LENS

LENS

Spectral Parameters

CCT (K):	3429	CRI (Ra):	90.9		
CIE u':	0.2376	R1:	91.1	R9:	50.7
CIE v':	0.5121	R2:	96.7	R10:	90.8
Duv:	-0.0004	R3:	97.7	R11:	88.9
CIE x:	0.4088	R4:	88.8	R12:	74.6
CIE y:	0.3916	R5:	90.3	R13:	92.9
CIE z:	0.1997	R6:	94.5	R14:	99.5
Peak Wavelength (nm):	609	R7:	89.8		
Dominant Wavelength (nm):	581	R8:	78.2		
Purity:	40.4				
Rf:	88.9				
Rg:	96.3				



Test Conditions

Stabilization Time: 23M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.7/55%
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2307-100-7

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	2/9/2023	8/9/2023
Power Meter	XITRON 2801 IN0071	11/29/2022	11/29/2023
AC Power Source	CHROMA 61603 IN0063	11/28/2022	11/28/2023
DC Power Source	AGILENT E3634A IN0208	11/28/2022	11/28/2023
Sphere Thermometer	ONSET IN0085	11/28/2022	11/28/2023
Room Thermometer	ONSET IN0046	11/28/2022	11/28/2023

REPORT NUMBER: SP1-2307-100-7

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2307-100-7

Photopic Flux vs. Wavelength



#####

λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)
360	5498	NR	490	81900	NR	620	217907	NR	750	17550	NR	880	6189	NR
365	4903	NR	495	90120	NR	625	213734	NR	755	15662	NR	885	6187	NR
370	4767	NR	500	98453	NR	630	206250	NR	760	13792	NR	890	3830	NR
375	5225	NR	505	109244	NR	635	198796	NR	765	12765	NR	895	4688	NR
380	5499	NR	510	117784	NR	640	189406	NR	770	11372	NR	900	4680	NR
385	5081	NR	515	125000	NR	645	180677	NR	775	9965	NR	905	4599	NR
390	4739	NR	520	131786	NR	650	168402	NR	780	9154	NR	910	4495	NR
395	4255	NR	525	136796	NR	655	157693	NR	785	8847	NR	915	3983	NR
400	3864	NR	530	142357	NR	660	145357	NR	790	7937	NR	920	4675	NR
405	3583	NR	535	147243	NR	665	132743	NR	795	6956	NR	925	4952	NR
410	3994	NR	540	152273	NR	670	120757	NR	800	6970	NR	930	6097	NR
415	5055	NR	545	157222	NR	675	108421	NR	805	6299	NR	935	5657	NR
420	7131	NR	550	161271	NR	680	97325	NR	810	6023	NR	940	4574	NR
425	11311	NR	555	167038	NR	685	86839	NR	815	6343	NR	945	5252	NR
430	17754	NR	560	173115	NR	690	76248	NR	820	6462	NR	950	5635	NR
435	28634	NR	565	178502	NR	695	67406	NR	825	5476	NR	955	4501	NR
440	46392	NR	570	184331	NR	700	60039	NR	830	5786	NR	960	2938	NR
445	78344	NR	575	189666	NR	705	53650	NR	835	5884	NR	965	5544	NR
450	131219	NR	580	196488	NR	710	47273	NR	840	4862	NR	970	5050	NR
455	170311	NR	585	202769	NR	715	41664	NR	845	5651	NR	975	5575	NR
460	154269	NR	590	207213	NR	720	37083	NR	850	5178	NR	980	2973	NR
465	126622	NR	595	213472	NR	725	32494	NR	855	5510	NR	985	4912	NR
470	109065	NR	600	218473	NR	730	28665	NR	860	5438	NR	990	5454	NR
475	91762	NR	605	220737	NR	735	25540	NR	865	5848	NR	995	6068	NR
480	78213	NR	610	221090	NR	740	22878	NR	870	4969	NR	1000	9406	NR
485	77035	NR	615	220059	NR	745	20304	NR	875	5438	NR			

REPORT NUMBER: SP1-2307-100-7

Scotopic Flux vs. Wavelength



Scotopic Lumens: 19629.6

S/P: 1.6

λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)
360	5498	NR	490	81900	NR	620	217907	NR	750	17550	NR	880	6189	NR
365	4903	NR	495	90120	NR	625	213734	NR	755	15662	NR	885	6187	NR
370	4767	NR	500	98453	NR	630	206250	NR	760	13792	NR	890	3830	NR
375	5225	NR	505	109244	NR	635	198796	NR	765	12765	NR	895	4688	NR
380	5499	NR	510	117784	NR	640	189406	NR	770	11372	NR	900	4680	NR
385	5081	NR	515	125000	NR	645	180677	NR	775	9965	NR	905	4599	NR
390	4739	NR	520	131786	NR	650	168402	NR	780	9154	NR	910	4495	NR
395	4255	NR	525	136796	NR	655	157693	NR	785	8847	NR	915	3983	NR
400	3864	NR	530	142357	NR	660	145357	NR	790	7937	NR	920	4675	NR
405	3583	NR	535	147243	NR	665	132743	NR	795	6956	NR	925	4952	NR
410	3994	NR	540	152273	NR	670	120757	NR	800	6970	NR	930	6097	NR
415	5055	NR	545	157222	NR	675	108421	NR	805	6299	NR	935	5657	NR
420	7131	NR	550	161271	NR	680	97325	NR	810	6023	NR	940	4574	NR
425	11311	NR	555	167038	NR	685	86839	NR	815	6343	NR	945	5252	NR
430	17754	NR	560	173115	NR	690	76248	NR	820	6462	NR	950	5635	NR
435	28634	NR	565	178502	NR	695	67406	NR	825	5476	NR	955	4501	NR
440	46392	NR	570	184331	NR	700	60039	NR	830	5786	NR	960	2938	NR
445	78344	NR	575	189666	NR	705	53650	NR	835	5884	NR	965	5544	NR
450	131219	NR	580	196488	NR	710	47273	NR	840	4862	NR	970	5050	NR
455	170311	NR	585	202769	NR	715	41664	NR	845	5651	NR	975	5575	NR
460	154269	NR	590	207213	NR	720	37083	NR	850	5178	NR	980	2973	NR
465	126622	NR	595	213472	NR	725	32494	NR	855	5510	NR	985	4912	NR
470	109065	NR	600	218473	NR	730	28665	NR	860	5438	NR	990	5454	NR
475	91762	NR	605	220737	NR	735	25540	NR	865	5848	NR	995	6068	NR
480	78213	NR	610	221090	NR	740	22878	NR	870	4969	NR	1000	9406	NR
485	77035	NR	615	220059	NR	745	20304	NR	875	5438	NR			

REPORT NUMBER: SP1-2307-100-7

Melanopic Flux vs. Wavelength



Melanopic Lumens: 7912.5

M/P: 0.65


λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)
360	5498	NR	490	81900	NR	620	217907	NR	750	17550	NR	880	6189	NR
365	4903	NR	495	90120	NR	625	213734	NR	755	15662	NR	885	6187	NR
370	4767	NR	500	98453	NR	630	206250	NR	760	13792	NR	890	3830	NR
375	5225	NR	505	109244	NR	635	198796	NR	765	12765	NR	895	4688	NR
380	5499	NR	510	117784	NR	640	189406	NR	770	11372	NR	900	4680	NR
385	5081	NR	515	125000	NR	645	180677	NR	775	9965	NR	905	4599	NR
390	4739	NR	520	131786	NR	650	168402	NR	780	9154	NR	910	4495	NR
395	4255	NR	525	136796	NR	655	157693	NR	785	8847	NR	915	3983	NR
400	3864	NR	530	142357	NR	660	145357	NR	790	7937	NR	920	4675	NR
405	3583	NR	535	147243	NR	665	132743	NR	795	6956	NR	925	4952	NR
410	3994	NR	540	152273	NR	670	120757	NR	800	6970	NR	930	6097	NR
415	5055	NR	545	157222	NR	675	108421	NR	805	6299	NR	935	5657	NR
420	7131	NR	550	161271	NR	680	97325	NR	810	6023	NR	940	4574	NR
425	11311	NR	555	167038	NR	685	86839	NR	815	6343	NR	945	5252	NR
430	17754	NR	560	173115	NR	690	76248	NR	820	6462	NR	950	5635	NR
435	28634	NR	565	178502	NR	695	67406	NR	825	5476	NR	955	4501	NR
440	46392	NR	570	184331	NR	700	60039	NR	830	5786	NR	960	2938	NR
445	78344	NR	575	189666	NR	705	53650	NR	835	5884	NR	965	5544	NR
450	131219	NR	580	196488	NR	710	47273	NR	840	4862	NR	970	5050	NR
455	170311	NR	585	202769	NR	715	41664	NR	845	5651	NR	975	5575	NR
460	154269	NR	590	207213	NR	720	37083	NR	850	5178	NR	980	2973	NR
465	126622	NR	595	213472	NR	725	32494	NR	855	5510	NR	985	4912	NR
470	109065	NR	600	218473	NR	730	28665	NR	860	5438	NR	990	5454	NR
475	91762	NR	605	220737	NR	735	25540	NR	865	5848	NR	995	6068	NR
480	78213	NR	610	221090	NR	740	22878	NR	870	4969	NR	1000	9406	NR
485	77035	NR	615	220059	NR	745	20304	NR	875	5438	NR			

REPORT NUMBER: SP1-2307-100-7


TM-30-18

Summary

$R_f = 88.9$
 $R_g = 96.3$
 CIE $R_a = 90.9$
 $R_9 = 50.7$



Color Vector Graphics



REPORT NUMBER: SP1-2307-100-7

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 95	CES51 = 92	CES76 = 89
CES02 = 62	CES27 = 89	CES52 = 95	CES77 = 88
CES03 = 31	CES28 = 97	CES53 = 92	CES78 = 87
CES04 = 70	CES29 = 93	CES54 = 89	CES79 = 93
CES05 = 49	CES30 = 82	CES55 = 86	CES80 = 92
CES06 = 51	CES31 = 95	CES56 = 87	CES81 = 82
CES07 = 42	CES32 = 94	CES57 = 85	CES82 = 97
CES08 = 41	CES33 = 91	CES58 = 85	CES83 = 95
CES09 = 29	CES34 = 96	CES59 = 94	CES84 = 94
CES10 = 75	CES35 = 97	CES60 = 89	CES85 = 80
CES11 = 58	CES36 = 77	CES61 = 89	CES86 = 82
CES12 = 64	CES37 = 97	CES62 = 79	CES87 = 90
CES13 = 43	CES38 = 78	CES63 = 88	CES88 = 93
CES14 = 74	CES39 = 97	CES64 = 83	CES89 = 85
CES15 = 71	CES40 = 98	CES65 = 84	CES90 = 92
CES16 = 47	CES41 = 92	CES66 = 80	CES91 = 72
CES17 = 50	CES42 = 99	CES67 = 80	CES92 = 75
CES18 = 56	CES43 = 95	CES68 = 85	CES93 = 85
CES19 = 71	CES44 = 99	CES69 = 86	CES94 = 77
CES20 = 66	CES45 = 96	CES70 = 84	CES95 = 81
CES21 = 86	CES46 = 94	CES71 = 77	CES96 = 91
CES22 = 78	CES47 = 91	CES72 = 93	CES97 = 93
CES23 = 91	CES48 = 83	CES73 = 81	CES98 = 91
CES24 = 90	CES49 = 95	CES74 = 89	CES99 = 87
CES25 = 71	CES50 = 93	CES75 = 81	



REPORT NUMBER: SP1-2307-100-7

TM-30-18

Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-2307-100-7

TM-30-18

Measure Comparisons



(END OF REPORT)