

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: METALUX

Report Number: P859893

Luminaire Tested: **SPHB-15HE-N-L835-CD**

Issue Date: 7/11/2024



Test Information

Test Method: LM-79-08
Report Number: P859893
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2404-343-7)
Test Lab: INNOVATION CENTER
Issue Date: 7/11/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: METALUX
Catalog Number: SPHB-15HE-N-L835-CD
Description: 15000 Lumen High Efficacy Select Pro High Bay with Narrow Lens and, 3500K 80CRI LEDs
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 14297.0 lumens
Efficiency: N/A
Efficacy: 161.9 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.54 / 0.94
Luminous Opening: Rectangular (W 1' x L: 1.38' x H: 0')
CIE Type: Direct

Input Watts (W): 88.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P859893

CATALOG NUMBER: SPHB-15HE-N-L835-CD

Luminous Intensity Polar Plot





TEST NUMBER: P859893

CATALOG NUMBER: SPHB-15HE-N-L835-CD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	110	106	102	98	107	103	100	97	99	96	94	95	93	91	92	90	88	86		
2	101	94	88	83	99	92	86	82	88	84	80	85	81	78	82	79	76	74		
3	93	84	76	71	91	82	75	70	79	73	69	77	72	68	74	70	66	64		
4	86	75	67	61	84	74	67	61	72	65	60	69	64	59	67	62	58	56		
5	80	68	60	54	78	67	59	54	65	58	53	63	57	53	61	56	52	50		
6	74	62	54	48	73	61	54	48	60	53	47	58	52	47	56	51	47	45		
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	46	42	40		
8	65	53	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37		
9	61	49	41	36	60	48	41	36	47	40	36	46	40	35	45	39	35	34		
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	76089	76089	76089
5°	76001	71593	68205
10°	75741	60346	52023
15°	75111	50094	43840
20°	73597	43667	43036
25°	71232	42250	44044
30°	67866	41573	40083
35°	63013	39505	33215
40°	57379	35465	27428
45°	51795	30773	24078
50°	45708	26758	22547
55°	40560	24134	21702
60°	34760	22317	21260
65°	30087	20974	21153
70°	25747	20176	21127
75°	21614	19592	20939
80°	16489	18933	20505
85°	10793	16798	15796



TEST NUMBER: P859893

CATALOG NUMBER: SPHB-15HE-N-L835-CD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	831.7	5.8
10°-20°	1909.7	13.4
20°-30°	2580.9	18.1
30°-40°	2716.2	19.0
40°-50°	2304.8	16.1
50°-60°	1785.4	12.5
60°-70°	1243.5	8.7
70°-80°	712.0	5.0
80°-90°	207.2	1.4
90°-100°	5.5	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5322.3	37.2
0°-40°	8038.5	56.2
0°-60°	12128.7	84.8
0°-90°	14291.4	100.0
90°-120°	5.5	0.0
90°-150°	5.5	0.0
90°-180°	6.0	0.0
0°-180°	14297.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	9755	9755	9755	9755	9755	
5°	9707	9529	9144	8793	8711	922
15°	9302	7895	6204	5584	5429	2617
25°	8277	5847	4909	5051	5118	3800
35°	6618	4497	4149	3747	3488	4125
45°	4696	3377	2790	2292	2183	3616
55°	2983	2274	1775	1613	1596	2667
65°	1630	1334	1136	1136	1146	1628
75°	717	638	650	691	695	765
85°	121	156	188	176	176	153
90°	1	14	28	35	36	7
95°	1	2	4	4	4	0
105°	0	0	0	0	0	0
115°	0	0	0	0	0	0
125°	0	0	0	0	0	0
135°	0	0	0	0	0	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	



TEST NUMBER: P859893

CATALOG NUMBER: SPHB-15HE-N-L835-CD

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	9755.1	9755.1	9755.1	9755.1	9755.1
2.5°	9726.8	9694.8	9616.6	9565.9	9526.5
5°	9706.7	9528.7	9143.7	8792.9	8711.0
7.5°	9646.4	9255.4	8432.5	7783.8	7620.0
10°	9563.0	8862.9	7619.2	6806.7	6568.4
12.5°	9452.0	8443.6	6840.3	6074.7	5957.8
15°	9301.6	7894.8	6203.5	5583.9	5429.0
17.5°	9106.4	7327.3	5615.9	5257.7	5214.5
20°	8866.6	6806.7	5260.7	5138.6	5184.7
22.5°	8597.1	6301.1	5054.4	5105.8	5192.2
25°	8276.8	5846.8	4909.2	5051.4	5117.7
27.5°	7917.1	5436.5	4775.9	4906.2	4906.2
30°	7535.1	5094.6	4615.8	4603.9	4450.4
32.5°	7089.0	4804.2	4406.5	4170.4	3942.5
35°	6617.6	4496.6	4148.8	3747.4	3488.3
37.5°	6123.1	4210.6	3822.6	3293.2	3051.9
40°	5635.3	3928.4	3483.1	2885.0	2693.7
42.5°	5149.7	3640.9	3129.3	2554.4	2403.2
45°	4695.5	3376.6	2789.7	2292.2	2182.8
47.5°	4233.7	3095.8	2476.2	2081.5	2005.5
50°	3766.8	2811.3	2205.1	1913.9	1858.1
52.5°	3373.6	2546.2	1975.0	1755.3	1721.8
55°	2982.6	2274.4	1774.7	1613.1	1595.9
57.5°	2594.6	2021.2	1591.5	1482.7	1479.0
60°	2228.2	1784.3	1430.6	1371.0	1362.8
62.5°	1916.2	1549.0	1277.9	1249.6	1253.4
65°	1630.2	1334.5	1136.4	1136.4	1146.1
67.5°	1365.1	1137.2	1006.9	1024.0	1037.4
70°	1129.0	958.5	884.7	914.5	926.4
72.5°	905.6	792.4	767.8	800.6	810.3
75°	717.2	637.5	650.1	691.1	694.8
77.5°	531.7	501.9	534.7	579.4	587.6
80°	367.1	370.1	421.5	452.8	456.5
82.5°	236.8	258.4	315.8	332.1	326.2
85°	120.6	156.4	187.7	176.5	176.5
87.5°	46.2	67.8	79.7	93.8	99.0
90°	0.7	14.1	27.6	35.0	36.5
92.5°	0.7	3.7	6.0	6.7	6.0
95°	0.7	2.2	4.5	4.5	3.7
97.5°	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P859893

CATALOG NUMBER: SPHB-15HE-N-L835-CD

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180° - - 45°-225° - - - 90°-270°







107.5°	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

METALUX

Report Number: SP1-2404-343-4

Test Date: 05/20/2024

Luminaire Tested: SPHB-24SE-M-UNV-L835-CD

Data in this report applies to families of products SPHB-24SE-M-UNV-L835-CD.

Test Information


Test Method: LM-79-2019
 Report Number: SP1-2404-343-4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 05/21/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: METALUX
 Catalog Number: **SPHB-24SE-M-UNV-L835-CD**
 Description: 18IN SPHB WITH MEDIUM LENS, 3500K/80CRI, 24K LUMENS, SE

Spectral Parameters

CCT (K): 3425
 CIE u': 0.2370
 CIE v': 0.5143
 Duv: 0.0012
 CIE x: 0.4108
 CIE y: 0.3961
 CIE z: 0.1931
 Peak Wavelength (nm): 598
 Dominant Wavelength (nm): 580
 Purity: 42.4
 Rf: 84.3
 Rg: 94.4

CRI (Ra): 82.9
 R1: 81.2
 R2: 90.5
 R3: 96.5
 R4: 80.4
 R5: 80.9
 R6: 87.3
 R7: 84.6
 R8: 61.9



R9: 8.8
 R10: 77.5
 R11: 79.1
 R12: 64.2
 R13: 83.5
 R14: 98.5



REPORT NUMBER: SP1-2404-343-4

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	2/12/2024	8/12/2024
Power Meter	XITRON 2801 IN0071	10/23/2023	10/23/2024
AC Power Source	CHROMA 61603 IN0063	10/24/2023	10/24/2024
DC Power Source	AGILENT E3634A IN0208	10/24/2023	10/24/2024
Sphere Thermometer	ONSET IN0085	10/24/2023	10/24/2024
Room Thermometer	ONSET IN0046	10/24/2023	10/24/2024


REPORT NUMBER: SP1-2404-343-4



Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2404-343-4

Photopic Flux vs. Wavelength




#####

λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)
360	6937	NR	490	86536	NR	620	285855	NR	750	14885	NR	880	8993	NR
365	5820	NR	495	100007	NR	625	270301	NR	755	13434	NR	885	6908	NR
370	6342	NR	500	117528	NR	630	253548	NR	760	12497	NR	890	6405	NR
375	7421	NR	505	135586	NR	635	235289	NR	765	11021	NR	895	6392	NR
380	6619	NR	510	153068	NR	640	217346	NR	770	9938	NR	900	5762	NR
385	5813	NR	515	167170	NR	645	198000	NR	775	9105	NR	905	5445	NR
390	5630	NR	520	178364	NR	650	180267	NR	780	8315	NR	910	6424	NR
395	4917	NR	525	186887	NR	655	162796	NR	785	8364	NR	915	5977	NR
400	4279	NR	530	194310	NR	660	143827	NR	790	7202	NR	920	5589	NR
405	4043	NR	535	201832	NR	665	127951	NR	795	7271	NR	925	6728	NR
410	4666	NR	540	208553	NR	670	112526	NR	800	6583	NR	930	7328	NR
415	6309	NR	545	216697	NR	675	97790	NR	805	6730	NR	935	5077	NR
420	9564	NR	550	224567	NR	680	85489	NR	810	7628	NR	940	5558	NR
425	16500	NR	555	235296	NR	685	74086	NR	815	6335	NR	945	2171	NR
430	28210	NR	560	246750	NR	690	65039	NR	820	5679	NR	950	10555	NR
435	47088	NR	565	258189	NR	695	56035	NR	825	6974	NR	955	8787	NR
440	76402	NR	570	270186	NR	700	49223	NR	830	7136	NR	960	6936	NR
445	124288	NR	575	282577	NR	705	43027	NR	835	5971	NR	965	8547	NR
450	197266	NR	580	295795	NR	710	38080	NR	840	6371	NR	970	7502	NR
455	240978	NR	585	304888	NR	715	33706	NR	845	6027	NR	975	8793	NR
460	199802	NR	590	313177	NR	720	29961	NR	850	6816	NR	980	5517	NR
465	147559	NR	595	317388	NR	725	26440	NR	855	6168	NR	985	4652	NR
470	121976	NR	600	317783	NR	730	23027	NR	860	6333	NR	990	7259	NR
475	97268	NR	605	315536	NR	735	20496	NR	865	6493	NR	995	11735	NR
480	80092	NR	610	309123	NR	740	18168	NR	870	7357	NR	1000	8351	NR
485	79203	NR	615	300672	NR	745	15812	NR	875	7188	NR			

REPORT NUMBER: SP1-2404-343-4

Scotopic Flux vs. Wavelength




Scotopic Lumens: 25661.8

S/P: 1.51

λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)
360	6937	NR	490	86536	NR	620	285855	NR	750	14885	NR	880	8993	NR
365	5820	NR	495	100007	NR	625	270301	NR	755	13434	NR	885	6908	NR
370	6342	NR	500	117528	NR	630	253548	NR	760	12497	NR	890	6405	NR
375	7421	NR	505	135586	NR	635	235289	NR	765	11021	NR	895	6392	NR
380	6619	NR	510	153068	NR	640	217346	NR	770	9938	NR	900	5762	NR
385	5813	NR	515	167170	NR	645	198000	NR	775	9105	NR	905	5445	NR
390	5630	NR	520	178364	NR	650	180267	NR	780	8315	NR	910	6424	NR
395	4917	NR	525	186887	NR	655	162796	NR	785	8364	NR	915	5977	NR
400	4279	NR	530	194310	NR	660	143827	NR	790	7202	NR	920	5589	NR
405	4043	NR	535	201832	NR	665	127951	NR	795	7271	NR	925	6728	NR
410	4666	NR	540	208553	NR	670	112526	NR	800	6583	NR	930	7328	NR
415	6309	NR	545	216697	NR	675	97790	NR	805	6730	NR	935	5077	NR
420	9564	NR	550	224567	NR	680	85489	NR	810	7628	NR	940	5558	NR
425	16500	NR	555	235296	NR	685	74086	NR	815	6335	NR	945	2171	NR
430	28210	NR	560	246750	NR	690	65039	NR	820	5679	NR	950	10555	NR
435	47088	NR	565	258189	NR	695	56035	NR	825	6974	NR	955	8787	NR
440	76402	NR	570	270186	NR	700	49223	NR	830	7136	NR	960	6936	NR
445	124288	NR	575	282577	NR	705	43027	NR	835	5971	NR	965	8547	NR
450	197266	NR	580	295795	NR	710	38080	NR	840	6371	NR	970	7502	NR
455	240978	NR	585	304888	NR	715	33706	NR	845	6027	NR	975	8793	NR
460	199802	NR	590	313177	NR	720	29961	NR	850	6816	NR	980	5517	NR
465	147559	NR	595	317388	NR	725	26440	NR	855	6168	NR	985	4652	NR
470	121976	NR	600	317783	NR	730	23027	NR	860	6333	NR	990	7259	NR
475	97268	NR	605	315536	NR	735	20496	NR	865	6493	NR	995	11735	NR
480	80092	NR	610	309123	NR	740	18168	NR	870	7357	NR	1000	8351	NR
485	79203	NR	615	300672	NR	745	15812	NR	875	7188	NR			

REPORT NUMBER: SP1-2404-343-4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 10080.3 M/P: 0.59


λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)
360	6937	NR	490	86536	NR	620	285855	NR	750	14885	NR	880	8993	NR
365	5820	NR	495	100007	NR	625	270301	NR	755	13434	NR	885	6908	NR
370	6342	NR	500	117528	NR	630	253548	NR	760	12497	NR	890	6405	NR
375	7421	NR	505	135586	NR	635	235289	NR	765	11021	NR	895	6392	NR
380	6619	NR	510	153068	NR	640	217346	NR	770	9938	NR	900	5762	NR
385	5813	NR	515	167170	NR	645	198000	NR	775	9105	NR	905	5445	NR
390	5630	NR	520	178364	NR	650	180267	NR	780	8315	NR	910	6424	NR
395	4917	NR	525	186887	NR	655	162796	NR	785	8364	NR	915	5977	NR
400	4279	NR	530	194310	NR	660	143827	NR	790	7202	NR	920	5589	NR
405	4043	NR	535	201832	NR	665	127951	NR	795	7271	NR	925	6728	NR
410	4666	NR	540	208553	NR	670	112526	NR	800	6583	NR	930	7328	NR
415	6309	NR	545	216697	NR	675	97790	NR	805	6730	NR	935	5077	NR
420	9564	NR	550	224567	NR	680	85489	NR	810	7628	NR	940	5558	NR
425	16500	NR	555	235296	NR	685	74086	NR	815	6335	NR	945	2171	NR
430	28210	NR	560	246750	NR	690	65039	NR	820	5679	NR	950	10555	NR
435	47088	NR	565	258189	NR	695	56035	NR	825	6974	NR	955	8787	NR
440	76402	NR	570	270186	NR	700	49223	NR	830	7136	NR	960	6936	NR
445	124288	NR	575	282577	NR	705	43027	NR	835	5971	NR	965	8547	NR
450	197266	NR	580	295795	NR	710	38080	NR	840	6371	NR	970	7502	NR
455	240978	NR	585	304888	NR	715	33706	NR	845	6027	NR	975	8793	NR
460	199802	NR	590	313177	NR	720	29961	NR	850	6816	NR	980	5517	NR
465	147559	NR	595	317388	NR	725	26440	NR	855	6168	NR	985	4652	NR
470	121976	NR	600	317783	NR	730	23027	NR	860	6333	NR	990	7259	NR
475	97268	NR	605	315536	NR	735	20496	NR	865	6493	NR	995	11735	NR
480	80092	NR	610	309123	NR	740	18168	NR	870	7357	NR	1000	8351	NR
485	79203	NR	615	300672	NR	745	15812	NR	875	7188	NR			

REPORT NUMBER: SP1-2404-343-4





TM-30-18

Summary

$R_f = 84.3$
 $R_g = 94.4$
 CIE $R_a = 82.9$
 $R_9 = 8.8$



Color Vector Graphics




REPORT NUMBER: SP1-2404-343-4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)




CES01 = 86	CES26 = 86	CES51 = 92	CES76 = 79
CES02 = 62	CES27 = 92	CES52 = 93	CES77 = 85
CES03 = 31	CES28 = 93	CES53 = 88	CES78 = 79
CES04 = 70	CES29 = 91	CES54 = 88	CES79 = 92
CES05 = 49	CES30 = 90	CES55 = 86	CES80 = 90
CES06 = 51	CES31 = 93	CES56 = 84	CES81 = 77
CES07 = 41	CES32 = 85	CES57 = 82	CES82 = 96
CES08 = 40	CES33 = 97	CES58 = 83	CES83 = 96
CES09 = 29	CES34 = 90	CES59 = 91	CES84 = 91
CES10 = 75	CES35 = 94	CES60 = 89	CES85 = 77
CES11 = 58	CES36 = 80	CES61 = 86	CES86 = 72
CES12 = 64	CES37 = 94	CES62 = 81	CES87 = 85
CES13 = 43	CES38 = 85	CES63 = 84	CES88 = 89
CES14 = 74	CES39 = 98	CES64 = 77	CES89 = 77
CES15 = 71	CES40 = 97	CES65 = 76	CES90 = 90
CES16 = 47	CES41 = 95	CES66 = 73	CES91 = 72
CES17 = 50	CES42 = 96	CES67 = 72	CES92 = 65
CES18 = 56	CES43 = 92	CES68 = 78	CES93 = 78
CES19 = 72	CES44 = 99	CES69 = 83	CES94 = 64
CES20 = 66	CES45 = 94	CES70 = 76	CES95 = 74
CES21 = 86	CES46 = 91	CES71 = 70	CES96 = 84
CES22 = 78	CES47 = 95	CES72 = 90	CES97 = 90
CES23 = 92	CES48 = 83	CES73 = 71	CES98 = 86
CES24 = 91	CES49 = 91	CES74 = 90	CES99 = 77
CES25 = 72	CES50 = 93	CES75 = 74	



REPORT NUMBER: SP1-2404-343-4

TM-30-18



Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-2404-343-4

TM-30-18

Measure Comparisons



(END OF REPORT)