

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: METALUX

Report Number: P860199

Luminaire Tested: **SPHB-48SE-W-L835-CD**

Issue Date: 7/11/2024

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P860199
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2404-343-6)
Test Lab: INNOVATION CENTER
Issue Date: 7/11/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: METALUX
Catalog Number: SPHB-48SE-W-L835-CD
Description: 48000 Lumen Standard Efficacy Select Pro High Bay with Wide Lens
and, 3500K 80CRI LEDs
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 47623.0 lumens
Efficiency: N/A
Efficacy: 156.2 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.5 / 1.51
Luminous Opening: Rectangular (W 1' x L: 3.38' x H: 0')
CIE Type: Direct

Input Watts (W): 304.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P860199

CATALOG NUMBER: SPHB-48SE-W-L835-CD

Luminous Intensity Polar Plot





TEST NUMBER: P860199

CATALOG NUMBER: SPHB-48SE-W-L835-CD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	110	105	101	98	107	103	99	96	99	96	93	95	92	90	91	89	87	85		
2	100	92	86	81	98	91	85	80	87	82	78	84	80	76	81	77	74	72		
3	92	82	74	68	89	80	73	67	77	71	66	74	69	65	72	67	64	62		
4	84	73	64	58	82	71	63	57	69	62	57	66	61	56	64	59	55	53		
5	77	65	56	50	75	64	56	50	62	55	49	60	54	49	58	52	48	46		
6	72	59	50	44	70	58	49	43	56	49	43	54	48	43	53	47	42	40		
7	66	53	45	39	65	52	44	38	51	43	38	49	43	38	48	42	38	36		
8	62	48	40	34	60	48	40	34	46	39	34	45	39	34	44	38	34	32		
9	58	44	36	31	56	44	36	31	43	36	31	42	35	30	41	35	30	29		
10	54	41	33	28	53	40	33	28	39	33	28	39	32	28	38	32	28	26		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	48200	48200	48200
5°	48148	49056	50219
10°	47767	51645	55560
15°	47020	55490	61199
20°	46003	59903	64256
25°	44675	63135	65099
30°	43221	65110	64922
35°	41599	65764	60579
40°	39923	62794	57218
45°	38412	56919	54897
50°	36915	51755	48667
55°	35227	47818	39603
60°	33485	42631	32616
65°	31178	36632	28280
70°	28365	31276	25579
75°	24360	26248	23451
80°	19040	22513	21750
85°	12876	19106	17930



TEST NUMBER: P860199

CATALOG NUMBER: SPHB-48SE-W-L835-CD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1486.0	3.1
10°-20°	4712.0	9.9
20°-30°	7711.5	16.2
30°-40°	9407.5	19.8
40°-50°	9317.1	19.6
50°-60°	7450.6	15.6
60°-70°	4648.0	9.8
70°-80°	2277.3	4.8
80°-90°	597.3	1.3
90°-100°	15.7	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	13909.5	29.2
0°-40°	23317.0	49.0
0°-60°	40084.8	84.2
0°-90°	47607.3	100.0
90°-120°	15.7	0.0
90°-150°	15.7	0.0
90°-180°	16.0	0.0
0°-180°	47623.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	15135	15135	15135	15135	15135	
5°	15061	15128	15346	15613	15709	###
15°	14262	15092	16831	18170	18562	4021
25°	12714	14866	17968	18489	18526	5851
35°	10700	14298	16916	16012	15582	6693
45°	8529	13250	12638	12214	12189	6588
55°	6345	10174	8612	7781	7133	5685
65°	4138	5708	4861	4032	3753	4103
75°	1980	2425	2133	1953	1906	2102
85°	352	500	523	496	491	436
90°	2	51	93	118	121	20
95°	2	8	8	6	4	1
105°	0	0	0	0	0	0
115°	0	0	0	0	0	0
125°	0	0	0	0	0	0
135°	0	0	0	0	0	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	



TEST NUMBER: P860199

CATALOG NUMBER: SPHB-48SE-W-L835-CD

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	15135.3	15135.3	15135.3	15135.3	15135.3
2.5°	15120.1	15114.5	15169.4	15269.8	15315.3
5°	15061.4	15127.7	15345.6	15612.7	15709.3
7.5°	14955.3	15133.4	15614.6	16105.3	16313.7
10°	14771.6	15137.2	15970.8	16836.6	17181.4
12.5°	14582.1	15123.9	16366.7	17592.5	17969.5
15°	14261.9	15091.7	16830.9	18170.3	18562.5
17.5°	13964.5	15053.8	17278.0	18661.0	18958.4
20°	13574.2	14998.9	17675.8	18810.7	18960.3
22.5°	13165.0	14955.3	17895.6	18710.3	18755.7
25°	12714.1	14866.3	17967.6	18488.6	18526.5
27.5°	12232.9	14786.7	17899.4	18213.9	18246.1
30°	11753.6	14642.7	17706.2	17785.7	17655.0
32.5°	11251.5	14498.7	17393.6	17035.5	16730.5
35°	10700.2	14297.9	16916.1	16012.5	15582.4
37.5°	10156.5	14104.7	16171.6	14868.2	14544.2
40°	9603.3	13866.0	15105.0	13799.7	13763.7
42.5°	9080.4	13608.3	13898.2	12968.0	13089.2
45°	8529.1	13250.3	12638.3	12214.0	12189.3
47.5°	8006.2	12755.8	11492.1	11380.4	11128.4
50°	7451.1	12073.8	10446.4	10340.3	9823.1
52.5°	6907.4	11204.2	9512.4	9114.5	8360.5
55°	6344.7	10173.6	8612.5	7780.8	7132.9
57.5°	5821.9	9040.6	7697.4	6619.4	6037.8
60°	5257.3	7892.6	6693.3	5600.2	5120.9
62.5°	4704.1	6761.5	5784.0	4732.5	4414.2
65°	4137.6	5708.2	4861.3	4031.5	3753.0
67.5°	3595.8	4796.9	4063.7	3398.8	3213.1
70°	3046.4	3891.3	3359.0	2855.0	2747.1
72.5°	2479.9	3108.9	2716.7	2409.8	2328.4
75°	1979.8	2425.0	2133.2	1953.2	1905.9
77.5°	1473.9	1803.6	1667.2	1561.1	1547.8
80°	1038.2	1301.5	1227.6	1206.8	1186.0
82.5°	663.1	850.6	873.4	860.1	845.0
85°	352.4	500.2	522.9	496.4	490.7
87.5°	142.1	217.9	234.9	259.5	267.1
90°	1.9	51.2	92.8	117.5	121.2
92.5°	1.9	11.4	13.3	13.3	11.4
95°	1.9	7.6	7.6	5.7	3.8
97.5°	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P860199

CATALOG NUMBER: SPHB-48SE-W-L835-CD

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180° - - 45°-225° - - - 90°-270°







107.5°	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

METALUX

Report Number: SP1-2404-343-4

Test Date: 05/20/2024

Luminaire Tested: SPHB-24SE-M-UNV-L835-CD

Data in this report applies to families of products SPHB-24SE-M-UNV-L835-CD.

Test Information


Test Method: LM-79-2019
 Report Number: SP1-2404-343-4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 05/21/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: METALUX
 Catalog Number: **SPHB-24SE-M-UNV-L835-CD**
 Description: 18IN SPHB WITH MEDIUM LENS, 3500K/80CRI, 24K LUMENS, SE

Spectral Parameters

CCT (K): 3425
 CIE u': 0.2370
 CIE v': 0.5143
 Duv: 0.0012
 CIE x: 0.4108
 CIE y: 0.3961
 CIE z: 0.1931
 Peak Wavelength (nm): 598
 Dominant Wavelength (nm): 580
 Purity: 42.4
 R_f: 84.3
 R_g: 94.4

CRI (Ra): 82.9
 R1: 81.2
 R2: 90.5
 R3: 96.5
 R4: 80.4
 R5: 80.9
 R6: 87.3
 R7: 84.6
 R8: 61.9

R9: 8.8
 R10: 77.5
 R11: 79.1
 R12: 64.2
 R13: 83.5
 R14: 98.5



Test Conditions


Stabilization Time: 27M
 Operation Time: 12H
 Room Temperature (°C) / RH%: 25.0/41%
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2404-343-4


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	2/12/2024	8/12/2024
Power Meter	XITRON 2801 IN0071	10/23/2023	10/23/2024
AC Power Source	CHROMA 61603 IN0063	10/24/2023	10/24/2024
DC Power Source	AGILENT E3634A IN0208	10/24/2023	10/24/2024
Sphere Thermometer	ONSET IN0085	10/24/2023	10/24/2024
Room Thermometer	ONSET IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2404-343-4

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2404-343-4

Photopic Flux vs. Wavelength




#####

λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)
360	6937	NR	490	86536	NR	620	285855	NR	750	14885	NR	880	8993	NR
365	5820	NR	495	100007	NR	625	270301	NR	755	13434	NR	885	6908	NR
370	6342	NR	500	117528	NR	630	253548	NR	760	12497	NR	890	6405	NR
375	7421	NR	505	135586	NR	635	235289	NR	765	11021	NR	895	6392	NR
380	6619	NR	510	153068	NR	640	217346	NR	770	9938	NR	900	5762	NR
385	5813	NR	515	167170	NR	645	198000	NR	775	9105	NR	905	5445	NR
390	5630	NR	520	178364	NR	650	180267	NR	780	8315	NR	910	6424	NR
395	4917	NR	525	186887	NR	655	162796	NR	785	8364	NR	915	5977	NR
400	4279	NR	530	194310	NR	660	143827	NR	790	7202	NR	920	5589	NR
405	4043	NR	535	201832	NR	665	127951	NR	795	7271	NR	925	6728	NR
410	4666	NR	540	208553	NR	670	112526	NR	800	6583	NR	930	7328	NR
415	6309	NR	545	216697	NR	675	97790	NR	805	6730	NR	935	5077	NR
420	9564	NR	550	224567	NR	680	85489	NR	810	7628	NR	940	5558	NR
425	16500	NR	555	235296	NR	685	74086	NR	815	6335	NR	945	2171	NR
430	28210	NR	560	246750	NR	690	65039	NR	820	5679	NR	950	10555	NR
435	47088	NR	565	258189	NR	695	56035	NR	825	6974	NR	955	8787	NR
440	76402	NR	570	270186	NR	700	49223	NR	830	7136	NR	960	6936	NR
445	124288	NR	575	282577	NR	705	43027	NR	835	5971	NR	965	8547	NR
450	197266	NR	580	295795	NR	710	38080	NR	840	6371	NR	970	7502	NR
455	240978	NR	585	304888	NR	715	33706	NR	845	6027	NR	975	8793	NR
460	199802	NR	590	313177	NR	720	29961	NR	850	6816	NR	980	5517	NR
465	147559	NR	595	317388	NR	725	26440	NR	855	6168	NR	985	4652	NR
470	121976	NR	600	317783	NR	730	23027	NR	860	6333	NR	990	7259	NR
475	97268	NR	605	315536	NR	735	20496	NR	865	6493	NR	995	11735	NR
480	80092	NR	610	309123	NR	740	18168	NR	870	7357	NR	1000	8351	NR
485	79203	NR	615	300672	NR	745	15812	NR	875	7188	NR			

REPORT NUMBER: SP1-2404-343-4

Scotopic Flux vs. Wavelength




Scotopic Lumens: 25661.8

S/P: 1.51

λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)
360	6937	NR	490	86536	NR	620	285855	NR	750	14885	NR	880	8993	NR
365	5820	NR	495	100007	NR	625	270301	NR	755	13434	NR	885	6908	NR
370	6342	NR	500	117528	NR	630	253548	NR	760	12497	NR	890	6405	NR
375	7421	NR	505	135586	NR	635	235289	NR	765	11021	NR	895	6392	NR
380	6619	NR	510	153068	NR	640	217346	NR	770	9938	NR	900	5762	NR
385	5813	NR	515	167170	NR	645	198000	NR	775	9105	NR	905	5445	NR
390	5630	NR	520	178364	NR	650	180267	NR	780	8315	NR	910	6424	NR
395	4917	NR	525	186887	NR	655	162796	NR	785	8364	NR	915	5977	NR
400	4279	NR	530	194310	NR	660	143827	NR	790	7202	NR	920	5589	NR
405	4043	NR	535	201832	NR	665	127951	NR	795	7271	NR	925	6728	NR
410	4666	NR	540	208553	NR	670	112526	NR	800	6583	NR	930	7328	NR
415	6309	NR	545	216697	NR	675	97790	NR	805	6730	NR	935	5077	NR
420	9564	NR	550	224567	NR	680	85489	NR	810	7628	NR	940	5558	NR
425	16500	NR	555	235296	NR	685	74086	NR	815	6335	NR	945	2171	NR
430	28210	NR	560	246750	NR	690	65039	NR	820	5679	NR	950	10555	NR
435	47088	NR	565	258189	NR	695	56035	NR	825	6974	NR	955	8787	NR
440	76402	NR	570	270186	NR	700	49223	NR	830	7136	NR	960	6936	NR
445	124288	NR	575	282577	NR	705	43027	NR	835	5971	NR	965	8547	NR
450	197266	NR	580	295795	NR	710	38080	NR	840	6371	NR	970	7502	NR
455	240978	NR	585	304888	NR	715	33706	NR	845	6027	NR	975	8793	NR
460	199802	NR	590	313177	NR	720	29961	NR	850	6816	NR	980	5517	NR
465	147559	NR	595	317388	NR	725	26440	NR	855	6168	NR	985	4652	NR
470	121976	NR	600	317783	NR	730	23027	NR	860	6333	NR	990	7259	NR
475	97268	NR	605	315536	NR	735	20496	NR	865	6493	NR	995	11735	NR
480	80092	NR	610	309123	NR	740	18168	NR	870	7357	NR	1000	8351	NR
485	79203	NR	615	300672	NR	745	15812	NR	875	7188	NR			

REPORT NUMBER: SP1-2404-343-4

Melanopic Flux vs. Wavelength



Melanopic Lumens: 10080.3 M/P: 0.59


λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)	λ (nm)	Power (μW/nm)	Lumens (φ/nm)
360	6937	NR	490	86536	NR	620	285855	NR	750	14885	NR	880	8993	NR
365	5820	NR	495	100007	NR	625	270301	NR	755	13434	NR	885	6908	NR
370	6342	NR	500	117528	NR	630	253548	NR	760	12497	NR	890	6405	NR
375	7421	NR	505	135586	NR	635	235289	NR	765	11021	NR	895	6392	NR
380	6619	NR	510	153068	NR	640	217346	NR	770	9938	NR	900	5762	NR
385	5813	NR	515	167170	NR	645	198000	NR	775	9105	NR	905	5445	NR
390	5630	NR	520	178364	NR	650	180267	NR	780	8315	NR	910	6424	NR
395	4917	NR	525	186887	NR	655	162796	NR	785	8364	NR	915	5977	NR
400	4279	NR	530	194310	NR	660	143827	NR	790	7202	NR	920	5589	NR
405	4043	NR	535	201832	NR	665	127951	NR	795	7271	NR	925	6728	NR
410	4666	NR	540	208553	NR	670	112526	NR	800	6583	NR	930	7328	NR
415	6309	NR	545	216697	NR	675	97790	NR	805	6730	NR	935	5077	NR
420	9564	NR	550	224567	NR	680	85489	NR	810	7628	NR	940	5558	NR
425	16500	NR	555	235296	NR	685	74086	NR	815	6335	NR	945	2171	NR
430	28210	NR	560	246750	NR	690	65039	NR	820	5679	NR	950	10555	NR
435	47088	NR	565	258189	NR	695	56035	NR	825	6974	NR	955	8787	NR
440	76402	NR	570	270186	NR	700	49223	NR	830	7136	NR	960	6936	NR
445	124288	NR	575	282577	NR	705	43027	NR	835	5971	NR	965	8547	NR
450	197266	NR	580	295795	NR	710	38080	NR	840	6371	NR	970	7502	NR
455	240978	NR	585	304888	NR	715	33706	NR	845	6027	NR	975	8793	NR
460	199802	NR	590	313177	NR	720	29961	NR	850	6816	NR	980	5517	NR
465	147559	NR	595	317388	NR	725	26440	NR	855	6168	NR	985	4652	NR
470	121976	NR	600	317783	NR	730	23027	NR	860	6333	NR	990	7259	NR
475	97268	NR	605	315536	NR	735	20496	NR	865	6493	NR	995	11735	NR
480	80092	NR	610	309123	NR	740	18168	NR	870	7357	NR	1000	8351	NR
485	79203	NR	615	300672	NR	745	15812	NR	875	7188	NR			

REPORT NUMBER: SP1-2404-343-4





TM-30-18

Summary

$R_f = 84.3$
 $R_g = 94.4$
 CIE $R_a = 82.9$
 $R_9 = 8.8$



Color Vector Graphics




REPORT NUMBER: SP1-2404-343-4

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)




CES01 = 86	CES26 = 86	CES51 = 92	CES76 = 79
CES02 = 62	CES27 = 92	CES52 = 93	CES77 = 85
CES03 = 31	CES28 = 93	CES53 = 88	CES78 = 79
CES04 = 70	CES29 = 91	CES54 = 88	CES79 = 92
CES05 = 49	CES30 = 90	CES55 = 86	CES80 = 90
CES06 = 51	CES31 = 93	CES56 = 84	CES81 = 77
CES07 = 41	CES32 = 85	CES57 = 82	CES82 = 96
CES08 = 40	CES33 = 97	CES58 = 83	CES83 = 96
CES09 = 29	CES34 = 90	CES59 = 91	CES84 = 91
CES10 = 75	CES35 = 94	CES60 = 89	CES85 = 77
CES11 = 58	CES36 = 80	CES61 = 86	CES86 = 72
CES12 = 64	CES37 = 94	CES62 = 81	CES87 = 85
CES13 = 43	CES38 = 85	CES63 = 84	CES88 = 89
CES14 = 74	CES39 = 98	CES64 = 77	CES89 = 77
CES15 = 71	CES40 = 97	CES65 = 76	CES90 = 90
CES16 = 47	CES41 = 95	CES66 = 73	CES91 = 72
CES17 = 50	CES42 = 96	CES67 = 72	CES92 = 65
CES18 = 56	CES43 = 92	CES68 = 78	CES93 = 78
CES19 = 72	CES44 = 99	CES69 = 83	CES94 = 64
CES20 = 66	CES45 = 94	CES70 = 76	CES95 = 74
CES21 = 86	CES46 = 91	CES71 = 70	CES96 = 84
CES22 = 78	CES47 = 95	CES72 = 90	CES97 = 90
CES23 = 92	CES48 = 83	CES73 = 71	CES98 = 86
CES24 = 91	CES49 = 91	CES74 = 90	CES99 = 77
CES25 = 72	CES50 = 93	CES75 = 74	



REPORT NUMBER: SP1-2404-343-4

TM-30-18



Color Rendition by Hue-Angle Bin



REPORT NUMBER: SP1-2404-343-4

TM-30-18

Measure Comparisons



(END OF REPORT)