

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: METALUX

Report Number: P980696

Luminaire Tested: UHBS2-2436-M-L83065-MID-4000K-CLR3

Issue Date: 4/4/2025

Test Information

Test Method: LM-79-2019
Report Number: P980696
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2502-344-2)
Test Lab: INNOVATION CENTER
Issue Date: 4/4/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: METALUX
Catalog Number: UHBS2-2436-M-L83065-MID-4000K-CLR3
Description: UHBS2 LED High Bay at 4000K and MID lumen setting 3in Deep Clear Refractor
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 30778.0 lumens
Efficiency: N/A
Efficacy: 162.0 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.24
Luminous Opening: Vertical Cylinder (Dia: 1.34' x H: 0.25')
CIE Type: Direct

Input Watts (W): 190
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.998
Total Harmonic Distortion (THDi): 5.15
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P980696

CATALOG NUMBER: UHBS2-2436-M-L83065-MID-4000K-CLR3

Luminous Intensity Polar Plot



TEST NUMBER: P980696

CATALOG NUMBER: UHBS2-2436-M-L83065-MID-4000K-CLR3

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	110	110	110		105	105	105		100
1	111	107	104	101	108	105	102	99	100	98	96		96	94	93		92
2	103	97	92	87	101	95	90	86	91	87	84		88	85	82		85
3	96	88	81	76	94	86	80	75	83	78	74		80	76	72		77
4	89	80	72	67	87	78	72	66	76	70	65		73	68	64		71
5	83	73	65	59	81	71	64	59	69	63	58		67	62	58		65
6	78	66	59	53	76	65	58	53	63	57	52		62	56	52		60
7	73	61	53	48	71	60	53	48	58	52	47		57	51	47		55
8	68	56	49	44	66	55	48	43	54	48	43		53	47	43		51
9	64	52	45	40	62	51	44	40	50	44	39		49	43	39		48
10	60	48	41	36	59	48	41	36	47	40	36		45	40	36		45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	124755
5°	122211
10°	119641
15°	116357
20°	113253
25°	109856
30°	104803
35°	97173
40°	84929
45°	64144
50°	46679
55°	31529
60°	14474
65°	8277
70°	7826
75°	8723
80°	6474
85°	3596

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 64144 cd/sqm

TEST NUMBER: P980696

CATALOG NUMBER: UHBS2-2436-M-L83065-MID-4000K-CLR3

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1541.2	5.0
10°-20°	4402.9	14.3
20°-30°	6629.0	21.5
30°-40°	7515.5	24.4
40°-50°	5717.1	18.6
50°-60°	2817.5	9.2
60°-70°	762.6	2.5
70°-80°	547.9	1.8
80°-90°	195.4	0.6
90°-100°	149.9	0.5
100°-110°	203.8	0.7
110°-120°	109.6	0.4
120°-130°	59.0	0.2
130°-140°	44.6	0.1
140°-150°	37.3	0.1
150°-160°	27.0	0.1
160°-170°	13.7	0.0
170°-180°	3.9	0.0
0°-30°	12573.1	40.9
0°-40°	20088.6	65.3
0°-60°	28623.1	93.0
0°-90°	30129.0	97.9
90°-120°	463.3	1.5
90°-150°	604.3	2.0
90°-180°	649.0	2.1
0°-180°	30778.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	16272	
5°	16210	###
15°	15595	4403
25°	14428	6629
35°	12113	7515
45°	7324	5717
55°	3161	2817
65°	689	763
75°	556	548
85°	152	165
90°	102	60
95°	131	121
105°	204	204
115°	107	110
125°	64	59
135°	57	45
145°	59	37
155°	59	27
165°	48	14
175°	40	4
180°	40	

TEST NUMBER: P980696

CATALOG NUMBER: UHBS2-2436-M-L83065-MID-4000K-CLR3

CANDELA DISTRIBUTION (FULL):

0°	
0°	16272.0
2.5°	16260.2
5°	16210.2
7.5°	16131.8
10°	16013.0
12.5°	15834.8
15°	15594.7
17.5°	15345.2
20°	15083.8
22.5°	14786.7
25°	14427.9
27.5°	13985.8
30°	13465.4
32.5°	12892.6
35°	12113.1
37.5°	11279.0
40°	10181.0
42.5°	8795.5
45°	7324.4
47.5°	6093.4
50°	5024.0
52.5°	4082.9
55°	3160.8
57.5°	2279.1
60°	1333.2
62.5°	836.5
65°	689.2
67.5°	608.4
70°	577.5
72.5°	582.2
75°	556.1
77.5°	475.3
80°	344.6
82.5°	223.4
85°	152.1
87.5°	118.8
90°	102.2
92.5°	111.7
95°	130.7
97.5°	161.6
100°	190.1
102.5°	206.8
105°	204.4
107.5°	185.4
110°	156.9

TEST NUMBER: P980696

CATALOG NUMBER: UHBS2-2436-M-L83065-MID-4000K-CLR3

CANDELA DISTRIBUTION (continued):

	0°
112.5°	128.3
115°	106.9
117.5°	87.9
120°	76.0
122.5°	68.9
125°	64.2
127.5°	61.8
130°	59.4
132.5°	57.0
135°	57.0
137.5°	57.0
140°	59.4
142.5°	59.4
145°	59.4
147.5°	59.4
150°	59.4
152.5°	59.4
155°	59.4
157.5°	57.0
160°	54.7
162.5°	49.9
165°	47.5
167.5°	45.2
170°	42.8
172.5°	40.4
175°	40.4
177.5°	40.4
180°	40.4

(END OF REPORT)