

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: METALUX

Report Number: P980731

Luminaire Tested: UHBS2-2436-N-L83065-MID-5000K-CLR3

Issue Date: 4/4/2025

Test Information

Test Method: LM-79-2019
Report Number: P980731
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2502-344-3)
Test Lab: INNOVATION CENTER
Issue Date: 4/4/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: METALUX
Catalog Number: UHBS2-2436-N-L83065-MID-5000K-CLR3
Description: UHBS2 LED High Bay at 5000K and MID lumen setting 3in Deep Clear Refractor
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 30480.1 lumens
Efficiency: N/A
Efficacy: 159.6 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.03
Luminous Opening: Vertical Cylinder (Dia: 1.34' x H: 0.25')
CIE Type: Direct

Input Watts (W): 191
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.998
Total Harmonic Distortion (THDi): 5.15
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P980731

CATALOG NUMBER: UHBS2-2436-N-L83065-MID-5000K-CLR3

Luminous Intensity Polar Plot





TEST NUMBER: P980731

CATALOG NUMBER: UHBS2-2436-N-L83065-MID-5000K-CLR3

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	115	115	115	115	110	110	110	105	105	105	100	100	100	98		
1	111	107	104	101	108	105	102	100	101	98	96	96	94	93	93	91	90	88		
2	104	97	92	88	101	95	91	87	92	88	84	88	85	82	85	82	80	78		
3	97	88	82	77	94	87	81	76	84	79	74	81	76	73	78	75	72	70		
4	90	80	73	68	88	79	73	67	76	71	66	74	69	65	72	68	64	62		
5	84	74	66	61	82	72	66	60	70	64	60	68	63	59	66	62	58	56		
6	79	68	60	55	77	67	60	55	65	59	54	63	58	53	61	57	53	51		
7	74	62	55	50	72	61	54	50	60	54	49	58	53	49	57	52	48	46		
8	69	58	50	45	68	57	50	45	56	49	45	54	49	45	53	48	44	43		
9	65	54	47	42	64	53	46	42	52	46	41	51	45	41	50	44	41	39		
10	62	50	43	39	60	49	43	38	48	42	38	47	42	38	46	41	38	36		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	155328
5°	151894
10°	146821
15°	137852
20°	127591
25°	115500
30°	98603
35°	80853
40°	64779
45°	53519
50°	47552
55°	34524
60°	16878
65°	9860
70°	8116
75°	8415
80°	6094
85°	3657

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 53519 cd/sqm

TEST NUMBER: P980731

CATALOG NUMBER: UHBS2-2436-N-L83065-MID-5000K-CLR3

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1908.0	6.3
10°-20°	5184.3	17.0
20°-30°	6902.0	22.6
30°-40°	6299.9	20.7
40°-50°	4848.1	15.9
50°-60°	3021.6	9.9
60°-70°	892.1	2.9
70°-80°	534.9	1.8
80°-90°	195.1	0.6
90°-100°	172.8	0.6
100°-110°	225.3	0.7
110°-120°	111.4	0.4
120°-130°	58.9	0.2
130°-140°	44.7	0.1
140°-150°	36.1	0.1
150°-160°	26.2	0.1
160°-170°	14.5	0.0
170°-180°	4.4	0.0
0°-30°	13994.3	45.9
0°-40°	20294.2	66.6
0°-60°	28163.8	92.4
0°-90°	29785.9	97.7
90°-120°	509.5	1.7
90°-150°	649.1	2.1
90°-180°	694.0	2.3
0°-180°	30480.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	20260	
5°	20147	###
15°	18476	5184
25°	15169	6902
35°	10079	6300
45°	6111	4848
55°	3461	3022
65°	821	892
75°	536	535
85°	155	162
90°	115	66
95°	152	140
105°	225	225
115°	107	111
125°	65	59
135°	57	45
145°	57	36
155°	57	26
165°	50	15
175°	45	4
180°	47	

TEST NUMBER: P980731

CATALOG NUMBER: UHBS2-2436-N-L83065-MID-5000K-CLR3

CANDELA DISTRIBUTION (FULL):

0°	
0°	20259.7
2.5°	20244.7
5°	20147.4
7.5°	19970.2
10°	19650.8
12.5°	19136.8
15°	18475.5
17.5°	17769.3
20°	16993.3
22.5°	16169.8
25°	15169.2
27.5°	13983.9
30°	12668.9
32.5°	11386.3
35°	10078.7
37.5°	8821.0
40°	7765.5
42.5°	6909.6
45°	6111.1
47.5°	5716.8
50°	5117.9
52.5°	4284.5
55°	3461.0
57.5°	2525.3
60°	1554.6
62.5°	1043.1
65°	821.0
67.5°	676.2
70°	598.9
72.5°	573.9
75°	536.5
77.5°	454.2
80°	324.4
82.5°	217.1
85°	154.7
87.5°	124.8
90°	114.8
92.5°	127.3
95°	152.2
97.5°	187.2
100°	219.6
102.5°	234.6
105°	224.6
107.5°	199.6
110°	164.7

TEST NUMBER: P980731

CATALOG NUMBER: UHBS2-2436-N-L83065-MID-5000K-CLR3

CANDELA DISTRIBUTION (continued):

	0°
112.5°	132.3
115°	107.3
117.5°	87.3
120°	74.9
122.5°	67.4
125°	64.9
127.5°	62.4
130°	59.9
132.5°	57.4
135°	57.4
137.5°	57.4
140°	57.4
142.5°	57.4
145°	57.4
147.5°	57.4
150°	57.4
152.5°	57.4
155°	57.4
157.5°	54.9
160°	54.9
162.5°	52.4
165°	49.9
167.5°	49.9
170°	47.4
172.5°	44.9
175°	44.9
177.5°	47.4
180°	47.4

(END OF REPORT)