

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: METALUX

Report Number: P980613

Luminaire Tested: UHBS2-1218-N-L83065-MID-6500K-CLR3

Issue Date: 4/4/2025

Test Information

Test Method: LM-79-2019
Report Number: P980613
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2502-344-3)
Test Lab: INNOVATION CENTER
Issue Date: 4/4/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: METALUX
Catalog Number: UHBS2-1218-N-L83065-MID-6500K-CLR3
Description: UHBS2 LED High Bay at 6500K and MID lumen setting 3in Deep Clear Refractor
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 14091.9 lumens
Efficiency: N/A
Efficacy: 142.8 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.03
Luminous Opening: Vertical Cylinder (Dia: 1.17' x H: 0.25')
CIE Type: Direct

Input Watts (W): 98.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.997
Total Harmonic Distortion (THDi): 7.15
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P980613

CATALOG NUMBER: UHBS2-1218-N-L83065-MID-6500K-CLR3

Luminous Intensity Polar Plot



CATALOG NUMBER: UHBS2-1218-N-L83065-MID-6500K-CLR3

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	115	115	115	115	110	110	110	105	105	105	100	100	100	98		
1	111	107	104	101	108	105	102	100	101	98	96	96	94	93	93	91	90	88		
2	104	97	92	88	101	95	91	87	92	88	84	88	85	82	85	82	80	78		
3	97	88	82	77	94	87	81	76	84	79	74	81	76	73	78	75	72	70		
4	90	80	73	68	88	79	73	67	76	71	66	74	69	65	72	68	64	62		
5	84	74	66	61	82	72	66	60	70	64	60	68	63	59	66	62	58	56		
6	79	68	60	55	77	67	60	55	65	59	54	63	58	53	61	57	53	51		
7	74	62	55	50	72	61	54	50	60	54	49	58	53	49	57	52	48	46		
8	69	58	50	45	68	57	50	45	56	49	45	54	49	45	53	48	44	43		
9	65	54	47	42	64	53	46	42	52	46	41	51	45	41	50	44	41	39		
10	62	50	43	39	60	49	43	38	48	42	38	47	42	38	46	41	38	36		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	94422
5°	92059
10°	88727
15°	83068
20°	76664
25°	69198
30°	58896
35°	48140
40°	38440
45°	31641
50°	27999
55°	20234
60°	9838
65°	5711
70°	4663
75°	4785
80°	3417
85°	2007

MAXIMUM LUMINANCE 45°-90°:

Luminance: 31641 cd/sqm

TEST NUMBER: P980613

CATALOG NUMBER: UHBS2-1218-N-L83065-MID-6500K-CLR3

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	882.1	6.3
10°-20°	2396.9	17.0
20°-30°	3191.1	22.6
30°-40°	2912.7	20.7
40°-50°	2241.4	15.9
50°-60°	1397.0	9.9
60°-70°	412.4	2.9
70°-80°	247.3	1.8
80°-90°	90.2	0.6
90°-100°	79.9	0.6
100°-110°	104.1	0.7
110°-120°	51.5	0.4
120°-130°	27.2	0.2
130°-140°	20.6	0.1
140°-150°	16.6	0.1
150°-160°	12.1	0.1
160°-170°	6.7	0.0
170°-180°	2.0	0.0
0°-30°	6470.1	45.9
0°-40°	9382.8	66.6
0°-60°	13021.2	92.4
0°-90°	13771.1	97.7
90°-120°	235.5	1.7
90°-150°	300.0	2.1
90°-180°	321.0	2.3
0°-180°	14091.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9367	
5°	9315	882
15°	8542	2397
25°	7013	3191
35°	4660	2913
45°	2825	2241
55°	1600	1397
65°	380	412
75°	248	247
85°	72	75
90°	53	31
95°	70	65
105°	104	104
115°	50	51
125°	30	27
135°	26	21
145°	26	17
155°	26	12
165°	23	7
175°	21	2
180°	22	

TEST NUMBER: P980613

CATALOG NUMBER: UHBS2-1218-N-L83065-MID-6500K-CLR3

CANDELA DISTRIBUTION (FULL):

0°	
0°	9366.8
2.5°	9359.9
5°	9314.9
7.5°	9233.0
10°	9085.3
12.5°	8847.6
15°	8541.9
17.5°	8215.4
20°	7856.6
22.5°	7475.9
25°	7013.3
27.5°	6465.3
30°	5857.3
32.5°	5264.3
35°	4659.7
37.5°	4078.3
40°	3590.3
42.5°	3194.6
45°	2825.4
47.5°	2643.1
50°	2366.2
52.5°	1980.9
55°	1600.2
57.5°	1167.5
60°	718.7
62.5°	482.2
65°	379.6
67.5°	312.6
70°	276.9
72.5°	265.3
75°	248.0
77.5°	210.0
80°	150.0
82.5°	100.4
85°	71.5
87.5°	57.7
90°	53.1
92.5°	58.8
95°	70.4
97.5°	86.5
100°	101.5
102.5°	108.4
105°	103.8
107.5°	92.3
110°	76.1



TEST NUMBER: P980613

CATALOG NUMBER: UHBS2-1218-N-L83065-MID-6500K-CLR3

CANDELA DISTRIBUTION (continued):

	0°
112.5°	61.1
115°	49.6
117.5°	40.4
120°	34.6
122.5°	31.1
125°	30.0
127.5°	28.8
130°	27.7
132.5°	26.5
135°	26.5
137.5°	26.5
140°	26.5
142.5°	26.5
145°	26.5
147.5°	26.5
150°	26.5
152.5°	26.5
155°	26.5
157.5°	25.4
160°	25.4
162.5°	24.2
165°	23.1
167.5°	23.1
170°	21.9
172.5°	20.8
175°	20.8
177.5°	21.9
180°	21.9

(END OF REPORT)