

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: METALUX

Report Number: P982551

Luminaire Tested: 14CZ-LD5-25-UNV-L850-CD1-U

Issue Date: 04/23/2025

**Test Information**

Test Method: LM-79-2019  
Report Number: P982551  
Test Lab: INNOVATION CENTER(P3)  
Issue Date: 04/23/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: METALUX  
Catalog Number: 14CZ-LD5-25-UNV-L850-CD1-U  
Description: METALUX CRUZE 1x4 2500LM PACKAGE 80CRI 5000K TROFFER STANDARD LENS  
Light Source: 5000K CCT, 80 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2495.4 lumens  
Efficiency: N/A  
Efficacy: 131.3 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.28 / 1.37  
Luminous Opening: Rectangular (W 1' x L: 4' x H: 0')  
CIE Type: Direct

Input Watts (W): 19  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT

TEST NUMBER: P982551

CATALOG NUMBER: 14CZ-LD5-25-UNV-L850-CD1-U

### Luminous Intensity Polar Plot



TEST NUMBER: P982551

CATALOG NUMBER: 14CZ-LD5-25-UNV-L850-CD1-U

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 |
| 1   | 109 | 104 | 100 | 96  | 106 | 102 | 98  | 95  | 98  | 95  | 92  | 94  | 91  | 89  | 90  | 88  | 86  |
| 2   | 99  | 91  | 84  | 79  | 97  | 89  | 83  | 78  | 86  | 80  | 76  | 82  | 78  | 74  | 79  | 76  | 73  |
| 3   | 90  | 80  | 72  | 66  | 88  | 78  | 71  | 65  | 75  | 69  | 64  | 73  | 67  | 63  | 70  | 66  | 62  |
| 4   | 83  | 71  | 62  | 56  | 81  | 70  | 61  | 55  | 67  | 60  | 54  | 65  | 59  | 54  | 63  | 57  | 53  |
| 5   | 76  | 63  | 54  | 48  | 74  | 62  | 54  | 48  | 60  | 53  | 47  | 58  | 52  | 46  | 56  | 51  | 46  |
| 6   | 70  | 57  | 48  | 42  | 68  | 56  | 48  | 42  | 54  | 47  | 41  | 53  | 46  | 41  | 51  | 45  | 40  |
| 7   | 65  | 52  | 43  | 37  | 63  | 51  | 43  | 37  | 49  | 42  | 36  | 48  | 41  | 36  | 47  | 40  | 36  |
| 8   | 61  | 47  | 39  | 33  | 59  | 46  | 38  | 33  | 45  | 38  | 33  | 44  | 37  | 32  | 43  | 37  | 32  |
| 9   | 57  | 43  | 35  | 30  | 55  | 43  | 35  | 29  | 42  | 34  | 29  | 40  | 34  | 29  | 39  | 33  | 29  |
| 10  | 53  | 40  | 32  | 27  | 52  | 39  | 32  | 27  | 38  | 31  | 27  | 37  | 31  | 26  | 37  | 31  | 26  |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°   | 45°  | 90°  |
|-----|------|------|------|
| 0°  | 2421 | 2421 | 2421 |
| 5°  | 2426 | 2410 | 2424 |
| 10° | 2415 | 2403 | 2425 |
| 15° | 2389 | 2392 | 2417 |
| 20° | 2360 | 2375 | 2416 |
| 25° | 2317 | 2355 | 2417 |
| 30° | 2268 | 2329 | 2412 |
| 35° | 2215 | 2303 | 2409 |
| 40° | 2146 | 2270 | 2417 |
| 45° | 2082 | 2244 | 2430 |
| 50° | 2001 | 2220 | 2431 |
| 55° | 1934 | 2203 | 2329 |
| 60° | 1859 | 2171 | 2136 |
| 65° | 1759 | 2067 | 1899 |
| 70° | 1643 | 1878 | 1606 |
| 75° | 1483 | 1639 | 1345 |
| 80° | 1193 | 1286 | 1026 |
| 85° | 849  | 738  | 534  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°

Vertical Angle: 50°

Luminance: 2431 cd/sqm

TEST NUMBER: P982551

CATALOG NUMBER: 14CZ-LD5-25-UNV-L850-CD1-U

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 85.1   | 3.4       |
| 10°-20°   | 243.2  | 9.7       |
| 20°-30°   | 367.0  | 14.7      |
| 30°-40°   | 440.0  | 17.6      |
| 40°-50°   | 456.6  | 18.3      |
| 50°-60°   | 412.2  | 16.5      |
| 60°-70°   | 300.2  | 12.0      |
| 70°-80°   | 157.5  | 6.3       |
| 80°-90°   | 33.7   | 1.3       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 695.3  | 27.9      |
| 0°-40°    | 1135.3 | 45.5      |
| 0°-60°    | 2004.1 | 80.3      |
| 0°-90°    | 2495.4 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 2495.4 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | 22.5° | 45° | 67.5° | 90° | Flux |
|-----|-----|-------|-----|-------|-----|------|
| 0°  | 900 | 900   | 900 | 900   | 900 |      |
| 5°  | 898 | 896   | 892 | 898   | 898 | 85   |
| 15° | 858 | 858   | 859 | 868   | 868 | 242  |
| 25° | 780 | 785   | 793 | 810   | 814 | 360  |
| 35° | 674 | 681   | 701 | 727   | 733 | 421  |
| 45° | 547 | 559   | 590 | 627   | 638 | 421  |
| 55° | 412 | 427   | 470 | 498   | 496 | 369  |
| 65° | 276 | 293   | 325 | 310   | 298 | 273  |
| 75° | 143 | 163   | 158 | 136   | 129 | 150  |
| 85° | 28  | 33    | 24  | 18    | 17  | 35   |
| 90° | 0   | 0     | 0   | 0     | 0   |      |

TEST NUMBER: P982551

CATALOG NUMBER: 14CZ-LD5-25-UNV-L850-CD1-U

**CANDELA DISTRIBUTION (FULL):**

|       | 0°    | 22.5° | 45°   | 67.5° | 90°   |
|-------|-------|-------|-------|-------|-------|
| 0°    | 899.8 | 899.8 | 899.8 | 899.8 | 899.8 |
| 2.5°  | 901.6 | 899.2 | 894.5 | 900.4 | 899.8 |
| 5°    | 898.0 | 896.3 | 892.1 | 898.0 | 897.5 |
| 7.5°  | 892.1 | 890.9 | 887.3 | 893.9 | 893.3 |
| 10°   | 883.8 | 882.0 | 879.6 | 886.8 | 887.3 |
| 12.5° | 872.5 | 871.9 | 870.6 | 878.4 | 877.8 |
| 15°   | 857.5 | 857.5 | 858.7 | 868.2 | 867.6 |
| 17.5° | 842.5 | 842.5 | 845.6 | 856.3 | 856.9 |
| 20°   | 824.1 | 825.3 | 829.5 | 842.5 | 843.7 |
| 22.5° | 803.2 | 804.4 | 811.5 | 828.3 | 831.2 |
| 25°   | 780.5 | 784.8 | 793.1 | 810.3 | 813.9 |
| 27.5° | 759.7 | 760.3 | 772.8 | 791.9 | 796.7 |
| 30°   | 729.9 | 738.2 | 749.5 | 771.6 | 776.3 |
| 32.5° | 700.5 | 708.9 | 726.2 | 750.1 | 756.6 |
| 35°   | 674.4 | 680.9 | 701.1 | 727.4 | 733.4 |
| 37.5° | 641.4 | 652.3 | 676.1 | 703.6 | 711.9 |
| 40°   | 611.0 | 620.6 | 646.3 | 677.3 | 688.0 |
| 42.5° | 579.4 | 590.2 | 619.4 | 652.8 | 663.6 |
| 45°   | 547.2 | 559.2 | 589.6 | 626.6 | 638.5 |
| 47.5° | 512.0 | 526.9 | 561.6 | 599.1 | 609.8 |
| 50°   | 478.0 | 493.5 | 530.4 | 569.9 | 580.6 |
| 52.5° | 447.0 | 460.7 | 501.3 | 537.7 | 542.4 |
| 55°   | 412.3 | 426.7 | 469.6 | 497.6 | 496.4 |
| 57.5° | 377.7 | 393.9 | 436.8 | 454.1 | 449.4 |
| 60°   | 345.5 | 360.5 | 403.4 | 407.0 | 396.8 |
| 62.5° | 309.7 | 327.0 | 363.4 | 358.1 | 345.5 |
| 65°   | 276.3 | 293.0 | 324.6 | 309.7 | 298.3 |
| 67.5° | 242.2 | 260.2 | 282.9 | 260.8 | 247.7 |
| 70°   | 208.8 | 230.3 | 238.7 | 214.9 | 204.1 |
| 72.5° | 174.8 | 197.5 | 196.9 | 174.2 | 165.3 |
| 75°   | 142.6 | 162.9 | 157.6 | 136.1 | 129.4 |
| 77.5° | 108.6 | 128.8 | 118.7 | 102.7 | 96.6  |
| 80°   | 77.0  | 96.0  | 83.0  | 70.5  | 66.2  |
| 82.5° | 52.5  | 63.8  | 51.9  | 41.1  | 39.3  |
| 85°   | 27.5  | 32.8  | 23.9  | 18.5  | 17.3  |
| 87.5° | 10.1  | 9.5   | 8.3   | 7.7   | 7.7   |
| 90°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP3-2508-516-8

Test Date: 09/03/2025

Luminaire Tested: 24CZ-LD5-65-S-UNV-L950-CD1-U

Data in this report applies to families of products including 24CZ-LD5-65-S-UNV-L950-CD1-U

### Test Information

Test Method: LM-79-2019  
 Report Number: SP3-2508-516-8  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP3 - 3M SPHERE  
 Measurement Geometry:  $4\pi$   
 Issue Date: 09/05/2025  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: Metalux  
 Catalog Number: **24CZ-LD5-65-S-UNV-L950-CD1-U**  
 Description: 2X4 CRUZE SB 6500LM 950 SMOOTH LENS

### Spectral Parameters

CCT (K): 5019  
 CIE  $u'$ : 0.2113  
 CIE  $v'$ : 0.4842  
 Duv: -0.0002  
 CIE x: 0.3445  
 CIE y: 0.3508  
 CIE z: 0.3046  
 Peak Wavelength (nm): 630  
 Dominant Wavelength (nm): 572  
 Purity: 8.636369  
 R<sub>f</sub>: 89.8  
 R<sub>g</sub>: 98.5

CRI (Ra): 94.6  
 R1: 96.4  
 R2: 98.4  
 R3: 96.9  
 R4: 94.5  
 R5: 94.5  
 R6: 93.5  
 R7: 93.6  
 R8: 89.4  
 R9: 74.6  
 R10: 94.2  
 R11: 95.5  
 R12: 70.8  
 R13: 98.0  
 R14: 98.0  
 R15: 95.0



### Test Conditions

Stabilization Time: M  
 Operation Time: 1H 0M  
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP3-2508-516-8

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | 3M SPHERE IN02505     | 7/1/2025         | 1/1/2026             |
| Power Meter                    | XITRON INXT2011006    | 1/20/2025        | 1/20/2026            |
| AC Power Source                | CHROMA 61604 IN6064A  | 10/22/2024       | 10/22/2025           |
| DC Power Source                | EYSIGHT N5770A IN0534 | 10/22/2024       | 10/22/2025           |
| Sphere Thermometer             | TANDD IN4036E         | 10/22/2024       | 10/22/2025           |
|                                |                       |                  |                      |

REPORT NUMBER: SP3-2508-516-8

**CIE 1931 Chromaticity Diagram**



**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 5000K 4-step quadrangle

REPORT NUMBER: SP3-2508-516-8

### Photopic Flux vs. Wavelength



### Photopic Lumens: NR

| λ (nm) | Power W <sup>λ</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>λ</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>λ</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>λ</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>λ</sup> /nm | Lumens (φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360    | 0                        | NR            | 490    | 249                      | NR            | 620    | 343                      | NR            | 750    | 8                        | NR            | 880    | 0                        | NR            |
| 365    | 0                        | NR            | 495    | 269                      | NR            | 625    | 339                      | NR            | 755    | 7                        | NR            | 885    | 0                        | NR            |
| 370    | 0                        | NR            | 500    | 296                      | NR            | 630    | 1000                     | NR            | 760    | 6                        | NR            | 890    | 0                        | NR            |
| 375    | 0                        | NR            | 505    | 325                      | NR            | 635    | 705                      | NR            | 765    | 5                        | NR            | 895    | 0                        | NR            |
| 380    | 0                        | NR            | 510    | 347                      | NR            | 640    | 221                      | NR            | 770    | 4                        | NR            | 900    | 0                        | NR            |
| 385    | 0                        | NR            | 515    | 363                      | NR            | 645    | 210                      | NR            | 775    | 4                        | NR            | 905    | 0                        | NR            |
| 390    | 1                        | NR            | 520    | 371                      | NR            | 650    | 186                      | NR            | 780    | 3                        | NR            | 910    | 0                        | NR            |
| 395    | 3                        | NR            | 525    | 378                      | NR            | 655    | 155                      | NR            | 785    | 3                        | NR            | 915    | 0                        | NR            |
| 400    | 4                        | NR            | 530    | 381                      | NR            | 660    | 132                      | NR            | 790    | 2                        | NR            | 920    | 0                        | NR            |
| 405    | 5                        | NR            | 535    | 383                      | NR            | 665    | 111                      | NR            | 795    | 2                        | NR            | 925    | 0                        | NR            |
| 410    | 7                        | NR            | 540    | 385                      | NR            | 670    | 102                      | NR            | 800    | 2                        | NR            | 930    | 0                        | NR            |
| 415    | 10                       | NR            | 545    | 389                      | NR            | 675    | 84                       | NR            | 805    | 1                        | NR            | 935    | 0                        | NR            |
| 420    | 17                       | NR            | 550    | 391                      | NR            | 680    | 72                       | NR            | 810    | 1                        | NR            | 940    | 0                        | NR            |
| 425    | 29                       | NR            | 555    | 392                      | NR            | 685    | 62                       | NR            | 815    | 1                        | NR            | 945    | 0                        | NR            |
| 430    | 53                       | NR            | 560    | 393                      | NR            | 690    | 53                       | NR            | 820    | 1                        | NR            | 950    | 0                        | NR            |
| 435    | 97                       | NR            | 565    | 394                      | NR            | 695    | 45                       | NR            | 825    | 1                        | NR            | 955    | 0                        | NR            |
| 440    | 173                      | NR            | 570    | 391                      | NR            | 700    | 39                       | NR            | 830    | 1                        | NR            | 960    | 0                        | NR            |
| 445    | 321                      | NR            | 575    | 389                      | NR            | 705    | 33                       | NR            | 835    | 1                        | NR            | 965    | 0                        | NR            |
| 450    | 597                      | NR            | 580    | 385                      | NR            | 710    | 28                       | NR            | 840    | 1                        | NR            | 970    | 0                        | NR            |
| 455    | 795                      | NR            | 585    | 382                      | NR            | 715    | 24                       | NR            | 845    | 1                        | NR            | 975    | 0                        | NR            |
| 460    | 615                      | NR            | 590    | 375                      | NR            | 720    | 21                       | NR            | 850    | 0                        | NR            | 980    | 0                        | NR            |
| 465    | 438                      | NR            | 595    | 367                      | NR            | 725    | 17                       | NR            | 855    | 0                        | NR            | 985    | 0                        | NR            |
| 470    | 372                      | NR            | 600    | 361                      | NR            | 730    | 15                       | NR            | 860    | 0                        | NR            | 990    | 0                        | NR            |
| 475    | 290                      | NR            | 605    | 355                      | NR            | 735    | 13                       | NR            | 865    | 0                        | NR            | 995    | 0                        | NR            |
| 480    | 236                      | NR            | 610    | 383                      | NR            | 740    | 11                       | NR            | 870    | 0                        | NR            | 1000   | 0                        | NR            |
| 485    | 232                      | NR            | 615    | 408                      | NR            | 745    | 9                        | NR            | 875    | 0                        | NR            |        |                          |               |

REPORT NUMBER: SP3-2508-516-8

### Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 2.11

| λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360    | 0                        | NR            | 490    | 249                      | NR            | 620    | 343                      | NR            | 750    | 8                        | NR            | 880    | 0                        | NR            |
| 365    | 0                        | NR            | 495    | 269                      | NR            | 625    | 339                      | NR            | 755    | 7                        | NR            | 885    | 0                        | NR            |
| 370    | 0                        | NR            | 500    | 296                      | NR            | 630    | 1000                     | NR            | 760    | 6                        | NR            | 890    | 0                        | NR            |
| 375    | 0                        | NR            | 505    | 325                      | NR            | 635    | 705                      | NR            | 765    | 5                        | NR            | 895    | 0                        | NR            |
| 380    | 0                        | NR            | 510    | 347                      | NR            | 640    | 221                      | NR            | 770    | 4                        | NR            | 900    | 0                        | NR            |
| 385    | 0                        | NR            | 515    | 363                      | NR            | 645    | 210                      | NR            | 775    | 4                        | NR            | 905    | 0                        | NR            |
| 390    | 1                        | NR            | 520    | 371                      | NR            | 650    | 186                      | NR            | 780    | 3                        | NR            | 910    | 0                        | NR            |
| 395    | 3                        | NR            | 525    | 378                      | NR            | 655    | 155                      | NR            | 785    | 3                        | NR            | 915    | 0                        | NR            |
| 400    | 4                        | NR            | 530    | 381                      | NR            | 660    | 132                      | NR            | 790    | 2                        | NR            | 920    | 0                        | NR            |
| 405    | 5                        | NR            | 535    | 383                      | NR            | 665    | 111                      | NR            | 795    | 2                        | NR            | 925    | 0                        | NR            |
| 410    | 7                        | NR            | 540    | 385                      | NR            | 670    | 102                      | NR            | 800    | 2                        | NR            | 930    | 0                        | NR            |
| 415    | 10                       | NR            | 545    | 389                      | NR            | 675    | 84                       | NR            | 805    | 1                        | NR            | 935    | 0                        | NR            |
| 420    | 17                       | NR            | 550    | 391                      | NR            | 680    | 72                       | NR            | 810    | 1                        | NR            | 940    | 0                        | NR            |
| 425    | 29                       | NR            | 555    | 392                      | NR            | 685    | 62                       | NR            | 815    | 1                        | NR            | 945    | 0                        | NR            |
| 430    | 53                       | NR            | 560    | 393                      | NR            | 690    | 53                       | NR            | 820    | 1                        | NR            | 950    | 0                        | NR            |
| 435    | 97                       | NR            | 565    | 394                      | NR            | 695    | 45                       | NR            | 825    | 1                        | NR            | 955    | 0                        | NR            |
| 440    | 173                      | NR            | 570    | 391                      | NR            | 700    | 39                       | NR            | 830    | 1                        | NR            | 960    | 0                        | NR            |
| 445    | 321                      | NR            | 575    | 389                      | NR            | 705    | 33                       | NR            | 835    | 1                        | NR            | 965    | 0                        | NR            |
| 450    | 597                      | NR            | 580    | 385                      | NR            | 710    | 28                       | NR            | 840    | 1                        | NR            | 970    | 0                        | NR            |
| 455    | 795                      | NR            | 585    | 382                      | NR            | 715    | 24                       | NR            | 845    | 1                        | NR            | 975    | 0                        | NR            |
| 460    | 615                      | NR            | 590    | 375                      | NR            | 720    | 21                       | NR            | 850    | 0                        | NR            | 980    | 0                        | NR            |
| 465    | 438                      | NR            | 595    | 367                      | NR            | 725    | 17                       | NR            | 855    | 0                        | NR            | 985    | 0                        | NR            |
| 470    | 372                      | NR            | 600    | 361                      | NR            | 730    | 15                       | NR            | 860    | 0                        | NR            | 990    | 0                        | NR            |
| 475    | 290                      | NR            | 605    | 355                      | NR            | 735    | 13                       | NR            | 865    | 0                        | NR            | 995    | 0                        | NR            |
| 480    | 236                      | NR            | 610    | 383                      | NR            | 740    | 11                       | NR            | 870    | 0                        | NR            | 1000   | 0                        | NR            |
| 485    | 232                      | NR            | 615    | 408                      | NR            | 745    | 9                        | NR            | 875    | 0                        | NR            |        |                          |               |

REPORT NUMBER: SP3-2508-516-8

### Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 4.62


| $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|
| 360               | 0                                      | NR                             | 490               | 249                                    | NR                             | 620               | 343                                    | NR                             | 750               | 8                                      | NR                             | 880               | 0                                      | NR                             |
| 365               | 0                                      | NR                             | 495               | 269                                    | NR                             | 625               | 339                                    | NR                             | 755               | 7                                      | NR                             | 885               | 0                                      | NR                             |
| 370               | 0                                      | NR                             | 500               | 296                                    | NR                             | 630               | 1000                                   | NR                             | 760               | 6                                      | NR                             | 890               | 0                                      | NR                             |
| 375               | 0                                      | NR                             | 505               | 325                                    | NR                             | 635               | 705                                    | NR                             | 765               | 5                                      | NR                             | 895               | 0                                      | NR                             |
| 380               | 0                                      | NR                             | 510               | 347                                    | NR                             | 640               | 221                                    | NR                             | 770               | 4                                      | NR                             | 900               | 0                                      | NR                             |
| 385               | 0                                      | NR                             | 515               | 363                                    | NR                             | 645               | 210                                    | NR                             | 775               | 4                                      | NR                             | 905               | 0                                      | NR                             |
| 390               | 1                                      | NR                             | 520               | 371                                    | NR                             | 650               | 186                                    | NR                             | 780               | 3                                      | NR                             | 910               | 0                                      | NR                             |
| 395               | 3                                      | NR                             | 525               | 378                                    | NR                             | 655               | 155                                    | NR                             | 785               | 3                                      | NR                             | 915               | 0                                      | NR                             |
| 400               | 4                                      | NR                             | 530               | 381                                    | NR                             | 660               | 132                                    | NR                             | 790               | 2                                      | NR                             | 920               | 0                                      | NR                             |
| 405               | 5                                      | NR                             | 535               | 383                                    | NR                             | 665               | 111                                    | NR                             | 795               | 2                                      | NR                             | 925               | 0                                      | NR                             |
| 410               | 7                                      | NR                             | 540               | 385                                    | NR                             | 670               | 102                                    | NR                             | 800               | 2                                      | NR                             | 930               | 0                                      | NR                             |
| 415               | 10                                     | NR                             | 545               | 389                                    | NR                             | 675               | 84                                     | NR                             | 805               | 1                                      | NR                             | 935               | 0                                      | NR                             |
| 420               | 17                                     | NR                             | 550               | 391                                    | NR                             | 680               | 72                                     | NR                             | 810               | 1                                      | NR                             | 940               | 0                                      | NR                             |
| 425               | 29                                     | NR                             | 555               | 392                                    | NR                             | 685               | 62                                     | NR                             | 815               | 1                                      | NR                             | 945               | 0                                      | NR                             |
| 430               | 53                                     | NR                             | 560               | 393                                    | NR                             | 690               | 53                                     | NR                             | 820               | 1                                      | NR                             | 950               | 0                                      | NR                             |
| 435               | 97                                     | NR                             | 565               | 394                                    | NR                             | 695               | 45                                     | NR                             | 825               | 1                                      | NR                             | 955               | 0                                      | NR                             |
| 440               | 173                                    | NR                             | 570               | 391                                    | NR                             | 700               | 39                                     | NR                             | 830               | 1                                      | NR                             | 960               | 0                                      | NR                             |
| 445               | 321                                    | NR                             | 575               | 389                                    | NR                             | 705               | 33                                     | NR                             | 835               | 1                                      | NR                             | 965               | 0                                      | NR                             |
| 450               | 597                                    | NR                             | 580               | 385                                    | NR                             | 710               | 28                                     | NR                             | 840               | 1                                      | NR                             | 970               | 0                                      | NR                             |
| 455               | 795                                    | NR                             | 585               | 382                                    | NR                             | 715               | 24                                     | NR                             | 845               | 1                                      | NR                             | 975               | 0                                      | NR                             |
| 460               | 615                                    | NR                             | 590               | 375                                    | NR                             | 720               | 21                                     | NR                             | 850               | 0                                      | NR                             | 980               | 0                                      | NR                             |
| 465               | 438                                    | NR                             | 595               | 367                                    | NR                             | 725               | 17                                     | NR                             | 855               | 0                                      | NR                             | 985               | 0                                      | NR                             |
| 470               | 372                                    | NR                             | 600               | 361                                    | NR                             | 730               | 15                                     | NR                             | 860               | 0                                      | NR                             | 990               | 0                                      | NR                             |
| 475               | 290                                    | NR                             | 605               | 355                                    | NR                             | 735               | 13                                     | NR                             | 865               | 0                                      | NR                             | 995               | 0                                      | NR                             |
| 480               | 236                                    | NR                             | 610               | 383                                    | NR                             | 740               | 11                                     | NR                             | 870               | 0                                      | NR                             | 1000              | 0                                      | NR                             |
| 485               | 232                                    | NR                             | 615               | 408                                    | NR                             | 745               | 9                                      | NR                             | 875               | 0                                      | NR                             |                   |                                        |                                |

REPORT NUMBER: SP3-2508-516-8


TM-30-18

### Summary

$R_f = 89.8$   
 $R_g = 98.5$   
 $CIE R_a = 94.6$   
 $R_9 = 74.6$



### Color Vector Graphics



**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |             |            |            |
|------------|-------------|------------|------------|
| CES01 = 85 | CES26 = 96  | CES51 = 93 | CES76 = 88 |
| CES02 = 61 | CES27 = 88  | CES52 = 97 | CES77 = 87 |
| CES03 = 31 | CES28 = 96  | CES53 = 95 | CES78 = 85 |
| CES04 = 69 | CES29 = 93  | CES54 = 89 | CES79 = 93 |
| CES05 = 48 | CES30 = 81  | CES55 = 86 | CES80 = 93 |
| CES06 = 50 | CES31 = 95  | CES56 = 90 | CES81 = 80 |
| CES07 = 41 | CES32 = 93  | CES57 = 87 | CES82 = 96 |
| CES08 = 40 | CES33 = 91  | CES58 = 87 | CES83 = 95 |
| CES09 = 29 | CES34 = 95  | CES59 = 96 | CES84 = 93 |
| CES10 = 73 | CES35 = 96  | CES60 = 89 | CES85 = 81 |
| CES11 = 56 | CES36 = 74  | CES61 = 89 | CES86 = 85 |
| CES12 = 62 | CES37 = 95  | CES62 = 78 | CES87 = 93 |
| CES13 = 42 | CES38 = 76  | CES63 = 89 | CES88 = 96 |
| CES14 = 74 | CES39 = 98  | CES64 = 84 | CES89 = 87 |
| CES15 = 71 | CES40 = 98  | CES65 = 86 | CES90 = 93 |
| CES16 = 47 | CES41 = 92  | CES66 = 81 | CES91 = 68 |
| CES17 = 48 | CES42 = 95  | CES67 = 80 | CES92 = 78 |
| CES18 = 56 | CES43 = 96  | CES68 = 85 | CES93 = 86 |
| CES19 = 70 | CES44 = 99  | CES69 = 85 | CES94 = 79 |
| CES20 = 65 | CES45 = 100 | CES70 = 84 | CES95 = 82 |
| CES21 = 85 | CES46 = 96  | CES71 = 75 | CES96 = 93 |
| CES22 = 77 | CES47 = 91  | CES72 = 92 | CES97 = 96 |
| CES23 = 91 | CES48 = 84  | CES73 = 80 | CES98 = 94 |
| CES24 = 90 | CES49 = 97  | CES74 = 89 | CES99 = 92 |
| CES25 = 70 | CES50 = 95  | CES75 = 78 |            |



**Color Rendition by Hue-Angle Bin**


**Measure Comparisons**



(END OF REPORT)