

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: METALUX

Report Number: P982571

Luminaire Tested: 14CZ-LD5-35-UNV-L940-S-CD1-U

Issue Date: 04/23/2025

**Test Information**

Test Method: LM-79-2019  
Report Number: P982571  
Test Lab: INNOVATION CENTER(P3)  
Issue Date: 04/23/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: METALUX  
Catalog Number: 14CZ-LD5-35-UNV-L940-S-CD1-U  
Description: METALUX CRUZE 1x4 3500LM PACKAGE 90CRI 4000K TROFFER SMOOTH LENS  
Light Source: 4000K CCT, 90 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3791.1 lumens  
Efficiency: N/A  
Efficacy: 133.0 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.28 / 1.37  
Luminous Opening: Rectangular (W 1' x L: 4' x H: 0')  
CIE Type: Direct

Input Watts (W): 28.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT

TEST NUMBER: P982571

CATALOG NUMBER: 14CZ-LD5-35-UNV-L940-S-CD1-U

### Luminous Intensity Polar Plot



TEST NUMBER: P982571

CATALOG NUMBER: 14CZ-LD5-35-UNV-L940-S-CD1-U

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 109 | 104 | 100 | 96  | 106 | 102 | 98  | 95  | 98  | 95  | 92  |  | 94  | 91  | 89  |  | 90  |
| 2   | 99  | 91  | 84  | 79  | 97  | 89  | 83  | 78  | 86  | 80  | 76  |  | 82  | 78  | 74  |  | 79  |
| 3   | 90  | 80  | 72  | 66  | 88  | 78  | 71  | 65  | 75  | 69  | 64  |  | 73  | 67  | 63  |  | 70  |
| 4   | 83  | 71  | 62  | 56  | 81  | 70  | 61  | 55  | 67  | 60  | 54  |  | 65  | 59  | 54  |  | 63  |
| 5   | 76  | 63  | 54  | 48  | 74  | 62  | 54  | 48  | 60  | 53  | 47  |  | 58  | 52  | 46  |  | 56  |
| 6   | 70  | 57  | 48  | 42  | 68  | 56  | 48  | 42  | 54  | 47  | 41  |  | 53  | 46  | 41  |  | 51  |
| 7   | 65  | 52  | 43  | 37  | 63  | 51  | 43  | 37  | 49  | 42  | 36  |  | 48  | 41  | 36  |  | 47  |
| 8   | 61  | 47  | 39  | 33  | 59  | 46  | 38  | 33  | 45  | 38  | 33  |  | 44  | 37  | 32  |  | 43  |
| 9   | 57  | 43  | 35  | 30  | 55  | 43  | 35  | 29  | 42  | 34  | 29  |  | 40  | 34  | 29  |  | 39  |
| 10  | 53  | 40  | 32  | 27  | 52  | 39  | 32  | 27  | 38  | 31  | 27  |  | 37  | 31  | 26  |  | 37  |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°   | 45°  | 90°  |
|-----|------|------|------|
| 0°  | 3679 | 3679 | 3679 |
| 5°  | 3685 | 3661 | 3683 |
| 10° | 3669 | 3651 | 3683 |
| 15° | 3629 | 3634 | 3672 |
| 20° | 3585 | 3609 | 3671 |
| 25° | 3521 | 3578 | 3672 |
| 30° | 3445 | 3538 | 3665 |
| 35° | 3366 | 3499 | 3660 |
| 40° | 3261 | 3449 | 3672 |
| 45° | 3164 | 3409 | 3692 |
| 50° | 3040 | 3374 | 3693 |
| 55° | 2939 | 3347 | 3538 |
| 60° | 2825 | 3299 | 3244 |
| 65° | 2672 | 3140 | 2886 |
| 70° | 2496 | 2854 | 2440 |
| 75° | 2252 | 2489 | 2045 |
| 80° | 1812 | 1954 | 1559 |
| 85° | 1291 | 1121 | 809  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°

Vertical Angle: 50°

Luminance: 3693 cd/sqm

TEST NUMBER: P982571

CATALOG NUMBER: 14CZ-LD5-35-UNV-L940-S-CD1-U

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 129.3  | 3.4       |
| 10°-20°   | 369.5  | 9.7       |
| 20°-30°   | 557.5  | 14.7      |
| 30°-40°   | 668.4  | 17.6      |
| 40°-50°   | 693.7  | 18.3      |
| 50°-60°   | 626.2  | 16.5      |
| 60°-70°   | 456.1  | 12.0      |
| 70°-80°   | 239.2  | 6.3       |
| 80°-90°   | 51.1   | 1.3       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1056.3 | 27.9      |
| 0°-40°    | 1724.8 | 45.5      |
| 0°-60°    | 3044.7 | 80.3      |
| 0°-90°    | 3791.1 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 3791.1 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | 22.5° | 45°  | 67.5° | 90°  | Flux |
|-----|------|-------|------|-------|------|------|
| 0°  | 1367 | 1367  | 1367 | 1367  | 1367 |      |
| 5°  | 1364 | 1362  | 1355 | 1364  | 1364 | 130  |
| 15° | 1303 | 1303  | 1305 | 1319  | 1318 | 368  |
| 25° | 1186 | 1192  | 1205 | 1231  | 1237 | 547  |
| 35° | 1024 | 1034  | 1065 | 1105  | 1114 | 639  |
| 45° | 831  | 850   | 896  | 952   | 970  | 640  |
| 55° | 626  | 648   | 714  | 756   | 754  | 560  |
| 65° | 420  | 445   | 493  | 470   | 453  | 415  |
| 75° | 217  | 247   | 239  | 207   | 197  | 228  |
| 85° | 42   | 50    | 36   | 28    | 26   | 53   |
| 90° | 0    | 0     | 0    | 0     | 0    |      |

TEST NUMBER: P982571

CATALOG NUMBER: 14CZ-LD5-35-UNV-L940-S-CD1-U

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 22.5°  | 45°    | 67.5°  | 90°    |
|-------|--------|--------|--------|--------|--------|
| 0°    | 1367.1 | 1367.1 | 1367.1 | 1367.1 | 1367.1 |
| 2.5°  | 1369.8 | 1366.1 | 1359.0 | 1368.0 | 1367.1 |
| 5°    | 1364.3 | 1361.7 | 1355.3 | 1364.3 | 1363.6 |
| 7.5°  | 1355.3 | 1353.5 | 1348.0 | 1358.1 | 1357.2 |
| 10°   | 1342.7 | 1339.9 | 1336.3 | 1347.3 | 1348.0 |
| 12.5° | 1325.5 | 1324.5 | 1322.7 | 1334.4 | 1333.5 |
| 15°   | 1302.7 | 1302.7 | 1304.6 | 1319.0 | 1318.1 |
| 17.5° | 1280.0 | 1280.0 | 1284.6 | 1300.9 | 1301.8 |
| 20°   | 1252.0 | 1253.8 | 1260.2 | 1280.0 | 1281.8 |
| 22.5° | 1220.3 | 1222.1 | 1232.9 | 1258.4 | 1262.8 |
| 25°   | 1185.8 | 1192.2 | 1204.9 | 1231.1 | 1236.6 |
| 27.5° | 1154.1 | 1155.0 | 1174.1 | 1203.0 | 1210.4 |
| 30°   | 1108.8 | 1121.5 | 1138.7 | 1172.2 | 1179.4 |
| 32.5° | 1064.3 | 1076.9 | 1103.3 | 1139.6 | 1149.5 |
| 35°   | 1024.5 | 1034.4 | 1065.2 | 1105.2 | 1114.1 |
| 37.5° | 974.5  | 991.0  | 1027.1 | 1068.9 | 1081.5 |
| 40°   | 928.3  | 942.8  | 981.8  | 1028.9 | 1045.2 |
| 42.5° | 880.3  | 896.6  | 940.9  | 991.7  | 1008.2 |
| 45°   | 831.3  | 849.5  | 895.7  | 951.9  | 970.1  |
| 47.5° | 777.8  | 800.6  | 853.2  | 910.2  | 926.5  |
| 50°   | 726.1  | 749.8  | 805.9  | 865.8  | 882.1  |
| 52.5° | 679.0  | 699.9  | 761.5  | 816.9  | 824.0  |
| 55°   | 626.4  | 648.3  | 713.5  | 756.0  | 754.2  |
| 57.5° | 573.8  | 598.4  | 663.6  | 689.9  | 682.7  |
| 60°   | 524.9  | 547.6  | 612.9  | 618.4  | 602.8  |
| 62.5° | 470.5  | 496.9  | 552.0  | 544.0  | 524.9  |
| 65°   | 419.7  | 445.2  | 493.2  | 470.5  | 453.2  |
| 67.5° | 368.0  | 395.3  | 429.8  | 396.2  | 376.3  |
| 70°   | 317.3  | 349.9  | 362.7  | 326.4  | 310.1  |
| 72.5° | 265.6  | 300.0  | 299.1  | 264.7  | 251.1  |
| 75°   | 216.6  | 247.4  | 239.4  | 206.7  | 196.7  |
| 77.5° | 164.9  | 195.7  | 180.3  | 156.0  | 146.8  |
| 80°   | 116.9  | 145.9  | 126.1  | 107.0  | 100.6  |
| 82.5° | 79.7   | 97.0   | 78.8   | 62.5   | 59.7   |
| 85°   | 41.8   | 49.9   | 36.3   | 28.0   | 26.2   |
| 87.5° | 15.4   | 14.5   | 12.6   | 11.7   | 11.7   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP3-2508-516-7

Test Date: 09/03/2025

Luminaire Tested: 24CZ-LD5-65-S-UNV-L940-CD1-U

Data in this report applies to families of products including 24CZ-LD5-65-S-UNV-L940-CD1-U

### Test Information

Test Method: LM-79-2019  
 Report Number: SP3-2508-516-7  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP3 - 3M SPHERE  
 Measurement Geometry:  $4\pi$   
 Issue Date: 09/05/2025  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: Metalux  
 Catalog Number: **24CZ-LD5-65-S-UNV-L940-CD1-U**  
 Description: 2X4 CRUZE SB 6500LM 940 SMOOTH LENS

### Spectral Parameters

CCT (K): 3955  
 CIE  $u'$ : 0.2264  
 CIE  $v'$ : 0.5014  
 Duv: -0.0009  
 CIE x: 0.3818  
 CIE y: 0.3758  
 CIE z: 0.2424  
 Peak Wavelength (nm): 630  
 Dominant Wavelength (nm): 579  
 Purity: 27.35334  
 R<sub>f</sub>: 90.3  
 R<sub>g</sub>: 99.3

CRI (Ra): 93.6  
 R1: 95.0  
 R2: 96.2  
 R3: 95.3  
 R4: 94.7  
 R5: 93.8  
 R6: 93.5  
 R7: 94.0  
 R8: 86.7  
 R9: 65.5  
 R10: 88.9  
 R11: 94.8  
 R12: 71.7  
 R13: 95.4  
 R14: 96.7  
 R15: 92.2



### Test Conditions

Stabilization Time: 22M  
 Operation Time: 1H 22M  
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP3-2508-516-7

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | 3M SPHERE IN02505     | 7/1/2025         | 1/1/2026             |
| Power Meter                    | XITRON INXT2011006    | 1/20/2025        | 1/20/2026            |
| AC Power Source                | CHROMA 61604 IN6064A  | 10/22/2024       | 10/22/2025           |
| DC Power Source                | EYSIGHT N5770A IN0534 | 10/22/2024       | 10/22/2025           |
| Sphere Thermometer             | TANDD IN4036E         | 10/22/2024       | 10/22/2025           |
|                                |                       |                  |                      |

REPORT NUMBER: SP3-2508-516-7

**CIE 1931 Chromaticity Diagram**



**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP3-2508-516-7

### Photopic Flux vs. Wavelength



### Photopic Lumens: NR

| λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) |
|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|
| 360       | 0                           | NR               | 490       | 171                         | NR               | 620       | 355                         | NR               | 750       | 8                           | NR               | 880       | 0                           | NR               |
| 365       | 0                           | NR               | 495       | 199                         | NR               | 625       | 352                         | NR               | 755       | 7                           | NR               | 885       | 0                           | NR               |
| 370       | 0                           | NR               | 500       | 230                         | NR               | 630       | 1000                        | NR               | 760       | 6                           | NR               | 890       | 0                           | NR               |
| 375       | 0                           | NR               | 505       | 257                         | NR               | 635       | 711                         | NR               | 765       | 5                           | NR               | 895       | 0                           | NR               |
| 380       | 0                           | NR               | 510       | 278                         | NR               | 640       | 235                         | NR               | 770       | 4                           | NR               | 900       | 0                           | NR               |
| 385       | 0                           | NR               | 515       | 295                         | NR               | 645       | 222                         | NR               | 775       | 4                           | NR               | 905       | 0                           | NR               |
| 390       | 1                           | NR               | 520       | 305                         | NR               | 650       | 198                         | NR               | 780       | 3                           | NR               | 910       | 0                           | NR               |
| 395       | 2                           | NR               | 525       | 313                         | NR               | 655       | 165                         | NR               | 785       | 3                           | NR               | 915       | 0                           | NR               |
| 400       | 3                           | NR               | 530       | 318                         | NR               | 660       | 142                         | NR               | 790       | 2                           | NR               | 920       | 0                           | NR               |
| 405       | 4                           | NR               | 535       | 323                         | NR               | 665       | 120                         | NR               | 795       | 2                           | NR               | 925       | 0                           | NR               |
| 410       | 6                           | NR               | 540       | 327                         | NR               | 670       | 110                         | NR               | 800       | 2                           | NR               | 930       | 0                           | NR               |
| 415       | 9                           | NR               | 545       | 333                         | NR               | 675       | 91                          | NR               | 805       | 2                           | NR               | 935       | 0                           | NR               |
| 420       | 15                          | NR               | 550       | 339                         | NR               | 680       | 77                          | NR               | 810       | 1                           | NR               | 940       | 0                           | NR               |
| 425       | 27                          | NR               | 555       | 343                         | NR               | 685       | 67                          | NR               | 815       | 1                           | NR               | 945       | 0                           | NR               |
| 430       | 48                          | NR               | 560       | 349                         | NR               | 690       | 57                          | NR               | 820       | 1                           | NR               | 950       | 0                           | NR               |
| 435       | 87                          | NR               | 565       | 355                         | NR               | 695       | 49                          | NR               | 825       | 1                           | NR               | 955       | 0                           | NR               |
| 440       | 155                         | NR               | 570       | 358                         | NR               | 700       | 42                          | NR               | 830       | 1                           | NR               | 960       | 0                           | NR               |
| 445       | 291                         | NR               | 575       | 363                         | NR               | 705       | 36                          | NR               | 835       | 1                           | NR               | 965       | 0                           | NR               |
| 450       | 475                         | NR               | 580       | 365                         | NR               | 710       | 30                          | NR               | 840       | 1                           | NR               | 970       | 0                           | NR               |
| 455       | 466                         | NR               | 585       | 367                         | NR               | 715       | 26                          | NR               | 845       | 1                           | NR               | 975       | 0                           | NR               |
| 460       | 308                         | NR               | 590       | 367                         | NR               | 720       | 22                          | NR               | 850       | 0                           | NR               | 980       | 0                           | NR               |
| 465       | 246                         | NR               | 595       | 364                         | NR               | 725       | 19                          | NR               | 855       | 0                           | NR               | 985       | 0                           | NR               |
| 470       | 202                         | NR               | 600       | 363                         | NR               | 730       | 16                          | NR               | 860       | 0                           | NR               | 990       | 0                           | NR               |
| 475       | 152                         | NR               | 605       | 361                         | NR               | 735       | 14                          | NR               | 865       | 0                           | NR               | 995       | 0                           | NR               |
| 480       | 140                         | NR               | 610       | 391                         | NR               | 740       | 11                          | NR               | 870       | 0                           | NR               | 1000      | 0                           | NR               |
| 485       | 152                         | NR               | 615       | 418                         | NR               | 745       | 10                          | NR               | 875       | 0                           | NR               |           |                             |                  |

REPORT NUMBER: SP3-2508-516-7

### Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.77

| $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 0                                    | NR                             | 490               | 171                                  | NR                             | 620               | 355                                  | NR                             | 750               | 8                                    | NR                             | 880               | 0                                    | NR                             |
| 365               | 0                                    | NR                             | 495               | 199                                  | NR                             | 625               | 352                                  | NR                             | 755               | 7                                    | NR                             | 885               | 0                                    | NR                             |
| 370               | 0                                    | NR                             | 500               | 230                                  | NR                             | 630               | 1000                                 | NR                             | 760               | 6                                    | NR                             | 890               | 0                                    | NR                             |
| 375               | 0                                    | NR                             | 505               | 257                                  | NR                             | 635               | 711                                  | NR                             | 765               | 5                                    | NR                             | 895               | 0                                    | NR                             |
| 380               | 0                                    | NR                             | 510               | 278                                  | NR                             | 640               | 235                                  | NR                             | 770               | 4                                    | NR                             | 900               | 0                                    | NR                             |
| 385               | 0                                    | NR                             | 515               | 295                                  | NR                             | 645               | 222                                  | NR                             | 775               | 4                                    | NR                             | 905               | 0                                    | NR                             |
| 390               | 1                                    | NR                             | 520               | 305                                  | NR                             | 650               | 198                                  | NR                             | 780               | 3                                    | NR                             | 910               | 0                                    | NR                             |
| 395               | 2                                    | NR                             | 525               | 313                                  | NR                             | 655               | 165                                  | NR                             | 785               | 3                                    | NR                             | 915               | 0                                    | NR                             |
| 400               | 3                                    | NR                             | 530               | 318                                  | NR                             | 660               | 142                                  | NR                             | 790               | 2                                    | NR                             | 920               | 0                                    | NR                             |
| 405               | 4                                    | NR                             | 535               | 323                                  | NR                             | 665               | 120                                  | NR                             | 795               | 2                                    | NR                             | 925               | 0                                    | NR                             |
| 410               | 6                                    | NR                             | 540               | 327                                  | NR                             | 670               | 110                                  | NR                             | 800               | 2                                    | NR                             | 930               | 0                                    | NR                             |
| 415               | 9                                    | NR                             | 545               | 333                                  | NR                             | 675               | 91                                   | NR                             | 805               | 2                                    | NR                             | 935               | 0                                    | NR                             |
| 420               | 15                                   | NR                             | 550               | 339                                  | NR                             | 680               | 77                                   | NR                             | 810               | 1                                    | NR                             | 940               | 0                                    | NR                             |
| 425               | 27                                   | NR                             | 555               | 343                                  | NR                             | 685               | 67                                   | NR                             | 815               | 1                                    | NR                             | 945               | 0                                    | NR                             |
| 430               | 48                                   | NR                             | 560               | 349                                  | NR                             | 690               | 57                                   | NR                             | 820               | 1                                    | NR                             | 950               | 0                                    | NR                             |
| 435               | 87                                   | NR                             | 565               | 355                                  | NR                             | 695               | 49                                   | NR                             | 825               | 1                                    | NR                             | 955               | 0                                    | NR                             |
| 440               | 155                                  | NR                             | 570               | 358                                  | NR                             | 700               | 42                                   | NR                             | 830               | 1                                    | NR                             | 960               | 0                                    | NR                             |
| 445               | 291                                  | NR                             | 575               | 363                                  | NR                             | 705               | 36                                   | NR                             | 835               | 1                                    | NR                             | 965               | 0                                    | NR                             |
| 450               | 475                                  | NR                             | 580               | 365                                  | NR                             | 710               | 30                                   | NR                             | 840               | 1                                    | NR                             | 970               | 0                                    | NR                             |
| 455               | 466                                  | NR                             | 585               | 367                                  | NR                             | 715               | 26                                   | NR                             | 845               | 1                                    | NR                             | 975               | 0                                    | NR                             |
| 460               | 308                                  | NR                             | 590               | 367                                  | NR                             | 720               | 22                                   | NR                             | 850               | 0                                    | NR                             | 980               | 0                                    | NR                             |
| 465               | 246                                  | NR                             | 595               | 364                                  | NR                             | 725               | 19                                   | NR                             | 855               | 0                                    | NR                             | 985               | 0                                    | NR                             |
| 470               | 202                                  | NR                             | 600               | 363                                  | NR                             | 730               | 16                                   | NR                             | 860               | 0                                    | NR                             | 990               | 0                                    | NR                             |
| 475               | 152                                  | NR                             | 605               | 361                                  | NR                             | 735               | 14                                   | NR                             | 865               | 0                                    | NR                             | 995               | 0                                    | NR                             |
| 480               | 140                                  | NR                             | 610               | 391                                  | NR                             | 740               | 11                                   | NR                             | 870               | 0                                    | NR                             | 1000              | 0                                    | NR                             |
| 485               | 152                                  | NR                             | 615               | 418                                  | NR                             | 745               | 10                                   | NR                             | 875               | 0                                    | NR                             |                   |                                      |                                |

REPORT NUMBER: SP3-2508-516-7

### Melanopic Flux vs. Wavelength


**Melanopic Lumens: NR**
**M/P: 3.69**


| $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 0                                    | NR                             | 490               | 171                                  | NR                             | 620               | 355                                  | NR                             | 750               | 8                                    | NR                             | 880               | 0                                    | NR                             |
| 365               | 0                                    | NR                             | 495               | 199                                  | NR                             | 625               | 352                                  | NR                             | 755               | 7                                    | NR                             | 885               | 0                                    | NR                             |
| 370               | 0                                    | NR                             | 500               | 230                                  | NR                             | 630               | 1000                                 | NR                             | 760               | 6                                    | NR                             | 890               | 0                                    | NR                             |
| 375               | 0                                    | NR                             | 505               | 257                                  | NR                             | 635               | 711                                  | NR                             | 765               | 5                                    | NR                             | 895               | 0                                    | NR                             |
| 380               | 0                                    | NR                             | 510               | 278                                  | NR                             | 640               | 235                                  | NR                             | 770               | 4                                    | NR                             | 900               | 0                                    | NR                             |
| 385               | 0                                    | NR                             | 515               | 295                                  | NR                             | 645               | 222                                  | NR                             | 775               | 4                                    | NR                             | 905               | 0                                    | NR                             |
| 390               | 1                                    | NR                             | 520               | 305                                  | NR                             | 650               | 198                                  | NR                             | 780               | 3                                    | NR                             | 910               | 0                                    | NR                             |
| 395               | 2                                    | NR                             | 525               | 313                                  | NR                             | 655               | 165                                  | NR                             | 785               | 3                                    | NR                             | 915               | 0                                    | NR                             |
| 400               | 3                                    | NR                             | 530               | 318                                  | NR                             | 660               | 142                                  | NR                             | 790               | 2                                    | NR                             | 920               | 0                                    | NR                             |
| 405               | 4                                    | NR                             | 535               | 323                                  | NR                             | 665               | 120                                  | NR                             | 795               | 2                                    | NR                             | 925               | 0                                    | NR                             |
| 410               | 6                                    | NR                             | 540               | 327                                  | NR                             | 670               | 110                                  | NR                             | 800               | 2                                    | NR                             | 930               | 0                                    | NR                             |
| 415               | 9                                    | NR                             | 545               | 333                                  | NR                             | 675               | 91                                   | NR                             | 805               | 2                                    | NR                             | 935               | 0                                    | NR                             |
| 420               | 15                                   | NR                             | 550               | 339                                  | NR                             | 680               | 77                                   | NR                             | 810               | 1                                    | NR                             | 940               | 0                                    | NR                             |
| 425               | 27                                   | NR                             | 555               | 343                                  | NR                             | 685               | 67                                   | NR                             | 815               | 1                                    | NR                             | 945               | 0                                    | NR                             |
| 430               | 48                                   | NR                             | 560               | 349                                  | NR                             | 690               | 57                                   | NR                             | 820               | 1                                    | NR                             | 950               | 0                                    | NR                             |
| 435               | 87                                   | NR                             | 565               | 355                                  | NR                             | 695               | 49                                   | NR                             | 825               | 1                                    | NR                             | 955               | 0                                    | NR                             |
| 440               | 155                                  | NR                             | 570               | 358                                  | NR                             | 700               | 42                                   | NR                             | 830               | 1                                    | NR                             | 960               | 0                                    | NR                             |
| 445               | 291                                  | NR                             | 575               | 363                                  | NR                             | 705               | 36                                   | NR                             | 835               | 1                                    | NR                             | 965               | 0                                    | NR                             |
| 450               | 475                                  | NR                             | 580               | 365                                  | NR                             | 710               | 30                                   | NR                             | 840               | 1                                    | NR                             | 970               | 0                                    | NR                             |
| 455               | 466                                  | NR                             | 585               | 367                                  | NR                             | 715               | 26                                   | NR                             | 845               | 1                                    | NR                             | 975               | 0                                    | NR                             |
| 460               | 308                                  | NR                             | 590               | 367                                  | NR                             | 720               | 22                                   | NR                             | 850               | 0                                    | NR                             | 980               | 0                                    | NR                             |
| 465               | 246                                  | NR                             | 595               | 364                                  | NR                             | 725               | 19                                   | NR                             | 855               | 0                                    | NR                             | 985               | 0                                    | NR                             |
| 470               | 202                                  | NR                             | 600               | 363                                  | NR                             | 730               | 16                                   | NR                             | 860               | 0                                    | NR                             | 990               | 0                                    | NR                             |
| 475               | 152                                  | NR                             | 605               | 361                                  | NR                             | 735               | 14                                   | NR                             | 865               | 0                                    | NR                             | 995               | 0                                    | NR                             |
| 480               | 140                                  | NR                             | 610               | 391                                  | NR                             | 740               | 11                                   | NR                             | 870               | 0                                    | NR                             | 1000              | 0                                    | NR                             |
| 485               | 152                                  | NR                             | 615               | 418                                  | NR                             | 745               | 10                                   | NR                             | 875               | 0                                    | NR                             |                   |                                      |                                |

REPORT NUMBER: SP3-2508-516-7

TM-30-18

### Summary

$R_f = 90.3$   
 $R_g = 99.3$   
 $CIE R_a = 93.6$   
 $R_9 = 65.5$



### Color Vector Graphics



Individual Sample Fidelity Index ( $R_{f,i}$ )

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 93 | CES51 = 97 | CES76 = 85 |
| CES02 = 62 | CES27 = 90 | CES52 = 99 | CES77 = 87 |
| CES03 = 31 | CES28 = 95 | CES53 = 97 | CES78 = 82 |
| CES04 = 69 | CES29 = 96 | CES54 = 92 | CES79 = 93 |
| CES05 = 49 | CES30 = 89 | CES55 = 90 | CES80 = 92 |
| CES06 = 50 | CES31 = 97 | CES56 = 94 | CES81 = 80 |
| CES07 = 42 | CES32 = 89 | CES57 = 92 | CES82 = 96 |
| CES08 = 41 | CES33 = 98 | CES58 = 92 | CES83 = 96 |
| CES09 = 29 | CES34 = 93 | CES59 = 97 | CES84 = 93 |
| CES10 = 74 | CES35 = 95 | CES60 = 91 | CES85 = 80 |
| CES11 = 57 | CES36 = 77 | CES61 = 91 | CES86 = 84 |
| CES12 = 63 | CES37 = 94 | CES62 = 83 | CES87 = 91 |
| CES13 = 43 | CES38 = 83 | CES63 = 91 | CES88 = 98 |
| CES14 = 74 | CES39 = 99 | CES64 = 88 | CES89 = 85 |
| CES15 = 71 | CES40 = 98 | CES65 = 87 | CES90 = 96 |
| CES16 = 47 | CES41 = 96 | CES66 = 84 | CES91 = 70 |
| CES17 = 49 | CES42 = 92 | CES67 = 83 | CES92 = 76 |
| CES18 = 56 | CES43 = 93 | CES68 = 86 | CES93 = 85 |
| CES19 = 71 | CES44 = 99 | CES69 = 87 | CES94 = 76 |
| CES20 = 66 | CES45 = 97 | CES70 = 84 | CES95 = 81 |
| CES21 = 85 | CES46 = 97 | CES71 = 76 | CES96 = 92 |
| CES22 = 78 | CES47 = 94 | CES72 = 93 | CES97 = 95 |
| CES23 = 91 | CES48 = 89 | CES73 = 78 | CES98 = 95 |
| CES24 = 90 | CES49 = 96 | CES74 = 90 | CES99 = 93 |
| CES25 = 71 | CES50 = 98 | CES75 = 79 |            |



Color Rendition by Hue-Angle Bin



**Measure Comparisons**



(END OF REPORT)