

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: METALUX

Report Number: P982774

Luminaire Tested: 22CZ-LD5-24SE-UNV-L935-RDP-CD1-U

Issue Date: 04/23/2025

**Test Information**

Test Method: LM-79-2019  
Report Number: P982774  
Test Lab: INNOVATION CENTER(P3)  
Issue Date: 04/23/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: METALUX  
Catalog Number: 22CZ-LD5-24SE-UNV-L935-RDP-CD1-U  
Description: METALUX CRUZE 2x2 2400LM STANDARD EFFICACY PACKAGE 90CRI 3500K TROFFER LENS WITH FILM INSERT  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1503.1 lumens  
Efficiency: N/A  
Efficacy: 81.3 lumens/watt  
Spacing Criteria (0/90/45): 1.25 / 1.31 / 1.41  
Luminous Opening: Rectangular (W 2' x L: 2' x H: 0')  
CIE Type: Direct

Input Watts (W): 18.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT

TEST NUMBER: P982774

CATALOG NUMBER: 22CZ-LD5-24SE-UNV-L935-RDP-CD1-U

### Luminous Intensity Polar Plot



TEST NUMBER: P982774

CATALOG NUMBER: 22CZ-LD5-24SE-UNV-L935-RDP-CD1-U

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 108 | 103 | 99  | 95  | 105 | 101 | 97  | 93  | 97  | 93  | 90  |  | 93  | 90  | 87  |  | 89  |
| 2   | 98  | 89  | 82  | 76  | 95  | 87  | 81  | 75  | 84  | 78  | 73  |  | 80  | 76  | 71  |  | 77  |
| 3   | 89  | 78  | 69  | 62  | 86  | 76  | 68  | 62  | 73  | 66  | 61  |  | 70  | 64  | 59  |  | 68  |
| 4   | 81  | 68  | 59  | 52  | 79  | 67  | 58  | 52  | 64  | 57  | 51  |  | 62  | 56  | 50  |  | 60  |
| 5   | 74  | 61  | 52  | 45  | 72  | 60  | 51  | 44  | 58  | 50  | 44  |  | 56  | 49  | 43  |  | 54  |
| 6   | 68  | 55  | 45  | 39  | 66  | 54  | 45  | 39  | 52  | 44  | 38  |  | 50  | 43  | 38  |  | 48  |
| 7   | 63  | 49  | 40  | 34  | 62  | 49  | 40  | 34  | 47  | 39  | 34  |  | 45  | 39  | 33  |  | 44  |
| 8   | 59  | 45  | 36  | 30  | 57  | 44  | 36  | 30  | 43  | 35  | 30  |  | 42  | 35  | 30  |  | 40  |
| 9   | 55  | 41  | 33  | 27  | 54  | 41  | 33  | 27  | 39  | 32  | 27  |  | 38  | 32  | 27  |  | 37  |
| 10  | 51  | 38  | 30  | 24  | 50  | 37  | 30  | 24  | 36  | 29  | 24  |  | 35  | 29  | 24  |  | 35  |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°   | 45°  | 90°  |
|-----|------|------|------|
| 0°  | 1285 | 1285 | 1285 |
| 5°  | 1287 | 1296 | 1280 |
| 10° | 1282 | 1282 | 1282 |
| 15° | 1278 | 1285 | 1291 |
| 20° | 1273 | 1287 | 1294 |
| 25° | 1258 | 1279 | 1296 |
| 30° | 1248 | 1269 | 1306 |
| 35° | 1235 | 1269 | 1323 |
| 40° | 1222 | 1271 | 1353 |
| 45° | 1200 | 1275 | 1404 |
| 50° | 1173 | 1285 | 1471 |
| 55° | 1133 | 1320 | 1550 |
| 60° | 1081 | 1357 | 1640 |
| 65° | 1019 | 1405 | 1732 |
| 70° | 909  | 1442 | 1810 |
| 75° | 789  | 1444 | 1432 |
| 80° | 669  | 1068 | 1158 |
| 85° | 577  | 719  | 648  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°

Vertical Angle: 70°

Luminance: 1810 cd/sqm

TEST NUMBER: P982774

CATALOG NUMBER: 22CZ-LD5-24SE-UNV-L935-RDP-CD1-U

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 45.3   | 3.0       |
| 10°-20°   | 130.2  | 8.7       |
| 20°-30°   | 198.4  | 13.2      |
| 30°-40°   | 242.7  | 16.1      |
| 40°-50°   | 261.2  | 17.4      |
| 50°-60°   | 253.0  | 16.8      |
| 60°-70°   | 214.3  | 14.3      |
| 70°-80°   | 129.5  | 8.6       |
| 80°-90°   | 28.5   | 1.9       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 373.9  | 24.9      |
| 0°-40°    | 616.6  | 41.0      |
| 0°-60°    | 1130.8 | 75.2      |
| 0°-90°    | 1503.1 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1503.1 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | 22.5° | 45° | 67.5° | 90° | Flux |
|-----|-----|-------|-----|-------|-----|------|
| 0°  | 478 | 478   | 478 | 478   | 478 |      |
| 5°  | 476 | 476   | 480 | 478   | 474 | 45   |
| 15° | 459 | 460   | 461 | 462   | 463 | 130  |
| 25° | 424 | 426   | 431 | 434   | 436 | 196  |
| 35° | 376 | 378   | 386 | 397   | 403 | 235  |
| 45° | 315 | 321   | 335 | 356   | 369 | 243  |
| 55° | 242 | 252   | 281 | 314   | 330 | 216  |
| 65° | 160 | 177   | 221 | 256   | 272 | 157  |
| 75° | 76  | 103   | 139 | 141   | 138 | 82   |
| 85° | 19  | 22    | 23  | 22    | 21  | 21   |
| 90° | 0   | 0     | 0   | 0     | 0   |      |

TEST NUMBER: P982774

CATALOG NUMBER: 22CZ-LD5-24SE-UNV-L935-RDP-CD1-U

**CANDELA DISTRIBUTION (FULL):**

|       | 0°    | 22.5° | 45°   | 67.5° | 90°   |
|-------|-------|-------|-------|-------|-------|
| 0°    | 477.5 | 477.5 | 477.5 | 477.5 | 477.5 |
| 2.5°  | 483.2 | 482.2 | 478.6 | 476.3 | 473.9 |
| 5°    | 476.3 | 476.3 | 479.8 | 477.5 | 473.9 |
| 7.5°  | 472.8 | 472.8 | 472.8 | 478.6 | 472.8 |
| 10°   | 469.3 | 470.4 | 469.3 | 473.9 | 469.3 |
| 12.5° | 465.7 | 465.7 | 465.7 | 466.9 | 466.9 |
| 15°   | 458.7 | 459.9 | 461.1 | 462.2 | 463.4 |
| 17.5° | 451.8 | 453.0 | 455.3 | 456.5 | 457.6 |
| 20°   | 444.7 | 445.9 | 449.4 | 449.4 | 451.8 |
| 22.5° | 435.4 | 435.4 | 440.1 | 441.2 | 444.7 |
| 25°   | 423.8 | 426.1 | 430.8 | 434.2 | 436.5 |
| 27.5° | 413.2 | 415.5 | 420.2 | 424.9 | 428.4 |
| 30°   | 401.6 | 403.9 | 408.5 | 415.5 | 420.2 |
| 32.5° | 388.7 | 391.0 | 398.1 | 406.3 | 410.9 |
| 35°   | 375.9 | 378.2 | 386.3 | 396.9 | 402.8 |
| 37.5° | 361.8 | 365.3 | 374.7 | 386.3 | 393.4 |
| 40°   | 347.9 | 351.4 | 361.8 | 374.7 | 385.2 |
| 42.5° | 331.6 | 336.1 | 347.9 | 365.3 | 377.1 |
| 45°   | 315.2 | 321.0 | 335.0 | 356.1 | 368.9 |
| 47.5° | 297.7 | 303.5 | 319.8 | 346.7 | 360.7 |
| 50°   | 280.2 | 287.1 | 307.0 | 336.1 | 351.4 |
| 52.5° | 261.4 | 268.5 | 294.2 | 325.7 | 342.0 |
| 55°   | 241.6 | 252.2 | 281.4 | 314.0 | 330.4 |
| 57.5° | 221.8 | 233.5 | 266.1 | 301.2 | 318.7 |
| 60°   | 200.8 | 214.8 | 252.2 | 287.1 | 304.7 |
| 62.5° | 181.0 | 196.1 | 236.9 | 272.0 | 289.5 |
| 65°   | 160.0 | 177.4 | 220.6 | 255.7 | 272.0 |
| 67.5° | 137.7 | 160.0 | 202.0 | 235.8 | 252.2 |
| 70°   | 115.5 | 141.2 | 183.3 | 214.8 | 230.0 |
| 72.5° | 95.7  | 122.6 | 162.2 | 189.1 | 189.1 |
| 75°   | 75.9  | 102.7 | 138.9 | 141.2 | 137.7 |
| 77.5° | 58.4  | 84.1  | 108.6 | 99.2  | 101.6 |
| 80°   | 43.2  | 64.2  | 68.9  | 72.4  | 74.7  |
| 82.5° | 29.2  | 43.2  | 44.3  | 46.7  | 46.7  |
| 85°   | 18.7  | 22.2  | 23.3  | 22.2  | 21.0  |
| 87.5° | 8.2   | 9.4   | 7.0   | 4.7   | 3.5   |
| 90°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP3-2508-516-6

Test Date: 09/03/2025

Luminaire Tested: 24CZ-LD5-65-S-UNV-L935-CD1-U

Data in this report applies to families of products including 24CZ-LD5-65-S-UNV-L935-CD1-U

### Test Information

Test Method: LM-79-2019  
 Report Number: SP3-2508-516-6  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP3 - 3M SPHERE  
 Measurement Geometry:  $4\pi$   
 Issue Date: 09/05/2025  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: Metalux  
 Catalog Number: **24CZ-LD5-65-S-UNV-L935-CD1-U**  
 Description: 2X4 CRUZE SB 6500LM 935 SMOOTH LENS

### Spectral Parameters

CCT (K): 3412  
 CIE  $u'$ : 0.2386  
 CIE  $v'$ : 0.5111  
 Duv: -0.0015  
 CIE x: 0.4087  
 CIE y: 0.3890  
 CIE z: 0.2023  
 Peak Wavelength (nm): 630  
 Dominant Wavelength (nm): 581  
 Purity: 39.41044  
 R<sub>f</sub>: 92.6  
 R<sub>g</sub>: 102

CRI (Ra): 96.3  
 R1: 99.2  
 R2: 97.9  
 R3: 94.7  
 R4: 96.6  
 R5: 98.4  
 R6: 96.1  
 R7: 95.6  
 R8: 92.0  
 R9: 78.4  
 R10: 93.0  
 R11: 94.5  
 R12: 81.5  
 R13: 99.0  
 R14: 95.8  
 R15: 96.7



### Test Conditions

Stabilization Time: 20M  
 Operation Time: 1H 20M  
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP3-2508-516-6

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | 3M SPHERE IN02505     | 7/1/2025         | 1/1/2026             |
| Power Meter                    | XITRON INXT2011006    | 1/20/2025        | 1/20/2026            |
| AC Power Source                | CHROMA 61604 IN6064A  | 10/22/2024       | 10/22/2025           |
| DC Power Source                | EYSIGHT N5770A IN0534 | 10/22/2024       | 10/22/2025           |
| Sphere Thermometer             | TANDD IN4036E         | 10/22/2024       | 10/22/2025           |
|                                |                       |                  |                      |

REPORT NUMBER: SP3-2508-516-6

**CIE 1931 Chromaticity Diagram**



**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP3-2508-516-6

### Photopic Flux vs. Wavelength



### Photopic Lumens: NR

| $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 0                                    | NR                             | 490               | 112                                  | NR                             | 620               | 281                                  | NR                             | 750               | 6                                    | NR                             | 880               | 0                                    | NR                             |
| 365               | 0                                    | NR                             | 495               | 134                                  | NR                             | 625               | 286                                  | NR                             | 755               | 5                                    | NR                             | 885               | 0                                    | NR                             |
| 370               | 0                                    | NR                             | 500               | 157                                  | NR                             | 630               | 1000                                 | NR                             | 760               | 4                                    | NR                             | 890               | 0                                    | NR                             |
| 375               | 0                                    | NR                             | 505               | 178                                  | NR                             | 635               | 695                                  | NR                             | 765               | 4                                    | NR                             | 895               | 0                                    | NR                             |
| 380               | 0                                    | NR                             | 510               | 193                                  | NR                             | 640               | 181                                  | NR                             | 770               | 3                                    | NR                             | 900               | 0                                    | NR                             |
| 385               | 0                                    | NR                             | 515               | 206                                  | NR                             | 645               | 175                                  | NR                             | 775               | 3                                    | NR                             | 905               | 0                                    | NR                             |
| 390               | 0                                    | NR                             | 520               | 213                                  | NR                             | 650               | 156                                  | NR                             | 780               | 2                                    | NR                             | 910               | 0                                    | NR                             |
| 395               | 1                                    | NR                             | 525               | 219                                  | NR                             | 655               | 127                                  | NR                             | 785               | 2                                    | NR                             | 915               | 0                                    | NR                             |
| 400               | 2                                    | NR                             | 530               | 223                                  | NR                             | 660               | 108                                  | NR                             | 790               | 2                                    | NR                             | 920               | 0                                    | NR                             |
| 405               | 2                                    | NR                             | 535               | 226                                  | NR                             | 665               | 89                                   | NR                             | 795               | 2                                    | NR                             | 925               | 0                                    | NR                             |
| 410               | 4                                    | NR                             | 540               | 230                                  | NR                             | 670               | 84                                   | NR                             | 800               | 1                                    | NR                             | 930               | 0                                    | NR                             |
| 415               | 6                                    | NR                             | 545               | 235                                  | NR                             | 675               | 67                                   | NR                             | 805               | 1                                    | NR                             | 935               | 0                                    | NR                             |
| 420               | 11                                   | NR                             | 550               | 239                                  | NR                             | 680               | 57                                   | NR                             | 810               | 1                                    | NR                             | 940               | 0                                    | NR                             |
| 425               | 19                                   | NR                             | 555               | 243                                  | NR                             | 685               | 50                                   | NR                             | 815               | 1                                    | NR                             | 945               | 0                                    | NR                             |
| 430               | 34                                   | NR                             | 560               | 248                                  | NR                             | 690               | 42                                   | NR                             | 820               | 1                                    | NR                             | 950               | 0                                    | NR                             |
| 435               | 60                                   | NR                             | 565               | 253                                  | NR                             | 695               | 36                                   | NR                             | 825               | 1                                    | NR                             | 955               | 0                                    | NR                             |
| 440               | 106                                  | NR                             | 570               | 256                                  | NR                             | 700               | 31                                   | NR                             | 830               | 0                                    | NR                             | 960               | 0                                    | NR                             |
| 445               | 193                                  | NR                             | 575               | 260                                  | NR                             | 705               | 26                                   | NR                             | 835               | 0                                    | NR                             | 965               | 0                                    | NR                             |
| 450               | 283                                  | NR                             | 580               | 263                                  | NR                             | 710               | 22                                   | NR                             | 840               | 0                                    | NR                             | 970               | 0                                    | NR                             |
| 455               | 234                                  | NR                             | 585               | 266                                  | NR                             | 715               | 19                                   | NR                             | 845               | 0                                    | NR                             | 975               | 0                                    | NR                             |
| 460               | 157                                  | NR                             | 590               | 267                                  | NR                             | 720               | 16                                   | NR                             | 850               | 0                                    | NR                             | 980               | 0                                    | NR                             |
| 465               | 134                                  | NR                             | 595               | 266                                  | NR                             | 725               | 14                                   | NR                             | 855               | 0                                    | NR                             | 985               | 0                                    | NR                             |
| 470               | 107                                  | NR                             | 600               | 268                                  | NR                             | 730               | 12                                   | NR                             | 860               | 0                                    | NR                             | 990               | 0                                    | NR                             |
| 475               | 85                                   | NR                             | 605               | 269                                  | NR                             | 735               | 10                                   | NR                             | 865               | 0                                    | NR                             | 995               | 0                                    | NR                             |
| 480               | 85                                   | NR                             | 610               | 309                                  | NR                             | 740               | 8                                    | NR                             | 870               | 0                                    | NR                             | 1000              | 0                                    | NR                             |
| 485               | 96                                   | NR                             | 615               | 345                                  | NR                             | 745               | 7                                    | NR                             | 875               | 0                                    | NR                             |                   |                                      |                                |

REPORT NUMBER: SP3-2508-516-6

### Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.61

| λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360    | 0                        | NR            | 490    | 112                      | NR            | 620    | 281                      | NR            | 750    | 6                        | NR            | 880    | 0                        | NR            |
| 365    | 0                        | NR            | 495    | 134                      | NR            | 625    | 286                      | NR            | 755    | 5                        | NR            | 885    | 0                        | NR            |
| 370    | 0                        | NR            | 500    | 157                      | NR            | 630    | 1000                     | NR            | 760    | 4                        | NR            | 890    | 0                        | NR            |
| 375    | 0                        | NR            | 505    | 178                      | NR            | 635    | 695                      | NR            | 765    | 4                        | NR            | 895    | 0                        | NR            |
| 380    | 0                        | NR            | 510    | 193                      | NR            | 640    | 181                      | NR            | 770    | 3                        | NR            | 900    | 0                        | NR            |
| 385    | 0                        | NR            | 515    | 206                      | NR            | 645    | 175                      | NR            | 775    | 3                        | NR            | 905    | 0                        | NR            |
| 390    | 0                        | NR            | 520    | 213                      | NR            | 650    | 156                      | NR            | 780    | 2                        | NR            | 910    | 0                        | NR            |
| 395    | 1                        | NR            | 525    | 219                      | NR            | 655    | 127                      | NR            | 785    | 2                        | NR            | 915    | 0                        | NR            |
| 400    | 2                        | NR            | 530    | 223                      | NR            | 660    | 108                      | NR            | 790    | 2                        | NR            | 920    | 0                        | NR            |
| 405    | 2                        | NR            | 535    | 226                      | NR            | 665    | 89                       | NR            | 795    | 2                        | NR            | 925    | 0                        | NR            |
| 410    | 4                        | NR            | 540    | 230                      | NR            | 670    | 84                       | NR            | 800    | 1                        | NR            | 930    | 0                        | NR            |
| 415    | 6                        | NR            | 545    | 235                      | NR            | 675    | 67                       | NR            | 805    | 1                        | NR            | 935    | 0                        | NR            |
| 420    | 11                       | NR            | 550    | 239                      | NR            | 680    | 57                       | NR            | 810    | 1                        | NR            | 940    | 0                        | NR            |
| 425    | 19                       | NR            | 555    | 243                      | NR            | 685    | 50                       | NR            | 815    | 1                        | NR            | 945    | 0                        | NR            |
| 430    | 34                       | NR            | 560    | 248                      | NR            | 690    | 42                       | NR            | 820    | 1                        | NR            | 950    | 0                        | NR            |
| 435    | 60                       | NR            | 565    | 253                      | NR            | 695    | 36                       | NR            | 825    | 1                        | NR            | 955    | 0                        | NR            |
| 440    | 106                      | NR            | 570    | 256                      | NR            | 700    | 31                       | NR            | 830    | 0                        | NR            | 960    | 0                        | NR            |
| 445    | 193                      | NR            | 575    | 260                      | NR            | 705    | 26                       | NR            | 835    | 0                        | NR            | 965    | 0                        | NR            |
| 450    | 283                      | NR            | 580    | 263                      | NR            | 710    | 22                       | NR            | 840    | 0                        | NR            | 970    | 0                        | NR            |
| 455    | 234                      | NR            | 585    | 266                      | NR            | 715    | 19                       | NR            | 845    | 0                        | NR            | 975    | 0                        | NR            |
| 460    | 157                      | NR            | 590    | 267                      | NR            | 720    | 16                       | NR            | 850    | 0                        | NR            | 980    | 0                        | NR            |
| 465    | 134                      | NR            | 595    | 266                      | NR            | 725    | 14                       | NR            | 855    | 0                        | NR            | 985    | 0                        | NR            |
| 470    | 107                      | NR            | 600    | 268                      | NR            | 730    | 12                       | NR            | 860    | 0                        | NR            | 990    | 0                        | NR            |
| 475    | 85                       | NR            | 605    | 269                      | NR            | 735    | 10                       | NR            | 865    | 0                        | NR            | 995    | 0                        | NR            |
| 480    | 85                       | NR            | 610    | 309                      | NR            | 740    | 8                        | NR            | 870    | 0                        | NR            | 1000   | 0                        | NR            |
| 485    | 96                       | NR            | 615    | 345                      | NR            | 745    | 7                        | NR            | 875    | 0                        | NR            |        |                          |               |

REPORT NUMBER: SP3-2508-516-6

### Melanopic Flux vs. Wavelength


**Melanopic Lumens: NR**
**M/P: 3.24**

| $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|
| 360               | 0                                      | NR                             | 490               | 112                                    | NR                             | 620               | 281                                    | NR                             | 750               | 6                                      | NR                             | 880               | 0                                      | NR                             |
| 365               | 0                                      | NR                             | 495               | 134                                    | NR                             | 625               | 286                                    | NR                             | 755               | 5                                      | NR                             | 885               | 0                                      | NR                             |
| 370               | 0                                      | NR                             | 500               | 157                                    | NR                             | 630               | 1000                                   | NR                             | 760               | 4                                      | NR                             | 890               | 0                                      | NR                             |
| 375               | 0                                      | NR                             | 505               | 178                                    | NR                             | 635               | 695                                    | NR                             | 765               | 4                                      | NR                             | 895               | 0                                      | NR                             |
| 380               | 0                                      | NR                             | 510               | 193                                    | NR                             | 640               | 181                                    | NR                             | 770               | 3                                      | NR                             | 900               | 0                                      | NR                             |
| 385               | 0                                      | NR                             | 515               | 206                                    | NR                             | 645               | 175                                    | NR                             | 775               | 3                                      | NR                             | 905               | 0                                      | NR                             |
| 390               | 0                                      | NR                             | 520               | 213                                    | NR                             | 650               | 156                                    | NR                             | 780               | 2                                      | NR                             | 910               | 0                                      | NR                             |
| 395               | 1                                      | NR                             | 525               | 219                                    | NR                             | 655               | 127                                    | NR                             | 785               | 2                                      | NR                             | 915               | 0                                      | NR                             |
| 400               | 2                                      | NR                             | 530               | 223                                    | NR                             | 660               | 108                                    | NR                             | 790               | 2                                      | NR                             | 920               | 0                                      | NR                             |
| 405               | 2                                      | NR                             | 535               | 226                                    | NR                             | 665               | 89                                     | NR                             | 795               | 2                                      | NR                             | 925               | 0                                      | NR                             |
| 410               | 4                                      | NR                             | 540               | 230                                    | NR                             | 670               | 84                                     | NR                             | 800               | 1                                      | NR                             | 930               | 0                                      | NR                             |
| 415               | 6                                      | NR                             | 545               | 235                                    | NR                             | 675               | 67                                     | NR                             | 805               | 1                                      | NR                             | 935               | 0                                      | NR                             |
| 420               | 11                                     | NR                             | 550               | 239                                    | NR                             | 680               | 57                                     | NR                             | 810               | 1                                      | NR                             | 940               | 0                                      | NR                             |
| 425               | 19                                     | NR                             | 555               | 243                                    | NR                             | 685               | 50                                     | NR                             | 815               | 1                                      | NR                             | 945               | 0                                      | NR                             |
| 430               | 34                                     | NR                             | 560               | 248                                    | NR                             | 690               | 42                                     | NR                             | 820               | 1                                      | NR                             | 950               | 0                                      | NR                             |
| 435               | 60                                     | NR                             | 565               | 253                                    | NR                             | 695               | 36                                     | NR                             | 825               | 1                                      | NR                             | 955               | 0                                      | NR                             |
| 440               | 106                                    | NR                             | 570               | 256                                    | NR                             | 700               | 31                                     | NR                             | 830               | 0                                      | NR                             | 960               | 0                                      | NR                             |
| 445               | 193                                    | NR                             | 575               | 260                                    | NR                             | 705               | 26                                     | NR                             | 835               | 0                                      | NR                             | 965               | 0                                      | NR                             |
| 450               | 283                                    | NR                             | 580               | 263                                    | NR                             | 710               | 22                                     | NR                             | 840               | 0                                      | NR                             | 970               | 0                                      | NR                             |
| 455               | 234                                    | NR                             | 585               | 266                                    | NR                             | 715               | 19                                     | NR                             | 845               | 0                                      | NR                             | 975               | 0                                      | NR                             |
| 460               | 157                                    | NR                             | 590               | 267                                    | NR                             | 720               | 16                                     | NR                             | 850               | 0                                      | NR                             | 980               | 0                                      | NR                             |
| 465               | 134                                    | NR                             | 595               | 266                                    | NR                             | 725               | 14                                     | NR                             | 855               | 0                                      | NR                             | 985               | 0                                      | NR                             |
| 470               | 107                                    | NR                             | 600               | 268                                    | NR                             | 730               | 12                                     | NR                             | 860               | 0                                      | NR                             | 990               | 0                                      | NR                             |
| 475               | 85                                     | NR                             | 605               | 269                                    | NR                             | 735               | 10                                     | NR                             | 865               | 0                                      | NR                             | 995               | 0                                      | NR                             |
| 480               | 85                                     | NR                             | 610               | 309                                    | NR                             | 740               | 8                                      | NR                             | 870               | 0                                      | NR                             | 1000              | 0                                      | NR                             |
| 485               | 96                                     | NR                             | 615               | 345                                    | NR                             | 745               | 7                                      | NR                             | 875               | 0                                      | NR                             |                   |                                        |                                |

REPORT NUMBER: SP3-2508-516-6

TM-30-18

### Summary

$R_f = 92.6$   
 $R_g = 102$   
 $\text{CIE } R_a = 96.3$   
 $R_9 = 78.4$



### Color Vector Graphics



**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |             |            |
|------------|------------|-------------|------------|
| CES01 = 86 | CES26 = 94 | CES51 = 97  | CES76 = 88 |
| CES02 = 63 | CES27 = 93 | CES52 = 96  | CES77 = 88 |
| CES03 = 32 | CES28 = 96 | CES53 = 95  | CES78 = 84 |
| CES04 = 70 | CES29 = 95 | CES54 = 95  | CES79 = 92 |
| CES05 = 50 | CES30 = 96 | CES55 = 95  | CES80 = 92 |
| CES06 = 51 | CES31 = 95 | CES56 = 98  | CES81 = 77 |
| CES07 = 43 | CES32 = 87 | CES57 = 98  | CES82 = 96 |
| CES08 = 42 | CES33 = 97 | CES58 = 98  | CES83 = 95 |
| CES09 = 29 | CES34 = 93 | CES59 = 100 | CES84 = 95 |
| CES10 = 75 | CES35 = 96 | CES60 = 94  | CES85 = 82 |
| CES11 = 58 | CES36 = 84 | CES61 = 95  | CES86 = 84 |
| CES12 = 64 | CES37 = 93 | CES62 = 90  | CES87 = 92 |
| CES13 = 44 | CES38 = 91 | CES63 = 95  | CES88 = 99 |
| CES14 = 74 | CES39 = 98 | CES64 = 95  | CES89 = 86 |
| CES15 = 72 | CES40 = 96 | CES65 = 92  | CES90 = 98 |
| CES16 = 48 | CES41 = 97 | CES66 = 93  | CES91 = 77 |
| CES17 = 49 | CES42 = 90 | CES67 = 92  | CES92 = 81 |
| CES18 = 56 | CES43 = 91 | CES68 = 91  | CES93 = 88 |
| CES19 = 71 | CES44 = 99 | CES69 = 92  | CES94 = 78 |
| CES20 = 67 | CES45 = 94 | CES70 = 89  | CES95 = 86 |
| CES21 = 86 | CES46 = 95 | CES71 = 85  | CES96 = 93 |
| CES22 = 78 | CES47 = 90 | CES72 = 95  | CES97 = 93 |
| CES23 = 91 | CES48 = 96 | CES73 = 84  | CES98 = 96 |
| CES24 = 90 | CES49 = 93 | CES74 = 91  | CES99 = 97 |
| CES25 = 71 | CES50 = 97 | CES75 = 86  |            |



**Color Rendition by Hue-Angle Bin**


**Measure Comparisons**


(END OF REPORT)