

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: METALUX

Report Number: P983080

Luminaire Tested: 24CZ-LD5-70-UNV-L930-RDP-CD1-U

Issue Date: 04/23/2025

**Test Information**

Test Method: LM-79-2019  
Report Number: P983080  
Test Lab: INNOVATION CENTER(P3)  
Issue Date: 04/23/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: METALUX  
Catalog Number: 24CZ-LD5-70-UNV-L930-RDP-CD1-U  
Description: METALUX CRUZE 2x4 7000LM PACKAGE 90CRI 3000K TROFFER LENS WITH RDP FILM INSERT  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4350.9 lumens  
Efficiency: N/A  
Efficacy: 88.3 lumens/watt  
Spacing Criteria (0/90/45): 1.25 / 1.31 / 1.41  
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')  
CIE Type: Direct

Input Watts (W): 49.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT

TEST NUMBER: P983080

CATALOG NUMBER: 24CZ-LD5-70-UNV-L930-RDP-CD1-U

### Luminous Intensity Polar Plot



TEST NUMBER: P983080

CATALOG NUMBER: 24CZ-LD5-70-UNV-L930-RDP-CD1-U

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |     |     |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |     |     | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 | 100 |
| 1   | 108 | 103 | 99  | 95  | 105 | 101 | 97  | 93  | 97  | 93  | 90  |  | 93  | 90  | 87  |  | 89  | 87  | 85  | 83  |
| 2   | 98  | 89  | 82  | 76  | 95  | 87  | 81  | 75  | 84  | 78  | 73  |  | 80  | 76  | 71  |  | 77  | 73  | 70  | 68  |
| 3   | 89  | 78  | 69  | 62  | 86  | 76  | 68  | 62  | 73  | 66  | 61  |  | 70  | 64  | 59  |  | 68  | 63  | 58  | 56  |
| 4   | 81  | 68  | 59  | 52  | 79  | 67  | 58  | 52  | 64  | 57  | 51  |  | 62  | 56  | 50  |  | 60  | 54  | 50  | 47  |
| 5   | 74  | 61  | 52  | 45  | 72  | 60  | 51  | 44  | 58  | 50  | 44  |  | 56  | 49  | 43  |  | 54  | 48  | 43  | 41  |
| 6   | 68  | 55  | 45  | 39  | 66  | 54  | 45  | 39  | 52  | 44  | 38  |  | 50  | 43  | 38  |  | 48  | 42  | 37  | 35  |
| 7   | 63  | 49  | 40  | 34  | 62  | 49  | 40  | 34  | 47  | 39  | 34  |  | 45  | 39  | 33  |  | 44  | 38  | 33  | 31  |
| 8   | 59  | 45  | 36  | 30  | 57  | 44  | 36  | 30  | 43  | 35  | 30  |  | 42  | 35  | 30  |  | 40  | 34  | 29  | 28  |
| 9   | 55  | 41  | 33  | 27  | 54  | 41  | 33  | 27  | 39  | 32  | 27  |  | 38  | 32  | 27  |  | 37  | 31  | 27  | 25  |
| 10  | 51  | 38  | 30  | 24  | 50  | 37  | 30  | 24  | 36  | 29  | 24  |  | 35  | 29  | 24  |  | 35  | 28  | 24  | 22  |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°   | 45°  | 90°  |
|-----|------|------|------|
| 0°  | 1859 | 1859 | 1859 |
| 5°  | 1862 | 1876 | 1853 |
| 10° | 1856 | 1856 | 1856 |
| 15° | 1850 | 1859 | 1869 |
| 20° | 1843 | 1863 | 1872 |
| 25° | 1821 | 1851 | 1876 |
| 30° | 1806 | 1837 | 1890 |
| 35° | 1787 | 1837 | 1915 |
| 40° | 1769 | 1840 | 1958 |
| 45° | 1736 | 1845 | 2032 |
| 50° | 1697 | 1860 | 2129 |
| 55° | 1641 | 1910 | 2243 |
| 60° | 1564 | 1964 | 2373 |
| 65° | 1474 | 2033 | 2507 |
| 70° | 1316 | 2087 | 2618 |
| 75° | 1142 | 2090 | 2073 |
| 80° | 969  | 1544 | 1675 |
| 85° | 835  | 1044 | 939  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°

Vertical Angle: 70°

Luminance: 2618 cd/sqm

TEST NUMBER: P983080

CATALOG NUMBER: 24CZ-LD5-70-UNV-L930-RDP-CD1-U

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 131.2  | 3.0       |
| 10°-20°   | 376.8  | 8.7       |
| 20°-30°   | 574.2  | 13.2      |
| 30°-40°   | 702.6  | 16.1      |
| 40°-50°   | 756.0  | 17.4      |
| 50°-60°   | 732.3  | 16.8      |
| 60°-70°   | 620.4  | 14.3      |
| 70°-80°   | 375.0  | 8.6       |
| 80°-90°   | 82.4   | 1.9       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1082.3 | 24.9      |
| 0°-40°    | 1784.9 | 41.0      |
| 0°-60°    | 3273.2 | 75.2      |
| 0°-90°    | 4350.9 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 4350.9 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | 22.5° | 45°  | 67.5° | 90°  | Flux |
|-----|------|-------|------|-------|------|------|
| 0°  | 1382 | 1382  | 1382 | 1382  | 1382 |      |
| 5°  | 1379 | 1379  | 1389 | 1382  | 1372 | 131  |
| 15° | 1328 | 1331  | 1335 | 1338  | 1342 | 375  |
| 25° | 1226 | 1233  | 1247 | 1257  | 1264 | 566  |
| 35° | 1088 | 1095  | 1118 | 1149  | 1166 | 681  |
| 45° | 912  | 929   | 970  | 1030  | 1068 | 703  |
| 55° | 699  | 730   | 814  | 909   | 956  | 625  |
| 65° | 463  | 514   | 639  | 740   | 787  | 456  |
| 75° | 220  | 297   | 402  | 409   | 399  | 236  |
| 85° | 54   | 64    | 68   | 64    | 61   | 61   |
| 90° | 0    | 0     | 0    | 0     | 0    |      |

TEST NUMBER: P983080

CATALOG NUMBER: 24CZ-LD5-70-UNV-L930-RDP-CD1-U

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 22.5°  | 45°    | 67.5°  | 90°    |
|-------|--------|--------|--------|--------|--------|
| 0°    | 1382.0 | 1382.0 | 1382.0 | 1382.0 | 1382.0 |
| 2.5°  | 1398.9 | 1395.5 | 1385.3 | 1378.6 | 1371.8 |
| 5°    | 1378.6 | 1378.6 | 1388.7 | 1382.0 | 1371.8 |
| 7.5°  | 1368.4 | 1368.4 | 1368.4 | 1385.3 | 1368.4 |
| 10°   | 1358.4 | 1361.7 | 1358.4 | 1371.8 | 1358.4 |
| 12.5° | 1348.2 | 1348.2 | 1348.2 | 1351.5 | 1351.5 |
| 15°   | 1327.9 | 1331.3 | 1334.6 | 1338.0 | 1341.5 |
| 17.5° | 1307.7 | 1311.0 | 1317.7 | 1321.2 | 1324.6 |
| 20°   | 1287.4 | 1290.8 | 1300.8 | 1300.8 | 1307.7 |
| 22.5° | 1260.3 | 1260.3 | 1273.9 | 1277.2 | 1287.4 |
| 25°   | 1226.5 | 1233.3 | 1246.8 | 1257.0 | 1263.7 |
| 27.5° | 1196.2 | 1202.9 | 1216.4 | 1229.9 | 1240.1 |
| 30°   | 1162.4 | 1169.1 | 1182.6 | 1202.9 | 1216.4 |
| 32.5° | 1125.2 | 1131.9 | 1152.2 | 1175.8 | 1189.4 |
| 35°   | 1088.0 | 1094.8 | 1118.4 | 1148.8 | 1165.7 |
| 37.5° | 1047.4 | 1057.6 | 1084.6 | 1118.4 | 1138.7 |
| 40°   | 1006.9 | 1017.1 | 1047.4 | 1084.6 | 1115.0 |
| 42.5° | 959.6  | 973.1  | 1006.9 | 1057.6 | 1091.4 |
| 45°   | 912.3  | 929.2  | 969.7  | 1030.5 | 1067.7 |
| 47.5° | 861.6  | 878.5  | 925.9  | 1003.5 | 1044.1 |
| 50°   | 810.9  | 831.2  | 888.6  | 973.1  | 1017.1 |
| 52.5° | 756.9  | 777.1  | 851.5  | 942.7  | 990.0  |
| 55°   | 699.4  | 729.9  | 814.3  | 909.0  | 956.2  |
| 57.5° | 642.0  | 675.8  | 770.4  | 871.8  | 922.4  |
| 60°   | 581.1  | 621.8  | 729.9  | 831.2  | 881.9  |
| 62.5° | 523.7  | 567.7  | 685.9  | 787.3  | 838.0  |
| 65°   | 462.9  | 513.6  | 638.7  | 740.0  | 787.3  |
| 67.5° | 398.7  | 462.9  | 584.6  | 682.5  | 729.9  |
| 70°   | 334.5  | 408.9  | 530.5  | 621.8  | 665.6  |
| 72.5° | 277.0  | 354.8  | 469.7  | 547.3  | 547.3  |
| 75°   | 219.6  | 297.4  | 402.1  | 408.9  | 398.7  |
| 77.5° | 168.9  | 243.3  | 314.2  | 287.2  | 293.9  |
| 80°   | 125.0  | 185.8  | 199.3  | 209.5  | 216.2  |
| 82.5° | 84.5   | 125.0  | 128.4  | 135.2  | 135.2  |
| 85°   | 54.1   | 64.2   | 67.6   | 64.2   | 60.8   |
| 87.5° | 23.6   | 27.1   | 20.3   | 13.5   | 10.2   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP3-2508-516-5

Test Date: 09/03/2025

Luminaire Tested: 24CZ-LD5-65-S-UNV-L930-CD1-U

Data in this report applies to families of products including 24CZ-LD5-65-S-UNV-L930-CD1-U

### Test Information

Test Method: LM-79-2019  
 Report Number: SP3-2508-516-5  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP3 - 3M SPHERE  
 Measurement Geometry:  $4\pi$   
 Issue Date: 09/05/2025  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: Metalux  
 Catalog Number: **24CZ-LD5-65-S-UNV-L930-CD1-U**  
 Description: 2X4 CRUZE SB 6500LM 930 SMOOTH LENS

### Spectral Parameters

CCT (K): 2988  
 CIE  $u'$ : 0.2517  
 CIE  $v'$ : 0.5189  
 Duv: -0.0019  
 CIE x: 0.4350  
 CIE y: 0.3986  
 CIE z: 0.1665  
 Peak Wavelength (nm): 630  
 Dominant Wavelength (nm): 583  
 Purity: 50.17903  
 R<sub>f</sub>: 91.6  
 R<sub>g</sub>: 101.1

CRI (Ra): 94.3  
 R1: 96.3  
 R2: 97.6  
 R3: 97.5  
 R4: 95.8  
 R5: 96.1  
 R6: 96.2  
 R7: 91.6  
 R8: 83.5  
 R9: 61.9  
 R10: 93.0  
 R11: 96.3  
 R12: 85.8  
 R13: 96.7  
 R14: 97.5  
 R15: 91.8



### Test Conditions

Stabilization Time: 21M  
 Operation Time: 1H 21M  
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP3-2508-516-5

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | 3M SPHERE IN02505     | 7/1/2025         | 1/1/2026             |
| Power Meter                    | XITRON INXT2011006    | 1/20/2025        | 1/20/2026            |
| AC Power Source                | CHROMA 61604 IN6064A  | 10/22/2024       | 10/22/2025           |
| DC Power Source                | EYSIGHT N5770A IN0534 | 10/22/2024       | 10/22/2025           |
| Sphere Thermometer             | TANDD IN4036E         | 10/22/2024       | 10/22/2025           |
|                                |                       |                  |                      |

REPORT NUMBER: SP3-2508-516-5

**CIE 1931 Chromaticity Diagram**



**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP3-2508-516-5

### Photopic Flux vs. Wavelength



### Photopic Lumens: NR

| $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 0                                    | NR                             | 490               | 101                                  | NR                             | 620               | 329                                  | NR                             | 750               | 8                                    | NR                             | 880               | 0                                    | NR                             |
| 365               | 0                                    | NR                             | 495               | 121                                  | NR                             | 625               | 331                                  | NR                             | 755               | 7                                    | NR                             | 885               | 0                                    | NR                             |
| 370               | 0                                    | NR                             | 500               | 143                                  | NR                             | 630               | 1000                                 | NR                             | 760               | 6                                    | NR                             | 890               | 0                                    | NR                             |
| 375               | 0                                    | NR                             | 505               | 161                                  | NR                             | 635               | 709                                  | NR                             | 765               | 5                                    | NR                             | 895               | 0                                    | NR                             |
| 380               | 0                                    | NR                             | 510               | 176                                  | NR                             | 640               | 220                                  | NR                             | 770               | 4                                    | NR                             | 900               | 0                                    | NR                             |
| 385               | 0                                    | NR                             | 515               | 189                                  | NR                             | 645               | 210                                  | NR                             | 775               | 3                                    | NR                             | 905               | 0                                    | NR                             |
| 390               | 0                                    | NR                             | 520               | 196                                  | NR                             | 650               | 188                                  | NR                             | 780               | 3                                    | NR                             | 910               | 0                                    | NR                             |
| 395               | 1                                    | NR                             | 525               | 203                                  | NR                             | 655               | 156                                  | NR                             | 785               | 2                                    | NR                             | 915               | 0                                    | NR                             |
| 400               | 1                                    | NR                             | 530               | 208                                  | NR                             | 660               | 134                                  | NR                             | 790               | 2                                    | NR                             | 920               | 0                                    | NR                             |
| 405               | 2                                    | NR                             | 535               | 213                                  | NR                             | 665               | 112                                  | NR                             | 795               | 2                                    | NR                             | 925               | 0                                    | NR                             |
| 410               | 3                                    | NR                             | 540               | 219                                  | NR                             | 670               | 104                                  | NR                             | 800               | 1                                    | NR                             | 930               | 0                                    | NR                             |
| 415               | 6                                    | NR                             | 545               | 226                                  | NR                             | 675               | 85                                   | NR                             | 805               | 1                                    | NR                             | 935               | 0                                    | NR                             |
| 420               | 10                                   | NR                             | 550               | 233                                  | NR                             | 680               | 72                                   | NR                             | 810               | 1                                    | NR                             | 940               | 0                                    | NR                             |
| 425               | 17                                   | NR                             | 555               | 241                                  | NR                             | 685               | 63                                   | NR                             | 815               | 1                                    | NR                             | 945               | 0                                    | NR                             |
| 430               | 30                                   | NR                             | 560               | 250                                  | NR                             | 690               | 53                                   | NR                             | 820               | 1                                    | NR                             | 950               | 0                                    | NR                             |
| 435               | 53                                   | NR                             | 565               | 260                                  | NR                             | 695               | 46                                   | NR                             | 825               | 1                                    | NR                             | 955               | 0                                    | NR                             |
| 440               | 92                                   | NR                             | 570               | 270                                  | NR                             | 700               | 39                                   | NR                             | 830               | 1                                    | NR                             | 960               | 0                                    | NR                             |
| 445               | 160                                  | NR                             | 575               | 280                                  | NR                             | 705               | 33                                   | NR                             | 835               | 1                                    | NR                             | 965               | 0                                    | NR                             |
| 450               | 214                                  | NR                             | 580               | 289                                  | NR                             | 710               | 28                                   | NR                             | 840               | 0                                    | NR                             | 970               | 0                                    | NR                             |
| 455               | 183                                  | NR                             | 585               | 298                                  | NR                             | 715               | 24                                   | NR                             | 845               | 0                                    | NR                             | 975               | 0                                    | NR                             |
| 460               | 133                                  | NR                             | 590               | 305                                  | NR                             | 720               | 20                                   | NR                             | 850               | 0                                    | NR                             | 980               | 0                                    | NR                             |
| 465               | 111                                  | NR                             | 595               | 309                                  | NR                             | 725               | 17                                   | NR                             | 855               | 0                                    | NR                             | 985               | 0                                    | NR                             |
| 470               | 91                                   | NR                             | 600               | 314                                  | NR                             | 730               | 15                                   | NR                             | 860               | 0                                    | NR                             | 990               | 0                                    | NR                             |
| 475               | 77                                   | NR                             | 605               | 318                                  | NR                             | 735               | 13                                   | NR                             | 865               | 0                                    | NR                             | 995               | 0                                    | NR                             |
| 480               | 76                                   | NR                             | 610               | 356                                  | NR                             | 740               | 11                                   | NR                             | 870               | 0                                    | NR                             | 1000              | 0                                    | NR                             |
| 485               | 86                                   | NR                             | 615               | 390                                  | NR                             | 745               | 9                                    | NR                             | 875               | 0                                    | NR                             |                   |                                      |                                |

REPORT NUMBER: SP3-2508-516-5

### Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.43

| λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(Φ/nm) |
|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|
| 360       | 0                           | NR               | 490       | 101                         | NR               | 620       | 329                         | NR               | 750       | 8                           | NR               | 880       | 0                           | NR               |
| 365       | 0                           | NR               | 495       | 121                         | NR               | 625       | 331                         | NR               | 755       | 7                           | NR               | 885       | 0                           | NR               |
| 370       | 0                           | NR               | 500       | 143                         | NR               | 630       | 1000                        | NR               | 760       | 6                           | NR               | 890       | 0                           | NR               |
| 375       | 0                           | NR               | 505       | 161                         | NR               | 635       | 709                         | NR               | 765       | 5                           | NR               | 895       | 0                           | NR               |
| 380       | 0                           | NR               | 510       | 176                         | NR               | 640       | 220                         | NR               | 770       | 4                           | NR               | 900       | 0                           | NR               |
| 385       | 0                           | NR               | 515       | 189                         | NR               | 645       | 210                         | NR               | 775       | 3                           | NR               | 905       | 0                           | NR               |
| 390       | 0                           | NR               | 520       | 196                         | NR               | 650       | 188                         | NR               | 780       | 3                           | NR               | 910       | 0                           | NR               |
| 395       | 1                           | NR               | 525       | 203                         | NR               | 655       | 156                         | NR               | 785       | 2                           | NR               | 915       | 0                           | NR               |
| 400       | 1                           | NR               | 530       | 208                         | NR               | 660       | 134                         | NR               | 790       | 2                           | NR               | 920       | 0                           | NR               |
| 405       | 2                           | NR               | 535       | 213                         | NR               | 665       | 112                         | NR               | 795       | 2                           | NR               | 925       | 0                           | NR               |
| 410       | 3                           | NR               | 540       | 219                         | NR               | 670       | 104                         | NR               | 800       | 1                           | NR               | 930       | 0                           | NR               |
| 415       | 6                           | NR               | 545       | 226                         | NR               | 675       | 85                          | NR               | 805       | 1                           | NR               | 935       | 0                           | NR               |
| 420       | 10                          | NR               | 550       | 233                         | NR               | 680       | 72                          | NR               | 810       | 1                           | NR               | 940       | 0                           | NR               |
| 425       | 17                          | NR               | 555       | 241                         | NR               | 685       | 63                          | NR               | 815       | 1                           | NR               | 945       | 0                           | NR               |
| 430       | 30                          | NR               | 560       | 250                         | NR               | 690       | 53                          | NR               | 820       | 1                           | NR               | 950       | 0                           | NR               |
| 435       | 53                          | NR               | 565       | 260                         | NR               | 695       | 46                          | NR               | 825       | 1                           | NR               | 955       | 0                           | NR               |
| 440       | 92                          | NR               | 570       | 270                         | NR               | 700       | 39                          | NR               | 830       | 1                           | NR               | 960       | 0                           | NR               |
| 445       | 160                         | NR               | 575       | 280                         | NR               | 705       | 33                          | NR               | 835       | 1                           | NR               | 965       | 0                           | NR               |
| 450       | 214                         | NR               | 580       | 289                         | NR               | 710       | 28                          | NR               | 840       | 0                           | NR               | 970       | 0                           | NR               |
| 455       | 183                         | NR               | 585       | 298                         | NR               | 715       | 24                          | NR               | 845       | 0                           | NR               | 975       | 0                           | NR               |
| 460       | 133                         | NR               | 590       | 305                         | NR               | 720       | 20                          | NR               | 850       | 0                           | NR               | 980       | 0                           | NR               |
| 465       | 111                         | NR               | 595       | 309                         | NR               | 725       | 17                          | NR               | 855       | 0                           | NR               | 985       | 0                           | NR               |
| 470       | 91                          | NR               | 600       | 314                         | NR               | 730       | 15                          | NR               | 860       | 0                           | NR               | 990       | 0                           | NR               |
| 475       | 77                          | NR               | 605       | 318                         | NR               | 735       | 13                          | NR               | 865       | 0                           | NR               | 995       | 0                           | NR               |
| 480       | 76                          | NR               | 610       | 356                         | NR               | 740       | 11                          | NR               | 870       | 0                           | NR               | 1000      | 0                           | NR               |
| 485       | 86                          | NR               | 615       | 390                         | NR               | 745       | 9                           | NR               | 875       | 0                           | NR               |           |                             |                  |

REPORT NUMBER: SP3-2508-516-5

### Melanopic Flux vs. Wavelength


**Melanopic Lumens: NR**
**M/P: 2.8**

| λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) |
|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|
| 360       | 0                           | NR               | 490       | 101                         | NR               | 620       | 329                         | NR               | 750       | 8                           | NR               | 880       | 0                           | NR               |
| 365       | 0                           | NR               | 495       | 121                         | NR               | 625       | 331                         | NR               | 755       | 7                           | NR               | 885       | 0                           | NR               |
| 370       | 0                           | NR               | 500       | 143                         | NR               | 630       | 1000                        | NR               | 760       | 6                           | NR               | 890       | 0                           | NR               |
| 375       | 0                           | NR               | 505       | 161                         | NR               | 635       | 709                         | NR               | 765       | 5                           | NR               | 895       | 0                           | NR               |
| 380       | 0                           | NR               | 510       | 176                         | NR               | 640       | 220                         | NR               | 770       | 4                           | NR               | 900       | 0                           | NR               |
| 385       | 0                           | NR               | 515       | 189                         | NR               | 645       | 210                         | NR               | 775       | 3                           | NR               | 905       | 0                           | NR               |
| 390       | 0                           | NR               | 520       | 196                         | NR               | 650       | 188                         | NR               | 780       | 3                           | NR               | 910       | 0                           | NR               |
| 395       | 1                           | NR               | 525       | 203                         | NR               | 655       | 156                         | NR               | 785       | 2                           | NR               | 915       | 0                           | NR               |
| 400       | 1                           | NR               | 530       | 208                         | NR               | 660       | 134                         | NR               | 790       | 2                           | NR               | 920       | 0                           | NR               |
| 405       | 2                           | NR               | 535       | 213                         | NR               | 665       | 112                         | NR               | 795       | 2                           | NR               | 925       | 0                           | NR               |
| 410       | 3                           | NR               | 540       | 219                         | NR               | 670       | 104                         | NR               | 800       | 1                           | NR               | 930       | 0                           | NR               |
| 415       | 6                           | NR               | 545       | 226                         | NR               | 675       | 85                          | NR               | 805       | 1                           | NR               | 935       | 0                           | NR               |
| 420       | 10                          | NR               | 550       | 233                         | NR               | 680       | 72                          | NR               | 810       | 1                           | NR               | 940       | 0                           | NR               |
| 425       | 17                          | NR               | 555       | 241                         | NR               | 685       | 63                          | NR               | 815       | 1                           | NR               | 945       | 0                           | NR               |
| 430       | 30                          | NR               | 560       | 250                         | NR               | 690       | 53                          | NR               | 820       | 1                           | NR               | 950       | 0                           | NR               |
| 435       | 53                          | NR               | 565       | 260                         | NR               | 695       | 46                          | NR               | 825       | 1                           | NR               | 955       | 0                           | NR               |
| 440       | 92                          | NR               | 570       | 270                         | NR               | 700       | 39                          | NR               | 830       | 1                           | NR               | 960       | 0                           | NR               |
| 445       | 160                         | NR               | 575       | 280                         | NR               | 705       | 33                          | NR               | 835       | 1                           | NR               | 965       | 0                           | NR               |
| 450       | 214                         | NR               | 580       | 289                         | NR               | 710       | 28                          | NR               | 840       | 0                           | NR               | 970       | 0                           | NR               |
| 455       | 183                         | NR               | 585       | 298                         | NR               | 715       | 24                          | NR               | 845       | 0                           | NR               | 975       | 0                           | NR               |
| 460       | 133                         | NR               | 590       | 305                         | NR               | 720       | 20                          | NR               | 850       | 0                           | NR               | 980       | 0                           | NR               |
| 465       | 111                         | NR               | 595       | 309                         | NR               | 725       | 17                          | NR               | 855       | 0                           | NR               | 985       | 0                           | NR               |
| 470       | 91                          | NR               | 600       | 314                         | NR               | 730       | 15                          | NR               | 860       | 0                           | NR               | 990       | 0                           | NR               |
| 475       | 77                          | NR               | 605       | 318                         | NR               | 735       | 13                          | NR               | 865       | 0                           | NR               | 995       | 0                           | NR               |
| 480       | 76                          | NR               | 610       | 356                         | NR               | 740       | 11                          | NR               | 870       | 0                           | NR               | 1000      | 0                           | NR               |
| 485       | 86                          | NR               | 615       | 390                         | NR               | 745       | 9                           | NR               | 875       | 0                           | NR               |           |                             |                  |

REPORT NUMBER: SP3-2508-516-5


TM-30-18

### Summary

$R_f = 91.6$   
 $R_g = 101.1$   
 $CIE R_a = 94.3$   
 $R_9 = 61.9$



### Color Vector Graphics



**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 92 | CES51 = 97 | CES76 = 89 |
| CES02 = 63 | CES27 = 95 | CES52 = 96 | CES77 = 85 |
| CES03 = 32 | CES28 = 96 | CES53 = 94 | CES78 = 86 |
| CES04 = 70 | CES29 = 92 | CES54 = 97 | CES79 = 89 |
| CES05 = 51 | CES30 = 99 | CES55 = 96 | CES80 = 91 |
| CES06 = 51 | CES31 = 93 | CES56 = 96 | CES81 = 72 |
| CES07 = 44 | CES32 = 85 | CES57 = 96 | CES82 = 96 |
| CES08 = 42 | CES33 = 94 | CES58 = 96 | CES83 = 93 |
| CES09 = 29 | CES34 = 93 | CES59 = 99 | CES84 = 96 |
| CES10 = 76 | CES35 = 96 | CES60 = 95 | CES85 = 80 |
| CES11 = 59 | CES36 = 87 | CES61 = 95 | CES86 = 78 |
| CES12 = 65 | CES37 = 94 | CES62 = 93 | CES87 = 91 |
| CES13 = 44 | CES38 = 96 | CES63 = 94 | CES88 = 97 |
| CES14 = 74 | CES39 = 98 | CES64 = 95 | CES89 = 82 |
| CES15 = 72 | CES40 = 95 | CES65 = 91 | CES90 = 98 |
| CES16 = 48 | CES41 = 96 | CES66 = 93 | CES91 = 81 |
| CES17 = 50 | CES42 = 92 | CES67 = 92 | CES92 = 78 |
| CES18 = 57 | CES43 = 90 | CES68 = 92 | CES93 = 87 |
| CES19 = 72 | CES44 = 99 | CES69 = 93 | CES94 = 73 |
| CES20 = 67 | CES45 = 94 | CES70 = 89 | CES95 = 85 |
| CES21 = 86 | CES46 = 94 | CES71 = 88 | CES96 = 92 |
| CES22 = 79 | CES47 = 88 | CES72 = 95 | CES97 = 94 |
| CES23 = 92 | CES48 = 95 | CES73 = 85 | CES98 = 94 |
| CES24 = 91 | CES49 = 92 | CES74 = 90 | CES99 = 93 |
| CES25 = 72 | CES50 = 97 | CES75 = 88 |            |



Color Rendition by Hue-Angle Bin



**Measure Comparisons**



(END OF REPORT)