

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: METALUX

Report Number: P983158

Luminaire Tested: 24CZ-LD5-40-UNV-L835-SQP-CD1-U

Issue Date: 04/23/2025

**Test Information**

Test Method: LM-79-2019  
Report Number: P983158  
Test Lab: INNOVATION CENTER(P3)  
Issue Date: 04/23/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: METALUX  
Catalog Number: 24CZ-LD5-40-UNV-L835-SQP-CD1-U  
Description: METALUX CRUZE 2x4 4000LM PACKAGE 80CRI 3500K TROFFER LENS WITH SQUARE PATTERN  
Light Source: 3500K CCT, 80 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2998.0 lumens  
Efficiency: N/A  
Efficacy: 97.7 lumens/watt  
Spacing Criteria (0/90/45): 1.25 / 1.31 / 1.41  
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')  
CIE Type: Direct

Input Watts (W): 30.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT

TEST NUMBER: P983158

CATALOG NUMBER: 24CZ-LD5-40-UNV-L835-SQP-CD1-U

### Luminous Intensity Polar Plot



TEST NUMBER: P983158

CATALOG NUMBER: 24CZ-LD5-40-UNV-L835-SQP-CD1-U

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 108 | 103 | 99  | 95  | 105 | 101 | 97  | 93  | 97  | 93  | 90  |  | 93  | 90  | 87  |  | 89  |
| 2   | 98  | 89  | 82  | 76  | 95  | 87  | 81  | 75  | 84  | 78  | 73  |  | 80  | 76  | 71  |  | 77  |
| 3   | 89  | 78  | 69  | 62  | 86  | 76  | 68  | 62  | 73  | 66  | 61  |  | 70  | 64  | 59  |  | 68  |
| 4   | 81  | 68  | 59  | 52  | 79  | 67  | 58  | 52  | 64  | 57  | 51  |  | 62  | 56  | 50  |  | 60  |
| 5   | 74  | 61  | 52  | 45  | 72  | 60  | 51  | 44  | 58  | 50  | 44  |  | 56  | 49  | 43  |  | 54  |
| 6   | 68  | 55  | 45  | 39  | 66  | 54  | 45  | 39  | 52  | 44  | 38  |  | 50  | 43  | 38  |  | 48  |
| 7   | 63  | 49  | 40  | 34  | 62  | 49  | 40  | 34  | 47  | 39  | 34  |  | 45  | 39  | 33  |  | 44  |
| 8   | 59  | 45  | 36  | 30  | 57  | 44  | 36  | 30  | 43  | 35  | 30  |  | 42  | 35  | 30  |  | 40  |
| 9   | 55  | 41  | 33  | 27  | 54  | 41  | 33  | 27  | 39  | 32  | 27  |  | 38  | 32  | 27  |  | 37  |
| 10  | 51  | 38  | 30  | 24  | 50  | 37  | 30  | 24  | 36  | 29  | 24  |  | 35  | 29  | 24  |  | 35  |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°   | 45°  | 90°  |
|-----|------|------|------|
| 0°  | 1281 | 1281 | 1281 |
| 5°  | 1283 | 1292 | 1277 |
| 10° | 1279 | 1279 | 1279 |
| 15° | 1275 | 1281 | 1288 |
| 20° | 1270 | 1283 | 1290 |
| 25° | 1255 | 1275 | 1293 |
| 30° | 1244 | 1266 | 1302 |
| 35° | 1231 | 1266 | 1319 |
| 40° | 1219 | 1268 | 1349 |
| 45° | 1196 | 1271 | 1400 |
| 50° | 1170 | 1282 | 1467 |
| 55° | 1130 | 1316 | 1546 |
| 60° | 1077 | 1353 | 1635 |
| 65° | 1016 | 1401 | 1727 |
| 70° | 907  | 1438 | 1805 |
| 75° | 787  | 1440 | 1428 |
| 80° | 667  | 1065 | 1155 |
| 85° | 576  | 719  | 647  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°

Vertical Angle: 70°

Luminance: 1805 cd/sqm

TEST NUMBER: P983158

CATALOG NUMBER: 24CZ-LD5-40-UNV-L835-SQP-CD1-U

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 90.4   | 3.0       |
| 10°-20°   | 259.6  | 8.7       |
| 20°-30°   | 395.7  | 13.2      |
| 30°-40°   | 484.1  | 16.1      |
| 40°-50°   | 520.9  | 17.4      |
| 50°-60°   | 504.6  | 16.8      |
| 60°-70°   | 427.5  | 14.3      |
| 70°-80°   | 258.4  | 8.6       |
| 80°-90°   | 56.8   | 1.9       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 745.7  | 24.9      |
| 0°-40°    | 1229.8 | 41.0      |
| 0°-60°    | 2255.4 | 75.2      |
| 0°-90°    | 2998.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 2998.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | 22.5° | 45° | 67.5° | 90° | Flux |
|-----|-----|-------|-----|-------|-----|------|
| 0°  | 952 | 952   | 952 | 952   | 952 |      |
| 5°  | 950 | 950   | 957 | 952   | 945 | 90   |
| 15° | 915 | 917   | 920 | 922   | 924 | 258  |
| 25° | 845 | 850   | 859 | 866   | 871 | 390  |
| 35° | 750 | 754   | 771 | 792   | 803 | 469  |
| 45° | 629 | 640   | 668 | 710   | 736 | 484  |
| 55° | 482 | 503   | 561 | 626   | 659 | 430  |
| 65° | 319 | 354   | 440 | 510   | 542 | 314  |
| 75° | 151 | 205   | 277 | 282   | 275 | 163  |
| 85° | 37  | 44    | 47  | 44    | 42  | 42   |
| 90° | 0   | 0     | 0   | 0     | 0   |      |

TEST NUMBER: P983158

CATALOG NUMBER: 24CZ-LD5-40-UNV-L835-SQP-CD1-U

**CANDELA DISTRIBUTION (FULL):**

|       | 0°    | 22.5° | 45°   | 67.5° | 90°   |
|-------|-------|-------|-------|-------|-------|
| 0°    | 952.2 | 952.2 | 952.2 | 952.2 | 952.2 |
| 2.5°  | 963.9 | 961.6 | 954.6 | 949.9 | 945.2 |
| 5°    | 949.9 | 949.9 | 956.9 | 952.2 | 945.2 |
| 7.5°  | 942.9 | 942.9 | 942.9 | 954.6 | 942.9 |
| 10°   | 936.0 | 938.3 | 936.0 | 945.2 | 936.0 |
| 12.5° | 928.9 | 928.9 | 928.9 | 931.3 | 931.3 |
| 15°   | 915.0 | 917.3 | 919.6 | 921.9 | 924.3 |
| 17.5° | 901.0 | 903.3 | 908.0 | 910.3 | 912.7 |
| 20°   | 887.1 | 889.4 | 896.3 | 896.3 | 901.0 |
| 22.5° | 868.4 | 868.4 | 877.7 | 880.1 | 887.1 |
| 25°   | 845.1 | 849.8 | 859.1 | 866.1 | 870.7 |
| 27.5° | 824.2 | 828.8 | 838.2 | 847.4 | 854.4 |
| 30°   | 800.9 | 805.5 | 814.9 | 828.8 | 838.2 |
| 32.5° | 775.3 | 779.9 | 793.9 | 810.2 | 819.5 |
| 35°   | 749.7 | 754.3 | 770.6 | 791.6 | 803.2 |
| 37.5° | 721.7 | 728.7 | 747.3 | 770.6 | 784.6 |
| 40°   | 693.8 | 700.8 | 721.7 | 747.3 | 768.3 |
| 42.5° | 661.2 | 670.5 | 693.8 | 728.7 | 752.0 |
| 45°   | 628.6 | 640.3 | 668.2 | 710.1 | 735.7 |
| 47.5° | 593.7 | 605.3 | 638.0 | 691.5 | 719.4 |
| 50°   | 558.8 | 572.7 | 612.3 | 670.5 | 700.8 |
| 52.5° | 521.5 | 535.5 | 586.7 | 649.5 | 682.2 |
| 55°   | 481.9 | 502.9 | 561.1 | 626.3 | 658.9 |
| 57.5° | 442.4 | 465.7 | 530.8 | 600.7 | 635.6 |
| 60°   | 400.4 | 428.4 | 502.9 | 572.7 | 607.7 |
| 62.5° | 360.9 | 391.2 | 472.6 | 542.5 | 577.4 |
| 65°   | 319.0 | 353.9 | 440.1 | 509.9 | 542.5 |
| 67.5° | 274.7 | 319.0 | 402.8 | 470.3 | 502.9 |
| 70°   | 230.5 | 281.7 | 365.6 | 428.4 | 458.7 |
| 72.5° | 190.9 | 244.5 | 323.6 | 377.1 | 377.1 |
| 75°   | 151.3 | 204.9 | 277.0 | 281.7 | 274.7 |
| 77.5° | 116.4 | 167.7 | 216.5 | 197.9 | 202.5 |
| 80°   | 86.1  | 128.0 | 137.4 | 144.4 | 149.0 |
| 82.5° | 58.2  | 86.1  | 88.5  | 93.2  | 93.2  |
| 85°   | 37.3  | 44.3  | 46.6  | 44.3  | 41.9  |
| 87.5° | 16.3  | 18.7  | 14.0  | 9.3   | 7.0   |
| 90°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP3-2508-516-6

Test Date: 09/03/2025

Luminaire Tested: 24CZ-LD5-65-S-UNV-L935-CD1-U

Data in this report applies to families of products including 24CZ-LD5-65-S-UNV-L935-CD1-U

### Test Information

Test Method: LM-79-2019  
 Report Number: SP3-2508-516-6  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP3 - 3M SPHERE  
 Measurement Geometry:  $4\pi$   
 Issue Date: 09/05/2025  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: Metalux  
 Catalog Number: **24CZ-LD5-65-S-UNV-L935-CD1-U**  
 Description: 2X4 CRUZE SB 6500LM 935 SMOOTH LENS

### Spectral Parameters

CCT (K): 3412  
 CIE  $u'$ : 0.2386  
 CIE  $v'$ : 0.5111  
 Duv: -0.0015  
 CIE x: 0.4087  
 CIE y: 0.3890  
 CIE z: 0.2023  
 Peak Wavelength (nm): 630  
 Dominant Wavelength (nm): 581  
 Purity: 39.41044  
 R<sub>f</sub>: 92.6  
 R<sub>g</sub>: 102

CRI (Ra): 96.3  
 R1: 99.2  
 R2: 97.9  
 R3: 94.7  
 R4: 96.6  
 R5: 98.4  
 R6: 96.1  
 R7: 95.6  
 R8: 92.0  
 R9: 78.4  
 R10: 93.0  
 R11: 94.5  
 R12: 81.5  
 R13: 99.0  
 R14: 95.8  
 R15: 96.7



### Test Conditions

Stabilization Time: 20M  
 Operation Time: 1H 20M  
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP3-2508-516-6

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | 3M SPHERE IN02505     | 7/1/2025         | 1/1/2026             |
| Power Meter                    | XITRON INXT2011006    | 1/20/2025        | 1/20/2026            |
| AC Power Source                | CHROMA 61604 IN6064A  | 10/22/2024       | 10/22/2025           |
| DC Power Source                | EYSIGHT N5770A IN0534 | 10/22/2024       | 10/22/2025           |
| Sphere Thermometer             | TANDD IN4036E         | 10/22/2024       | 10/22/2025           |
|                                |                       |                  |                      |

REPORT NUMBER: SP3-2508-516-6

**CIE 1931 Chromaticity Diagram**



**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP3-2508-516-6

### Photopic Flux vs. Wavelength



### Photopic Lumens: NR

| $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|
| 360               | 0                                      | NR                             | 490               | 112                                    | NR                             | 620               | 281                                    | NR                             | 750               | 6                                      | NR                             | 880               | 0                                      | NR                             |
| 365               | 0                                      | NR                             | 495               | 134                                    | NR                             | 625               | 286                                    | NR                             | 755               | 5                                      | NR                             | 885               | 0                                      | NR                             |
| 370               | 0                                      | NR                             | 500               | 157                                    | NR                             | 630               | 1000                                   | NR                             | 760               | 4                                      | NR                             | 890               | 0                                      | NR                             |
| 375               | 0                                      | NR                             | 505               | 178                                    | NR                             | 635               | 695                                    | NR                             | 765               | 4                                      | NR                             | 895               | 0                                      | NR                             |
| 380               | 0                                      | NR                             | 510               | 193                                    | NR                             | 640               | 181                                    | NR                             | 770               | 3                                      | NR                             | 900               | 0                                      | NR                             |
| 385               | 0                                      | NR                             | 515               | 206                                    | NR                             | 645               | 175                                    | NR                             | 775               | 3                                      | NR                             | 905               | 0                                      | NR                             |
| 390               | 0                                      | NR                             | 520               | 213                                    | NR                             | 650               | 156                                    | NR                             | 780               | 2                                      | NR                             | 910               | 0                                      | NR                             |
| 395               | 1                                      | NR                             | 525               | 219                                    | NR                             | 655               | 127                                    | NR                             | 785               | 2                                      | NR                             | 915               | 0                                      | NR                             |
| 400               | 2                                      | NR                             | 530               | 223                                    | NR                             | 660               | 108                                    | NR                             | 790               | 2                                      | NR                             | 920               | 0                                      | NR                             |
| 405               | 2                                      | NR                             | 535               | 226                                    | NR                             | 665               | 89                                     | NR                             | 795               | 2                                      | NR                             | 925               | 0                                      | NR                             |
| 410               | 4                                      | NR                             | 540               | 230                                    | NR                             | 670               | 84                                     | NR                             | 800               | 1                                      | NR                             | 930               | 0                                      | NR                             |
| 415               | 6                                      | NR                             | 545               | 235                                    | NR                             | 675               | 67                                     | NR                             | 805               | 1                                      | NR                             | 935               | 0                                      | NR                             |
| 420               | 11                                     | NR                             | 550               | 239                                    | NR                             | 680               | 57                                     | NR                             | 810               | 1                                      | NR                             | 940               | 0                                      | NR                             |
| 425               | 19                                     | NR                             | 555               | 243                                    | NR                             | 685               | 50                                     | NR                             | 815               | 1                                      | NR                             | 945               | 0                                      | NR                             |
| 430               | 34                                     | NR                             | 560               | 248                                    | NR                             | 690               | 42                                     | NR                             | 820               | 1                                      | NR                             | 950               | 0                                      | NR                             |
| 435               | 60                                     | NR                             | 565               | 253                                    | NR                             | 695               | 36                                     | NR                             | 825               | 1                                      | NR                             | 955               | 0                                      | NR                             |
| 440               | 106                                    | NR                             | 570               | 256                                    | NR                             | 700               | 31                                     | NR                             | 830               | 0                                      | NR                             | 960               | 0                                      | NR                             |
| 445               | 193                                    | NR                             | 575               | 260                                    | NR                             | 705               | 26                                     | NR                             | 835               | 0                                      | NR                             | 965               | 0                                      | NR                             |
| 450               | 283                                    | NR                             | 580               | 263                                    | NR                             | 710               | 22                                     | NR                             | 840               | 0                                      | NR                             | 970               | 0                                      | NR                             |
| 455               | 234                                    | NR                             | 585               | 266                                    | NR                             | 715               | 19                                     | NR                             | 845               | 0                                      | NR                             | 975               | 0                                      | NR                             |
| 460               | 157                                    | NR                             | 590               | 267                                    | NR                             | 720               | 16                                     | NR                             | 850               | 0                                      | NR                             | 980               | 0                                      | NR                             |
| 465               | 134                                    | NR                             | 595               | 266                                    | NR                             | 725               | 14                                     | NR                             | 855               | 0                                      | NR                             | 985               | 0                                      | NR                             |
| 470               | 107                                    | NR                             | 600               | 268                                    | NR                             | 730               | 12                                     | NR                             | 860               | 0                                      | NR                             | 990               | 0                                      | NR                             |
| 475               | 85                                     | NR                             | 605               | 269                                    | NR                             | 735               | 10                                     | NR                             | 865               | 0                                      | NR                             | 995               | 0                                      | NR                             |
| 480               | 85                                     | NR                             | 610               | 309                                    | NR                             | 740               | 8                                      | NR                             | 870               | 0                                      | NR                             | 1000              | 0                                      | NR                             |
| 485               | 96                                     | NR                             | 615               | 345                                    | NR                             | 745               | 7                                      | NR                             | 875               | 0                                      | NR                             |                   |                                        |                                |

REPORT NUMBER: SP3-2508-516-6

### Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.61

| λ (nm) | Power W <sup>λ</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>λ</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>λ</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>λ</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>λ</sup> /nm | Lumens (Φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360    | 0                        | NR            | 490    | 112                      | NR            | 620    | 281                      | NR            | 750    | 6                        | NR            | 880    | 0                        | NR            |
| 365    | 0                        | NR            | 495    | 134                      | NR            | 625    | 286                      | NR            | 755    | 5                        | NR            | 885    | 0                        | NR            |
| 370    | 0                        | NR            | 500    | 157                      | NR            | 630    | 1000                     | NR            | 760    | 4                        | NR            | 890    | 0                        | NR            |
| 375    | 0                        | NR            | 505    | 178                      | NR            | 635    | 695                      | NR            | 765    | 4                        | NR            | 895    | 0                        | NR            |
| 380    | 0                        | NR            | 510    | 193                      | NR            | 640    | 181                      | NR            | 770    | 3                        | NR            | 900    | 0                        | NR            |
| 385    | 0                        | NR            | 515    | 206                      | NR            | 645    | 175                      | NR            | 775    | 3                        | NR            | 905    | 0                        | NR            |
| 390    | 0                        | NR            | 520    | 213                      | NR            | 650    | 156                      | NR            | 780    | 2                        | NR            | 910    | 0                        | NR            |
| 395    | 1                        | NR            | 525    | 219                      | NR            | 655    | 127                      | NR            | 785    | 2                        | NR            | 915    | 0                        | NR            |
| 400    | 2                        | NR            | 530    | 223                      | NR            | 660    | 108                      | NR            | 790    | 2                        | NR            | 920    | 0                        | NR            |
| 405    | 2                        | NR            | 535    | 226                      | NR            | 665    | 89                       | NR            | 795    | 2                        | NR            | 925    | 0                        | NR            |
| 410    | 4                        | NR            | 540    | 230                      | NR            | 670    | 84                       | NR            | 800    | 1                        | NR            | 930    | 0                        | NR            |
| 415    | 6                        | NR            | 545    | 235                      | NR            | 675    | 67                       | NR            | 805    | 1                        | NR            | 935    | 0                        | NR            |
| 420    | 11                       | NR            | 550    | 239                      | NR            | 680    | 57                       | NR            | 810    | 1                        | NR            | 940    | 0                        | NR            |
| 425    | 19                       | NR            | 555    | 243                      | NR            | 685    | 50                       | NR            | 815    | 1                        | NR            | 945    | 0                        | NR            |
| 430    | 34                       | NR            | 560    | 248                      | NR            | 690    | 42                       | NR            | 820    | 1                        | NR            | 950    | 0                        | NR            |
| 435    | 60                       | NR            | 565    | 253                      | NR            | 695    | 36                       | NR            | 825    | 1                        | NR            | 955    | 0                        | NR            |
| 440    | 106                      | NR            | 570    | 256                      | NR            | 700    | 31                       | NR            | 830    | 0                        | NR            | 960    | 0                        | NR            |
| 445    | 193                      | NR            | 575    | 260                      | NR            | 705    | 26                       | NR            | 835    | 0                        | NR            | 965    | 0                        | NR            |
| 450    | 283                      | NR            | 580    | 263                      | NR            | 710    | 22                       | NR            | 840    | 0                        | NR            | 970    | 0                        | NR            |
| 455    | 234                      | NR            | 585    | 266                      | NR            | 715    | 19                       | NR            | 845    | 0                        | NR            | 975    | 0                        | NR            |
| 460    | 157                      | NR            | 590    | 267                      | NR            | 720    | 16                       | NR            | 850    | 0                        | NR            | 980    | 0                        | NR            |
| 465    | 134                      | NR            | 595    | 266                      | NR            | 725    | 14                       | NR            | 855    | 0                        | NR            | 985    | 0                        | NR            |
| 470    | 107                      | NR            | 600    | 268                      | NR            | 730    | 12                       | NR            | 860    | 0                        | NR            | 990    | 0                        | NR            |
| 475    | 85                       | NR            | 605    | 269                      | NR            | 735    | 10                       | NR            | 865    | 0                        | NR            | 995    | 0                        | NR            |
| 480    | 85                       | NR            | 610    | 309                      | NR            | 740    | 8                        | NR            | 870    | 0                        | NR            | 1000   | 0                        | NR            |
| 485    | 96                       | NR            | 615    | 345                      | NR            | 745    | 7                        | NR            | 875    | 0                        | NR            |        |                          |               |

REPORT NUMBER: SP3-2508-516-6

### Melanopic Flux vs. Wavelength


**Melanopic Lumens: NR**
**M/P: 3.24**

| λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) |
|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|
| 360       | 0                           | NR               | 490       | 112                         | NR               | 620       | 281                         | NR               | 750       | 6                           | NR               | 880       | 0                           | NR               |
| 365       | 0                           | NR               | 495       | 134                         | NR               | 625       | 286                         | NR               | 755       | 5                           | NR               | 885       | 0                           | NR               |
| 370       | 0                           | NR               | 500       | 157                         | NR               | 630       | 1000                        | NR               | 760       | 4                           | NR               | 890       | 0                           | NR               |
| 375       | 0                           | NR               | 505       | 178                         | NR               | 635       | 695                         | NR               | 765       | 4                           | NR               | 895       | 0                           | NR               |
| 380       | 0                           | NR               | 510       | 193                         | NR               | 640       | 181                         | NR               | 770       | 3                           | NR               | 900       | 0                           | NR               |
| 385       | 0                           | NR               | 515       | 206                         | NR               | 645       | 175                         | NR               | 775       | 3                           | NR               | 905       | 0                           | NR               |
| 390       | 0                           | NR               | 520       | 213                         | NR               | 650       | 156                         | NR               | 780       | 2                           | NR               | 910       | 0                           | NR               |
| 395       | 1                           | NR               | 525       | 219                         | NR               | 655       | 127                         | NR               | 785       | 2                           | NR               | 915       | 0                           | NR               |
| 400       | 2                           | NR               | 530       | 223                         | NR               | 660       | 108                         | NR               | 790       | 2                           | NR               | 920       | 0                           | NR               |
| 405       | 2                           | NR               | 535       | 226                         | NR               | 665       | 89                          | NR               | 795       | 2                           | NR               | 925       | 0                           | NR               |
| 410       | 4                           | NR               | 540       | 230                         | NR               | 670       | 84                          | NR               | 800       | 1                           | NR               | 930       | 0                           | NR               |
| 415       | 6                           | NR               | 545       | 235                         | NR               | 675       | 67                          | NR               | 805       | 1                           | NR               | 935       | 0                           | NR               |
| 420       | 11                          | NR               | 550       | 239                         | NR               | 680       | 57                          | NR               | 810       | 1                           | NR               | 940       | 0                           | NR               |
| 425       | 19                          | NR               | 555       | 243                         | NR               | 685       | 50                          | NR               | 815       | 1                           | NR               | 945       | 0                           | NR               |
| 430       | 34                          | NR               | 560       | 248                         | NR               | 690       | 42                          | NR               | 820       | 1                           | NR               | 950       | 0                           | NR               |
| 435       | 60                          | NR               | 565       | 253                         | NR               | 695       | 36                          | NR               | 825       | 1                           | NR               | 955       | 0                           | NR               |
| 440       | 106                         | NR               | 570       | 256                         | NR               | 700       | 31                          | NR               | 830       | 0                           | NR               | 960       | 0                           | NR               |
| 445       | 193                         | NR               | 575       | 260                         | NR               | 705       | 26                          | NR               | 835       | 0                           | NR               | 965       | 0                           | NR               |
| 450       | 283                         | NR               | 580       | 263                         | NR               | 710       | 22                          | NR               | 840       | 0                           | NR               | 970       | 0                           | NR               |
| 455       | 234                         | NR               | 585       | 266                         | NR               | 715       | 19                          | NR               | 845       | 0                           | NR               | 975       | 0                           | NR               |
| 460       | 157                         | NR               | 590       | 267                         | NR               | 720       | 16                          | NR               | 850       | 0                           | NR               | 980       | 0                           | NR               |
| 465       | 134                         | NR               | 595       | 266                         | NR               | 725       | 14                          | NR               | 855       | 0                           | NR               | 985       | 0                           | NR               |
| 470       | 107                         | NR               | 600       | 268                         | NR               | 730       | 12                          | NR               | 860       | 0                           | NR               | 990       | 0                           | NR               |
| 475       | 85                          | NR               | 605       | 269                         | NR               | 735       | 10                          | NR               | 865       | 0                           | NR               | 995       | 0                           | NR               |
| 480       | 85                          | NR               | 610       | 309                         | NR               | 740       | 8                           | NR               | 870       | 0                           | NR               | 1000      | 0                           | NR               |
| 485       | 96                          | NR               | 615       | 345                         | NR               | 745       | 7                           | NR               | 875       | 0                           | NR               |           |                             |                  |

REPORT NUMBER: SP3-2508-516-6

TM-30-18

### Summary

$R_f = 92.6$   
 $R_g = 102$   
 $\text{CIE } R_a = 96.3$   
 $R_9 = 78.4$



### Color Vector Graphics



**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |             |            |
|------------|------------|-------------|------------|
| CES01 = 86 | CES26 = 94 | CES51 = 97  | CES76 = 88 |
| CES02 = 63 | CES27 = 93 | CES52 = 96  | CES77 = 88 |
| CES03 = 32 | CES28 = 96 | CES53 = 95  | CES78 = 84 |
| CES04 = 70 | CES29 = 95 | CES54 = 95  | CES79 = 92 |
| CES05 = 50 | CES30 = 96 | CES55 = 95  | CES80 = 92 |
| CES06 = 51 | CES31 = 95 | CES56 = 98  | CES81 = 77 |
| CES07 = 43 | CES32 = 87 | CES57 = 98  | CES82 = 96 |
| CES08 = 42 | CES33 = 97 | CES58 = 98  | CES83 = 95 |
| CES09 = 29 | CES34 = 93 | CES59 = 100 | CES84 = 95 |
| CES10 = 75 | CES35 = 96 | CES60 = 94  | CES85 = 82 |
| CES11 = 58 | CES36 = 84 | CES61 = 95  | CES86 = 84 |
| CES12 = 64 | CES37 = 93 | CES62 = 90  | CES87 = 92 |
| CES13 = 44 | CES38 = 91 | CES63 = 95  | CES88 = 99 |
| CES14 = 74 | CES39 = 98 | CES64 = 95  | CES89 = 86 |
| CES15 = 72 | CES40 = 96 | CES65 = 92  | CES90 = 98 |
| CES16 = 48 | CES41 = 97 | CES66 = 93  | CES91 = 77 |
| CES17 = 49 | CES42 = 90 | CES67 = 92  | CES92 = 81 |
| CES18 = 56 | CES43 = 91 | CES68 = 91  | CES93 = 88 |
| CES19 = 71 | CES44 = 99 | CES69 = 92  | CES94 = 78 |
| CES20 = 67 | CES45 = 94 | CES70 = 89  | CES95 = 86 |
| CES21 = 86 | CES46 = 95 | CES71 = 85  | CES96 = 93 |
| CES22 = 78 | CES47 = 90 | CES72 = 95  | CES97 = 93 |
| CES23 = 91 | CES48 = 96 | CES73 = 84  | CES98 = 96 |
| CES24 = 90 | CES49 = 93 | CES74 = 91  | CES99 = 97 |
| CES25 = 71 | CES50 = 97 | CES75 = 86  |            |



Color Rendition by Hue-Angle Bin



**Measure Comparisons**



(END OF REPORT)