

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: METALUX

Report Number: P983152

Luminaire Tested: 24CZ-LD5-70-UNV-L930-SQP-CD1-U

Issue Date: 04/23/2025

**Test Information**

Test Method: LM-79-2019  
Report Number: P983152  
Test Lab: INNOVATION CENTER(P3)  
Issue Date: 04/23/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: METALUX  
Catalog Number: 24CZ-LD5-70-UNV-L930-SQP-CD1-U  
Description: METALUX CRUZE 2x4 7000LM PACKAGE 90CRI 3000K TROFFER LENS WITH SQUARE PATTERN  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5168.9 lumens  
Efficiency: N/A  
Efficacy: 104.8 lumens/watt  
Spacing Criteria (0/90/45): 1.25 / 1.31 / 1.41  
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')  
CIE Type: Direct

Input Watts (W): 49.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT

TEST NUMBER: P983152

CATALOG NUMBER: 24CZ-LD5-70-UNV-L930-SQP-CD1-U

### Luminous Intensity Polar Plot



TEST NUMBER: P983152

CATALOG NUMBER: 24CZ-LD5-70-UNV-L930-SQP-CD1-U

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |     |     |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |     |     | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 | 100 |
| 1   | 108 | 103 | 99  | 95  | 105 | 101 | 97  | 93  | 97  | 93  | 90  |  | 93  | 90  | 87  |  | 89  | 87  | 85  | 83  |
| 2   | 98  | 89  | 82  | 76  | 95  | 87  | 81  | 75  | 84  | 78  | 73  |  | 80  | 76  | 71  |  | 77  | 73  | 70  | 68  |
| 3   | 89  | 78  | 69  | 62  | 86  | 76  | 68  | 62  | 73  | 66  | 61  |  | 70  | 64  | 59  |  | 68  | 63  | 58  | 56  |
| 4   | 81  | 68  | 59  | 52  | 79  | 67  | 58  | 52  | 64  | 57  | 51  |  | 62  | 56  | 50  |  | 60  | 54  | 50  | 47  |
| 5   | 74  | 61  | 52  | 45  | 72  | 60  | 51  | 44  | 58  | 50  | 44  |  | 56  | 49  | 43  |  | 54  | 48  | 43  | 41  |
| 6   | 68  | 55  | 45  | 39  | 66  | 54  | 45  | 39  | 52  | 44  | 38  |  | 50  | 43  | 38  |  | 48  | 42  | 37  | 35  |
| 7   | 63  | 49  | 40  | 34  | 62  | 49  | 40  | 34  | 47  | 39  | 34  |  | 45  | 39  | 33  |  | 44  | 38  | 33  | 31  |
| 8   | 59  | 45  | 36  | 30  | 57  | 44  | 36  | 30  | 43  | 35  | 30  |  | 42  | 35  | 30  |  | 40  | 34  | 29  | 28  |
| 9   | 55  | 41  | 33  | 27  | 54  | 41  | 33  | 27  | 39  | 32  | 27  |  | 38  | 32  | 27  |  | 37  | 31  | 27  | 25  |
| 10  | 51  | 38  | 30  | 24  | 50  | 37  | 30  | 24  | 36  | 29  | 24  |  | 35  | 29  | 24  |  | 35  | 28  | 24  | 22  |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°   | 45°  | 90°  |
|-----|------|------|------|
| 0°  | 2209 | 2209 | 2209 |
| 5°  | 2212 | 2228 | 2201 |
| 10° | 2205 | 2205 | 2205 |
| 15° | 2198 | 2209 | 2220 |
| 20° | 2190 | 2213 | 2224 |
| 25° | 2163 | 2199 | 2229 |
| 30° | 2145 | 2183 | 2245 |
| 35° | 2123 | 2182 | 2275 |
| 40° | 2101 | 2186 | 2327 |
| 45° | 2062 | 2192 | 2414 |
| 50° | 2017 | 2210 | 2529 |
| 55° | 1949 | 2269 | 2665 |
| 60° | 1858 | 2333 | 2819 |
| 65° | 1751 | 2415 | 2978 |
| 70° | 1563 | 2480 | 3111 |
| 75° | 1356 | 2483 | 2463 |
| 80° | 1151 | 1835 | 1991 |
| 85° | 991  | 1240 | 1115 |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°

Vertical Angle: 70°

Luminance: 3111 cd/sqm

TEST NUMBER: P983152

CATALOG NUMBER: 24CZ-LD5-70-UNV-L930-SQP-CD1-U

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 155.9  | 3.0       |
| 10°-20°   | 447.7  | 8.7       |
| 20°-30°   | 682.2  | 13.2      |
| 30°-40°   | 834.7  | 16.1      |
| 40°-50°   | 898.1  | 17.4      |
| 50°-60°   | 870.0  | 16.8      |
| 60°-70°   | 737.0  | 14.3      |
| 70°-80°   | 445.5  | 8.6       |
| 80°-90°   | 97.9   | 1.9       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1285.7 | 24.9      |
| 0°-40°    | 2120.5 | 41.0      |
| 0°-60°    | 3888.6 | 75.2      |
| 0°-90°    | 5168.9 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 5168.9 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | 22.5° | 45°  | 67.5° | 90°  | Flux |
|-----|------|-------|------|-------|------|------|
| 0°  | 1642 | 1642  | 1642 | 1642  | 1642 |      |
| 5°  | 1638 | 1638  | 1650 | 1642  | 1630 | 156  |
| 15° | 1578 | 1582  | 1586 | 1590  | 1594 | 445  |
| 25° | 1457 | 1465  | 1481 | 1493  | 1501 | 673  |
| 35° | 1293 | 1301  | 1329 | 1365  | 1385 | 808  |
| 45° | 1084 | 1104  | 1152 | 1224  | 1268 | 835  |
| 55° | 831  | 867   | 967  | 1080  | 1136 | 742  |
| 65° | 550  | 610   | 759  | 879   | 935  | 542  |
| 75° | 261  | 353   | 478  | 486   | 474  | 280  |
| 85° | 64   | 76    | 80   | 76    | 72   | 73   |
| 90° | 0    | 0     | 0    | 0     | 0    |      |

TEST NUMBER: P983152

CATALOG NUMBER: 24CZ-LD5-70-UNV-L930-SQP-CD1-U

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 22.5°  | 45°    | 67.5°  | 90°    |
|-------|--------|--------|--------|--------|--------|
| 0°    | 1641.8 | 1641.8 | 1641.8 | 1641.8 | 1641.8 |
| 2.5°  | 1661.9 | 1657.9 | 1645.8 | 1637.8 | 1629.7 |
| 5°    | 1637.8 | 1637.8 | 1649.8 | 1641.8 | 1629.7 |
| 7.5°  | 1625.7 | 1625.7 | 1625.7 | 1645.8 | 1625.7 |
| 10°   | 1613.7 | 1617.7 | 1613.7 | 1629.7 | 1613.7 |
| 12.5° | 1601.6 | 1601.6 | 1601.6 | 1605.6 | 1605.6 |
| 15°   | 1577.6 | 1581.6 | 1585.6 | 1589.6 | 1593.7 |
| 17.5° | 1553.5 | 1557.5 | 1565.5 | 1569.6 | 1573.6 |
| 20°   | 1529.4 | 1533.4 | 1545.4 | 1545.4 | 1553.5 |
| 22.5° | 1497.3 | 1497.3 | 1513.3 | 1517.3 | 1529.4 |
| 25°   | 1457.1 | 1465.2 | 1481.2 | 1493.3 | 1501.3 |
| 27.5° | 1421.1 | 1429.0 | 1445.1 | 1461.1 | 1473.2 |
| 30°   | 1380.9 | 1388.9 | 1405.0 | 1429.0 | 1445.1 |
| 32.5° | 1336.7 | 1344.7 | 1368.8 | 1396.9 | 1413.0 |
| 35°   | 1292.6 | 1300.6 | 1328.7 | 1364.8 | 1384.9 |
| 37.5° | 1244.4 | 1256.4 | 1288.5 | 1328.7 | 1352.7 |
| 40°   | 1196.2 | 1208.3 | 1244.4 | 1288.5 | 1324.7 |
| 42.5° | 1140.0 | 1156.1 | 1196.2 | 1256.4 | 1296.6 |
| 45°   | 1083.8 | 1103.9 | 1152.1 | 1224.3 | 1268.4 |
| 47.5° | 1023.6 | 1043.7 | 1099.9 | 1192.2 | 1240.4 |
| 50°   | 963.4  | 987.5  | 1055.7 | 1156.1 | 1208.3 |
| 52.5° | 899.2  | 923.2  | 1011.5 | 1119.9 | 1176.1 |
| 55°   | 830.9  | 867.1  | 967.4  | 1079.8 | 1136.0 |
| 57.5° | 762.7  | 802.9  | 915.2  | 1035.7 | 1095.8 |
| 60°   | 690.4  | 738.6  | 867.1  | 987.5  | 1047.7 |
| 62.5° | 622.2  | 674.4  | 814.9  | 935.3  | 995.5  |
| 65°   | 550.0  | 610.2  | 758.7  | 879.1  | 935.3  |
| 67.5° | 473.7  | 550.0  | 694.5  | 810.9  | 867.1  |
| 70°   | 397.4  | 485.7  | 630.3  | 738.6  | 790.8  |
| 72.5° | 329.1  | 421.5  | 558.0  | 650.2  | 650.2  |
| 75°   | 260.9  | 353.3  | 477.6  | 485.7  | 473.7  |
| 77.5° | 200.7  | 289.1  | 373.3  | 341.2  | 349.2  |
| 80°   | 148.5  | 220.7  | 236.8  | 248.9  | 256.9  |
| 82.5° | 100.4  | 148.5  | 152.5  | 160.6  | 160.6  |
| 85°   | 64.2   | 76.3   | 80.3   | 76.3   | 72.2   |
| 87.5° | 28.1   | 32.2   | 24.1   | 16.1   | 12.1   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP3-2508-516-5

Test Date: 09/03/2025

Luminaire Tested: 24CZ-LD5-65-S-UNV-L930-CD1-U

Data in this report applies to families of products including 24CZ-LD5-65-S-UNV-L930-CD1-U

### Test Information

Test Method: LM-79-2019  
 Report Number: SP3-2508-516-5  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP3 - 3M SPHERE  
 Measurement Geometry:  $4\pi$   
 Issue Date: 09/05/2025  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: Metalux  
 Catalog Number: **24CZ-LD5-65-S-UNV-L930-CD1-U**  
 Description: 2X4 CRUZE SB 6500LM 930 SMOOTH LENS

### Spectral Parameters

CCT (K): 2988  
 CIE  $u'$ : 0.2517  
 CIE  $v'$ : 0.5189  
 Duv: -0.0019  
 CIE x: 0.4350  
 CIE y: 0.3986  
 CIE z: 0.1665  
 Peak Wavelength (nm): 630  
 Dominant Wavelength (nm): 583  
 Purity: 50.17903  
 R<sub>f</sub>: 91.6  
 R<sub>g</sub>: 101.1

CRI (Ra): 94.3  
 R1: 96.3  
 R2: 97.6  
 R3: 97.5  
 R4: 95.8  
 R5: 96.1  
 R6: 96.2  
 R7: 91.6  
 R8: 83.5  
 R9: 61.9  
 R10: 93.0  
 R11: 96.3  
 R12: 85.8  
 R13: 96.7  
 R14: 97.5  
 R15: 91.8



### Test Conditions

Stabilization Time: 21M  
 Operation Time: 1H 21M  
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP3-2508-516-5

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | 3M SPHERE IN02505     | 7/1/2025         | 1/1/2026             |
| Power Meter                    | XITRON INXT2011006    | 1/20/2025        | 1/20/2026            |
| AC Power Source                | CHROMA 61604 IN6064A  | 10/22/2024       | 10/22/2025           |
| DC Power Source                | EYSIGHT N5770A IN0534 | 10/22/2024       | 10/22/2025           |
| Sphere Thermometer             | TANDD IN4036E         | 10/22/2024       | 10/22/2025           |
|                                |                       |                  |                      |

REPORT NUMBER: SP3-2508-516-5

**CIE 1931 Chromaticity Diagram**



**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP3-2508-516-5

### Photopic Flux vs. Wavelength



### Photopic Lumens: NR

| λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) |
|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|
| 360       | 0                           | NR               | 490       | 101                         | NR               | 620       | 329                         | NR               | 750       | 8                           | NR               | 880       | 0                           | NR               |
| 365       | 0                           | NR               | 495       | 121                         | NR               | 625       | 331                         | NR               | 755       | 7                           | NR               | 885       | 0                           | NR               |
| 370       | 0                           | NR               | 500       | 143                         | NR               | 630       | 1000                        | NR               | 760       | 6                           | NR               | 890       | 0                           | NR               |
| 375       | 0                           | NR               | 505       | 161                         | NR               | 635       | 709                         | NR               | 765       | 5                           | NR               | 895       | 0                           | NR               |
| 380       | 0                           | NR               | 510       | 176                         | NR               | 640       | 220                         | NR               | 770       | 4                           | NR               | 900       | 0                           | NR               |
| 385       | 0                           | NR               | 515       | 189                         | NR               | 645       | 210                         | NR               | 775       | 3                           | NR               | 905       | 0                           | NR               |
| 390       | 0                           | NR               | 520       | 196                         | NR               | 650       | 188                         | NR               | 780       | 3                           | NR               | 910       | 0                           | NR               |
| 395       | 1                           | NR               | 525       | 203                         | NR               | 655       | 156                         | NR               | 785       | 2                           | NR               | 915       | 0                           | NR               |
| 400       | 1                           | NR               | 530       | 208                         | NR               | 660       | 134                         | NR               | 790       | 2                           | NR               | 920       | 0                           | NR               |
| 405       | 2                           | NR               | 535       | 213                         | NR               | 665       | 112                         | NR               | 795       | 2                           | NR               | 925       | 0                           | NR               |
| 410       | 3                           | NR               | 540       | 219                         | NR               | 670       | 104                         | NR               | 800       | 1                           | NR               | 930       | 0                           | NR               |
| 415       | 6                           | NR               | 545       | 226                         | NR               | 675       | 85                          | NR               | 805       | 1                           | NR               | 935       | 0                           | NR               |
| 420       | 10                          | NR               | 550       | 233                         | NR               | 680       | 72                          | NR               | 810       | 1                           | NR               | 940       | 0                           | NR               |
| 425       | 17                          | NR               | 555       | 241                         | NR               | 685       | 63                          | NR               | 815       | 1                           | NR               | 945       | 0                           | NR               |
| 430       | 30                          | NR               | 560       | 250                         | NR               | 690       | 53                          | NR               | 820       | 1                           | NR               | 950       | 0                           | NR               |
| 435       | 53                          | NR               | 565       | 260                         | NR               | 695       | 46                          | NR               | 825       | 1                           | NR               | 955       | 0                           | NR               |
| 440       | 92                          | NR               | 570       | 270                         | NR               | 700       | 39                          | NR               | 830       | 1                           | NR               | 960       | 0                           | NR               |
| 445       | 160                         | NR               | 575       | 280                         | NR               | 705       | 33                          | NR               | 835       | 1                           | NR               | 965       | 0                           | NR               |
| 450       | 214                         | NR               | 580       | 289                         | NR               | 710       | 28                          | NR               | 840       | 0                           | NR               | 970       | 0                           | NR               |
| 455       | 183                         | NR               | 585       | 298                         | NR               | 715       | 24                          | NR               | 845       | 0                           | NR               | 975       | 0                           | NR               |
| 460       | 133                         | NR               | 590       | 305                         | NR               | 720       | 20                          | NR               | 850       | 0                           | NR               | 980       | 0                           | NR               |
| 465       | 111                         | NR               | 595       | 309                         | NR               | 725       | 17                          | NR               | 855       | 0                           | NR               | 985       | 0                           | NR               |
| 470       | 91                          | NR               | 600       | 314                         | NR               | 730       | 15                          | NR               | 860       | 0                           | NR               | 990       | 0                           | NR               |
| 475       | 77                          | NR               | 605       | 318                         | NR               | 735       | 13                          | NR               | 865       | 0                           | NR               | 995       | 0                           | NR               |
| 480       | 76                          | NR               | 610       | 356                         | NR               | 740       | 11                          | NR               | 870       | 0                           | NR               | 1000      | 0                           | NR               |
| 485       | 86                          | NR               | 615       | 390                         | NR               | 745       | 9                           | NR               | 875       | 0                           | NR               |           |                             |                  |

REPORT NUMBER: SP3-2508-516-5

### Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.43

| λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360    | 0                        | NR            | 490    | 101                      | NR            | 620    | 329                      | NR            | 750    | 8                        | NR            | 880    | 0                        | NR            |
| 365    | 0                        | NR            | 495    | 121                      | NR            | 625    | 331                      | NR            | 755    | 7                        | NR            | 885    | 0                        | NR            |
| 370    | 0                        | NR            | 500    | 143                      | NR            | 630    | 1000                     | NR            | 760    | 6                        | NR            | 890    | 0                        | NR            |
| 375    | 0                        | NR            | 505    | 161                      | NR            | 635    | 709                      | NR            | 765    | 5                        | NR            | 895    | 0                        | NR            |
| 380    | 0                        | NR            | 510    | 176                      | NR            | 640    | 220                      | NR            | 770    | 4                        | NR            | 900    | 0                        | NR            |
| 385    | 0                        | NR            | 515    | 189                      | NR            | 645    | 210                      | NR            | 775    | 3                        | NR            | 905    | 0                        | NR            |
| 390    | 0                        | NR            | 520    | 196                      | NR            | 650    | 188                      | NR            | 780    | 3                        | NR            | 910    | 0                        | NR            |
| 395    | 1                        | NR            | 525    | 203                      | NR            | 655    | 156                      | NR            | 785    | 2                        | NR            | 915    | 0                        | NR            |
| 400    | 1                        | NR            | 530    | 208                      | NR            | 660    | 134                      | NR            | 790    | 2                        | NR            | 920    | 0                        | NR            |
| 405    | 2                        | NR            | 535    | 213                      | NR            | 665    | 112                      | NR            | 795    | 2                        | NR            | 925    | 0                        | NR            |
| 410    | 3                        | NR            | 540    | 219                      | NR            | 670    | 104                      | NR            | 800    | 1                        | NR            | 930    | 0                        | NR            |
| 415    | 6                        | NR            | 545    | 226                      | NR            | 675    | 85                       | NR            | 805    | 1                        | NR            | 935    | 0                        | NR            |
| 420    | 10                       | NR            | 550    | 233                      | NR            | 680    | 72                       | NR            | 810    | 1                        | NR            | 940    | 0                        | NR            |
| 425    | 17                       | NR            | 555    | 241                      | NR            | 685    | 63                       | NR            | 815    | 1                        | NR            | 945    | 0                        | NR            |
| 430    | 30                       | NR            | 560    | 250                      | NR            | 690    | 53                       | NR            | 820    | 1                        | NR            | 950    | 0                        | NR            |
| 435    | 53                       | NR            | 565    | 260                      | NR            | 695    | 46                       | NR            | 825    | 1                        | NR            | 955    | 0                        | NR            |
| 440    | 92                       | NR            | 570    | 270                      | NR            | 700    | 39                       | NR            | 830    | 1                        | NR            | 960    | 0                        | NR            |
| 445    | 160                      | NR            | 575    | 280                      | NR            | 705    | 33                       | NR            | 835    | 1                        | NR            | 965    | 0                        | NR            |
| 450    | 214                      | NR            | 580    | 289                      | NR            | 710    | 28                       | NR            | 840    | 0                        | NR            | 970    | 0                        | NR            |
| 455    | 183                      | NR            | 585    | 298                      | NR            | 715    | 24                       | NR            | 845    | 0                        | NR            | 975    | 0                        | NR            |
| 460    | 133                      | NR            | 590    | 305                      | NR            | 720    | 20                       | NR            | 850    | 0                        | NR            | 980    | 0                        | NR            |
| 465    | 111                      | NR            | 595    | 309                      | NR            | 725    | 17                       | NR            | 855    | 0                        | NR            | 985    | 0                        | NR            |
| 470    | 91                       | NR            | 600    | 314                      | NR            | 730    | 15                       | NR            | 860    | 0                        | NR            | 990    | 0                        | NR            |
| 475    | 77                       | NR            | 605    | 318                      | NR            | 735    | 13                       | NR            | 865    | 0                        | NR            | 995    | 0                        | NR            |
| 480    | 76                       | NR            | 610    | 356                      | NR            | 740    | 11                       | NR            | 870    | 0                        | NR            | 1000   | 0                        | NR            |
| 485    | 86                       | NR            | 615    | 390                      | NR            | 745    | 9                        | NR            | 875    | 0                        | NR            |        |                          |               |

REPORT NUMBER: SP3-2508-516-5

### Melanopic Flux vs. Wavelength


**Melanopic Lumens: NR**
**M/P: 2.8**

| $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 0                                    | NR                             | 490               | 101                                  | NR                             | 620               | 329                                  | NR                             | 750               | 8                                    | NR                             | 880               | 0                                    | NR                             |
| 365               | 0                                    | NR                             | 495               | 121                                  | NR                             | 625               | 331                                  | NR                             | 755               | 7                                    | NR                             | 885               | 0                                    | NR                             |
| 370               | 0                                    | NR                             | 500               | 143                                  | NR                             | 630               | 1000                                 | NR                             | 760               | 6                                    | NR                             | 890               | 0                                    | NR                             |
| 375               | 0                                    | NR                             | 505               | 161                                  | NR                             | 635               | 709                                  | NR                             | 765               | 5                                    | NR                             | 895               | 0                                    | NR                             |
| 380               | 0                                    | NR                             | 510               | 176                                  | NR                             | 640               | 220                                  | NR                             | 770               | 4                                    | NR                             | 900               | 0                                    | NR                             |
| 385               | 0                                    | NR                             | 515               | 189                                  | NR                             | 645               | 210                                  | NR                             | 775               | 3                                    | NR                             | 905               | 0                                    | NR                             |
| 390               | 0                                    | NR                             | 520               | 196                                  | NR                             | 650               | 188                                  | NR                             | 780               | 3                                    | NR                             | 910               | 0                                    | NR                             |
| 395               | 1                                    | NR                             | 525               | 203                                  | NR                             | 655               | 156                                  | NR                             | 785               | 2                                    | NR                             | 915               | 0                                    | NR                             |
| 400               | 1                                    | NR                             | 530               | 208                                  | NR                             | 660               | 134                                  | NR                             | 790               | 2                                    | NR                             | 920               | 0                                    | NR                             |
| 405               | 2                                    | NR                             | 535               | 213                                  | NR                             | 665               | 112                                  | NR                             | 795               | 2                                    | NR                             | 925               | 0                                    | NR                             |
| 410               | 3                                    | NR                             | 540               | 219                                  | NR                             | 670               | 104                                  | NR                             | 800               | 1                                    | NR                             | 930               | 0                                    | NR                             |
| 415               | 6                                    | NR                             | 545               | 226                                  | NR                             | 675               | 85                                   | NR                             | 805               | 1                                    | NR                             | 935               | 0                                    | NR                             |
| 420               | 10                                   | NR                             | 550               | 233                                  | NR                             | 680               | 72                                   | NR                             | 810               | 1                                    | NR                             | 940               | 0                                    | NR                             |
| 425               | 17                                   | NR                             | 555               | 241                                  | NR                             | 685               | 63                                   | NR                             | 815               | 1                                    | NR                             | 945               | 0                                    | NR                             |
| 430               | 30                                   | NR                             | 560               | 250                                  | NR                             | 690               | 53                                   | NR                             | 820               | 1                                    | NR                             | 950               | 0                                    | NR                             |
| 435               | 53                                   | NR                             | 565               | 260                                  | NR                             | 695               | 46                                   | NR                             | 825               | 1                                    | NR                             | 955               | 0                                    | NR                             |
| 440               | 92                                   | NR                             | 570               | 270                                  | NR                             | 700               | 39                                   | NR                             | 830               | 1                                    | NR                             | 960               | 0                                    | NR                             |
| 445               | 160                                  | NR                             | 575               | 280                                  | NR                             | 705               | 33                                   | NR                             | 835               | 1                                    | NR                             | 965               | 0                                    | NR                             |
| 450               | 214                                  | NR                             | 580               | 289                                  | NR                             | 710               | 28                                   | NR                             | 840               | 0                                    | NR                             | 970               | 0                                    | NR                             |
| 455               | 183                                  | NR                             | 585               | 298                                  | NR                             | 715               | 24                                   | NR                             | 845               | 0                                    | NR                             | 975               | 0                                    | NR                             |
| 460               | 133                                  | NR                             | 590               | 305                                  | NR                             | 720               | 20                                   | NR                             | 850               | 0                                    | NR                             | 980               | 0                                    | NR                             |
| 465               | 111                                  | NR                             | 595               | 309                                  | NR                             | 725               | 17                                   | NR                             | 855               | 0                                    | NR                             | 985               | 0                                    | NR                             |
| 470               | 91                                   | NR                             | 600               | 314                                  | NR                             | 730               | 15                                   | NR                             | 860               | 0                                    | NR                             | 990               | 0                                    | NR                             |
| 475               | 77                                   | NR                             | 605               | 318                                  | NR                             | 735               | 13                                   | NR                             | 865               | 0                                    | NR                             | 995               | 0                                    | NR                             |
| 480               | 76                                   | NR                             | 610               | 356                                  | NR                             | 740               | 11                                   | NR                             | 870               | 0                                    | NR                             | 1000              | 0                                    | NR                             |
| 485               | 86                                   | NR                             | 615               | 390                                  | NR                             | 745               | 9                                    | NR                             | 875               | 0                                    | NR                             |                   |                                      |                                |

REPORT NUMBER: SP3-2508-516-5

TM-30-18

### Summary

$R_f = 91.6$   
 $R_g = 101.1$   
 CIE  $R_a = 94.3$   
 $R_9 = 61.9$



### Color Vector Graphics



**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 92 | CES51 = 97 | CES76 = 89 |
| CES02 = 63 | CES27 = 95 | CES52 = 96 | CES77 = 85 |
| CES03 = 32 | CES28 = 96 | CES53 = 94 | CES78 = 86 |
| CES04 = 70 | CES29 = 92 | CES54 = 97 | CES79 = 89 |
| CES05 = 51 | CES30 = 99 | CES55 = 96 | CES80 = 91 |
| CES06 = 51 | CES31 = 93 | CES56 = 96 | CES81 = 72 |
| CES07 = 44 | CES32 = 85 | CES57 = 96 | CES82 = 96 |
| CES08 = 42 | CES33 = 94 | CES58 = 96 | CES83 = 93 |
| CES09 = 29 | CES34 = 93 | CES59 = 99 | CES84 = 96 |
| CES10 = 76 | CES35 = 96 | CES60 = 95 | CES85 = 80 |
| CES11 = 59 | CES36 = 87 | CES61 = 95 | CES86 = 78 |
| CES12 = 65 | CES37 = 94 | CES62 = 93 | CES87 = 91 |
| CES13 = 44 | CES38 = 96 | CES63 = 94 | CES88 = 97 |
| CES14 = 74 | CES39 = 98 | CES64 = 95 | CES89 = 82 |
| CES15 = 72 | CES40 = 95 | CES65 = 91 | CES90 = 98 |
| CES16 = 48 | CES41 = 96 | CES66 = 93 | CES91 = 81 |
| CES17 = 50 | CES42 = 92 | CES67 = 92 | CES92 = 78 |
| CES18 = 57 | CES43 = 90 | CES68 = 92 | CES93 = 87 |
| CES19 = 72 | CES44 = 99 | CES69 = 93 | CES94 = 73 |
| CES20 = 67 | CES45 = 94 | CES70 = 89 | CES95 = 85 |
| CES21 = 86 | CES46 = 94 | CES71 = 88 | CES96 = 92 |
| CES22 = 79 | CES47 = 88 | CES72 = 95 | CES97 = 94 |
| CES23 = 92 | CES48 = 95 | CES73 = 85 | CES98 = 94 |
| CES24 = 91 | CES49 = 92 | CES74 = 90 | CES99 = 93 |
| CES25 = 72 | CES50 = 97 | CES75 = 88 |            |



Color Rendition by Hue-Angle Bin



**Measure Comparisons**


(END OF REPORT)