

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: METALUX

Report Number: P982883

Luminaire Tested: 24CZ-LD5-75-UNV-L835-CD1-U

Issue Date: 04/23/2025

**Test Information**

Test Method: LM-79-2019  
Report Number: P982883  
Test Lab: INNOVATION CENTER(P3)  
Issue Date: 04/23/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: METALUX  
Catalog Number: 24CZ-LD5-75-UNV-L835-CD1-U  
Description: METALUX CRUZE 2x4 7500LM PACKAGE 80CRI 3500K TROFFER STANDARD LENS  
Light Source: 3500K CCT, 80 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7079.0 lumens  
Efficiency: N/A  
Efficacy: 127.8 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.26 / 1.35  
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')  
CIE Type: Direct

Input Watts (W): 55.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT

TEST NUMBER: P982883

CATALOG NUMBER: 24CZ-LD5-75-UNV-L835-CD1-U

### Luminous Intensity Polar Plot



TEST NUMBER: P982883

CATALOG NUMBER: 24CZ-LD5-75-UNV-L835-CD1-U

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 |
| 1   | 108 | 103 | 99  | 95  | 106 | 101 | 97  | 93  | 97  | 93  | 90  | 93  | 90  | 88  | 89  | 87  | 85  |
| 2   | 98  | 90  | 83  | 77  | 96  | 88  | 81  | 76  | 84  | 79  | 74  | 81  | 76  | 72  | 78  | 74  | 71  |
| 3   | 89  | 79  | 70  | 63  | 87  | 77  | 69  | 63  | 74  | 67  | 62  | 71  | 65  | 61  | 69  | 64  | 60  |
| 4   | 82  | 69  | 60  | 54  | 79  | 68  | 60  | 53  | 66  | 58  | 52  | 63  | 57  | 52  | 61  | 56  | 51  |
| 5   | 75  | 62  | 53  | 46  | 73  | 61  | 52  | 46  | 59  | 51  | 45  | 57  | 50  | 45  | 55  | 49  | 44  |
| 6   | 69  | 56  | 47  | 40  | 67  | 55  | 46  | 40  | 53  | 45  | 40  | 51  | 44  | 39  | 50  | 44  | 39  |
| 7   | 64  | 51  | 42  | 35  | 63  | 50  | 41  | 35  | 48  | 41  | 35  | 47  | 40  | 35  | 45  | 39  | 35  |
| 8   | 60  | 46  | 38  | 32  | 58  | 45  | 37  | 32  | 44  | 37  | 31  | 43  | 36  | 31  | 42  | 36  | 31  |
| 9   | 56  | 42  | 34  | 28  | 55  | 42  | 34  | 28  | 41  | 33  | 28  | 40  | 33  | 28  | 39  | 32  | 28  |
| 10  | 52  | 39  | 31  | 26  | 51  | 39  | 31  | 26  | 38  | 31  | 26  | 37  | 30  | 26  | 36  | 30  | 25  |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°   | 45°  | 90°  |
|-----|------|------|------|
| 0°  | 3347 | 3347 | 3347 |
| 5°  | 3360 | 3350 | 3344 |
| 10° | 3336 | 3336 | 3336 |
| 15° | 3297 | 3311 | 3331 |
| 20° | 3245 | 3279 | 3310 |
| 25° | 3175 | 3236 | 3286 |
| 30° | 3094 | 3184 | 3259 |
| 35° | 2998 | 3125 | 3240 |
| 40° | 2906 | 3067 | 3219 |
| 45° | 2809 | 3010 | 3231 |
| 50° | 2702 | 2959 | 3246 |
| 55° | 2598 | 2926 | 3271 |
| 60° | 2489 | 2903 | 3331 |
| 65° | 2361 | 2898 | 3435 |
| 70° | 2198 | 2946 | 3628 |
| 75° | 1966 | 3067 | 3480 |
| 80° | 1679 | 2930 | 3191 |
| 85° | 1301 | 2342 | 2231 |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°

Vertical Angle: 72.5°

Luminance: 3696 cd/sqm

TEST NUMBER: P982883

CATALOG NUMBER: 24CZ-LD5-75-UNV-L835-CD1-U

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 235.2  | 3.3       |
| 10°-20°   | 669.6  | 9.5       |
| 20°-30°   | 1000.9 | 14.1      |
| 30°-40°   | 1186.8 | 16.8      |
| 40°-50°   | 1220.5 | 17.2      |
| 50°-60°   | 1116.4 | 15.8      |
| 60°-70°   | 900.4  | 12.7      |
| 70°-80°   | 584.6  | 8.3       |
| 80°-90°   | 164.5  | 2.3       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1905.7 | 26.9      |
| 0°-40°    | 3092.5 | 43.7      |
| 0°-60°    | 5429.5 | 76.7      |
| 0°-90°    | 7079.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 7079.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | 22.5° | 45°  | 67.5° | 90°  | Flux |
|-----|------|-------|------|-------|------|------|
| 0°  | 2488 | 2488  | 2488 | 2488  | 2488 |      |
| 5°  | 2488 | 2471  | 2480 | 2476  | 2476 | 236  |
| 15° | 2367 | 2355  | 2377 | 2386  | 2391 | 667  |
| 25° | 2138 | 2138  | 2179 | 2196  | 2213 | 984  |
| 35° | 1825 | 1842  | 1902 | 1941  | 1972 | 1142 |
| 45° | 1476 | 1503  | 1582 | 1654  | 1698 | 1138 |
| 55° | 1108 | 1144  | 1247 | 1346  | 1394 | 991  |
| 65° | 742  | 785   | 910  | 1028  | 1079 | 733  |
| 75° | 378  | 448   | 590  | 662   | 669  | 403  |
| 85° | 84   | 140   | 152  | 149   | 144  | 102  |
| 90° | 0    | 0     | 0    | 0     | 0    |      |

TEST NUMBER: P982883

CATALOG NUMBER: 24CZ-LD5-75-UNV-L835-CD1-U

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 22.5°  | 45°    | 67.5°  | 90°    |
|-------|--------|--------|--------|--------|--------|
| 0°    | 2487.6 | 2487.6 | 2487.6 | 2487.6 | 2487.6 |
| 2.5°  | 2499.7 | 2480.4 | 2490.1 | 2485.3 | 2475.6 |
| 5°    | 2487.6 | 2470.8 | 2480.4 | 2475.6 | 2475.6 |
| 7.5°  | 2470.8 | 2453.9 | 2463.5 | 2463.5 | 2463.5 |
| 10°   | 2441.9 | 2427.4 | 2441.9 | 2441.9 | 2441.9 |
| 12.5° | 2408.1 | 2396.1 | 2413.0 | 2415.4 | 2420.2 |
| 15°   | 2367.2 | 2355.2 | 2376.9 | 2386.5 | 2391.3 |
| 17.5° | 2321.5 | 2311.8 | 2335.9 | 2347.9 | 2355.2 |
| 20°   | 2266.1 | 2258.8 | 2290.1 | 2302.2 | 2311.8 |
| 22.5° | 2203.5 | 2203.5 | 2234.7 | 2249.2 | 2266.1 |
| 25°   | 2138.4 | 2138.4 | 2179.4 | 2196.3 | 2213.1 |
| 27.5° | 2068.6 | 2071.1 | 2116.8 | 2140.9 | 2157.7 |
| 30°   | 1991.6 | 2001.2 | 2049.3 | 2078.2 | 2097.5 |
| 32.5° | 1909.7 | 1921.8 | 1977.1 | 2013.2 | 2037.3 |
| 35°   | 1825.4 | 1842.3 | 1902.5 | 1940.9 | 1972.3 |
| 37.5° | 1741.1 | 1762.8 | 1827.8 | 1871.1 | 1902.5 |
| 40°   | 1654.4 | 1678.5 | 1745.9 | 1796.4 | 1832.6 |
| 42.5° | 1565.3 | 1591.8 | 1666.4 | 1724.2 | 1767.6 |
| 45°   | 1476.2 | 1502.6 | 1582.1 | 1654.4 | 1697.8 |
| 47.5° | 1382.3 | 1413.6 | 1497.9 | 1582.1 | 1625.5 |
| 50°   | 1290.8 | 1324.5 | 1413.6 | 1505.1 | 1550.8 |
| 52.5° | 1199.3 | 1237.8 | 1331.7 | 1428.1 | 1473.8 |
| 55°   | 1107.7 | 1143.8 | 1247.4 | 1346.2 | 1394.3 |
| 57.5° | 1016.3 | 1054.8 | 1163.1 | 1266.7 | 1317.2 |
| 60°   | 924.8  | 965.7  | 1078.8 | 1187.2 | 1237.8 |
| 62.5° | 830.8  | 874.1  | 994.6  | 1107.7 | 1158.3 |
| 65°   | 741.7  | 785.1  | 910.3  | 1028.3 | 1078.8 |
| 67.5° | 650.2  | 698.4  | 828.4  | 948.8  | 1001.8 |
| 70°   | 558.7  | 611.7  | 748.9  | 869.3  | 922.3  |
| 72.5° | 467.2  | 527.4  | 667.1  | 787.5  | 826.0  |
| 75°   | 378.1  | 447.9  | 590.0  | 662.3  | 669.4  |
| 77.5° | 296.2  | 368.5  | 503.3  | 532.2  | 546.7  |
| 80°   | 216.7  | 296.2  | 378.1  | 414.2  | 411.8  |
| 82.5° | 144.5  | 226.3  | 272.2  | 277.0  | 272.2  |
| 85°   | 84.3   | 139.7  | 151.7  | 149.3  | 144.5  |
| 87.5° | 36.1   | 55.4   | 48.2   | 40.9   | 33.7   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP3-2508-516-6

Test Date: 09/03/2025

Luminaire Tested: 24CZ-LD5-65-S-UNV-L935-CD1-U

Data in this report applies to families of products including 24CZ-LD5-65-S-UNV-L935-CD1-U

### Test Information

Test Method: LM-79-2019  
 Report Number: SP3-2508-516-6  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP3 - 3M SPHERE  
 Measurement Geometry:  $4\pi$   
 Issue Date: 09/05/2025  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: Metalux  
 Catalog Number: **24CZ-LD5-65-S-UNV-L935-CD1-U**  
 Description: 2X4 CRUZE SB 6500LM 935 SMOOTH LENS

### Spectral Parameters

CCT (K): 3412  
 CIE  $u'$ : 0.2386  
 CIE  $v'$ : 0.5111  
 Duv: -0.0015  
 CIE x: 0.4087  
 CIE y: 0.3890  
 CIE z: 0.2023  
 Peak Wavelength (nm): 630  
 Dominant Wavelength (nm): 581  
 Purity: 39.41044  
 R<sub>f</sub>: 92.6  
 R<sub>g</sub>: 102

CRI (Ra): 96.3  
 R1: 99.2  
 R2: 97.9  
 R3: 94.7  
 R4: 96.6  
 R5: 98.4  
 R6: 96.1  
 R7: 95.6  
 R8: 92.0  
 R9: 78.4  
 R10: 93.0  
 R11: 94.5  
 R12: 81.5  
 R13: 99.0  
 R14: 95.8  
 R15: 96.7



### Test Conditions

Stabilization Time: 20M  
 Operation Time: 1H 20M  
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP3-2508-516-6

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | 3M SPHERE IN02505     | 7/1/2025         | 1/1/2026             |
| Power Meter                    | XITRON INXT2011006    | 1/20/2025        | 1/20/2026            |
| AC Power Source                | CHROMA 61604 IN6064A  | 10/22/2024       | 10/22/2025           |
| DC Power Source                | EYSIGHT N5770A IN0534 | 10/22/2024       | 10/22/2025           |
| Sphere Thermometer             | TANDD IN4036E         | 10/22/2024       | 10/22/2025           |
|                                |                       |                  |                      |

REPORT NUMBER: SP3-2508-516-6

**CIE 1931 Chromaticity Diagram**



**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP3-2508-516-6

### Photopic Flux vs. Wavelength



### Photopic Lumens: NR

| $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|
| 360               | 0                                      | NR                             | 490               | 112                                    | NR                             | 620               | 281                                    | NR                             | 750               | 6                                      | NR                             | 880               | 0                                      | NR                             |
| 365               | 0                                      | NR                             | 495               | 134                                    | NR                             | 625               | 286                                    | NR                             | 755               | 5                                      | NR                             | 885               | 0                                      | NR                             |
| 370               | 0                                      | NR                             | 500               | 157                                    | NR                             | 630               | 1000                                   | NR                             | 760               | 4                                      | NR                             | 890               | 0                                      | NR                             |
| 375               | 0                                      | NR                             | 505               | 178                                    | NR                             | 635               | 695                                    | NR                             | 765               | 4                                      | NR                             | 895               | 0                                      | NR                             |
| 380               | 0                                      | NR                             | 510               | 193                                    | NR                             | 640               | 181                                    | NR                             | 770               | 3                                      | NR                             | 900               | 0                                      | NR                             |
| 385               | 0                                      | NR                             | 515               | 206                                    | NR                             | 645               | 175                                    | NR                             | 775               | 3                                      | NR                             | 905               | 0                                      | NR                             |
| 390               | 0                                      | NR                             | 520               | 213                                    | NR                             | 650               | 156                                    | NR                             | 780               | 2                                      | NR                             | 910               | 0                                      | NR                             |
| 395               | 1                                      | NR                             | 525               | 219                                    | NR                             | 655               | 127                                    | NR                             | 785               | 2                                      | NR                             | 915               | 0                                      | NR                             |
| 400               | 2                                      | NR                             | 530               | 223                                    | NR                             | 660               | 108                                    | NR                             | 790               | 2                                      | NR                             | 920               | 0                                      | NR                             |
| 405               | 2                                      | NR                             | 535               | 226                                    | NR                             | 665               | 89                                     | NR                             | 795               | 2                                      | NR                             | 925               | 0                                      | NR                             |
| 410               | 4                                      | NR                             | 540               | 230                                    | NR                             | 670               | 84                                     | NR                             | 800               | 1                                      | NR                             | 930               | 0                                      | NR                             |
| 415               | 6                                      | NR                             | 545               | 235                                    | NR                             | 675               | 67                                     | NR                             | 805               | 1                                      | NR                             | 935               | 0                                      | NR                             |
| 420               | 11                                     | NR                             | 550               | 239                                    | NR                             | 680               | 57                                     | NR                             | 810               | 1                                      | NR                             | 940               | 0                                      | NR                             |
| 425               | 19                                     | NR                             | 555               | 243                                    | NR                             | 685               | 50                                     | NR                             | 815               | 1                                      | NR                             | 945               | 0                                      | NR                             |
| 430               | 34                                     | NR                             | 560               | 248                                    | NR                             | 690               | 42                                     | NR                             | 820               | 1                                      | NR                             | 950               | 0                                      | NR                             |
| 435               | 60                                     | NR                             | 565               | 253                                    | NR                             | 695               | 36                                     | NR                             | 825               | 1                                      | NR                             | 955               | 0                                      | NR                             |
| 440               | 106                                    | NR                             | 570               | 256                                    | NR                             | 700               | 31                                     | NR                             | 830               | 0                                      | NR                             | 960               | 0                                      | NR                             |
| 445               | 193                                    | NR                             | 575               | 260                                    | NR                             | 705               | 26                                     | NR                             | 835               | 0                                      | NR                             | 965               | 0                                      | NR                             |
| 450               | 283                                    | NR                             | 580               | 263                                    | NR                             | 710               | 22                                     | NR                             | 840               | 0                                      | NR                             | 970               | 0                                      | NR                             |
| 455               | 234                                    | NR                             | 585               | 266                                    | NR                             | 715               | 19                                     | NR                             | 845               | 0                                      | NR                             | 975               | 0                                      | NR                             |
| 460               | 157                                    | NR                             | 590               | 267                                    | NR                             | 720               | 16                                     | NR                             | 850               | 0                                      | NR                             | 980               | 0                                      | NR                             |
| 465               | 134                                    | NR                             | 595               | 266                                    | NR                             | 725               | 14                                     | NR                             | 855               | 0                                      | NR                             | 985               | 0                                      | NR                             |
| 470               | 107                                    | NR                             | 600               | 268                                    | NR                             | 730               | 12                                     | NR                             | 860               | 0                                      | NR                             | 990               | 0                                      | NR                             |
| 475               | 85                                     | NR                             | 605               | 269                                    | NR                             | 735               | 10                                     | NR                             | 865               | 0                                      | NR                             | 995               | 0                                      | NR                             |
| 480               | 85                                     | NR                             | 610               | 309                                    | NR                             | 740               | 8                                      | NR                             | 870               | 0                                      | NR                             | 1000              | 0                                      | NR                             |
| 485               | 96                                     | NR                             | 615               | 345                                    | NR                             | 745               | 7                                      | NR                             | 875               | 0                                      | NR                             |                   |                                        |                                |

REPORT NUMBER: SP3-2508-516-6

### Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.61

| λ (nm) | Power W <sup>λ</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>λ</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>λ</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>λ</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>λ</sup> /nm | Lumens (Φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360    | 0                        | NR            | 490    | 112                      | NR            | 620    | 281                      | NR            | 750    | 6                        | NR            | 880    | 0                        | NR            |
| 365    | 0                        | NR            | 495    | 134                      | NR            | 625    | 286                      | NR            | 755    | 5                        | NR            | 885    | 0                        | NR            |
| 370    | 0                        | NR            | 500    | 157                      | NR            | 630    | 1000                     | NR            | 760    | 4                        | NR            | 890    | 0                        | NR            |
| 375    | 0                        | NR            | 505    | 178                      | NR            | 635    | 695                      | NR            | 765    | 4                        | NR            | 895    | 0                        | NR            |
| 380    | 0                        | NR            | 510    | 193                      | NR            | 640    | 181                      | NR            | 770    | 3                        | NR            | 900    | 0                        | NR            |
| 385    | 0                        | NR            | 515    | 206                      | NR            | 645    | 175                      | NR            | 775    | 3                        | NR            | 905    | 0                        | NR            |
| 390    | 0                        | NR            | 520    | 213                      | NR            | 650    | 156                      | NR            | 780    | 2                        | NR            | 910    | 0                        | NR            |
| 395    | 1                        | NR            | 525    | 219                      | NR            | 655    | 127                      | NR            | 785    | 2                        | NR            | 915    | 0                        | NR            |
| 400    | 2                        | NR            | 530    | 223                      | NR            | 660    | 108                      | NR            | 790    | 2                        | NR            | 920    | 0                        | NR            |
| 405    | 2                        | NR            | 535    | 226                      | NR            | 665    | 89                       | NR            | 795    | 2                        | NR            | 925    | 0                        | NR            |
| 410    | 4                        | NR            | 540    | 230                      | NR            | 670    | 84                       | NR            | 800    | 1                        | NR            | 930    | 0                        | NR            |
| 415    | 6                        | NR            | 545    | 235                      | NR            | 675    | 67                       | NR            | 805    | 1                        | NR            | 935    | 0                        | NR            |
| 420    | 11                       | NR            | 550    | 239                      | NR            | 680    | 57                       | NR            | 810    | 1                        | NR            | 940    | 0                        | NR            |
| 425    | 19                       | NR            | 555    | 243                      | NR            | 685    | 50                       | NR            | 815    | 1                        | NR            | 945    | 0                        | NR            |
| 430    | 34                       | NR            | 560    | 248                      | NR            | 690    | 42                       | NR            | 820    | 1                        | NR            | 950    | 0                        | NR            |
| 435    | 60                       | NR            | 565    | 253                      | NR            | 695    | 36                       | NR            | 825    | 1                        | NR            | 955    | 0                        | NR            |
| 440    | 106                      | NR            | 570    | 256                      | NR            | 700    | 31                       | NR            | 830    | 0                        | NR            | 960    | 0                        | NR            |
| 445    | 193                      | NR            | 575    | 260                      | NR            | 705    | 26                       | NR            | 835    | 0                        | NR            | 965    | 0                        | NR            |
| 450    | 283                      | NR            | 580    | 263                      | NR            | 710    | 22                       | NR            | 840    | 0                        | NR            | 970    | 0                        | NR            |
| 455    | 234                      | NR            | 585    | 266                      | NR            | 715    | 19                       | NR            | 845    | 0                        | NR            | 975    | 0                        | NR            |
| 460    | 157                      | NR            | 590    | 267                      | NR            | 720    | 16                       | NR            | 850    | 0                        | NR            | 980    | 0                        | NR            |
| 465    | 134                      | NR            | 595    | 266                      | NR            | 725    | 14                       | NR            | 855    | 0                        | NR            | 985    | 0                        | NR            |
| 470    | 107                      | NR            | 600    | 268                      | NR            | 730    | 12                       | NR            | 860    | 0                        | NR            | 990    | 0                        | NR            |
| 475    | 85                       | NR            | 605    | 269                      | NR            | 735    | 10                       | NR            | 865    | 0                        | NR            | 995    | 0                        | NR            |
| 480    | 85                       | NR            | 610    | 309                      | NR            | 740    | 8                        | NR            | 870    | 0                        | NR            | 1000   | 0                        | NR            |
| 485    | 96                       | NR            | 615    | 345                      | NR            | 745    | 7                        | NR            | 875    | 0                        | NR            |        |                          |               |

REPORT NUMBER: SP3-2508-516-6

### Melanopic Flux vs. Wavelength


**Melanopic Lumens: NR**
**M/P: 3.24**

| $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|
| 360               | 0                                      | NR                             | 490               | 112                                    | NR                             | 620               | 281                                    | NR                             | 750               | 6                                      | NR                             | 880               | 0                                      | NR                             |
| 365               | 0                                      | NR                             | 495               | 134                                    | NR                             | 625               | 286                                    | NR                             | 755               | 5                                      | NR                             | 885               | 0                                      | NR                             |
| 370               | 0                                      | NR                             | 500               | 157                                    | NR                             | 630               | 1000                                   | NR                             | 760               | 4                                      | NR                             | 890               | 0                                      | NR                             |
| 375               | 0                                      | NR                             | 505               | 178                                    | NR                             | 635               | 695                                    | NR                             | 765               | 4                                      | NR                             | 895               | 0                                      | NR                             |
| 380               | 0                                      | NR                             | 510               | 193                                    | NR                             | 640               | 181                                    | NR                             | 770               | 3                                      | NR                             | 900               | 0                                      | NR                             |
| 385               | 0                                      | NR                             | 515               | 206                                    | NR                             | 645               | 175                                    | NR                             | 775               | 3                                      | NR                             | 905               | 0                                      | NR                             |
| 390               | 0                                      | NR                             | 520               | 213                                    | NR                             | 650               | 156                                    | NR                             | 780               | 2                                      | NR                             | 910               | 0                                      | NR                             |
| 395               | 1                                      | NR                             | 525               | 219                                    | NR                             | 655               | 127                                    | NR                             | 785               | 2                                      | NR                             | 915               | 0                                      | NR                             |
| 400               | 2                                      | NR                             | 530               | 223                                    | NR                             | 660               | 108                                    | NR                             | 790               | 2                                      | NR                             | 920               | 0                                      | NR                             |
| 405               | 2                                      | NR                             | 535               | 226                                    | NR                             | 665               | 89                                     | NR                             | 795               | 2                                      | NR                             | 925               | 0                                      | NR                             |
| 410               | 4                                      | NR                             | 540               | 230                                    | NR                             | 670               | 84                                     | NR                             | 800               | 1                                      | NR                             | 930               | 0                                      | NR                             |
| 415               | 6                                      | NR                             | 545               | 235                                    | NR                             | 675               | 67                                     | NR                             | 805               | 1                                      | NR                             | 935               | 0                                      | NR                             |
| 420               | 11                                     | NR                             | 550               | 239                                    | NR                             | 680               | 57                                     | NR                             | 810               | 1                                      | NR                             | 940               | 0                                      | NR                             |
| 425               | 19                                     | NR                             | 555               | 243                                    | NR                             | 685               | 50                                     | NR                             | 815               | 1                                      | NR                             | 945               | 0                                      | NR                             |
| 430               | 34                                     | NR                             | 560               | 248                                    | NR                             | 690               | 42                                     | NR                             | 820               | 1                                      | NR                             | 950               | 0                                      | NR                             |
| 435               | 60                                     | NR                             | 565               | 253                                    | NR                             | 695               | 36                                     | NR                             | 825               | 1                                      | NR                             | 955               | 0                                      | NR                             |
| 440               | 106                                    | NR                             | 570               | 256                                    | NR                             | 700               | 31                                     | NR                             | 830               | 0                                      | NR                             | 960               | 0                                      | NR                             |
| 445               | 193                                    | NR                             | 575               | 260                                    | NR                             | 705               | 26                                     | NR                             | 835               | 0                                      | NR                             | 965               | 0                                      | NR                             |
| 450               | 283                                    | NR                             | 580               | 263                                    | NR                             | 710               | 22                                     | NR                             | 840               | 0                                      | NR                             | 970               | 0                                      | NR                             |
| 455               | 234                                    | NR                             | 585               | 266                                    | NR                             | 715               | 19                                     | NR                             | 845               | 0                                      | NR                             | 975               | 0                                      | NR                             |
| 460               | 157                                    | NR                             | 590               | 267                                    | NR                             | 720               | 16                                     | NR                             | 850               | 0                                      | NR                             | 980               | 0                                      | NR                             |
| 465               | 134                                    | NR                             | 595               | 266                                    | NR                             | 725               | 14                                     | NR                             | 855               | 0                                      | NR                             | 985               | 0                                      | NR                             |
| 470               | 107                                    | NR                             | 600               | 268                                    | NR                             | 730               | 12                                     | NR                             | 860               | 0                                      | NR                             | 990               | 0                                      | NR                             |
| 475               | 85                                     | NR                             | 605               | 269                                    | NR                             | 735               | 10                                     | NR                             | 865               | 0                                      | NR                             | 995               | 0                                      | NR                             |
| 480               | 85                                     | NR                             | 610               | 309                                    | NR                             | 740               | 8                                      | NR                             | 870               | 0                                      | NR                             | 1000              | 0                                      | NR                             |
| 485               | 96                                     | NR                             | 615               | 345                                    | NR                             | 745               | 7                                      | NR                             | 875               | 0                                      | NR                             |                   |                                        |                                |

REPORT NUMBER: SP3-2508-516-6

TM-30-18

### Summary

$R_f = 92.6$   
 $R_g = 102$   
 $\text{CIE } R_a = 96.3$   
 $R_9 = 78.4$



### Color Vector Graphics



**Individual Sample Fidelity Index ( $R_{fi}$ )**

|            |            |             |            |
|------------|------------|-------------|------------|
| CES01 = 86 | CES26 = 94 | CES51 = 97  | CES76 = 88 |
| CES02 = 63 | CES27 = 93 | CES52 = 96  | CES77 = 88 |
| CES03 = 32 | CES28 = 96 | CES53 = 95  | CES78 = 84 |
| CES04 = 70 | CES29 = 95 | CES54 = 95  | CES79 = 92 |
| CES05 = 50 | CES30 = 96 | CES55 = 95  | CES80 = 92 |
| CES06 = 51 | CES31 = 95 | CES56 = 98  | CES81 = 77 |
| CES07 = 43 | CES32 = 87 | CES57 = 98  | CES82 = 96 |
| CES08 = 42 | CES33 = 97 | CES58 = 98  | CES83 = 95 |
| CES09 = 29 | CES34 = 93 | CES59 = 100 | CES84 = 95 |
| CES10 = 75 | CES35 = 96 | CES60 = 94  | CES85 = 82 |
| CES11 = 58 | CES36 = 84 | CES61 = 95  | CES86 = 84 |
| CES12 = 64 | CES37 = 93 | CES62 = 90  | CES87 = 92 |
| CES13 = 44 | CES38 = 91 | CES63 = 95  | CES88 = 99 |
| CES14 = 74 | CES39 = 98 | CES64 = 95  | CES89 = 86 |
| CES15 = 72 | CES40 = 96 | CES65 = 92  | CES90 = 98 |
| CES16 = 48 | CES41 = 97 | CES66 = 93  | CES91 = 77 |
| CES17 = 49 | CES42 = 90 | CES67 = 92  | CES92 = 81 |
| CES18 = 56 | CES43 = 91 | CES68 = 91  | CES93 = 88 |
| CES19 = 71 | CES44 = 99 | CES69 = 92  | CES94 = 78 |
| CES20 = 67 | CES45 = 94 | CES70 = 89  | CES95 = 86 |
| CES21 = 86 | CES46 = 95 | CES71 = 85  | CES96 = 93 |
| CES22 = 78 | CES47 = 90 | CES72 = 95  | CES97 = 93 |
| CES23 = 91 | CES48 = 96 | CES73 = 84  | CES98 = 96 |
| CES24 = 90 | CES49 = 93 | CES74 = 91  | CES99 = 97 |
| CES25 = 71 | CES50 = 97 | CES75 = 86  |            |



Color Rendition by Hue-Angle Bin



**Measure Comparisons**



(END OF REPORT)