

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: METALUX

Report Number: P982894

Luminaire Tested: 24CZ-LD5-55-UNV-L840-CD1-U

Issue Date: 04/23/2025

**Test Information**

Test Method: LM-79-2019  
Report Number: P982894  
Test Lab: INNOVATION CENTER(P3)  
Issue Date: 04/23/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: METALUX  
Catalog Number: 24CZ-LD5-55-UNV-L840-CD1-U  
Description: METALUX CRUZE 2x4 5500LM PACKAGE 80CRI 4000K TROFFER STANDARD LENS  
Light Source: 4000K CCT, 80 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5361.0 lumens  
Efficiency: N/A  
Efficacy: 123.2 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.26 / 1.35  
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')  
CIE Type: Direct

Input Watts (W): 43.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT

TEST NUMBER: P982894

CATALOG NUMBER: 24CZ-LD5-55-UNV-L840-CD1-U

### Luminous Intensity Polar Plot



TEST NUMBER: P982894

CATALOG NUMBER: 24CZ-LD5-55-UNV-L840-CD1-U

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 108 | 103 | 99  | 95  | 106 | 101 | 97  | 93  | 97  | 93  | 90  |  | 93  | 90  | 88  |  | 89  |
| 2   | 98  | 90  | 83  | 77  | 96  | 88  | 81  | 76  | 84  | 79  | 74  |  | 81  | 76  | 72  |  | 78  |
| 3   | 89  | 79  | 70  | 63  | 87  | 77  | 69  | 63  | 74  | 67  | 62  |  | 71  | 65  | 61  |  | 69  |
| 4   | 82  | 69  | 60  | 54  | 79  | 68  | 60  | 53  | 66  | 58  | 52  |  | 63  | 57  | 52  |  | 61  |
| 5   | 75  | 62  | 53  | 46  | 73  | 61  | 52  | 46  | 59  | 51  | 45  |  | 57  | 50  | 45  |  | 55  |
| 6   | 69  | 56  | 47  | 40  | 67  | 55  | 46  | 40  | 53  | 45  | 40  |  | 51  | 44  | 39  |  | 50  |
| 7   | 64  | 51  | 42  | 35  | 63  | 50  | 41  | 35  | 48  | 41  | 35  |  | 47  | 40  | 35  |  | 45  |
| 8   | 60  | 46  | 38  | 32  | 58  | 45  | 37  | 32  | 44  | 37  | 31  |  | 43  | 36  | 31  |  | 42  |
| 9   | 56  | 42  | 34  | 28  | 55  | 42  | 34  | 28  | 41  | 33  | 28  |  | 40  | 33  | 28  |  | 39  |
| 10  | 52  | 39  | 31  | 26  | 51  | 39  | 31  | 26  | 38  | 31  | 26  |  | 37  | 30  | 26  |  | 36  |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°   | 45°  | 90°  |
|-----|------|------|------|
| 0°  | 2535 | 2535 | 2535 |
| 5°  | 2544 | 2537 | 2532 |
| 10° | 2527 | 2527 | 2527 |
| 15° | 2497 | 2507 | 2523 |
| 20° | 2457 | 2483 | 2507 |
| 25° | 2404 | 2450 | 2488 |
| 30° | 2343 | 2411 | 2468 |
| 35° | 2271 | 2367 | 2453 |
| 40° | 2201 | 2322 | 2438 |
| 45° | 2127 | 2280 | 2447 |
| 50° | 2046 | 2241 | 2458 |
| 55° | 1968 | 2216 | 2477 |
| 60° | 1884 | 2199 | 2523 |
| 65° | 1788 | 2195 | 2601 |
| 70° | 1664 | 2231 | 2748 |
| 75° | 1488 | 2323 | 2636 |
| 80° | 1272 | 2218 | 2417 |
| 85° | 985  | 1774 | 1689 |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
Vertical Angle: 72.5°  
Luminance: 2799 cd/sqm

TEST NUMBER: P982894

CATALOG NUMBER: 24CZ-LD5-55-UNV-L840-CD1-U

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 178.2  | 3.3       |
| 10°-20°   | 507.1  | 9.5       |
| 20°-30°   | 758.0  | 14.1      |
| 30°-40°   | 898.8  | 16.8      |
| 40°-50°   | 924.3  | 17.2      |
| 50°-60°   | 845.5  | 15.8      |
| 60°-70°   | 681.9  | 12.7      |
| 70°-80°   | 442.7  | 8.3       |
| 80°-90°   | 124.6  | 2.3       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1443.2 | 26.9      |
| 0°-40°    | 2342.0 | 43.7      |
| 0°-60°    | 4111.8 | 76.7      |
| 0°-90°    | 5361.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 5361.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | 22.5° | 45°  | 67.5° | 90°  | Flux |
|-----|------|-------|------|-------|------|------|
| 0°  | 1884 | 1884  | 1884 | 1884  | 1884 |      |
| 5°  | 1884 | 1871  | 1878 | 1875  | 1875 | 179  |
| 15° | 1793 | 1784  | 1800 | 1807  | 1811 | 505  |
| 25° | 1620 | 1620  | 1650 | 1663  | 1676 | 746  |
| 35° | 1382 | 1395  | 1441 | 1470  | 1494 | 865  |
| 45° | 1118 | 1138  | 1198 | 1253  | 1286 | 862  |
| 55° | 839  | 866   | 945  | 1020  | 1056 | 750  |
| 65° | 562  | 595   | 689  | 779   | 817  | 555  |
| 75° | 286  | 339   | 447  | 502   | 507  | 305  |
| 85° | 64   | 106   | 115  | 113   | 109  | 77   |
| 90° | 0    | 0     | 0    | 0     | 0    |      |

TEST NUMBER: P982894

CATALOG NUMBER: 24CZ-LD5-55-UNV-L840-CD1-U

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 22.5°  | 45°    | 67.5°  | 90°    |
|-------|--------|--------|--------|--------|--------|
| 0°    | 1883.9 | 1883.9 | 1883.9 | 1883.9 | 1883.9 |
| 2.5°  | 1893.1 | 1878.5 | 1885.8 | 1882.1 | 1874.8 |
| 5°    | 1883.9 | 1871.2 | 1878.5 | 1874.8 | 1874.8 |
| 7.5°  | 1871.2 | 1858.4 | 1865.7 | 1865.7 | 1865.7 |
| 10°   | 1849.3 | 1838.3 | 1849.3 | 1849.3 | 1849.3 |
| 12.5° | 1823.7 | 1814.6 | 1827.4 | 1829.2 | 1832.9 |
| 15°   | 1792.7 | 1783.6 | 1800.0 | 1807.3 | 1811.0 |
| 17.5° | 1758.1 | 1750.8 | 1769.0 | 1778.1 | 1783.6 |
| 20°   | 1716.1 | 1710.6 | 1734.3 | 1743.5 | 1750.8 |
| 22.5° | 1668.7 | 1668.7 | 1692.4 | 1703.3 | 1716.1 |
| 25°   | 1619.5 | 1619.5 | 1650.5 | 1663.3 | 1676.0 |
| 27.5° | 1566.6 | 1568.4 | 1603.1 | 1621.3 | 1634.1 |
| 30°   | 1508.3 | 1515.6 | 1552.0 | 1573.9 | 1588.5 |
| 32.5° | 1446.2 | 1455.4 | 1497.3 | 1524.6 | 1542.9 |
| 35°   | 1382.4 | 1395.2 | 1440.8 | 1469.9 | 1493.7 |
| 37.5° | 1318.5 | 1335.0 | 1384.2 | 1417.0 | 1440.8 |
| 40°   | 1252.9 | 1271.2 | 1322.2 | 1360.5 | 1387.9 |
| 42.5° | 1185.4 | 1205.5 | 1262.0 | 1305.8 | 1338.6 |
| 45°   | 1117.9 | 1138.0 | 1198.2 | 1252.9 | 1285.8 |
| 47.5° | 1046.8 | 1070.6 | 1134.4 | 1198.2 | 1231.0 |
| 50°   | 977.5  | 1003.1 | 1070.6 | 1139.8 | 1174.5 |
| 52.5° | 908.2  | 937.4  | 1008.5 | 1081.5 | 1116.1 |
| 55°   | 838.9  | 866.2  | 944.7  | 1019.5 | 1056.0 |
| 57.5° | 769.6  | 798.8  | 880.8  | 959.3  | 997.6  |
| 60°   | 700.3  | 731.3  | 817.0  | 899.1  | 937.4  |
| 62.5° | 629.2  | 662.0  | 753.2  | 838.9  | 877.2  |
| 65°   | 561.7  | 594.6  | 689.4  | 778.7  | 817.0  |
| 67.5° | 492.4  | 528.9  | 627.3  | 718.5  | 758.7  |
| 70°   | 423.1  | 463.2  | 567.2  | 658.3  | 698.5  |
| 72.5° | 353.8  | 399.4  | 505.2  | 596.4  | 625.6  |
| 75°   | 286.3  | 339.2  | 446.8  | 501.5  | 507.0  |
| 77.5° | 224.3  | 279.0  | 381.2  | 403.1  | 414.0  |
| 80°   | 164.1  | 224.3  | 286.3  | 313.7  | 311.9  |
| 82.5° | 109.4  | 171.4  | 206.1  | 209.8  | 206.1  |
| 85°   | 63.8   | 105.8  | 114.9  | 113.1  | 109.4  |
| 87.5° | 27.3   | 41.9   | 36.5   | 31.0   | 25.5   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP3-2508-516-7

Test Date: 09/03/2025

Luminaire Tested: 24CZ-LD5-65-S-UNV-L940-CD1-U

Data in this report applies to families of products including 24CZ-LD5-65-S-UNV-L940-CD1-U

### Test Information

Test Method: LM-79-2019  
 Report Number: SP3-2508-516-7  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP3 - 3M SPHERE  
 Measurement Geometry:  $4\pi$   
 Issue Date: 09/05/2025  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: Metalux  
 Catalog Number: **24CZ-LD5-65-S-UNV-L940-CD1-U**  
 Description: 2X4 CRUZE SB 6500LM 940 SMOOTH LENS

### Spectral Parameters

CCT (K): 3955  
 CIE  $u'$ : 0.2264  
 CIE  $v'$ : 0.5014  
 Duv: -0.0009  
 CIE x: 0.3818  
 CIE y: 0.3758  
 CIE z: 0.2424  
 Peak Wavelength (nm): 630  
 Dominant Wavelength (nm): 579  
 Purity: 27.35334  
 R<sub>f</sub>: 90.3  
 R<sub>g</sub>: 99.3

CRI (Ra): 93.6  
 R1: 95.0  
 R2: 96.2  
 R3: 95.3  
 R4: 94.7  
 R5: 93.8  
 R6: 93.5  
 R7: 94.0  
 R8: 86.7  
 R9: 65.5  
 R10: 88.9  
 R11: 94.8  
 R12: 71.7  
 R13: 95.4  
 R14: 96.7  
 R15: 92.2



### Test Conditions

Stabilization Time: 22M  
 Operation Time: 1H 22M  
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP3-2508-516-7

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | 3M SPHERE IN02505     | 7/1/2025         | 1/1/2026             |
| Power Meter                    | XITRON INXT2011006    | 1/20/2025        | 1/20/2026            |
| AC Power Source                | CHROMA 61604 IN6064A  | 10/22/2024       | 10/22/2025           |
| DC Power Source                | EYSIGHT N5770A IN0534 | 10/22/2024       | 10/22/2025           |
| Sphere Thermometer             | TANDD IN4036E         | 10/22/2024       | 10/22/2025           |
|                                |                       |                  |                      |

REPORT NUMBER: SP3-2508-516-7

**CIE 1931 Chromaticity Diagram**



**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP3-2508-516-7

### Photopic Flux vs. Wavelength



### Photopic Lumens: NR

| λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) |
|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|
| 360       | 0                           | NR               | 490       | 171                         | NR               | 620       | 355                         | NR               | 750       | 8                           | NR               | 880       | 0                           | NR               |
| 365       | 0                           | NR               | 495       | 199                         | NR               | 625       | 352                         | NR               | 755       | 7                           | NR               | 885       | 0                           | NR               |
| 370       | 0                           | NR               | 500       | 230                         | NR               | 630       | 1000                        | NR               | 760       | 6                           | NR               | 890       | 0                           | NR               |
| 375       | 0                           | NR               | 505       | 257                         | NR               | 635       | 711                         | NR               | 765       | 5                           | NR               | 895       | 0                           | NR               |
| 380       | 0                           | NR               | 510       | 278                         | NR               | 640       | 235                         | NR               | 770       | 4                           | NR               | 900       | 0                           | NR               |
| 385       | 0                           | NR               | 515       | 295                         | NR               | 645       | 222                         | NR               | 775       | 4                           | NR               | 905       | 0                           | NR               |
| 390       | 1                           | NR               | 520       | 305                         | NR               | 650       | 198                         | NR               | 780       | 3                           | NR               | 910       | 0                           | NR               |
| 395       | 2                           | NR               | 525       | 313                         | NR               | 655       | 165                         | NR               | 785       | 3                           | NR               | 915       | 0                           | NR               |
| 400       | 3                           | NR               | 530       | 318                         | NR               | 660       | 142                         | NR               | 790       | 2                           | NR               | 920       | 0                           | NR               |
| 405       | 4                           | NR               | 535       | 323                         | NR               | 665       | 120                         | NR               | 795       | 2                           | NR               | 925       | 0                           | NR               |
| 410       | 6                           | NR               | 540       | 327                         | NR               | 670       | 110                         | NR               | 800       | 2                           | NR               | 930       | 0                           | NR               |
| 415       | 9                           | NR               | 545       | 333                         | NR               | 675       | 91                          | NR               | 805       | 2                           | NR               | 935       | 0                           | NR               |
| 420       | 15                          | NR               | 550       | 339                         | NR               | 680       | 77                          | NR               | 810       | 1                           | NR               | 940       | 0                           | NR               |
| 425       | 27                          | NR               | 555       | 343                         | NR               | 685       | 67                          | NR               | 815       | 1                           | NR               | 945       | 0                           | NR               |
| 430       | 48                          | NR               | 560       | 349                         | NR               | 690       | 57                          | NR               | 820       | 1                           | NR               | 950       | 0                           | NR               |
| 435       | 87                          | NR               | 565       | 355                         | NR               | 695       | 49                          | NR               | 825       | 1                           | NR               | 955       | 0                           | NR               |
| 440       | 155                         | NR               | 570       | 358                         | NR               | 700       | 42                          | NR               | 830       | 1                           | NR               | 960       | 0                           | NR               |
| 445       | 291                         | NR               | 575       | 363                         | NR               | 705       | 36                          | NR               | 835       | 1                           | NR               | 965       | 0                           | NR               |
| 450       | 475                         | NR               | 580       | 365                         | NR               | 710       | 30                          | NR               | 840       | 1                           | NR               | 970       | 0                           | NR               |
| 455       | 466                         | NR               | 585       | 367                         | NR               | 715       | 26                          | NR               | 845       | 1                           | NR               | 975       | 0                           | NR               |
| 460       | 308                         | NR               | 590       | 367                         | NR               | 720       | 22                          | NR               | 850       | 0                           | NR               | 980       | 0                           | NR               |
| 465       | 246                         | NR               | 595       | 364                         | NR               | 725       | 19                          | NR               | 855       | 0                           | NR               | 985       | 0                           | NR               |
| 470       | 202                         | NR               | 600       | 363                         | NR               | 730       | 16                          | NR               | 860       | 0                           | NR               | 990       | 0                           | NR               |
| 475       | 152                         | NR               | 605       | 361                         | NR               | 735       | 14                          | NR               | 865       | 0                           | NR               | 995       | 0                           | NR               |
| 480       | 140                         | NR               | 610       | 391                         | NR               | 740       | 11                          | NR               | 870       | 0                           | NR               | 1000      | 0                           | NR               |
| 485       | 152                         | NR               | 615       | 418                         | NR               | 745       | 10                          | NR               | 875       | 0                           | NR               |           |                             |                  |

REPORT NUMBER: SP3-2508-516-7

### Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.77

| $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 0                                    | NR                             | 490               | 171                                  | NR                             | 620               | 355                                  | NR                             | 750               | 8                                    | NR                             | 880               | 0                                    | NR                             |
| 365               | 0                                    | NR                             | 495               | 199                                  | NR                             | 625               | 352                                  | NR                             | 755               | 7                                    | NR                             | 885               | 0                                    | NR                             |
| 370               | 0                                    | NR                             | 500               | 230                                  | NR                             | 630               | 1000                                 | NR                             | 760               | 6                                    | NR                             | 890               | 0                                    | NR                             |
| 375               | 0                                    | NR                             | 505               | 257                                  | NR                             | 635               | 711                                  | NR                             | 765               | 5                                    | NR                             | 895               | 0                                    | NR                             |
| 380               | 0                                    | NR                             | 510               | 278                                  | NR                             | 640               | 235                                  | NR                             | 770               | 4                                    | NR                             | 900               | 0                                    | NR                             |
| 385               | 0                                    | NR                             | 515               | 295                                  | NR                             | 645               | 222                                  | NR                             | 775               | 4                                    | NR                             | 905               | 0                                    | NR                             |
| 390               | 1                                    | NR                             | 520               | 305                                  | NR                             | 650               | 198                                  | NR                             | 780               | 3                                    | NR                             | 910               | 0                                    | NR                             |
| 395               | 2                                    | NR                             | 525               | 313                                  | NR                             | 655               | 165                                  | NR                             | 785               | 3                                    | NR                             | 915               | 0                                    | NR                             |
| 400               | 3                                    | NR                             | 530               | 318                                  | NR                             | 660               | 142                                  | NR                             | 790               | 2                                    | NR                             | 920               | 0                                    | NR                             |
| 405               | 4                                    | NR                             | 535               | 323                                  | NR                             | 665               | 120                                  | NR                             | 795               | 2                                    | NR                             | 925               | 0                                    | NR                             |
| 410               | 6                                    | NR                             | 540               | 327                                  | NR                             | 670               | 110                                  | NR                             | 800               | 2                                    | NR                             | 930               | 0                                    | NR                             |
| 415               | 9                                    | NR                             | 545               | 333                                  | NR                             | 675               | 91                                   | NR                             | 805               | 2                                    | NR                             | 935               | 0                                    | NR                             |
| 420               | 15                                   | NR                             | 550               | 339                                  | NR                             | 680               | 77                                   | NR                             | 810               | 1                                    | NR                             | 940               | 0                                    | NR                             |
| 425               | 27                                   | NR                             | 555               | 343                                  | NR                             | 685               | 67                                   | NR                             | 815               | 1                                    | NR                             | 945               | 0                                    | NR                             |
| 430               | 48                                   | NR                             | 560               | 349                                  | NR                             | 690               | 57                                   | NR                             | 820               | 1                                    | NR                             | 950               | 0                                    | NR                             |
| 435               | 87                                   | NR                             | 565               | 355                                  | NR                             | 695               | 49                                   | NR                             | 825               | 1                                    | NR                             | 955               | 0                                    | NR                             |
| 440               | 155                                  | NR                             | 570               | 358                                  | NR                             | 700               | 42                                   | NR                             | 830               | 1                                    | NR                             | 960               | 0                                    | NR                             |
| 445               | 291                                  | NR                             | 575               | 363                                  | NR                             | 705               | 36                                   | NR                             | 835               | 1                                    | NR                             | 965               | 0                                    | NR                             |
| 450               | 475                                  | NR                             | 580               | 365                                  | NR                             | 710               | 30                                   | NR                             | 840               | 1                                    | NR                             | 970               | 0                                    | NR                             |
| 455               | 466                                  | NR                             | 585               | 367                                  | NR                             | 715               | 26                                   | NR                             | 845               | 1                                    | NR                             | 975               | 0                                    | NR                             |
| 460               | 308                                  | NR                             | 590               | 367                                  | NR                             | 720               | 22                                   | NR                             | 850               | 0                                    | NR                             | 980               | 0                                    | NR                             |
| 465               | 246                                  | NR                             | 595               | 364                                  | NR                             | 725               | 19                                   | NR                             | 855               | 0                                    | NR                             | 985               | 0                                    | NR                             |
| 470               | 202                                  | NR                             | 600               | 363                                  | NR                             | 730               | 16                                   | NR                             | 860               | 0                                    | NR                             | 990               | 0                                    | NR                             |
| 475               | 152                                  | NR                             | 605               | 361                                  | NR                             | 735               | 14                                   | NR                             | 865               | 0                                    | NR                             | 995               | 0                                    | NR                             |
| 480               | 140                                  | NR                             | 610               | 391                                  | NR                             | 740               | 11                                   | NR                             | 870               | 0                                    | NR                             | 1000              | 0                                    | NR                             |
| 485               | 152                                  | NR                             | 615               | 418                                  | NR                             | 745               | 10                                   | NR                             | 875               | 0                                    | NR                             |                   |                                      |                                |

REPORT NUMBER: SP3-2508-516-7

### Melanopic Flux vs. Wavelength


**Melanopic Lumens: NR**
**M/P: 3.69**

| $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 0                                    | NR                             | 490               | 171                                  | NR                             | 620               | 355                                  | NR                             | 750               | 8                                    | NR                             | 880               | 0                                    | NR                             |
| 365               | 0                                    | NR                             | 495               | 199                                  | NR                             | 625               | 352                                  | NR                             | 755               | 7                                    | NR                             | 885               | 0                                    | NR                             |
| 370               | 0                                    | NR                             | 500               | 230                                  | NR                             | 630               | 1000                                 | NR                             | 760               | 6                                    | NR                             | 890               | 0                                    | NR                             |
| 375               | 0                                    | NR                             | 505               | 257                                  | NR                             | 635               | 711                                  | NR                             | 765               | 5                                    | NR                             | 895               | 0                                    | NR                             |
| 380               | 0                                    | NR                             | 510               | 278                                  | NR                             | 640               | 235                                  | NR                             | 770               | 4                                    | NR                             | 900               | 0                                    | NR                             |
| 385               | 0                                    | NR                             | 515               | 295                                  | NR                             | 645               | 222                                  | NR                             | 775               | 4                                    | NR                             | 905               | 0                                    | NR                             |
| 390               | 1                                    | NR                             | 520               | 305                                  | NR                             | 650               | 198                                  | NR                             | 780               | 3                                    | NR                             | 910               | 0                                    | NR                             |
| 395               | 2                                    | NR                             | 525               | 313                                  | NR                             | 655               | 165                                  | NR                             | 785               | 3                                    | NR                             | 915               | 0                                    | NR                             |
| 400               | 3                                    | NR                             | 530               | 318                                  | NR                             | 660               | 142                                  | NR                             | 790               | 2                                    | NR                             | 920               | 0                                    | NR                             |
| 405               | 4                                    | NR                             | 535               | 323                                  | NR                             | 665               | 120                                  | NR                             | 795               | 2                                    | NR                             | 925               | 0                                    | NR                             |
| 410               | 6                                    | NR                             | 540               | 327                                  | NR                             | 670               | 110                                  | NR                             | 800               | 2                                    | NR                             | 930               | 0                                    | NR                             |
| 415               | 9                                    | NR                             | 545               | 333                                  | NR                             | 675               | 91                                   | NR                             | 805               | 2                                    | NR                             | 935               | 0                                    | NR                             |
| 420               | 15                                   | NR                             | 550               | 339                                  | NR                             | 680               | 77                                   | NR                             | 810               | 1                                    | NR                             | 940               | 0                                    | NR                             |
| 425               | 27                                   | NR                             | 555               | 343                                  | NR                             | 685               | 67                                   | NR                             | 815               | 1                                    | NR                             | 945               | 0                                    | NR                             |
| 430               | 48                                   | NR                             | 560               | 349                                  | NR                             | 690               | 57                                   | NR                             | 820               | 1                                    | NR                             | 950               | 0                                    | NR                             |
| 435               | 87                                   | NR                             | 565               | 355                                  | NR                             | 695               | 49                                   | NR                             | 825               | 1                                    | NR                             | 955               | 0                                    | NR                             |
| 440               | 155                                  | NR                             | 570               | 358                                  | NR                             | 700               | 42                                   | NR                             | 830               | 1                                    | NR                             | 960               | 0                                    | NR                             |
| 445               | 291                                  | NR                             | 575               | 363                                  | NR                             | 705               | 36                                   | NR                             | 835               | 1                                    | NR                             | 965               | 0                                    | NR                             |
| 450               | 475                                  | NR                             | 580               | 365                                  | NR                             | 710               | 30                                   | NR                             | 840               | 1                                    | NR                             | 970               | 0                                    | NR                             |
| 455               | 466                                  | NR                             | 585               | 367                                  | NR                             | 715               | 26                                   | NR                             | 845               | 1                                    | NR                             | 975               | 0                                    | NR                             |
| 460               | 308                                  | NR                             | 590               | 367                                  | NR                             | 720               | 22                                   | NR                             | 850               | 0                                    | NR                             | 980               | 0                                    | NR                             |
| 465               | 246                                  | NR                             | 595               | 364                                  | NR                             | 725               | 19                                   | NR                             | 855               | 0                                    | NR                             | 985               | 0                                    | NR                             |
| 470               | 202                                  | NR                             | 600               | 363                                  | NR                             | 730               | 16                                   | NR                             | 860               | 0                                    | NR                             | 990               | 0                                    | NR                             |
| 475               | 152                                  | NR                             | 605               | 361                                  | NR                             | 735               | 14                                   | NR                             | 865               | 0                                    | NR                             | 995               | 0                                    | NR                             |
| 480               | 140                                  | NR                             | 610               | 391                                  | NR                             | 740               | 11                                   | NR                             | 870               | 0                                    | NR                             | 1000              | 0                                    | NR                             |
| 485               | 152                                  | NR                             | 615               | 418                                  | NR                             | 745               | 10                                   | NR                             | 875               | 0                                    | NR                             |                   |                                      |                                |


REPORT NUMBER: SP3-2508-516-7

TM-30-18





### Summary

$R_f = 90.3$   
 $R_g = 99.3$   
 $CIE R_a = 93.6$   
 $R_9 = 65.5$

### Spectral Power Distribution Comparison



### Color Vector Graphics




**Individual Sample Fidelity Index ( $R_{fi}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 93 | CES51 = 97 | CES76 = 85 |
| CES02 = 62 | CES27 = 90 | CES52 = 99 | CES77 = 87 |
| CES03 = 31 | CES28 = 95 | CES53 = 97 | CES78 = 82 |
| CES04 = 69 | CES29 = 96 | CES54 = 92 | CES79 = 93 |
| CES05 = 49 | CES30 = 89 | CES55 = 90 | CES80 = 92 |
| CES06 = 50 | CES31 = 97 | CES56 = 94 | CES81 = 80 |
| CES07 = 42 | CES32 = 89 | CES57 = 92 | CES82 = 96 |
| CES08 = 41 | CES33 = 98 | CES58 = 92 | CES83 = 96 |
| CES09 = 29 | CES34 = 93 | CES59 = 97 | CES84 = 93 |
| CES10 = 74 | CES35 = 95 | CES60 = 91 | CES85 = 80 |
| CES11 = 57 | CES36 = 77 | CES61 = 91 | CES86 = 84 |
| CES12 = 63 | CES37 = 94 | CES62 = 83 | CES87 = 91 |
| CES13 = 43 | CES38 = 83 | CES63 = 91 | CES88 = 98 |
| CES14 = 74 | CES39 = 99 | CES64 = 88 | CES89 = 85 |
| CES15 = 71 | CES40 = 98 | CES65 = 87 | CES90 = 96 |
| CES16 = 47 | CES41 = 96 | CES66 = 84 | CES91 = 70 |
| CES17 = 49 | CES42 = 92 | CES67 = 83 | CES92 = 76 |
| CES18 = 56 | CES43 = 93 | CES68 = 86 | CES93 = 85 |
| CES19 = 71 | CES44 = 99 | CES69 = 87 | CES94 = 76 |
| CES20 = 66 | CES45 = 97 | CES70 = 84 | CES95 = 81 |
| CES21 = 85 | CES46 = 97 | CES71 = 76 | CES96 = 92 |
| CES22 = 78 | CES47 = 94 | CES72 = 93 | CES97 = 95 |
| CES23 = 91 | CES48 = 89 | CES73 = 78 | CES98 = 95 |
| CES24 = 90 | CES49 = 96 | CES74 = 90 | CES99 = 93 |
| CES25 = 71 | CES50 = 98 | CES75 = 79 |            |



### Color Rendition by Hue-Angle Bin



**Measure Comparisons**



(END OF REPORT)