

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: METALUX

Report Number: P983054

Luminaire Tested: 24CZ-LD5-50-UNV-L850-HRP-CD1-U

Issue Date: 04/23/2025

**Test Information**

Test Method: LM-79-2019  
Report Number: P983054  
Test Lab: INNOVATION CENTER(P3)  
Issue Date: 04/23/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: METALUX  
Catalog Number: 24CZ-LD5-50-UNV-L850-HRP-CD1-U  
Description: METALUX CRUZE 2x4 5000LM PACKAGE 80CRI 5000K TROFFER LENS WITH HRP FILM INSERT  
Light Source: 5000K CCT, 80 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3880.0 lumens  
Efficiency: N/A  
Efficacy: 100.5 lumens/watt  
Spacing Criteria (0/90/45): 1.25 / 1.29 / 1.4  
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')  
CIE Type: Direct

Input Watts (W): 38.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT

TEST NUMBER: P983054

CATALOG NUMBER: 24CZ-LD5-50-UNV-L850-HRP-CD1-U

### Luminous Intensity Polar Plot



TEST NUMBER: P983054

CATALOG NUMBER: 24CZ-LD5-50-UNV-L850-HRP-CD1-U

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 |
| 1   | 108 | 103 | 99  | 95  | 105 | 101 | 97  | 93  | 97  | 93  | 90  | 93  | 90  | 87  | 89  | 87  | 85  |
| 2   | 98  | 89  | 82  | 76  | 95  | 87  | 81  | 75  | 84  | 78  | 74  | 81  | 76  | 72  | 77  | 74  | 70  |
| 3   | 89  | 78  | 70  | 63  | 86  | 76  | 69  | 62  | 73  | 67  | 61  | 71  | 65  | 60  | 68  | 63  | 59  |
| 4   | 81  | 69  | 60  | 53  | 79  | 68  | 59  | 52  | 65  | 58  | 52  | 63  | 56  | 51  | 60  | 55  | 50  |
| 5   | 75  | 61  | 52  | 45  | 72  | 60  | 52  | 45  | 58  | 50  | 44  | 56  | 49  | 44  | 54  | 48  | 43  |
| 6   | 69  | 55  | 46  | 39  | 67  | 54  | 45  | 39  | 52  | 45  | 39  | 51  | 44  | 38  | 49  | 43  | 38  |
| 7   | 64  | 50  | 41  | 35  | 62  | 49  | 41  | 34  | 48  | 40  | 34  | 46  | 39  | 34  | 45  | 38  | 34  |
| 8   | 59  | 45  | 37  | 31  | 58  | 45  | 36  | 31  | 43  | 36  | 31  | 42  | 35  | 30  | 41  | 35  | 30  |
| 9   | 55  | 42  | 33  | 28  | 54  | 41  | 33  | 28  | 40  | 33  | 27  | 39  | 32  | 27  | 38  | 32  | 27  |
| 10  | 52  | 38  | 30  | 25  | 51  | 38  | 30  | 25  | 37  | 30  | 25  | 36  | 29  | 25  | 35  | 29  | 25  |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°   | 45°  | 90°  |
|-----|------|------|------|
| 0°  | 1715 | 1715 | 1715 |
| 5°  | 1722 | 1719 | 1715 |
| 10° | 1717 | 1717 | 1717 |
| 15° | 1709 | 1716 | 1720 |
| 20° | 1697 | 1711 | 1721 |
| 25° | 1683 | 1703 | 1720 |
| 30° | 1663 | 1694 | 1720 |
| 35° | 1643 | 1687 | 1725 |
| 40° | 1620 | 1679 | 1731 |
| 45° | 1588 | 1670 | 1755 |
| 50° | 1548 | 1663 | 1788 |
| 55° | 1501 | 1665 | 1836 |
| 60° | 1436 | 1682 | 1905 |
| 65° | 1328 | 1699 | 2000 |
| 70° | 1196 | 1752 | 2125 |
| 75° | 1011 | 1806 | 1901 |
| 80° | 786  | 1545 | 1597 |
| 85° | 565  | 1051 | 923  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°

Vertical Angle: 72.5°

Luminance: 2149 cd/sqm

TEST NUMBER: P983054

CATALOG NUMBER: 24CZ-LD5-50-UNV-L850-HRP-CD1-U

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 120.8  | 3.1       |
| 10°-20°   | 347.0  | 8.9       |
| 20°-30°   | 527.7  | 13.6      |
| 30°-40°   | 641.1  | 16.5      |
| 40°-50°   | 676.6  | 17.4      |
| 50°-60°   | 635.8  | 16.4      |
| 60°-70°   | 523.4  | 13.5      |
| 70°-80°   | 329.7  | 8.5       |
| 80°-90°   | 77.9   | 2.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 995.5  | 25.7      |
| 0°-40°    | 1636.6 | 42.2      |
| 0°-60°    | 2949.0 | 76.0      |
| 0°-90°    | 3880.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 3880.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | 22.5° | 45°  | 67.5° | 90°  | Flux |
|-----|------|-------|------|-------|------|------|
| 0°  | 1275 | 1275  | 1275 | 1275  | 1275 |      |
| 5°  | 1275 | 1268  | 1273 | 1272  | 1270 | 121  |
| 15° | 1227 | 1222  | 1232 | 1235  | 1235 | 346  |
| 25° | 1134 | 1132  | 1147 | 1154  | 1158 | 522  |
| 35° | 1000 | 1006  | 1027 | 1040  | 1050 | 626  |
| 45° | 834  | 848   | 878  | 902   | 922  | 643  |
| 55° | 640  | 663   | 710  | 760   | 783  | 571  |
| 65° | 417  | 457   | 534  | 602   | 628  | 414  |
| 75° | 194  | 254   | 347  | 379   | 366  | 208  |
| 85° | 37   | 62    | 68   | 63    | 60   | 46   |
| 90° | 0    | 0     | 0    | 0     | 0    |      |

TEST NUMBER: P983054

CATALOG NUMBER: 24CZ-LD5-50-UNV-L850-HRP-CD1-U

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 22.5°  | 45°    | 67.5°  | 90°    |
|-------|--------|--------|--------|--------|--------|
| 0°    | 1274.8 | 1274.8 | 1274.8 | 1274.8 | 1274.8 |
| 2.5°  | 1279.8 | 1271.5 | 1276.5 | 1274.8 | 1269.8 |
| 5°    | 1274.8 | 1268.2 | 1273.1 | 1271.5 | 1269.8 |
| 7.5°  | 1268.2 | 1261.5 | 1266.5 | 1264.8 | 1264.8 |
| 10°   | 1256.6 | 1251.5 | 1256.6 | 1256.6 | 1256.6 |
| 12.5° | 1243.2 | 1238.3 | 1244.9 | 1246.5 | 1248.2 |
| 15°   | 1226.6 | 1221.6 | 1231.6 | 1234.9 | 1234.9 |
| 17.5° | 1206.6 | 1203.3 | 1213.3 | 1216.6 | 1220.0 |
| 20°   | 1185.1 | 1183.4 | 1195.0 | 1198.3 | 1201.7 |
| 22.5° | 1160.1 | 1160.1 | 1171.8 | 1175.1 | 1181.8 |
| 25°   | 1133.5 | 1131.8 | 1146.8 | 1153.5 | 1158.5 |
| 27.5° | 1103.6 | 1103.6 | 1120.2 | 1128.6 | 1133.5 |
| 30°   | 1070.4 | 1073.7 | 1090.3 | 1100.3 | 1107.0 |
| 32.5° | 1037.1 | 1040.5 | 1060.4 | 1072.0 | 1080.4 |
| 35°   | 1000.5 | 1005.6 | 1027.1 | 1040.5 | 1050.5 |
| 37.5° | 960.7  | 969.0  | 992.2  | 1007.2 | 1018.8 |
| 40°   | 922.4  | 929.1  | 955.7  | 972.3  | 985.6  |
| 42.5° | 879.2  | 890.9  | 917.5  | 937.4  | 952.4  |
| 45°   | 834.4  | 847.6  | 877.6  | 902.5  | 922.4  |
| 47.5° | 787.8  | 804.5  | 836.0  | 869.2  | 889.2  |
| 50°   | 739.7  | 757.9  | 794.4  | 834.4  | 854.3  |
| 52.5° | 691.4  | 711.4  | 751.3  | 797.8  | 819.4  |
| 55°   | 639.9  | 663.1  | 709.7  | 759.6  | 782.8  |
| 57.5° | 586.7  | 613.3  | 666.5  | 723.0  | 746.2  |
| 60°   | 533.5  | 561.8  | 624.9  | 681.4  | 708.0  |
| 62.5° | 478.7  | 510.2  | 578.4  | 643.2  | 668.2  |
| 65°   | 417.2  | 457.1  | 533.5  | 601.7  | 628.3  |
| 67.5° | 360.6  | 402.2  | 490.3  | 558.4  | 586.7  |
| 70°   | 304.1  | 352.3  | 445.4  | 513.6  | 540.1  |
| 72.5° | 247.6  | 304.1  | 395.6  | 465.3  | 480.3  |
| 75°   | 194.5  | 254.3  | 347.4  | 378.9  | 365.7  |
| 77.5° | 142.9  | 209.4  | 292.5  | 275.9  | 272.6  |
| 80°   | 101.4  | 166.2  | 199.4  | 201.1  | 206.1  |
| 82.5° | 64.8   | 123.0  | 129.7  | 131.3  | 133.0  |
| 85°   | 36.6   | 61.5   | 68.1   | 63.2   | 59.8   |
| 87.5° | 16.6   | 19.9   | 16.6   | 11.6   | 10.0   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP3-2508-516-8

Test Date: 09/03/2025

Luminaire Tested: 24CZ-LD5-65-S-UNV-L950-CD1-U

Data in this report applies to families of products including 24CZ-LD5-65-S-UNV-L950-CD1-U

### Test Information

Test Method: LM-79-2019  
 Report Number: SP3-2508-516-8  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP3 - 3M SPHERE  
 Measurement Geometry:  $4\pi$   
 Issue Date: 09/05/2025  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: Metalux  
 Catalog Number: **24CZ-LD5-65-S-UNV-L950-CD1-U**  
 Description: 2X4 CRUZE SB 6500LM 950 SMOOTH LENS

### Spectral Parameters

CCT (K): 5019  
 CIE  $u'$ : 0.2113  
 CIE  $v'$ : 0.4842  
 Duv: -0.0002  
 CIE x: 0.3445  
 CIE y: 0.3508  
 CIE z: 0.3046  
 Peak Wavelength (nm): 630  
 Dominant Wavelength (nm): 572  
 Purity: 8.636369  
 R<sub>f</sub>: 89.8  
 R<sub>g</sub>: 98.5

CRI (Ra): 94.6  
 R1: 96.4  
 R2: 98.4  
 R3: 96.9  
 R4: 94.5  
 R5: 94.5  
 R6: 93.5  
 R7: 93.6  
 R8: 89.4  
 R9: 74.6  
 R10: 94.2  
 R11: 95.5  
 R12: 70.8  
 R13: 98.0  
 R14: 98.0  
 R15: 95.0



### Test Conditions

Stabilization Time: M  
 Operation Time: 1H 0M  
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP3-2508-516-8

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | 3M SPHERE IN02505     | 7/1/2025         | 1/1/2026             |
| Power Meter                    | XITRON INXT2011006    | 1/20/2025        | 1/20/2026            |
| AC Power Source                | CHROMA 61604 IN6064A  | 10/22/2024       | 10/22/2025           |
| DC Power Source                | EYSIGHT N5770A IN0534 | 10/22/2024       | 10/22/2025           |
| Sphere Thermometer             | TANDD IN4036E         | 10/22/2024       | 10/22/2025           |
|                                |                       |                  |                      |

REPORT NUMBER: SP3-2508-516-8

**CIE 1931 Chromaticity Diagram**



**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 5000K 4-step quadrangle

REPORT NUMBER: SP3-2508-516-8

### Photopic Flux vs. Wavelength



### Photopic Lumens: NR

| λ (nm) | Power W <sup>λ</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>λ</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>λ</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>λ</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>λ</sup> /nm | Lumens (φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360    | 0                        | NR            | 490    | 249                      | NR            | 620    | 343                      | NR            | 750    | 8                        | NR            | 880    | 0                        | NR            |
| 365    | 0                        | NR            | 495    | 269                      | NR            | 625    | 339                      | NR            | 755    | 7                        | NR            | 885    | 0                        | NR            |
| 370    | 0                        | NR            | 500    | 296                      | NR            | 630    | 1000                     | NR            | 760    | 6                        | NR            | 890    | 0                        | NR            |
| 375    | 0                        | NR            | 505    | 325                      | NR            | 635    | 705                      | NR            | 765    | 5                        | NR            | 895    | 0                        | NR            |
| 380    | 0                        | NR            | 510    | 347                      | NR            | 640    | 221                      | NR            | 770    | 4                        | NR            | 900    | 0                        | NR            |
| 385    | 0                        | NR            | 515    | 363                      | NR            | 645    | 210                      | NR            | 775    | 4                        | NR            | 905    | 0                        | NR            |
| 390    | 1                        | NR            | 520    | 371                      | NR            | 650    | 186                      | NR            | 780    | 3                        | NR            | 910    | 0                        | NR            |
| 395    | 3                        | NR            | 525    | 378                      | NR            | 655    | 155                      | NR            | 785    | 3                        | NR            | 915    | 0                        | NR            |
| 400    | 4                        | NR            | 530    | 381                      | NR            | 660    | 132                      | NR            | 790    | 2                        | NR            | 920    | 0                        | NR            |
| 405    | 5                        | NR            | 535    | 383                      | NR            | 665    | 111                      | NR            | 795    | 2                        | NR            | 925    | 0                        | NR            |
| 410    | 7                        | NR            | 540    | 385                      | NR            | 670    | 102                      | NR            | 800    | 2                        | NR            | 930    | 0                        | NR            |
| 415    | 10                       | NR            | 545    | 389                      | NR            | 675    | 84                       | NR            | 805    | 1                        | NR            | 935    | 0                        | NR            |
| 420    | 17                       | NR            | 550    | 391                      | NR            | 680    | 72                       | NR            | 810    | 1                        | NR            | 940    | 0                        | NR            |
| 425    | 29                       | NR            | 555    | 392                      | NR            | 685    | 62                       | NR            | 815    | 1                        | NR            | 945    | 0                        | NR            |
| 430    | 53                       | NR            | 560    | 393                      | NR            | 690    | 53                       | NR            | 820    | 1                        | NR            | 950    | 0                        | NR            |
| 435    | 97                       | NR            | 565    | 394                      | NR            | 695    | 45                       | NR            | 825    | 1                        | NR            | 955    | 0                        | NR            |
| 440    | 173                      | NR            | 570    | 391                      | NR            | 700    | 39                       | NR            | 830    | 1                        | NR            | 960    | 0                        | NR            |
| 445    | 321                      | NR            | 575    | 389                      | NR            | 705    | 33                       | NR            | 835    | 1                        | NR            | 965    | 0                        | NR            |
| 450    | 597                      | NR            | 580    | 385                      | NR            | 710    | 28                       | NR            | 840    | 1                        | NR            | 970    | 0                        | NR            |
| 455    | 795                      | NR            | 585    | 382                      | NR            | 715    | 24                       | NR            | 845    | 1                        | NR            | 975    | 0                        | NR            |
| 460    | 615                      | NR            | 590    | 375                      | NR            | 720    | 21                       | NR            | 850    | 0                        | NR            | 980    | 0                        | NR            |
| 465    | 438                      | NR            | 595    | 367                      | NR            | 725    | 17                       | NR            | 855    | 0                        | NR            | 985    | 0                        | NR            |
| 470    | 372                      | NR            | 600    | 361                      | NR            | 730    | 15                       | NR            | 860    | 0                        | NR            | 990    | 0                        | NR            |
| 475    | 290                      | NR            | 605    | 355                      | NR            | 735    | 13                       | NR            | 865    | 0                        | NR            | 995    | 0                        | NR            |
| 480    | 236                      | NR            | 610    | 383                      | NR            | 740    | 11                       | NR            | 870    | 0                        | NR            | 1000   | 0                        | NR            |
| 485    | 232                      | NR            | 615    | 408                      | NR            | 745    | 9                        | NR            | 875    | 0                        | NR            |        |                          |               |

REPORT NUMBER: SP3-2508-516-8

### Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 2.11

| $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 0                                    | NR                             | 490               | 249                                  | NR                             | 620               | 343                                  | NR                             | 750               | 8                                    | NR                             | 880               | 0                                    | NR                             |
| 365               | 0                                    | NR                             | 495               | 269                                  | NR                             | 625               | 339                                  | NR                             | 755               | 7                                    | NR                             | 885               | 0                                    | NR                             |
| 370               | 0                                    | NR                             | 500               | 296                                  | NR                             | 630               | 1000                                 | NR                             | 760               | 6                                    | NR                             | 890               | 0                                    | NR                             |
| 375               | 0                                    | NR                             | 505               | 325                                  | NR                             | 635               | 705                                  | NR                             | 765               | 5                                    | NR                             | 895               | 0                                    | NR                             |
| 380               | 0                                    | NR                             | 510               | 347                                  | NR                             | 640               | 221                                  | NR                             | 770               | 4                                    | NR                             | 900               | 0                                    | NR                             |
| 385               | 0                                    | NR                             | 515               | 363                                  | NR                             | 645               | 210                                  | NR                             | 775               | 4                                    | NR                             | 905               | 0                                    | NR                             |
| 390               | 1                                    | NR                             | 520               | 371                                  | NR                             | 650               | 186                                  | NR                             | 780               | 3                                    | NR                             | 910               | 0                                    | NR                             |
| 395               | 3                                    | NR                             | 525               | 378                                  | NR                             | 655               | 155                                  | NR                             | 785               | 3                                    | NR                             | 915               | 0                                    | NR                             |
| 400               | 4                                    | NR                             | 530               | 381                                  | NR                             | 660               | 132                                  | NR                             | 790               | 2                                    | NR                             | 920               | 0                                    | NR                             |
| 405               | 5                                    | NR                             | 535               | 383                                  | NR                             | 665               | 111                                  | NR                             | 795               | 2                                    | NR                             | 925               | 0                                    | NR                             |
| 410               | 7                                    | NR                             | 540               | 385                                  | NR                             | 670               | 102                                  | NR                             | 800               | 2                                    | NR                             | 930               | 0                                    | NR                             |
| 415               | 10                                   | NR                             | 545               | 389                                  | NR                             | 675               | 84                                   | NR                             | 805               | 1                                    | NR                             | 935               | 0                                    | NR                             |
| 420               | 17                                   | NR                             | 550               | 391                                  | NR                             | 680               | 72                                   | NR                             | 810               | 1                                    | NR                             | 940               | 0                                    | NR                             |
| 425               | 29                                   | NR                             | 555               | 392                                  | NR                             | 685               | 62                                   | NR                             | 815               | 1                                    | NR                             | 945               | 0                                    | NR                             |
| 430               | 53                                   | NR                             | 560               | 393                                  | NR                             | 690               | 53                                   | NR                             | 820               | 1                                    | NR                             | 950               | 0                                    | NR                             |
| 435               | 97                                   | NR                             | 565               | 394                                  | NR                             | 695               | 45                                   | NR                             | 825               | 1                                    | NR                             | 955               | 0                                    | NR                             |
| 440               | 173                                  | NR                             | 570               | 391                                  | NR                             | 700               | 39                                   | NR                             | 830               | 1                                    | NR                             | 960               | 0                                    | NR                             |
| 445               | 321                                  | NR                             | 575               | 389                                  | NR                             | 705               | 33                                   | NR                             | 835               | 1                                    | NR                             | 965               | 0                                    | NR                             |
| 450               | 597                                  | NR                             | 580               | 385                                  | NR                             | 710               | 28                                   | NR                             | 840               | 1                                    | NR                             | 970               | 0                                    | NR                             |
| 455               | 795                                  | NR                             | 585               | 382                                  | NR                             | 715               | 24                                   | NR                             | 845               | 1                                    | NR                             | 975               | 0                                    | NR                             |
| 460               | 615                                  | NR                             | 590               | 375                                  | NR                             | 720               | 21                                   | NR                             | 850               | 0                                    | NR                             | 980               | 0                                    | NR                             |
| 465               | 438                                  | NR                             | 595               | 367                                  | NR                             | 725               | 17                                   | NR                             | 855               | 0                                    | NR                             | 985               | 0                                    | NR                             |
| 470               | 372                                  | NR                             | 600               | 361                                  | NR                             | 730               | 15                                   | NR                             | 860               | 0                                    | NR                             | 990               | 0                                    | NR                             |
| 475               | 290                                  | NR                             | 605               | 355                                  | NR                             | 735               | 13                                   | NR                             | 865               | 0                                    | NR                             | 995               | 0                                    | NR                             |
| 480               | 236                                  | NR                             | 610               | 383                                  | NR                             | 740               | 11                                   | NR                             | 870               | 0                                    | NR                             | 1000              | 0                                    | NR                             |
| 485               | 232                                  | NR                             | 615               | 408                                  | NR                             | 745               | 9                                    | NR                             | 875               | 0                                    | NR                             |                   |                                      |                                |

REPORT NUMBER: SP3-2508-516-8

### Melanopic Flux vs. Wavelength


**Melanopic Lumens: NR**
**M/P: 4.62**

| $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 0                                    | NR                             | 490               | 249                                  | NR                             | 620               | 343                                  | NR                             | 750               | 8                                    | NR                             | 880               | 0                                    | NR                             |
| 365               | 0                                    | NR                             | 495               | 269                                  | NR                             | 625               | 339                                  | NR                             | 755               | 7                                    | NR                             | 885               | 0                                    | NR                             |
| 370               | 0                                    | NR                             | 500               | 296                                  | NR                             | 630               | 1000                                 | NR                             | 760               | 6                                    | NR                             | 890               | 0                                    | NR                             |
| 375               | 0                                    | NR                             | 505               | 325                                  | NR                             | 635               | 705                                  | NR                             | 765               | 5                                    | NR                             | 895               | 0                                    | NR                             |
| 380               | 0                                    | NR                             | 510               | 347                                  | NR                             | 640               | 221                                  | NR                             | 770               | 4                                    | NR                             | 900               | 0                                    | NR                             |
| 385               | 0                                    | NR                             | 515               | 363                                  | NR                             | 645               | 210                                  | NR                             | 775               | 4                                    | NR                             | 905               | 0                                    | NR                             |
| 390               | 1                                    | NR                             | 520               | 371                                  | NR                             | 650               | 186                                  | NR                             | 780               | 3                                    | NR                             | 910               | 0                                    | NR                             |
| 395               | 3                                    | NR                             | 525               | 378                                  | NR                             | 655               | 155                                  | NR                             | 785               | 3                                    | NR                             | 915               | 0                                    | NR                             |
| 400               | 4                                    | NR                             | 530               | 381                                  | NR                             | 660               | 132                                  | NR                             | 790               | 2                                    | NR                             | 920               | 0                                    | NR                             |
| 405               | 5                                    | NR                             | 535               | 383                                  | NR                             | 665               | 111                                  | NR                             | 795               | 2                                    | NR                             | 925               | 0                                    | NR                             |
| 410               | 7                                    | NR                             | 540               | 385                                  | NR                             | 670               | 102                                  | NR                             | 800               | 2                                    | NR                             | 930               | 0                                    | NR                             |
| 415               | 10                                   | NR                             | 545               | 389                                  | NR                             | 675               | 84                                   | NR                             | 805               | 1                                    | NR                             | 935               | 0                                    | NR                             |
| 420               | 17                                   | NR                             | 550               | 391                                  | NR                             | 680               | 72                                   | NR                             | 810               | 1                                    | NR                             | 940               | 0                                    | NR                             |
| 425               | 29                                   | NR                             | 555               | 392                                  | NR                             | 685               | 62                                   | NR                             | 815               | 1                                    | NR                             | 945               | 0                                    | NR                             |
| 430               | 53                                   | NR                             | 560               | 393                                  | NR                             | 690               | 53                                   | NR                             | 820               | 1                                    | NR                             | 950               | 0                                    | NR                             |
| 435               | 97                                   | NR                             | 565               | 394                                  | NR                             | 695               | 45                                   | NR                             | 825               | 1                                    | NR                             | 955               | 0                                    | NR                             |
| 440               | 173                                  | NR                             | 570               | 391                                  | NR                             | 700               | 39                                   | NR                             | 830               | 1                                    | NR                             | 960               | 0                                    | NR                             |
| 445               | 321                                  | NR                             | 575               | 389                                  | NR                             | 705               | 33                                   | NR                             | 835               | 1                                    | NR                             | 965               | 0                                    | NR                             |
| 450               | 597                                  | NR                             | 580               | 385                                  | NR                             | 710               | 28                                   | NR                             | 840               | 1                                    | NR                             | 970               | 0                                    | NR                             |
| 455               | 795                                  | NR                             | 585               | 382                                  | NR                             | 715               | 24                                   | NR                             | 845               | 1                                    | NR                             | 975               | 0                                    | NR                             |
| 460               | 615                                  | NR                             | 590               | 375                                  | NR                             | 720               | 21                                   | NR                             | 850               | 0                                    | NR                             | 980               | 0                                    | NR                             |
| 465               | 438                                  | NR                             | 595               | 367                                  | NR                             | 725               | 17                                   | NR                             | 855               | 0                                    | NR                             | 985               | 0                                    | NR                             |
| 470               | 372                                  | NR                             | 600               | 361                                  | NR                             | 730               | 15                                   | NR                             | 860               | 0                                    | NR                             | 990               | 0                                    | NR                             |
| 475               | 290                                  | NR                             | 605               | 355                                  | NR                             | 735               | 13                                   | NR                             | 865               | 0                                    | NR                             | 995               | 0                                    | NR                             |
| 480               | 236                                  | NR                             | 610               | 383                                  | NR                             | 740               | 11                                   | NR                             | 870               | 0                                    | NR                             | 1000              | 0                                    | NR                             |
| 485               | 232                                  | NR                             | 615               | 408                                  | NR                             | 745               | 9                                    | NR                             | 875               | 0                                    | NR                             |                   |                                      |                                |

REPORT NUMBER: SP3-2508-516-8

TM-30-18

### Summary

$R_f = 89.8$   
 $R_g = 98.5$   
 $\text{CIE } R_a = 94.6$   
 $R_9 = 74.6$



### Color Vector Graphics



**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |             |            |            |
|------------|-------------|------------|------------|
| CES01 = 85 | CES26 = 96  | CES51 = 93 | CES76 = 88 |
| CES02 = 61 | CES27 = 88  | CES52 = 97 | CES77 = 87 |
| CES03 = 31 | CES28 = 96  | CES53 = 95 | CES78 = 85 |
| CES04 = 69 | CES29 = 93  | CES54 = 89 | CES79 = 93 |
| CES05 = 48 | CES30 = 81  | CES55 = 86 | CES80 = 93 |
| CES06 = 50 | CES31 = 95  | CES56 = 90 | CES81 = 80 |
| CES07 = 41 | CES32 = 93  | CES57 = 87 | CES82 = 96 |
| CES08 = 40 | CES33 = 91  | CES58 = 87 | CES83 = 95 |
| CES09 = 29 | CES34 = 95  | CES59 = 96 | CES84 = 93 |
| CES10 = 73 | CES35 = 96  | CES60 = 89 | CES85 = 81 |
| CES11 = 56 | CES36 = 74  | CES61 = 89 | CES86 = 85 |
| CES12 = 62 | CES37 = 95  | CES62 = 78 | CES87 = 93 |
| CES13 = 42 | CES38 = 76  | CES63 = 89 | CES88 = 96 |
| CES14 = 74 | CES39 = 98  | CES64 = 84 | CES89 = 87 |
| CES15 = 71 | CES40 = 98  | CES65 = 86 | CES90 = 93 |
| CES16 = 47 | CES41 = 92  | CES66 = 81 | CES91 = 68 |
| CES17 = 48 | CES42 = 95  | CES67 = 80 | CES92 = 78 |
| CES18 = 56 | CES43 = 96  | CES68 = 85 | CES93 = 86 |
| CES19 = 70 | CES44 = 99  | CES69 = 85 | CES94 = 79 |
| CES20 = 65 | CES45 = 100 | CES70 = 84 | CES95 = 82 |
| CES21 = 85 | CES46 = 96  | CES71 = 75 | CES96 = 93 |
| CES22 = 77 | CES47 = 91  | CES72 = 92 | CES97 = 96 |
| CES23 = 91 | CES48 = 84  | CES73 = 80 | CES98 = 94 |
| CES24 = 90 | CES49 = 97  | CES74 = 89 | CES99 = 92 |
| CES25 = 70 | CES50 = 95  | CES75 = 78 |            |



Color Rendition by Hue-Angle Bin



**Measure Comparisons**



(END OF REPORT)