

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: METALUX

Report Number: P982867

Luminaire Tested: 24CZ-LD5-30SE-UNV-L935-CD1-U

Issue Date: 04/23/2025

**Test Information**

Test Method: LM-79-2019  
Report Number: P982867  
Test Lab: INNOVATION CENTER(P3)  
Issue Date: 04/23/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: METALUX  
Catalog Number: 24CZ-LD5-30SE-UNV-L935-CD1-U  
Description: METALUX CRUZE 2x4 3000LM STANDARD EFFICACY PACKAGE 90CRI 3500K TROFFER STANDAR  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2752.0 lumens  
Efficiency: N/A  
Efficacy: 122.9 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.26 / 1.35  
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')  
CIE Type: Direct

Input Watts (W): 22.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT

TEST NUMBER: P982867

CATALOG NUMBER: 24CZ-LD5-30SE-UNV-L935-CD1-U

### Luminous Intensity Polar Plot



TEST NUMBER: P982867

CATALOG NUMBER: 24CZ-LD5-30SE-UNV-L935-CD1-U

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|
| RF  | 20  |     |     |     | 20  |     |     |     |     | 20  |     |     |     |     | 20  |     |     |     |    | 20 |
| RC  | 80  |     |     |     | 70  |     |     |     |     | 50  |     |     |     |     | 30  |     |     |     |    | 10 |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |
| 1   | 108 | 103 | 99  | 95  | 106 | 101 | 97  | 93  | 97  | 93  | 90  | 93  | 90  | 88  | 89  | 87  | 85  | 83  |    |    |
| 2   | 98  | 90  | 83  | 77  | 96  | 88  | 81  | 76  | 84  | 79  | 74  | 81  | 76  | 72  | 78  | 74  | 71  | 68  |    |    |
| 3   | 89  | 79  | 70  | 63  | 87  | 77  | 69  | 63  | 74  | 67  | 62  | 71  | 65  | 61  | 69  | 64  | 60  | 57  |    |    |
| 4   | 82  | 69  | 60  | 54  | 79  | 68  | 60  | 53  | 66  | 58  | 52  | 63  | 57  | 52  | 61  | 56  | 51  | 49  |    |    |
| 5   | 75  | 62  | 53  | 46  | 73  | 61  | 52  | 46  | 59  | 51  | 45  | 57  | 50  | 45  | 55  | 49  | 44  | 42  |    |    |
| 6   | 69  | 56  | 47  | 40  | 67  | 55  | 46  | 40  | 53  | 45  | 40  | 51  | 44  | 39  | 50  | 44  | 39  | 37  |    |    |
| 7   | 64  | 51  | 42  | 35  | 63  | 50  | 41  | 35  | 48  | 41  | 35  | 47  | 40  | 35  | 45  | 39  | 35  | 33  |    |    |
| 8   | 60  | 46  | 38  | 32  | 58  | 45  | 37  | 32  | 44  | 37  | 31  | 43  | 36  | 31  | 42  | 36  | 31  | 29  |    |    |
| 9   | 56  | 42  | 34  | 28  | 55  | 42  | 34  | 28  | 41  | 33  | 28  | 40  | 33  | 28  | 39  | 32  | 28  | 26  |    |    |
| 10  | 52  | 39  | 31  | 26  | 51  | 39  | 31  | 26  | 38  | 31  | 26  | 37  | 30  | 26  | 36  | 30  | 25  | 24  |    |    |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°   | 45°  | 90°  |
|-----|------|------|------|
| 0°  | 1301 | 1301 | 1301 |
| 5°  | 1306 | 1302 | 1300 |
| 10° | 1297 | 1297 | 1297 |
| 15° | 1282 | 1287 | 1295 |
| 20° | 1261 | 1275 | 1287 |
| 25° | 1234 | 1258 | 1277 |
| 30° | 1203 | 1238 | 1267 |
| 35° | 1166 | 1215 | 1259 |
| 40° | 1130 | 1192 | 1251 |
| 45° | 1092 | 1170 | 1256 |
| 50° | 1050 | 1150 | 1262 |
| 55° | 1010 | 1137 | 1272 |
| 60° | 967  | 1129 | 1295 |
| 65° | 918  | 1127 | 1335 |
| 70° | 854  | 1145 | 1411 |
| 75° | 764  | 1193 | 1353 |
| 80° | 652  | 1139 | 1241 |
| 85° | 506  | 911  | 868  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°

Vertical Angle: 72.5°

Luminance: 1437 cd/sqm

TEST NUMBER: P982867

CATALOG NUMBER: 24CZ-LD5-30SE-UNV-L935-CD1-U

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 91.5   | 3.3       |
| 10°-20°   | 260.3  | 9.5       |
| 20°-30°   | 389.1  | 14.1      |
| 30°-40°   | 461.4  | 16.8      |
| 40°-50°   | 474.5  | 17.2      |
| 50°-60°   | 434.0  | 15.8      |
| 60°-70°   | 350.0  | 12.7      |
| 70°-80°   | 227.2  | 8.3       |
| 80°-90°   | 63.9   | 2.3       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 740.8  | 26.9      |
| 0°-40°    | 1202.2 | 43.7      |
| 0°-60°    | 2110.7 | 76.7      |
| 0°-90°    | 2752.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 2752.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | 22.5° | 45° | 67.5° | 90° | Flux |
|-----|-----|-------|-----|-------|-----|------|
| 0°  | 967 | 967   | 967 | 967   | 967 |      |
| 5°  | 967 | 960   | 964 | 962   | 962 | 92   |
| 15° | 920 | 916   | 924 | 928   | 930 | 259  |
| 25° | 831 | 831   | 847 | 854   | 860 | 383  |
| 35° | 710 | 716   | 740 | 754   | 767 | 444  |
| 45° | 574 | 584   | 615 | 643   | 660 | 442  |
| 55° | 431 | 445   | 485 | 523   | 542 | 385  |
| 65° | 288 | 305   | 354 | 400   | 419 | 285  |
| 75° | 147 | 174   | 229 | 258   | 260 | 157  |
| 85° | 33  | 54    | 59  | 58    | 56  | 39   |
| 90° | 0   | 0     | 0   | 0     | 0   |      |

TEST NUMBER: P982867

CATALOG NUMBER: 24CZ-LD5-30SE-UNV-L935-CD1-U

**CANDELA DISTRIBUTION (FULL):**

|       | 0°    | 22.5° | 45°   | 67.5° | 90°   |
|-------|-------|-------|-------|-------|-------|
| 0°    | 967.1 | 967.1 | 967.1 | 967.1 | 967.1 |
| 2.5°  | 971.8 | 964.3 | 968.0 | 966.2 | 962.4 |
| 5°    | 967.1 | 960.5 | 964.3 | 962.4 | 962.4 |
| 7.5°  | 960.5 | 954.0 | 957.7 | 957.7 | 957.7 |
| 10°   | 949.3 | 943.7 | 949.3 | 949.3 | 949.3 |
| 12.5° | 936.2 | 931.5 | 938.1 | 939.0 | 940.9 |
| 15°   | 920.3 | 915.6 | 924.0 | 927.8 | 929.6 |
| 17.5° | 902.5 | 898.7 | 908.1 | 912.8 | 915.6 |
| 20°   | 881.0 | 878.1 | 890.3 | 895.0 | 898.7 |
| 22.5° | 856.6 | 856.6 | 868.8 | 874.4 | 881.0 |
| 25°   | 831.3 | 831.3 | 847.2 | 853.8 | 860.4 |
| 27.5° | 804.2 | 805.1 | 822.9 | 832.3 | 838.8 |
| 30°   | 774.2 | 778.0 | 796.7 | 807.9 | 815.4 |
| 32.5° | 742.4 | 747.1 | 768.6 | 782.7 | 792.0 |
| 35°   | 709.6 | 716.2 | 739.6 | 754.5 | 766.7 |
| 37.5° | 676.9 | 685.3 | 710.6 | 727.4 | 739.6 |
| 40°   | 643.2 | 652.5 | 678.7 | 698.4 | 712.4 |
| 42.5° | 608.5 | 618.8 | 647.8 | 670.3 | 687.2 |
| 45°   | 573.9 | 584.2 | 615.1 | 643.2 | 660.0 |
| 47.5° | 537.4 | 549.6 | 582.3 | 615.1 | 631.9 |
| 50°   | 501.8 | 514.9 | 549.6 | 585.1 | 602.9 |
| 52.5° | 466.2 | 481.2 | 517.7 | 555.2 | 573.0 |
| 55°   | 430.6 | 444.7 | 484.9 | 523.3 | 542.1 |
| 57.5° | 395.1 | 410.1 | 452.2 | 492.4 | 512.1 |
| 60°   | 359.5 | 375.4 | 419.4 | 461.5 | 481.2 |
| 62.5° | 323.0 | 339.8 | 386.7 | 430.6 | 450.3 |
| 65°   | 288.4 | 305.2 | 353.9 | 399.7 | 419.4 |
| 67.5° | 252.8 | 271.5 | 322.0 | 368.8 | 389.5 |
| 70°   | 217.2 | 237.8 | 291.1 | 337.9 | 358.6 |
| 72.5° | 181.6 | 205.0 | 259.3 | 306.1 | 321.1 |
| 75°   | 147.0 | 174.1 | 229.4 | 257.5 | 260.2 |
| 77.5° | 115.1 | 143.2 | 195.7 | 206.9 | 212.5 |
| 80°   | 84.2  | 115.1 | 147.0 | 161.0 | 160.1 |
| 82.5° | 56.2  | 88.0  | 105.8 | 107.7 | 105.8 |
| 85°   | 32.8  | 54.3  | 59.0  | 58.0  | 56.2  |
| 87.5° | 14.0  | 21.5  | 18.7  | 15.9  | 13.1  |
| 90°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP3-2508-516-6

Test Date: 09/03/2025

Luminaire Tested: 24CZ-LD5-65-S-UNV-L935-CD1-U

Data in this report applies to families of products including 24CZ-LD5-65-S-UNV-L935-CD1-U

### Test Information

Test Method: LM-79-2019  
 Report Number: SP3-2508-516-6  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP3 - 3M SPHERE  
 Measurement Geometry:  $4\pi$   
 Issue Date: 09/05/2025  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: Metalux  
 Catalog Number: **24CZ-LD5-65-S-UNV-L935-CD1-U**  
 Description: 2X4 CRUZE SB 6500LM 935 SMOOTH LENS

### Spectral Parameters

CCT (K): 3412  
 CIE  $u'$ : 0.2386  
 CIE  $v'$ : 0.5111  
 Duv: -0.0015  
 CIE x: 0.4087  
 CIE y: 0.3890  
 CIE z: 0.2023  
 Peak Wavelength (nm): 630  
 Dominant Wavelength (nm): 581  
 Purity: 39.41044  
 R<sub>f</sub>: 92.6  
 R<sub>g</sub>: 102

CRI (Ra): 96.3  
 R1: 99.2  
 R2: 97.9  
 R3: 94.7  
 R4: 96.6  
 R5: 98.4  
 R6: 96.1  
 R7: 95.6  
 R8: 92.0  
 R9: 78.4  
 R10: 93.0  
 R11: 94.5  
 R12: 81.5  
 R13: 99.0  
 R14: 95.8  
 R15: 96.7



### Test Conditions

Stabilization Time: 20M  
 Operation Time: 1H 20M  
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP3-2508-516-6

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | 3M SPHERE IN02505     | 7/1/2025         | 1/1/2026             |
| Power Meter                    | XITRON INXT2011006    | 1/20/2025        | 1/20/2026            |
| AC Power Source                | CHROMA 61604 IN6064A  | 10/22/2024       | 10/22/2025           |
| DC Power Source                | EYSIGHT N5770A IN0534 | 10/22/2024       | 10/22/2025           |
| Sphere Thermometer             | TANDD IN4036E         | 10/22/2024       | 10/22/2025           |
|                                |                       |                  |                      |

REPORT NUMBER: SP3-2508-516-6

**CIE 1931 Chromaticity Diagram**



**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP3-2508-516-6

### Photopic Flux vs. Wavelength



### Photopic Lumens: NR

| $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 0                                    | NR                             | 490               | 112                                  | NR                             | 620               | 281                                  | NR                             | 750               | 6                                    | NR                             | 880               | 0                                    | NR                             |
| 365               | 0                                    | NR                             | 495               | 134                                  | NR                             | 625               | 286                                  | NR                             | 755               | 5                                    | NR                             | 885               | 0                                    | NR                             |
| 370               | 0                                    | NR                             | 500               | 157                                  | NR                             | 630               | 1000                                 | NR                             | 760               | 4                                    | NR                             | 890               | 0                                    | NR                             |
| 375               | 0                                    | NR                             | 505               | 178                                  | NR                             | 635               | 695                                  | NR                             | 765               | 4                                    | NR                             | 895               | 0                                    | NR                             |
| 380               | 0                                    | NR                             | 510               | 193                                  | NR                             | 640               | 181                                  | NR                             | 770               | 3                                    | NR                             | 900               | 0                                    | NR                             |
| 385               | 0                                    | NR                             | 515               | 206                                  | NR                             | 645               | 175                                  | NR                             | 775               | 3                                    | NR                             | 905               | 0                                    | NR                             |
| 390               | 0                                    | NR                             | 520               | 213                                  | NR                             | 650               | 156                                  | NR                             | 780               | 2                                    | NR                             | 910               | 0                                    | NR                             |
| 395               | 1                                    | NR                             | 525               | 219                                  | NR                             | 655               | 127                                  | NR                             | 785               | 2                                    | NR                             | 915               | 0                                    | NR                             |
| 400               | 2                                    | NR                             | 530               | 223                                  | NR                             | 660               | 108                                  | NR                             | 790               | 2                                    | NR                             | 920               | 0                                    | NR                             |
| 405               | 2                                    | NR                             | 535               | 226                                  | NR                             | 665               | 89                                   | NR                             | 795               | 2                                    | NR                             | 925               | 0                                    | NR                             |
| 410               | 4                                    | NR                             | 540               | 230                                  | NR                             | 670               | 84                                   | NR                             | 800               | 1                                    | NR                             | 930               | 0                                    | NR                             |
| 415               | 6                                    | NR                             | 545               | 235                                  | NR                             | 675               | 67                                   | NR                             | 805               | 1                                    | NR                             | 935               | 0                                    | NR                             |
| 420               | 11                                   | NR                             | 550               | 239                                  | NR                             | 680               | 57                                   | NR                             | 810               | 1                                    | NR                             | 940               | 0                                    | NR                             |
| 425               | 19                                   | NR                             | 555               | 243                                  | NR                             | 685               | 50                                   | NR                             | 815               | 1                                    | NR                             | 945               | 0                                    | NR                             |
| 430               | 34                                   | NR                             | 560               | 248                                  | NR                             | 690               | 42                                   | NR                             | 820               | 1                                    | NR                             | 950               | 0                                    | NR                             |
| 435               | 60                                   | NR                             | 565               | 253                                  | NR                             | 695               | 36                                   | NR                             | 825               | 1                                    | NR                             | 955               | 0                                    | NR                             |
| 440               | 106                                  | NR                             | 570               | 256                                  | NR                             | 700               | 31                                   | NR                             | 830               | 0                                    | NR                             | 960               | 0                                    | NR                             |
| 445               | 193                                  | NR                             | 575               | 260                                  | NR                             | 705               | 26                                   | NR                             | 835               | 0                                    | NR                             | 965               | 0                                    | NR                             |
| 450               | 283                                  | NR                             | 580               | 263                                  | NR                             | 710               | 22                                   | NR                             | 840               | 0                                    | NR                             | 970               | 0                                    | NR                             |
| 455               | 234                                  | NR                             | 585               | 266                                  | NR                             | 715               | 19                                   | NR                             | 845               | 0                                    | NR                             | 975               | 0                                    | NR                             |
| 460               | 157                                  | NR                             | 590               | 267                                  | NR                             | 720               | 16                                   | NR                             | 850               | 0                                    | NR                             | 980               | 0                                    | NR                             |
| 465               | 134                                  | NR                             | 595               | 266                                  | NR                             | 725               | 14                                   | NR                             | 855               | 0                                    | NR                             | 985               | 0                                    | NR                             |
| 470               | 107                                  | NR                             | 600               | 268                                  | NR                             | 730               | 12                                   | NR                             | 860               | 0                                    | NR                             | 990               | 0                                    | NR                             |
| 475               | 85                                   | NR                             | 605               | 269                                  | NR                             | 735               | 10                                   | NR                             | 865               | 0                                    | NR                             | 995               | 0                                    | NR                             |
| 480               | 85                                   | NR                             | 610               | 309                                  | NR                             | 740               | 8                                    | NR                             | 870               | 0                                    | NR                             | 1000              | 0                                    | NR                             |
| 485               | 96                                   | NR                             | 615               | 345                                  | NR                             | 745               | 7                                    | NR                             | 875               | 0                                    | NR                             |                   |                                      |                                |

REPORT NUMBER: SP3-2508-516-6

### Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.61

| λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) |
|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|
| 360       | 0                           | NR               | 490       | 112                         | NR               | 620       | 281                         | NR               | 750       | 6                           | NR               | 880       | 0                           | NR               |
| 365       | 0                           | NR               | 495       | 134                         | NR               | 625       | 286                         | NR               | 755       | 5                           | NR               | 885       | 0                           | NR               |
| 370       | 0                           | NR               | 500       | 157                         | NR               | 630       | 1000                        | NR               | 760       | 4                           | NR               | 890       | 0                           | NR               |
| 375       | 0                           | NR               | 505       | 178                         | NR               | 635       | 695                         | NR               | 765       | 4                           | NR               | 895       | 0                           | NR               |
| 380       | 0                           | NR               | 510       | 193                         | NR               | 640       | 181                         | NR               | 770       | 3                           | NR               | 900       | 0                           | NR               |
| 385       | 0                           | NR               | 515       | 206                         | NR               | 645       | 175                         | NR               | 775       | 3                           | NR               | 905       | 0                           | NR               |
| 390       | 0                           | NR               | 520       | 213                         | NR               | 650       | 156                         | NR               | 780       | 2                           | NR               | 910       | 0                           | NR               |
| 395       | 1                           | NR               | 525       | 219                         | NR               | 655       | 127                         | NR               | 785       | 2                           | NR               | 915       | 0                           | NR               |
| 400       | 2                           | NR               | 530       | 223                         | NR               | 660       | 108                         | NR               | 790       | 2                           | NR               | 920       | 0                           | NR               |
| 405       | 2                           | NR               | 535       | 226                         | NR               | 665       | 89                          | NR               | 795       | 2                           | NR               | 925       | 0                           | NR               |
| 410       | 4                           | NR               | 540       | 230                         | NR               | 670       | 84                          | NR               | 800       | 1                           | NR               | 930       | 0                           | NR               |
| 415       | 6                           | NR               | 545       | 235                         | NR               | 675       | 67                          | NR               | 805       | 1                           | NR               | 935       | 0                           | NR               |
| 420       | 11                          | NR               | 550       | 239                         | NR               | 680       | 57                          | NR               | 810       | 1                           | NR               | 940       | 0                           | NR               |
| 425       | 19                          | NR               | 555       | 243                         | NR               | 685       | 50                          | NR               | 815       | 1                           | NR               | 945       | 0                           | NR               |
| 430       | 34                          | NR               | 560       | 248                         | NR               | 690       | 42                          | NR               | 820       | 1                           | NR               | 950       | 0                           | NR               |
| 435       | 60                          | NR               | 565       | 253                         | NR               | 695       | 36                          | NR               | 825       | 1                           | NR               | 955       | 0                           | NR               |
| 440       | 106                         | NR               | 570       | 256                         | NR               | 700       | 31                          | NR               | 830       | 0                           | NR               | 960       | 0                           | NR               |
| 445       | 193                         | NR               | 575       | 260                         | NR               | 705       | 26                          | NR               | 835       | 0                           | NR               | 965       | 0                           | NR               |
| 450       | 283                         | NR               | 580       | 263                         | NR               | 710       | 22                          | NR               | 840       | 0                           | NR               | 970       | 0                           | NR               |
| 455       | 234                         | NR               | 585       | 266                         | NR               | 715       | 19                          | NR               | 845       | 0                           | NR               | 975       | 0                           | NR               |
| 460       | 157                         | NR               | 590       | 267                         | NR               | 720       | 16                          | NR               | 850       | 0                           | NR               | 980       | 0                           | NR               |
| 465       | 134                         | NR               | 595       | 266                         | NR               | 725       | 14                          | NR               | 855       | 0                           | NR               | 985       | 0                           | NR               |
| 470       | 107                         | NR               | 600       | 268                         | NR               | 730       | 12                          | NR               | 860       | 0                           | NR               | 990       | 0                           | NR               |
| 475       | 85                          | NR               | 605       | 269                         | NR               | 735       | 10                          | NR               | 865       | 0                           | NR               | 995       | 0                           | NR               |
| 480       | 85                          | NR               | 610       | 309                         | NR               | 740       | 8                           | NR               | 870       | 0                           | NR               | 1000      | 0                           | NR               |
| 485       | 96                          | NR               | 615       | 345                         | NR               | 745       | 7                           | NR               | 875       | 0                           | NR               |           |                             |                  |

REPORT NUMBER: SP3-2508-516-6

### Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 3.24

| λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) |
|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|
| 360       | 0                           | NR               | 490       | 112                         | NR               | 620       | 281                         | NR               | 750       | 6                           | NR               | 880       | 0                           | NR               |
| 365       | 0                           | NR               | 495       | 134                         | NR               | 625       | 286                         | NR               | 755       | 5                           | NR               | 885       | 0                           | NR               |
| 370       | 0                           | NR               | 500       | 157                         | NR               | 630       | 1000                        | NR               | 760       | 4                           | NR               | 890       | 0                           | NR               |
| 375       | 0                           | NR               | 505       | 178                         | NR               | 635       | 695                         | NR               | 765       | 4                           | NR               | 895       | 0                           | NR               |
| 380       | 0                           | NR               | 510       | 193                         | NR               | 640       | 181                         | NR               | 770       | 3                           | NR               | 900       | 0                           | NR               |
| 385       | 0                           | NR               | 515       | 206                         | NR               | 645       | 175                         | NR               | 775       | 3                           | NR               | 905       | 0                           | NR               |
| 390       | 0                           | NR               | 520       | 213                         | NR               | 650       | 156                         | NR               | 780       | 2                           | NR               | 910       | 0                           | NR               |
| 395       | 1                           | NR               | 525       | 219                         | NR               | 655       | 127                         | NR               | 785       | 2                           | NR               | 915       | 0                           | NR               |
| 400       | 2                           | NR               | 530       | 223                         | NR               | 660       | 108                         | NR               | 790       | 2                           | NR               | 920       | 0                           | NR               |
| 405       | 2                           | NR               | 535       | 226                         | NR               | 665       | 89                          | NR               | 795       | 2                           | NR               | 925       | 0                           | NR               |
| 410       | 4                           | NR               | 540       | 230                         | NR               | 670       | 84                          | NR               | 800       | 1                           | NR               | 930       | 0                           | NR               |
| 415       | 6                           | NR               | 545       | 235                         | NR               | 675       | 67                          | NR               | 805       | 1                           | NR               | 935       | 0                           | NR               |
| 420       | 11                          | NR               | 550       | 239                         | NR               | 680       | 57                          | NR               | 810       | 1                           | NR               | 940       | 0                           | NR               |
| 425       | 19                          | NR               | 555       | 243                         | NR               | 685       | 50                          | NR               | 815       | 1                           | NR               | 945       | 0                           | NR               |
| 430       | 34                          | NR               | 560       | 248                         | NR               | 690       | 42                          | NR               | 820       | 1                           | NR               | 950       | 0                           | NR               |
| 435       | 60                          | NR               | 565       | 253                         | NR               | 695       | 36                          | NR               | 825       | 1                           | NR               | 955       | 0                           | NR               |
| 440       | 106                         | NR               | 570       | 256                         | NR               | 700       | 31                          | NR               | 830       | 0                           | NR               | 960       | 0                           | NR               |
| 445       | 193                         | NR               | 575       | 260                         | NR               | 705       | 26                          | NR               | 835       | 0                           | NR               | 965       | 0                           | NR               |
| 450       | 283                         | NR               | 580       | 263                         | NR               | 710       | 22                          | NR               | 840       | 0                           | NR               | 970       | 0                           | NR               |
| 455       | 234                         | NR               | 585       | 266                         | NR               | 715       | 19                          | NR               | 845       | 0                           | NR               | 975       | 0                           | NR               |
| 460       | 157                         | NR               | 590       | 267                         | NR               | 720       | 16                          | NR               | 850       | 0                           | NR               | 980       | 0                           | NR               |
| 465       | 134                         | NR               | 595       | 266                         | NR               | 725       | 14                          | NR               | 855       | 0                           | NR               | 985       | 0                           | NR               |
| 470       | 107                         | NR               | 600       | 268                         | NR               | 730       | 12                          | NR               | 860       | 0                           | NR               | 990       | 0                           | NR               |
| 475       | 85                          | NR               | 605       | 269                         | NR               | 735       | 10                          | NR               | 865       | 0                           | NR               | 995       | 0                           | NR               |
| 480       | 85                          | NR               | 610       | 309                         | NR               | 740       | 8                           | NR               | 870       | 0                           | NR               | 1000      | 0                           | NR               |
| 485       | 96                          | NR               | 615       | 345                         | NR               | 745       | 7                           | NR               | 875       | 0                           | NR               |           |                             |                  |

REPORT NUMBER: SP3-2508-516-6

TM-30-18

### Summary

$R_f = 92.6$   
 $R_g = 102$   
 $\text{CIE } R_a = 96.3$   
 $R_9 = 78.4$



### Color Vector Graphics



**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |             |            |
|------------|------------|-------------|------------|
| CES01 = 86 | CES26 = 94 | CES51 = 97  | CES76 = 88 |
| CES02 = 63 | CES27 = 93 | CES52 = 96  | CES77 = 88 |
| CES03 = 32 | CES28 = 96 | CES53 = 95  | CES78 = 84 |
| CES04 = 70 | CES29 = 95 | CES54 = 95  | CES79 = 92 |
| CES05 = 50 | CES30 = 96 | CES55 = 95  | CES80 = 92 |
| CES06 = 51 | CES31 = 95 | CES56 = 98  | CES81 = 77 |
| CES07 = 43 | CES32 = 87 | CES57 = 98  | CES82 = 96 |
| CES08 = 42 | CES33 = 97 | CES58 = 98  | CES83 = 95 |
| CES09 = 29 | CES34 = 93 | CES59 = 100 | CES84 = 95 |
| CES10 = 75 | CES35 = 96 | CES60 = 94  | CES85 = 82 |
| CES11 = 58 | CES36 = 84 | CES61 = 95  | CES86 = 84 |
| CES12 = 64 | CES37 = 93 | CES62 = 90  | CES87 = 92 |
| CES13 = 44 | CES38 = 91 | CES63 = 95  | CES88 = 99 |
| CES14 = 74 | CES39 = 98 | CES64 = 95  | CES89 = 86 |
| CES15 = 72 | CES40 = 96 | CES65 = 92  | CES90 = 98 |
| CES16 = 48 | CES41 = 97 | CES66 = 93  | CES91 = 77 |
| CES17 = 49 | CES42 = 90 | CES67 = 92  | CES92 = 81 |
| CES18 = 56 | CES43 = 91 | CES68 = 91  | CES93 = 88 |
| CES19 = 71 | CES44 = 99 | CES69 = 92  | CES94 = 78 |
| CES20 = 67 | CES45 = 94 | CES70 = 89  | CES95 = 86 |
| CES21 = 86 | CES46 = 95 | CES71 = 85  | CES96 = 93 |
| CES22 = 78 | CES47 = 90 | CES72 = 95  | CES97 = 93 |
| CES23 = 91 | CES48 = 96 | CES73 = 84  | CES98 = 96 |
| CES24 = 90 | CES49 = 93 | CES74 = 91  | CES99 = 97 |
| CES25 = 71 | CES50 = 97 | CES75 = 86  |            |



Color Rendition by Hue-Angle Bin



**Measure Comparisons**



(END OF REPORT)