

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: METALUX

Report Number: P983117

Luminaire Tested: 24CZ-LD5-75-UNV-L940-RDP-CD1-U

Issue Date: 04/23/2025

**Test Information**

Test Method: LM-79-2019  
Report Number: P983117  
Test Lab: INNOVATION CENTER(P3)  
Issue Date: 04/23/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: METALUX  
Catalog Number: 24CZ-LD5-75-UNV-L940-RDP-CD1-U  
Description: METALUX CRUZE 2x4 7500LM PACKAGE 90CRI 4000K TROFFER LENS WITH RDP FILM INSERT  
Light Source: 4000K CCT, 90 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4888.0 lumens  
Efficiency: N/A  
Efficacy: 88.2 lumens/watt  
Spacing Criteria (0/90/45): 1.25 / 1.31 / 1.41  
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')  
CIE Type: Direct

Input Watts (W): 55.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT

TEST NUMBER: P983117

CATALOG NUMBER: 24CZ-LD5-75-UNV-L940-RDP-CD1-U

### Luminous Intensity Polar Plot



TEST NUMBER: P983117

CATALOG NUMBER: 24CZ-LD5-75-UNV-L940-RDP-CD1-U

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 108 | 103 | 99  | 95  | 105 | 101 | 97  | 93  | 97  | 93  | 90  |  | 93  | 90  | 87  |  | 89  |
| 2   | 98  | 89  | 82  | 76  | 95  | 87  | 81  | 75  | 84  | 78  | 73  |  | 80  | 76  | 71  |  | 77  |
| 3   | 89  | 78  | 69  | 62  | 86  | 76  | 68  | 62  | 73  | 66  | 61  |  | 70  | 64  | 59  |  | 68  |
| 4   | 81  | 68  | 59  | 52  | 79  | 67  | 58  | 52  | 64  | 57  | 51  |  | 62  | 56  | 50  |  | 60  |
| 5   | 74  | 61  | 52  | 45  | 72  | 60  | 51  | 44  | 58  | 50  | 44  |  | 56  | 49  | 43  |  | 54  |
| 6   | 68  | 55  | 45  | 39  | 66  | 54  | 45  | 39  | 52  | 44  | 38  |  | 50  | 43  | 38  |  | 48  |
| 7   | 63  | 49  | 40  | 34  | 62  | 49  | 40  | 34  | 47  | 39  | 34  |  | 45  | 39  | 33  |  | 44  |
| 8   | 59  | 45  | 36  | 30  | 57  | 44  | 36  | 30  | 43  | 35  | 30  |  | 42  | 35  | 30  |  | 40  |
| 9   | 55  | 41  | 33  | 27  | 54  | 41  | 33  | 27  | 39  | 32  | 27  |  | 38  | 32  | 27  |  | 37  |
| 10  | 51  | 38  | 30  | 24  | 50  | 37  | 30  | 24  | 36  | 29  | 24  |  | 35  | 29  | 24  |  | 35  |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°   | 45°  | 90°  |
|-----|------|------|------|
| 0°  | 2089 | 2089 | 2089 |
| 5°  | 2092 | 2107 | 2081 |
| 10° | 2085 | 2085 | 2085 |
| 15° | 2078 | 2089 | 2099 |
| 20° | 2071 | 2092 | 2103 |
| 25° | 2046 | 2079 | 2108 |
| 30° | 2029 | 2064 | 2123 |
| 35° | 2008 | 2064 | 2151 |
| 40° | 1987 | 2067 | 2200 |
| 45° | 1950 | 2073 | 2282 |
| 50° | 1907 | 2090 | 2392 |
| 55° | 1843 | 2146 | 2520 |
| 60° | 1757 | 2207 | 2666 |
| 65° | 1656 | 2284 | 2816 |
| 70° | 1478 | 2345 | 2942 |
| 75° | 1282 | 2348 | 2328 |
| 80° | 1089 | 1736 | 1882 |
| 85° | 937  | 1172 | 1054 |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°

Vertical Angle: 70°

Luminance: 2942 cd/sqm

TEST NUMBER: P983117

CATALOG NUMBER: 24CZ-LD5-75-UNV-L940-RDP-CD1-U

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 147.4  | 3.0       |
| 10°-20°   | 423.3  | 8.7       |
| 20°-30°   | 645.1  | 13.2      |
| 30°-40°   | 789.3  | 16.1      |
| 40°-50°   | 849.3  | 17.4      |
| 50°-60°   | 822.7  | 16.8      |
| 60°-70°   | 696.9  | 14.3      |
| 70°-80°   | 421.3  | 8.6       |
| 80°-90°   | 92.6   | 1.9       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1215.9 | 24.9      |
| 0°-40°    | 2005.2 | 41.0      |
| 0°-60°    | 3677.2 | 75.2      |
| 0°-90°    | 4888.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 4888.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | 22.5° | 45°  | 67.5° | 90°  | Flux |
|-----|------|-------|------|-------|------|------|
| 0°  | 1552 | 1552  | 1552 | 1552  | 1552 |      |
| 5°  | 1549 | 1549  | 1560 | 1552  | 1541 | 147  |
| 15° | 1492 | 1496  | 1499 | 1503  | 1507 | 421  |
| 25° | 1378 | 1386  | 1401 | 1412  | 1420 | 636  |
| 35° | 1222 | 1230  | 1256 | 1291  | 1310 | 765  |
| 45° | 1025 | 1044  | 1089 | 1158  | 1200 | 790  |
| 55° | 786  | 820   | 915  | 1021  | 1074 | 702  |
| 65° | 520  | 577   | 718  | 831   | 884  | 512  |
| 75° | 247  | 334   | 452  | 459   | 448  | 265  |
| 85° | 61   | 72    | 76   | 72    | 68   | 69   |
| 90° | 0    | 0     | 0    | 0     | 0    |      |

TEST NUMBER: P983117

CATALOG NUMBER: 24CZ-LD5-75-UNV-L940-RDP-CD1-U

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 22.5°  | 45°    | 67.5°  | 90°    |
|-------|--------|--------|--------|--------|--------|
| 0°    | 1552.5 | 1552.5 | 1552.5 | 1552.5 | 1552.5 |
| 2.5°  | 1571.5 | 1567.7 | 1556.3 | 1548.8 | 1541.1 |
| 5°    | 1548.8 | 1548.8 | 1560.1 | 1552.5 | 1541.1 |
| 7.5°  | 1537.3 | 1537.3 | 1537.3 | 1556.3 | 1537.3 |
| 10°   | 1526.0 | 1529.8 | 1526.0 | 1541.1 | 1526.0 |
| 12.5° | 1514.6 | 1514.6 | 1514.6 | 1518.3 | 1518.3 |
| 15°   | 1491.8 | 1495.6 | 1499.4 | 1503.1 | 1507.0 |
| 17.5° | 1469.0 | 1472.8 | 1480.4 | 1484.3 | 1488.0 |
| 20°   | 1446.3 | 1450.1 | 1461.4 | 1461.4 | 1469.0 |
| 22.5° | 1415.9 | 1415.9 | 1431.1 | 1434.9 | 1446.3 |
| 25°   | 1377.9 | 1385.5 | 1400.7 | 1412.1 | 1419.6 |
| 27.5° | 1343.8 | 1351.4 | 1366.6 | 1381.7 | 1393.1 |
| 30°   | 1305.8 | 1313.4 | 1328.6 | 1351.4 | 1366.6 |
| 32.5° | 1264.1 | 1271.6 | 1294.4 | 1320.9 | 1336.1 |
| 35°   | 1222.3 | 1229.9 | 1256.4 | 1290.6 | 1309.6 |
| 37.5° | 1176.7 | 1188.1 | 1218.5 | 1256.4 | 1279.2 |
| 40°   | 1131.2 | 1142.6 | 1176.7 | 1218.5 | 1252.7 |
| 42.5° | 1078.0 | 1093.2 | 1131.2 | 1188.1 | 1226.1 |
| 45°   | 1024.9 | 1043.9 | 1089.4 | 1157.7 | 1199.5 |
| 47.5° | 968.0  | 987.0  | 1040.1 | 1127.4 | 1172.9 |
| 50°   | 911.0  | 933.8  | 998.3  | 1093.2 | 1142.6 |
| 52.5° | 850.3  | 873.0  | 956.5  | 1059.0 | 1112.2 |
| 55°   | 785.8  | 820.0  | 914.8  | 1021.1 | 1074.2 |
| 57.5° | 721.3  | 759.2  | 865.5  | 979.4  | 1036.3 |
| 60°   | 652.9  | 698.5  | 820.0  | 933.8  | 990.7  |
| 62.5° | 588.4  | 637.8  | 770.6  | 884.5  | 941.4  |
| 65°   | 520.1  | 577.0  | 717.5  | 831.3  | 884.5  |
| 67.5° | 447.9  | 520.1  | 656.7  | 766.8  | 820.0  |
| 70°   | 375.8  | 459.3  | 596.0  | 698.5  | 747.8  |
| 72.5° | 311.2  | 398.6  | 527.6  | 614.9  | 614.9  |
| 75°   | 246.7  | 334.1  | 451.7  | 459.3  | 447.9  |
| 77.5° | 189.8  | 273.4  | 353.0  | 322.7  | 330.2  |
| 80°   | 140.5  | 208.7  | 224.0  | 235.4  | 242.9  |
| 82.5° | 94.9   | 140.5  | 144.2  | 151.9  | 151.9  |
| 85°   | 60.7   | 72.2   | 75.9   | 72.2   | 68.3   |
| 87.5° | 26.5   | 30.4   | 22.8   | 15.2   | 11.4   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP3-2508-516-7

Test Date: 09/03/2025

Luminaire Tested: 24CZ-LD5-65-S-UNV-L940-CD1-U

Data in this report applies to families of products including 24CZ-LD5-65-S-UNV-L940-CD1-U

### Test Information

Test Method: LM-79-2019  
 Report Number: SP3-2508-516-7  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP3 - 3M SPHERE  
 Measurement Geometry:  $4\pi$   
 Issue Date: 09/05/2025  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: Metalux  
 Catalog Number: **24CZ-LD5-65-S-UNV-L940-CD1-U**  
 Description: 2X4 CRUZE SB 6500LM 940 SMOOTH LENS

### Spectral Parameters

CCT (K): 3955  
 CIE  $u'$ : 0.2264  
 CIE  $v'$ : 0.5014  
 Duv: -0.0009  
 CIE x: 0.3818  
 CIE y: 0.3758  
 CIE z: 0.2424  
 Peak Wavelength (nm): 630  
 Dominant Wavelength (nm): 579  
 Purity: 27.35334  
 R<sub>f</sub>: 90.3  
 R<sub>g</sub>: 99.3

CRI (Ra): 93.6  
 R1: 95.0  
 R2: 96.2  
 R3: 95.3  
 R4: 94.7  
 R5: 93.8  
 R6: 93.5  
 R7: 94.0  
 R8: 86.7  
 R9: 65.5  
 R10: 88.9  
 R11: 94.8  
 R12: 71.7  
 R13: 95.4  
 R14: 96.7  
 R15: 92.2



### Test Conditions

Stabilization Time: 22M  
 Operation Time: 1H 22M  
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP3-2508-516-7

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | 3M SPHERE IN02505     | 7/1/2025         | 1/1/2026             |
| Power Meter                    | XITRON INXT2011006    | 1/20/2025        | 1/20/2026            |
| AC Power Source                | CHROMA 61604 IN6064A  | 10/22/2024       | 10/22/2025           |
| DC Power Source                | EYSIGHT N5770A IN0534 | 10/22/2024       | 10/22/2025           |
| Sphere Thermometer             | TANDD IN4036E         | 10/22/2024       | 10/22/2025           |
|                                |                       |                  |                      |



REPORT NUMBER: SP3-2508-516-7

### Photopic Flux vs. Wavelength



### Photopic Lumens: NR

| λ (nm) | Power W <sup>λ</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>λ</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>λ</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>λ</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>λ</sup> /nm | Lumens (φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360    | 0                        | NR            | 490    | 171                      | NR            | 620    | 355                      | NR            | 750    | 8                        | NR            | 880    | 0                        | NR            |
| 365    | 0                        | NR            | 495    | 199                      | NR            | 625    | 352                      | NR            | 755    | 7                        | NR            | 885    | 0                        | NR            |
| 370    | 0                        | NR            | 500    | 230                      | NR            | 630    | 1000                     | NR            | 760    | 6                        | NR            | 890    | 0                        | NR            |
| 375    | 0                        | NR            | 505    | 257                      | NR            | 635    | 711                      | NR            | 765    | 5                        | NR            | 895    | 0                        | NR            |
| 380    | 0                        | NR            | 510    | 278                      | NR            | 640    | 235                      | NR            | 770    | 4                        | NR            | 900    | 0                        | NR            |
| 385    | 0                        | NR            | 515    | 295                      | NR            | 645    | 222                      | NR            | 775    | 4                        | NR            | 905    | 0                        | NR            |
| 390    | 1                        | NR            | 520    | 305                      | NR            | 650    | 198                      | NR            | 780    | 3                        | NR            | 910    | 0                        | NR            |
| 395    | 2                        | NR            | 525    | 313                      | NR            | 655    | 165                      | NR            | 785    | 3                        | NR            | 915    | 0                        | NR            |
| 400    | 3                        | NR            | 530    | 318                      | NR            | 660    | 142                      | NR            | 790    | 2                        | NR            | 920    | 0                        | NR            |
| 405    | 4                        | NR            | 535    | 323                      | NR            | 665    | 120                      | NR            | 795    | 2                        | NR            | 925    | 0                        | NR            |
| 410    | 6                        | NR            | 540    | 327                      | NR            | 670    | 110                      | NR            | 800    | 2                        | NR            | 930    | 0                        | NR            |
| 415    | 9                        | NR            | 545    | 333                      | NR            | 675    | 91                       | NR            | 805    | 2                        | NR            | 935    | 0                        | NR            |
| 420    | 15                       | NR            | 550    | 339                      | NR            | 680    | 77                       | NR            | 810    | 1                        | NR            | 940    | 0                        | NR            |
| 425    | 27                       | NR            | 555    | 343                      | NR            | 685    | 67                       | NR            | 815    | 1                        | NR            | 945    | 0                        | NR            |
| 430    | 48                       | NR            | 560    | 349                      | NR            | 690    | 57                       | NR            | 820    | 1                        | NR            | 950    | 0                        | NR            |
| 435    | 87                       | NR            | 565    | 355                      | NR            | 695    | 49                       | NR            | 825    | 1                        | NR            | 955    | 0                        | NR            |
| 440    | 155                      | NR            | 570    | 358                      | NR            | 700    | 42                       | NR            | 830    | 1                        | NR            | 960    | 0                        | NR            |
| 445    | 291                      | NR            | 575    | 363                      | NR            | 705    | 36                       | NR            | 835    | 1                        | NR            | 965    | 0                        | NR            |
| 450    | 475                      | NR            | 580    | 365                      | NR            | 710    | 30                       | NR            | 840    | 1                        | NR            | 970    | 0                        | NR            |
| 455    | 466                      | NR            | 585    | 367                      | NR            | 715    | 26                       | NR            | 845    | 1                        | NR            | 975    | 0                        | NR            |
| 460    | 308                      | NR            | 590    | 367                      | NR            | 720    | 22                       | NR            | 850    | 0                        | NR            | 980    | 0                        | NR            |
| 465    | 246                      | NR            | 595    | 364                      | NR            | 725    | 19                       | NR            | 855    | 0                        | NR            | 985    | 0                        | NR            |
| 470    | 202                      | NR            | 600    | 363                      | NR            | 730    | 16                       | NR            | 860    | 0                        | NR            | 990    | 0                        | NR            |
| 475    | 152                      | NR            | 605    | 361                      | NR            | 735    | 14                       | NR            | 865    | 0                        | NR            | 995    | 0                        | NR            |
| 480    | 140                      | NR            | 610    | 391                      | NR            | 740    | 11                       | NR            | 870    | 0                        | NR            | 1000   | 0                        | NR            |
| 485    | 152                      | NR            | 615    | 418                      | NR            | 745    | 10                       | NR            | 875    | 0                        | NR            |        |                          |               |

REPORT NUMBER: SP3-2508-516-7

### Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.77

| λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(Φ/nm) |
|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|
| 360       | 0                           | NR               | 490       | 171                         | NR               | 620       | 355                         | NR               | 750       | 8                           | NR               | 880       | 0                           | NR               |
| 365       | 0                           | NR               | 495       | 199                         | NR               | 625       | 352                         | NR               | 755       | 7                           | NR               | 885       | 0                           | NR               |
| 370       | 0                           | NR               | 500       | 230                         | NR               | 630       | 1000                        | NR               | 760       | 6                           | NR               | 890       | 0                           | NR               |
| 375       | 0                           | NR               | 505       | 257                         | NR               | 635       | 711                         | NR               | 765       | 5                           | NR               | 895       | 0                           | NR               |
| 380       | 0                           | NR               | 510       | 278                         | NR               | 640       | 235                         | NR               | 770       | 4                           | NR               | 900       | 0                           | NR               |
| 385       | 0                           | NR               | 515       | 295                         | NR               | 645       | 222                         | NR               | 775       | 4                           | NR               | 905       | 0                           | NR               |
| 390       | 1                           | NR               | 520       | 305                         | NR               | 650       | 198                         | NR               | 780       | 3                           | NR               | 910       | 0                           | NR               |
| 395       | 2                           | NR               | 525       | 313                         | NR               | 655       | 165                         | NR               | 785       | 3                           | NR               | 915       | 0                           | NR               |
| 400       | 3                           | NR               | 530       | 318                         | NR               | 660       | 142                         | NR               | 790       | 2                           | NR               | 920       | 0                           | NR               |
| 405       | 4                           | NR               | 535       | 323                         | NR               | 665       | 120                         | NR               | 795       | 2                           | NR               | 925       | 0                           | NR               |
| 410       | 6                           | NR               | 540       | 327                         | NR               | 670       | 110                         | NR               | 800       | 2                           | NR               | 930       | 0                           | NR               |
| 415       | 9                           | NR               | 545       | 333                         | NR               | 675       | 91                          | NR               | 805       | 2                           | NR               | 935       | 0                           | NR               |
| 420       | 15                          | NR               | 550       | 339                         | NR               | 680       | 77                          | NR               | 810       | 1                           | NR               | 940       | 0                           | NR               |
| 425       | 27                          | NR               | 555       | 343                         | NR               | 685       | 67                          | NR               | 815       | 1                           | NR               | 945       | 0                           | NR               |
| 430       | 48                          | NR               | 560       | 349                         | NR               | 690       | 57                          | NR               | 820       | 1                           | NR               | 950       | 0                           | NR               |
| 435       | 87                          | NR               | 565       | 355                         | NR               | 695       | 49                          | NR               | 825       | 1                           | NR               | 955       | 0                           | NR               |
| 440       | 155                         | NR               | 570       | 358                         | NR               | 700       | 42                          | NR               | 830       | 1                           | NR               | 960       | 0                           | NR               |
| 445       | 291                         | NR               | 575       | 363                         | NR               | 705       | 36                          | NR               | 835       | 1                           | NR               | 965       | 0                           | NR               |
| 450       | 475                         | NR               | 580       | 365                         | NR               | 710       | 30                          | NR               | 840       | 1                           | NR               | 970       | 0                           | NR               |
| 455       | 466                         | NR               | 585       | 367                         | NR               | 715       | 26                          | NR               | 845       | 1                           | NR               | 975       | 0                           | NR               |
| 460       | 308                         | NR               | 590       | 367                         | NR               | 720       | 22                          | NR               | 850       | 0                           | NR               | 980       | 0                           | NR               |
| 465       | 246                         | NR               | 595       | 364                         | NR               | 725       | 19                          | NR               | 855       | 0                           | NR               | 985       | 0                           | NR               |
| 470       | 202                         | NR               | 600       | 363                         | NR               | 730       | 16                          | NR               | 860       | 0                           | NR               | 990       | 0                           | NR               |
| 475       | 152                         | NR               | 605       | 361                         | NR               | 735       | 14                          | NR               | 865       | 0                           | NR               | 995       | 0                           | NR               |
| 480       | 140                         | NR               | 610       | 391                         | NR               | 740       | 11                          | NR               | 870       | 0                           | NR               | 1000      | 0                           | NR               |
| 485       | 152                         | NR               | 615       | 418                         | NR               | 745       | 10                          | NR               | 875       | 0                           | NR               |           |                             |                  |

REPORT NUMBER: SP3-2508-516-7

### Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 3.69

| λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) |
|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|
| 360       | 0                           | NR               | 490       | 171                         | NR               | 620       | 355                         | NR               | 750       | 8                           | NR               | 880       | 0                           | NR               |
| 365       | 0                           | NR               | 495       | 199                         | NR               | 625       | 352                         | NR               | 755       | 7                           | NR               | 885       | 0                           | NR               |
| 370       | 0                           | NR               | 500       | 230                         | NR               | 630       | 1000                        | NR               | 760       | 6                           | NR               | 890       | 0                           | NR               |
| 375       | 0                           | NR               | 505       | 257                         | NR               | 635       | 711                         | NR               | 765       | 5                           | NR               | 895       | 0                           | NR               |
| 380       | 0                           | NR               | 510       | 278                         | NR               | 640       | 235                         | NR               | 770       | 4                           | NR               | 900       | 0                           | NR               |
| 385       | 0                           | NR               | 515       | 295                         | NR               | 645       | 222                         | NR               | 775       | 4                           | NR               | 905       | 0                           | NR               |
| 390       | 1                           | NR               | 520       | 305                         | NR               | 650       | 198                         | NR               | 780       | 3                           | NR               | 910       | 0                           | NR               |
| 395       | 2                           | NR               | 525       | 313                         | NR               | 655       | 165                         | NR               | 785       | 3                           | NR               | 915       | 0                           | NR               |
| 400       | 3                           | NR               | 530       | 318                         | NR               | 660       | 142                         | NR               | 790       | 2                           | NR               | 920       | 0                           | NR               |
| 405       | 4                           | NR               | 535       | 323                         | NR               | 665       | 120                         | NR               | 795       | 2                           | NR               | 925       | 0                           | NR               |
| 410       | 6                           | NR               | 540       | 327                         | NR               | 670       | 110                         | NR               | 800       | 2                           | NR               | 930       | 0                           | NR               |
| 415       | 9                           | NR               | 545       | 333                         | NR               | 675       | 91                          | NR               | 805       | 2                           | NR               | 935       | 0                           | NR               |
| 420       | 15                          | NR               | 550       | 339                         | NR               | 680       | 77                          | NR               | 810       | 1                           | NR               | 940       | 0                           | NR               |
| 425       | 27                          | NR               | 555       | 343                         | NR               | 685       | 67                          | NR               | 815       | 1                           | NR               | 945       | 0                           | NR               |
| 430       | 48                          | NR               | 560       | 349                         | NR               | 690       | 57                          | NR               | 820       | 1                           | NR               | 950       | 0                           | NR               |
| 435       | 87                          | NR               | 565       | 355                         | NR               | 695       | 49                          | NR               | 825       | 1                           | NR               | 955       | 0                           | NR               |
| 440       | 155                         | NR               | 570       | 358                         | NR               | 700       | 42                          | NR               | 830       | 1                           | NR               | 960       | 0                           | NR               |
| 445       | 291                         | NR               | 575       | 363                         | NR               | 705       | 36                          | NR               | 835       | 1                           | NR               | 965       | 0                           | NR               |
| 450       | 475                         | NR               | 580       | 365                         | NR               | 710       | 30                          | NR               | 840       | 1                           | NR               | 970       | 0                           | NR               |
| 455       | 466                         | NR               | 585       | 367                         | NR               | 715       | 26                          | NR               | 845       | 1                           | NR               | 975       | 0                           | NR               |
| 460       | 308                         | NR               | 590       | 367                         | NR               | 720       | 22                          | NR               | 850       | 0                           | NR               | 980       | 0                           | NR               |
| 465       | 246                         | NR               | 595       | 364                         | NR               | 725       | 19                          | NR               | 855       | 0                           | NR               | 985       | 0                           | NR               |
| 470       | 202                         | NR               | 600       | 363                         | NR               | 730       | 16                          | NR               | 860       | 0                           | NR               | 990       | 0                           | NR               |
| 475       | 152                         | NR               | 605       | 361                         | NR               | 735       | 14                          | NR               | 865       | 0                           | NR               | 995       | 0                           | NR               |
| 480       | 140                         | NR               | 610       | 391                         | NR               | 740       | 11                          | NR               | 870       | 0                           | NR               | 1000      | 0                           | NR               |
| 485       | 152                         | NR               | 615       | 418                         | NR               | 745       | 10                          | NR               | 875       | 0                           | NR               |           |                             |                  |

REPORT NUMBER: SP3-2508-516-7

TM-30-18

### Summary

$R_f = 90.3$   
 $R_g = 99.3$   
 $CIE R_a = 93.6$   
 $R_9 = 65.5$



### Color Vector Graphics



**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 93 | CES51 = 97 | CES76 = 85 |
| CES02 = 62 | CES27 = 90 | CES52 = 99 | CES77 = 87 |
| CES03 = 31 | CES28 = 95 | CES53 = 97 | CES78 = 82 |
| CES04 = 69 | CES29 = 96 | CES54 = 92 | CES79 = 93 |
| CES05 = 49 | CES30 = 89 | CES55 = 90 | CES80 = 92 |
| CES06 = 50 | CES31 = 97 | CES56 = 94 | CES81 = 80 |
| CES07 = 42 | CES32 = 89 | CES57 = 92 | CES82 = 96 |
| CES08 = 41 | CES33 = 98 | CES58 = 92 | CES83 = 96 |
| CES09 = 29 | CES34 = 93 | CES59 = 97 | CES84 = 93 |
| CES10 = 74 | CES35 = 95 | CES60 = 91 | CES85 = 80 |
| CES11 = 57 | CES36 = 77 | CES61 = 91 | CES86 = 84 |
| CES12 = 63 | CES37 = 94 | CES62 = 83 | CES87 = 91 |
| CES13 = 43 | CES38 = 83 | CES63 = 91 | CES88 = 98 |
| CES14 = 74 | CES39 = 99 | CES64 = 88 | CES89 = 85 |
| CES15 = 71 | CES40 = 98 | CES65 = 87 | CES90 = 96 |
| CES16 = 47 | CES41 = 96 | CES66 = 84 | CES91 = 70 |
| CES17 = 49 | CES42 = 92 | CES67 = 83 | CES92 = 76 |
| CES18 = 56 | CES43 = 93 | CES68 = 86 | CES93 = 85 |
| CES19 = 71 | CES44 = 99 | CES69 = 87 | CES94 = 76 |
| CES20 = 66 | CES45 = 97 | CES70 = 84 | CES95 = 81 |
| CES21 = 85 | CES46 = 97 | CES71 = 76 | CES96 = 92 |
| CES22 = 78 | CES47 = 94 | CES72 = 93 | CES97 = 95 |
| CES23 = 91 | CES48 = 89 | CES73 = 78 | CES98 = 95 |
| CES24 = 90 | CES49 = 96 | CES74 = 90 | CES99 = 93 |
| CES25 = 71 | CES50 = 98 | CES75 = 79 |            |



### Color Rendition by Hue-Angle Bin



**Measure Comparisons**


(END OF REPORT)