

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: METALUX

Report Number: P983060

Luminaire Tested: 24CZ-LD5-65-UNV-L950-HRP-CD1-U

Issue Date: 04/23/2025

**Test Information**

Test Method: LM-79-2019  
Report Number: P983060  
Test Lab: INNOVATION CENTER(P3)  
Issue Date: 04/23/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: METALUX  
Catalog Number: 24CZ-LD5-65-UNV-L950-HRP-CD1-U  
Description: METALUX CRUZE 2x4 6500LM PACKAGE 90CRI 5000K TROFFER LENS WITH HRP FILM INSERT  
Light Source: 5000K CCT, 90 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5092.0 lumens  
Efficiency: N/A  
Efficacy: 104.1 lumens/watt  
Spacing Criteria (0/90/45): 1.25 / 1.29 / 1.4  
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')  
CIE Type: Direct

Input Watts (W): 48.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT

TEST NUMBER: P983060

CATALOG NUMBER: 24CZ-LD5-65-UNV-L950-HRP-CD1-U

### Luminous Intensity Polar Plot



TEST NUMBER: P983060

CATALOG NUMBER: 24CZ-LD5-65-UNV-L950-HRP-CD1-U

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 108 | 103 | 99  | 95  | 105 | 101 | 97  | 93  | 97  | 93  | 90  |  | 93  | 90  | 87  |  | 89  |
| 2   | 98  | 89  | 82  | 76  | 95  | 87  | 81  | 75  | 84  | 78  | 74  |  | 81  | 76  | 72  |  | 77  |
| 3   | 89  | 78  | 70  | 63  | 86  | 76  | 69  | 62  | 73  | 67  | 61  |  | 71  | 65  | 60  |  | 68  |
| 4   | 81  | 69  | 60  | 53  | 79  | 68  | 59  | 52  | 65  | 58  | 52  |  | 63  | 56  | 51  |  | 60  |
| 5   | 75  | 61  | 52  | 45  | 72  | 60  | 52  | 45  | 58  | 50  | 44  |  | 56  | 49  | 44  |  | 54  |
| 6   | 69  | 55  | 46  | 39  | 67  | 54  | 45  | 39  | 52  | 45  | 39  |  | 51  | 44  | 38  |  | 49  |
| 7   | 64  | 50  | 41  | 35  | 62  | 49  | 41  | 34  | 48  | 40  | 34  |  | 46  | 39  | 34  |  | 45  |
| 8   | 59  | 45  | 37  | 31  | 58  | 45  | 36  | 31  | 43  | 36  | 31  |  | 42  | 35  | 30  |  | 41  |
| 9   | 55  | 42  | 33  | 28  | 54  | 41  | 33  | 28  | 40  | 33  | 27  |  | 39  | 32  | 27  |  | 38  |
| 10  | 52  | 38  | 30  | 25  | 51  | 38  | 30  | 25  | 37  | 30  | 25  |  | 36  | 29  | 25  |  | 35  |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°   | 45°  | 90°  |
|-----|------|------|------|
| 0°  | 2251 | 2251 | 2251 |
| 5°  | 2260 | 2257 | 2251 |
| 10° | 2253 | 2253 | 2253 |
| 15° | 2242 | 2251 | 2257 |
| 20° | 2227 | 2246 | 2258 |
| 25° | 2208 | 2234 | 2257 |
| 30° | 2183 | 2223 | 2257 |
| 35° | 2157 | 2214 | 2264 |
| 40° | 2126 | 2203 | 2272 |
| 45° | 2084 | 2191 | 2304 |
| 50° | 2032 | 2182 | 2347 |
| 55° | 1970 | 2185 | 2410 |
| 60° | 1884 | 2207 | 2500 |
| 65° | 1743 | 2229 | 2625 |
| 70° | 1570 | 2299 | 2789 |
| 75° | 1327 | 2370 | 2495 |
| 80° | 1031 | 2028 | 2096 |
| 85° | 741  | 1380 | 1212 |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°

Vertical Angle: 72.5°

Luminance: 2821 cd/sqm

TEST NUMBER: P983060

CATALOG NUMBER: 24CZ-LD5-65-UNV-L950-HRP-CD1-U

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 158.6  | 3.1       |
| 10°-20°   | 455.4  | 8.9       |
| 20°-30°   | 692.5  | 13.6      |
| 30°-40°   | 841.3  | 16.5      |
| 40°-50°   | 888.0  | 17.4      |
| 50°-60°   | 834.4  | 16.4      |
| 60°-70°   | 686.9  | 13.5      |
| 70°-80°   | 432.7  | 8.5       |
| 80°-90°   | 102.2  | 2.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1306.4 | 25.7      |
| 0°-40°    | 2147.8 | 42.2      |
| 0°-60°    | 3870.2 | 76.0      |
| 0°-90°    | 5092.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 5092.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | 22.5° | 45°  | 67.5° | 90°  | Flux |
|-----|------|-------|------|-------|------|------|
| 0°  | 1673 | 1673  | 1673 | 1673  | 1673 |      |
| 5°  | 1673 | 1664  | 1671 | 1669  | 1666 | 159  |
| 15° | 1610 | 1603  | 1616 | 1621  | 1621 | 454  |
| 25° | 1488 | 1485  | 1505 | 1514  | 1520 | 685  |
| 35° | 1313 | 1320  | 1348 | 1366  | 1379 | 821  |
| 45° | 1095 | 1112  | 1152 | 1184  | 1211 | 844  |
| 55° | 840  | 870   | 931  | 997   | 1027 | 750  |
| 65° | 548  | 600   | 700  | 790   | 824  | 544  |
| 75° | 255  | 334   | 456  | 497   | 480  | 272  |
| 85° | 48   | 81    | 89   | 83    | 78   | 60   |
| 90° | 0    | 0     | 0    | 0     | 0    |      |

TEST NUMBER: P983060

CATALOG NUMBER: 24CZ-LD5-65-UNV-L950-HRP-CD1-U

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 22.5°  | 45°    | 67.5°  | 90°    |
|-------|--------|--------|--------|--------|--------|
| 0°    | 1673.1 | 1673.1 | 1673.1 | 1673.1 | 1673.1 |
| 2.5°  | 1679.6 | 1668.6 | 1675.2 | 1673.1 | 1666.5 |
| 5°    | 1673.1 | 1664.3 | 1670.8 | 1668.6 | 1666.5 |
| 7.5°  | 1664.3 | 1655.6 | 1662.2 | 1659.9 | 1659.9 |
| 10°   | 1649.1 | 1642.5 | 1649.1 | 1649.1 | 1649.1 |
| 12.5° | 1631.6 | 1625.1 | 1633.7 | 1635.9 | 1638.2 |
| 15°   | 1609.7 | 1603.2 | 1616.3 | 1620.6 | 1620.6 |
| 17.5° | 1583.6 | 1579.2 | 1592.3 | 1596.6 | 1601.1 |
| 20°   | 1555.2 | 1553.1 | 1568.3 | 1572.6 | 1577.1 |
| 22.5° | 1522.5 | 1522.5 | 1537.8 | 1542.2 | 1550.9 |
| 25°   | 1487.6 | 1485.4 | 1505.1 | 1513.8 | 1520.3 |
| 27.5° | 1448.3 | 1448.3 | 1470.2 | 1481.1 | 1487.6 |
| 30°   | 1404.8 | 1409.1 | 1430.9 | 1444.0 | 1452.7 |
| 32.5° | 1361.1 | 1365.5 | 1391.7 | 1406.9 | 1417.8 |
| 35°   | 1313.1 | 1319.7 | 1348.0 | 1365.5 | 1378.6 |
| 37.5° | 1260.8 | 1271.7 | 1302.2 | 1321.8 | 1337.1 |
| 40°   | 1210.6 | 1219.3 | 1254.3 | 1276.0 | 1293.5 |
| 42.5° | 1153.8 | 1169.2 | 1204.1 | 1230.3 | 1249.8 |
| 45°   | 1095.0 | 1112.4 | 1151.7 | 1184.4 | 1210.6 |
| 47.5° | 1033.9 | 1055.8 | 1097.2 | 1140.8 | 1167.0 |
| 50°   | 970.7  | 994.7  | 1042.6 | 1095.0 | 1121.2 |
| 52.5° | 907.4  | 933.6  | 985.9  | 1047.0 | 1075.3 |
| 55°   | 839.8  | 870.3  | 931.4  | 996.9  | 1027.4 |
| 57.5° | 769.9  | 804.9  | 874.7  | 948.9  | 979.4  |
| 60°   | 700.2  | 737.3  | 820.1  | 894.3  | 929.2  |
| 62.5° | 628.2  | 669.6  | 759.0  | 844.1  | 876.9  |
| 65°   | 547.5  | 599.9  | 700.2  | 789.6  | 824.5  |
| 67.5° | 473.3  | 527.9  | 643.5  | 732.9  | 769.9  |
| 70°   | 399.1  | 462.4  | 584.5  | 674.0  | 708.9  |
| 72.5° | 325.0  | 399.1  | 519.1  | 610.7  | 630.4  |
| 75°   | 255.2  | 333.7  | 455.9  | 497.3  | 479.9  |
| 77.5° | 187.6  | 274.8  | 383.9  | 362.1  | 357.7  |
| 80°   | 133.1  | 218.2  | 261.7  | 263.9  | 270.5  |
| 82.5° | 85.1   | 161.4  | 170.2  | 172.3  | 174.5  |
| 85°   | 48.0   | 80.8   | 89.4   | 82.9   | 78.5   |
| 87.5° | 21.8   | 26.2   | 21.8   | 15.2   | 13.1   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP3-2508-516-8

Test Date: 09/03/2025

Luminaire Tested: 24CZ-LD5-65-S-UNV-L950-CD1-U

Data in this report applies to families of products including 24CZ-LD5-65-S-UNV-L950-CD1-U

### Test Information

Test Method: LM-79-2019  
 Report Number: SP3-2508-516-8  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP3 - 3M SPHERE  
 Measurement Geometry:  $4\pi$   
 Issue Date: 09/05/2025  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: Metalux  
 Catalog Number: **24CZ-LD5-65-S-UNV-L950-CD1-U**  
 Description: 2X4 CRUZE SB 6500LM 950 SMOOTH LENS

### Spectral Parameters

CCT (K): 5019  
 CIE  $u'$ : 0.2113  
 CIE  $v'$ : 0.4842  
 Duv: -0.0002  
 CIE x: 0.3445  
 CIE y: 0.3508  
 CIE z: 0.3046  
 Peak Wavelength (nm): 630  
 Dominant Wavelength (nm): 572  
 Purity: 8.636369  
 R<sub>f</sub>: 89.8  
 R<sub>g</sub>: 98.5

CRI (Ra): 94.6  
 R1: 96.4  
 R2: 98.4  
 R3: 96.9  
 R4: 94.5  
 R5: 94.5  
 R6: 93.5  
 R7: 93.6  
 R8: 89.4  
 R9: 74.6  
 R10: 94.2  
 R11: 95.5  
 R12: 70.8  
 R13: 98.0  
 R14: 98.0  
 R15: 95.0



### Test Conditions

Stabilization Time: M  
 Operation Time: 1H 0M  
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP3-2508-516-8

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | 3M SPHERE IN02505     | 7/1/2025         | 1/1/2026             |
| Power Meter                    | XITRON INXT2011006    | 1/20/2025        | 1/20/2026            |
| AC Power Source                | CHROMA 61604 IN6064A  | 10/22/2024       | 10/22/2025           |
| DC Power Source                | EYSIGHT N5770A IN0534 | 10/22/2024       | 10/22/2025           |
| Sphere Thermometer             | TANDD IN4036E         | 10/22/2024       | 10/22/2025           |
|                                |                       |                  |                      |

REPORT NUMBER: SP3-2508-516-8

**CIE 1931 Chromaticity Diagram**



**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 5000K 4-step quadrangle

REPORT NUMBER: SP3-2508-516-8

### Photopic Flux vs. Wavelength



### Photopic Lumens: NR

| λ (nm) | Power W <sup>λ</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>λ</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>λ</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>λ</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>λ</sup> /nm | Lumens (φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360    | 0                        | NR            | 490    | 249                      | NR            | 620    | 343                      | NR            | 750    | 8                        | NR            | 880    | 0                        | NR            |
| 365    | 0                        | NR            | 495    | 269                      | NR            | 625    | 339                      | NR            | 755    | 7                        | NR            | 885    | 0                        | NR            |
| 370    | 0                        | NR            | 500    | 296                      | NR            | 630    | 1000                     | NR            | 760    | 6                        | NR            | 890    | 0                        | NR            |
| 375    | 0                        | NR            | 505    | 325                      | NR            | 635    | 705                      | NR            | 765    | 5                        | NR            | 895    | 0                        | NR            |
| 380    | 0                        | NR            | 510    | 347                      | NR            | 640    | 221                      | NR            | 770    | 4                        | NR            | 900    | 0                        | NR            |
| 385    | 0                        | NR            | 515    | 363                      | NR            | 645    | 210                      | NR            | 775    | 4                        | NR            | 905    | 0                        | NR            |
| 390    | 1                        | NR            | 520    | 371                      | NR            | 650    | 186                      | NR            | 780    | 3                        | NR            | 910    | 0                        | NR            |
| 395    | 3                        | NR            | 525    | 378                      | NR            | 655    | 155                      | NR            | 785    | 3                        | NR            | 915    | 0                        | NR            |
| 400    | 4                        | NR            | 530    | 381                      | NR            | 660    | 132                      | NR            | 790    | 2                        | NR            | 920    | 0                        | NR            |
| 405    | 5                        | NR            | 535    | 383                      | NR            | 665    | 111                      | NR            | 795    | 2                        | NR            | 925    | 0                        | NR            |
| 410    | 7                        | NR            | 540    | 385                      | NR            | 670    | 102                      | NR            | 800    | 2                        | NR            | 930    | 0                        | NR            |
| 415    | 10                       | NR            | 545    | 389                      | NR            | 675    | 84                       | NR            | 805    | 1                        | NR            | 935    | 0                        | NR            |
| 420    | 17                       | NR            | 550    | 391                      | NR            | 680    | 72                       | NR            | 810    | 1                        | NR            | 940    | 0                        | NR            |
| 425    | 29                       | NR            | 555    | 392                      | NR            | 685    | 62                       | NR            | 815    | 1                        | NR            | 945    | 0                        | NR            |
| 430    | 53                       | NR            | 560    | 393                      | NR            | 690    | 53                       | NR            | 820    | 1                        | NR            | 950    | 0                        | NR            |
| 435    | 97                       | NR            | 565    | 394                      | NR            | 695    | 45                       | NR            | 825    | 1                        | NR            | 955    | 0                        | NR            |
| 440    | 173                      | NR            | 570    | 391                      | NR            | 700    | 39                       | NR            | 830    | 1                        | NR            | 960    | 0                        | NR            |
| 445    | 321                      | NR            | 575    | 389                      | NR            | 705    | 33                       | NR            | 835    | 1                        | NR            | 965    | 0                        | NR            |
| 450    | 597                      | NR            | 580    | 385                      | NR            | 710    | 28                       | NR            | 840    | 1                        | NR            | 970    | 0                        | NR            |
| 455    | 795                      | NR            | 585    | 382                      | NR            | 715    | 24                       | NR            | 845    | 1                        | NR            | 975    | 0                        | NR            |
| 460    | 615                      | NR            | 590    | 375                      | NR            | 720    | 21                       | NR            | 850    | 0                        | NR            | 980    | 0                        | NR            |
| 465    | 438                      | NR            | 595    | 367                      | NR            | 725    | 17                       | NR            | 855    | 0                        | NR            | 985    | 0                        | NR            |
| 470    | 372                      | NR            | 600    | 361                      | NR            | 730    | 15                       | NR            | 860    | 0                        | NR            | 990    | 0                        | NR            |
| 475    | 290                      | NR            | 605    | 355                      | NR            | 735    | 13                       | NR            | 865    | 0                        | NR            | 995    | 0                        | NR            |
| 480    | 236                      | NR            | 610    | 383                      | NR            | 740    | 11                       | NR            | 870    | 0                        | NR            | 1000   | 0                        | NR            |
| 485    | 232                      | NR            | 615    | 408                      | NR            | 745    | 9                        | NR            | 875    | 0                        | NR            |        |                          |               |

REPORT NUMBER: SP3-2508-516-8

### Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 2.11

| $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 0                                    | NR                             | 490               | 249                                  | NR                             | 620               | 343                                  | NR                             | 750               | 8                                    | NR                             | 880               | 0                                    | NR                             |
| 365               | 0                                    | NR                             | 495               | 269                                  | NR                             | 625               | 339                                  | NR                             | 755               | 7                                    | NR                             | 885               | 0                                    | NR                             |
| 370               | 0                                    | NR                             | 500               | 296                                  | NR                             | 630               | 1000                                 | NR                             | 760               | 6                                    | NR                             | 890               | 0                                    | NR                             |
| 375               | 0                                    | NR                             | 505               | 325                                  | NR                             | 635               | 705                                  | NR                             | 765               | 5                                    | NR                             | 895               | 0                                    | NR                             |
| 380               | 0                                    | NR                             | 510               | 347                                  | NR                             | 640               | 221                                  | NR                             | 770               | 4                                    | NR                             | 900               | 0                                    | NR                             |
| 385               | 0                                    | NR                             | 515               | 363                                  | NR                             | 645               | 210                                  | NR                             | 775               | 4                                    | NR                             | 905               | 0                                    | NR                             |
| 390               | 1                                    | NR                             | 520               | 371                                  | NR                             | 650               | 186                                  | NR                             | 780               | 3                                    | NR                             | 910               | 0                                    | NR                             |
| 395               | 3                                    | NR                             | 525               | 378                                  | NR                             | 655               | 155                                  | NR                             | 785               | 3                                    | NR                             | 915               | 0                                    | NR                             |
| 400               | 4                                    | NR                             | 530               | 381                                  | NR                             | 660               | 132                                  | NR                             | 790               | 2                                    | NR                             | 920               | 0                                    | NR                             |
| 405               | 5                                    | NR                             | 535               | 383                                  | NR                             | 665               | 111                                  | NR                             | 795               | 2                                    | NR                             | 925               | 0                                    | NR                             |
| 410               | 7                                    | NR                             | 540               | 385                                  | NR                             | 670               | 102                                  | NR                             | 800               | 2                                    | NR                             | 930               | 0                                    | NR                             |
| 415               | 10                                   | NR                             | 545               | 389                                  | NR                             | 675               | 84                                   | NR                             | 805               | 1                                    | NR                             | 935               | 0                                    | NR                             |
| 420               | 17                                   | NR                             | 550               | 391                                  | NR                             | 680               | 72                                   | NR                             | 810               | 1                                    | NR                             | 940               | 0                                    | NR                             |
| 425               | 29                                   | NR                             | 555               | 392                                  | NR                             | 685               | 62                                   | NR                             | 815               | 1                                    | NR                             | 945               | 0                                    | NR                             |
| 430               | 53                                   | NR                             | 560               | 393                                  | NR                             | 690               | 53                                   | NR                             | 820               | 1                                    | NR                             | 950               | 0                                    | NR                             |
| 435               | 97                                   | NR                             | 565               | 394                                  | NR                             | 695               | 45                                   | NR                             | 825               | 1                                    | NR                             | 955               | 0                                    | NR                             |
| 440               | 173                                  | NR                             | 570               | 391                                  | NR                             | 700               | 39                                   | NR                             | 830               | 1                                    | NR                             | 960               | 0                                    | NR                             |
| 445               | 321                                  | NR                             | 575               | 389                                  | NR                             | 705               | 33                                   | NR                             | 835               | 1                                    | NR                             | 965               | 0                                    | NR                             |
| 450               | 597                                  | NR                             | 580               | 385                                  | NR                             | 710               | 28                                   | NR                             | 840               | 1                                    | NR                             | 970               | 0                                    | NR                             |
| 455               | 795                                  | NR                             | 585               | 382                                  | NR                             | 715               | 24                                   | NR                             | 845               | 1                                    | NR                             | 975               | 0                                    | NR                             |
| 460               | 615                                  | NR                             | 590               | 375                                  | NR                             | 720               | 21                                   | NR                             | 850               | 0                                    | NR                             | 980               | 0                                    | NR                             |
| 465               | 438                                  | NR                             | 595               | 367                                  | NR                             | 725               | 17                                   | NR                             | 855               | 0                                    | NR                             | 985               | 0                                    | NR                             |
| 470               | 372                                  | NR                             | 600               | 361                                  | NR                             | 730               | 15                                   | NR                             | 860               | 0                                    | NR                             | 990               | 0                                    | NR                             |
| 475               | 290                                  | NR                             | 605               | 355                                  | NR                             | 735               | 13                                   | NR                             | 865               | 0                                    | NR                             | 995               | 0                                    | NR                             |
| 480               | 236                                  | NR                             | 610               | 383                                  | NR                             | 740               | 11                                   | NR                             | 870               | 0                                    | NR                             | 1000              | 0                                    | NR                             |
| 485               | 232                                  | NR                             | 615               | 408                                  | NR                             | 745               | 9                                    | NR                             | 875               | 0                                    | NR                             |                   |                                      |                                |

REPORT NUMBER: SP3-2508-516-8

### Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 4.62

| λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) |
|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|
| 360       | 0                           | NR               | 490       | 249                         | NR               | 620       | 343                         | NR               | 750       | 8                           | NR               | 880       | 0                           | NR               |
| 365       | 0                           | NR               | 495       | 269                         | NR               | 625       | 339                         | NR               | 755       | 7                           | NR               | 885       | 0                           | NR               |
| 370       | 0                           | NR               | 500       | 296                         | NR               | 630       | 1000                        | NR               | 760       | 6                           | NR               | 890       | 0                           | NR               |
| 375       | 0                           | NR               | 505       | 325                         | NR               | 635       | 705                         | NR               | 765       | 5                           | NR               | 895       | 0                           | NR               |
| 380       | 0                           | NR               | 510       | 347                         | NR               | 640       | 221                         | NR               | 770       | 4                           | NR               | 900       | 0                           | NR               |
| 385       | 0                           | NR               | 515       | 363                         | NR               | 645       | 210                         | NR               | 775       | 4                           | NR               | 905       | 0                           | NR               |
| 390       | 1                           | NR               | 520       | 371                         | NR               | 650       | 186                         | NR               | 780       | 3                           | NR               | 910       | 0                           | NR               |
| 395       | 3                           | NR               | 525       | 378                         | NR               | 655       | 155                         | NR               | 785       | 3                           | NR               | 915       | 0                           | NR               |
| 400       | 4                           | NR               | 530       | 381                         | NR               | 660       | 132                         | NR               | 790       | 2                           | NR               | 920       | 0                           | NR               |
| 405       | 5                           | NR               | 535       | 383                         | NR               | 665       | 111                         | NR               | 795       | 2                           | NR               | 925       | 0                           | NR               |
| 410       | 7                           | NR               | 540       | 385                         | NR               | 670       | 102                         | NR               | 800       | 2                           | NR               | 930       | 0                           | NR               |
| 415       | 10                          | NR               | 545       | 389                         | NR               | 675       | 84                          | NR               | 805       | 1                           | NR               | 935       | 0                           | NR               |
| 420       | 17                          | NR               | 550       | 391                         | NR               | 680       | 72                          | NR               | 810       | 1                           | NR               | 940       | 0                           | NR               |
| 425       | 29                          | NR               | 555       | 392                         | NR               | 685       | 62                          | NR               | 815       | 1                           | NR               | 945       | 0                           | NR               |
| 430       | 53                          | NR               | 560       | 393                         | NR               | 690       | 53                          | NR               | 820       | 1                           | NR               | 950       | 0                           | NR               |
| 435       | 97                          | NR               | 565       | 394                         | NR               | 695       | 45                          | NR               | 825       | 1                           | NR               | 955       | 0                           | NR               |
| 440       | 173                         | NR               | 570       | 391                         | NR               | 700       | 39                          | NR               | 830       | 1                           | NR               | 960       | 0                           | NR               |
| 445       | 321                         | NR               | 575       | 389                         | NR               | 705       | 33                          | NR               | 835       | 1                           | NR               | 965       | 0                           | NR               |
| 450       | 597                         | NR               | 580       | 385                         | NR               | 710       | 28                          | NR               | 840       | 1                           | NR               | 970       | 0                           | NR               |
| 455       | 795                         | NR               | 585       | 382                         | NR               | 715       | 24                          | NR               | 845       | 1                           | NR               | 975       | 0                           | NR               |
| 460       | 615                         | NR               | 590       | 375                         | NR               | 720       | 21                          | NR               | 850       | 0                           | NR               | 980       | 0                           | NR               |
| 465       | 438                         | NR               | 595       | 367                         | NR               | 725       | 17                          | NR               | 855       | 0                           | NR               | 985       | 0                           | NR               |
| 470       | 372                         | NR               | 600       | 361                         | NR               | 730       | 15                          | NR               | 860       | 0                           | NR               | 990       | 0                           | NR               |
| 475       | 290                         | NR               | 605       | 355                         | NR               | 735       | 13                          | NR               | 865       | 0                           | NR               | 995       | 0                           | NR               |
| 480       | 236                         | NR               | 610       | 383                         | NR               | 740       | 11                          | NR               | 870       | 0                           | NR               | 1000      | 0                           | NR               |
| 485       | 232                         | NR               | 615       | 408                         | NR               | 745       | 9                           | NR               | 875       | 0                           | NR               |           |                             |                  |

REPORT NUMBER: SP3-2508-516-8


TM-30-18

### Summary

$R_f = 89.8$   
 $R_g = 98.5$   
 $CIE R_a = 94.6$   
 $R_9 = 74.6$



### Color Vector Graphics



**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |             |            |            |
|------------|-------------|------------|------------|
| CES01 = 85 | CES26 = 96  | CES51 = 93 | CES76 = 88 |
| CES02 = 61 | CES27 = 88  | CES52 = 97 | CES77 = 87 |
| CES03 = 31 | CES28 = 96  | CES53 = 95 | CES78 = 85 |
| CES04 = 69 | CES29 = 93  | CES54 = 89 | CES79 = 93 |
| CES05 = 48 | CES30 = 81  | CES55 = 86 | CES80 = 93 |
| CES06 = 50 | CES31 = 95  | CES56 = 90 | CES81 = 80 |
| CES07 = 41 | CES32 = 93  | CES57 = 87 | CES82 = 96 |
| CES08 = 40 | CES33 = 91  | CES58 = 87 | CES83 = 95 |
| CES09 = 29 | CES34 = 95  | CES59 = 96 | CES84 = 93 |
| CES10 = 73 | CES35 = 96  | CES60 = 89 | CES85 = 81 |
| CES11 = 56 | CES36 = 74  | CES61 = 89 | CES86 = 85 |
| CES12 = 62 | CES37 = 95  | CES62 = 78 | CES87 = 93 |
| CES13 = 42 | CES38 = 76  | CES63 = 89 | CES88 = 96 |
| CES14 = 74 | CES39 = 98  | CES64 = 84 | CES89 = 87 |
| CES15 = 71 | CES40 = 98  | CES65 = 86 | CES90 = 93 |
| CES16 = 47 | CES41 = 92  | CES66 = 81 | CES91 = 68 |
| CES17 = 48 | CES42 = 95  | CES67 = 80 | CES92 = 78 |
| CES18 = 56 | CES43 = 96  | CES68 = 85 | CES93 = 86 |
| CES19 = 70 | CES44 = 99  | CES69 = 85 | CES94 = 79 |
| CES20 = 65 | CES45 = 100 | CES70 = 84 | CES95 = 82 |
| CES21 = 85 | CES46 = 96  | CES71 = 75 | CES96 = 93 |
| CES22 = 77 | CES47 = 91  | CES72 = 92 | CES97 = 96 |
| CES23 = 91 | CES48 = 84  | CES73 = 80 | CES98 = 94 |
| CES24 = 90 | CES49 = 97  | CES74 = 89 | CES99 = 92 |
| CES25 = 70 | CES50 = 95  | CES75 = 78 |            |



Color Rendition by Hue-Angle Bin



**Measure Comparisons**



(END OF REPORT)