

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: METALUX

Report Number: P1589873

Luminaire Tested: 24CZSP-SB-57HE-L830

Issue Date: 9/3/2026

Test Information

Test Method: LM-79-2019
Report Number: P1589873
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2608-884-7)
Test Lab: INNOVATION CENTER
Issue Date: 9/3/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: METALUX
Catalog Number: 24CZSP-SB-57HE-L830
Description: 2x4 CZSP LED Luminaire, 3000K CCT and 5500 lumens, 80CRI, Ribbed Lens, SB housing
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5587.0 lumens
Efficiency: N/A
Efficacy: 141.8 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.26 / 1.38
Luminous Opening: Rectangular (W 1.83' x L: 3.83' x H: 0')
CIE Type: Direct

Input Watts (W): 39.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

TEST NUMBER: P1589873

CATALOG NUMBER: 24CZSP-SB-57HE-L830

Luminous Intensity Polar Plot



TEST NUMBER: P1589873

CATALOG NUMBER: 24CZSP-SB-57HE-L830

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	108	103	99	95	106	101	97	93	97	93	90		93	90	88		89	87	85	83
2	98	90	83	77	96	88	81	76	84	79	74		81	76	72		78	74	71	68
3	89	79	70	63	87	77	69	63	74	67	62		71	65	61		69	64	60	57
4	82	69	60	54	79	68	60	53	66	58	52		63	57	52		61	56	51	49
5	75	62	53	46	73	61	52	46	59	51	45		57	50	45		55	49	44	42
6	69	56	47	40	67	55	46	40	53	45	40		51	44	39		50	44	39	37
7	64	50	42	35	62	50	41	35	48	40	35		47	40	35		45	39	34	32
8	60	46	37	32	58	45	37	31	44	37	31		43	36	31		42	35	31	29
9	56	42	34	28	54	42	34	28	40	33	28		39	33	28		38	32	28	26
10	52	39	31	26	51	38	31	26	37	30	25		37	30	25		36	30	25	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2932	2932	2932
5°	2922	2938	2931
10°	2911	2931	2920
15°	2889	2919	2923
20°	2864	2899	2908
25°	2818	2868	2888
30°	2773	2844	2876
35°	2728	2817	2865
40°	2683	2792	2858
45°	2633	2766	2856
50°	2575	2736	2849
55°	2516	2706	2848
60°	2423	2666	2865
65°	2310	2614	2867
70°	2155	2542	2875
75°	1917	2449	2925
80°	1575	2347	3035
85°	1039	2202	2743

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 82.5°

Luminance: 3108 cd/sqm

TEST NUMBER: P1589873

CATALOG NUMBER: 24CZSP-SB-57HE-L830

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	181.1	3.2
10°-20°	518.4	9.3
20°-30°	781.3	14.0
30°-40°	940.9	16.8
40°-50°	983.0	17.6
50°-60°	903.1	16.2
60°-70°	711.1	12.7
70°-80°	436.0	7.8
80°-90°	132.2	2.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1480.7	26.5
0°-40°	2421.6	43.3
0°-60°	4307.7	77.1
0°-90°	5587.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5587.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1914	1914	1914	1914	1914	
5°	1900	1904	1911	1908	1906	180
15°	1822	1829	1841	1848	1844	514
25°	1667	1678	1697	1715	1709	769
35°	1459	1478	1506	1534	1532	913
45°	1216	1242	1277	1313	1318	938
55°	942	970	1013	1057	1067	841
65°	637	670	721	770	791	630
75°	324	362	414	464	494	344
85°	59	88	125	140	156	76
90°	0	0	0	0	0	

TEST NUMBER: P1589873

CATALOG NUMBER: 24CZSP-SB-57HE-L830

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1914.4	1914.4	1914.4	1914.4	1914.4
2.5°	1907.3	1912.1	1918.0	1908.5	1903.8
5°	1900.3	1903.8	1910.9	1908.5	1906.2
7.5°	1887.2	1889.6	1899.1	1899.1	1896.7
10°	1871.9	1876.6	1884.9	1883.7	1877.8
12.5°	1851.8	1855.3	1864.8	1864.8	1861.2
15°	1822.2	1829.3	1841.1	1848.2	1843.5
17.5°	1791.5	1798.6	1813.9	1821.0	1818.7
20°	1757.2	1763.1	1778.5	1789.1	1784.4
22.5°	1714.6	1721.7	1739.4	1751.3	1746.5
25°	1667.3	1677.9	1696.9	1714.6	1708.7
27.5°	1620.0	1631.8	1655.5	1673.2	1670.8
30°	1568.0	1583.3	1608.2	1630.6	1625.9
32.5°	1514.8	1532.5	1558.5	1582.2	1581.0
35°	1459.2	1478.1	1506.5	1533.7	1532.5
37.5°	1400.1	1422.5	1452.1	1481.7	1482.8
40°	1342.1	1363.4	1396.5	1428.4	1429.6
42.5°	1280.6	1303.1	1338.6	1371.7	1372.9
45°	1215.6	1241.6	1277.1	1312.6	1318.5
47.5°	1149.4	1176.6	1213.2	1251.1	1258.2
50°	1080.8	1109.2	1148.2	1188.4	1195.5
52.5°	1011.0	1040.6	1080.8	1121.0	1131.6
55°	942.4	969.6	1013.4	1057.1	1066.6
57.5°	870.3	895.1	942.4	988.6	1000.4
60°	791.1	821.8	870.3	916.4	935.3
62.5°	714.2	747.3	797.0	843.1	864.4
65°	637.4	670.5	721.3	769.8	791.1
67.5°	559.3	593.6	648.0	694.1	717.8
70°	481.3	515.6	567.6	617.3	642.1
72.5°	403.2	439.9	490.7	541.6	566.4
75°	324.0	361.8	413.9	463.5	494.3
77.5°	249.5	286.2	338.2	389.0	415.1
80°	178.6	215.2	266.1	316.9	344.1
82.5°	113.5	147.8	197.5	240.0	264.9
85°	59.1	87.5	125.3	139.5	156.1
87.5°	17.7	34.3	48.5	54.4	67.4
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1589873

CATALOG NUMBER: 24CZSP-SB-57HE-L830

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room Dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.3	16.9	15.6	17.2	17.5	16.0	17.7	16.4	18.0	18.3
	3H	17.0	18.5	17.4	18.8	19.2	18.1	19.6	18.5	19.9	20.3
	4H	17.6	19.1	18.0	19.4	19.8	19.0	20.4	19.4	20.7	21.1
	6H	18.1	19.4	18.5	19.7	20.1	19.7	21.1	20.2	21.4	21.8
	8H	18.2	19.4	18.6	19.8	20.2	20.1	21.3	20.5	21.7	22.1
	12H	18.2	19.4	18.6	19.8	20.2	20.3	21.5	20.7	21.9	22.3
4H	2H	16.0	17.4	16.4	17.8	18.2	16.6	18.0	17.0	18.4	18.7
	3H	18.0	19.2	18.4	19.6	20.0	18.9	20.1	19.3	20.5	20.9
	4H	18.8	19.9	19.2	20.3	20.7	20.0	21.1	20.4	21.5	21.9
	6H	19.3	20.3	19.8	20.7	21.2	20.9	21.8	21.3	22.3	22.7
	8H	19.5	20.3	19.9	20.8	21.3	21.3	22.2	21.7	22.6	23.1
	12H	19.5	20.3	20.0	20.8	21.3	21.6	22.4	22.0	22.8	23.3
8H	4H	19.2	20.1	19.7	20.6	21.0	20.3	21.2	20.7	21.6	22.1
	6H	19.9	20.6	20.4	21.1	21.6	21.3	22.1	21.8	22.6	23.1
	8H	20.1	20.8	20.6	21.3	21.8	21.8	22.5	22.3	23.0	23.5
	12H	20.3	20.9	20.8	21.3	21.9	22.2	22.8	22.7	23.3	23.9
12H	4H	19.3	20.1	19.8	20.6	21.1	20.3	21.1	20.8	21.6	22.0
	6H	20.0	20.7	20.6	21.2	21.7	21.4	22.1	21.9	22.5	23.1
	8H	20.3	20.9	20.8	21.4	22.0	22.0	22.5	22.5	23.0	23.6

(END OF REPORT)