

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: METALUX

Report Number: P1588700

Luminaire Tested: 24CZSP-A-52HE-L850-S

Issue Date: 9/3/2026

Test Information

Test Method: LM-79-2019
Report Number: P1588700
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2608-884-6)
Test Lab: INNOVATION CENTER
Issue Date: 9/3/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: METALUX
Catalog Number: 24CZSP-A-52HE-L850-S
Description: 2x4 CZSP LED Luminaire, 5000K CCT and 5000 lumens, 80CRI, Smooth Lens, Air Vented Housing
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5308.0 lumens
Efficiency: N/A
Efficacy: 144.6 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.27 / 1.37
Luminous Opening: Rectangular (W 1.83' x L: 3.83' x H: 0')
CIE Type: Direct

Input Watts (W): 36.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1588700

CATALOG NUMBER: 24CZSP-A-52HE-L850-S

Luminous Intensity Polar Plot



TEST NUMBER: P1588700

CATALOG NUMBER: 24CZSP-A-52HE-L850-S

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	108	103	99	95	106	101	97	93	97	93	90		93	90	88		89	87	85	83
2	98	90	83	77	96	88	81	76	84	79	74		81	76	72		78	74	71	69
3	89	79	70	64	87	77	69	63	74	67	62		71	65	61		69	64	60	57
4	82	69	60	54	79	68	60	53	66	58	52		63	57	52		61	56	51	49
5	75	62	53	46	73	61	52	46	59	51	45		57	50	45		55	49	44	42
6	69	56	47	40	67	55	46	40	53	45	40		51	44	39		50	44	39	37
7	64	50	42	35	62	50	41	35	48	40	35		47	40	35		45	39	34	32
8	60	46	37	32	58	45	37	31	44	37	31		43	36	31		42	35	31	29
9	56	42	34	28	54	42	34	28	40	33	28		39	33	28		38	32	28	26
10	52	39	31	26	51	38	31	26	37	30	25		37	30	25		36	30	25	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2785	2785	2785
5°	2772	2783	2781
10°	2766	2779	2777
15°	2746	2768	2785
20°	2719	2751	2774
25°	2685	2722	2756
30°	2643	2698	2748
35°	2605	2672	2740
40°	2562	2645	2732
45°	2513	2619	2735
50°	2459	2587	2734
55°	2395	2550	2737
60°	2305	2523	2744
65°	2199	2473	2752
70°	2050	2404	2764
75°	1827	2309	2791
80°	1510	2199	2927
85°	982	1986	2559

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 82.5°

Luminance: 3020 cd/sqm

TEST NUMBER: P1588700

CATALOG NUMBER: 24CZSP-A-52HE-L850-S

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	171.9	3.2
10°-20°	492.4	9.3
20°-30°	742.6	14.0
30°-40°	894.4	16.8
40°-50°	934.1	17.6
50°-60°	857.8	16.2
60°-70°	675.6	12.7
70°-80°	414.5	7.8
80°-90°	124.8	2.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1406.9	26.5
0°-40°	2301.2	43.4
0°-60°	4093.1	77.1
0°-90°	5308.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5308.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1818	1818	1818	1818	1818	
5°	1803	1805	1810	1816	1809	171
15°	1732	1735	1746	1756	1756	488
25°	1589	1592	1611	1631	1631	731
35°	1393	1400	1429	1458	1465	871
45°	1160	1173	1209	1251	1263	894
55°	897	913	955	1009	1025	801
65°	607	628	682	740	759	600
75°	309	333	390	452	472	327
85°	56	77	113	143	146	73
90°	0	0	0	0	0	

TEST NUMBER: P1588700

CATALOG NUMBER: 24CZSP-A-52HE-L850-S

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1818.1	1818.1	1818.1	1818.1	1818.1
2.5°	1811.1	1814.6	1815.8	1817.0	1808.8
5°	1803.0	1805.3	1810.0	1815.8	1808.8
7.5°	1791.3	1793.7	1799.5	1807.6	1804.2
10°	1778.5	1779.7	1786.7	1792.5	1785.5
12.5°	1757.6	1761.1	1769.2	1773.9	1771.5
15°	1731.9	1735.4	1745.9	1756.4	1756.4
17.5°	1701.7	1706.3	1719.1	1733.1	1734.3
20°	1667.9	1671.4	1687.7	1701.7	1701.7
22.5°	1629.4	1634.1	1650.4	1665.6	1667.9
25°	1588.7	1592.2	1610.8	1630.6	1630.6
27.5°	1540.9	1547.9	1571.2	1591.0	1595.7
30°	1494.3	1500.2	1525.8	1550.2	1553.7
32.5°	1445.4	1452.4	1479.2	1506.0	1511.8
35°	1393.0	1400.0	1429.1	1458.2	1465.2
37.5°	1338.3	1346.4	1376.7	1410.5	1417.5
40°	1281.2	1290.5	1323.1	1359.2	1366.2
42.5°	1220.6	1233.4	1268.4	1305.7	1316.1
45°	1160.1	1172.9	1209.0	1250.9	1262.6
47.5°	1096.0	1111.1	1148.4	1192.7	1205.5
50°	1031.9	1047.1	1085.5	1133.3	1147.3
52.5°	966.7	981.9	1021.5	1071.5	1086.7
55°	896.8	913.1	955.1	1008.6	1025.0
57.5°	824.6	845.6	889.8	944.6	960.9
60°	752.4	773.4	823.5	877.0	895.7
62.5°	681.4	701.2	752.4	809.5	829.3
65°	606.8	627.8	682.5	739.6	759.4
67.5°	533.4	554.4	609.1	668.6	689.5
70°	457.7	481.0	536.9	596.3	617.3
72.5°	382.0	406.5	463.6	524.1	543.9
75°	308.7	333.1	390.2	451.9	471.7
77.5°	236.4	263.2	319.1	382.0	400.7
80°	171.2	196.8	249.3	311.0	331.9
82.5°	109.5	131.6	184.0	242.3	257.4
85°	55.9	76.9	113.0	143.3	145.6
87.5°	17.5	24.5	37.3	55.9	57.1
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1588700

CATALOG NUMBER: 24CZSP-A-52HE-L850-S

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.04	16.70	15.40	17.01	17.33	15.87	17.53	16.23	17.84	18.16
	3H	16.79	18.30	17.17	18.63	18.98	17.98	19.49	18.36	19.82	20.18
	4H	17.41	18.83	17.81	19.18	19.55	18.87	20.29	19.27	20.64	21.02
	6H	17.82	19.14	18.23	19.51	19.90	19.65	20.97	20.06	21.34	21.73
	8H	17.93	19.19	18.35	19.58	19.98	19.97	21.24	20.40	21.62	22.02
	12H	17.98	19.19	18.41	19.57	20.00	20.18	21.39	20.61	21.78	22.20
4H	2H	15.81	17.23	16.21	17.58	17.95	16.45	17.88	16.85	18.22	18.60
	3H	17.79	18.98	18.19	19.38	19.78	18.81	20.01	19.22	20.40	20.80
	4H	18.52	19.61	18.95	20.02	20.46	19.86	20.95	20.29	21.36	21.79
	6H	19.05	20.00	19.50	20.44	20.90	20.81	21.77	21.27	22.21	22.66
	8H	19.20	20.09	19.66	20.53	20.99	21.21	22.10	21.67	22.54	23.01
	12H	19.28	20.08	19.76	20.56	21.03	21.49	22.29	21.97	22.77	23.23
8H	4H	18.98	19.87	19.44	20.31	20.78	20.15	21.04	20.61	21.48	21.95
	6H	19.64	20.39	20.13	20.87	21.35	21.26	22.01	21.75	22.49	22.97
	8H	19.85	20.52	20.36	21.03	21.51	21.77	22.44	22.28	22.95	23.43
	12H	19.99	20.58	20.50	21.07	21.63	22.16	22.75	22.67	23.24	23.80
12H	4H	19.07	19.87	19.55	20.35	20.82	20.17	20.98	20.65	21.45	21.92
	6H	19.77	20.44	20.28	20.95	21.43	21.31	21.98	21.82	22.48	22.97
	8H	20.05	20.64	20.56	21.13	21.69	21.89	22.48	22.39	22.97	23.53