

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: METALUX

Report Number: P731804

Luminaire Tested: **14CZ2-20-S-B2750-W2D-4000K**

Issue Date: 1/5/2024



**Test Information**

Test Method: LM-79-08  
Report Number: P731804  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P275670)  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 1/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: METALUX  
Catalog Number: 14CZ2-20-S-B2750-W2D-4000K  
Description: 1X4 2000 LUMEN CRUZE TROFFER WITH BIO UP LEDS AT 4000K CCT AND SMOOTH LENS  
  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1928.0 lumens  
Efficiency: N/A  
Efficacy: 120.5 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.26 / 1.36  
Luminous Opening: Rectangular (W 0.96' x L: 3.98' x H: 0')  
CIE Type: Direct

Input Watts (W): 16  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P731804

CATALOG NUMBER: 14CZ2-20-S-B2750-W2D-4000K

### Luminous Intensity Polar Plot





TEST NUMBER: P731804

CATALOG NUMBER: 14CZ2-20-S-B2750-W2D-4000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	109	104	100	96	106	102	98	94	97	94	91	94	91	89	90	88	86	84																			
2	99	90	84	78	96	89	82	77	85	80	75	82	77	73	79	75	72	70																			
3	90	79	71	65	87	78	70	64	75	68	63	72	66	62	69	65	61	58																			
4	82	70	61	55	80	69	61	54	66	59	53	64	58	53	62	56	52	50																			
5	76	63	54	47	74	62	53	47	59	52	46	57	51	46	56	50	45	43																			
6	70	56	47	41	68	55	47	41	54	46	40	52	45	40	50	44	40	38																			
7	65	51	42	36	63	50	42	36	49	41	36	47	41	35	46	40	35	33																			
8	60	47	38	32	59	46	38	32	45	37	32	43	37	32	42	36	32	30																			
9	56	43	35	29	55	42	34	29	41	34	29	40	33	29	39	33	28	27																			
10	53	40	32	26	52	39	31	26	38	31	26	37	31	26	36	30	26	24																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1943	1943	1943
5°	1945	1929	1942
10°	1929	1924	1940
15°	1902	1908	1933
20°	1872	1889	1927
25°	1834	1867	1920
30°	1788	1844	1910
35°	1739	1818	1904
40°	1684	1796	1899
45°	1621	1774	1897
50°	1562	1754	1901
55°	1496	1741	1896
60°	1425	1716	1883
65°	1341	1711	1884
70°	1263	1697	1830
75°	1095	1658	1564
80°	886	1336	1042
85°	589	463	311



TEST NUMBER: P731804

CATALOG NUMBER: 14CZ2-20-S-B2750-W2D-4000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	65.0	3.4
10°-20°	184.9	9.6
20°-30°	277.4	14.4
30°-40°	330.9	17.2
40°-50°	342.1	17.7
50°-60°	312.4	16.2
60°-70°	245.8	12.7
70°-80°	143.1	7.4
80°-90°	26.4	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	527.4	27.4
0°-40°	858.3	44.5
0°-60°	1512.7	78.5
0°-90°	1928.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1928.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	688	688	688	688	688	
5°	686	684	681	686	685	65
15°	651	652	653	661	661	184
25°	589	592	599	614	617	271
35°	505	511	528	548	552	315
45°	406	420	444	469	475	314
55°	304	320	354	380	385	272
65°	201	222	256	276	282	199
75°	100	124	152	149	143	107
85°	18	26	14	12	10	24
90°	0	0	0	0	0	



TEST NUMBER: P731804

CATALOG NUMBER: 14CZ2-20-S-B2750-W2D-4000K

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	688.3	688.3	688.3	688.3	688.3
2.5°	689.2	687.3	684.4	689.2	688.3
5°	686.4	684.4	680.7	686.4	685.3
7.5°	680.7	678.7	676.8	682.5	681.6
10°	672.9	672.0	671.1	677.7	676.8
12.5°	663.4	663.4	662.5	670.1	670.1
15°	651.0	652.0	652.9	661.4	661.4
17.5°	639.5	638.6	641.4	651.0	652.0
20°	623.3	625.1	629.0	640.5	641.4
22.5°	607.0	609.0	615.6	627.1	629.9
25°	588.8	591.8	599.4	613.7	616.6
27.5°	569.7	573.6	584.0	599.4	602.2
30°	548.6	554.4	565.9	583.1	586.0
32.5°	527.7	533.4	547.7	564.9	568.8
35°	504.7	511.4	527.7	547.7	552.5
37.5°	480.8	489.4	508.6	528.6	534.4
40°	456.9	466.5	487.5	508.6	515.3
42.5°	433.0	442.6	465.5	489.4	496.2
45°	406.2	419.7	444.5	469.3	475.1
47.5°	380.4	394.9	422.5	447.3	455.1
50°	355.6	369.9	399.5	425.4	433.0
52.5°	329.8	345.1	376.6	403.4	410.1
55°	304.0	320.2	353.7	379.5	385.2
57.5°	278.2	295.4	329.8	354.7	361.4
60°	252.4	270.6	304.0	328.8	333.6
62.5°	226.5	245.6	280.1	302.1	306.9
65°	200.8	221.7	256.2	276.3	282.1
67.5°	175.9	196.9	230.4	249.5	254.3
70°	153.0	172.1	205.6	219.9	221.7
72.5°	124.3	148.2	180.6	188.3	183.5
75°	100.4	124.3	152.0	149.1	143.4
77.5°	76.5	100.4	118.5	108.9	101.3
80°	54.5	78.4	82.2	67.8	64.1
82.5°	35.4	54.5	45.9	35.4	28.7
85°	18.2	25.8	14.3	11.5	9.6
87.5°	5.7	3.9	1.9	1.9	0.9
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°    - - 45°-225°    - - - - 90°-270°







(END OF REPORT)