

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: METALUX

Report Number: P276636

Luminaire Tested: **24CZ2-50HE-S-UNV-L92765-W2A1-U-4000K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P276636
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1805-783-1)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: METALUX
Catalog Number: 24CZ2-50HE-S-UNV-L92765-W2A1-U-4000K
Description: CRUZE 2.0 2x4 TUNABLE WHITE LED TROFFER WITH SMOOTH LENS
Light Source: (336) 90 CRI LEDS TUNED TO 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment: Sample No. Condition Description

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4412.3 lumens
Efficiency: N/A
Efficacy: 122.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.26 / 1.35
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 36.084
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P276636

CATALOG NUMBER: 24CZ2-50HE-S-UNV-L92765-W2A1-U-4000K

Luminous Intensity Polar Plot





TEST NUMBER: P276636

CATALOG NUMBER: 24CZ2-50HE-S-UNV-L92765-W2A1-U-4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	106	101	97	93	97	93	90	93	90	88	89	87	85	83
2	98	90	83	77	96	88	81	76	84	79	74	81	76	72	78	74	71	69
3	89	79	70	64	87	77	69	63	74	67	62	71	66	61	69	64	60	58
4	82	70	61	54	80	68	60	54	66	59	53	63	57	52	61	56	51	49
5	75	62	53	46	73	61	53	46	59	51	46	57	50	45	55	49	45	42
6	70	56	47	40	68	55	47	40	53	46	40	52	45	40	50	44	39	37
7	64	51	42	36	63	50	42	36	48	41	35	47	40	35	46	39	35	33
8	60	46	38	32	58	46	37	32	44	37	32	43	36	31	42	36	31	29
9	56	43	34	29	55	42	34	29	41	34	28	40	33	28	39	33	28	26
10	53	39	31	26	51	39	31	26	38	31	26	37	30	26	36	30	26	24

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2086	2086	2086
5°	2084	2078	2092
10°	2076	2076	2091
15°	2056	2065	2087
20°	2029	2049	2081
25°	1991	2029	2068
30°	1947	2005	2051
35°	1904	1973	2035
40°	1839	1940	2011
45°	1779	1901	1989
50°	1710	1866	1966
55°	1634	1831	1946
60°	1558	1803	1942
65°	1459	1771	1954
70°	1351	1781	2007
75°	1210	1814	2120
80°	977	1922	2074
85°	736	1687	1644



TEST NUMBER: P276636

CATALOG NUMBER: 24CZ2-50HE-S-UNV-L92765-W2A1-U-4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	146.7	3.3
10°-20°	419.3	9.5
20°-30°	630.3	14.3
30°-40°	750.8	17.0
40°-50°	768.4	17.4
50°-60°	691.8	15.7
60°-70°	543.3	12.3
70°-80°	352.6	8.0
80°-90°	109.0	2.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1196.4	27.1
0°-40°	1947.2	44.1
0°-60°	3407.4	77.2
0°-90°	4412.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4412.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1550	1550	1550	1550	1550	
5°	1543	1546	1539	1547	1549	147
15°	1476	1480	1483	1495	1498	416
25°	1341	1352	1366	1389	1393	618
35°	1159	1173	1201	1230	1239	723
45°	935	957	999	1037	1046	721
55°	697	727	781	821	830	624
65°	458	493	556	603	614	456
75°	233	278	349	397	408	246
85°	48	88	109	106	106	58
90°	0	0	0	0	0	



TEST NUMBER: P276636

CATALOG NUMBER: 24CZ2-50HE-S-UNV-L92765-W2A1-U-4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1550.1	1550.1	1550.1	1550.1	1550.1
2.5°	1551.5	1551.5	1544.5	1551.5	1552.9
5°	1543.1	1545.9	1538.9	1547.3	1548.7
7.5°	1534.7	1534.7	1530.5	1538.9	1540.3
10°	1519.3	1520.7	1519.3	1529.1	1530.5
12.5°	1499.6	1502.4	1503.8	1513.6	1515.0
15°	1475.8	1480.0	1482.8	1495.4	1498.2
17.5°	1449.2	1453.4	1460.4	1474.4	1477.2
20°	1416.9	1422.5	1431.0	1449.2	1453.4
22.5°	1381.9	1387.5	1401.5	1418.3	1425.3
25°	1341.3	1352.5	1366.5	1388.9	1393.1
27.5°	1300.6	1310.4	1328.6	1352.5	1358.1
30°	1253.0	1268.4	1290.8	1314.6	1320.2
32.5°	1206.7	1222.1	1248.8	1274.0	1281.0
35°	1159.1	1173.1	1201.1	1230.5	1238.9
37.5°	1104.4	1122.6	1153.5	1182.9	1191.3
40°	1046.9	1069.4	1104.4	1135.2	1145.0
42.5°	992.3	1016.1	1051.1	1084.8	1096.0
45°	934.8	957.2	999.3	1037.1	1045.5
47.5°	876.0	901.2	946.0	983.9	997.9
50°	817.1	843.7	891.4	930.6	939.0
52.5°	758.2	786.3	836.7	878.8	883.0
55°	696.6	727.4	780.6	821.3	829.7
57.5°	640.5	667.1	724.6	766.6	776.4
60°	578.8	608.3	669.9	709.2	721.8
62.5°	520.0	550.8	615.3	654.5	665.7
65°	458.3	493.3	556.4	602.7	613.9
67.5°	405.0	438.7	505.9	550.8	562.0
70°	343.4	381.2	452.7	498.9	510.2
72.5°	290.1	329.4	400.8	445.7	462.5
75°	232.7	277.5	349.0	396.6	407.8
77.5°	176.6	228.4	301.3	337.8	337.8
80°	126.1	180.8	248.1	264.9	267.7
82.5°	82.7	135.9	183.6	182.2	182.2
85°	47.7	88.3	109.3	106.5	106.5
87.5°	18.2	36.4	39.2	39.2	37.8
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)