

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: METALUX

Report Number: P975435

Luminaire Tested: 24EN-LD2-58-UNV-L940-CD1

Issue Date: 03/13/2025

**Test Information**

Test Method: LM-79-2019  
Report Number: P975435  
Test Lab: INNOVATION CENTER(P3)  
Issue Date: 03/13/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: METALUX  
Catalog Number: 24EN-LD2-58-UNV-L940-CD1  
Description: METALUX ENCOUNTER 2x4 5800LM PACKAGE 90CRI 4000K STANDARD TROFFER  
Light Source: 4000K CCT, 90 CRI LEDS  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5930.8 lumens  
Efficiency: N/A  
Efficacy: 126.2 lumens/watt  
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.4  
Luminous Opening: Rectangular (W 1.83' x L: 3.83' x H: 0')  
CIE Type: Direct

Input Watts (W): 47  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT

TEST NUMBER: P975435

CATALOG NUMBER: 24EN-LD2-58-UNV-L940-CD1

### Luminous Intensity Polar Plot



TEST NUMBER: P975435

CATALOG NUMBER: 24EN-LD2-58-UNV-L940-CD1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 109 | 104 | 99  | 95  | 106 | 101 | 97  | 94  | 97  | 94  | 91  |  | 93  | 90  | 88  |  | 90  |
| 2   | 98  | 90  | 83  | 77  | 96  | 88  | 82  | 76  | 84  | 79  | 74  |  | 81  | 77  | 73  |  | 78  |
| 3   | 90  | 79  | 70  | 64  | 87  | 77  | 69  | 63  | 74  | 67  | 62  |  | 71  | 66  | 61  |  | 69  |
| 4   | 82  | 70  | 61  | 54  | 79  | 68  | 60  | 53  | 66  | 58  | 53  |  | 63  | 57  | 52  |  | 61  |
| 5   | 75  | 62  | 53  | 46  | 73  | 61  | 52  | 46  | 59  | 51  | 45  |  | 57  | 50  | 45  |  | 55  |
| 6   | 69  | 56  | 47  | 40  | 67  | 55  | 46  | 40  | 53  | 45  | 40  |  | 51  | 44  | 39  |  | 50  |
| 7   | 64  | 50  | 42  | 35  | 62  | 50  | 41  | 35  | 48  | 40  | 35  |  | 47  | 40  | 35  |  | 45  |
| 8   | 60  | 46  | 37  | 31  | 58  | 45  | 37  | 31  | 44  | 36  | 31  |  | 43  | 36  | 31  |  | 41  |
| 9   | 56  | 42  | 34  | 28  | 54  | 42  | 34  | 28  | 40  | 33  | 28  |  | 39  | 33  | 28  |  | 38  |
| 10  | 52  | 39  | 31  | 26  | 51  | 38  | 31  | 25  | 37  | 30  | 25  |  | 36  | 30  | 25  |  | 35  |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°   | 45°  | 90°  |
|-----|------|------|------|
| 0°  | 3027 | 3027 | 3027 |
| 5°  | 3039 | 3024 | 3031 |
| 10° | 3037 | 3022 | 3030 |
| 15° | 3034 | 3020 | 3028 |
| 20° | 3034 | 3020 | 3030 |
| 25° | 3031 | 3016 | 3031 |
| 30° | 3027 | 3009 | 3027 |
| 35° | 3024 | 3003 | 3019 |
| 40° | 3025 | 2993 | 3011 |
| 45° | 3017 | 2974 | 2996 |
| 50° | 3009 | 2956 | 2982 |
| 55° | 2998 | 2925 | 2955 |
| 60° | 2961 | 2870 | 2931 |
| 65° | 2902 | 2780 | 2883 |
| 70° | 2797 | 2681 | 2674 |
| 75° | 2632 | 2516 | 2126 |
| 80° | 2317 | 1968 | 2023 |
| 85° | 1828 | 1722 | 1592 |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
Vertical Angle: 45°  
Luminance: 3017 cd/sqm

TEST NUMBER: P975435

CATALOG NUMBER: 24EN-LD2-58-UNV-L940-CD1

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 187.2  | 3.2       |
| 10°-20°   | 538.4  | 9.1       |
| 20°-30°   | 823.9  | 13.9      |
| 30°-40°   | 1007.0 | 17.0      |
| 40°-50°   | 1064.1 | 17.9      |
| 50°-60°   | 986.0  | 16.6      |
| 60°-70°   | 772.4  | 13.0      |
| 70°-80°   | 436.7  | 7.4       |
| 80°-90°   | 115.0  | 1.9       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1549.5 | 26.1      |
| 0°-40°    | 2556.5 | 43.1      |
| 0°-60°    | 4606.6 | 77.7      |
| 0°-90°    | 5930.8 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 5930.8 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | 22.5° | 45°  | 67.5° | 90°  | Flux |
|-----|------|-------|------|-------|------|------|
| 0°  | 1976 | 1976  | 1976 | 1976  | 1976 |      |
| 5°  | 1976 | 1970  | 1966 | 1965  | 1972 | 188  |
| 15° | 1913 | 1906  | 1905 | 1903  | 1910 | 541  |
| 25° | 1793 | 1786  | 1784 | 1784  | 1793 | 827  |
| 35° | 1617 | 1610  | 1606 | 1606  | 1615 | 1012 |
| 45° | 1393 | 1383  | 1373 | 1373  | 1383 | 1075 |
| 55° | 1123 | 1110  | 1095 | 1098  | 1107 | 1003 |
| 65° | 801  | 786   | 767  | 777   | 796  | 792  |
| 75° | 445  | 432   | 425  | 379   | 359  | 468  |
| 85° | 104  | 98    | 98   | 93    | 91   | 123  |
| 90° | 0    | 0     | 0    | 0     | 0    |      |

TEST NUMBER: P975435

CATALOG NUMBER: 24EN-LD2-58-UNV-L940-CD1

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 22.5°  | 45°    | 67.5°  | 90°    |
|-------|--------|--------|--------|--------|--------|
| 0°    | 1976.4 | 1976.4 | 1976.4 | 1976.4 | 1976.4 |
| 2.5°  | 1983.8 | 1975.2 | 1972.7 | 1970.4 | 1976.4 |
| 5°    | 1976.4 | 1970.4 | 1966.5 | 1965.3 | 1971.5 |
| 7.5°  | 1967.8 | 1960.4 | 1957.9 | 1955.3 | 1961.6 |
| 10°   | 1953.0 | 1945.6 | 1943.0 | 1941.7 | 1947.9 |
| 12.5° | 1935.6 | 1926.8 | 1925.7 | 1924.5 | 1930.6 |
| 15°   | 1913.2 | 1905.8 | 1904.6 | 1903.4 | 1909.5 |
| 17.5° | 1889.8 | 1882.3 | 1879.8 | 1878.6 | 1887.2 |
| 20°   | 1861.3 | 1853.9 | 1852.5 | 1851.3 | 1858.7 |
| 22.5° | 1829.1 | 1821.7 | 1819.1 | 1820.3 | 1827.7 |
| 25°   | 1793.2 | 1785.5 | 1784.4 | 1784.4 | 1793.2 |
| 27.5° | 1753.3 | 1745.9 | 1745.9 | 1745.9 | 1755.9 |
| 30°   | 1711.4 | 1705.1 | 1701.4 | 1702.6 | 1711.4 |
| 32.5° | 1667.9 | 1657.9 | 1655.6 | 1656.7 | 1665.5 |
| 35°   | 1617.1 | 1609.7 | 1606.0 | 1606.0 | 1614.6 |
| 37.5° | 1565.0 | 1557.6 | 1552.7 | 1552.7 | 1561.3 |
| 40°   | 1513.1 | 1501.8 | 1496.9 | 1494.4 | 1505.7 |
| 42.5° | 1454.7 | 1446.2 | 1435.0 | 1435.0 | 1444.8 |
| 45°   | 1392.9 | 1382.9 | 1373.0 | 1373.0 | 1382.9 |
| 47.5° | 1329.6 | 1319.7 | 1308.6 | 1308.6 | 1318.5 |
| 50°   | 1262.7 | 1252.8 | 1240.5 | 1240.5 | 1251.6 |
| 52.5° | 1194.6 | 1183.5 | 1169.8 | 1168.4 | 1179.8 |
| 55°   | 1122.8 | 1110.3 | 1095.4 | 1098.0 | 1106.6 |
| 57.5° | 1049.6 | 1033.4 | 1018.6 | 1018.6 | 1032.2 |
| 60°   | 966.6  | 953.0  | 936.8  | 939.3  | 956.7  |
| 62.5° | 887.2  | 869.8  | 853.8  | 859.9  | 874.9  |
| 65°   | 800.6  | 785.7  | 767.0  | 776.9  | 795.5  |
| 67.5° | 715.1  | 698.9  | 684.0  | 696.3  | 705.1  |
| 70°   | 624.5  | 609.7  | 598.6  | 598.6  | 597.2  |
| 72.5° | 534.2  | 520.5  | 518.0  | 494.3  | 479.5  |
| 75°   | 444.8  | 432.5  | 425.1  | 379.2  | 359.3  |
| 77.5° | 351.9  | 348.2  | 324.8  | 276.4  | 270.1  |
| 80°   | 262.7  | 265.2  | 223.1  | 224.2  | 229.3  |
| 82.5° | 180.9  | 177.2  | 167.3  | 159.8  | 157.3  |
| 85°   | 104.0  | 98.0   | 98.0   | 92.9   | 90.6   |
| 87.5° | 34.7   | 38.4   | 38.4   | 38.4   | 39.6   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2506-457-3

Test Date: 07/15/2025

Luminaire Tested: 14EN-LD2-51-UNV-L940-CD1-U

Data in this report applies to families of products including 14EN-LD2-51-UNV-L940-CD1-U



REPORT NUMBER: SP1-2506-457-3

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | 76INCH SPHERE IN0058  | 6/16/2025        | 12/16/2025           |
| Power Meter                    | XITRON INXT2011004    | 1/21/2025        | 1/21/2026            |
| AC Power Source                | CHROMA 61603 IN0063   | 10/22/2024       | 10/22/2025           |
| DC Power Source                | AGILENT E3634A IN0208 | 10/22/2024       | 10/22/2025           |
| Sphere Thermometer             | ONSET IN0085          | 10/22/2024       | 10/22/2025           |
| Room Thermometer               | ONSET IN0046          | 10/22/2024       | 10/22/2025           |

REPORT NUMBER: SP1-2506-457-3

**CIE 1931 Chromaticity Diagram**



**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2506-457-3

### Photopic Flux vs. Wavelength



### Photopic Lumens: NR

| $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 0                                    | NR                             | 490               | 168                                  | NR                             | 620               | 331                                  | NR                             | 750               | 8                                    | NR                             | 880               | 0                                    | NR                             |
| 365               | 0                                    | NR                             | 495               | 199                                  | NR                             | 625               | 331                                  | NR                             | 755               | 6                                    | NR                             | 885               | 0                                    | NR                             |
| 370               | 0                                    | NR                             | 500               | 227                                  | NR                             | 630               | 1000                                 | NR                             | 760               | 6                                    | NR                             | 890               | 0                                    | NR                             |
| 375               | 0                                    | NR                             | 505               | 248                                  | NR                             | 635               | 646                                  | NR                             | 765               | 5                                    | NR                             | 895               | 0                                    | NR                             |
| 380               | 0                                    | NR                             | 510               | 263                                  | NR                             | 640               | 219                                  | NR                             | 770               | 4                                    | NR                             | 900               | 0                                    | NR                             |
| 385               | 0                                    | NR                             | 515               | 272                                  | NR                             | 645               | 210                                  | NR                             | 775               | 3                                    | NR                             | 905               | 0                                    | NR                             |
| 390               | 1                                    | NR                             | 520               | 277                                  | NR                             | 650               | 183                                  | NR                             | 780               | 3                                    | NR                             | 910               | 0                                    | NR                             |
| 395               | 2                                    | NR                             | 525               | 283                                  | NR                             | 655               | 155                                  | NR                             | 785               | 3                                    | NR                             | 915               | 0                                    | NR                             |
| 400               | 3                                    | NR                             | 530               | 288                                  | NR                             | 660               | 132                                  | NR                             | 790               | 2                                    | NR                             | 920               | 0                                    | NR                             |
| 405               | 5                                    | NR                             | 535               | 294                                  | NR                             | 665               | 111                                  | NR                             | 795               | 2                                    | NR                             | 925               | 0                                    | NR                             |
| 410               | 7                                    | NR                             | 540               | 301                                  | NR                             | 670               | 102                                  | NR                             | 800               | 2                                    | NR                             | 930               | 0                                    | NR                             |
| 415               | 11                                   | NR                             | 545               | 308                                  | NR                             | 675               | 84                                   | NR                             | 805               | 1                                    | NR                             | 935               | 0                                    | NR                             |
| 420               | 19                                   | NR                             | 550               | 315                                  | NR                             | 680               | 72                                   | NR                             | 810               | 1                                    | NR                             | 940               | 0                                    | NR                             |
| 425               | 34                                   | NR                             | 555               | 322                                  | NR                             | 685               | 61                                   | NR                             | 815               | 1                                    | NR                             | 945               | 0                                    | NR                             |
| 430               | 57                                   | NR                             | 560               | 327                                  | NR                             | 690               | 53                                   | NR                             | 820               | 1                                    | NR                             | 950               | 0                                    | NR                             |
| 435               | 97                                   | NR                             | 565               | 331                                  | NR                             | 695               | 45                                   | NR                             | 825               | 1                                    | NR                             | 955               | 0                                    | NR                             |
| 440               | 163                                  | NR                             | 570               | 334                                  | NR                             | 700               | 39                                   | NR                             | 830               | 1                                    | NR                             | 960               | 0                                    | NR                             |
| 445               | 293                                  | NR                             | 575               | 337                                  | NR                             | 705               | 33                                   | NR                             | 835               | 1                                    | NR                             | 965               | 0                                    | NR                             |
| 450               | 428                                  | NR                             | 580               | 339                                  | NR                             | 710               | 28                                   | NR                             | 840               | 1                                    | NR                             | 970               | 0                                    | NR                             |
| 455               | 351                                  | NR                             | 585               | 341                                  | NR                             | 715               | 23                                   | NR                             | 845               | 0                                    | NR                             | 975               | 0                                    | NR                             |
| 460               | 229                                  | NR                             | 590               | 342                                  | NR                             | 720               | 19                                   | NR                             | 850               | 0                                    | NR                             | 980               | 0                                    | NR                             |
| 465               | 192                                  | NR                             | 595               | 339                                  | NR                             | 725               | 16                                   | NR                             | 855               | 0                                    | NR                             | 985               | 0                                    | NR                             |
| 470               | 152                                  | NR                             | 600               | 338                                  | NR                             | 730               | 13                                   | NR                             | 860               | 0                                    | NR                             | 990               | 0                                    | NR                             |
| 475               | 122                                  | NR                             | 605               | 337                                  | NR                             | 735               | 11                                   | NR                             | 865               | 0                                    | NR                             | 995               | 0                                    | NR                             |
| 480               | 125                                  | NR                             | 610               | 361                                  | NR                             | 740               | 10                                   | NR                             | 870               | 0                                    | NR                             | 1000              | 0                                    | NR                             |
| 485               | 144                                  | NR                             | 615               | 378                                  | NR                             | 745               | 9                                    | NR                             | 875               | 0                                    | NR                             |                   |                                      |                                |

REPORT NUMBER: SP1-2506-457-3

### Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.74

| λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360    | 0                        | NR            | 490    | 168                      | NR            | 620    | 331                      | NR            | 750    | 8                        | NR            | 880    | 0                        | NR            |
| 365    | 0                        | NR            | 495    | 199                      | NR            | 625    | 331                      | NR            | 755    | 6                        | NR            | 885    | 0                        | NR            |
| 370    | 0                        | NR            | 500    | 227                      | NR            | 630    | 1000                     | NR            | 760    | 6                        | NR            | 890    | 0                        | NR            |
| 375    | 0                        | NR            | 505    | 248                      | NR            | 635    | 646                      | NR            | 765    | 5                        | NR            | 895    | 0                        | NR            |
| 380    | 0                        | NR            | 510    | 263                      | NR            | 640    | 219                      | NR            | 770    | 4                        | NR            | 900    | 0                        | NR            |
| 385    | 0                        | NR            | 515    | 272                      | NR            | 645    | 210                      | NR            | 775    | 3                        | NR            | 905    | 0                        | NR            |
| 390    | 1                        | NR            | 520    | 277                      | NR            | 650    | 183                      | NR            | 780    | 3                        | NR            | 910    | 0                        | NR            |
| 395    | 2                        | NR            | 525    | 283                      | NR            | 655    | 155                      | NR            | 785    | 3                        | NR            | 915    | 0                        | NR            |
| 400    | 3                        | NR            | 530    | 288                      | NR            | 660    | 132                      | NR            | 790    | 2                        | NR            | 920    | 0                        | NR            |
| 405    | 5                        | NR            | 535    | 294                      | NR            | 665    | 111                      | NR            | 795    | 2                        | NR            | 925    | 0                        | NR            |
| 410    | 7                        | NR            | 540    | 301                      | NR            | 670    | 102                      | NR            | 800    | 2                        | NR            | 930    | 0                        | NR            |
| 415    | 11                       | NR            | 545    | 308                      | NR            | 675    | 84                       | NR            | 805    | 1                        | NR            | 935    | 0                        | NR            |
| 420    | 19                       | NR            | 550    | 315                      | NR            | 680    | 72                       | NR            | 810    | 1                        | NR            | 940    | 0                        | NR            |
| 425    | 34                       | NR            | 555    | 322                      | NR            | 685    | 61                       | NR            | 815    | 1                        | NR            | 945    | 0                        | NR            |
| 430    | 57                       | NR            | 560    | 327                      | NR            | 690    | 53                       | NR            | 820    | 1                        | NR            | 950    | 0                        | NR            |
| 435    | 97                       | NR            | 565    | 331                      | NR            | 695    | 45                       | NR            | 825    | 1                        | NR            | 955    | 0                        | NR            |
| 440    | 163                      | NR            | 570    | 334                      | NR            | 700    | 39                       | NR            | 830    | 1                        | NR            | 960    | 0                        | NR            |
| 445    | 293                      | NR            | 575    | 337                      | NR            | 705    | 33                       | NR            | 835    | 1                        | NR            | 965    | 0                        | NR            |
| 450    | 428                      | NR            | 580    | 339                      | NR            | 710    | 28                       | NR            | 840    | 1                        | NR            | 970    | 0                        | NR            |
| 455    | 351                      | NR            | 585    | 341                      | NR            | 715    | 23                       | NR            | 845    | 0                        | NR            | 975    | 0                        | NR            |
| 460    | 229                      | NR            | 590    | 342                      | NR            | 720    | 19                       | NR            | 850    | 0                        | NR            | 980    | 0                        | NR            |
| 465    | 192                      | NR            | 595    | 339                      | NR            | 725    | 16                       | NR            | 855    | 0                        | NR            | 985    | 0                        | NR            |
| 470    | 152                      | NR            | 600    | 338                      | NR            | 730    | 13                       | NR            | 860    | 0                        | NR            | 990    | 0                        | NR            |
| 475    | 122                      | NR            | 605    | 337                      | NR            | 735    | 11                       | NR            | 865    | 0                        | NR            | 995    | 0                        | NR            |
| 480    | 125                      | NR            | 610    | 361                      | NR            | 740    | 10                       | NR            | 870    | 0                        | NR            | 1000   | 0                        | NR            |
| 485    | 144                      | NR            | 615    | 378                      | NR            | 745    | 9                        | NR            | 875    | 0                        | NR            |        |                          |               |

REPORT NUMBER: SP1-2506-457-3

### Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 3.58

| λ (nm) | Power W <sup>λ</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>λ</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>λ</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>λ</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>λ</sup> /nm | Lumens (φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360    | 0                        | NR            | 490    | 168                      | NR            | 620    | 331                      | NR            | 750    | 8                        | NR            | 880    | 0                        | NR            |
| 365    | 0                        | NR            | 495    | 199                      | NR            | 625    | 331                      | NR            | 755    | 6                        | NR            | 885    | 0                        | NR            |
| 370    | 0                        | NR            | 500    | 227                      | NR            | 630    | 1000                     | NR            | 760    | 6                        | NR            | 890    | 0                        | NR            |
| 375    | 0                        | NR            | 505    | 248                      | NR            | 635    | 646                      | NR            | 765    | 5                        | NR            | 895    | 0                        | NR            |
| 380    | 0                        | NR            | 510    | 263                      | NR            | 640    | 219                      | NR            | 770    | 4                        | NR            | 900    | 0                        | NR            |
| 385    | 0                        | NR            | 515    | 272                      | NR            | 645    | 210                      | NR            | 775    | 3                        | NR            | 905    | 0                        | NR            |
| 390    | 1                        | NR            | 520    | 277                      | NR            | 650    | 183                      | NR            | 780    | 3                        | NR            | 910    | 0                        | NR            |
| 395    | 2                        | NR            | 525    | 283                      | NR            | 655    | 155                      | NR            | 785    | 3                        | NR            | 915    | 0                        | NR            |
| 400    | 3                        | NR            | 530    | 288                      | NR            | 660    | 132                      | NR            | 790    | 2                        | NR            | 920    | 0                        | NR            |
| 405    | 5                        | NR            | 535    | 294                      | NR            | 665    | 111                      | NR            | 795    | 2                        | NR            | 925    | 0                        | NR            |
| 410    | 7                        | NR            | 540    | 301                      | NR            | 670    | 102                      | NR            | 800    | 2                        | NR            | 930    | 0                        | NR            |
| 415    | 11                       | NR            | 545    | 308                      | NR            | 675    | 84                       | NR            | 805    | 1                        | NR            | 935    | 0                        | NR            |
| 420    | 19                       | NR            | 550    | 315                      | NR            | 680    | 72                       | NR            | 810    | 1                        | NR            | 940    | 0                        | NR            |
| 425    | 34                       | NR            | 555    | 322                      | NR            | 685    | 61                       | NR            | 815    | 1                        | NR            | 945    | 0                        | NR            |
| 430    | 57                       | NR            | 560    | 327                      | NR            | 690    | 53                       | NR            | 820    | 1                        | NR            | 950    | 0                        | NR            |
| 435    | 97                       | NR            | 565    | 331                      | NR            | 695    | 45                       | NR            | 825    | 1                        | NR            | 955    | 0                        | NR            |
| 440    | 163                      | NR            | 570    | 334                      | NR            | 700    | 39                       | NR            | 830    | 1                        | NR            | 960    | 0                        | NR            |
| 445    | 293                      | NR            | 575    | 337                      | NR            | 705    | 33                       | NR            | 835    | 1                        | NR            | 965    | 0                        | NR            |
| 450    | 428                      | NR            | 580    | 339                      | NR            | 710    | 28                       | NR            | 840    | 1                        | NR            | 970    | 0                        | NR            |
| 455    | 351                      | NR            | 585    | 341                      | NR            | 715    | 23                       | NR            | 845    | 0                        | NR            | 975    | 0                        | NR            |
| 460    | 229                      | NR            | 590    | 342                      | NR            | 720    | 19                       | NR            | 850    | 0                        | NR            | 980    | 0                        | NR            |
| 465    | 192                      | NR            | 595    | 339                      | NR            | 725    | 16                       | NR            | 855    | 0                        | NR            | 985    | 0                        | NR            |
| 470    | 152                      | NR            | 600    | 338                      | NR            | 730    | 13                       | NR            | 860    | 0                        | NR            | 990    | 0                        | NR            |
| 475    | 122                      | NR            | 605    | 337                      | NR            | 735    | 11                       | NR            | 865    | 0                        | NR            | 995    | 0                        | NR            |
| 480    | 125                      | NR            | 610    | 361                      | NR            | 740    | 10                       | NR            | 870    | 0                        | NR            | 1000   | 0                        | NR            |
| 485    | 144                      | NR            | 615    | 378                      | NR            | 745    | 9                        | NR            | 875    | 0                        | NR            |        |                          |               |

REPORT NUMBER: SP1-2506-457-3



TM-30-18

### Summary

$R_f = 91.2$   
 $R_g = 99.8$   
 $CIE\ R_a = 93.4$   
 $R_9 = 62.8$



### Color Vector Graphics



Individual Sample Fidelity Index ( $R_{f,i}$ )

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 93 | CES51 = 98 | CES76 = 86 |
| CES02 = 62 | CES27 = 92 | CES52 = 99 | CES77 = 88 |
| CES03 = 31 | CES28 = 96 | CES53 = 97 | CES78 = 82 |
| CES04 = 69 | CES29 = 95 | CES54 = 94 | CES79 = 93 |
| CES05 = 49 | CES30 = 94 | CES55 = 93 | CES80 = 92 |
| CES06 = 50 | CES31 = 96 | CES56 = 95 | CES81 = 79 |
| CES07 = 42 | CES32 = 88 | CES57 = 94 | CES82 = 96 |
| CES08 = 41 | CES33 = 98 | CES58 = 95 | CES83 = 95 |
| CES09 = 29 | CES34 = 93 | CES59 = 97 | CES84 = 94 |
| CES10 = 74 | CES35 = 96 | CES60 = 93 | CES85 = 81 |
| CES11 = 57 | CES36 = 82 | CES61 = 92 | CES86 = 83 |
| CES12 = 63 | CES37 = 94 | CES62 = 88 | CES87 = 91 |
| CES13 = 43 | CES38 = 89 | CES63 = 93 | CES88 = 97 |
| CES14 = 74 | CES39 = 99 | CES64 = 91 | CES89 = 85 |
| CES15 = 71 | CES40 = 97 | CES65 = 89 | CES90 = 97 |
| CES16 = 47 | CES41 = 97 | CES66 = 88 | CES91 = 73 |
| CES17 = 49 | CES42 = 93 | CES67 = 87 | CES92 = 77 |
| CES18 = 56 | CES43 = 93 | CES68 = 88 | CES93 = 86 |
| CES19 = 71 | CES44 = 99 | CES69 = 89 | CES94 = 75 |
| CES20 = 66 | CES45 = 96 | CES70 = 86 | CES95 = 82 |
| CES21 = 85 | CES46 = 96 | CES71 = 81 | CES96 = 92 |
| CES22 = 78 | CES47 = 93 | CES72 = 94 | CES97 = 94 |
| CES23 = 91 | CES48 = 93 | CES73 = 80 | CES98 = 94 |
| CES24 = 90 | CES49 = 95 | CES74 = 92 | CES99 = 93 |
| CES25 = 71 | CES50 = 99 | CES75 = 82 |            |



Color Rendition by Hue-Angle Bin



**Measure Comparisons**



(END OF REPORT)