

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: METALUX

Report Number: P219213

Luminaire Tested: **24GR-LD5-90-A19/156-UNV-L930-CD1-U**

Issue Date: 3/12/2020

Test Information

Test Method: LM-79-08
Report Number: P219213
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P33306)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/12/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: METALUX
Catalog Number: 24GR-LD5-90-A19/156-UNV-L930-CD1-U
Description: METALUX GR 2X4 LED TROFFER WITH A19/156 LENS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7133.2 lumens
Efficiency: N/A
Efficacy: 103.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.2 / 1.26
Luminous Opening: Rectangular (W 1.83' x L: 3.83' x H: 0')
CIE Type: Direct


Input Watts (W): 69.117
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P219213

CATALOG NUMBER: 24GR-LD5-90-A19/156-UNV-L930-CD1-U

Luminous Intensity Polar Plot





TEST NUMBER: P219213

CATALOG NUMBER: 24GR-LD5-90-A19/156-UNV-L930-CD1-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	110	105	101	98	107	103	99	96		99	96	93		95	93	90		91	89	88
2	101	93	87	82	98	91	86	81		88	83	79		85	81	77		82	78	75
3	93	83	75	69	90	81	74	69		79	73	68		76	71	67		73	69	65
4	86	74	66	60	83	73	65	60		71	64	59		68	63	58		66	61	57
5	79	67	59	53	77	66	58	52		64	57	52		62	56	51		60	55	51
6	73	61	53	46	72	60	52	46		58	51	46		57	50	45		55	49	45
7	68	56	47	42	67	55	47	41		53	46	41		52	46	41		51	45	41
8	64	51	43	37	62	50	43	37		49	42	37		48	41	37		47	41	37
9	60	47	39	34	58	46	39	34		45	38	34		44	38	33		43	38	33
10	56	44	36	31	55	43	36	31		42	35	31		41	35	31		40	35	30

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4848	4848	4848
5°	4871	4844	4856
10°	4862	4823	4837
15°	4844	4795	4816
20°	4798	4749	4747
25°	4704	4654	4650
30°	4549	4502	4512
35°	4321	4271	4277
40°	4063	3992	3968
45°	3724	3673	3528
50°	3366	3274	3028
55°	3022	2751	2610
60°	2647	2214	2295
65°	2309	1741	2113
70°	2112	1520	2112
75°	2113	1617	2328
80°	2294	1905	2654
85°	2518	2149	2847



TEST NUMBER: P219213

CATALOG NUMBER: 24GR-LD5-90-A19/156-UNV-L930-CD1-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	299.7	4.2
10°-20°	855.3	12.0
20°-30°	1268.3	17.8
30°-40°	1430.7	20.1
40°-50°	1295.8	18.2
50°-60°	934.9	13.1
60°-70°	558.2	7.8
70°-80°	345.0	4.8
80°-90°	145.3	2.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2423.3	34.0
0°-40°	3854.0	54.0
0°-60°	6084.6	85.3
0°-90°	7133.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7133.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3165	3165	3165	3165	3165	
5°	3168	3164	3151	3147	3158	301
15°	3055	3036	3024	3025	3037	861
25°	2784	2768	2754	2744	2752	1279
35°	2311	2308	2284	2286	2288	1446
45°	1719	1708	1696	1654	1629	1325
55°	1132	1096	1030	980	977	1010
65°	637	561	480	546	583	641
75°	357	310	273	340	393	381
85°	143	126	122	160	162	150
90°	0	0	0	0	0	



TEST NUMBER: P219213

CATALOG NUMBER: 24GR-LD5-90-A19/156-UNV-L930-CD1-U

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3165.0	3165.0	3165.0	3165.0	3165.0
2.5°	3175.9	3167.1	3156.1	3162.7	3168.2
5°	3168.2	3163.8	3150.6	3147.2	3158.3
7.5°	3151.7	3140.7	3128.5	3134.0	3129.6
10°	3126.3	3116.4	3101.0	3102.1	3109.8
12.5°	3095.5	3083.4	3066.8	3071.2	3077.9
15°	3054.7	3036.0	3023.8	3025.0	3037.1
17.5°	3002.9	2988.6	2973.2	2976.4	2982.0
20°	2943.4	2935.7	2913.6	2907.1	2912.6
22.5°	2868.4	2854.2	2842.0	2838.8	2839.8
25°	2783.7	2768.2	2753.9	2744.0	2751.7
27.5°	2684.4	2671.2	2652.5	2649.2	2655.8
30°	2572.0	2562.1	2545.6	2541.2	2551.1
32.5°	2457.5	2440.9	2417.8	2417.8	2420.0
35°	2310.8	2307.6	2284.4	2285.5	2287.7
37.5°	2178.7	2163.2	2150.0	2136.8	2143.4
40°	2032.0	2014.4	1996.8	1988.0	1984.6
42.5°	1874.5	1861.2	1853.5	1821.5	1813.8
45°	1719.1	1708.1	1695.9	1654.1	1628.8
47.5°	1560.4	1558.2	1548.3	1474.4	1449.1
50°	1412.8	1409.4	1374.2	1295.9	1270.6
52.5°	1272.8	1250.7	1204.5	1127.3	1122.9
55°	1131.8	1096.5	1030.3	979.7	977.4
57.5°	982.9	941.1	873.9	846.3	860.7
60°	864.0	800.1	722.9	726.2	749.3
62.5°	740.5	668.9	592.9	625.9	653.5
65°	637.0	560.9	480.4	545.5	582.9
67.5°	546.6	476.1	398.9	486.0	522.3
70°	471.7	414.3	339.4	430.9	471.7
72.5°	412.1	359.2	300.9	386.8	434.2
75°	357.0	309.6	273.3	340.5	393.4
77.5°	309.6	263.4	246.8	300.9	352.6
80°	260.1	218.2	216.0	262.2	300.9
82.5°	202.8	174.1	174.1	219.3	242.5
85°	143.3	125.6	122.3	159.8	162.0
87.5°	73.8	70.5	63.9	83.7	83.7
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)