

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: METALUX

Report Number: P976982

Luminaire Tested: 24SR-LD2-C-59-UNV-L940-CD1-SO-U

Issue Date: 03/18/2025

Test Information

Test Method: LM-79-2019
Report Number: P976982
Test Lab: INNOVATION CENTER(P3)
Issue Date: 03/18/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: METALUX
Catalog Number: 24SR-LD2-C-59-UNV-L940-CD1-SO-U
Description: METALUX SKYRIDGE 2x4 5900LM PACKAGE 90CRI 4000K TROFFER with Storaro Orange SKYTR
Light Source: 4000K CCT, 90+ CRI LEDS
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4130.0 lumens
Efficiency: N/A
Efficacy: 94.3 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.85 / 1.72
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 43.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

TEST NUMBER: P976982
CATALOG NUMBER: 24SR-LD2-C-59-UNV-L940-CD1-SO-U

Luminous Intensity Polar Plot





TEST NUMBER: P976982

CATALOG NUMBER: 24SR-LD2-C-59-UNV-L940-CD1-SO-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	107	101	96	91	104	99	94	90	94	90	87	90	87	84	87	84	82	87	84	82	79
2	96	87	79	72	93	85	77	71	81	75	70	78	73	68	74	70	66	74	70	66	64
3	87	75	66	59	84	74	65	58	70	63	57	68	61	56	65	60	55	65	60	55	53
4	79	66	56	49	77	65	56	49	62	54	48	60	53	47	57	52	47	57	52	47	44
5	72	59	49	42	70	57	48	42	55	47	41	53	46	41	51	45	40	51	45	40	38
6	67	53	43	36	65	52	43	36	50	42	36	48	41	35	46	40	35	46	40	35	33
7	62	47	38	32	60	47	38	32	45	37	31	43	36	31	42	36	31	42	36	31	29
8	57	43	34	28	56	42	34	28	41	33	28	40	33	28	39	32	27	39	32	27	25
9	53	39	31	25	52	39	31	25	38	30	25	37	30	25	35	29	24	35	29	24	23
10	50	36	28	23	49	36	28	22	35	27	22	34	27	22	33	27	22	33	27	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1202	1202	1202
5°	1209	1273	1336
10°	1200	1443	1584
15°	1177	1595	1786
20°	1151	1707	1934
25°	1121	1780	2030
30°	1082	1819	2085
35°	1041	1831	2099
40°	1000	1825	2084
45°	962	1820	2051
50°	920	1826	2023
55°	887	1862	2016
60°	861	1932	2052
65°	836	2041	2131
70°	815	2207	2291
75°	794	2479	2523
80°	797	2930	2743
85°	881	3680	3327

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 87.5°
 Luminance: 4670 cd/sqm



TEST NUMBER: P976982
 CATALOG NUMBER: 24SR-LD2-C-59-UNV-L940-CD1-SO-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.7	2.2
10°-20°	312.3	7.6
20°-30°	522.9	12.7
30°-40°	654.7	15.9
40°-50°	686.8	16.6
50°-60°	649.0	15.7
60°-70°	568.1	13.8
70°-80°	438.8	10.6
80°-90°	204.7	5.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	927.8	22.5
0°-40°	1582.5	38.3
0°-60°	2918.4	70.7
0°-90°	4130.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4130.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	894	894	894	894	894	
5°	895	894	942	978	989	85
15°	845	964	1145	1248	1282	238
25°	755	969	1199	1321	1368	347
35°	634	886	1115	1235	1278	397
45°	505	751	956	1049	1078	390
55°	378	624	794	845	859	339
65°	263	511	641	659	669	260
75°	153	383	477	481	485	162
85°	57	201	238	221	216	60
90°	0	0	0	0	0	



TEST NUMBER: P976982
 CATALOG NUMBER: 24SR-LD2-C-59-UNV-L940-CD1-SO-U

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	893.6	893.6	893.6	893.6	893.6	893.6	893.6	893.6	893.6	893.6	893.6
2.5°	899.4	898.0	896.5	893.6	892.3	892.3	892.3	892.3	893.6	898.0	900.7
5°	895.2	895.2	892.3	890.7	892.3	896.5	903.6	915.1	926.5	942.2	955.1
7.5°	888.0	886.5	885.2	886.5	899.4	918.0	936.5	958.0	977.9	1000.8	1019.2
10°	878.1	876.5	878.1	889.4	915.1	945.1	972.2	999.3	1026.4	1056.3	1082.1
12.5°	862.3	862.3	867.9	893.6	929.3	966.4	1002.1	1036.3	1070.7	1104.9	1134.9
15°	845.2	846.6	860.8	898.0	942.2	985.1	1026.4	1066.5	1106.5	1144.9	1177.7
17.5°	825.2	827.9	852.3	898.0	948.0	997.9	1045.0	1089.2	1132.0	1173.5	1207.7
20°	803.7	806.6	842.3	895.2	950.9	1005.0	1055.0	1103.6	1149.3	1192.1	1227.7
22.5°	779.5	783.7	829.5	886.5	948.0	1006.4	1057.9	1107.8	1154.9	1200.6	1236.3
25°	755.1	760.9	813.7	875.2	939.3	999.3	1053.6	1103.6	1153.5	1199.2	1234.8
27.5°	725.2	735.1	795.1	857.9	926.5	986.4	1040.8	1093.6	1143.5	1189.2	1224.8
30°	696.7	709.6	772.4	837.9	908.0	968.0	1022.1	1075.0	1124.9	1170.6	1206.3
32.5°	665.2	681.0	746.7	815.2	883.6	942.2	997.9	1050.7	1100.7	1146.4	1180.6
35°	633.9	652.3	719.6	789.5	856.5	915.1	969.3	1022.1	1070.7	1114.9	1147.8
37.5°	602.4	622.4	689.6	760.9	825.2	882.3	936.5	987.9	1037.9	1079.2	1112.0
40°	569.6	592.4	659.5	728.0	792.4	847.9	902.3	952.2	999.3	1039.2	1070.7
42.5°	536.7	562.4	629.5	696.7	758.0	812.4	866.5	915.1	959.3	997.9	1027.9
45°	505.4	531.1	596.6	663.9	723.8	778.0	830.8	878.1	920.7	956.4	985.1
47.5°	472.5	501.2	566.7	632.4	689.6	743.8	795.1	839.4	880.7	913.6	940.9
50°	439.7	471.0	535.4	599.5	658.1	710.9	760.9	803.7	842.3	872.3	898.0
52.5°	408.2	441.0	506.7	569.6	626.8	679.6	728.0	769.5	805.3	832.3	855.2
55°	378.2	412.6	478.3	539.6	598.2	649.5	695.2	735.1	768.0	793.7	813.7
57.5°	348.3	385.5	451.0	513.8	569.6	621.0	665.2	702.3	732.3	756.7	773.8
60°	319.8	358.3	425.5	486.8	542.5	592.4	635.3	669.4	698.1	718.0	730.9
62.5°	289.9	331.2	398.2	461.0	516.7	564.0	605.3	638.1	662.3	679.6	691.0
65°	262.6	304.1	372.7	435.5	488.3	533.8	572.4	603.9	626.8	641.0	648.1
67.5°	235.5	278.3	346.9	408.2	459.7	503.9	539.6	569.6	589.5	601.1	606.6
70°	207.1	252.6	319.8	379.8	429.7	471.0	506.7	532.5	551.1	561.1	564.0
72.5°	178.5	225.5	292.7	351.1	398.2	438.4	471.0	495.4	512.5	519.6	521.1
75°	152.7	197.1	262.6	318.3	364.0	401.1	433.9	456.8	469.7	476.8	478.3
77.5°	127.0	169.8	232.6	285.5	325.4	361.1	392.6	414.0	426.8	432.6	432.6
80°	102.8	142.7	199.8	247.0	285.5	318.3	346.9	368.2	379.8	378.2	372.7
82.5°	79.9	117.0	165.6	207.1	241.3	271.2	299.9	312.7	317.0	312.7	308.3
85°	57.1	87.0	125.6	159.8	189.8	212.6	231.3	241.3	242.6	238.4	234.2
87.5°	32.8	48.6	71.5	97.0	112.8	127.0	142.7	148.5	148.5	151.4	142.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P976982

CATALOG NUMBER: 24SR-LD2-C-59-UNV-L940-CD1-SO-U

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	893.6	893.6	893.6	893.6	893.6	893.6	893.6	893.6
2.5°	899.4	900.7	900.7	903.6	905.1	905.1	903.6	900.7
5°	959.3	968.0	973.5	982.2	986.4	990.8	992.2	989.3
7.5°	1029.2	1042.1	1053.6	1066.5	1072.1	1076.5	1082.1	1077.8
10°	1096.5	1113.6	1127.8	1142.0	1150.6	1156.4	1160.6	1159.3
12.5°	1153.5	1173.5	1189.2	1203.5	1214.8	1223.4	1227.7	1227.7
15°	1197.7	1220.6	1240.5	1256.3	1267.6	1276.3	1282.0	1282.0
17.5°	1232.1	1254.8	1276.3	1292.0	1303.4	1314.9	1320.4	1323.3
20°	1252.1	1276.3	1297.6	1314.9	1327.7	1340.4	1346.2	1350.4
22.5°	1262.1	1286.3	1309.1	1327.7	1342.0	1353.3	1360.4	1363.3
25°	1262.1	1287.6	1312.0	1330.4	1344.8	1357.7	1364.8	1367.7
27.5°	1253.4	1280.5	1304.9	1322.0	1337.7	1350.4	1357.7	1360.4
30°	1236.3	1263.4	1287.6	1304.9	1320.4	1332.0	1339.1	1342.0
32.5°	1209.2	1237.7	1260.5	1277.6	1293.4	1304.9	1312.0	1313.3
35°	1177.7	1204.8	1226.3	1243.4	1259.2	1269.2	1274.9	1277.6
37.5°	1139.3	1164.9	1186.4	1202.1	1216.3	1227.7	1233.4	1234.8
40°	1097.8	1122.0	1140.6	1154.9	1169.3	1179.3	1184.8	1186.4
42.5°	1053.6	1076.5	1093.6	1106.5	1119.1	1127.8	1132.0	1133.5
45°	1007.9	1027.9	1043.6	1055.0	1066.5	1073.6	1077.8	1077.8
47.5°	962.2	980.8	993.5	1002.1	1012.1	1019.2	1023.7	1022.1
50°	916.5	932.2	942.2	950.9	959.3	963.5	968.0	966.4
52.5°	870.8	885.2	890.7	898.0	905.1	909.4	913.6	910.7
55°	826.6	836.6	842.3	847.9	853.7	857.9	860.8	859.4
57.5°	783.7	790.8	795.1	800.8	805.3	807.9	810.8	809.5
60°	738.0	743.8	746.7	752.4	756.7	759.5	762.4	762.4
62.5°	695.2	699.6	700.9	706.7	709.6	712.3	716.7	715.2
65°	649.5	653.9	656.8	661.0	663.9	666.8	671.0	669.4
67.5°	606.6	611.0	612.4	616.8	621.0	625.3	626.8	626.8
70°	564.0	566.7	568.2	574.0	575.3	579.5	582.4	582.4
72.5°	521.1	522.5	525.4	529.6	532.5	535.4	538.2	536.7
75°	475.4	478.3	479.7	482.5	482.5	485.4	485.4	485.4
77.5°	428.4	423.9	422.6	421.1	419.7	419.7	419.7	418.2
80°	364.0	359.8	358.3	355.6	355.6	355.6	355.6	354.0
82.5°	301.2	295.4	292.7	291.2	289.9	289.9	289.9	288.3
85°	228.4	222.6	221.3	219.8	219.8	218.4	217.1	215.5
87.5°	141.4	137.0	135.6	132.7	134.3	131.4	131.4	131.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P976982
 CATALOG NUMBER: 24SR-LD2-C-59-UNV-L940-CD1-SO-U

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room Dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.4	14.2	12.8	14.5	14.8	15.0	16.8	15.4	17.1	17.4
	3H	14.3	15.9	14.7	16.2	16.6	17.5	19.1	17.9	19.4	19.8
	4H	15.1	16.6	15.4	16.9	17.3	18.6	20.2	19.0	20.5	20.9
	6H	15.6	17.0	16.0	17.4	17.8	19.7	21.1	20.1	21.4	21.8
	8H	15.8	17.1	16.2	17.5	17.9	20.1	21.5	20.5	21.9	22.2
	12H	16.0	17.3	16.4	17.6	18.1	20.5	21.8	20.9	22.2	22.6
4H	2H	14.0	15.5	14.4	15.8	16.2	15.8	17.3	16.2	17.6	18.0
	3H	16.4	17.7	16.8	18.0	18.4	18.5	19.8	18.9	20.2	20.6
	4H	17.4	18.6	17.8	19.0	19.4	19.8	21.0	20.3	21.4	21.8
	6H	18.2	19.3	18.7	19.7	20.2	21.0	22.1	21.5	22.5	23.0
	8H	18.6	19.5	19.0	20.0	20.4	21.6	22.5	22.0	23.0	23.4
	12H	18.8	19.7	19.3	20.2	20.6	22.1	22.9	22.5	23.4	23.9
8H	4H	18.5	19.4	18.9	19.9	20.3	20.4	21.3	20.8	21.8	22.2
	6H	19.7	20.6	20.2	21.1	21.5	21.8	22.6	22.3	23.1	23.6
	8H	20.3	21.0	20.8	21.5	22.0	22.4	23.2	22.9	23.7	24.2
	12H	20.7	21.4	21.2	21.9	22.4	23.1	23.7	23.6	24.2	24.8
12H	4H	18.7	19.6	19.1	20.0	20.5	20.5	21.3	20.9	21.8	22.3
	6H	20.1	20.9	20.6	21.3	21.8	22.0	22.7	22.5	23.2	23.7
	8H	20.8	21.5	21.3	22.0	22.5	22.7	23.4	23.2	23.9	24.4

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2506-457-7

Test Date: 07/02/2025

Luminaire Tested: 24SR-LD2-64-C-UNV-L940-CD1-U

Data in this report applies to families of products including 24SR-LD2-64-C-UNV-L940-CD1-U

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2506-457-7
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 07/02/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Metalux
 Catalog Number: **24SR-LD2-64-C-UNV-L940-CD1-U**
 Description: 2X4 SKYRIDGE 6400LM Fixture with new LTN chip

Spectral Parameters

CCT (K): 3850
 CIE u': 0.2283
 CIE v': 0.5037
 Duv: -0.0006
 CIE x: 0.3868
 CIE y: 0.3794
 CIE z: 0.2338
 Peak Wavelength (nm): 630
 Dominant Wavelength (nm): 579
 Purity: 29.94798
 Rf: 91.3
 Rg: 99.8

CRI (Ra): 94.0
 R1: 95.3
 R2: 96.3
 R3: 95.7
 R4: 95.2
 R5: 94.4
 R6: 94.3
 R7: 94.1
 R8: 86.7
 R9: 65.3
 R10: 89.6
 R11: 95.5
 R12: 76.1
 R13: 95.5
 R14: 96.8
 R15: 92.3



Test Conditions

Stabilization Time: 38M
 Operation Time: 1H 38M
 Sphere Temperature (°C): 24.4

REPORT NUMBER: SP1-2506-457-7

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2506-457-7

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



CCT = 3850K
 CIE x = 0.3868
 CIE y = 0.3794
 Duv = -0.0006

Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2506-457-7

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	173	NR	620	343	NR	750	8	NR	880	0	NR
365	0	NR	495	201	NR	625	342	NR	755	7	NR	885	0	NR
370	0	NR	500	231	NR	630	1000	NR	760	6	NR	890	0	NR
375	0	NR	505	253	NR	635	692	NR	765	5	NR	895	0	NR
380	0	NR	510	268	NR	640	226	NR	770	4	NR	900	0	NR
385	1	NR	515	277	NR	645	214	NR	775	4	NR	905	0	NR
390	1	NR	520	284	NR	650	190	NR	780	3	NR	910	0	NR
395	3	NR	525	290	NR	655	160	NR	785	3	NR	915	0	NR
400	4	NR	530	296	NR	660	136	NR	790	2	NR	920	0	NR
405	5	NR	535	303	NR	665	115	NR	795	2	NR	925	0	NR
410	8	NR	540	310	NR	670	106	NR	800	2	NR	930	0	NR
415	13	NR	545	316	NR	675	87	NR	805	2	NR	935	0	NR
420	22	NR	550	323	NR	680	75	NR	810	1	NR	940	0	NR
425	37	NR	555	330	NR	685	64	NR	815	1	NR	945	0	NR
430	62	NR	560	335	NR	690	55	NR	820	1	NR	950	0	NR
435	102	NR	565	340	NR	695	47	NR	825	1	NR	955	0	NR
440	164	NR	570	342	NR	700	40	NR	830	1	NR	960	0	NR
445	281	NR	575	345	NR	705	34	NR	835	1	NR	965	0	NR
450	423	NR	580	348	NR	710	29	NR	840	1	NR	970	0	NR
455	384	NR	585	350	NR	715	25	NR	845	1	NR	975	0	NR
460	256	NR	590	351	NR	720	21	NR	850	0	NR	980	0	NR
465	208	NR	595	348	NR	725	17	NR	855	0	NR	985	0	NR
470	169	NR	600	348	NR	730	14	NR	860	0	NR	990	0	NR
475	135	NR	605	347	NR	735	12	NR	865	0	NR	995	0	NR
480	133	NR	610	379	NR	740	11	NR	870	0	NR	1000	0	NR
485	149	NR	615	406	NR	745	9	NR	875	0	NR			

REPORT NUMBER: SP1-2506-457-7

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.74

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	173	NR	620	343	NR	750	8	NR	880	0	NR
365	0	NR	495	201	NR	625	342	NR	755	7	NR	885	0	NR
370	0	NR	500	231	NR	630	1000	NR	760	6	NR	890	0	NR
375	0	NR	505	253	NR	635	692	NR	765	5	NR	895	0	NR
380	0	NR	510	268	NR	640	226	NR	770	4	NR	900	0	NR
385	1	NR	515	277	NR	645	214	NR	775	4	NR	905	0	NR
390	1	NR	520	284	NR	650	190	NR	780	3	NR	910	0	NR
395	3	NR	525	290	NR	655	160	NR	785	3	NR	915	0	NR
400	4	NR	530	296	NR	660	136	NR	790	2	NR	920	0	NR
405	5	NR	535	303	NR	665	115	NR	795	2	NR	925	0	NR
410	8	NR	540	310	NR	670	106	NR	800	2	NR	930	0	NR
415	13	NR	545	316	NR	675	87	NR	805	2	NR	935	0	NR
420	22	NR	550	323	NR	680	75	NR	810	1	NR	940	0	NR
425	37	NR	555	330	NR	685	64	NR	815	1	NR	945	0	NR
430	62	NR	560	335	NR	690	55	NR	820	1	NR	950	0	NR
435	102	NR	565	340	NR	695	47	NR	825	1	NR	955	0	NR
440	164	NR	570	342	NR	700	40	NR	830	1	NR	960	0	NR
445	281	NR	575	345	NR	705	34	NR	835	1	NR	965	0	NR
450	423	NR	580	348	NR	710	29	NR	840	1	NR	970	0	NR
455	384	NR	585	350	NR	715	25	NR	845	1	NR	975	0	NR
460	256	NR	590	351	NR	720	21	NR	850	0	NR	980	0	NR
465	208	NR	595	348	NR	725	17	NR	855	0	NR	985	0	NR
470	169	NR	600	348	NR	730	14	NR	860	0	NR	990	0	NR
475	135	NR	605	347	NR	735	12	NR	865	0	NR	995	0	NR
480	133	NR	610	379	NR	740	11	NR	870	0	NR	1000	0	NR
485	149	NR	615	406	NR	745	9	NR	875	0	NR			

REPORT NUMBER: SP1-2506-457-7

Melanopic Flux vs. Wavelength




Melanopic Lumens: NR

M/P: 3.6

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	173	NR	620	343	NR	750	8	NR	880	0	NR
365	0	NR	495	201	NR	625	342	NR	755	7	NR	885	0	NR
370	0	NR	500	231	NR	630	1000	NR	760	6	NR	890	0	NR
375	0	NR	505	253	NR	635	692	NR	765	5	NR	895	0	NR
380	0	NR	510	268	NR	640	226	NR	770	4	NR	900	0	NR
385	1	NR	515	277	NR	645	214	NR	775	4	NR	905	0	NR
390	1	NR	520	284	NR	650	190	NR	780	3	NR	910	0	NR
395	3	NR	525	290	NR	655	160	NR	785	3	NR	915	0	NR
400	4	NR	530	296	NR	660	136	NR	790	2	NR	920	0	NR
405	5	NR	535	303	NR	665	115	NR	795	2	NR	925	0	NR
410	8	NR	540	310	NR	670	106	NR	800	2	NR	930	0	NR
415	13	NR	545	316	NR	675	87	NR	805	2	NR	935	0	NR
420	22	NR	550	323	NR	680	75	NR	810	1	NR	940	0	NR
425	37	NR	555	330	NR	685	64	NR	815	1	NR	945	0	NR
430	62	NR	560	335	NR	690	55	NR	820	1	NR	950	0	NR
435	102	NR	565	340	NR	695	47	NR	825	1	NR	955	0	NR
440	164	NR	570	342	NR	700	40	NR	830	1	NR	960	0	NR
445	281	NR	575	345	NR	705	34	NR	835	1	NR	965	0	NR
450	423	NR	580	348	NR	710	29	NR	840	1	NR	970	0	NR
455	384	NR	585	350	NR	715	25	NR	845	1	NR	975	0	NR
460	256	NR	590	351	NR	720	21	NR	850	0	NR	980	0	NR
465	208	NR	595	348	NR	725	17	NR	855	0	NR	985	0	NR
470	169	NR	600	348	NR	730	14	NR	860	0	NR	990	0	NR
475	135	NR	605	347	NR	735	12	NR	865	0	NR	995	0	NR
480	133	NR	610	379	NR	740	11	NR	870	0	NR	1000	0	NR
485	149	NR	615	406	NR	745	9	NR	875	0	NR			

Summary

$R_f = 91.3$
 $R_g = 99.8$
 $CIE R_a = 94.0$
 $R_9 = 65.3$



Color Vector Graphics





Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 93	CES51 = 98	CES76 = 87
CES02 = 62	CES27 = 91	CES52 = 99	CES77 = 88
CES03 = 31	CES28 = 96	CES53 = 97	CES78 = 83
CES04 = 69	CES29 = 96	CES54 = 94	CES79 = 93
CES05 = 49	CES30 = 93	CES55 = 92	CES80 = 92
CES06 = 50	CES31 = 96	CES56 = 95	CES81 = 79
CES07 = 42	CES32 = 88	CES57 = 94	CES82 = 96
CES08 = 41	CES33 = 99	CES58 = 95	CES83 = 95
CES09 = 29	CES34 = 93	CES59 = 97	CES84 = 94
CES10 = 74	CES35 = 96	CES60 = 93	CES85 = 81
CES11 = 57	CES36 = 81	CES61 = 92	CES86 = 83
CES12 = 63	CES37 = 94	CES62 = 87	CES87 = 92
CES13 = 43	CES38 = 88	CES63 = 93	CES88 = 98
CES14 = 74	CES39 = 99	CES64 = 91	CES89 = 85
CES15 = 71	CES40 = 97	CES65 = 89	CES90 = 97
CES16 = 47	CES41 = 97	CES66 = 88	CES91 = 73
CES17 = 49	CES42 = 93	CES67 = 87	CES92 = 77
CES18 = 56	CES43 = 93	CES68 = 88	CES93 = 86
CES19 = 71	CES44 = 99	CES69 = 89	CES94 = 76
CES20 = 66	CES45 = 96	CES70 = 86	CES95 = 83
CES21 = 85	CES46 = 97	CES71 = 81	CES96 = 92
CES22 = 78	CES47 = 93	CES72 = 94	CES97 = 95
CES23 = 91	CES48 = 92	CES73 = 80	CES98 = 95
CES24 = 90	CES49 = 96	CES74 = 91	CES99 = 93
CES25 = 71	CES50 = 98	CES75 = 83	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)