

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: METALUX

Report Number: P976206

Luminaire Tested: 12SR-LD2-12-S-UNV-L835-CD1-U

Issue Date: 03/18/2025

Test Information

Test Method: LM-79-2019
Report Number: P976206
Test Lab: INNOVATION CENTER(P3)
Issue Date: 03/18/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: METALUX
Catalog Number: 12SR-LD2-12-S-UNV-L835-CD1-U
Description: METALUX SKYRIDGE 1x2 1200LM PACKAGE 80CRI 3500K STANDARD TROFFER
Light Source: 3500K CCT, 80+ CRI LEDS
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1218.4 lumens
Efficiency: N/A
Efficacy: 136.9 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.54 / 1.5
Luminous Opening: Rectangular (W 1' x L: 2' x H: 0')
CIE Type: Direct

Input Watts (W): 8.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

TEST NUMBER: P976206
CATALOG NUMBER: 12SR-LD2-12-S-UNV-L835-CD1-U

Luminous Intensity Polar Plot





TEST NUMBER: P976206
 CATALOG NUMBER: 12SR-LD2-12-S-UNV-L835-CD1-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 | 100 | 100 |
| 1 | 108 | 104 | 99 | 95 | 106 | 101 | 97 | 94 | 97 | 94 | 91 | 93 | 90 | 88 | 90 | 87 | 85 | 83 | 83 | 83 | 83 |
| 2 | 99 | 90 | 83 | 77 | 96 | 88 | 82 | 76 | 85 | 79 | 75 | 81 | 77 | 73 | 78 | 75 | 71 | 69 | 69 | 69 | 69 |
| 3 | 90 | 79 | 71 | 64 | 87 | 78 | 70 | 64 | 75 | 68 | 63 | 72 | 66 | 61 | 69 | 64 | 60 | 58 | 58 | 58 | 58 |
| 4 | 82 | 70 | 61 | 54 | 80 | 69 | 60 | 54 | 66 | 59 | 53 | 64 | 58 | 53 | 62 | 56 | 52 | 50 | 50 | 50 | 50 |
| 5 | 76 | 63 | 54 | 47 | 73 | 61 | 53 | 47 | 59 | 52 | 46 | 57 | 51 | 46 | 55 | 50 | 45 | 43 | 43 | 43 | 43 |
| 6 | 70 | 56 | 47 | 41 | 68 | 55 | 47 | 41 | 54 | 46 | 40 | 52 | 45 | 40 | 50 | 44 | 40 | 37 | 37 | 37 | 37 |
| 7 | 65 | 51 | 42 | 36 | 63 | 50 | 42 | 36 | 49 | 41 | 36 | 47 | 40 | 35 | 46 | 40 | 35 | 33 | 33 | 33 | 33 |
| 8 | 60 | 47 | 38 | 32 | 59 | 46 | 38 | 32 | 45 | 37 | 32 | 43 | 37 | 32 | 42 | 36 | 31 | 29 | 29 | 29 | 29 |
| 9 | 56 | 43 | 34 | 29 | 55 | 42 | 34 | 29 | 41 | 34 | 29 | 40 | 33 | 28 | 39 | 33 | 28 | 26 | 26 | 26 | 26 |
| 10 | 53 | 39 | 31 | 26 | 51 | 39 | 31 | 26 | 38 | 31 | 26 | 37 | 30 | 26 | 36 | 30 | 26 | 24 | 24 | 24 | 24 |

AVERAGE LUMINANCE (cd/sqm):

| | 0° | 45° | 90° |
|-----|------|------|------|
| 0° | 1968 | 1968 | 1968 |
| 5° | 1998 | 2122 | 2130 |
| 10° | 1999 | 2206 | 2273 |
| 15° | 1992 | 2272 | 2430 |
| 20° | 1978 | 2335 | 2568 |
| 25° | 1954 | 2358 | 2614 |
| 30° | 1936 | 2373 | 2626 |
| 35° | 1895 | 2340 | 2554 |
| 40° | 1855 | 2304 | 2445 |
| 45° | 1805 | 2226 | 2320 |
| 50° | 1735 | 2167 | 2210 |
| 55° | 1653 | 2136 | 2109 |
| 60° | 1546 | 2085 | 2027 |
| 65° | 1415 | 2052 | 1914 |
| 70° | 1300 | 2046 | 1789 |
| 75° | 1183 | 1971 | 1661 |
| 80° | 1048 | 1888 | 1556 |
| 85° | 1007 | 1840 | 1340 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 2320 cd/sqm



TEST NUMBER: P976206
 CATALOG NUMBER: 12SR-LD2-12-S-UNV-L835-CD1-U

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 37.2 | 3.1 |
| 10°-20° | 113.9 | 9.4 |
| 20°-30° | 180.0 | 14.8 |
| 30°-40° | 216.5 | 17.8 |
| 40°-50° | 216.6 | 17.8 |
| 50°-60° | 190.6 | 15.6 |
| 60°-70° | 145.6 | 12.0 |
| 70°-80° | 89.1 | 7.3 |
| 80°-90° | 28.8 | 2.4 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 331.2 | 27.2 |
| 0°-40° | 547.7 | 45.0 |
| 0°-60° | 954.9 | 78.4 |
| 0°-90° | 1218.4 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 1218.4 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | 22.5° | 45° | 67.5° | 90° | Flux |
|-----|-----|-------|-----|-------|-----|------|
| 0° | 366 | 366 | 366 | 366 | 366 | |
| 5° | 370 | 378 | 393 | 394 | 394 | 35 |
| 15° | 358 | 378 | 408 | 428 | 436 | 101 |
| 25° | 329 | 352 | 397 | 428 | 440 | 152 |
| 35° | 288 | 310 | 356 | 382 | 389 | 181 |
| 45° | 237 | 253 | 292 | 303 | 305 | 183 |
| 55° | 176 | 199 | 228 | 226 | 225 | 157 |
| 65° | 111 | 142 | 161 | 153 | 150 | 111 |
| 75° | 57 | 91 | 95 | 84 | 80 | 60 |
| 85° | 16 | 32 | 30 | 23 | 22 | 18 |
| 90° | 0 | 0 | 0 | 0 | 0 | |



TEST NUMBER: P976206

CATALOG NUMBER: 12SR-LD2-12-S-UNV-L835-CD1-U

CANDELA DISTRIBUTION (FULL):

| | 0° | 22.5° | 45° | 67.5° | 90° |
|-------|-------|-------|-------|-------|-------|
| 0° | 365.7 | 365.7 | 365.7 | 365.7 | 365.7 |
| 2.5° | 371.1 | 369.8 | 381.9 | 383.3 | 383.3 |
| 5° | 369.8 | 377.9 | 392.8 | 394.2 | 394.2 |
| 7.5° | 367.1 | 383.3 | 395.4 | 405.0 | 409.1 |
| 10° | 365.7 | 384.7 | 403.6 | 410.4 | 415.9 |
| 12.5° | 361.6 | 381.9 | 405.0 | 419.9 | 428.0 |
| 15° | 357.6 | 377.9 | 407.7 | 428.0 | 436.2 |
| 17.5° | 352.2 | 375.1 | 410.4 | 432.1 | 441.6 |
| 20° | 345.4 | 371.1 | 407.7 | 434.8 | 448.4 |
| 22.5° | 338.6 | 361.6 | 402.2 | 433.4 | 444.2 |
| 25° | 329.1 | 352.2 | 397.0 | 428.0 | 440.2 |
| 27.5° | 319.7 | 342.7 | 392.8 | 422.5 | 433.4 |
| 30° | 311.5 | 333.1 | 381.9 | 410.4 | 422.5 |
| 32.5° | 300.7 | 322.4 | 369.8 | 398.2 | 409.1 |
| 35° | 288.5 | 310.2 | 356.2 | 381.9 | 388.8 |
| 37.5° | 277.7 | 296.6 | 342.7 | 363.0 | 368.5 |
| 40° | 264.0 | 281.7 | 327.9 | 342.7 | 348.0 |
| 42.5° | 251.9 | 269.5 | 310.2 | 326.5 | 326.5 |
| 45° | 237.1 | 253.3 | 292.5 | 303.4 | 304.8 |
| 47.5° | 222.0 | 241.1 | 276.3 | 283.1 | 283.1 |
| 50° | 207.2 | 227.6 | 258.8 | 264.0 | 264.0 |
| 52.5° | 192.3 | 212.6 | 242.5 | 245.1 | 243.9 |
| 55° | 176.2 | 199.1 | 227.6 | 226.2 | 224.8 |
| 57.5° | 158.5 | 184.2 | 210.0 | 207.2 | 207.2 |
| 60° | 143.6 | 170.6 | 193.7 | 189.7 | 188.3 |
| 62.5° | 127.4 | 155.7 | 177.4 | 172.0 | 169.4 |
| 65° | 111.1 | 142.2 | 161.1 | 153.1 | 150.3 |
| 67.5° | 96.2 | 130.0 | 144.9 | 134.2 | 131.4 |
| 70° | 82.6 | 116.5 | 130.0 | 116.5 | 113.7 |
| 72.5° | 69.1 | 102.9 | 112.5 | 100.2 | 96.2 |
| 75° | 56.9 | 90.7 | 94.8 | 84.0 | 79.9 |
| 77.5° | 44.8 | 77.2 | 77.2 | 66.3 | 65.1 |
| 80° | 33.8 | 63.7 | 60.9 | 51.4 | 50.2 |
| 82.5° | 24.3 | 47.4 | 46.0 | 38.0 | 35.3 |
| 85° | 16.3 | 32.5 | 29.8 | 23.1 | 21.7 |
| 87.5° | 8.2 | 16.3 | 13.5 | 9.5 | 9.5 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



TEST NUMBER: P976206
 CATALOG NUMBER: 12SR-LD2-12-S-UNV-L835-CD1-U

CIE UGR TABLE:

| Reflectances: | | | | | | | | | | | |
|-----------------|------|------------------|------|------|------|------|----------------|------|------|------|------|
| Ceiling | | 0.7 | 0.7 | 0.5 | 0.5 | 0.3 | 0.7 | 0.7 | 0.5 | 0.5 | 0.3 |
| Wall | | 0.5 | 0.3 | 0.5 | 0.3 | 0.3 | 0.5 | 0.3 | 0.5 | 0.3 | 0.3 |
| Reference plane | | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 |
| Room Dimensions | | Viewed crosswise | | | | | Viewed endwise | | | | |
| X=2H | Y=2H | 13.8 | 15.5 | 14.2 | 15.8 | 16.1 | 14.8 | 16.4 | 15.2 | 16.8 | 17.1 |
| | 3H | 15.5 | 17.0 | 15.9 | 17.3 | 17.7 | 16.5 | 18.0 | 16.9 | 18.4 | 18.7 |
| | 4H | 16.1 | 17.5 | 16.5 | 17.9 | 18.3 | 17.2 | 18.6 | 17.6 | 18.9 | 19.3 |
| | 6H | 16.6 | 17.9 | 17.0 | 18.3 | 18.7 | 17.7 | 19.0 | 18.1 | 19.4 | 19.8 |
| | 8H | 16.7 | 18.0 | 17.2 | 18.4 | 18.8 | 17.9 | 19.1 | 18.3 | 19.5 | 19.9 |
| | 12H | 16.8 | 18.0 | 17.3 | 18.4 | 18.9 | 18.0 | 19.2 | 18.4 | 19.6 | 20.0 |
| 4H | 2H | 14.8 | 16.2 | 15.2 | 16.5 | 16.9 | 15.5 | 16.9 | 15.9 | 17.3 | 17.6 |
| | 3H | 16.8 | 18.0 | 17.2 | 18.4 | 18.8 | 17.5 | 18.7 | 17.9 | 19.1 | 19.5 |
| | 4H | 17.6 | 18.7 | 18.1 | 19.1 | 19.6 | 18.3 | 19.3 | 18.7 | 19.8 | 20.2 |
| | 6H | 18.3 | 19.2 | 18.8 | 19.7 | 20.1 | 18.9 | 19.8 | 19.4 | 20.3 | 20.7 |
| | 8H | 18.5 | 19.4 | 19.0 | 19.8 | 20.3 | 19.1 | 20.0 | 19.6 | 20.4 | 20.9 |
| | 12H | 18.7 | 19.5 | 19.2 | 19.9 | 20.4 | 19.3 | 20.1 | 19.8 | 20.5 | 21.0 |
| 8H | 4H | 18.2 | 19.0 | 18.6 | 19.5 | 19.9 | 18.7 | 19.6 | 19.1 | 20.0 | 20.5 |
| | 6H | 19.1 | 19.8 | 19.5 | 20.3 | 20.7 | 19.5 | 20.2 | 19.9 | 20.7 | 21.1 |
| | 8H | 19.4 | 20.1 | 19.9 | 20.6 | 21.1 | 19.8 | 20.4 | 20.3 | 20.9 | 21.4 |
| | 12H | 19.7 | 20.3 | 20.2 | 20.8 | 21.3 | 20.0 | 20.6 | 20.5 | 21.1 | 21.6 |
| 12H | 4H | 18.2 | 19.0 | 18.7 | 19.5 | 19.9 | 18.7 | 19.5 | 19.2 | 20.0 | 20.5 |
| | 6H | 19.2 | 19.8 | 19.7 | 20.3 | 20.8 | 19.6 | 20.2 | 20.1 | 20.7 | 21.2 |
| | 8H | 19.6 | 20.2 | 20.1 | 20.7 | 21.3 | 19.9 | 20.5 | 20.4 | 21.0 | 21.6 |

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2506-457-6

Test Date: 07/01/2025

Luminaire Tested: 24SR-LD2-64-C-UNV-L935-CD1-U

Data in this report applies to families of products including 24SR-LD2-64-C-UNV-L935-CD1-U

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2506-457-6
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 07/02/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Metalux
 Catalog Number: **24SR-LD2-64-C-UNV-L935-CD1-U**
 Description: 2X4 SKYRIDGE 6400LM Fixture with new LTN chip

Spectral Parameters

CCT (K): 3329
 CIE u': 0.2411
 CIE v': 0.5118
 Duv: -0.0021
 CIE x: 0.4128
 CIE y: 0.3894
 CIE z: 0.1979
 Peak Wavelength (nm): 630
 Dominant Wavelength (nm): 582
 Purity: 40.74075
 Rf: 91.4
 Rg: 100.2

| | | | |
|-----------|------|------|------|
| CRI (Ra): | 93.9 | | |
| R1: | 95.4 | R9: | 60.5 |
| R2: | 97.4 | R10: | 92.5 |
| R3: | 97.7 | R11: | 95.9 |
| R4: | 94.9 | R12: | 82.0 |
| R5: | 95.1 | R13: | 96.0 |
| R6: | 95.7 | R14: | 98.0 |
| R7: | 91.7 | R15: | 91.5 |
| R8: | 83.2 | | |



Test Conditions

Stabilization Time: 48M
 Operation Time: 1H 48M
 Sphere Temperature (°C): 24.0

REPORT NUMBER: SP1-2506-457-6

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | 76INCH SPHERE IN0058 | 6/16/2025 | 12/16/2025 |
| Power Meter | XITRON INXT2011004 | 1/21/2025 | 1/21/2026 |
| AC Power Source | CHROMA 61603 IN0063 | 10/22/2024 | 10/22/2025 |
| DC Power Source | AGILENT E3634A IN0208 | 10/22/2024 | 10/22/2025 |
| Sphere Thermometer | ONSET IN0085 | 10/22/2024 | 10/22/2025 |
| Room Thermometer | ONSET IN0046 | 10/22/2024 | 10/22/2025 |

REPORT NUMBER: SP1-2506-457-6

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3500K 7-step quadrangle

REPORT NUMBER: SP1-2506-457-6

Photopic Flux vs. Wavelength



Photopic Lumens: NR

| λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360 | 0 | NR | 490 | 143 | NR | 620 | 358 | NR | 750 | 9 | NR | 880 | 0 | NR |
| 365 | 0 | NR | 495 | 166 | NR | 625 | 357 | NR | 755 | 7 | NR | 885 | 0 | NR |
| 370 | 0 | NR | 500 | 191 | NR | 630 | 1000 | NR | 760 | 6 | NR | 890 | 0 | NR |
| 375 | 0 | NR | 505 | 210 | NR | 635 | 705 | NR | 765 | 5 | NR | 895 | 0 | NR |
| 380 | 0 | NR | 510 | 223 | NR | 640 | 239 | NR | 770 | 5 | NR | 900 | 0 | NR |
| 385 | 0 | NR | 515 | 233 | NR | 645 | 226 | NR | 775 | 4 | NR | 905 | 0 | NR |
| 390 | 1 | NR | 520 | 240 | NR | 650 | 201 | NR | 780 | 3 | NR | 910 | 0 | NR |
| 395 | 2 | NR | 525 | 246 | NR | 655 | 170 | NR | 785 | 3 | NR | 915 | 0 | NR |
| 400 | 3 | NR | 530 | 251 | NR | 660 | 145 | NR | 790 | 2 | NR | 920 | 0 | NR |
| 405 | 4 | NR | 535 | 260 | NR | 665 | 123 | NR | 795 | 2 | NR | 925 | 0 | NR |
| 410 | 6 | NR | 540 | 267 | NR | 670 | 113 | NR | 800 | 2 | NR | 930 | 0 | NR |
| 415 | 9 | NR | 545 | 276 | NR | 675 | 93 | NR | 805 | 2 | NR | 935 | 0 | NR |
| 420 | 16 | NR | 550 | 284 | NR | 680 | 80 | NR | 810 | 1 | NR | 940 | 0 | NR |
| 425 | 28 | NR | 555 | 294 | NR | 685 | 69 | NR | 815 | 1 | NR | 945 | 0 | NR |
| 430 | 46 | NR | 560 | 303 | NR | 690 | 59 | NR | 820 | 1 | NR | 950 | 0 | NR |
| 435 | 75 | NR | 565 | 313 | NR | 695 | 51 | NR | 825 | 1 | NR | 955 | 0 | NR |
| 440 | 120 | NR | 570 | 319 | NR | 700 | 43 | NR | 830 | 1 | NR | 960 | 0 | NR |
| 445 | 203 | NR | 575 | 327 | NR | 705 | 37 | NR | 835 | 1 | NR | 965 | 0 | NR |
| 450 | 311 | NR | 580 | 336 | NR | 710 | 31 | NR | 840 | 1 | NR | 970 | 0 | NR |
| 455 | 290 | NR | 585 | 344 | NR | 715 | 26 | NR | 845 | 1 | NR | 975 | 0 | NR |
| 460 | 197 | NR | 590 | 349 | NR | 720 | 22 | NR | 850 | 0 | NR | 980 | 0 | NR |
| 465 | 163 | NR | 595 | 350 | NR | 725 | 18 | NR | 855 | 0 | NR | 985 | 0 | NR |
| 470 | 135 | NR | 600 | 355 | NR | 730 | 15 | NR | 860 | 0 | NR | 990 | 0 | NR |
| 475 | 110 | NR | 605 | 357 | NR | 735 | 13 | NR | 865 | 0 | NR | 995 | 0 | NR |
| 480 | 108 | NR | 610 | 391 | NR | 740 | 11 | NR | 870 | 0 | NR | 1000 | 0 | NR |
| 485 | 123 | NR | 615 | 421 | NR | 745 | 10 | NR | 875 | 0 | NR | | | |

REPORT NUMBER: SP1-2506-457-6

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.57

| λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360 | 0 | NR | 490 | 143 | NR | 620 | 358 | NR | 750 | 9 | NR | 880 | 0 | NR |
| 365 | 0 | NR | 495 | 166 | NR | 625 | 357 | NR | 755 | 7 | NR | 885 | 0 | NR |
| 370 | 0 | NR | 500 | 191 | NR | 630 | 1000 | NR | 760 | 6 | NR | 890 | 0 | NR |
| 375 | 0 | NR | 505 | 210 | NR | 635 | 705 | NR | 765 | 5 | NR | 895 | 0 | NR |
| 380 | 0 | NR | 510 | 223 | NR | 640 | 239 | NR | 770 | 5 | NR | 900 | 0 | NR |
| 385 | 0 | NR | 515 | 233 | NR | 645 | 226 | NR | 775 | 4 | NR | 905 | 0 | NR |
| 390 | 1 | NR | 520 | 240 | NR | 650 | 201 | NR | 780 | 3 | NR | 910 | 0 | NR |
| 395 | 2 | NR | 525 | 246 | NR | 655 | 170 | NR | 785 | 3 | NR | 915 | 0 | NR |
| 400 | 3 | NR | 530 | 251 | NR | 660 | 145 | NR | 790 | 2 | NR | 920 | 0 | NR |
| 405 | 4 | NR | 535 | 260 | NR | 665 | 123 | NR | 795 | 2 | NR | 925 | 0 | NR |
| 410 | 6 | NR | 540 | 267 | NR | 670 | 113 | NR | 800 | 2 | NR | 930 | 0 | NR |
| 415 | 9 | NR | 545 | 276 | NR | 675 | 93 | NR | 805 | 2 | NR | 935 | 0 | NR |
| 420 | 16 | NR | 550 | 284 | NR | 680 | 80 | NR | 810 | 1 | NR | 940 | 0 | NR |
| 425 | 28 | NR | 555 | 294 | NR | 685 | 69 | NR | 815 | 1 | NR | 945 | 0 | NR |
| 430 | 46 | NR | 560 | 303 | NR | 690 | 59 | NR | 820 | 1 | NR | 950 | 0 | NR |
| 435 | 75 | NR | 565 | 313 | NR | 695 | 51 | NR | 825 | 1 | NR | 955 | 0 | NR |
| 440 | 120 | NR | 570 | 319 | NR | 700 | 43 | NR | 830 | 1 | NR | 960 | 0 | NR |
| 445 | 203 | NR | 575 | 327 | NR | 705 | 37 | NR | 835 | 1 | NR | 965 | 0 | NR |
| 450 | 311 | NR | 580 | 336 | NR | 710 | 31 | NR | 840 | 1 | NR | 970 | 0 | NR |
| 455 | 290 | NR | 585 | 344 | NR | 715 | 26 | NR | 845 | 1 | NR | 975 | 0 | NR |
| 460 | 197 | NR | 590 | 349 | NR | 720 | 22 | NR | 850 | 0 | NR | 980 | 0 | NR |
| 465 | 163 | NR | 595 | 350 | NR | 725 | 18 | NR | 855 | 0 | NR | 985 | 0 | NR |
| 470 | 135 | NR | 600 | 355 | NR | 730 | 15 | NR | 860 | 0 | NR | 990 | 0 | NR |
| 475 | 110 | NR | 605 | 357 | NR | 735 | 13 | NR | 865 | 0 | NR | 995 | 0 | NR |
| 480 | 108 | NR | 610 | 391 | NR | 740 | 11 | NR | 870 | 0 | NR | 1000 | 0 | NR |
| 485 | 123 | NR | 615 | 421 | NR | 745 | 10 | NR | 875 | 0 | NR | | | |

REPORT NUMBER: SP1-2506-457-6

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 3.17

| λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360 | 0 | NR | 490 | 143 | NR | 620 | 358 | NR | 750 | 9 | NR | 880 | 0 | NR |
| 365 | 0 | NR | 495 | 166 | NR | 625 | 357 | NR | 755 | 7 | NR | 885 | 0 | NR |
| 370 | 0 | NR | 500 | 191 | NR | 630 | 1000 | NR | 760 | 6 | NR | 890 | 0 | NR |
| 375 | 0 | NR | 505 | 210 | NR | 635 | 705 | NR | 765 | 5 | NR | 895 | 0 | NR |
| 380 | 0 | NR | 510 | 223 | NR | 640 | 239 | NR | 770 | 5 | NR | 900 | 0 | NR |
| 385 | 0 | NR | 515 | 233 | NR | 645 | 226 | NR | 775 | 4 | NR | 905 | 0 | NR |
| 390 | 1 | NR | 520 | 240 | NR | 650 | 201 | NR | 780 | 3 | NR | 910 | 0 | NR |
| 395 | 2 | NR | 525 | 246 | NR | 655 | 170 | NR | 785 | 3 | NR | 915 | 0 | NR |
| 400 | 3 | NR | 530 | 251 | NR | 660 | 145 | NR | 790 | 2 | NR | 920 | 0 | NR |
| 405 | 4 | NR | 535 | 260 | NR | 665 | 123 | NR | 795 | 2 | NR | 925 | 0 | NR |
| 410 | 6 | NR | 540 | 267 | NR | 670 | 113 | NR | 800 | 2 | NR | 930 | 0 | NR |
| 415 | 9 | NR | 545 | 276 | NR | 675 | 93 | NR | 805 | 2 | NR | 935 | 0 | NR |
| 420 | 16 | NR | 550 | 284 | NR | 680 | 80 | NR | 810 | 1 | NR | 940 | 0 | NR |
| 425 | 28 | NR | 555 | 294 | NR | 685 | 69 | NR | 815 | 1 | NR | 945 | 0 | NR |
| 430 | 46 | NR | 560 | 303 | NR | 690 | 59 | NR | 820 | 1 | NR | 950 | 0 | NR |
| 435 | 75 | NR | 565 | 313 | NR | 695 | 51 | NR | 825 | 1 | NR | 955 | 0 | NR |
| 440 | 120 | NR | 570 | 319 | NR | 700 | 43 | NR | 830 | 1 | NR | 960 | 0 | NR |
| 445 | 203 | NR | 575 | 327 | NR | 705 | 37 | NR | 835 | 1 | NR | 965 | 0 | NR |
| 450 | 311 | NR | 580 | 336 | NR | 710 | 31 | NR | 840 | 1 | NR | 970 | 0 | NR |
| 455 | 290 | NR | 585 | 344 | NR | 715 | 26 | NR | 845 | 1 | NR | 975 | 0 | NR |
| 460 | 197 | NR | 590 | 349 | NR | 720 | 22 | NR | 850 | 0 | NR | 980 | 0 | NR |
| 465 | 163 | NR | 595 | 350 | NR | 725 | 18 | NR | 855 | 0 | NR | 985 | 0 | NR |
| 470 | 135 | NR | 600 | 355 | NR | 730 | 15 | NR | 860 | 0 | NR | 990 | 0 | NR |
| 475 | 110 | NR | 605 | 357 | NR | 735 | 13 | NR | 865 | 0 | NR | 995 | 0 | NR |
| 480 | 108 | NR | 610 | 391 | NR | 740 | 11 | NR | 870 | 0 | NR | 1000 | 0 | NR |
| 485 | 123 | NR | 615 | 421 | NR | 745 | 10 | NR | 875 | 0 | NR | | | |

Summary

$R_f = 91.4$
 $R_g = 100.2$
 $CIE R_a = 93.9$
 $R_9 = 60.5$




Color Vector Graphics






Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 93 | CES51 = 98 | CES76 = 88 |
| CES02 = 63 | CES27 = 93 | CES52 = 98 | CES77 = 87 |
| CES03 = 31 | CES28 = 96 | CES53 = 97 | CES78 = 85 |
| CES04 = 70 | CES29 = 95 | CES54 = 95 | CES79 = 91 |
| CES05 = 50 | CES30 = 96 | CES55 = 94 | CES80 = 92 |
| CES06 = 51 | CES31 = 95 | CES56 = 96 | CES81 = 75 |
| CES07 = 43 | CES32 = 87 | CES57 = 95 | CES82 = 96 |
| CES08 = 42 | CES33 = 97 | CES58 = 96 | CES83 = 94 |
| CES09 = 29 | CES34 = 94 | CES59 = 98 | CES84 = 95 |
| CES10 = 75 | CES35 = 96 | CES60 = 94 | CES85 = 80 |
| CES11 = 58 | CES36 = 84 | CES61 = 93 | CES86 = 79 |
| CES12 = 64 | CES37 = 95 | CES62 = 89 | CES87 = 91 |
| CES13 = 44 | CES38 = 91 | CES63 = 94 | CES88 = 97 |
| CES14 = 74 | CES39 = 99 | CES64 = 92 | CES89 = 83 |
| CES15 = 72 | CES40 = 97 | CES65 = 90 | CES90 = 98 |
| CES16 = 48 | CES41 = 97 | CES66 = 90 | CES91 = 77 |
| CES17 = 49 | CES42 = 93 | CES67 = 89 | CES92 = 77 |
| CES18 = 56 | CES43 = 92 | CES68 = 89 | CES93 = 86 |
| CES19 = 71 | CES44 = 99 | CES69 = 91 | CES94 = 74 |
| CES20 = 67 | CES45 = 96 | CES70 = 88 | CES95 = 84 |
| CES21 = 86 | CES46 = 96 | CES71 = 84 | CES96 = 92 |
| CES22 = 78 | CES47 = 91 | CES72 = 94 | CES97 = 95 |
| CES23 = 91 | CES48 = 94 | CES73 = 83 | CES98 = 94 |
| CES24 = 90 | CES49 = 94 | CES74 = 91 | CES99 = 92 |
| CES25 = 71 | CES50 = 98 | CES75 = 86 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)