

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: METALUX

Report Number: P976344

Luminaire Tested: 22SR-LD2-20-C-UNV-L935-CD1-U

Issue Date: 03/18/2025

**Test Information**

Test Method: LM-79-2019  
Report Number: P976344  
Test Lab: INNOVATION CENTER(P3)  
Issue Date: 03/18/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: METALUX  
Catalog Number: 22SR-LD2-20-C-UNV-L935-CD1-U  
Description: METALUX SKYRIDGE 2x2 2000LM PACKAGE 90CRI 3500K CURVED REFLECTOR TROFFER  
Light Source: 3500K CCT, 90+ CRI LEDs  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1927.0 lumens  
Efficiency: N/A  
Efficacy: 139.6 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.51 / 1.48  
Luminous Opening: Rectangular (W 2' x L: 2' x H: 0')  
CIE Type: Direct

Input Watts (W): 13.8  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT

TEST NUMBER: P976344  
CATALOG NUMBER: 22SR-LD2-20-C-UNV-L935-CD1-U

### Luminous Intensity Polar Plot





TEST NUMBER: P976344

CATALOG NUMBER: 22SR-LD2-20-C-UNV-L935-CD1-U

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	108	103	98	94	105	100	96	92	96	92	89	92	89	87	88	86	84	82				82
2	98	89	82	75	95	87	80	75	83	78	73	80	75	71	77	73	69	67				67
3	89	78	69	62	86	76	68	62	73	66	61	70	64	59	68	63	58	56				56
4	81	69	59	52	79	67	59	52	65	57	51	62	56	51	60	55	50	48				48
5	74	61	52	45	72	60	51	45	58	50	44	56	49	44	54	48	43	41				41
6	69	55	46	39	67	54	45	39	52	44	39	50	44	38	49	43	38	36				36
7	64	50	41	35	62	49	40	34	47	40	34	46	39	34	45	38	34	32				32
8	59	45	37	31	58	45	36	31	43	36	30	42	35	30	41	35	30	28				28
9	55	42	33	28	54	41	33	27	40	32	27	39	32	27	38	32	27	25				25
10	52	38	30	25	51	38	30	25	37	30	25	36	29	25	35	29	24	23				23

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1577	1577	1577
5°	1567	1524	1567
10°	1558	1602	1687
15°	1543	1678	1821
20°	1526	1742	1926
25°	1502	1776	1985
30°	1474	1787	1996
35°	1437	1777	1962
40°	1395	1748	1897
45°	1347	1718	1818
50°	1279	1688	1751
55°	1212	1679	1707
60°	1131	1678	1693
65°	1037	1696	1715
70°	957	1748	1764
75°	898	1861	1861
80°	872	2041	1900
85°	868	2174	1862

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 40°  
 Vertical Angle: 85°  
 Luminance: 2266 cd/sqm



TEST NUMBER: P976344  
 CATALOG NUMBER: 22SR-LD2-20-C-UNV-L935-CD1-U

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	55.1	2.9
10°-20°	169.2	8.8
20°-30°	270.3	14.0
30°-40°	326.9	17.0
40°-50°	331.6	17.2
50°-60°	298.7	15.5
60°-70°	241.8	12.5
70°-80°	168.8	8.8
80°-90°	64.5	3.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	494.6	25.7
0°-40°	821.6	42.6
0°-60°	1451.9	75.3
0°-90°	1927.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1927.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	586	586	586	586	586	
5°	580	562	564	578	580	55
15°	554	553	602	641	654	156
25°	506	523	598	652	668	233
35°	437	459	541	586	597	274
45°	354	383	451	474	478	272
55°	258	305	358	364	364	230
65°	163	226	266	264	269	162
75°	86	151	179	177	179	92
85°	28	62	70	63	60	31
90°	0	0	0	0	0	



TEST NUMBER: P976344  
 CATALOG NUMBER: 22SR-LD2-20-C-UNV-L935-CD1-U

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	586.1	586.1	586.1	586.1	586.1	586.1	586.1	586.1	586.1	586.1	586.1
2.5°	582.0	583.1	582.0	581.1	580.1	579.1	578.1	576.1	573.0	571.0	569.0
5°	580.1	580.1	576.1	570.0	564.9	562.0	559.0	557.0	557.9	561.0	564.0
7.5°	576.1	574.1	564.9	557.0	552.9	552.9	555.0	562.0	569.0	574.1	577.0
10°	570.0	566.0	552.9	546.9	551.9	555.9	561.0	568.0	572.1	578.1	586.1
12.5°	562.0	555.9	540.8	542.9	552.9	557.9	561.0	567.0	577.0	587.1	595.2
15°	553.9	543.9	530.8	539.9	549.9	552.9	557.0	569.0	580.1	590.1	602.2
17.5°	543.9	530.8	521.7	532.8	541.9	547.9	555.0	567.0	580.1	594.1	607.2
20°	532.8	517.7	512.7	524.8	535.9	542.9	548.9	564.0	579.1	593.2	608.2
22.5°	519.7	501.7	501.7	512.7	526.8	532.8	540.8	557.9	573.0	589.1	604.2
25°	505.7	486.6	488.6	500.6	514.7	522.8	530.8	547.9	566.0	581.1	598.2
27.5°	490.6	470.5	474.5	486.6	499.7	509.7	518.8	536.8	553.9	572.1	589.1
30°	474.5	454.4	457.4	469.5	484.6	494.7	503.7	521.7	539.9	559.0	575.0
32.5°	457.4	437.3	440.3	452.4	468.5	477.6	486.6	504.6	524.8	542.9	557.9
35°	437.3	419.2	422.3	434.3	450.4	459.4	468.5	488.6	506.7	523.8	540.8
37.5°	417.2	400.1	402.1	415.2	432.3	441.4	450.4	469.5	487.6	504.6	520.8
40°	397.1	381.0	384.1	396.1	413.1	421.2	430.2	450.4	468.5	484.6	497.6
42.5°	375.0	361.9	364.9	377.0	393.1	402.1	412.2	430.2	447.3	462.4	474.5
45°	353.9	342.8	344.8	356.9	373.0	383.0	392.1	411.1	427.3	439.4	451.4
47.5°	329.7	320.7	325.7	337.8	353.9	362.9	373.0	391.1	405.2	418.2	428.2
50°	305.6	298.6	304.7	317.7	333.7	344.8	353.9	369.9	384.1	396.1	403.2
52.5°	281.5	278.4	284.5	297.5	314.6	323.8	332.8	349.9	363.9	374.0	381.0
55°	258.4	256.4	264.4	278.4	296.6	304.7	313.7	329.7	342.8	351.9	357.9
57.5°	233.2	234.3	243.3	259.3	276.4	285.5	293.5	308.6	321.7	328.8	334.8
60°	210.1	211.1	223.1	239.3	257.3	266.4	274.4	288.5	299.6	306.7	311.7
62.5°	185.0	191.0	204.1	219.2	237.3	246.3	255.4	268.5	279.5	285.5	288.5
65°	162.8	169.9	185.0	201.1	219.2	226.2	235.2	248.3	257.3	263.4	266.4
67.5°	141.7	150.8	165.9	183.0	200.1	209.1	216.1	228.2	236.3	241.3	244.3
70°	121.6	132.7	148.8	164.9	181.0	189.0	196.1	208.1	215.2	220.2	222.2
72.5°	103.5	114.6	131.7	146.8	161.9	170.9	177.0	188.0	195.0	199.0	200.1
75°	86.4	98.5	113.6	128.7	143.7	150.8	157.8	166.9	173.9	177.9	179.0
77.5°	71.3	82.5	97.6	111.6	124.6	130.7	137.7	146.8	152.9	155.8	156.8
80°	56.3	67.4	80.5	93.5	105.5	109.6	115.6	123.7	130.7	131.7	131.7
82.5°	42.2	52.2	63.4	74.4	84.5	88.4	92.5	99.6	103.5	104.6	103.5
85°	28.1	35.1	43.2	51.3	59.3	62.3	66.3	71.3	71.3	73.4	70.4
87.5°	14.1	17.1	22.1	25.2	30.1	32.2	34.2	35.1	35.1	35.1	34.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P976344  
 CATALOG NUMBER: 22SR-LD2-20-C-UNV-L935-CD1-U

**CANDELA DISTRIBUTION (continued):**

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°
0°	586.1	586.1	586.1	586.1	586.1	586.1	586.1	586.1	586.1	586.1
2.5°	567.0	566.0	564.0	564.0	564.0	563.0	563.0	563.0	562.0	562.0
5°	568.0	571.0	575.0	578.1	578.1	578.1	579.1	579.1	580.1	580.1
7.5°	580.1	583.1	587.1	590.1	592.1	593.2	596.2	597.2	599.1	599.1
10°	594.1	599.1	604.2	607.2	610.3	612.3	613.2	617.3	617.3	617.3
12.5°	603.2	611.2	618.2	625.3	628.3	630.3	633.3	635.3	638.4	638.4
15°	613.2	622.3	630.3	638.4	641.4	644.4	648.5	651.5	652.4	653.5
17.5°	618.2	629.4	638.4	646.5	649.4	652.4	658.5	662.5	664.5	665.6
20°	620.3	632.3	643.4	652.4	656.4	659.5	665.6	669.5	672.6	672.6
22.5°	619.3	631.4	643.4	653.5	657.5	660.5	666.5	670.6	672.6	673.5
25°	614.3	626.3	638.4	648.5	652.4	655.5	661.5	665.6	668.5	668.5
27.5°	604.2	617.3	628.3	638.4	641.4	646.5	651.5	655.5	658.5	659.5
30°	590.1	603.2	615.3	623.3	627.4	630.3	635.3	640.4	641.4	642.4
32.5°	573.0	586.1	596.2	604.2	608.2	611.2	616.2	620.3	622.3	621.3
35°	553.9	564.9	575.0	583.1	586.1	588.1	593.2	595.2	597.2	597.2
37.5°	532.8	541.9	551.9	557.9	560.0	562.0	566.0	569.0	569.0	570.0
40°	507.7	517.7	524.8	530.8	532.8	533.8	537.9	538.8	539.9	539.9
42.5°	484.6	492.6	497.6	501.7	503.7	505.7	507.7	507.7	507.7	508.7
45°	459.4	465.5	470.5	473.5	474.5	475.6	476.5	477.6	477.6	477.6
47.5°	435.3	440.3	443.4	446.4	446.4	447.3	447.3	448.4	448.4	448.4
50°	409.2	413.1	415.2	417.2	417.2	417.2	418.2	418.2	418.2	418.2
52.5°	385.0	388.1	389.0	390.1	390.1	391.1	391.1	390.1	391.1	390.1
55°	360.9	362.9	363.9	362.9	363.9	363.9	363.9	362.9	363.9	363.9
57.5°	336.8	337.8	337.8	336.8	337.8	336.8	336.8	337.8	338.8	338.8
60°	312.6	312.6	311.7	311.7	311.7	311.7	311.7	313.7	313.7	314.6
62.5°	289.6	289.6	288.5	287.6	287.6	287.6	288.5	289.6	290.5	290.5
65°	266.4	266.4	265.4	264.4	264.4	264.4	265.4	266.4	267.4	269.4
67.5°	245.3	243.3	243.3	242.2	242.2	242.2	244.3	245.3	246.3	246.3
70°	221.2	221.2	219.2	220.2	220.2	220.2	221.2	222.2	223.1	224.2
72.5°	200.1	199.0	198.1	199.0	199.0	199.0	200.1	202.1	203.1	204.1
75°	179.0	177.9	177.9	177.0	177.0	177.9	177.9	179.0	179.0	179.0
77.5°	156.8	153.8	152.9	150.8	150.8	150.8	150.8	150.8	150.8	150.8
80°	130.7	126.6	123.7	123.7	122.6	122.6	122.6	122.6	121.6	122.6
82.5°	100.5	98.5	95.5	94.5	94.5	94.5	92.5	92.5	92.5	94.5
85°	68.4	67.4	64.3	63.4	63.4	62.3	61.4	61.4	62.3	60.3
87.5°	33.2	32.2	30.1	30.1	30.1	29.2	29.2	28.1	29.2	28.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P976344  
 CATALOG NUMBER: 22SR-LD2-20-C-UNV-L935-CD1-U

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room Dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.6	14.3	13.0	14.6	14.9	14.1	15.8	14.5	16.1	16.4
	3H	14.3	15.9	14.7	16.2	16.6	16.3	17.8	16.7	18.2	18.5
	4H	15.0	16.5	15.4	16.8	17.2	17.3	18.8	17.7	19.1	19.5
	6H	15.5	16.9	15.9	17.2	17.6	18.2	19.5	18.6	19.9	20.2
	8H	15.7	17.0	16.2	17.4	17.8	18.5	19.8	18.9	20.1	20.5
	12H	15.9	17.1	16.3	17.5	17.9	18.7	19.9	19.1	20.3	20.8
4H	2H	13.8	15.2	14.2	15.6	15.9	14.9	16.3	15.3	16.6	17.0
	3H	15.9	17.1	16.3	17.5	17.9	17.3	18.5	17.7	18.9	19.3
	4H	16.8	17.9	17.3	18.3	18.8	18.4	19.6	18.9	20.0	20.4
	6H	17.6	18.5	18.0	19.0	19.4	19.4	20.4	19.9	20.9	21.3
	8H	17.8	18.7	18.3	19.2	19.6	19.8	20.7	20.3	21.2	21.7
	12H	18.0	18.8	18.5	19.3	19.8	20.1	21.0	20.6	21.4	21.9
8H	4H	17.6	18.5	18.1	19.0	19.4	18.9	19.8	19.4	20.3	20.7
	6H	18.7	19.4	19.1	19.9	20.4	20.1	20.9	20.6	21.3	21.8
	8H	19.1	19.8	19.6	20.3	20.8	20.6	21.3	21.1	21.8	22.3
	12H	19.4	20.0	19.9	20.5	21.1	21.0	21.6	21.5	22.1	22.7
12H	4H	17.7	18.6	18.2	19.0	19.5	19.0	19.8	19.5	20.3	20.8
	6H	18.9	19.6	19.4	20.0	20.6	20.2	20.9	20.8	21.4	21.9
	8H	19.5	20.1	20.0	20.6	21.1	20.8	21.4	21.3	21.9	22.5

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2506-457-6

Test Date: 07/01/2025

Luminaire Tested: 24SR-LD2-64-C-UNV-L935-CD1-U

Data in this report applies to families of products including 24SR-LD2-64-C-UNV-L935-CD1-U

**Test Information**

Test Method: LM-79-2019  
 Report Number: SP1-2506-457-6  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry: 4π  
 Issue Date: 07/02/2025  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: Metalux  
 Catalog Number: **24SR-LD2-64-C-UNV-L935-CD1-U**  
 Description: 2X4 SKYRIDGE 6400LM Fixture with new LTN chip

**Spectral Parameters**

CCT (K): 3329  
 CIE u': 0.2411  
 CIE v': 0.5118  
 Duv: -0.0021  
 CIE x: 0.4128  
 CIE y: 0.3894  
 CIE z: 0.1979  
 Peak Wavelength (nm): 630  
 Dominant Wavelength (nm): 582  
 Purity: 40.74075  
 Rf: 91.4  
 Rg: 100.2

CRI (Ra):	93.9		
R1:	95.4	R9:	60.5
R2:	97.4	R10:	92.5
R3:	97.7	R11:	95.9
R4:	94.9	R12:	82.0
R5:	95.1	R13:	96.0
R6:	95.7	R14:	98.0
R7:	91.7	R15:	91.5
R8:	83.2		



**Test Conditions**

Stabilization Time: 48M  
 Operation Time: 1H 48M  
 Sphere Temperature (°C): 24.0

REPORT NUMBER: SP1-2506-457-6

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2506-457-6

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



CCT = 3329K  
 CIE x = 0.4128  
 CIE y = 0.3894  
 Duv = -0.0021

Point lies inside the ANSI 3500K 7-step quadrangle

REPORT NUMBER: SP1-2506-457-6

**Photopic Flux vs. Wavelength**



**Photopic Lumens: NR**

$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)	$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)	$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)	$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)	$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)
360	0	NR	490	143	NR	620	358	NR	750	9	NR	880	0	NR
365	0	NR	495	166	NR	625	357	NR	755	7	NR	885	0	NR
370	0	NR	500	191	NR	630	1000	NR	760	6	NR	890	0	NR
375	0	NR	505	210	NR	635	705	NR	765	5	NR	895	0	NR
380	0	NR	510	223	NR	640	239	NR	770	5	NR	900	0	NR
385	0	NR	515	233	NR	645	226	NR	775	4	NR	905	0	NR
390	1	NR	520	240	NR	650	201	NR	780	3	NR	910	0	NR
395	2	NR	525	246	NR	655	170	NR	785	3	NR	915	0	NR
400	3	NR	530	251	NR	660	145	NR	790	2	NR	920	0	NR
405	4	NR	535	260	NR	665	123	NR	795	2	NR	925	0	NR
410	6	NR	540	267	NR	670	113	NR	800	2	NR	930	0	NR
415	9	NR	545	276	NR	675	93	NR	805	2	NR	935	0	NR
420	16	NR	550	284	NR	680	80	NR	810	1	NR	940	0	NR
425	28	NR	555	294	NR	685	69	NR	815	1	NR	945	0	NR
430	46	NR	560	303	NR	690	59	NR	820	1	NR	950	0	NR
435	75	NR	565	313	NR	695	51	NR	825	1	NR	955	0	NR
440	120	NR	570	319	NR	700	43	NR	830	1	NR	960	0	NR
445	203	NR	575	327	NR	705	37	NR	835	1	NR	965	0	NR
450	311	NR	580	336	NR	710	31	NR	840	1	NR	970	0	NR
455	290	NR	585	344	NR	715	26	NR	845	1	NR	975	0	NR
460	197	NR	590	349	NR	720	22	NR	850	0	NR	980	0	NR
465	163	NR	595	350	NR	725	18	NR	855	0	NR	985	0	NR
470	135	NR	600	355	NR	730	15	NR	860	0	NR	990	0	NR
475	110	NR	605	357	NR	735	13	NR	865	0	NR	995	0	NR
480	108	NR	610	391	NR	740	11	NR	870	0	NR	1000	0	NR
485	123	NR	615	421	NR	745	10	NR	875	0	NR			

REPORT NUMBER: SP1-2506-457-6

**Scotopic Flux vs. Wavelength**



**Scotopic Lumens: NR**

**S/P: 1.57**

$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)	$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)	$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)	$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)	$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)
360	0	NR	490	143	NR	620	358	NR	750	9	NR	880	0	NR
365	0	NR	495	166	NR	625	357	NR	755	7	NR	885	0	NR
370	0	NR	500	191	NR	630	1000	NR	760	6	NR	890	0	NR
375	0	NR	505	210	NR	635	705	NR	765	5	NR	895	0	NR
380	0	NR	510	223	NR	640	239	NR	770	5	NR	900	0	NR
385	0	NR	515	233	NR	645	226	NR	775	4	NR	905	0	NR
390	1	NR	520	240	NR	650	201	NR	780	3	NR	910	0	NR
395	2	NR	525	246	NR	655	170	NR	785	3	NR	915	0	NR
400	3	NR	530	251	NR	660	145	NR	790	2	NR	920	0	NR
405	4	NR	535	260	NR	665	123	NR	795	2	NR	925	0	NR
410	6	NR	540	267	NR	670	113	NR	800	2	NR	930	0	NR
415	9	NR	545	276	NR	675	93	NR	805	2	NR	935	0	NR
420	16	NR	550	284	NR	680	80	NR	810	1	NR	940	0	NR
425	28	NR	555	294	NR	685	69	NR	815	1	NR	945	0	NR
430	46	NR	560	303	NR	690	59	NR	820	1	NR	950	0	NR
435	75	NR	565	313	NR	695	51	NR	825	1	NR	955	0	NR
440	120	NR	570	319	NR	700	43	NR	830	1	NR	960	0	NR
445	203	NR	575	327	NR	705	37	NR	835	1	NR	965	0	NR
450	311	NR	580	336	NR	710	31	NR	840	1	NR	970	0	NR
455	290	NR	585	344	NR	715	26	NR	845	1	NR	975	0	NR
460	197	NR	590	349	NR	720	22	NR	850	0	NR	980	0	NR
465	163	NR	595	350	NR	725	18	NR	855	0	NR	985	0	NR
470	135	NR	600	355	NR	730	15	NR	860	0	NR	990	0	NR
475	110	NR	605	357	NR	735	13	NR	865	0	NR	995	0	NR
480	108	NR	610	391	NR	740	11	NR	870	0	NR	1000	0	NR
485	123	NR	615	421	NR	745	10	NR	875	0	NR			

REPORT NUMBER: SP1-2506-457-6

Melanopic Flux vs. Wavelength




Melanopic Lumens: NR

M/P: 3.17



λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)
360	0	NR	490	143	NR	620	358	NR	750	9	NR	880	0	NR
365	0	NR	495	166	NR	625	357	NR	755	7	NR	885	0	NR
370	0	NR	500	191	NR	630	1000	NR	760	6	NR	890	0	NR
375	0	NR	505	210	NR	635	705	NR	765	5	NR	895	0	NR
380	0	NR	510	223	NR	640	239	NR	770	5	NR	900	0	NR
385	0	NR	515	233	NR	645	226	NR	775	4	NR	905	0	NR
390	1	NR	520	240	NR	650	201	NR	780	3	NR	910	0	NR
395	2	NR	525	246	NR	655	170	NR	785	3	NR	915	0	NR
400	3	NR	530	251	NR	660	145	NR	790	2	NR	920	0	NR
405	4	NR	535	260	NR	665	123	NR	795	2	NR	925	0	NR
410	6	NR	540	267	NR	670	113	NR	800	2	NR	930	0	NR
415	9	NR	545	276	NR	675	93	NR	805	2	NR	935	0	NR
420	16	NR	550	284	NR	680	80	NR	810	1	NR	940	0	NR
425	28	NR	555	294	NR	685	69	NR	815	1	NR	945	0	NR
430	46	NR	560	303	NR	690	59	NR	820	1	NR	950	0	NR
435	75	NR	565	313	NR	695	51	NR	825	1	NR	955	0	NR
440	120	NR	570	319	NR	700	43	NR	830	1	NR	960	0	NR
445	203	NR	575	327	NR	705	37	NR	835	1	NR	965	0	NR
450	311	NR	580	336	NR	710	31	NR	840	1	NR	970	0	NR
455	290	NR	585	344	NR	715	26	NR	845	1	NR	975	0	NR
460	197	NR	590	349	NR	720	22	NR	850	0	NR	980	0	NR
465	163	NR	595	350	NR	725	18	NR	855	0	NR	985	0	NR
470	135	NR	600	355	NR	730	15	NR	860	0	NR	990	0	NR
475	110	NR	605	357	NR	735	13	NR	865	0	NR	995	0	NR
480	108	NR	610	391	NR	740	11	NR	870	0	NR	1000	0	NR
485	123	NR	615	421	NR	745	10	NR	875	0	NR			

**Summary**

$R_f = 91.4$   
 $R_g = 100.2$   
 $CIE R_a = 93.9$   
 $R_9 = 60.5$




**Color Vector Graphics**



**Individual Sample Fidelity Index ( $R_{f,i}$ )**


CES01 = 86	CES26 = 93	CES51 = 98	CES76 = 88
CES02 = 63	CES27 = 93	CES52 = 98	CES77 = 87
CES03 = 31	CES28 = 96	CES53 = 97	CES78 = 85
CES04 = 70	CES29 = 95	CES54 = 95	CES79 = 91
CES05 = 50	CES30 = 96	CES55 = 94	CES80 = 92
CES06 = 51	CES31 = 95	CES56 = 96	CES81 = 75
CES07 = 43	CES32 = 87	CES57 = 95	CES82 = 96
CES08 = 42	CES33 = 97	CES58 = 96	CES83 = 94
CES09 = 29	CES34 = 94	CES59 = 98	CES84 = 95
CES10 = 75	CES35 = 96	CES60 = 94	CES85 = 80
CES11 = 58	CES36 = 84	CES61 = 93	CES86 = 79
CES12 = 64	CES37 = 95	CES62 = 89	CES87 = 91
CES13 = 44	CES38 = 91	CES63 = 94	CES88 = 97
CES14 = 74	CES39 = 99	CES64 = 92	CES89 = 83
CES15 = 72	CES40 = 97	CES65 = 90	CES90 = 98
CES16 = 48	CES41 = 97	CES66 = 90	CES91 = 77
CES17 = 49	CES42 = 93	CES67 = 89	CES92 = 77
CES18 = 56	CES43 = 92	CES68 = 89	CES93 = 86
CES19 = 71	CES44 = 99	CES69 = 91	CES94 = 74
CES20 = 67	CES45 = 96	CES70 = 88	CES95 = 84
CES21 = 86	CES46 = 96	CES71 = 84	CES96 = 92
CES22 = 78	CES47 = 91	CES72 = 94	CES97 = 95
CES23 = 91	CES48 = 94	CES73 = 83	CES98 = 94
CES24 = 90	CES49 = 94	CES74 = 91	CES99 = 92
CES25 = 71	CES50 = 98	CES75 = 86	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)