

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: METALUX

Report Number: P976585

Luminaire Tested: 22SR-LD2-C-29-UNV-L840-CD1-PL-U

Issue Date: 03/18/2025

Test Information

Test Method: LM-79-2019
Report Number: P976585
Test Lab: INNOVATION CENTER(P3)
Issue Date: 03/18/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: METALUX
Catalog Number: 22SR-LD2-C-29-UNV-L840-CD1-PL-U
Description: METALUX SKYRIDGE 2x2 2900LM PACKAGE 80CRI 4000K TROFFER with Pearl SKYTRIM
Light Source: 4000K CCT, 80+ CRI LEDS
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2648.0 lumens
Efficiency: N/A
Efficacy: 130.4 lumens/watt
Spacing Criteria (0/90/45): 1.3 / 2 / 1.87
Luminous Opening: Rectangular (W 2' x L: 2' x H: 0')
CIE Type: Direct

Input Watts (W): 20.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

TEST NUMBER: P976585
CATALOG NUMBER: 22SR-LD2-C-29-UNV-L840-CD1-PL-U

Luminous Intensity Polar Plot





TEST NUMBER: P976585

CATALOG NUMBER: 22SR-LD2-C-29-UNV-L840-CD1-PL-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	106	100	95	90	103	98	93	88	93	89	85	89	86	83	85	83	80	85	83	80	78
2	95	85	77	70	92	83	76	69	79	73	68	76	71	66	73	68	64	73	68	64	62
3	85	73	64	56	83	72	63	56	69	61	55	66	59	54	63	57	53	63	57	53	50
4	78	64	54	47	75	63	53	46	60	52	46	58	51	45	55	49	44	55	49	44	42
5	71	57	47	39	69	55	46	39	53	45	39	51	44	38	49	43	38	49	43	38	35
6	65	51	41	34	63	50	40	34	48	39	33	46	39	33	44	38	33	44	38	33	30
7	60	46	36	29	58	45	36	29	43	35	29	42	34	29	40	34	28	40	34	28	26
8	56	41	32	26	54	41	32	26	39	31	26	38	31	25	37	30	25	37	30	25	23
9	52	38	29	23	51	37	29	23	36	28	23	35	28	23	34	27	22	34	27	22	20
10	49	35	26	21	47	34	26	21	33	26	20	32	25	20	31	25	20	31	25	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1285	1285	1285
5°	1292	1350	1421
10°	1296	1538	1694
15°	1301	1724	1959
20°	1303	1883	2180
25°	1303	2016	2363
30°	1303	2119	2486
35°	1307	2187	2548
40°	1309	2238	2570
45°	1317	2285	2564
50°	1317	2352	2565
55°	1323	2459	2622
60°	1320	2618	2755
65°	1322	2845	2988
70°	1338	3163	3307
75°	1354	3640	3703
80°	1418	4307	4259
85°	1572	5502	5626

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 85°
 Vertical Angle: 87.5°
 Luminance: 7348 cd/sqm



TEST NUMBER: P976585
 CATALOG NUMBER: 22SR-LD2-C-29-UNV-L840-CD1-PL-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.5	1.9
10°-20°	171.0	6.5
20°-30°	300.4	11.3
30°-40°	395.4	14.9
40°-50°	434.9	16.4
50°-60°	430.9	16.3
60°-70°	396.6	15.0
70°-80°	318.0	12.0
80°-90°	151.2	5.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	520.9	19.7
0°-40°	916.3	34.6
0°-60°	1782.2	67.3
0°-90°	2648.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2648.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	477	477	477	477	477	
5°	478	480	500	520	526	46
15°	467	528	619	680	703	132
25°	439	548	679	765	796	202
35°	398	529	666	749	776	249
45°	346	481	600	658	674	267
55°	282	419	524	555	559	252
65°	208	349	447	462	469	206
75°	130	262	350	355	356	138
85°	51	124	178	179	182	53
90°	0	0	0	0	0	



TEST NUMBER: P976585
 CATALOG NUMBER: 22SR-LD2-C-29-UNV-L840-CD1-PL-U

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	477.4	477.4	477.4	477.4	477.4	477.4	477.4	477.4	477.4	477.4	477.4
2.5°	478.4	479.4	478.4	478.4	478.4	478.4	478.4	478.4	478.4	478.4	479.4
5°	478.4	478.4	478.4	478.4	478.4	481.4	484.5	488.5	494.6	499.7	505.8
7.5°	477.4	477.4	477.4	478.4	484.5	492.5	502.8	512.9	524.1	533.3	541.5
10°	474.2	474.2	475.3	482.4	493.6	508.9	523.2	537.3	549.5	562.8	576.0
12.5°	472.3	472.3	475.3	488.5	505.8	525.1	542.4	559.8	577.1	592.3	607.6
15°	467.1	467.1	474.2	493.6	517.1	538.4	559.8	580.1	600.5	618.8	636.2
17.5°	462.0	462.0	473.2	498.6	524.1	548.5	573.1	597.5	619.8	640.2	659.5
20°	454.9	455.9	472.3	500.7	528.3	556.7	584.2	609.7	635.1	657.5	678.9
22.5°	447.9	448.8	470.2	501.8	531.2	561.8	591.4	619.8	646.3	669.7	693.0
25°	438.7	441.8	466.2	499.7	532.3	563.8	595.4	624.9	653.4	678.9	702.3
27.5°	429.4	433.6	461.0	495.7	530.2	562.8	595.4	626.9	655.4	682.9	706.3
30°	419.3	424.4	454.9	490.6	526.2	559.8	593.3	624.9	654.5	681.9	705.2
32.5°	409.2	414.2	446.8	483.5	519.0	553.7	587.2	619.8	648.4	675.8	700.2
35°	398.0	405.0	438.7	475.3	511.9	546.6	580.1	611.6	640.2	665.6	689.0
37.5°	384.8	393.9	427.5	465.1	501.8	536.3	568.9	600.5	628.0	652.4	674.7
40°	372.6	382.7	417.2	454.0	490.6	525.1	556.7	587.2	613.7	637.1	658.5
42.5°	360.4	371.5	405.0	441.8	477.4	511.9	543.4	572.0	597.5	618.8	639.2
45°	346.1	358.3	391.8	428.5	464.1	497.7	528.3	555.6	581.1	600.5	618.8
47.5°	330.7	345.0	378.7	415.3	449.8	482.4	512.9	538.4	561.8	582.1	598.5
50°	314.5	330.7	364.4	401.0	434.6	467.1	496.7	522.2	543.4	561.8	577.1
52.5°	299.2	315.6	349.0	384.8	419.3	451.9	480.3	504.7	525.1	543.4	556.7
55°	281.9	299.2	333.9	368.4	403.1	434.6	463.1	487.5	506.8	524.1	536.3
57.5°	264.7	283.0	316.5	352.2	385.7	418.3	446.8	470.2	489.6	504.7	516.1
60°	245.3	265.7	299.2	334.9	369.4	401.0	429.4	452.9	471.3	486.4	495.7
62.5°	227.0	247.4	283.0	317.5	351.1	383.7	412.2	434.6	452.9	467.1	475.3
65°	207.6	228.9	263.6	299.2	332.8	365.4	392.8	416.3	433.6	446.8	454.9
67.5°	189.3	210.6	244.3	278.9	312.4	346.1	372.6	394.9	412.2	425.4	432.6
70°	170.0	191.3	224.9	257.5	292.0	323.6	351.1	373.5	389.8	402.0	409.2
72.5°	150.6	173.0	203.6	237.1	269.7	302.3	327.8	350.1	366.5	377.6	383.7
75°	130.2	152.7	183.2	212.7	246.3	277.9	303.4	324.6	340.0	350.1	355.2
77.5°	110.9	131.3	160.8	190.4	219.8	250.4	274.8	296.2	308.4	317.5	322.7
80°	91.5	109.8	136.3	163.9	190.4	218.8	241.3	260.5	272.7	277.9	280.9
82.5°	72.2	88.6	109.0	133.4	156.7	180.1	200.5	216.7	226.0	233.1	235.0
85°	50.9	61.0	77.4	94.7	114.0	133.4	151.7	163.9	173.0	178.2	179.1
87.5°	26.5	30.5	38.7	48.8	63.1	76.4	86.5	94.7	101.8	106.9	111.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P976585

CATALOG NUMBER: 22SR-LD2-C-29-UNV-L840-CD1-PL-U

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	477.4	477.4	477.4	477.4	477.4	477.4	477.4	477.4
2.5°	479.4	479.4	481.4	481.4	482.4	482.4	481.4	482.4
5°	510.0	514.0	520.1	520.1	524.1	526.2	526.2	526.2
7.5°	547.6	553.7	560.9	564.9	569.9	573.1	574.0	574.0
10°	584.2	593.3	601.5	607.6	613.7	616.8	619.8	619.8
12.5°	618.8	629.9	640.2	648.4	655.4	659.5	662.5	663.6
15°	650.3	664.6	674.7	685.0	693.0	698.2	701.2	703.3
17.5°	676.8	692.1	704.3	714.5	723.7	729.8	734.9	735.9
20°	697.2	713.4	727.7	738.9	749.0	755.3	760.3	761.4
22.5°	712.4	730.7	746.0	758.2	768.4	775.5	779.7	781.6
25°	722.7	741.0	758.2	771.5	782.6	789.8	792.9	795.9
27.5°	727.7	747.1	764.3	777.6	788.7	795.9	799.9	800.9
30°	727.7	746.0	763.3	776.5	786.7	793.8	798.0	799.9
32.5°	720.6	738.9	755.3	768.4	777.6	784.7	788.7	790.8
35°	709.4	726.7	742.9	754.2	764.3	769.4	774.5	775.5
37.5°	694.1	710.4	725.6	735.9	745.0	750.0	754.2	755.3
40°	675.8	691.1	704.3	713.4	721.6	726.7	729.8	731.7
42.5°	655.4	668.6	679.9	688.0	694.1	699.1	701.2	703.3
45°	633.0	644.2	654.5	661.5	666.7	669.7	672.8	673.8
47.5°	610.7	620.8	629.0	635.1	637.1	640.2	641.2	642.3
50°	588.2	596.4	603.6	606.6	609.7	611.6	611.6	612.7
52.5°	565.9	574.0	577.1	581.1	583.2	584.2	584.2	584.2
55°	544.5	550.6	553.7	555.6	556.7	558.8	558.8	558.8
57.5°	524.1	528.3	529.3	531.2	532.3	534.4	534.4	534.4
60°	501.8	505.8	506.8	507.9	508.9	510.8	511.9	511.9
62.5°	481.4	484.5	483.5	485.5	486.4	488.5	490.6	491.6
65°	459.0	461.0	461.0	462.0	465.1	466.2	468.1	469.2
67.5°	436.6	437.6	437.6	439.7	441.8	443.7	444.8	445.8
70°	411.1	413.2	412.2	414.2	416.3	418.3	420.3	420.3
72.5°	384.8	385.7	386.7	385.7	387.7	389.8	390.9	391.8
75°	354.1	356.2	356.2	354.1	355.2	355.2	356.2	356.2
77.5°	318.5	317.5	314.5	312.4	312.4	313.5	313.5	314.5
80°	277.9	275.8	273.7	271.8	271.8	272.7	272.7	274.8
82.5°	233.1	231.0	228.9	228.0	228.9	228.9	230.0	231.0
85°	180.1	177.1	180.1	178.2	180.1	180.1	180.1	182.2
87.5°	111.9	113.0	116.0	115.1	114.0	115.1	119.1	117.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P976585
 CATALOG NUMBER: 22SR-LD2-C-29-UNV-L840-CD1-PL-U

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room Dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.7	15.4	14.0	15.8	16.1	16.1	17.9	16.4	18.2	18.5
	3H	15.6	17.2	16.0	17.6	17.9	18.8	20.4	19.2	20.8	21.1
	4H	16.4	18.0	16.8	18.3	18.7	20.1	21.6	20.5	22.0	22.4
	6H	17.1	18.5	17.5	18.9	19.3	21.3	22.7	21.7	23.1	23.5
	8H	17.3	18.7	17.7	19.1	19.5	21.8	23.2	22.2	23.6	24.0
	12H	17.5	18.8	17.9	19.2	19.7	22.3	23.6	22.7	24.0	24.4
4H	2H	15.3	16.8	15.7	17.2	17.5	16.9	18.4	17.3	18.8	19.2
	3H	17.7	19.0	18.1	19.4	19.8	19.9	21.2	20.3	21.6	22.0
	4H	18.8	20.0	19.2	20.4	20.8	21.4	22.6	21.8	23.0	23.4
	6H	19.6	20.7	20.1	21.1	21.6	22.7	23.8	23.1	24.2	24.7
	8H	19.9	20.9	20.4	21.4	21.8	23.3	24.3	23.8	24.8	25.2
	12H	20.2	21.1	20.6	21.6	22.0	23.9	24.9	24.4	25.3	25.8
8H	4H	19.9	20.9	20.4	21.4	21.8	21.9	22.9	22.4	23.4	23.8
	6H	21.2	22.0	21.7	22.5	23.0	23.5	24.4	24.0	24.8	25.3
	8H	21.7	22.5	22.2	23.0	23.4	24.2	25.0	24.7	25.5	26.0
	12H	22.1	22.8	22.6	23.3	23.8	25.0	25.7	25.5	26.2	26.7
12H	4H	20.2	21.1	20.6	21.6	22.0	22.0	22.9	22.5	23.4	23.9
	6H	21.6	22.4	22.1	22.8	23.4	23.7	24.5	24.2	24.9	25.5
	8H	22.3	23.0	22.8	23.4	24.0	24.5	25.2	25.0	25.7	26.3

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2506-457-7

Test Date: 07/02/2025

Luminaire Tested: 24SR-LD2-64-C-UNV-L940-CD1-U

Data in this report applies to families of products including 24SR-LD2-64-C-UNV-L940-CD1-U

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2506-457-7
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 07/02/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Metalux
 Catalog Number: **24SR-LD2-64-C-UNV-L940-CD1-U**
 Description: 2X4 SKYRIDGE 6400LM Fixture with new LTN chip

Spectral Parameters

CCT (K): 3850
 CIE u': 0.2283
 CIE v': 0.5037
 Duv: -0.0006
 CIE x: 0.3868
 CIE y: 0.3794
 CIE z: 0.2338
 Peak Wavelength (nm): 630
 Dominant Wavelength (nm): 579
 Purity: 29.94798
 Rf: 91.3
 Rg: 99.8

CRI (Ra): 94.0
 R1: 95.3
 R2: 96.3
 R3: 95.7
 R4: 95.2
 R5: 94.4
 R6: 94.3
 R7: 94.1
 R8: 86.7
 R9: 65.3
 R10: 89.6
 R11: 95.5
 R12: 76.1
 R13: 95.5
 R14: 96.8
 R15: 92.3



Test Conditions


Stabilization Time: 38M
 Operation Time: 1H 38M
 Sphere Temperature (°C): 24.4

REPORT NUMBER: SP1-2506-457-7

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2506-457-7

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



CCT = 3850K
 CIE x = 0.3868
 CIE y = 0.3794
 Duv = -0.0006

Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2506-457-7

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	173	NR	620	343	NR	750	8	NR	880	0	NR
365	0	NR	495	201	NR	625	342	NR	755	7	NR	885	0	NR
370	0	NR	500	231	NR	630	1000	NR	760	6	NR	890	0	NR
375	0	NR	505	253	NR	635	692	NR	765	5	NR	895	0	NR
380	0	NR	510	268	NR	640	226	NR	770	4	NR	900	0	NR
385	1	NR	515	277	NR	645	214	NR	775	4	NR	905	0	NR
390	1	NR	520	284	NR	650	190	NR	780	3	NR	910	0	NR
395	3	NR	525	290	NR	655	160	NR	785	3	NR	915	0	NR
400	4	NR	530	296	NR	660	136	NR	790	2	NR	920	0	NR
405	5	NR	535	303	NR	665	115	NR	795	2	NR	925	0	NR
410	8	NR	540	310	NR	670	106	NR	800	2	NR	930	0	NR
415	13	NR	545	316	NR	675	87	NR	805	2	NR	935	0	NR
420	22	NR	550	323	NR	680	75	NR	810	1	NR	940	0	NR
425	37	NR	555	330	NR	685	64	NR	815	1	NR	945	0	NR
430	62	NR	560	335	NR	690	55	NR	820	1	NR	950	0	NR
435	102	NR	565	340	NR	695	47	NR	825	1	NR	955	0	NR
440	164	NR	570	342	NR	700	40	NR	830	1	NR	960	0	NR
445	281	NR	575	345	NR	705	34	NR	835	1	NR	965	0	NR
450	423	NR	580	348	NR	710	29	NR	840	1	NR	970	0	NR
455	384	NR	585	350	NR	715	25	NR	845	1	NR	975	0	NR
460	256	NR	590	351	NR	720	21	NR	850	0	NR	980	0	NR
465	208	NR	595	348	NR	725	17	NR	855	0	NR	985	0	NR
470	169	NR	600	348	NR	730	14	NR	860	0	NR	990	0	NR
475	135	NR	605	347	NR	735	12	NR	865	0	NR	995	0	NR
480	133	NR	610	379	NR	740	11	NR	870	0	NR	1000	0	NR
485	149	NR	615	406	NR	745	9	NR	875	0	NR			

REPORT NUMBER: SP1-2506-457-7

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.74

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	173	NR	620	343	NR	750	8	NR	880	0	NR
365	0	NR	495	201	NR	625	342	NR	755	7	NR	885	0	NR
370	0	NR	500	231	NR	630	1000	NR	760	6	NR	890	0	NR
375	0	NR	505	253	NR	635	692	NR	765	5	NR	895	0	NR
380	0	NR	510	268	NR	640	226	NR	770	4	NR	900	0	NR
385	1	NR	515	277	NR	645	214	NR	775	4	NR	905	0	NR
390	1	NR	520	284	NR	650	190	NR	780	3	NR	910	0	NR
395	3	NR	525	290	NR	655	160	NR	785	3	NR	915	0	NR
400	4	NR	530	296	NR	660	136	NR	790	2	NR	920	0	NR
405	5	NR	535	303	NR	665	115	NR	795	2	NR	925	0	NR
410	8	NR	540	310	NR	670	106	NR	800	2	NR	930	0	NR
415	13	NR	545	316	NR	675	87	NR	805	2	NR	935	0	NR
420	22	NR	550	323	NR	680	75	NR	810	1	NR	940	0	NR
425	37	NR	555	330	NR	685	64	NR	815	1	NR	945	0	NR
430	62	NR	560	335	NR	690	55	NR	820	1	NR	950	0	NR
435	102	NR	565	340	NR	695	47	NR	825	1	NR	955	0	NR
440	164	NR	570	342	NR	700	40	NR	830	1	NR	960	0	NR
445	281	NR	575	345	NR	705	34	NR	835	1	NR	965	0	NR
450	423	NR	580	348	NR	710	29	NR	840	1	NR	970	0	NR
455	384	NR	585	350	NR	715	25	NR	845	1	NR	975	0	NR
460	256	NR	590	351	NR	720	21	NR	850	0	NR	980	0	NR
465	208	NR	595	348	NR	725	17	NR	855	0	NR	985	0	NR
470	169	NR	600	348	NR	730	14	NR	860	0	NR	990	0	NR
475	135	NR	605	347	NR	735	12	NR	865	0	NR	995	0	NR
480	133	NR	610	379	NR	740	11	NR	870	0	NR	1000	0	NR
485	149	NR	615	406	NR	745	9	NR	875	0	NR			

REPORT NUMBER: SP1-2506-457-7

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 3.6

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	173	NR	620	343	NR	750	8	NR	880	0	NR
365	0	NR	495	201	NR	625	342	NR	755	7	NR	885	0	NR
370	0	NR	500	231	NR	630	1000	NR	760	6	NR	890	0	NR
375	0	NR	505	253	NR	635	692	NR	765	5	NR	895	0	NR
380	0	NR	510	268	NR	640	226	NR	770	4	NR	900	0	NR
385	1	NR	515	277	NR	645	214	NR	775	4	NR	905	0	NR
390	1	NR	520	284	NR	650	190	NR	780	3	NR	910	0	NR
395	3	NR	525	290	NR	655	160	NR	785	3	NR	915	0	NR
400	4	NR	530	296	NR	660	136	NR	790	2	NR	920	0	NR
405	5	NR	535	303	NR	665	115	NR	795	2	NR	925	0	NR
410	8	NR	540	310	NR	670	106	NR	800	2	NR	930	0	NR
415	13	NR	545	316	NR	675	87	NR	805	2	NR	935	0	NR
420	22	NR	550	323	NR	680	75	NR	810	1	NR	940	0	NR
425	37	NR	555	330	NR	685	64	NR	815	1	NR	945	0	NR
430	62	NR	560	335	NR	690	55	NR	820	1	NR	950	0	NR
435	102	NR	565	340	NR	695	47	NR	825	1	NR	955	0	NR
440	164	NR	570	342	NR	700	40	NR	830	1	NR	960	0	NR
445	281	NR	575	345	NR	705	34	NR	835	1	NR	965	0	NR
450	423	NR	580	348	NR	710	29	NR	840	1	NR	970	0	NR
455	384	NR	585	350	NR	715	25	NR	845	1	NR	975	0	NR
460	256	NR	590	351	NR	720	21	NR	850	0	NR	980	0	NR
465	208	NR	595	348	NR	725	17	NR	855	0	NR	985	0	NR
470	169	NR	600	348	NR	730	14	NR	860	0	NR	990	0	NR
475	135	NR	605	347	NR	735	12	NR	865	0	NR	995	0	NR
480	133	NR	610	379	NR	740	11	NR	870	0	NR	1000	0	NR
485	149	NR	615	406	NR	745	9	NR	875	0	NR			

Summary

$R_f = 91.3$
 $R_g = 99.8$
 $CIE R_a = 94.0$
 $R_9 = 65.3$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 93	CES51 = 98	CES76 = 87
CES02 = 62	CES27 = 91	CES52 = 99	CES77 = 88
CES03 = 31	CES28 = 96	CES53 = 97	CES78 = 83
CES04 = 69	CES29 = 96	CES54 = 94	CES79 = 93
CES05 = 49	CES30 = 93	CES55 = 92	CES80 = 92
CES06 = 50	CES31 = 96	CES56 = 95	CES81 = 79
CES07 = 42	CES32 = 88	CES57 = 94	CES82 = 96
CES08 = 41	CES33 = 99	CES58 = 95	CES83 = 95
CES09 = 29	CES34 = 93	CES59 = 97	CES84 = 94
CES10 = 74	CES35 = 96	CES60 = 93	CES85 = 81
CES11 = 57	CES36 = 81	CES61 = 92	CES86 = 83
CES12 = 63	CES37 = 94	CES62 = 87	CES87 = 92
CES13 = 43	CES38 = 88	CES63 = 93	CES88 = 98
CES14 = 74	CES39 = 99	CES64 = 91	CES89 = 85
CES15 = 71	CES40 = 97	CES65 = 89	CES90 = 97
CES16 = 47	CES41 = 97	CES66 = 88	CES91 = 73
CES17 = 49	CES42 = 93	CES67 = 87	CES92 = 77
CES18 = 56	CES43 = 93	CES68 = 88	CES93 = 86
CES19 = 71	CES44 = 99	CES69 = 89	CES94 = 76
CES20 = 66	CES45 = 96	CES70 = 86	CES95 = 83
CES21 = 85	CES46 = 97	CES71 = 81	CES96 = 92
CES22 = 78	CES47 = 93	CES72 = 94	CES97 = 95
CES23 = 91	CES48 = 92	CES73 = 80	CES98 = 95
CES24 = 90	CES49 = 96	CES74 = 91	CES99 = 93
CES25 = 71	CES50 = 98	CES75 = 83	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)