

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: METALUX

Report Number: P976684

Luminaire Tested: 24SR-LD2-C-48-UNV-L835-CD1-BR-U

Issue Date: 03/18/2025

**Test Information**

Test Method: LM-79-2019  
Report Number: P976684  
Test Lab: INNOVATION CENTER(P3)  
Issue Date: 03/18/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: METALUX  
Catalog Number: 24SR-LD2-C-48-UNV-L835-CD1-BR-U  
Description: METALUX SKYRIDGE 2x4 4800LM PACKAGE 80CRI 3500K TROFFER with Belladonna Rose SKYT  
Light Source: 3500K CCT, 80+ CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2747.0 lumens  
Efficiency: N/A  
Efficacy: 78.9 lumens/watt  
Spacing Criteria (0/90/45): 1.29 / 2.29 / 2.08  
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')  
CIE Type: Direct

Input Watts (W): 34.8  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT

TEST NUMBER: P976684  
CATALOG NUMBER: 24SR-LD2-C-48-UNV-L835-CD1-BR-U

### Luminous Intensity Polar Plot





TEST NUMBER: P976684

CATALOG NUMBER: 24SR-LD2-C-48-UNV-L835-CD1-BR-U

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	106	100	94	90	103	97	93	88	93	89	85	89	86	83	85	83	80	85	83	80	78
2	95	85	77	70	92	83	75	69	79	73	67	76	70	66	73	68	64	73	68	64	62
3	85	73	64	56	83	71	63	56	68	61	55	65	59	54	63	57	53	63	57	53	50
4	77	64	54	46	75	62	53	46	60	52	45	57	50	45	55	49	44	55	49	44	41
5	71	56	46	39	68	55	46	39	53	45	38	51	44	38	49	42	37	49	42	37	35
6	65	50	40	33	63	49	40	33	47	39	33	46	38	33	44	37	32	44	37	32	30
7	60	45	36	29	58	44	35	29	43	35	29	41	34	28	40	33	28	40	33	28	26
8	56	41	32	25	54	40	31	25	39	31	25	38	30	25	36	30	25	36	30	25	23
9	52	37	29	23	50	37	28	22	36	28	22	34	27	22	33	27	22	33	27	22	20
10	48	34	26	20	47	34	26	20	33	25	20	32	25	20	31	24	20	31	24	20	18

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	533	533	533
5°	536	591	648
10°	536	738	859
15°	536	879	1039
20°	535	989	1178
25°	533	1072	1283
30°	533	1134	1355
35°	532	1171	1394
40°	531	1197	1411
45°	533	1220	1415
50°	531	1254	1422
55°	532	1305	1445
60°	537	1382	1500
65°	535	1491	1591
70°	537	1642	1745
75°	540	1882	1954
80°	559	2281	2159
85°	644	2942	2665

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 45°  
 Vertical Angle: 87.5°  
 Luminance: 3587 cd/sqm



TEST NUMBER: P976684  
 CATALOG NUMBER: 24SR-LD2-C-48-UNV-L835-CD1-BR-U

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	44.5	1.6
10°-20°	169.8	6.2
20°-30°	310.5	11.3
30°-40°	412.9	15.0
40°-50°	454.6	16.6
50°-60°	450.6	16.4
60°-70°	412.5	15.0
70°-80°	332.1	12.1
80°-90°	159.4	5.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	524.8	19.1
0°-40°	937.7	34.1
0°-60°	1843.0	67.1
0°-90°	2747.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2747.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	396	396	396	396	396	
5°	397	400	438	468	480	38
15°	385	484	631	715	746	109
25°	359	538	722	826	864	166
35°	324	529	713	814	848	203
45°	280	477	641	718	744	215
55°	227	420	556	603	616	203
65°	168	363	468	489	500	167
75°	104	283	362	372	376	109
85°	42	155	191	175	173	43
90°	0	0	0	0	0	



TEST NUMBER: P976684

CATALOG NUMBER: 24SR-LD2-C-48-UNV-L835-CD1-BR-U

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	396.0	396.0	396.0	396.0	396.0	396.0	396.0	396.0	396.0	396.0	396.0
2.5°	398.2	398.2	397.2	397.2	397.2	397.2	397.2	397.2	398.2	400.5	401.7
5°	397.2	397.2	397.2	397.2	398.2	402.8	408.4	417.5	426.5	437.9	447.9
7.5°	394.9	394.9	394.9	398.2	408.4	424.2	438.9	455.8	472.8	489.6	503.3
10°	392.6	392.6	394.9	407.3	427.7	451.4	473.8	496.4	517.8	540.4	559.6
12.5°	389.3	389.3	396.0	418.6	447.9	477.3	506.6	533.6	560.8	589.0	610.4
15°	384.7	384.7	399.5	429.8	465.9	502.0	535.9	568.7	600.2	630.7	654.4
17.5°	379.1	381.4	402.8	441.2	481.7	523.6	560.8	598.0	631.8	663.4	691.6
20°	373.5	376.8	406.1	450.1	495.4	541.5	582.2	620.6	656.7	690.5	719.8
22.5°	366.7	371.2	408.4	457.0	505.5	554.0	596.9	637.4	675.8	709.7	740.2
25°	358.8	365.6	409.6	460.3	513.4	561.8	605.9	647.6	687.1	722.1	752.6
27.5°	351.9	361.1	408.4	462.6	516.8	566.4	611.5	653.2	693.9	728.9	760.5
30°	343.0	354.2	406.1	461.5	515.6	566.4	610.4	653.2	693.9	730.0	760.5
32.5°	334.0	347.5	400.5	457.0	512.2	560.8	605.9	648.8	688.3	724.4	753.7
35°	323.9	339.7	393.8	450.1	504.3	552.9	596.9	638.6	679.2	713.0	742.4
37.5°	313.7	330.6	384.7	441.2	494.2	541.5	584.5	626.2	664.6	699.5	726.7
40°	302.3	321.6	375.8	431.0	481.7	528.0	571.0	611.5	648.8	681.4	707.4
42.5°	291.1	311.4	365.6	419.8	469.4	513.4	556.2	594.6	630.7	662.3	686.0
45°	279.9	300.2	353.2	407.3	454.7	498.7	539.4	577.6	611.5	640.9	663.4
47.5°	266.2	288.8	341.9	393.8	440.0	484.0	523.6	559.6	593.4	619.4	640.9
50°	253.9	277.6	329.5	380.2	425.4	469.4	507.7	542.7	574.3	599.2	618.3
52.5°	240.4	265.1	317.0	367.9	413.0	454.7	493.1	525.7	554.0	577.6	595.7
55°	226.7	252.7	305.8	354.2	399.5	441.2	477.3	508.9	535.9	556.2	573.2
57.5°	213.2	240.4	293.4	343.0	387.0	427.7	462.6	490.8	516.8	534.8	549.4
60°	199.7	228.0	279.9	329.5	374.6	413.0	446.8	473.8	496.4	513.4	525.7
62.5°	183.9	214.4	267.4	316.0	360.0	397.2	429.8	454.7	476.1	490.8	501.0
65°	168.2	200.8	253.9	302.3	345.3	381.4	411.9	435.6	454.7	468.2	475.0
67.5°	152.4	187.3	240.4	288.8	329.5	363.3	392.6	415.2	432.1	443.5	449.1
70°	136.6	171.5	224.5	272.0	311.4	343.0	371.2	392.6	407.3	417.5	421.9
72.5°	119.6	155.7	207.6	253.9	291.1	322.7	348.6	368.9	382.5	390.3	393.8
75°	103.8	138.7	189.6	233.6	268.5	297.9	322.7	343.0	356.5	362.1	365.6
77.5°	86.8	121.9	170.4	211.0	243.7	270.8	294.4	313.7	326.1	331.8	335.1
80°	72.2	103.8	147.8	185.0	215.5	241.5	262.9	283.2	293.4	294.4	291.1
82.5°	56.5	85.7	124.1	156.8	182.7	207.6	228.0	241.5	246.0	246.0	242.5
85°	41.7	64.3	97.0	122.9	145.5	163.6	176.1	187.3	189.6	190.6	186.2
87.5°	23.7	36.1	57.5	74.5	88.0	100.5	109.4	115.0	115.0	116.3	114.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P976684

CATALOG NUMBER: 24SR-LD2-C-48-UNV-L835-CD1-BR-U

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	396.0	396.0	396.0	396.0	396.0	396.0	396.0	396.0
2.5°	401.7	403.9	403.9	406.1	407.3	407.3	408.4	408.4
5°	452.4	461.5	464.9	470.5	473.8	478.4	480.6	479.6
7.5°	513.4	526.9	533.6	541.5	550.6	552.9	556.2	556.2
10°	574.3	590.1	600.2	609.3	619.4	623.9	628.5	628.5
12.5°	629.5	645.3	659.0	670.2	680.4	687.1	691.6	692.8
15°	674.8	695.1	708.6	721.0	732.3	739.0	744.7	745.8
17.5°	711.9	731.1	749.1	762.8	772.8	783.0	786.5	788.7
20°	741.2	761.6	780.8	794.4	805.6	815.8	820.3	822.6
22.5°	762.8	784.2	803.3	818.0	829.3	839.4	845.0	847.3
25°	776.3	798.8	819.1	833.8	846.3	856.4	862.0	864.3
27.5°	785.2	807.9	827.0	841.7	854.2	864.3	869.9	873.3
30°	785.2	807.9	827.0	841.7	854.2	864.3	869.9	872.2
32.5°	778.6	801.0	820.3	833.8	846.3	856.4	862.0	864.3
35°	766.1	788.7	806.8	820.3	832.8	841.7	847.3	848.5
37.5°	749.1	770.7	787.5	801.0	812.4	821.4	827.0	828.2
40°	730.0	750.3	766.1	778.6	788.7	796.6	802.2	803.3
42.5°	707.4	726.7	740.2	752.6	761.6	769.5	775.1	774.0
45°	683.7	701.8	713.0	723.2	733.3	739.0	743.5	743.5
47.5°	660.0	674.8	684.9	693.9	701.8	707.4	710.9	710.9
50°	635.3	647.6	656.7	664.6	671.3	675.8	679.2	679.2
52.5°	610.4	621.6	628.5	635.3	640.9	644.3	647.6	646.5
55°	585.5	594.6	599.2	605.9	610.4	615.0	617.2	616.0
57.5°	560.8	566.4	571.0	576.6	581.1	585.5	586.7	587.8
60°	533.6	539.4	542.7	548.3	552.9	556.2	558.5	557.4
62.5°	507.7	511.2	514.5	519.0	522.4	526.9	528.0	528.0
65°	479.6	482.9	486.3	490.8	494.2	498.7	501.0	499.8
67.5°	452.4	455.8	459.2	462.6	467.1	471.7	472.8	472.8
70°	424.2	427.7	429.8	434.4	437.9	442.3	443.5	443.5
72.5°	397.2	399.5	401.7	406.1	408.4	411.9	414.0	414.0
75°	366.7	368.9	371.2	373.5	374.6	375.8	376.8	375.8
77.5°	332.8	330.6	328.3	328.3	326.1	327.2	328.3	327.2
80°	286.5	284.3	282.1	280.9	278.6	278.6	279.9	278.6
82.5°	238.1	233.6	231.3	230.2	228.0	228.0	228.0	228.0
85°	179.4	177.1	176.1	173.8	171.5	170.4	171.5	172.6
87.5°	111.7	109.4	107.1	104.9	103.8	102.7	104.9	101.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P976684  
 CATALOG NUMBER: 24SR-LD2-C-48-UNV-L835-CD1-BR-U

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room Dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.1	12.9	11.4	13.2	13.5	14.1	15.9	14.5	16.2	16.5
	3H	13.1	14.7	13.4	15.0	15.4	16.7	18.4	17.1	18.7	19.1
	4H	13.8	15.4	14.2	15.8	16.1	18.0	19.6	18.4	19.9	20.3
	6H	14.4	15.9	14.9	16.3	16.7	19.1	20.6	19.5	20.9	21.3
	8H	14.7	16.1	15.1	16.5	16.9	19.6	21.0	20.0	21.4	21.8
	12H	14.8	16.2	15.3	16.6	17.0	20.0	21.4	20.4	21.7	22.2
4H	2H	12.8	14.4	13.2	14.7	15.1	14.9	16.4	15.3	16.8	17.1
	3H	15.3	16.7	15.7	17.1	17.5	17.8	19.1	18.2	19.5	19.9
	4H	16.4	17.7	16.9	18.1	18.5	19.2	20.4	19.6	20.8	21.3
	6H	17.3	18.4	17.8	18.9	19.3	20.5	21.6	21.0	22.0	22.5
	8H	17.7	18.7	18.1	19.1	19.6	21.1	22.1	21.5	22.5	23.0
	12H	17.9	18.9	18.4	19.3	19.8	21.6	22.5	22.1	23.0	23.5
8H	4H	17.6	18.7	18.1	19.1	19.6	19.8	20.8	20.2	21.2	21.7
	6H	19.0	19.9	19.5	20.3	20.8	21.3	22.1	21.8	22.6	23.1
	8H	19.6	20.3	20.1	20.8	21.3	22.0	22.8	22.5	23.3	23.7
	12H	20.0	20.7	20.5	21.2	21.8	22.6	23.4	23.1	23.8	24.4
12H	4H	17.9	18.8	18.3	19.3	19.7	19.9	20.8	20.3	21.3	21.7
	6H	19.4	20.2	19.9	20.6	21.2	21.5	22.3	22.0	22.7	23.3
	8H	20.1	20.9	20.6	21.3	21.9	22.3	23.0	22.8	23.5	24.0

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2506-457-6

Test Date: 07/01/2025

Luminaire Tested: 24SR-LD2-64-C-UNV-L935-CD1-U

Data in this report applies to families of products including 24SR-LD2-64-C-UNV-L935-CD1-U

**Test Information**

Test Method: LM-79-2019  
 Report Number: SP1-2506-457-6  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry: 4π  
 Issue Date: 07/02/2025  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: Metalux  
 Catalog Number: **24SR-LD2-64-C-UNV-L935-CD1-U**  
 Description: 2X4 SKYRIDGE 6400LM Fixture with new LTN chip

**Spectral Parameters**

CCT (K): 3329  
 CIE u': 0.2411  
 CIE v': 0.5118  
 Duv: -0.0021  
 CIE x: 0.4128  
 CIE y: 0.3894  
 CIE z: 0.1979  
 Peak Wavelength (nm): 630  
 Dominant Wavelength (nm): 582  
 Purity: 40.74075  
 Rf: 91.4  
 Rg: 100.2

CRI (Ra):	93.9		
R1:	95.4	R9:	60.5
R2:	97.4	R10:	92.5
R3:	97.7	R11:	95.9
R4:	94.9	R12:	82.0
R5:	95.1	R13:	96.0
R6:	95.7	R14:	98.0
R7:	91.7	R15:	91.5
R8:	83.2		



**Test Conditions**

Stabilization Time: 48M  
 Operation Time: 1H 48M  
 Sphere Temperature (°C): 24.0

REPORT NUMBER: SP1-2506-457-6

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2506-457-6

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3500K 7-step quadrangle

REPORT NUMBER: SP1-2506-457-6

**Photopic Flux vs. Wavelength**



**Photopic Lumens: NR**

λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)
360	0	NR	490	143	NR	620	358	NR	750	9	NR	880	0	NR
365	0	NR	495	166	NR	625	357	NR	755	7	NR	885	0	NR
370	0	NR	500	191	NR	630	1000	NR	760	6	NR	890	0	NR
375	0	NR	505	210	NR	635	705	NR	765	5	NR	895	0	NR
380	0	NR	510	223	NR	640	239	NR	770	5	NR	900	0	NR
385	0	NR	515	233	NR	645	226	NR	775	4	NR	905	0	NR
390	1	NR	520	240	NR	650	201	NR	780	3	NR	910	0	NR
395	2	NR	525	246	NR	655	170	NR	785	3	NR	915	0	NR
400	3	NR	530	251	NR	660	145	NR	790	2	NR	920	0	NR
405	4	NR	535	260	NR	665	123	NR	795	2	NR	925	0	NR
410	6	NR	540	267	NR	670	113	NR	800	2	NR	930	0	NR
415	9	NR	545	276	NR	675	93	NR	805	2	NR	935	0	NR
420	16	NR	550	284	NR	680	80	NR	810	1	NR	940	0	NR
425	28	NR	555	294	NR	685	69	NR	815	1	NR	945	0	NR
430	46	NR	560	303	NR	690	59	NR	820	1	NR	950	0	NR
435	75	NR	565	313	NR	695	51	NR	825	1	NR	955	0	NR
440	120	NR	570	319	NR	700	43	NR	830	1	NR	960	0	NR
445	203	NR	575	327	NR	705	37	NR	835	1	NR	965	0	NR
450	311	NR	580	336	NR	710	31	NR	840	1	NR	970	0	NR
455	290	NR	585	344	NR	715	26	NR	845	1	NR	975	0	NR
460	197	NR	590	349	NR	720	22	NR	850	0	NR	980	0	NR
465	163	NR	595	350	NR	725	18	NR	855	0	NR	985	0	NR
470	135	NR	600	355	NR	730	15	NR	860	0	NR	990	0	NR
475	110	NR	605	357	NR	735	13	NR	865	0	NR	995	0	NR
480	108	NR	610	391	NR	740	11	NR	870	0	NR	1000	0	NR
485	123	NR	615	421	NR	745	10	NR	875	0	NR			

REPORT NUMBER: SP1-2506-457-6

**Scotopic Flux vs. Wavelength**



**Scotopic Lumens: NR**

**S/P: 1.57**

$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)	$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)	$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)	$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)	$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)
360	0	NR	490	143	NR	620	358	NR	750	9	NR	880	0	NR
365	0	NR	495	166	NR	625	357	NR	755	7	NR	885	0	NR
370	0	NR	500	191	NR	630	1000	NR	760	6	NR	890	0	NR
375	0	NR	505	210	NR	635	705	NR	765	5	NR	895	0	NR
380	0	NR	510	223	NR	640	239	NR	770	5	NR	900	0	NR
385	0	NR	515	233	NR	645	226	NR	775	4	NR	905	0	NR
390	1	NR	520	240	NR	650	201	NR	780	3	NR	910	0	NR
395	2	NR	525	246	NR	655	170	NR	785	3	NR	915	0	NR
400	3	NR	530	251	NR	660	145	NR	790	2	NR	920	0	NR
405	4	NR	535	260	NR	665	123	NR	795	2	NR	925	0	NR
410	6	NR	540	267	NR	670	113	NR	800	2	NR	930	0	NR
415	9	NR	545	276	NR	675	93	NR	805	2	NR	935	0	NR
420	16	NR	550	284	NR	680	80	NR	810	1	NR	940	0	NR
425	28	NR	555	294	NR	685	69	NR	815	1	NR	945	0	NR
430	46	NR	560	303	NR	690	59	NR	820	1	NR	950	0	NR
435	75	NR	565	313	NR	695	51	NR	825	1	NR	955	0	NR
440	120	NR	570	319	NR	700	43	NR	830	1	NR	960	0	NR
445	203	NR	575	327	NR	705	37	NR	835	1	NR	965	0	NR
450	311	NR	580	336	NR	710	31	NR	840	1	NR	970	0	NR
455	290	NR	585	344	NR	715	26	NR	845	1	NR	975	0	NR
460	197	NR	590	349	NR	720	22	NR	850	0	NR	980	0	NR
465	163	NR	595	350	NR	725	18	NR	855	0	NR	985	0	NR
470	135	NR	600	355	NR	730	15	NR	860	0	NR	990	0	NR
475	110	NR	605	357	NR	735	13	NR	865	0	NR	995	0	NR
480	108	NR	610	391	NR	740	11	NR	870	0	NR	1000	0	NR
485	123	NR	615	421	NR	745	10	NR	875	0	NR			

REPORT NUMBER: SP1-2506-457-6

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 3.17


λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)
360	0	NR	490	143	NR	620	358	NR	750	9	NR	880	0	NR
365	0	NR	495	166	NR	625	357	NR	755	7	NR	885	0	NR
370	0	NR	500	191	NR	630	1000	NR	760	6	NR	890	0	NR
375	0	NR	505	210	NR	635	705	NR	765	5	NR	895	0	NR
380	0	NR	510	223	NR	640	239	NR	770	5	NR	900	0	NR
385	0	NR	515	233	NR	645	226	NR	775	4	NR	905	0	NR
390	1	NR	520	240	NR	650	201	NR	780	3	NR	910	0	NR
395	2	NR	525	246	NR	655	170	NR	785	3	NR	915	0	NR
400	3	NR	530	251	NR	660	145	NR	790	2	NR	920	0	NR
405	4	NR	535	260	NR	665	123	NR	795	2	NR	925	0	NR
410	6	NR	540	267	NR	670	113	NR	800	2	NR	930	0	NR
415	9	NR	545	276	NR	675	93	NR	805	2	NR	935	0	NR
420	16	NR	550	284	NR	680	80	NR	810	1	NR	940	0	NR
425	28	NR	555	294	NR	685	69	NR	815	1	NR	945	0	NR
430	46	NR	560	303	NR	690	59	NR	820	1	NR	950	0	NR
435	75	NR	565	313	NR	695	51	NR	825	1	NR	955	0	NR
440	120	NR	570	319	NR	700	43	NR	830	1	NR	960	0	NR
445	203	NR	575	327	NR	705	37	NR	835	1	NR	965	0	NR
450	311	NR	580	336	NR	710	31	NR	840	1	NR	970	0	NR
455	290	NR	585	344	NR	715	26	NR	845	1	NR	975	0	NR
460	197	NR	590	349	NR	720	22	NR	850	0	NR	980	0	NR
465	163	NR	595	350	NR	725	18	NR	855	0	NR	985	0	NR
470	135	NR	600	355	NR	730	15	NR	860	0	NR	990	0	NR
475	110	NR	605	357	NR	735	13	NR	865	0	NR	995	0	NR
480	108	NR	610	391	NR	740	11	NR	870	0	NR	1000	0	NR
485	123	NR	615	421	NR	745	10	NR	875	0	NR			

**Summary**

$R_f = 91.4$   
 $R_g = 100.2$   
 $CIE R_a = 93.9$   
 $R_9 = 60.5$



**Color Vector Graphics**



Individual Sample Fidelity Index ( $R_{f,i}$ )


CES01 = 86	CES26 = 93	CES51 = 98	CES76 = 88
CES02 = 63	CES27 = 93	CES52 = 98	CES77 = 87
CES03 = 31	CES28 = 96	CES53 = 97	CES78 = 85
CES04 = 70	CES29 = 95	CES54 = 95	CES79 = 91
CES05 = 50	CES30 = 96	CES55 = 94	CES80 = 92
CES06 = 51	CES31 = 95	CES56 = 96	CES81 = 75
CES07 = 43	CES32 = 87	CES57 = 95	CES82 = 96
CES08 = 42	CES33 = 97	CES58 = 96	CES83 = 94
CES09 = 29	CES34 = 94	CES59 = 98	CES84 = 95
CES10 = 75	CES35 = 96	CES60 = 94	CES85 = 80
CES11 = 58	CES36 = 84	CES61 = 93	CES86 = 79
CES12 = 64	CES37 = 95	CES62 = 89	CES87 = 91
CES13 = 44	CES38 = 91	CES63 = 94	CES88 = 97
CES14 = 74	CES39 = 99	CES64 = 92	CES89 = 83
CES15 = 72	CES40 = 97	CES65 = 90	CES90 = 98
CES16 = 48	CES41 = 97	CES66 = 90	CES91 = 77
CES17 = 49	CES42 = 93	CES67 = 89	CES92 = 77
CES18 = 56	CES43 = 92	CES68 = 89	CES93 = 86
CES19 = 71	CES44 = 99	CES69 = 91	CES94 = 74
CES20 = 67	CES45 = 96	CES70 = 88	CES95 = 84
CES21 = 86	CES46 = 96	CES71 = 84	CES96 = 92
CES22 = 78	CES47 = 91	CES72 = 94	CES97 = 95
CES23 = 91	CES48 = 94	CES73 = 83	CES98 = 94
CES24 = 90	CES49 = 94	CES74 = 91	CES99 = 92
CES25 = 71	CES50 = 98	CES75 = 86	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)