

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: METALUX

Report Number: P976877

Luminaire Tested: 24SR-LD2-C-53-UNV-L835-CD1-PL-U

Issue Date: 03/18/2025

Test Information

Test Method: LM-79-2019
Report Number: P976877
Test Lab: INNOVATION CENTER(P3)
Issue Date: 03/18/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: METALUX
Catalog Number: 24SR-LD2-C-53-UNV-L835-CD1-PL-U
Description: METALUX SKYRIDGE 2x4 5300LM PACKAGE 80CRI 3500K TROFFER with Pearl SKYTRIM
Light Source: 3500K CCT, 80+ CRI LEDS
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4878.0 lumens
Efficiency: N/A
Efficacy: 127.0 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.98 / 1.87
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

TEST NUMBER: P976877
CATALOG NUMBER: 24SR-LD2-C-53-UNV-L835-CD1-PL-U

Luminous Intensity Polar Plot





TEST NUMBER: P976877

CATALOG NUMBER: 24SR-LD2-C-53-UNV-L835-CD1-PL-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	106	100	95	90	103	98	93	88	93	89	85	89	86	83	86	83	80	78	78	78	78
2	95	85	77	70	92	83	76	70	80	73	68	76	71	66	73	69	65	62	62	62	62
3	86	74	64	57	83	72	63	56	69	61	55	66	60	54	63	58	53	51	51	51	51
4	78	64	55	47	75	63	54	47	60	52	46	58	51	45	56	50	45	42	42	42	42
5	71	57	47	40	69	56	47	40	54	45	39	52	44	39	50	43	38	36	36	36	36
6	65	51	41	34	63	50	41	34	48	40	34	46	39	33	45	38	33	31	31	31	31
7	60	46	36	30	59	45	36	30	43	35	29	42	35	29	40	34	29	27	27	27	27
8	56	42	32	26	54	41	32	26	39	32	26	38	31	26	37	30	26	23	23	23	23
9	52	38	29	23	51	37	29	23	36	28	23	35	28	23	34	27	23	21	21	21	21
10	49	35	26	21	48	34	26	21	33	26	21	32	25	21	31	25	20	19	19	19	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1190	1190	1190
5°	1200	1254	1318
10°	1202	1434	1585
15°	1200	1618	1837
20°	1198	1779	2056
25°	1197	1918	2233
30°	1196	2027	2345
35°	1193	2100	2380
40°	1194	2138	2364
45°	1193	2159	2337
50°	1191	2189	2326
55°	1190	2250	2362
60°	1185	2349	2443
65°	1177	2501	2595
70°	1155	2736	2821
75°	1138	3126	3147
80°	1148	3832	3711
85°	1252	5308	5406

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 87.5°
 Luminance: 8066 cd/sqm



TEST NUMBER: P976877
 CATALOG NUMBER: 24SR-LD2-C-53-UNV-L835-CD1-PL-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.0	1.9
10°-20°	319.5	6.5
20°-30°	566.3	11.6
30°-40°	745.3	15.3
40°-50°	808.1	16.6
50°-60°	786.7	16.1
60°-70°	706.8	14.5
70°-80°	559.9	11.5
80°-90°	293.4	6.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	977.8	20.0
0°-40°	1723.0	35.3
0°-60°	3317.9	68.0
0°-90°	4878.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4878.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	885	885	885	885	885	
5°	889	888	928	964	976	85
15°	862	974	1162	1278	1319	243
25°	806	1026	1292	1448	1504	372
35°	726	1000	1279	1409	1449	455
45°	627	907	1134	1209	1228	484
55°	507	789	959	993	1007	453
65°	370	661	786	800	815	365
75°	219	497	601	602	605	233
85°	81	264	344	344	350	86
90°	0	0	0	0	0	



TEST NUMBER: P976877

CATALOG NUMBER: 24SR-LD2-C-53-UNV-L835-CD1-PL-U

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	884.6	884.6	884.6	884.6	884.6	884.6	884.6	884.6	884.6	884.6	884.6
2.5°	891.0	889.8	888.6	887.2	886.0	884.6	884.6	884.6	886.0	888.6	892.4
5°	888.6	887.2	886.0	886.0	887.2	889.8	897.6	906.6	915.6	928.5	942.7
7.5°	884.6	883.4	883.4	886.0	896.2	911.7	929.7	949.1	968.3	988.9	1008.4
10°	879.6	878.2	879.6	891.0	914.3	940.1	967.1	994.1	1020.0	1049.6	1076.6
12.5°	870.6	870.6	877.0	900.0	933.7	968.3	1003.2	1039.2	1072.6	1108.7	1139.7
15°	861.6	861.6	875.6	910.4	952.9	994.1	1038.0	1080.4	1120.3	1161.5	1197.6
17.5°	850.0	850.0	874.4	918.2	967.1	1017.4	1067.6	1115.3	1160.3	1205.4	1244.0
20°	837.0	839.6	871.8	924.7	979.9	1036.6	1090.7	1143.5	1193.8	1242.6	1285.1
22.5°	821.5	826.7	868.0	927.3	990.3	1049.6	1108.7	1165.3	1218.2	1272.3	1314.7
25°	806.1	813.9	862.8	927.3	994.1	1058.6	1120.3	1179.6	1236.2	1291.7	1337.9
27.5°	789.3	799.7	855.0	923.3	995.4	1061.0	1125.5	1187.4	1246.6	1303.1	1350.8
30°	770.1	782.9	843.6	915.6	990.3	1057.2	1124.3	1188.6	1247.8	1304.5	1350.8
32.5°	748.2	764.9	829.3	904.0	979.9	1048.2	1115.3	1179.6	1240.0	1295.5	1339.3
35°	726.2	746.9	813.9	889.8	965.7	1034.0	1101.1	1166.7	1226.0	1278.7	1317.3
37.5°	704.4	726.2	794.5	870.6	946.5	1014.8	1083.0	1146.1	1202.8	1251.6	1286.5
40°	680.0	704.4	772.7	850.0	924.7	992.9	1059.8	1120.3	1171.9	1217.0	1249.0
42.5°	652.9	680.0	749.5	826.7	900.0	967.1	1031.4	1088.1	1137.1	1177.0	1204.0
45°	627.1	655.5	725.0	802.3	874.4	940.1	1001.9	1054.6	1098.5	1134.5	1157.7
47.5°	598.9	628.3	700.6	775.3	846.0	910.4	969.7	1017.4	1059.8	1090.7	1111.3
50°	569.2	601.3	673.6	748.2	817.7	880.8	937.5	981.3	1020.0	1045.6	1065.0
52.5°	539.6	573.1	645.1	719.8	789.3	850.0	904.0	946.5	979.9	1003.2	1020.0
55°	507.4	544.6	616.9	691.6	758.5	818.9	870.6	909.2	940.1	959.3	974.9
57.5°	473.9	513.8	588.5	663.2	730.2	788.1	837.0	873.0	900.0	916.9	928.5
60°	440.5	482.9	557.6	632.3	698.0	755.9	802.3	835.8	860.2	873.0	882.0
62.5°	405.7	450.7	526.6	601.3	668.4	722.4	766.3	797.1	818.9	829.3	838.4
65°	369.6	417.3	494.6	569.2	636.1	686.4	728.8	757.3	776.5	785.5	790.7
67.5°	332.2	382.4	460.9	535.6	600.1	649.0	689.0	717.2	732.7	740.5	744.3
70°	293.5	346.4	424.9	499.6	561.4	607.9	646.5	672.2	687.6	695.4	696.6
72.5°	257.5	309.1	388.9	460.9	520.2	565.3	601.3	628.3	643.9	650.3	650.3
75°	218.9	270.5	349.0	418.5	475.2	519.0	555.0	580.9	594.9	601.3	601.3
77.5°	185.4	233.1	306.5	373.4	426.3	468.7	503.6	530.6	546.0	552.4	552.4
80°	148.2	194.4	262.7	324.6	373.4	412.1	448.1	476.5	492.0	494.6	490.6
82.5°	114.5	157.2	215.0	270.5	315.6	351.6	387.6	410.9	422.3	424.9	423.7
85°	81.1	115.9	164.8	209.8	247.3	280.7	306.5	328.4	340.0	343.8	346.4
87.5°	47.7	66.9	97.9	132.6	161.0	182.8	198.2	217.6	229.3	236.9	244.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P976877

CATALOG NUMBER: 24SR-LD2-C-53-UNV-L835-CD1-PL-U

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	884.6	884.6	884.6	884.6	884.6	884.6	884.6	884.6
2.5°	891.0	892.4	893.6	893.6	893.6	895.0	893.6	893.6
5°	947.7	955.5	961.9	965.7	969.7	976.1	974.9	976.1
7.5°	1018.6	1031.4	1045.6	1053.4	1058.6	1066.2	1068.8	1068.8
10°	1092.0	1110.1	1126.7	1138.3	1146.1	1157.7	1158.9	1160.3
12.5°	1161.5	1183.4	1202.8	1215.6	1227.2	1237.4	1242.6	1244.0
15°	1220.8	1247.8	1269.7	1286.5	1298.1	1309.7	1316.1	1318.7
17.5°	1273.7	1301.9	1326.3	1345.7	1359.8	1371.4	1379.2	1381.8
20°	1314.7	1345.7	1372.8	1393.4	1410.0	1423.0	1433.2	1435.8
22.5°	1348.3	1380.4	1408.8	1432.0	1448.7	1464.1	1473.1	1477.1
25°	1372.8	1407.4	1437.1	1459.1	1477.1	1491.1	1500.1	1504.1
27.5°	1387.0	1421.6	1450.1	1471.9	1489.9	1502.7	1511.7	1515.7
30°	1387.0	1420.4	1448.7	1469.3	1486.1	1498.9	1505.3	1509.3
32.5°	1372.8	1405.0	1430.6	1448.7	1464.1	1477.1	1482.1	1484.7
35°	1349.6	1378.0	1401.0	1416.4	1429.4	1441.0	1446.1	1448.7
37.5°	1316.1	1341.8	1359.8	1374.0	1384.4	1396.0	1399.8	1402.4
40°	1273.7	1298.1	1310.9	1323.7	1332.7	1343.1	1345.7	1345.7
42.5°	1227.2	1247.8	1260.7	1269.7	1276.1	1282.7	1286.5	1286.5
45°	1178.3	1196.4	1205.4	1213.0	1219.4	1224.6	1228.4	1228.4
47.5°	1129.3	1143.5	1151.3	1156.3	1161.5	1166.7	1169.3	1169.3
50°	1080.4	1090.7	1097.1	1101.1	1106.3	1110.1	1112.7	1111.3
52.5°	1031.4	1039.2	1044.4	1048.2	1050.8	1054.6	1056.0	1057.2
55°	982.5	987.7	991.5	994.1	999.3	1003.2	1004.4	1007.0
57.5°	934.9	937.5	942.7	943.9	949.1	952.9	954.3	955.5
60°	886.0	888.6	892.4	895.0	901.4	904.0	905.2	907.8
62.5°	838.4	839.6	844.8	850.0	855.0	857.6	859.0	860.2
65°	790.7	794.5	798.3	802.3	807.3	811.3	812.5	815.1
67.5°	744.3	746.9	752.1	755.9	759.7	763.7	766.3	767.5
70°	696.6	699.2	703.2	705.6	709.6	713.4	717.2	717.2
72.5°	650.3	650.3	652.9	655.5	659.4	662.0	663.2	663.2
75°	600.1	598.9	601.3	602.7	602.7	602.7	603.9	605.3
77.5°	546.0	540.8	538.2	538.2	539.6	537.0	538.2	539.6
80°	484.2	479.0	477.7	477.7	479.0	477.7	479.0	479.0
82.5°	418.5	418.5	414.7	415.9	417.3	414.7	417.3	419.9
85°	342.6	343.8	342.6	346.4	346.4	346.4	347.6	350.2
87.5°	245.9	253.7	251.1	256.3	254.9	256.3	257.5	261.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P976877
 CATALOG NUMBER: 24SR-LD2-C-53-UNV-L835-CD1-PL-U

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room Dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.6	15.3	13.9	15.7	16.0	15.6	17.3	15.9	17.6	18.0
	3H	15.5	17.2	15.9	17.5	17.8	18.1	19.8	18.5	20.1	20.5
	4H	16.3	17.8	16.7	18.2	18.6	19.4	20.9	19.8	21.3	21.6
	6H	16.9	18.3	17.3	18.7	19.1	20.5	22.0	21.0	22.3	22.7
	8H	17.1	18.5	17.5	18.9	19.3	21.1	22.5	21.5	22.9	23.3
	12H	17.3	18.6	17.7	19.0	19.4	21.7	23.0	22.1	23.4	23.8
4H	2H	15.0	16.5	15.4	16.9	17.2	16.4	17.9	16.7	18.2	18.6
	3H	17.5	18.8	17.9	19.2	19.6	19.2	20.5	19.6	20.9	21.3
	4H	18.5	19.8	19.0	20.2	20.6	20.6	21.8	21.0	22.2	22.7
	6H	19.4	20.5	19.9	21.0	21.4	22.0	23.1	22.4	23.5	23.9
	8H	19.8	20.8	20.2	21.2	21.7	22.6	23.7	23.1	24.1	24.6
	12H	20.0	20.9	20.5	21.4	21.9	23.3	24.3	23.8	24.7	25.2
8H	4H	19.6	20.6	20.0	21.0	21.5	21.2	22.2	21.6	22.6	23.1
	6H	20.9	21.8	21.4	22.2	22.7	22.8	23.6	23.3	24.1	24.6
	8H	21.5	22.2	22.0	22.7	23.2	23.6	24.4	24.1	24.9	25.4
	12H	21.9	22.6	22.4	23.1	23.7	24.5	25.2	25.0	25.7	26.2
12H	4H	19.8	20.7	20.3	21.2	21.7	21.3	22.2	21.8	22.7	23.2
	6H	21.3	22.1	21.8	22.5	23.1	23.0	23.8	23.5	24.2	24.8
	8H	22.0	22.7	22.5	23.2	23.8	23.9	24.6	24.4	25.1	25.6

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2506-457-6

Test Date: 07/01/2025

Luminaire Tested: 24SR-LD2-64-C-UNV-L935-CD1-U

Data in this report applies to families of products including 24SR-LD2-64-C-UNV-L935-CD1-U

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2506-457-6
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 07/02/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Metalux
 Catalog Number: **24SR-LD2-64-C-UNV-L935-CD1-U**
 Description: 2X4 SKYRIDGE 6400LM Fixture with new LTN chip

Spectral Parameters

CCT (K): 3329
 CIE u': 0.2411
 CIE v': 0.5118
 Duv: -0.0021
 CIE x: 0.4128
 CIE y: 0.3894
 CIE z: 0.1979
 Peak Wavelength (nm): 630
 Dominant Wavelength (nm): 582
 Purity: 40.74075
 Rf: 91.4
 Rg: 100.2

CRI (Ra):	93.9		
R1:	95.4	R9:	60.5
R2:	97.4	R10:	92.5
R3:	97.7	R11:	95.9
R4:	94.9	R12:	82.0
R5:	95.1	R13:	96.0
R6:	95.7	R14:	98.0
R7:	91.7	R15:	91.5
R8:	83.2		



Test Conditions

Stabilization Time: 48M
 Operation Time: 1H 48M
 Sphere Temperature (°C): 24.0

REPORT NUMBER: SP1-2506-457-6

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2506-457-6

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3500K 7-step quadrangle

REPORT NUMBER: SP1-2506-457-6

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	143	NR	620	358	NR	750	9	NR	880	0	NR
365	0	NR	495	166	NR	625	357	NR	755	7	NR	885	0	NR
370	0	NR	500	191	NR	630	1000	NR	760	6	NR	890	0	NR
375	0	NR	505	210	NR	635	705	NR	765	5	NR	895	0	NR
380	0	NR	510	223	NR	640	239	NR	770	5	NR	900	0	NR
385	0	NR	515	233	NR	645	226	NR	775	4	NR	905	0	NR
390	1	NR	520	240	NR	650	201	NR	780	3	NR	910	0	NR
395	2	NR	525	246	NR	655	170	NR	785	3	NR	915	0	NR
400	3	NR	530	251	NR	660	145	NR	790	2	NR	920	0	NR
405	4	NR	535	260	NR	665	123	NR	795	2	NR	925	0	NR
410	6	NR	540	267	NR	670	113	NR	800	2	NR	930	0	NR
415	9	NR	545	276	NR	675	93	NR	805	2	NR	935	0	NR
420	16	NR	550	284	NR	680	80	NR	810	1	NR	940	0	NR
425	28	NR	555	294	NR	685	69	NR	815	1	NR	945	0	NR
430	46	NR	560	303	NR	690	59	NR	820	1	NR	950	0	NR
435	75	NR	565	313	NR	695	51	NR	825	1	NR	955	0	NR
440	120	NR	570	319	NR	700	43	NR	830	1	NR	960	0	NR
445	203	NR	575	327	NR	705	37	NR	835	1	NR	965	0	NR
450	311	NR	580	336	NR	710	31	NR	840	1	NR	970	0	NR
455	290	NR	585	344	NR	715	26	NR	845	1	NR	975	0	NR
460	197	NR	590	349	NR	720	22	NR	850	0	NR	980	0	NR
465	163	NR	595	350	NR	725	18	NR	855	0	NR	985	0	NR
470	135	NR	600	355	NR	730	15	NR	860	0	NR	990	0	NR
475	110	NR	605	357	NR	735	13	NR	865	0	NR	995	0	NR
480	108	NR	610	391	NR	740	11	NR	870	0	NR	1000	0	NR
485	123	NR	615	421	NR	745	10	NR	875	0	NR			

REPORT NUMBER: SP1-2506-457-6

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.57

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	143	NR	620	358	NR	750	9	NR	880	0	NR
365	0	NR	495	166	NR	625	357	NR	755	7	NR	885	0	NR
370	0	NR	500	191	NR	630	1000	NR	760	6	NR	890	0	NR
375	0	NR	505	210	NR	635	705	NR	765	5	NR	895	0	NR
380	0	NR	510	223	NR	640	239	NR	770	5	NR	900	0	NR
385	0	NR	515	233	NR	645	226	NR	775	4	NR	905	0	NR
390	1	NR	520	240	NR	650	201	NR	780	3	NR	910	0	NR
395	2	NR	525	246	NR	655	170	NR	785	3	NR	915	0	NR
400	3	NR	530	251	NR	660	145	NR	790	2	NR	920	0	NR
405	4	NR	535	260	NR	665	123	NR	795	2	NR	925	0	NR
410	6	NR	540	267	NR	670	113	NR	800	2	NR	930	0	NR
415	9	NR	545	276	NR	675	93	NR	805	2	NR	935	0	NR
420	16	NR	550	284	NR	680	80	NR	810	1	NR	940	0	NR
425	28	NR	555	294	NR	685	69	NR	815	1	NR	945	0	NR
430	46	NR	560	303	NR	690	59	NR	820	1	NR	950	0	NR
435	75	NR	565	313	NR	695	51	NR	825	1	NR	955	0	NR
440	120	NR	570	319	NR	700	43	NR	830	1	NR	960	0	NR
445	203	NR	575	327	NR	705	37	NR	835	1	NR	965	0	NR
450	311	NR	580	336	NR	710	31	NR	840	1	NR	970	0	NR
455	290	NR	585	344	NR	715	26	NR	845	1	NR	975	0	NR
460	197	NR	590	349	NR	720	22	NR	850	0	NR	980	0	NR
465	163	NR	595	350	NR	725	18	NR	855	0	NR	985	0	NR
470	135	NR	600	355	NR	730	15	NR	860	0	NR	990	0	NR
475	110	NR	605	357	NR	735	13	NR	865	0	NR	995	0	NR
480	108	NR	610	391	NR	740	11	NR	870	0	NR	1000	0	NR
485	123	NR	615	421	NR	745	10	NR	875	0	NR			

REPORT NUMBER: SP1-2506-457-6

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 3.17

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	143	NR	620	358	NR	750	9	NR	880	0	NR
365	0	NR	495	166	NR	625	357	NR	755	7	NR	885	0	NR
370	0	NR	500	191	NR	630	1000	NR	760	6	NR	890	0	NR
375	0	NR	505	210	NR	635	705	NR	765	5	NR	895	0	NR
380	0	NR	510	223	NR	640	239	NR	770	5	NR	900	0	NR
385	0	NR	515	233	NR	645	226	NR	775	4	NR	905	0	NR
390	1	NR	520	240	NR	650	201	NR	780	3	NR	910	0	NR
395	2	NR	525	246	NR	655	170	NR	785	3	NR	915	0	NR
400	3	NR	530	251	NR	660	145	NR	790	2	NR	920	0	NR
405	4	NR	535	260	NR	665	123	NR	795	2	NR	925	0	NR
410	6	NR	540	267	NR	670	113	NR	800	2	NR	930	0	NR
415	9	NR	545	276	NR	675	93	NR	805	2	NR	935	0	NR
420	16	NR	550	284	NR	680	80	NR	810	1	NR	940	0	NR
425	28	NR	555	294	NR	685	69	NR	815	1	NR	945	0	NR
430	46	NR	560	303	NR	690	59	NR	820	1	NR	950	0	NR
435	75	NR	565	313	NR	695	51	NR	825	1	NR	955	0	NR
440	120	NR	570	319	NR	700	43	NR	830	1	NR	960	0	NR
445	203	NR	575	327	NR	705	37	NR	835	1	NR	965	0	NR
450	311	NR	580	336	NR	710	31	NR	840	1	NR	970	0	NR
455	290	NR	585	344	NR	715	26	NR	845	1	NR	975	0	NR
460	197	NR	590	349	NR	720	22	NR	850	0	NR	980	0	NR
465	163	NR	595	350	NR	725	18	NR	855	0	NR	985	0	NR
470	135	NR	600	355	NR	730	15	NR	860	0	NR	990	0	NR
475	110	NR	605	357	NR	735	13	NR	865	0	NR	995	0	NR
480	108	NR	610	391	NR	740	11	NR	870	0	NR	1000	0	NR
485	123	NR	615	421	NR	745	10	NR	875	0	NR			

Summary

$R_f = 91.4$
 $R_g = 100.2$
 $CIE R_a = 93.9$
 $R_9 = 60.5$



Color Vector Graphics




Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 93	CES51 = 98	CES76 = 88
CES02 = 63	CES27 = 93	CES52 = 98	CES77 = 87
CES03 = 31	CES28 = 96	CES53 = 97	CES78 = 85
CES04 = 70	CES29 = 95	CES54 = 95	CES79 = 91
CES05 = 50	CES30 = 96	CES55 = 94	CES80 = 92
CES06 = 51	CES31 = 95	CES56 = 96	CES81 = 75
CES07 = 43	CES32 = 87	CES57 = 95	CES82 = 96
CES08 = 42	CES33 = 97	CES58 = 96	CES83 = 94
CES09 = 29	CES34 = 94	CES59 = 98	CES84 = 95
CES10 = 75	CES35 = 96	CES60 = 94	CES85 = 80
CES11 = 58	CES36 = 84	CES61 = 93	CES86 = 79
CES12 = 64	CES37 = 95	CES62 = 89	CES87 = 91
CES13 = 44	CES38 = 91	CES63 = 94	CES88 = 97
CES14 = 74	CES39 = 99	CES64 = 92	CES89 = 83
CES15 = 72	CES40 = 97	CES65 = 90	CES90 = 98
CES16 = 48	CES41 = 97	CES66 = 90	CES91 = 77
CES17 = 49	CES42 = 93	CES67 = 89	CES92 = 77
CES18 = 56	CES43 = 92	CES68 = 89	CES93 = 86
CES19 = 71	CES44 = 99	CES69 = 91	CES94 = 74
CES20 = 67	CES45 = 96	CES70 = 88	CES95 = 84
CES21 = 86	CES46 = 96	CES71 = 84	CES96 = 92
CES22 = 78	CES47 = 91	CES72 = 94	CES97 = 95
CES23 = 91	CES48 = 94	CES73 = 83	CES98 = 94
CES24 = 90	CES49 = 94	CES74 = 91	CES99 = 92
CES25 = 71	CES50 = 98	CES75 = 86	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)