

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: METALUX

Report Number: P284659

Luminaire Tested: **4SNLED-LD5-35SL-SLW-UNV-L935-CD1-U**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P284659
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P#)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: METALUX
Catalog Number: 4SNLED-LD5-35SL-SLW-UNV-L935-CD1-U
Description: 4FT LINEAR SNLED LED FIXTURE
SQUARE FROSTED LENS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2935.0 lumens
Efficiency: N/A
Efficacy: 94.7 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.56 / 1.59
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.12')
CIE Type: Semi-Direct


Input Watts (W): 31
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P284659

CATALOG NUMBER: 4SNLED-LD5-35SL-SLW-UNV-L935-CD1-U

Luminous Intensity Polar Plot





TEST NUMBER: P284659

CATALOG NUMBER: 4SNLED-LD5-35SL-SLW-UNV-L935-CD1-U

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	113	113	113	113	107	107	107	107	97	97	97	88	88	88	79	79	79	75		
1	100	94	89	84	95	89	84	80	80	76	73	72	69	66	64	62	60	56		
2	90	80	72	66	85	76	69	63	68	63	58	61	57	53	55	51	48	44		
3	81	69	60	53	76	66	58	51	59	53	47	53	48	43	47	43	39	36		
4	74	61	51	44	69	58	49	43	52	45	39	47	41	36	42	37	33	30		
5	67	54	44	37	63	51	43	36	46	39	33	42	35	31	37	32	28	25		
6	62	48	39	32	58	46	37	31	41	34	29	37	31	27	34	28	24	22		
7	57	43	34	28	54	41	33	27	37	30	25	34	28	23	30	25	21	19		
8	53	39	31	25	50	37	29	24	34	27	22	31	25	21	28	23	19	17		
9	49	36	27	22	47	34	26	21	31	24	20	28	23	18	26	21	17	15		
10	46	33	25	20	44	31	24	19	29	22	18	26	21	16	24	19	15	13		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4120	4120	4120
5°	4151	4070	4040
10°	4131	4035	4017
15°	4103	4013	4027
20°	4064	3994	4034
25°	4025	3980	4041
30°	3970	3968	4062
35°	3908	3954	4089
40°	3850	3951	4116
45°	3777	3942	4149
50°	3788	3933	4182
55°	3720	3933	4232
60°	3585	3936	4289
65°	3385	3940	4369
70°	3166	3970	4492
75°	2779	4062	4674
80°	2348	4256	4974
85°	1742	4653	5414



TEST NUMBER: P284659

CATALOG NUMBER: 4SNLED-LD5-35SL-SLW-UNV-L935-CD1-U

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.0	1.7
10°-20°	145.2	4.9
20°-30°	230.8	7.9
30°-40°	296.2	10.1
40°-50°	334.4	11.4
50°-60°	341.3	11.6
60°-70°	316.2	10.8
70°-80°	267.7	9.1
80°-90°	213.6	7.3
90°-100°	181.4	6.2
100°-110°	161.6	5.5
110°-120°	137.7	4.7
120°-130°	109.3	3.7
130°-140°	77.6	2.6
140°-150°	46.3	1.6
150°-160°	21.6	0.7
160°-170°	5.1	0.2
170°-180°	0.0	0.0
0°-30°	424.9	14.5
0°-40°	721.1	24.6
0°-60°	1396.8	47.6
0°-90°	2194.3	74.8
90°-120°	480.7	16.4
90°-150°	714.0	24.3
90°-180°	741.0	25.2
0°-180°	2935.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	510	510	510	510	510	
5°	513	509	514	514	514	49
15°	494	499	517	526	530	139
25°	458	473	506	524	532	211
35°	405	435	482	511	524	253
45°	341	387	444	483	499	265
55°	276	322	394	442	461	242
65°	189	252	333	390	412	187
75°	99	176	270	336	359	106
85°	26	113	215	285	309	28
90°	1	92	192	262	286	2
95°	0	87	186	254	278	0
105°	0	80	170	234	257	0
115°	0	74	154	210	231	0
125°	0	64	137	186	203	0
135°	0	48	110	156	171	0
145°	0	31	77	117	134	0
155°	1	19	48	72	89	0
165°	1	10	21	30	42	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0



TEST NUMBER: P284659

CATALOG NUMBER: 4SNLED-LD5-35SL-SLW-UNV-L935-CD1-U

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	509.8	509.8	509.8	509.8	509.8
2.5°	514.4	509.0	511.8	511.1	508.3
5°	513.1	509.0	514.4	514.4	514.4
7.5°	510.3	507.5	515.2	517.9	518.7
10°	506.2	506.2	516.6	520.7	522.0
12.5°	500.6	502.7	516.6	522.8	526.1
15°	494.5	498.6	516.6	526.1	529.7
17.5°	486.9	493.7	515.2	526.9	531.7
20°	477.9	488.4	513.1	526.9	533.2
22.5°	468.3	481.5	510.3	525.6	533.2
25°	458.0	473.1	506.2	524.1	532.5
27.5°	445.5	464.9	501.4	522.0	531.7
30°	433.1	455.2	495.8	519.2	529.7
32.5°	419.3	444.8	488.9	515.2	526.9
35°	404.8	434.6	481.5	511.1	523.5
37.5°	390.3	422.1	473.8	505.5	519.2
40°	374.5	409.6	464.9	498.6	513.1
42.5°	362.7	396.6	455.2	491.7	507.0
45°	340.8	386.9	444.1	482.8	499.3
47.5°	323.5	368.3	433.1	473.8	491.0
50°	312.5	353.0	420.0	463.4	481.5
52.5°	286.2	342.8	407.6	453.2	472.3
55°	275.8	322.2	393.8	442.0	461.4
57.5°	247.5	307.6	380.0	429.7	449.6
60°	233.8	287.5	364.8	417.3	437.9
62.5°	212.4	270.4	349.7	403.5	424.9
65°	188.9	251.8	333.1	390.3	412.4
67.5°	166.9	233.2	317.3	376.5	399.9
70°	145.5	213.8	300.8	362.7	386.2
72.5°	120.6	194.5	284.7	349.7	373.1
75°	99.4	175.9	269.7	335.9	359.4
77.5°	78.5	158.0	255.2	323.5	346.9
80°	59.4	140.7	240.6	310.4	334.4
82.5°	41.3	126.2	227.6	298.0	321.4
85°	25.5	113.2	215.1	284.7	308.9
87.5°	11.7	101.4	202.7	272.5	297.2
90°	1.3	92.5	192.4	262.0	286.2
92.5°	0.7	89.7	188.3	257.2	280.7
95°	0.0	86.9	186.3	254.4	277.9
97.5°	0.0	84.1	181.5	250.3	274.5
100°	0.0	82.8	177.9	244.2	267.6
102.5°	0.0	80.8	173.8	238.6	262.0
105°	0.0	80.0	169.7	233.8	256.6
107.5°	0.0	78.5	165.5	227.6	250.3
110°	0.0	77.2	162.1	222.0	244.2



TEST NUMBER: P284659

CATALOG NUMBER: 4SNLED-LD5-35SL-SLW-UNV-L935-CD1-U

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	0.0	75.9	158.6	216.6	237.8
115°	0.0	74.4	154.5	210.3	231.0
117.5°	0.0	72.4	150.4	204.2	224.8
120°	0.0	69.6	146.3	198.6	217.9
122.5°	0.0	66.8	142.0	191.7	210.3
125°	0.0	64.2	137.2	185.6	203.4
127.5°	0.0	59.9	131.8	178.7	195.2
130°	0.0	55.8	124.9	171.8	187.6
132.5°	0.7	51.7	118.0	164.1	180.0
135°	0.0	47.6	110.4	156.5	171.0
137.5°	0.0	44.1	102.0	148.3	162.1
140°	0.0	40.0	93.8	138.7	153.2
142.5°	0.0	35.2	85.6	128.2	143.5
145°	0.0	31.1	77.2	117.2	133.8
147.5°	0.7	27.5	69.6	105.5	123.4
150°	0.7	24.8	62.2	93.8	111.7
152.5°	0.7	22.1	54.5	82.8	99.9
155°	0.7	19.4	47.6	71.7	89.0
157.5°	0.7	16.6	40.0	60.7	77.2
160°	0.7	14.5	33.1	51.0	66.3
162.5°	0.7	12.5	27.0	40.0	54.5
165°	0.7	10.4	21.4	29.6	42.1
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)