

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: METALUX

Report Number: P709783

Luminaire Tested: **8AWS-L3C3-SQR-UNV-5000K-HI**

Issue Date: 9/26/2023



Test Information

Test Method: LM-79-08
Report Number: P709783
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2307-090-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/26/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: METALUX
Catalog Number: 8AWS-L3C3-SQR-UNV-5000K-HI
Description: 8foot, Adapt Surface Wrap with, SQR lens and HI lumen setting, 5000K, 80CRI

Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 12227.0 lumens
Efficiency: N/A
Efficacy: 140.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.4
Luminous Opening: Rectangular w/ Sides (W: 0.46' x L: 7.42' x H: 0.12')
CIE Type: Semi-Direct

Input Watts (W): 87
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P709783
CATALOG NUMBER: 8AWS-L3C3-SQR-UNV-5000K-HI

Luminous Intensity Polar Plot





TEST NUMBER: P709783

CATALOG NUMBER: 8AWS-L3C3-SQR-UNV-5000K-HI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	116	116	116	116	112	112	112	112	105	105	105	98	98	98	92	92	92	89																			
1	105	100	95	91	101	96	92	88	90	87	83	84	82	79	79	77	75	72																			
2	95	86	79	73	91	83	77	71	78	73	68	73	69	65	69	65	62	59																			
3	86	75	67	60	83	73	65	59	68	62	56	64	59	54	60	56	52	49																			
4	79	67	57	51	76	64	56	50	61	53	48	57	51	46	54	48	44	42																			
5	72	59	50	43	69	57	49	43	54	47	41	51	45	40	48	43	38	36																			
6	67	53	44	38	64	52	43	37	49	41	36	46	40	35	43	38	34	31																			
7	62	48	39	33	59	47	38	33	44	37	32	42	35	31	40	34	30	27																			
8	57	44	35	29	55	43	35	29	40	33	28	38	32	27	36	31	27	24																			
9	54	40	32	26	52	39	31	26	37	30	25	35	29	25	34	28	24	22																			
10	50	37	29	24	48	36	29	23	34	28	23	33	27	22	31	26	22	20																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11049	11049	11049
5°	10934	10916	10821
10°	10926	10729	10635
15°	10748	10499	10498
20°	10608	10241	10282
25°	10415	10067	10107
30°	10262	9744	9756
35°	10035	9517	9514
40°	9815	9254	9268
45°	9478	8984	9008
50°	9247	8678	8821
55°	8924	8350	8546
60°	8521	8013	8217
65°	8028	7591	7893
70°	7428	7052	7439
75°	6546	6473	7034
80°	5079	5829	6545
85°	3069	5407	6293



TEST NUMBER: P709783

CATALOG NUMBER: 8AWS-L3C3-SQR-UNV-5000K-HI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	332.4	2.7
10°-20°	953.2	7.8
20°-30°	1445.6	11.8
30°-40°	1749.7	14.3
40°-50°	1842.0	15.1
50°-60°	1715.8	14.0
60°-70°	1399.5	11.4
70°-80°	943.6	7.7
80°-90°	507.1	4.1
90°-100°	351.5	2.9
100°-110°	300.8	2.5
110°-120°	245.4	2.0
120°-130°	186.6	1.5
130°-140°	129.2	1.1
140°-150°	77.0	0.6
150°-160°	35.9	0.3
160°-170°	10.6	0.1
170°-180°	1.1	0.0
0°-30°	2731.2	22.3
0°-40°	4480.9	36.6
0°-60°	8038.7	65.7
0°-90°	10888.9	89.1
90°-120°	897.8	7.3
90°-150°	1290.6	10.6
90°-180°	1338.0	10.9
0°-180°	12227.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3504	3504	3504	3504	3504	
5°	3459	3496	3507	3507	3496	329
15°	3306	3343	3384	3414	3440	935
25°	3016	3075	3157	3187	3258	1391
35°	2636	2699	2811	2893	2923	1648
45°	2160	2264	2409	2513	2547	1675
55°	1661	1780	1944	2066	2133	1485
65°	1113	1251	1445	1586	1649	1107
75°	570	719	920	1069	1139	602
85°	100	276	484	637	692	126
90°	4	175	380	529	584	6
95°	0	160	357	495	547	0
105°	0	142	313	439	488	0
115°	4	123	272	380	421	4
125°	4	100	231	320	354	3
135°	4	78	186	257	287	3
145°	7	52	134	190	212	4
155°	7	30	78	123	134	3
165°	7	15	34	52	63	2
175°	7	7	7	7	7	1
180°	4	4	4	4	4	



TEST NUMBER: P709783

CATALOG NUMBER: 8AWS-L3C3-SQR-UNV-5000K-HI

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3503.5	3503.5	3503.5	3503.5	3503.5
2.5°	3492.4	3496.1	3507.3	3518.4	3499.8
5°	3458.9	3496.1	3507.3	3507.3	3496.1
7.5°	3432.8	3466.3	3492.4	3484.9	3488.7
10°	3421.6	3440.3	3466.3	3484.9	3473.8
12.5°	3380.7	3391.9	3414.2	3444.0	3466.3
15°	3306.2	3343.4	3384.4	3414.2	3440.3
17.5°	3250.4	3283.9	3336.0	3362.1	3399.3
20°	3179.6	3216.9	3269.0	3324.8	3354.6
22.5°	3112.6	3146.1	3216.9	3254.1	3317.4
25°	3015.8	3075.4	3157.3	3187.1	3257.8
27.5°	2922.7	2989.7	3060.5	3142.4	3172.2
30°	2844.5	2892.9	2978.6	3049.3	3082.8
32.5°	2736.6	2803.6	2892.9	2978.6	3027.0
35°	2636.0	2699.3	2811.0	2892.9	2922.7
37.5°	2524.3	2595.1	2706.8	2803.6	2859.4
40°	2416.4	2494.6	2617.4	2710.5	2744.0
42.5°	2300.9	2382.9	2513.2	2621.1	2650.9
45°	2159.5	2263.7	2408.9	2513.2	2546.7
47.5°	2051.5	2148.3	2286.1	2408.9	2457.3
50°	1921.2	2029.2	2181.8	2293.5	2356.8
52.5°	1802.0	1902.6	2058.9	2166.9	2241.4
55°	1660.6	1779.7	1943.5	2066.4	2133.4
57.5°	1522.8	1645.7	1816.9	1943.5	2010.5
60°	1388.8	1515.3	1701.5	1828.1	1891.4
62.5°	1258.4	1392.5	1560.0	1712.7	1764.8
65°	1113.2	1251.0	1444.6	1586.1	1649.4
67.5°	986.7	1109.5	1318.0	1448.3	1519.1
70°	841.4	986.7	1176.5	1325.5	1385.0
72.5°	700.0	852.6	1049.9	1202.6	1262.2
75°	569.7	718.6	919.6	1068.6	1139.3
77.5°	439.3	592.0	796.8	949.4	1009.0
80°	305.3	472.8	677.6	830.3	893.6
82.5°	193.6	364.9	577.1	722.3	781.9
85°	100.5	275.5	484.0	636.7	692.5
87.5°	33.5	208.5	417.0	565.9	621.8
90°	3.7	175.0	379.8	528.7	584.5
92.5°	0.0	167.5	368.6	510.1	562.2
95°	0.0	160.1	357.4	495.2	547.3
97.5°	0.0	156.4	342.5	480.3	532.4
100°	0.0	148.9	335.1	469.1	517.5
102.5°	0.0	145.2	323.9	454.2	502.6
105°	0.0	141.5	312.8	439.3	487.7



TEST NUMBER: P709783

CATALOG NUMBER: 8AWS-L3C3-SQR-UNV-5000K-HI

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	3.7	126.6	283.0	398.4	439.3
115°	3.7	122.9	271.8	379.8	420.7
117.5°	3.7	115.4	264.3	364.9	402.1
120°	3.7	111.7	253.2	353.7	387.2
122.5°	3.7	108.0	242.0	335.1	372.3
125°	3.7	100.5	230.8	320.2	353.7
127.5°	3.7	93.1	219.7	305.3	335.1
130°	3.7	89.4	208.5	286.7	320.2
132.5°	3.7	81.9	197.3	275.5	301.6
135°	3.7	78.2	186.2	256.9	286.7
137.5°	3.7	70.7	175.0	242.0	268.1
140°	3.7	63.3	160.1	227.1	249.5
142.5°	3.7	59.6	148.9	208.5	230.8
145°	7.4	52.1	134.0	189.9	212.2
147.5°	7.4	48.4	119.1	175.0	193.6
150°	7.4	41.0	104.3	156.4	175.0
152.5°	7.4	37.2	93.1	137.8	156.4
155°	7.4	29.8	78.2	122.9	134.0
157.5°	7.4	26.1	67.0	104.3	119.1
160°	7.4	22.3	55.8	89.4	100.5
162.5°	7.4	18.6	44.7	70.7	81.9
165°	7.4	14.9	33.5	52.1	63.3
167.5°	7.4	11.2	26.1	37.2	48.4
170°	7.4	11.2	18.6	26.1	37.2
172.5°	7.4	7.4	11.2	14.9	22.3
175°	7.4	7.4	7.4	7.4	7.4
177.5°	7.4	7.4	3.7	3.7	0.0
180°	3.7	3.7	3.7	3.7	3.7



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180° - - 45°-225° - - - - 90°-270°







107.5°	0.0	134.0	305.3	424.4	469.1
110°	3.7	130.3	294.1	409.6	454.2



(END OF REPORT)